

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333007

Luminaire Tested: **SA4XXRDIP-C1195D1035U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P333007
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D1035U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8402.7 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333007
CATALOG NUMBER: SA4XXRDIP-C1195D1035U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333007

CATALOG NUMBER: SA4XXRDIP-C1195D1035U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	95	92	88	93	89	86	83	77	75	73	66	64	63	56	55	54	49
2	91	84	78	73	85	78	73	68	68	64	61	59	56	53	50	48	46	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	42	39	35
4	76	66	58	52	71	61	54	49	54	48	44	46	42	39	40	37	34	31
5	70	59	51	45	65	55	48	42	48	42	38	42	37	34	36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	38	31	26	33	28	24	29	25	21	26	22	19	17
10	49	37	29	24	45	35	28	23	31	25	21	27	23	19	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16835	16835	16835
5°	16874	16667	16771
10°	16768	16467	16467
15°	16575	16121	16002
20°	16311	15667	15378
25°	15973	15134	14750
30°	15645	14573	13962
35°	15281	13991	13172
40°	14842	13328	12318
45°	14439	12670	11449
50°	13978	11912	10528
55°	13485	11125	9529
60°	12943	10261	8507
65°	12445	9181	7503
70°	11722	7990	6371
75°	10808	6625	5181
80°	9428	5049	4751
85°	7984	4585	4289



TEST NUMBER: P333007

CATALOG NUMBER: SA4XXRDIP-C1195D1035U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.9	2.3
10°-20°	546.3	6.5
20°-30°	788.8	9.4
30°-40°	894.2	10.6
40°-50°	863.5	10.3
50°-60°	718.0	8.5
60°-70°	495.8	5.9
70°-80°	251.3	3.0
80°-90°	68.3	0.8
90°-100°	85.1	1.0
100°-110°	252.2	3.0
110°-120°	428.0	5.1
120°-130°	564.3	6.7
130°-140°	633.8	7.5
140°-150°	622.8	7.4
150°-160°	523.8	6.2
160°-170°	348.5	4.1
170°-180°	122.0	1.5
0°-30°	1531.0	18.2
0°-40°	2425.2	28.9
0°-60°	4006.7	47.7
0°-90°	4822.1	57.4
90°-120°	765.3	9.1
90°-150°	2586.3	30.8
90°-180°	3581.0	42.6
0°-180°	8402.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2057	2072	2070	197
15°	1983	1967	1929	1925	1915	559
25°	1793	1762	1699	1672	1656	826
35°	1550	1498	1420	1367	1336	968
45°	1265	1204	1110	1034	1003	975
55°	958	892	790	710	677	857
65°	652	581	481	415	393	643
75°	346	287	212	177	166	366
85°	86	56	50	46	46	97
90°	3	14	22	28	30	8
95°	60	69	76	79	79	67
105°	233	234	238	241	244	247
115°	435	435	433	432	431	429
125°	634	634	633	631	629	565
135°	818	823	824	821	818	632
145°	993	997	998	997	994	621
155°	1138	1138	1137	1140	1137	523
165°	1239	1236	1234	1239	1236	349
175°	1289	1284	1283	1289	1283	122
180°	1291	1291	1291	1291	1291	



TEST NUMBER: P333007

CATALOG NUMBER: SA4XXRDIP-C1195D1035U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2090.5	2089.4	2088.3	2087.1	2086.0	2083.9	2080.8	2077.6	2074.5	2071.4	2074.5
5°	2082.2	2080.8	2079.4	2078.0	2076.6	2073.7	2069.5	2065.2	2061.0	2056.7	2060.2
7.5°	2063.4	2061.9	2060.4	2058.9	2057.4	2053.9	2048.4	2042.9	2037.3	2031.8	2034.1
10°	2045.5	2043.7	2042.0	2040.2	2038.4	2034.3	2028.0	2021.6	2015.2	2008.8	2010.2
12.5°	2022.5	2020.5	2018.4	2016.3	2014.3	2009.5	2002.0	1994.5	1986.9	1979.4	1980.3
15°	1983.2	1980.0	1976.9	1973.7	1970.5	1964.4	1955.6	1946.7	1937.8	1928.9	1928.2
17.5°	1935.7	1931.0	1926.4	1921.8	1917.2	1909.6	1898.9	1888.3	1877.6	1867.0	1865.0
20°	1898.6	1894.0	1889.4	1884.8	1880.2	1871.8	1859.8	1847.7	1835.6	1823.6	1820.7
22.5°	1857.7	1852.6	1847.4	1842.2	1837.0	1828.0	1815.0	1802.1	1789.2	1776.3	1772.0
25°	1793.2	1786.8	1780.4	1774.1	1767.7	1757.2	1742.7	1728.1	1713.6	1699.0	1693.0
27.5°	1725.5	1717.5	1709.5	1701.5	1693.4	1681.7	1666.1	1650.6	1635.0	1619.5	1612.0
30°	1678.3	1669.4	1660.5	1651.6	1642.8	1630.0	1613.3	1596.6	1580.0	1563.3	1554.4
32.5°	1628.4	1618.4	1608.4	1598.4	1588.4	1574.8	1557.5	1540.3	1523.0	1505.8	1495.5
35°	1550.5	1539.1	1527.8	1516.4	1505.1	1490.5	1472.8	1455.1	1437.3	1419.6	1407.5
37.5°	1467.2	1455.4	1443.7	1432.0	1420.3	1404.6	1385.0	1365.3	1345.7	1326.0	1312.5
40°	1408.4	1396.7	1385.0	1373.3	1361.5	1345.6	1325.4	1305.1	1284.9	1264.7	1249.8
42.5°	1352.2	1339.9	1327.6	1315.3	1303.1	1286.4	1265.3	1244.2	1223.2	1202.1	1186.9
45°	1264.7	1251.5	1238.4	1225.3	1212.2	1194.9	1173.7	1152.4	1131.1	1109.8	1092.4
47.5°	1174.3	1160.7	1147.2	1133.6	1120.1	1102.2	1080.1	1057.9	1035.8	1013.7	995.6
50°	1113.0	1099.1	1085.3	1071.5	1057.6	1039.3	1016.6	993.9	971.2	948.5	930.8
52.5°	1050.4	1036.8	1023.3	1009.7	996.2	977.7	954.5	931.2	907.9	884.6	866.6
55°	958.1	943.9	929.7	915.5	901.3	882.7	859.6	836.6	813.5	790.4	772.0
57.5°	866.7	852.0	837.2	822.5	807.7	789.0	766.3	743.5	720.8	698.1	679.4
60°	801.6	787.4	773.2	759.0	744.8	726.4	703.7	681.0	658.2	635.5	617.1
62.5°	742.8	728.1	713.3	698.6	683.8	664.8	641.5	618.2	594.9	571.7	554.6
65°	651.5	636.2	621.0	605.7	590.5	571.5	548.8	526.1	503.4	480.6	465.4
67.5°	556.6	542.0	527.4	512.8	498.2	480.3	459.2	438.2	417.1	396.0	382.9
70°	496.6	481.7	466.8	451.9	437.0	419.4	399.2	379.0	358.8	338.5	326.8
72.5°	432.7	419.3	405.8	392.3	378.8	362.5	343.4	324.3	305.2	286.1	276.1
75°	346.5	333.4	320.2	307.1	294.0	279.1	262.4	245.7	229.1	212.4	204.2
77.5°	259.0	247.9	236.7	225.6	214.4	202.1	188.6	175.2	161.7	148.2	143.4
80°	202.8	192.5	182.2	171.9	161.6	151.2	140.5	129.9	119.2	108.6	107.5
82.5°	154.3	144.8	135.4	125.9	116.5	108.7	102.6	96.5	90.4	84.3	83.5
85°	86.2	79.1	72.0	64.9	57.8	53.8	52.7	51.6	50.6	49.5	48.8
87.5°	30.0	28.2	26.4	24.6	22.8	22.0	22.1	22.1	22.2	22.3	22.3
90°	3.0	5.4	7.9	10.3	12.8	14.9	16.6	18.4	20.2	22.0	23.3
92.5°	21.4	24.2	26.9	29.7	32.5	34.6	35.8	37.0	38.3	39.5	40.3
95°	59.9	61.9	63.9	65.9	67.9	69.6	71.2	72.8	74.3	75.9	76.5
97.5°	104.6	106.2	107.8	109.4	111.0	112.7	114.5	116.3	118.2	120.0	120.8
100°	139.7	140.6	141.5	142.4	143.3	144.7	146.7	148.7	150.7	152.7	153.2
102.5°	176.5	176.8	177.2	177.5	177.9	179.0	180.8	182.6	184.4	186.3	186.9
105°	232.6	232.8	233.0	233.2	233.5	234.0	234.9	235.8	236.7	237.6	238.2
107.5°	291.5	291.7	292.0	292.3	292.5	292.7	292.9	293.0	293.1	293.3	293.9
110°	331.4	331.8	332.3	332.7	333.2	333.3	333.0	332.8	332.6	332.4	331.9



TEST NUMBER: P333007

CATALOG NUMBER: SA4XXRDIP-C1195D1035U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	372.9	373.0	373.1	373.2	373.3	373.1	372.7	372.3	371.9	371.5	371.4
115°	435.2	435.2	435.2	435.2	435.2	435.0	434.5	434.1	433.6	433.2	433.0
117.5°	493.9	494.1	494.2	494.4	494.6	494.5	494.2	493.9	493.6	493.3	492.5
120°	533.0	533.9	534.8	535.7	536.6	536.7	536.0	535.3	534.7	534.0	532.9
122.5°	573.7	574.1	574.4	574.8	575.1	575.2	574.9	574.5	574.2	573.9	573.2
125°	633.8	633.8	633.8	633.8	633.8	633.7	633.5	633.3	633.0	632.8	632.4
127.5°	688.3	689.0	689.6	690.3	691.0	691.1	690.8	690.4	690.1	689.7	689.3
130°	726.6	727.3	728.0	728.6	729.3	729.6	729.6	729.6	729.6	729.6	729.2
132.5°	765.8	766.3	766.7	767.2	767.7	767.9	767.7	767.5	767.3	767.2	766.7
135°	817.5	818.8	820.1	821.5	822.8	823.5	823.5	823.5	823.5	823.5	823.0
137.5°	873.8	874.4	875.0	875.6	876.3	876.7	877.1	877.5	877.8	878.2	877.6
140°	911.3	911.7	912.2	912.6	913.1	913.3	913.3	913.3	913.3	913.3	913.1
142.5°	945.6	946.1	946.5	947.0	947.4	947.5	947.4	947.2	947.0	946.8	946.8
145°	993.1	994.0	994.9	995.8	996.7	997.2	997.5	997.7	997.9	998.1	997.9
147.5°	1040.3	1041.3	1042.4	1043.5	1044.5	1045.0	1044.8	1044.6	1044.4	1044.3	1044.1
150°	1069.0	1069.9	1070.8	1071.7	1072.6	1073.0	1073.0	1073.0	1073.0	1073.0	1073.0
152.5°	1096.2	1096.7	1097.2	1097.8	1098.3	1098.6	1098.8	1099.0	1099.2	1099.3	1099.9
155°	1137.9	1137.9	1137.9	1137.9	1137.9	1137.8	1137.5	1137.3	1137.1	1136.9	1137.8
157.5°	1173.0	1172.6	1172.2	1171.8	1171.4	1171.2	1171.1	1171.1	1171.1	1171.0	1171.7
160°	1193.8	1193.5	1193.3	1193.1	1192.9	1192.7	1192.4	1192.2	1192.0	1191.8	1192.4
162.5°	1212.9	1212.4	1211.8	1211.2	1210.6	1210.2	1210.0	1209.8	1209.6	1209.3	1210.5
165°	1238.7	1238.0	1237.4	1236.7	1236.0	1235.5	1235.0	1234.6	1234.1	1233.7	1235.0
167.5°	1258.5	1257.5	1256.6	1255.7	1254.7	1254.3	1254.3	1254.4	1254.4	1254.5	1255.8
170°	1269.6	1268.5	1267.4	1266.3	1265.2	1264.7	1265.0	1265.2	1265.4	1265.6	1267.0
172.5°	1277.6	1276.7	1275.8	1274.8	1273.9	1273.4	1273.5	1273.5	1273.6	1273.6	1275.1
175°	1288.6	1287.5	1286.4	1285.3	1284.2	1283.5	1283.3	1283.0	1282.8	1282.6	1284.2
177.5°	1292.2	1291.3	1290.4	1289.5	1288.6	1288.2	1288.2	1288.2	1288.2	1288.2	1289.4
180°	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6



TEST NUMBER: P333007

CATALOG NUMBER: SA4XXRDIP-C1195D1035U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2077.6	2080.8	2083.9	2085.3	2085.0	2084.7	2084.4	2084.2
5°	2063.8	2067.3	2070.9	2072.3	2071.6	2070.9	2070.2	2069.5
7.5°	2036.3	2038.6	2040.9	2041.4	2040.3	2039.2	2038.0	2036.9
10°	2011.6	2013.0	2014.5	2014.5	2013.0	2011.6	2010.2	2008.8
12.5°	1981.1	1982.0	1982.8	1982.2	1980.3	1978.3	1976.3	1974.3
15°	1927.5	1926.8	1926.1	1924.5	1922.0	1919.5	1917.1	1914.6
17.5°	1863.0	1861.0	1859.0	1856.2	1852.4	1848.6	1844.9	1841.1
20°	1817.9	1815.0	1812.2	1808.5	1803.9	1799.3	1794.6	1790.0
22.5°	1767.8	1763.5	1759.3	1755.3	1751.5	1747.7	1744.0	1740.2
25°	1686.9	1680.9	1674.9	1670.1	1666.5	1663.0	1659.4	1655.9
27.5°	1604.6	1597.1	1589.7	1583.4	1578.3	1573.2	1568.1	1563.0
30°	1545.5	1536.7	1527.8	1520.5	1514.8	1509.2	1503.5	1497.8
32.5°	1485.2	1474.9	1464.6	1456.8	1451.4	1446.0	1440.6	1435.2
35°	1395.4	1383.4	1371.3	1362.1	1355.7	1349.3	1342.9	1336.5
37.5°	1299.0	1285.5	1272.1	1262.1	1255.7	1249.3	1243.0	1236.6
40°	1234.9	1220.0	1205.1	1194.4	1188.0	1181.6	1175.3	1168.9
42.5°	1171.7	1156.5	1141.3	1130.4	1123.7	1117.1	1110.4	1103.7
45°	1075.0	1057.6	1040.2	1028.3	1022.0	1015.6	1009.2	1002.8
47.5°	977.6	959.6	941.6	929.0	922.0	915.0	907.9	900.9
50°	913.0	895.3	877.5	865.3	858.6	851.8	845.1	838.3
52.5°	848.6	830.6	812.5	800.0	793.0	786.0	778.9	771.9
55°	753.5	735.1	716.6	704.0	697.3	690.5	683.8	677.0
57.5°	660.7	641.9	623.2	611.3	606.2	601.0	595.9	590.8
60°	598.6	580.2	561.7	549.7	544.0	538.3	532.6	526.9
62.5°	537.6	520.6	503.5	492.7	488.2	483.7	479.1	474.6
65°	450.1	434.9	419.6	409.8	405.6	401.3	397.1	392.8
67.5°	369.8	356.6	343.5	334.6	329.9	325.2	320.5	315.8
70°	315.1	303.4	291.7	284.1	280.5	277.0	273.4	269.9
72.5°	266.1	256.1	246.1	239.5	236.2	233.0	229.7	226.4
75°	196.1	187.9	179.7	174.6	172.5	170.3	168.2	166.1
77.5°	138.7	133.9	129.2	126.5	125.8	125.2	124.6	123.9
80°	106.5	105.4	104.3	103.6	103.3	102.9	102.6	102.2
82.5°	82.8	82.0	81.2	80.6	80.3	79.9	79.6	79.2
85°	48.1	47.4	46.7	46.3	46.3	46.3	46.3	46.3
87.5°	22.2	22.2	22.2	22.4	22.8	23.1	23.5	23.9
90°	24.6	26.0	27.3	28.2	28.6	29.1	29.5	29.9
92.5°	41.1	41.9	42.7	43.3	43.5	43.8	44.1	44.3
95°	77.2	77.9	78.5	78.9	78.9	78.9	78.9	78.9
97.5°	121.6	122.4	123.2	123.6	123.6	123.6	123.6	123.6
100°	153.6	154.0	154.5	154.7	154.7	154.7	154.7	154.7
102.5°	187.5	188.1	188.7	189.1	189.3	189.5	189.7	189.8
105°	238.9	239.6	240.2	240.9	241.5	242.2	242.9	243.5
107.5°	294.5	295.1	295.7	296.0	296.0	295.9	295.9	295.8
110°	331.5	331.0	330.6	330.7	331.4	332.0	332.7	333.4



TEST NUMBER: P333007

CATALOG NUMBER: SA4XXRDIP-C1195D1035U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	371.3	371.2	371.2	371.2	371.3	371.4	371.6	371.7
115°	432.7	432.5	432.3	432.1	431.9	431.6	431.4	431.2
117.5°	491.8	491.0	490.3	489.7	489.2	488.8	488.3	487.9
120°	531.8	530.7	529.6	529.2	529.7	530.1	530.6	531.0
122.5°	572.4	571.7	570.9	570.1	569.3	568.5	567.7	566.9
125°	631.9	631.5	631.0	630.6	630.2	629.7	629.3	628.8
127.5°	688.8	688.4	687.9	687.5	687.2	686.8	686.5	686.1
130°	728.8	728.3	727.9	727.2	726.3	725.4	724.5	723.6
132.5°	766.3	765.8	765.4	765.0	764.6	764.3	763.9	763.6
135°	822.6	822.1	821.7	821.1	820.5	819.8	819.1	818.5
137.5°	877.0	876.4	875.9	875.6	875.8	875.9	876.0	876.2
140°	912.9	912.6	912.4	912.2	912.0	911.7	911.5	911.3
142.5°	946.7	946.7	946.7	946.6	946.6	946.5	946.5	946.4
145°	997.7	997.5	997.2	996.8	996.1	995.5	994.8	994.1
147.5°	1043.9	1043.7	1043.5	1043.3	1043.1	1042.9	1042.7	1042.5
150°	1073.0	1073.0	1073.0	1072.9	1072.7	1072.4	1072.2	1072.0
152.5°	1100.4	1100.9	1101.5	1101.5	1100.9	1100.3	1099.7	1099.1
155°	1138.7	1139.5	1140.4	1140.4	1139.5	1138.7	1137.8	1136.9
157.5°	1172.3	1173.0	1173.7	1173.6	1172.9	1172.1	1171.4	1170.6
160°	1193.1	1193.8	1194.4	1194.2	1193.1	1192.0	1190.9	1189.8
162.5°	1211.7	1212.9	1214.1	1214.2	1213.1	1212.0	1210.9	1209.7
165°	1236.4	1237.7	1239.0	1239.2	1238.4	1237.5	1236.6	1235.7
167.5°	1257.1	1258.5	1259.8	1259.8	1258.4	1257.0	1255.6	1254.3
170°	1268.3	1269.6	1271.0	1270.8	1269.3	1267.7	1266.2	1264.6
172.5°	1276.6	1278.1	1279.7	1279.6	1278.1	1276.5	1275.0	1273.4
175°	1285.7	1287.3	1288.8	1288.8	1287.3	1285.7	1284.2	1282.6
177.5°	1290.7	1291.9	1293.2	1293.1	1291.7	1290.2	1288.8	1287.4
180°	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6

(END OF REPORT)