

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332703-927

Luminaire Tested: **SA4XXDIP-C1195D1035U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332703-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D1035U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7324.8 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332703-927

CATALOG NUMBER: SA4XXDIP-C1195D1035U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332703-927

CATALOG NUMBER: SA4XXDIP-C1195D1035U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	95	91	87	92	88	85	81	76	73	71	64	63	61	54	53	51	47				
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33				
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	38	34	32	28				
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28	25				
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24	22				
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	19	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12745	12745	12745
5°	12783	12630	12721
10°	12703	12527	12588
15°	12549	12349	12380
20°	12345	12128	12138
25°	12113	11875	11843
30°	11828	11580	11473
35°	11532	11269	11121
40°	11225	10918	10718
45°	10904	10572	10369
50°	10550	10262	9946
55°	10166	9864	9543
60°	9783	9415	9131
65°	9352	8990	8627
70°	8868	8419	8091
75°	8125	7735	7536
80°	7234	6936	6760
85°	6326	6095	5974



TEST NUMBER: P332703-927

CATALOG NUMBER: SA4XXDIP-C1195D1035U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.7	2.0
10°-20°	418.9	5.7
20°-30°	616.5	8.4
30°-40°	716.7	9.8
40°-50°	716.8	9.8
50°-60°	627.0	8.6
60°-70°	465.6	6.4
70°-80°	264.5	3.6
80°-90°	79.4	1.1
90°-100°	36.2	0.5
100°-110°	230.6	3.1
110°-120°	441.1	6.0
120°-130°	559.9	7.6
130°-140°	599.1	8.2
140°-150°	560.2	7.6
150°-160°	451.8	6.2
160°-170°	291.4	4.0
170°-180°	100.4	1.4
0°-30°	1184.1	16.2
0°-40°	1900.8	26.0
0°-60°	3244.6	44.3
0°-90°	4054.2	55.3
90°-120°	707.8	9.7
90°-150°	2427.0	33.1
90°-180°	3271.0	44.7
0°-180°	7324.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1579	1579	1579	1579	1579	
5°	1577	1572	1558	1571	1570	150
15°	1502	1496	1478	1484	1481	423
25°	1360	1350	1333	1334	1330	625
35°	1170	1161	1144	1135	1128	731
45°	955	946	926	913	908	736
55°	722	718	701	686	678	647
65°	490	483	471	458	452	485
75°	260	254	248	243	242	277
85°	68	68	66	66	64	75
90°	2	11	17	22	24	6
95°	44	18	17	22	23	56
105°	238	243	247	252	225	249
115°	444	447	446	448	448	437
125°	625	628	626	629	630	558
135°	775	774	777	779	780	597
145°	894	896	896	897	898	558
155°	980	980	978	981	979	452
165°	1034	1030	1030	1035	1029	292
175°	1057	1053	1053	1060	1051	101
180°	1057	1057	1057	1057	1057	



TEST NUMBER: P332703-927

CATALOG NUMBER: SA4XXDIP-C1195D1035U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1582.7	1582.1	1581.4	1580.7	1580.0	1578.4	1576.0	1573.5	1571.1	1568.6	1570.8
5°	1577.4	1576.3	1575.2	1574.1	1573.0	1570.8	1567.7	1564.6	1561.5	1558.5	1561.5
7.5°	1562.7	1561.6	1560.5	1559.3	1558.2	1556.0	1552.5	1549.1	1545.7	1542.2	1544.8
10°	1549.6	1548.5	1547.4	1546.2	1545.1	1542.7	1539.1	1535.4	1531.8	1528.1	1530.3
12.5°	1532.4	1531.3	1530.1	1529.0	1527.9	1525.3	1521.5	1517.7	1513.8	1509.9	1512.4
15°	1501.5	1500.4	1499.3	1498.2	1497.0	1494.4	1490.1	1485.9	1481.7	1477.5	1479.2
17.5°	1464.3	1462.9	1461.5	1460.2	1458.7	1456.0	1452.0	1448.0	1444.1	1440.0	1441.1
20°	1437.0	1435.6	1434.2	1432.8	1431.4	1428.5	1424.3	1420.1	1415.9	1411.7	1412.5
22.5°	1407.6	1405.8	1404.0	1402.1	1400.3	1397.2	1393.0	1388.8	1384.6	1380.3	1381.9
25°	1359.9	1357.9	1355.9	1353.9	1351.9	1349.0	1345.0	1341.2	1337.2	1333.2	1333.6
27.5°	1305.2	1303.1	1301.2	1299.1	1297.1	1294.3	1290.6	1287.0	1283.3	1279.6	1279.0
30°	1268.8	1266.5	1264.2	1262.0	1259.8	1256.8	1253.2	1249.5	1245.9	1242.2	1241.1
32.5°	1230.3	1228.3	1226.3	1224.2	1222.2	1219.2	1215.4	1211.5	1207.6	1203.7	1202.4
35°	1170.1	1168.2	1166.2	1164.2	1162.2	1159.3	1155.3	1151.4	1147.5	1143.5	1141.5
37.5°	1106.6	1104.8	1103.0	1101.2	1099.4	1096.4	1092.2	1088.0	1083.7	1079.5	1077.4
40°	1065.1	1062.9	1060.6	1058.4	1056.1	1052.9	1048.7	1044.4	1040.2	1036.0	1033.2
42.5°	1020.6	1019.2	1017.9	1016.5	1015.2	1012.2	1007.5	1002.8	998.1	993.5	990.2
45°	955.1	953.1	951.1	949.1	947.2	944.0	939.4	934.9	930.4	926.0	922.9
47.5°	886.5	885.1	883.8	882.4	881.1	878.4	874.2	870.1	865.9	861.7	858.3
50°	840.0	838.8	837.7	836.5	835.4	832.9	828.9	825.1	821.1	817.1	813.3
52.5°	794.4	793.1	791.7	790.4	789.0	786.2	782.1	777.9	773.8	769.6	766.1
55°	722.3	721.4	720.6	719.8	718.9	716.5	712.6	708.7	704.7	700.8	697.4
57.5°	653.5	652.5	651.6	650.6	649.7	647.2	643.3	639.4	635.6	631.7	628.5
60°	605.9	604.5	603.1	601.7	600.3	597.8	594.1	590.5	586.8	583.1	580.6
62.5°	559.4	558.2	557.0	555.8	554.7	552.2	548.3	544.4	540.5	536.6	534.3
65°	489.6	488.1	486.7	485.3	483.9	481.8	479.0	476.2	473.4	470.6	467.8
67.5°	419.2	418.0	416.6	415.3	414.1	412.0	409.3	406.6	403.9	401.2	398.5
70°	375.7	373.8	371.8	369.8	367.8	365.8	363.5	361.2	358.9	356.7	354.5
72.5°	329.2	327.2	325.2	323.2	321.3	319.4	317.6	315.8	314.0	312.2	310.4
75°	260.5	259.2	257.8	256.4	254.9	253.6	252.2	250.7	249.4	248.0	246.8
77.5°	195.0	194.4	193.8	193.2	192.6	191.6	190.4	189.2	188.0	186.7	186.4
80°	155.6	154.7	153.9	153.0	152.3	151.5	151.0	150.4	149.8	149.2	148.7
82.5°	117.2	116.8	116.4	116.0	115.6	115.3	115.2	115.1	114.9	114.9	114.5
85°	68.3	68.3	68.3	68.3	68.3	68.0	67.5	66.9	66.3	65.8	65.8
87.5°	26.8	26.9	27.1	27.3	27.4	27.6	27.6	27.6	27.7	27.8	28.0
90°	2.4	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5
92.5°	10.0	10.1	10.1	10.3	10.4	11.2	12.5	13.9	15.4	16.8	17.8
95°	43.5	37.5	31.5	25.6	19.6	16.7	16.9	17.0	17.2	17.4	18.5
97.5°	92.4	96.1	99.8	103.5	107.3	99.3	79.7	60.1	40.5	20.9	21.0
100°	129.7	132.8	136.0	139.2	142.4	131.8	107.6	83.3	59.0	34.8	31.8
102.5°	171.4	173.8	176.1	178.4	180.7	180.3	177.1	174.0	170.8	167.6	135.4
105°	238.1	239.1	240.1	241.2	242.2	243.2	244.1	244.9	245.9	246.8	248.3
107.5°	299.8	300.4	301.0	301.4	302.0	302.9	304.0	305.2	306.4	307.6	308.4
110°	341.7	342.1	342.7	343.2	343.7	344.5	345.5	346.7	347.7	348.7	349.1



TEST NUMBER: P332703-927

CATALOG NUMBER: SA4XXDIP-C1195D1035U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.1	383.1	384.0	385.0	386.0	386.7	387.1	387.6	388.1	388.6	388.6
115°	444.4	445.0	445.5	446.0	446.6	446.7	446.6	446.4	446.2	446.0	446.4
117.5°	500.6	501.3	502.0	502.7	503.4	503.9	504.3	504.7	505.1	505.5	505.4
120°	538.5	539.2	540.0	540.7	541.4	541.6	541.5	541.3	541.1	540.9	541.3
122.5°	573.9	574.4	574.8	575.2	575.7	576.0	576.2	576.5	576.7	576.9	577.2
125°	624.7	625.4	626.1	626.9	627.6	627.7	627.4	627.0	626.7	626.3	626.9
127.5°	672.8	673.0	673.2	673.4	673.5	674.0	674.9	675.7	676.4	677.2	677.2
130°	703.9	704.0	704.2	704.3	704.5	704.9	705.4	705.9	706.5	707.0	707.2
132.5°	732.3	732.6	732.9	733.2	733.6	734.0	734.7	735.4	736.0	736.7	736.9
135°	775.0	774.8	774.7	774.4	774.3	774.5	775.2	775.9	776.7	777.4	777.7
137.5°	812.8	812.9	812.9	813.0	813.1	813.5	814.3	815.1	815.8	816.6	817.0
140°	837.5	837.8	838.2	838.5	838.8	839.2	839.6	840.0	840.3	840.7	841.1
142.5°	859.6	860.2	860.9	861.5	862.1	862.5	862.8	863.0	863.2	863.4	863.8
145°	893.6	894.1	894.7	895.2	895.7	896.0	896.0	896.0	896.0	896.0	896.2
147.5°	920.7	921.6	922.7	923.6	924.6	925.0	924.8	924.6	924.5	924.3	924.5
150°	940.2	941.0	941.7	942.4	943.1	943.3	943.2	943.0	942.9	942.6	942.6
152.5°	956.7	957.3	957.8	958.4	958.9	959.1	958.8	958.5	958.1	957.8	958.1
155°	979.9	980.0	980.2	980.3	980.5	980.3	979.9	979.3	978.7	978.3	978.9
157.5°	999.3	999.2	999.0	998.9	998.9	998.5	997.9	997.3	996.7	996.1	997.0
160°	1010.7	1010.1	1009.6	1009.1	1008.5	1008.2	1008.1	1007.8	1007.7	1007.5	1008.5
162.5°	1020.8	1020.1	1019.5	1018.7	1018.1	1017.7	1017.5	1017.3	1017.2	1017.0	1018.0
165°	1033.6	1032.7	1031.8	1030.9	1030.1	1029.6	1029.6	1029.6	1029.6	1029.6	1031.0
167.5°	1043.7	1042.8	1041.9	1041.0	1040.1	1039.6	1039.4	1039.3	1039.3	1039.1	1040.7
170°	1049.4	1048.4	1047.3	1046.2	1045.2	1044.7	1044.9	1045.1	1045.3	1045.4	1046.9
172.5°	1053.2	1052.2	1051.1	1050.0	1049.0	1048.5	1048.7	1048.9	1049.1	1049.2	1050.7
175°	1057.3	1056.3	1055.2	1054.2	1053.1	1052.7	1052.8	1053.0	1053.2	1053.4	1054.9
177.5°	1059.2	1058.2	1057.2	1056.3	1055.3	1054.9	1055.2	1055.5	1055.7	1056.1	1057.2
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332703-927

CATALOG NUMBER: SA4XXDIP-C1195D1035U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1573.0	1575.3	1577.6	1578.6	1578.3	1578.1	1577.9	1577.6
5°	1564.6	1567.7	1570.8	1572.1	1571.5	1571.0	1570.4	1569.8
7.5°	1547.2	1549.7	1552.1	1553.2	1552.9	1552.5	1552.2	1551.9
10°	1532.6	1534.9	1537.1	1537.9	1537.4	1536.8	1536.2	1535.6
12.5°	1514.8	1517.3	1519.8	1520.6	1519.8	1519.0	1518.2	1517.4
15°	1480.8	1482.6	1484.2	1484.6	1483.8	1483.0	1482.1	1481.3
17.5°	1442.2	1443.3	1444.3	1444.5	1444.0	1443.4	1442.9	1442.3
20°	1413.4	1414.2	1415.1	1415.2	1414.7	1414.1	1413.6	1412.9
22.5°	1383.4	1384.9	1386.4	1386.6	1385.7	1384.7	1383.6	1382.6
25°	1333.9	1334.1	1334.4	1334.0	1332.8	1331.7	1330.6	1329.5
27.5°	1278.3	1277.6	1276.9	1275.9	1274.5	1273.1	1271.7	1270.3
30°	1239.9	1238.8	1237.7	1236.4	1235.0	1233.7	1232.2	1230.8
32.5°	1201.0	1199.7	1198.3	1197.0	1195.6	1194.1	1192.8	1191.4
35°	1139.6	1137.7	1135.7	1134.0	1132.6	1131.2	1129.7	1128.4
37.5°	1075.2	1073.1	1071.0	1069.0	1067.1	1065.2	1063.4	1061.5
40°	1030.4	1027.5	1024.8	1022.6	1021.3	1019.9	1018.4	1017.0
42.5°	987.0	983.7	980.5	978.3	977.4	976.4	975.5	974.5
45°	919.8	916.7	913.6	911.6	910.8	909.9	909.1	908.2
47.5°	854.8	851.3	847.8	844.9	842.8	840.7	838.5	836.4
50°	809.3	805.3	801.5	798.6	796.9	795.3	793.5	791.9
52.5°	762.6	759.1	755.7	752.9	750.8	748.6	746.5	744.3
55°	694.0	690.7	687.3	684.8	683.1	681.4	679.7	678.0
57.5°	625.3	622.1	618.9	616.5	614.9	613.2	611.6	610.0
60°	578.1	575.6	573.1	571.1	569.7	568.2	566.9	565.5
62.5°	532.0	529.7	527.4	525.5	524.1	522.7	521.3	519.9
65°	464.9	462.2	459.3	457.2	455.8	454.4	453.0	451.6
67.5°	395.9	393.2	390.5	388.9	388.5	388.1	387.7	387.3
70°	352.2	350.0	347.7	346.2	345.3	344.5	343.6	342.8
72.5°	308.6	306.8	305.0	303.6	302.9	302.0	301.1	300.3
75°	245.7	244.5	243.4	242.7	242.5	242.2	241.9	241.6
77.5°	186.0	185.7	185.4	184.8	184.1	183.4	182.6	181.9
80°	148.1	147.6	147.0	146.6	146.3	146.0	145.8	145.4
82.5°	114.2	113.8	113.5	113.2	112.9	112.6	112.3	112.1
85°	65.8	65.8	65.8	65.7	65.4	65.0	64.8	64.5
87.5°	28.2	28.4	28.6	28.8	28.8	28.9	29.0	29.0
90°	19.5	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	18.9	20.0	21.0	21.5	21.6	21.7	21.8	21.9
95°	19.5	20.6	21.6	22.3	22.4	22.6	22.7	22.9
97.5°	21.1	21.2	21.3	21.5	21.6	21.8	21.9	22.2
100°	28.8	25.8	22.8	21.5	21.6	21.8	21.9	22.2
102.5°	103.2	71.0	38.7	22.7	22.7	22.7	22.7	22.8
105°	249.9	251.4	253.0	250.7	244.4	238.1	231.7	225.4
107.5°	309.2	310.0	310.7	311.4	312.1	312.8	313.5	314.1
110°	349.4	349.8	350.1	350.6	351.1	351.6	352.2	352.7



TEST NUMBER: P332703-927

CATALOG NUMBER: SA4XXDIP-C1195D1035U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	388.5	388.4	388.3	388.6	389.3	390.0	390.6	391.3
115°	446.7	447.1	447.4	447.6	447.6	447.6	447.6	447.6
117.5°	505.3	505.3	505.2	505.2	505.1	505.0	504.9	504.9
120°	541.6	541.9	542.3	542.3	541.9	541.6	541.3	540.9
122.5°	577.4	577.6	577.8	577.7	577.4	577.0	576.7	576.3
125°	627.4	627.9	628.4	628.8	629.0	629.2	629.3	629.5
127.5°	677.1	676.9	676.8	676.7	676.6	676.4	676.3	676.1
130°	707.3	707.5	707.7	707.8	707.8	707.8	707.8	707.8
132.5°	737.0	737.3	737.4	737.4	737.3	737.1	737.0	736.9
135°	778.1	778.4	778.8	779.1	779.5	779.8	780.1	780.5
137.5°	817.4	817.8	818.2	818.2	818.2	818.1	817.9	817.8
140°	841.7	842.2	842.7	843.1	843.3	843.4	843.6	843.8
142.5°	864.2	864.6	865.0	865.1	865.2	865.2	865.3	865.3
145°	896.4	896.5	896.7	897.0	897.3	897.6	898.0	898.3
147.5°	924.6	924.7	924.9	925.0	925.2	925.3	925.6	925.7
150°	942.6	942.6	942.6	942.7	942.9	943.1	943.3	943.4
152.5°	958.4	958.7	958.9	959.0	958.9	958.9	958.7	958.6
155°	979.6	980.3	981.0	981.1	980.6	980.1	979.5	979.1
157.5°	997.9	998.9	999.7	999.7	998.9	997.9	997.0	996.1
160°	1009.6	1010.7	1011.7	1011.7	1010.7	1009.6	1008.5	1007.5
162.5°	1019.1	1020.2	1021.2	1021.1	1019.9	1018.7	1017.6	1016.4
165°	1032.5	1033.9	1035.2	1035.1	1033.6	1032.0	1030.4	1028.8
167.5°	1042.2	1043.8	1045.3	1045.2	1043.5	1041.7	1039.9	1038.2
170°	1048.3	1049.6	1051.1	1050.9	1049.2	1047.4	1045.6	1043.9
172.5°	1052.1	1053.4	1054.9	1054.6	1052.7	1050.8	1048.9	1047.0
175°	1056.5	1058.1	1059.7	1059.4	1057.3	1055.2	1053.1	1051.0
177.5°	1058.3	1059.4	1060.6	1060.3	1058.6	1056.9	1055.2	1053.5
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3

(END OF REPORT)