

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332713-927

Luminaire Tested: **SA4XXDIP-C1195D1205U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332713-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D1205U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7356.3 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332713-927

CATALOG NUMBER: SA4XXDIP-C1195D1205U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332713-927

CATALOG NUMBER: SA4XXDIP-C1195D1205U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	94	91	87	92	88	84	81	76	73	71	64	62	61	54	52	51	46				
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28				
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24				
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21				
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12745	12745	12745
5°	12783	12630	12721
10°	12703	12527	12588
15°	12549	12349	12380
20°	12345	12128	12138
25°	12113	11875	11843
30°	11828	11580	11473
35°	11532	11269	11121
40°	11225	10918	10718
45°	10904	10572	10369
50°	10550	10262	9946
55°	10166	9864	9543
60°	9783	9415	9131
65°	9352	8990	8627
70°	8868	8419	8091
75°	8125	7735	7536
80°	7234	6936	6760
85°	6326	6095	5974



TEST NUMBER: P332713-927

CATALOG NUMBER: SA4XXDIP-C1195D1205U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.7	2.0
10°-20°	418.9	5.7
20°-30°	616.5	8.4
30°-40°	716.7	9.7
40°-50°	716.8	9.7
50°-60°	627.0	8.5
60°-70°	465.6	6.3
70°-80°	264.5	3.6
80°-90°	79.9	1.1
90°-100°	78.5	1.1
100°-110°	232.5	3.2
110°-120°	394.6	5.4
120°-130°	520.4	7.1
130°-140°	584.4	7.9
140°-150°	574.3	7.8
150°-160°	483.0	6.6
160°-170°	321.4	4.4
170°-180°	112.5	1.5
0°-30°	1184.1	16.1
0°-40°	1900.8	25.8
0°-60°	3244.6	44.1
0°-90°	4054.7	55.1
90°-120°	705.6	9.6
90°-150°	2384.7	32.4
90°-180°	3302.0	44.9
0°-180°	7356.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1579	1579	1579	1579	1579	
5°	1577	1572	1558	1571	1570	150
15°	1502	1496	1478	1484	1481	423
25°	1360	1350	1333	1334	1330	625
35°	1170	1161	1144	1135	1128	731
45°	955	946	926	913	908	736
55°	722	718	701	686	678	647
65°	490	483	471	458	452	485
75°	260	254	248	243	242	277
85°	68	68	66	66	64	75
90°	3	13	20	26	28	7
95°	55	63	70	73	73	61
105°	214	216	219	222	225	228
115°	401	401	399	398	398	396
125°	584	584	584	582	580	521
135°	754	759	759	757	755	583
145°	916	919	920	919	917	573
155°	1049	1049	1048	1052	1048	483
165°	1142	1139	1138	1143	1139	322
175°	1188	1184	1183	1188	1183	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P332713-927

CATALOG NUMBER: SA4XXDIP-C1195D1205U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1582.7	1582.1	1581.4	1580.7	1580.0	1578.4	1576.0	1573.5	1571.1	1568.6	1570.8
5°	1577.4	1576.3	1575.2	1574.1	1573.0	1570.8	1567.7	1564.6	1561.5	1558.5	1561.5
7.5°	1562.7	1561.6	1560.5	1559.3	1558.2	1556.0	1552.5	1549.1	1545.7	1542.2	1544.8
10°	1549.6	1548.5	1547.4	1546.2	1545.1	1542.7	1539.1	1535.4	1531.8	1528.1	1530.3
12.5°	1532.4	1531.3	1530.1	1529.0	1527.9	1525.3	1521.5	1517.7	1513.8	1509.9	1512.4
15°	1501.5	1500.4	1499.3	1498.2	1497.0	1494.4	1490.1	1485.9	1481.7	1477.5	1479.2
17.5°	1464.3	1462.9	1461.5	1460.2	1458.7	1456.0	1452.0	1448.0	1444.1	1440.0	1441.1
20°	1437.0	1435.6	1434.2	1432.8	1431.4	1428.5	1424.3	1420.1	1415.9	1411.7	1412.5
22.5°	1407.6	1405.8	1404.0	1402.1	1400.3	1397.2	1393.0	1388.8	1384.6	1380.3	1381.9
25°	1359.9	1357.9	1355.9	1353.9	1351.9	1349.0	1345.0	1341.2	1337.2	1333.2	1333.6
27.5°	1305.2	1303.1	1301.2	1299.1	1297.1	1294.3	1290.6	1287.0	1283.3	1279.6	1279.0
30°	1268.8	1266.5	1264.2	1262.0	1259.8	1256.8	1253.2	1249.5	1245.9	1242.2	1241.1
32.5°	1230.3	1228.3	1226.3	1224.2	1222.2	1219.2	1215.4	1211.5	1207.6	1203.7	1202.4
35°	1170.1	1168.2	1166.2	1164.2	1162.2	1159.3	1155.3	1151.4	1147.5	1143.5	1141.5
37.5°	1106.6	1104.8	1103.0	1101.2	1099.4	1096.4	1092.2	1088.0	1083.7	1079.5	1077.4
40°	1065.1	1062.9	1060.6	1058.4	1056.1	1052.9	1048.7	1044.4	1040.2	1036.0	1033.2
42.5°	1020.6	1019.2	1017.9	1016.5	1015.2	1012.2	1007.5	1002.8	998.1	993.5	990.2
45°	955.1	953.1	951.1	949.1	947.2	944.0	939.4	934.9	930.4	926.0	922.9
47.5°	886.5	885.1	883.8	882.4	881.1	878.4	874.2	870.1	865.9	861.7	858.3
50°	840.0	838.8	837.7	836.5	835.4	832.9	828.9	825.1	821.1	817.1	813.3
52.5°	794.4	793.1	791.7	790.4	789.0	786.2	782.1	777.9	773.8	769.6	766.1
55°	722.3	721.4	720.6	719.8	718.9	716.5	712.6	708.7	704.7	700.8	697.4
57.5°	653.5	652.5	651.6	650.6	649.7	647.2	643.3	639.4	635.6	631.7	628.5
60°	605.9	604.5	603.1	601.7	600.3	597.8	594.1	590.5	586.8	583.1	580.6
62.5°	559.4	558.2	557.0	555.8	554.7	552.2	548.3	544.4	540.5	536.6	534.3
65°	489.6	488.1	486.7	485.3	483.9	481.8	479.0	476.2	473.4	470.6	467.8
67.5°	419.2	418.0	416.6	415.3	414.1	412.0	409.3	406.6	403.9	401.2	398.5
70°	375.7	373.8	371.8	369.8	367.8	365.8	363.5	361.2	358.9	356.7	354.5
72.5°	329.2	327.2	325.2	323.2	321.3	319.4	317.6	315.8	314.0	312.2	310.4
75°	260.5	259.2	257.8	256.4	254.9	253.6	252.2	250.7	249.4	248.0	246.8
77.5°	195.0	194.4	193.8	193.2	192.6	191.6	190.4	189.2	188.0	186.7	186.4
80°	155.6	154.7	153.9	153.0	152.3	151.5	151.0	150.4	149.8	149.2	148.7
82.5°	117.2	116.8	116.4	116.0	115.6	115.3	115.2	115.1	114.9	114.9	114.5
85°	68.3	68.3	68.3	68.3	68.3	68.0	67.5	66.9	66.3	65.8	65.8
87.5°	26.9	27.1	27.3	27.6	27.7	28.0	28.0	28.1	28.2	28.4	28.6
90°	2.8	5.0	7.3	9.5	11.7	13.7	15.4	17.0	18.6	20.3	21.5
92.5°	19.7	22.3	24.9	27.4	30.0	31.8	33.0	34.1	35.3	36.4	37.2
95°	55.2	57.0	58.9	60.8	62.6	64.2	65.7	67.1	68.5	69.9	70.6
97.5°	96.5	97.9	99.4	100.8	102.3	103.9	105.6	107.3	108.9	110.6	111.4
100°	128.9	129.7	130.5	131.3	132.1	133.5	135.3	137.1	138.9	140.9	141.2
102.5°	162.7	163.0	163.3	163.7	164.1	165.0	166.7	168.4	170.1	171.7	172.3
105°	214.4	214.7	214.8	215.1	215.2	215.8	216.6	217.4	218.2	219.0	219.7
107.5°	268.7	269.0	269.3	269.5	269.7	269.9	270.1	270.1	270.3	270.4	271.0
110°	305.5	305.9	306.3	306.8	307.2	307.3	307.1	306.9	306.7	306.5	306.1



TEST NUMBER: P332713-927

CATALOG NUMBER: SA4XXDIP-C1195D1205U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.8	344.0	344.0	344.1	344.2	344.0	343.6	343.3	342.9	342.5	342.5
115°	401.2	401.2	401.2	401.2	401.2	401.1	400.7	400.3	399.8	399.4	399.3
117.5°	455.4	455.6	455.7	455.9	456.1	456.0	455.7	455.4	455.1	454.9	454.2
120°	491.5	492.3	493.1	493.9	494.7	494.9	494.2	493.6	493.0	492.4	491.4
122.5°	529.0	529.3	529.7	530.0	530.4	530.4	530.0	529.8	529.5	529.2	528.5
125°	584.4	584.4	584.4	584.4	584.4	584.3	584.2	583.9	583.7	583.5	583.1
127.5°	634.7	635.3	635.9	636.5	637.2	637.3	636.9	636.6	636.3	636.0	635.6
130°	670.0	670.7	671.2	671.8	672.5	672.8	672.8	672.8	672.8	672.8	672.4
132.5°	706.1	706.5	707.0	707.4	707.9	708.1	707.9	707.7	707.6	707.4	706.9
135°	753.8	755.0	756.2	757.5	758.7	759.3	759.3	759.3	759.3	759.3	758.9
137.5°	805.6	806.3	806.8	807.4	807.9	808.4	808.7	809.1	809.4	809.7	809.2
140°	840.3	840.7	841.1	841.5	841.9	842.1	842.1	842.1	842.1	842.1	841.9
142.5°	872.0	872.4	872.7	873.1	873.6	873.7	873.5	873.4	873.2	873.1	873.0
145°	915.8	916.6	917.4	918.2	919.0	919.6	919.7	920.0	920.1	920.4	920.1
147.5°	959.2	960.2	961.2	962.1	963.1	963.5	963.4	963.2	963.1	962.9	962.7
150°	985.7	986.5	987.4	988.2	989.0	989.4	989.4	989.4	989.4	989.4	989.4
152.5°	1010.7	1011.2	1011.7	1012.2	1012.7	1013.0	1013.2	1013.4	1013.5	1013.7	1014.2
155°	1049.2	1049.2	1049.2	1049.2	1049.2	1049.1	1048.9	1048.7	1048.5	1048.3	1049.1
157.5°	1081.6	1081.2	1080.9	1080.5	1080.1	1079.9	1079.9	1079.8	1079.8	1079.7	1080.4
160°	1100.7	1100.6	1100.3	1100.1	1099.9	1099.7	1099.5	1099.3	1099.1	1098.9	1099.5
162.5°	1118.4	1117.8	1117.4	1116.8	1116.3	1115.9	1115.7	1115.6	1115.3	1115.1	1116.2
165°	1142.2	1141.5	1140.9	1140.3	1139.7	1139.2	1138.8	1138.4	1138.0	1137.6	1138.8
167.5°	1160.4	1159.5	1158.6	1157.8	1157.0	1156.5	1156.6	1156.6	1156.7	1156.7	1157.9
170°	1170.7	1169.7	1168.6	1167.6	1166.6	1166.2	1166.4	1166.6	1166.8	1167.0	1168.2
172.5°	1178.1	1177.2	1176.3	1175.4	1174.6	1174.2	1174.3	1174.3	1174.3	1174.4	1175.8
175°	1188.2	1187.2	1186.1	1185.1	1184.1	1183.4	1183.3	1183.0	1182.9	1182.6	1184.1
177.5°	1191.5	1190.6	1189.9	1189.1	1188.2	1187.8	1187.8	1187.8	1187.8	1187.8	1189.0
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0



TEST NUMBER: P332713-927

CATALOG NUMBER: SA4XXDIP-C1195D1205U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1573.0	1575.3	1577.6	1578.6	1578.3	1578.1	1577.9	1577.6
5°	1564.6	1567.7	1570.8	1572.1	1571.5	1571.0	1570.4	1569.8
7.5°	1547.2	1549.7	1552.1	1553.2	1552.9	1552.5	1552.2	1551.9
10°	1532.6	1534.9	1537.1	1537.9	1537.4	1536.8	1536.2	1535.6
12.5°	1514.8	1517.3	1519.8	1520.6	1519.8	1519.0	1518.2	1517.4
15°	1480.8	1482.6	1484.2	1484.6	1483.8	1483.0	1482.1	1481.3
17.5°	1442.2	1443.3	1444.3	1444.5	1444.0	1443.4	1442.9	1442.3
20°	1413.4	1414.2	1415.1	1415.2	1414.7	1414.1	1413.6	1412.9
22.5°	1383.4	1384.9	1386.4	1386.6	1385.7	1384.7	1383.6	1382.6
25°	1333.9	1334.1	1334.4	1334.0	1332.8	1331.7	1330.6	1329.5
27.5°	1278.3	1277.6	1276.9	1275.9	1274.5	1273.1	1271.7	1270.3
30°	1239.9	1238.8	1237.7	1236.4	1235.0	1233.7	1232.2	1230.8
32.5°	1201.0	1199.7	1198.3	1197.0	1195.6	1194.1	1192.8	1191.4
35°	1139.6	1137.7	1135.7	1134.0	1132.6	1131.2	1129.7	1128.4
37.5°	1075.2	1073.1	1071.0	1069.0	1067.1	1065.2	1063.4	1061.5
40°	1030.4	1027.5	1024.8	1022.6	1021.3	1019.9	1018.4	1017.0
42.5°	987.0	983.7	980.5	978.3	977.4	976.4	975.5	974.5
45°	919.8	916.7	913.6	911.6	910.8	909.9	909.1	908.2
47.5°	854.8	851.3	847.8	844.9	842.8	840.7	838.5	836.4
50°	809.3	805.3	801.5	798.6	796.9	795.3	793.5	791.9
52.5°	762.6	759.1	755.7	752.9	750.8	748.6	746.5	744.3
55°	694.0	690.7	687.3	684.8	683.1	681.4	679.7	678.0
57.5°	625.3	622.1	618.9	616.5	614.9	613.2	611.6	610.0
60°	578.1	575.6	573.1	571.1	569.7	568.2	566.9	565.5
62.5°	532.0	529.7	527.4	525.5	524.1	522.7	521.3	519.9
65°	464.9	462.2	459.3	457.2	455.8	454.4	453.0	451.6
67.5°	395.9	393.2	390.5	388.9	388.5	388.1	387.7	387.3
70°	352.2	350.0	347.7	346.2	345.3	344.5	343.6	342.8
72.5°	308.6	306.8	305.0	303.6	302.9	302.0	301.1	300.3
75°	245.7	244.5	243.4	242.7	242.5	242.2	241.9	241.6
77.5°	186.0	185.7	185.4	184.8	184.1	183.4	182.6	181.9
80°	148.1	147.6	147.0	146.6	146.3	146.0	145.8	145.4
82.5°	114.2	113.8	113.5	113.2	112.9	112.6	112.3	112.1
85°	65.8	65.8	65.8	65.7	65.4	65.0	64.8	64.5
87.5°	28.8	29.1	29.3	29.5	29.5	29.6	29.7	29.8
90°	22.7	23.9	25.2	26.0	26.4	26.8	27.2	27.6
92.5°	37.9	38.7	39.4	39.8	40.2	40.4	40.6	40.9
95°	71.1	71.8	72.4	72.7	72.7	72.7	72.7	72.7
97.5°	112.1	112.8	113.6	113.9	113.9	113.9	113.9	113.9
100°	141.6	142.0	142.4	142.7	142.7	142.7	142.7	142.7
102.5°	172.9	173.5	174.0	174.4	174.6	174.8	174.9	175.1
105°	220.3	220.9	221.5	222.1	222.8	223.3	223.9	224.6
107.5°	271.6	272.1	272.7	273.0	272.9	272.9	272.8	272.8
110°	305.6	305.2	304.8	304.9	305.5	306.2	306.8	307.4



TEST NUMBER: P332713-927

CATALOG NUMBER: SA4XXDIP-C1195D1205U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	342.4	342.3	342.2	342.2	342.4	342.5	342.6	342.8
115°	399.0	398.8	398.6	398.4	398.2	398.0	397.8	397.6
117.5°	453.4	452.7	452.0	451.5	451.1	450.7	450.3	449.9
120°	490.4	489.3	488.3	488.0	488.4	488.8	489.3	489.6
122.5°	527.8	527.1	526.4	525.7	525.0	524.3	523.5	522.8
125°	582.7	582.3	581.9	581.5	581.1	580.7	580.2	579.8
127.5°	635.2	634.8	634.3	634.0	633.7	633.3	633.0	632.6
130°	671.9	671.5	671.1	670.5	669.7	668.9	668.0	667.3
132.5°	706.5	706.2	705.8	705.4	705.0	704.7	704.4	704.1
135°	758.5	758.0	757.6	757.2	756.5	755.9	755.3	754.7
137.5°	808.7	808.1	807.6	807.4	807.6	807.6	807.8	807.9
140°	841.7	841.5	841.3	841.1	840.9	840.7	840.5	840.3
142.5°	873.0	872.9	872.9	872.8	872.8	872.7	872.7	872.7
145°	920.0	919.7	919.6	919.1	918.5	917.9	917.3	916.7
147.5°	962.6	962.4	962.2	962.0	961.9	961.6	961.4	961.2
150°	989.4	989.4	989.4	989.3	989.0	988.9	988.6	988.5
152.5°	1014.6	1015.2	1015.7	1015.7	1015.1	1014.5	1014.0	1013.5
155°	1050.0	1050.8	1051.5	1051.5	1050.8	1050.0	1049.1	1048.3
157.5°	1081.0	1081.6	1082.2	1082.2	1081.5	1080.8	1080.1	1079.4
160°	1100.1	1100.7	1101.4	1101.1	1100.1	1099.1	1098.1	1097.1
162.5°	1117.3	1118.4	1119.5	1119.6	1118.6	1117.5	1116.5	1115.5
165°	1140.0	1141.2	1142.5	1142.6	1141.9	1141.1	1140.2	1139.4
167.5°	1159.1	1160.4	1161.6	1161.6	1160.3	1159.0	1157.8	1156.5
170°	1169.5	1170.7	1172.0	1171.8	1170.4	1168.9	1167.5	1166.1
172.5°	1177.2	1178.5	1180.0	1180.0	1178.5	1177.0	1175.6	1174.2
175°	1185.5	1186.9	1188.4	1188.4	1186.9	1185.5	1184.1	1182.6
177.5°	1190.1	1191.3	1192.4	1192.3	1191.0	1189.7	1188.4	1187.1
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0

(END OF REPORT)