

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332994

Luminaire Tested: **SA4XXRDIP-C1195D590U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332994
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D590U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7179.6 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332994
CATALOG NUMBER: SA4XXRDIP-C1195D590U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332994

CATALOG NUMBER: SA4XXRDIP-C1195D590U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	61	57				
2	93	86	80	74	88	81	76	71	72	68	65	64	61	58	57	54	52	49				
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	42				
4	78	67	59	53	73	64	57	51	57	52	47	51	47	43	46	42	39	36				
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31				
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	37	33	30	28				
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	25				
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	32	27	24	22				
9	54	41	33	28	50	39	32	27	36	30	26	32	27	24	29	25	22	20				
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16835	16835	16835
5°	16874	16667	16771
10°	16768	16467	16467
15°	16575	16121	16002
20°	16311	15667	15378
25°	15973	15134	14750
30°	15645	14573	13962
35°	15281	13991	13172
40°	14842	13328	12318
45°	14439	12670	11449
50°	13978	11912	10528
55°	13485	11125	9529
60°	12943	10261	8507
65°	12445	9181	7503
70°	11722	7990	6371
75°	10808	6625	5181
80°	9428	5049	4751
85°	7984	4585	4289



TEST NUMBER: P332994

CATALOG NUMBER: SA4XXRDIP-C1195D590U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.9	2.7
10°-20°	546.3	7.6
20°-30°	788.8	11.0
30°-40°	894.2	12.5
40°-50°	863.5	12.0
50°-60°	718.0	10.0
60°-70°	495.8	6.9
70°-80°	251.3	3.5
80°-90°	66.7	0.9
90°-100°	26.1	0.4
100°-110°	166.3	2.3
110°-120°	318.2	4.4
120°-130°	403.9	5.6
130°-140°	432.1	6.0
140°-150°	404.1	5.6
150°-160°	325.9	4.5
160°-170°	210.2	2.9
170°-180°	72.4	1.0
0°-30°	1531.0	21.3
0°-40°	2425.2	33.8
0°-60°	4006.7	55.8
0°-90°	4820.4	67.1
90°-120°	510.6	7.1
90°-150°	1750.6	24.4
90°-180°	2359.0	32.9
0°-180°	7179.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2057	2072	2070	197
15°	1983	1967	1929	1925	1915	559
25°	1793	1762	1699	1672	1656	826
35°	1550	1498	1420	1367	1336	968
45°	1265	1204	1110	1034	1003	975
55°	958	892	790	710	677	857
65°	652	581	481	415	393	643
75°	346	287	212	177	166	366
85°	86	56	50	46	46	97
90°	2	8	12	16	17	6
95°	31	13	12	16	16	40
105°	172	175	178	182	163	180
115°	321	322	322	323	323	315
125°	451	453	452	453	454	402
135°	559	559	561	562	563	431
145°	645	646	646	647	648	403
155°	707	707	706	708	706	326
165°	746	743	743	747	742	211
175°	763	759	760	764	758	73
180°	763	763	763	763	763	



TEST NUMBER: P332994

CATALOG NUMBER: SA4XXRDIP-C1195D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2090.5	2089.4	2088.3	2087.1	2086.0	2083.9	2080.8	2077.6	2074.5	2071.4	2074.5
5°	2082.2	2080.8	2079.4	2078.0	2076.6	2073.7	2069.5	2065.2	2061.0	2056.7	2060.2
7.5°	2063.4	2061.9	2060.4	2058.9	2057.4	2053.9	2048.4	2042.9	2037.3	2031.8	2034.1
10°	2045.5	2043.7	2042.0	2040.2	2038.4	2034.3	2028.0	2021.6	2015.2	2008.8	2010.2
12.5°	2022.5	2020.5	2018.4	2016.3	2014.3	2009.5	2002.0	1994.5	1986.9	1979.4	1980.3
15°	1983.2	1980.0	1976.9	1973.7	1970.5	1964.4	1955.6	1946.7	1937.8	1928.9	1928.2
17.5°	1935.7	1931.0	1926.4	1921.8	1917.2	1909.6	1898.9	1888.3	1877.6	1867.0	1865.0
20°	1898.6	1894.0	1889.4	1884.8	1880.2	1871.8	1859.8	1847.7	1835.6	1823.6	1820.7
22.5°	1857.7	1852.6	1847.4	1842.2	1837.0	1828.0	1815.0	1802.1	1789.2	1776.3	1772.0
25°	1793.2	1786.8	1780.4	1774.1	1767.7	1757.2	1742.7	1728.1	1713.6	1699.0	1693.0
27.5°	1725.5	1717.5	1709.5	1701.5	1693.4	1681.7	1666.1	1650.6	1635.0	1619.5	1612.0
30°	1678.3	1669.4	1660.5	1651.6	1642.8	1630.0	1613.3	1596.6	1580.0	1563.3	1554.4
32.5°	1628.4	1618.4	1608.4	1598.4	1588.4	1574.8	1557.5	1540.3	1523.0	1505.8	1495.5
35°	1550.5	1539.1	1527.8	1516.4	1505.1	1490.5	1472.8	1455.1	1437.3	1419.6	1407.5
37.5°	1467.2	1455.4	1443.7	1432.0	1420.3	1404.6	1385.0	1365.3	1345.7	1326.0	1312.5
40°	1408.4	1396.7	1385.0	1373.3	1361.5	1345.6	1325.4	1305.1	1284.9	1264.7	1249.8
42.5°	1352.2	1339.9	1327.6	1315.3	1303.1	1286.4	1265.3	1244.2	1223.2	1202.1	1186.9
45°	1264.7	1251.5	1238.4	1225.3	1212.2	1194.9	1173.7	1152.4	1131.1	1109.8	1092.4
47.5°	1174.3	1160.7	1147.2	1133.6	1120.1	1102.2	1080.1	1057.9	1035.8	1013.7	995.6
50°	1113.0	1099.1	1085.3	1071.5	1057.6	1039.3	1016.6	993.9	971.2	948.5	930.8
52.5°	1050.4	1036.8	1023.3	1009.7	996.2	977.7	954.5	931.2	907.9	884.6	866.6
55°	958.1	943.9	929.7	915.5	901.3	882.7	859.6	836.6	813.5	790.4	772.0
57.5°	866.7	852.0	837.2	822.5	807.7	789.0	766.3	743.5	720.8	698.1	679.4
60°	801.6	787.4	773.2	759.0	744.8	726.4	703.7	681.0	658.2	635.5	617.1
62.5°	742.8	728.1	713.3	698.6	683.8	664.8	641.5	618.2	594.9	571.7	554.6
65°	651.5	636.2	621.0	605.7	590.5	571.5	548.8	526.1	503.4	480.6	465.4
67.5°	556.6	542.0	527.4	512.8	498.2	480.3	459.2	438.2	417.1	396.0	382.9
70°	496.6	481.7	466.8	451.9	437.0	419.4	399.2	379.0	358.8	338.5	326.8
72.5°	432.7	419.3	405.8	392.3	378.8	362.5	343.4	324.3	305.2	286.1	276.1
75°	346.5	333.4	320.2	307.1	294.0	279.1	262.4	245.7	229.1	212.4	204.2
77.5°	259.0	247.9	236.7	225.6	214.4	202.1	188.6	175.2	161.7	148.2	143.4
80°	202.8	192.5	182.2	171.9	161.6	151.2	140.5	129.9	119.2	108.6	107.5
82.5°	154.3	144.8	135.4	125.9	116.5	108.7	102.6	96.5	90.4	84.3	83.5
85°	86.2	79.1	72.0	64.9	57.8	53.8	52.7	51.6	50.6	49.5	48.8
87.5°	29.7	27.7	25.7	23.7	21.8	20.7	20.6	20.6	20.5	20.4	20.3
90°	1.7	3.1	4.5	5.9	7.3	8.5	9.5	10.5	11.5	12.5	13.3
92.5°	7.2	7.3	7.3	7.4	7.5	8.0	9.1	10.1	11.1	12.1	12.9
95°	31.4	27.1	22.8	18.4	14.1	12.0	12.2	12.3	12.4	12.5	13.3
97.5°	66.6	69.3	72.0	74.7	77.4	71.6	57.5	43.4	29.2	15.1	15.1
100°	93.5	95.8	98.1	100.4	102.7	95.1	77.6	60.1	42.6	25.1	22.9
102.5°	123.7	125.3	127.0	128.7	130.4	130.1	127.8	125.5	123.2	120.9	97.7
105°	171.7	172.5	173.2	174.0	174.7	175.4	176.1	176.7	177.3	178.0	179.1
107.5°	216.3	216.7	217.1	217.4	217.8	218.4	219.3	220.2	221.0	221.9	222.5
110°	246.4	246.8	247.2	247.6	247.9	248.5	249.3	250.0	250.8	251.6	251.8



TEST NUMBER: P332994

CATALOG NUMBER: SA4XXRDIP-C1195D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.6	276.3	277.0	277.7	278.4	278.9	279.2	279.6	280.0	280.3	280.3
115°	320.6	321.0	321.3	321.7	322.1	322.2	322.1	322.0	321.8	321.7	322.0
117.5°	361.1	361.6	362.1	362.6	363.1	363.5	363.8	364.1	364.3	364.6	364.6
120°	388.5	389.0	389.5	390.0	390.5	390.7	390.6	390.4	390.3	390.2	390.4
122.5°	414.0	414.3	414.6	414.9	415.2	415.5	415.7	415.8	416.0	416.2	416.3
125°	450.6	451.1	451.7	452.2	452.7	452.8	452.5	452.3	452.0	451.8	452.2
127.5°	485.3	485.4	485.6	485.7	485.8	486.2	486.8	487.3	487.9	488.5	488.4
130°	507.7	507.8	507.9	508.1	508.2	508.4	508.8	509.2	509.6	510.0	510.1
132.5°	528.2	528.4	528.7	528.9	529.1	529.5	530.0	530.4	530.9	531.4	531.5
135°	559.0	558.9	558.8	558.6	558.5	558.7	559.2	559.7	560.2	560.7	561.0
137.5°	586.3	586.3	586.4	586.4	586.5	586.8	587.3	587.9	588.5	589.0	589.3
140°	604.1	604.3	604.6	604.8	605.1	605.3	605.6	605.9	606.1	606.4	606.7
142.5°	620.1	620.5	621.0	621.4	621.9	622.2	622.3	622.5	622.6	622.8	623.1
145°	644.6	645.0	645.3	645.7	646.1	646.3	646.3	646.3	646.3	646.3	646.4
147.5°	664.1	664.8	665.5	666.2	666.9	667.2	667.1	667.0	666.8	666.7	666.8
150°	678.2	678.7	679.3	679.8	680.3	680.5	680.3	680.2	680.1	679.9	679.9
152.5°	690.1	690.5	690.9	691.3	691.7	691.8	691.6	691.4	691.1	690.9	691.1
155°	706.8	706.9	707.0	707.1	707.3	707.1	706.8	706.4	706.0	705.6	706.1
157.5°	720.8	720.7	720.6	720.6	720.5	720.2	719.8	719.4	718.9	718.5	719.2
160°	729.0	728.6	728.2	727.9	727.5	727.2	727.1	727.0	726.8	726.7	727.5
162.5°	736.3	735.8	735.3	734.9	734.4	734.1	733.9	733.8	733.7	733.6	734.3
165°	745.5	744.9	744.3	743.6	743.0	742.7	742.7	742.7	742.7	742.7	743.7
167.5°	752.8	752.2	751.5	750.9	750.2	749.8	749.8	749.7	749.6	749.5	750.7
170°	757.0	756.2	755.4	754.7	753.9	753.6	753.7	753.8	754.0	754.1	755.1
172.5°	759.7	758.9	758.2	757.4	756.7	756.3	756.5	756.6	756.7	756.8	757.9
175°	762.7	761.9	761.1	760.4	759.6	759.3	759.4	759.6	759.7	759.8	760.9
177.5°	764.0	763.3	762.6	761.9	761.2	760.9	761.1	761.3	761.5	761.7	762.6
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332994

CATALOG NUMBER: SA4XXRDIP-C1195D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2077.6	2080.8	2083.9	2085.3	2085.0	2084.7	2084.4	2084.2
5°	2063.8	2067.3	2070.9	2072.3	2071.6	2070.9	2070.2	2069.5
7.5°	2036.3	2038.6	2040.9	2041.4	2040.3	2039.2	2038.0	2036.9
10°	2011.6	2013.0	2014.5	2014.5	2013.0	2011.6	2010.2	2008.8
12.5°	1981.1	1982.0	1982.8	1982.2	1980.3	1978.3	1976.3	1974.3
15°	1927.5	1926.8	1926.1	1924.5	1922.0	1919.5	1917.1	1914.6
17.5°	1863.0	1861.0	1859.0	1856.2	1852.4	1848.6	1844.9	1841.1
20°	1817.9	1815.0	1812.2	1808.5	1803.9	1799.3	1794.6	1790.0
22.5°	1767.8	1763.5	1759.3	1755.3	1751.5	1747.7	1744.0	1740.2
25°	1686.9	1680.9	1674.9	1670.1	1666.5	1663.0	1659.4	1655.9
27.5°	1604.6	1597.1	1589.7	1583.4	1578.3	1573.2	1568.1	1563.0
30°	1545.5	1536.7	1527.8	1520.5	1514.8	1509.2	1503.5	1497.8
32.5°	1485.2	1474.9	1464.6	1456.8	1451.4	1446.0	1440.6	1435.2
35°	1395.4	1383.4	1371.3	1362.1	1355.7	1349.3	1342.9	1336.5
37.5°	1299.0	1285.5	1272.1	1262.1	1255.7	1249.3	1243.0	1236.6
40°	1234.9	1220.0	1205.1	1194.4	1188.0	1181.6	1175.3	1168.9
42.5°	1171.7	1156.5	1141.3	1130.4	1123.7	1117.1	1110.4	1103.7
45°	1075.0	1057.6	1040.2	1028.3	1022.0	1015.6	1009.2	1002.8
47.5°	977.6	959.6	941.6	929.0	922.0	915.0	907.9	900.9
50°	913.0	895.3	877.5	865.3	858.6	851.8	845.1	838.3
52.5°	848.6	830.6	812.5	800.0	793.0	786.0	778.9	771.9
55°	753.5	735.1	716.6	704.0	697.3	690.5	683.8	677.0
57.5°	660.7	641.9	623.2	611.3	606.2	601.0	595.9	590.8
60°	598.6	580.2	561.7	549.7	544.0	538.3	532.6	526.9
62.5°	537.6	520.6	503.5	492.7	488.2	483.7	479.1	474.6
65°	450.1	434.9	419.6	409.8	405.6	401.3	397.1	392.8
67.5°	369.8	356.6	343.5	334.6	329.9	325.2	320.5	315.8
70°	315.1	303.4	291.7	284.1	280.5	277.0	273.4	269.9
72.5°	266.1	256.1	246.1	239.5	236.2	233.0	229.7	226.4
75°	196.1	187.9	179.7	174.6	172.5	170.3	168.2	166.1
77.5°	138.7	133.9	129.2	126.5	125.8	125.2	124.6	123.9
80°	106.5	105.4	104.3	103.6	103.3	102.9	102.6	102.2
82.5°	82.8	82.0	81.2	80.6	80.3	79.9	79.6	79.2
85°	48.1	47.4	46.7	46.3	46.3	46.3	46.3	46.3
87.5°	20.1	20.0	19.9	20.0	20.3	20.6	21.0	21.3
90°	14.1	14.8	15.6	16.1	16.4	16.6	16.9	17.1
92.5°	13.6	14.4	15.1	15.5	15.6	15.6	15.7	15.7
95°	14.1	14.8	15.6	16.0	16.2	16.3	16.4	16.5
97.5°	15.2	15.3	15.4	15.5	15.6	15.7	15.8	16.0
100°	20.8	18.6	16.5	15.5	15.6	15.7	15.8	16.0
102.5°	74.4	51.2	27.9	16.3	16.4	16.4	16.4	16.4
105°	180.3	181.4	182.5	180.8	176.3	171.7	167.1	162.6
107.5°	223.0	223.6	224.1	224.6	225.1	225.6	226.1	226.6
110°	252.1	252.3	252.6	252.9	253.3	253.6	254.0	254.4



TEST NUMBER: P332994

CATALOG NUMBER: SA4XXRDIP-C1195D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	280.2	280.2	280.1	280.3	280.8	281.3	281.8	282.2
115°	322.2	322.5	322.7	322.9	322.9	322.9	322.9	322.9
117.5°	364.5	364.5	364.4	364.4	364.3	364.3	364.2	364.2
120°	390.7	390.9	391.2	391.2	390.9	390.7	390.4	390.2
122.5°	416.5	416.6	416.8	416.7	416.5	416.2	416.0	415.7
125°	452.5	452.9	453.3	453.6	453.7	453.8	453.9	454.1
127.5°	488.4	488.3	488.2	488.1	488.0	487.9	487.8	487.7
130°	510.2	510.3	510.5	510.5	510.5	510.5	510.5	510.5
132.5°	531.7	531.8	531.9	531.9	531.8	531.7	531.6	531.5
135°	561.2	561.5	561.7	562.0	562.2	562.5	562.8	563.0
137.5°	589.6	589.9	590.1	590.2	590.2	590.1	590.0	589.9
140°	607.1	607.5	607.9	608.1	608.3	608.4	608.5	608.6
142.5°	623.3	623.6	623.9	624.1	624.1	624.1	624.1	624.2
145°	646.5	646.7	646.8	647.0	647.2	647.5	647.8	648.0
147.5°	666.9	667.0	667.1	667.2	667.4	667.5	667.6	667.7
150°	679.9	679.9	679.9	680.0	680.1	680.3	680.4	680.5
152.5°	691.3	691.5	691.7	691.8	691.7	691.6	691.5	691.5
155°	706.6	707.1	707.6	707.7	707.3	706.9	706.6	706.2
157.5°	719.8	720.5	721.1	721.1	720.5	719.8	719.2	718.5
160°	728.2	729.0	729.8	729.8	729.0	728.2	727.5	726.7
162.5°	735.1	735.8	736.6	736.6	735.7	734.8	734.0	733.1
165°	744.7	745.7	746.8	746.7	745.5	744.4	743.3	742.1
167.5°	751.8	752.9	754.0	753.9	752.7	751.4	750.1	748.9
170°	756.1	757.1	758.2	758.0	756.8	755.5	754.2	753.0
172.5°	758.9	759.9	760.9	760.7	759.4	758.0	756.6	755.2
175°	762.1	763.2	764.4	764.2	762.7	761.1	759.6	758.1
177.5°	763.4	764.2	765.0	764.8	763.6	762.4	761.1	759.9
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7

(END OF REPORT)