

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332999

Luminaire Tested: **SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332999
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7905.9 lumens
Efficiency: N/A
Efficacy: 130.2 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	61	60	59	55
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	53	51	47
3	85	76	69	63	80	71	65	60	63	58	54	56	52	49	49	46	44	40
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35
5	72	60	52	46	67	57	50	44	51	45	41	45	41	37	40	36	33	31
6	66	54	46	41	62	52	44	39	46	40	36	41	36	33	36	33	30	27
7	62	49	41	36	58	47	40	34	42	36	32	38	33	29	33	30	27	24
8	57	45	37	32	54	43	36	31	38	33	28	35	30	26	31	27	24	22
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	25	22	20
10	50	38	31	26	47	36	29	25	33	27	23	29	25	21	26	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15998	15998	15998	15998
5°	18556	16046	14182	16046
10°	21952	15976	12658	15976
15°	25357	15828	10877	15828
20°	28233	15625	9836	15625
25°	29144	15425	9132	15425
30°	25513	15183	8708	15183
35°	19860	14824	8451	14824
40°	14893	14413	8313	14413
45°	11758	13755	8241	13755
50°	9927	12995	8002	12995
55°	8653	12159	7574	12159
60°	7786	11292	6704	11292
65°	6863	10355	5765	10355
70°	6182	9385	5202	9385
75°	5181	8319	4432	8319
80°	4379	7090	4156	7090
85°	3696	5548	3696	5548



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.0	2.4
10°-20°	579.2	7.3
20°-30°	905.9	11.5
30°-40°	1007.1	12.7
40°-50°	893.5	11.3
50°-60°	696.2	8.8
60°-70°	455.8	5.8
70°-80°	224.2	2.8
80°-90°	57.5	0.7
90°-100°	287.5	3.6
100°-110°	598.3	7.6
110°-120°	535.9	6.8
120°-130°	450.8	5.7
130°-140°	375.9	4.8
140°-150°	287.1	3.6
150°-160°	201.8	2.6
160°-170°	118.7	1.5
170°-180°	38.6	0.5
0°-30°	1677.1	21.2
0°-40°	2684.1	34.0
0°-60°	4273.8	54.1
0°-90°	5011.3	63.4
90°-120°	1421.6	18.0
90°-150°	2535.4	32.1
90°-180°	2895.0	36.6
0°-180°	7905.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1982	1982	1982	1982	1982	
5°	2290	1980	1750	1980	2290	232
15°	3034	1894	1301	1894	3034	863
25°	3272	1732	1025	1732	3272	1452
35°	2015	1504	858	1504	2015	1263
45°	1030	1205	722	1205	1030	816
55°	615	864	538	864	615	559
65°	359	542	302	542	359	361
75°	166	267	142	267	166	183
85°	40	60	40	60	40	45
90°	16	1	16	1	16	15
95°	191	26	191	26	191	296
105°	1100	92	1100	92	1100	1088
115°	1056	161	1056	161	1056	1049
125°	843	224	843	224	843	766
135°	754	267	754	267	754	582
145°	615	307	615	307	615	390
155°	515	350	515	350	515	240
165°	450	381	450	381	450	129
175°	405	397	405	397	405	39
180°	398	398	398	398	398	



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2090.2	2096.0	2090.2	2089.6	2083.2	2081.3	2078.7	2070.4	2055.1	2046.2	2048.1
5°	2289.8	2309.8	2298.6	2297.0	2279.5	2261.9	2250.7	2225.2	2198.0	2179.7	2164.5
7.5°	2520.7	2532.2	2525.2	2514.0	2485.6	2469.5	2443.6	2409.9	2361.2	2324.0	2290.0
10°	2677.9	2687.4	2684.3	2663.5	2642.7	2600.4	2576.5	2529.4	2467.9	2419.2	2373.7
12.5°	2832.4	2842.7	2814.6	2815.5	2776.2	2742.9	2704.9	2645.6	2574.6	2511.8	2454.8
15°	3034.0	3021.2	3021.2	3005.2	2961.3	2915.0	2875.9	2813.6	2724.2	2649.1	2570.1
17.5°	3191.7	3196.2	3189.6	3152.0	3117.5	3069.6	2997.9	2925.2	2842.2	2741.4	2660.6
20°	3286.3	3286.3	3279.1	3253.5	3208.8	3157.7	3080.3	3001.2	2895.8	2794.4	2703.4
22.5°	3324.6	3327.1	3318.7	3297.6	3257.4	3207.5	3141.6	3061.3	2952.7	2838.5	2725.8
25°	3271.9	3287.1	3288.6	3283.1	3271.1	3240.7	3184.1	3101.8	3004.4	2880.7	2759.3
27.5°	3003.9	3023.1	3039.9	3067.5	3104.2	3123.4	3125.9	3084.1	2999.1	2880.0	2757.9
30°	2736.9	2752.9	2804.8	2872.7	2925.4	2973.3	3014.8	3026.0	2978.1	2871.1	2742.5
32.5°	2440.6	2462.3	2514.2	2587.2	2675.0	2756.1	2849.4	2896.9	2895.7	2831.5	2712.5
35°	2015.2	2031.2	2079.1	2155.7	2261.1	2381.7	2529.4	2644.3	2722.6	2717.0	2644.3
37.5°	1625.2	1643.3	1691.7	1755.2	1857.4	2006.7	2149.6	2308.0	2452.7	2534.0	2509.7
40°	1413.2	1414.0	1461.1	1526.6	1622.4	1752.5	1908.2	2083.8	2245.1	2376.9	2402.4
42.5°	1245.8	1246.0	1277.1	1347.7	1416.7	1539.2	1687.8	1862.2	2051.0	2203.1	2270.8
45°	1029.9	1037.1	1062.7	1105.0	1159.3	1263.1	1382.0	1544.1	1755.7	1936.1	2048.7
47.5°	872.2	882.7	899.0	933.5	976.8	1045.9	1144.3	1289.9	1462.0	1660.5	1820.7
50°	790.4	792.0	812.8	831.9	869.5	924.6	1010.8	1132.1	1290.2	1481.0	1659.1
52.5°	720.2	719.8	732.3	756.6	787.1	830.0	899.6	1010.1	1150.3	1321.4	1505.2
55°	614.8	618.8	628.3	647.5	670.7	701.0	756.1	839.1	949.3	1095.4	1262.3
57.5°	534.6	536.7	544.2	552.3	573.6	595.6	637.0	694.6	787.6	907.2	1062.7
60°	482.2	483.0	485.4	497.4	514.2	534.9	562.9	611.6	689.8	799.2	922.2
62.5°	431.1	432.6	436.3	445.0	458.0	472.3	501.6	540.7	605.5	698.9	809.7
65°	359.3	360.1	365.7	368.9	379.2	392.0	413.6	439.9	484.6	562.9	646.7
67.5°	300.2	300.2	300.5	304.8	312.0	320.5	333.4	354.5	388.2	436.3	510.2
70°	261.9	261.9	263.5	265.9	269.9	277.0	284.2	300.2	325.0	364.1	420.8
72.5°	226.1	226.7	228.3	228.8	230.9	236.8	242.1	252.3	270.7	300.2	346.0
75°	166.1	168.5	172.5	175.7	179.6	178.8	184.4	190.8	196.4	214.0	240.3
77.5°	123.6	122.3	122.8	125.5	126.0	126.8	130.8	135.7	139.9	148.2	157.6
80°	94.2	94.2	96.6	97.4	96.6	97.4	101.4	103.8	105.4	108.6	117.4
82.5°	71.2	72.5	71.7	72.5	73.0	73.8	77.1	77.6	79.2	80.5	84.2
85°	39.9	40.7	41.5	39.9	39.9	39.9	41.5	42.3	43.9	43.1	44.7
87.5°	17.3	16.7	17.5	17.3	17.8	17.2	17.7	18.8	17.3	18.1	17.8
90°	16.4	16.4	17.2	16.4	15.6	15.6	14.9	14.1	13.3	14.1	12.5
92.5°	60.2	60.2	62.9	67.1	76.3	92.0	115.6	153.6	206.6	248.0	217.1
95°	190.8	201.0	215.0	239.3	277.6	353.4	458.2	579.4	655.3	637.3	480.9
97.5°	510.0	526.2	549.7	596.8	652.9	734.5	811.0	856.0	823.2	671.2	450.1
100°	717.0	723.3	746.7	794.4	862.5	920.3	958.6	943.0	828.8	628.7	408.2
102.5°	897.2	902.2	926.9	961.5	1003.2	1027.3	1016.2	938.6	781.9	575.5	380.0
105°	1100.2	1104.9	1115.8	1122.1	1120.5	1088.4	1011.0	875.8	696.7	512.9	355.8
107.5°	1175.5	1173.5	1165.7	1147.9	1109.2	1039.5	930.5	786.5	627.9	477.9	351.4
110°	1176.8	1169.8	1155.7	1122.8	1067.3	981.3	867.9	732.7	593.5	466.0	352.6



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1139.9	1128.5	1108.8	1069.0	1006.0	920.0	812.9	693.3	574.1	460.4	356.4
115°	1056.4	1050.1	1025.1	978.2	916.4	841.3	749.9	653.7	555.9	457.4	363.6
117.5°	971.8	966.9	941.6	902.2	849.5	785.8	713.9	634.3	547.8	456.6	371.3
120°	924.2	915.6	895.3	860.9	816.3	760.8	698.3	625.5	543.4	456.6	376.9
122.5°	886.7	878.1	860.9	831.5	793.8	745.2	688.2	618.0	538.4	456.0	382.5
125°	842.9	838.2	823.4	800.7	769.4	726.4	672.5	605.2	530.1	455.1	391.0
127.5°	817.3	812.6	800.1	779.9	748.5	707.6	653.8	589.6	519.0	453.4	397.7
130°	802.3	797.6	785.1	765.5	733.4	692.0	638.8	577.1	512.2	452.7	402.7
132.5°	785.4	780.7	768.8	746.7	715.3	673.9	621.9	563.9	505.9	452.1	407.1
135°	753.8	749.1	736.6	714.7	683.4	644.3	596.6	545.8	496.5	451.2	413.6
137.5°	714.7	709.0	698.7	677.1	647.9	612.6	572.4	529.4	488.4	451.0	417.5
140°	686.5	680.3	669.3	652.1	624.8	591.9	556.7	520.0	484.0	450.4	420.7
142.5°	656.5	652.1	642.4	626.5	602.2	573.8	543.6	511.2	480.3	450.4	423.2
145°	615.4	611.5	603.6	590.4	570.8	548.9	525.5	498.9	473.8	448.8	424.6
147.5°	578.9	577.5	571.6	560.2	545.8	528.6	509.8	488.7	468.1	446.0	425.4
150°	558.3	557.5	552.8	542.7	530.1	516.1	500.4	482.4	463.7	444.1	425.4
152.5°	539.5	538.7	535.9	527.6	517.0	505.4	491.0	475.6	458.7	441.0	424.1
155°	515.3	515.3	512.9	506.7	498.9	489.5	477.8	465.2	451.2	436.3	422.2
157.5°	494.0	494.0	492.6	487.9	482.0	474.5	464.6	454.1	443.5	431.5	420.2
160°	480.9	480.9	480.1	475.4	470.7	464.5	455.9	447.3	437.9	427.7	418.3
162.5°	468.4	469.0	468.2	463.5	460.1	454.5	447.7	440.4	432.9	424.0	416.5
165°	449.6	450.4	451.2	448.0	444.9	441.0	435.5	430.8	424.6	418.3	412.9
167.5°	434.7	435.4	435.5	433.5	431.9	429.6	425.2	421.6	417.1	412.7	409.1
170°	425.4	425.4	426.1	425.4	423.8	421.5	418.3	416.0	412.1	408.9	406.6
172.5°	416.0	417.2	418.0	417.2	416.3	414.6	412.7	411.0	407.7	405.2	404.1
175°	405.0	406.6	408.2	406.6	406.6	406.6	405.0	404.3	402.7	401.1	401.1
177.5°	398.6	399.9	401.1	400.5	401.1	400.5	400.5	399.9	399.2	398.6	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2041.7	2032.8	2028.3	2018.1	2005.9	1999.5	1993.8	1985.5	1974.6	1963.1	1954.8
5°	2145.3	2126.2	2102.2	2073.5	2047.9	2023.2	2001.6	1980.1	1955.3	1929.8	1904.2
7.5°	2251.7	2214.0	2173.3	2126.2	2080.3	2038.7	2000.3	1963.6	1922.1	1884.9	1851.0
10°	2325.8	2274.7	2218.0	2158.1	2098.2	2046.3	1995.2	1948.9	1897.8	1852.3	1814.0
12.5°	2385.8	2325.8	2257.6	2183.0	2111.0	2048.2	1989.5	1929.1	1871.0	1821.7	1770.6
15°	2485.4	2403.2	2311.4	2222.0	2128.6	2043.1	1964.1	1893.8	1827.6	1758.1	1709.4
17.5°	2554.0	2456.4	2344.8	2237.3	2127.0	2026.2	1935.0	1851.4	1774.9	1704.0	1646.0
20°	2594.8	2487.0	2363.3	2241.1	2117.4	2009.6	1911.4	1818.8	1739.7	1663.1	1603.2
22.5°	2617.8	2498.5	2363.3	2235.4	2107.2	1990.4	1882.6	1786.2	1700.1	1623.5	1557.2
25°	2625.2	2497.4	2359.3	2212.4	2071.9	1948.1	1836.3	1731.7	1635.9	1559.3	1489.0
27.5°	2615.0	2464.5	2323.1	2172.3	2027.3	1896.9	1779.5	1669.6	1573.7	1491.4	1419.4
30°	2599.6	2438.3	2286.6	2130.2	1983.2	1857.9	1734.1	1628.8	1529.0	1443.5	1370.9
32.5°	2566.4	2406.4	2243.2	2082.9	1934.1	1804.9	1687.5	1581.5	1483.6	1396.3	1319.1
35°	2500.6	2338.5	2161.3	1996.8	1850.7	1716.6	1606.4	1504.2	1410.8	1317.4	1235.9
37.5°	2413.9	2248.3	2072.0	1891.9	1745.6	1619.0	1517.9	1422.0	1330.8	1245.5	1155.3
40°	2332.2	2181.3	1999.2	1820.4	1670.3	1548.1	1454.7	1367.7	1275.9	1191.2	1101.0
42.5°	2233.2	2104.6	1920.7	1741.2	1593.0	1475.3	1388.3	1303.2	1219.7	1137.6	1043.5
45°	2067.9	1970.5	1798.0	1625.6	1476.3	1359.7	1279.9	1204.8	1131.3	1053.1	964.5
47.5°	1878.5	1812.5	1663.7	1487.1	1349.0	1244.1	1167.0	1105.6	1043.5	965.3	887.5
50°	1746.9	1704.6	1560.9	1399.6	1267.9	1171.3	1092.2	1034.7	982.8	907.8	838.3
52.5°	1606.4	1583.9	1462.5	1308.3	1181.0	1086.3	1018.8	967.0	914.5	852.2	787.2
55°	1392.4	1404.4	1301.4	1168.1	1048.3	968.5	907.0	863.9	819.2	766.5	716.2
57.5°	1173.7	1217.4	1148.3	1031.2	919.0	845.2	798.9	762.6	725.1	681.4	638.4
60°	1042.7	1079.4	1040.3	937.3	839.1	770.5	727.4	699.4	661.9	622.0	589.2
62.5°	915.0	954.3	931.1	847.9	756.7	697.7	659.6	633.6	605.7	570.9	536.9
65°	754.5	780.0	768.9	711.4	646.7	596.4	561.3	542.1	516.6	491.0	460.7
67.5°	577.9	627.2	620.7	590.2	534.3	495.0	472.0	455.1	431.8	412.8	392.2
70°	475.1	520.6	519.8	495.0	464.7	427.9	412.0	397.6	376.8	358.5	341.7
72.5°	388.8	430.5	436.7	417.7	397.0	369.2	353.9	344.0	323.8	311.2	297.6
75°	272.3	302.6	310.6	310.6	301.0	286.6	273.1	266.7	252.3	241.1	233.1
77.5°	178.5	197.7	210.1	213.0	214.5	209.7	198.5	194.0	183.0	179.0	171.3
80°	126.1	138.9	153.3	158.1	162.1	160.5	155.7	152.5	142.1	138.1	134.9
82.5°	87.2	94.2	106.0	116.6	115.4	119.6	115.4	112.9	105.1	103.6	100.4
85°	45.5	46.3	47.9	55.1	59.1	60.7	61.5	59.9	57.5	57.5	51.9
87.5°	17.5	16.9	17.2	17.2	17.7	20.1	21.5	21.9	20.3	18.8	17.1
90°	10.9	10.9	6.3	6.3	5.5	4.7	2.3	0.8	2.3	4.7	5.5
92.5°	157.9	97.3	57.5	41.3	29.9	20.3	13.0	8.9	13.0	20.3	29.9
95°	294.0	165.8	97.7	64.9	46.1	36.0	28.1	25.8	28.1	36.0	46.1
97.5°	264.3	158.4	106.0	78.5	62.4	53.0	46.3	46.3	46.3	53.0	62.4
100°	248.7	160.3	114.2	89.1	74.3	64.9	59.4	59.4	59.4	64.9	74.3
102.5°	244.3	166.5	124.8	101.0	86.8	78.0	73.2	71.9	73.2	78.0	86.8
105°	246.3	181.4	143.9	121.2	107.1	97.7	93.8	91.5	93.8	97.7	107.1
107.5°	257.9	198.8	164.4	142.0	128.5	118.5	114.6	113.1	114.6	118.5	128.5
110°	266.6	211.9	177.5	156.4	142.3	132.9	129.0	127.5	129.0	132.9	142.3



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	276.0	224.4	191.3	170.1	156.1	147.3	142.8	141.2	142.8	147.3	156.1
115°	290.9	244.0	212.7	191.6	176.7	168.9	163.4	161.1	163.4	168.9	176.7
117.5°	306.0	262.9	233.2	211.3	197.4	188.8	183.9	181.7	183.9	188.8	197.4
120°	316.7	276.0	246.3	224.4	211.1	202.5	197.0	195.5	197.0	202.5	211.1
122.5°	326.7	288.5	258.8	237.5	223.0	215.0	209.6	208.0	209.6	215.0	223.0
125°	341.7	305.7	277.6	255.7	240.8	232.2	227.5	224.4	227.5	232.2	240.8
127.5°	354.7	321.7	294.5	272.4	256.9	247.1	241.5	239.0	241.5	247.1	256.9
130°	362.8	332.3	305.7	283.1	268.2	256.5	250.2	247.1	250.2	256.5	268.2
132.5°	370.9	341.1	314.5	293.1	277.0	265.9	257.7	255.2	257.7	265.9	277.0
135°	381.6	353.4	327.6	307.3	290.9	277.6	269.8	266.6	269.8	277.6	290.9
137.5°	389.1	362.8	338.7	319.3	302.3	289.6	281.0	278.1	281.0	289.6	302.3
140°	394.1	369.1	345.6	326.8	310.4	297.1	288.5	286.2	288.5	297.1	310.4
142.5°	397.8	374.7	351.9	333.7	317.9	305.3	297.3	294.9	297.3	305.3	317.9
145°	401.9	380.8	360.5	343.3	328.4	317.5	309.6	307.3	309.6	317.5	328.4
147.5°	405.5	387.1	368.0	352.5	340.1	328.9	322.0	321.2	322.0	328.9	340.1
150°	407.4	390.2	373.0	358.1	346.4	337.0	330.8	330.0	330.8	337.0	346.4
152.5°	408.6	392.7	377.4	363.8	353.3	344.5	338.3	338.1	338.3	344.5	353.3
155°	409.7	396.4	383.1	371.4	362.8	355.0	350.3	349.5	350.3	355.0	362.8
157.5°	409.7	399.1	387.8	378.6	371.1	365.0	360.6	360.6	360.6	365.0	371.1
160°	409.7	400.3	391.0	382.4	376.1	370.6	367.5	367.5	367.5	370.6	376.1
162.5°	409.7	401.6	392.8	386.1	380.5	375.6	373.1	373.8	373.1	375.6	380.5
165°	408.2	401.9	394.9	390.2	386.3	382.4	380.8	380.8	380.8	382.4	386.3
167.5°	406.3	401.8	396.6	393.0	390.8	387.8	387.1	387.8	387.1	387.8	390.8
170°	405.0	401.1	397.2	394.9	393.3	391.0	390.2	391.0	390.2	391.0	393.3
172.5°	403.8	400.5	397.8	396.1	395.2	393.5	393.3	394.1	393.3	393.5	395.2
175°	401.9	399.6	398.0	398.0	397.2	396.4	396.4	397.2	396.4	396.4	397.2
177.5°	399.9	398.6	398.0	398.0	398.0	397.4	398.0	398.6	398.0	397.4	398.0
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1945.9	1939.5	1931.2	1921.6	1910.1	1899.9	1895.4	1899.3	1901.2	1896.1	1895.4
5°	1886.6	1866.7	1850.7	1826.8	1807.6	1791.6	1780.5	1775.7	1777.3	1764.5	1761.3
7.5°	1820.1	1796.4	1770.2	1741.8	1715.3	1691.8	1679.5	1672.8	1659.3	1653.5	1643.8
10°	1777.3	1745.3	1719.8	1686.2	1655.9	1628.0	1614.4	1603.2	1589.6	1583.2	1569.7
12.5°	1733.2	1696.1	1668.0	1633.2	1602.2	1568.6	1555.6	1534.9	1513.6	1500.2	1482.8
15°	1671.1	1626.4	1592.0	1550.5	1513.8	1475.5	1441.1	1402.8	1388.4	1358.1	1340.5
17.5°	1598.4	1553.1	1510.6	1454.9	1398.2	1350.6	1314.0	1277.3	1255.3	1235.9	1227.0
20°	1550.5	1509.0	1449.9	1385.2	1322.2	1269.5	1239.9	1216.0	1192.0	1178.5	1168.9
22.5°	1505.2	1452.1	1383.5	1313.7	1250.6	1209.4	1184.4	1159.8	1140.3	1127.4	1114.6
25°	1429.2	1359.7	1287.0	1207.2	1164.1	1128.2	1101.0	1081.0	1069.1	1052.3	1045.9
27.5°	1351.1	1266.9	1186.8	1133.1	1088.2	1055.3	1031.7	1016.7	1001.5	990.8	982.5
30°	1291.0	1205.6	1133.7	1082.6	1037.1	1010.0	990.8	973.3	961.3	952.5	946.1
32.5°	1231.6	1146.2	1085.8	1030.9	995.0	968.5	948.0	934.9	925.5	914.2	910.3
35°	1145.7	1069.9	1017.2	967.7	930.9	907.0	891.0	877.5	869.5	866.3	863.9
37.5°	1063.2	1001.0	944.4	903.8	871.1	852.2	833.4	826.7	821.2	815.5	818.1
40°	1010.8	952.5	902.2	859.1	832.7	812.0	800.8	792.8	788.0	788.0	788.0
42.5°	965.4	908.4	859.4	820.8	794.4	776.9	764.4	757.7	756.1	755.5	759.3
45°	895.0	842.3	792.8	760.9	738.5	721.0	713.8	708.2	708.2	711.4	712.2
47.5°	825.2	775.9	736.1	700.4	679.9	668.9	662.7	659.8	660.1	663.3	667.0
50°	782.4	733.7	694.6	662.7	643.5	633.1	627.5	626.0	627.5	627.5	633.1
52.5°	735.8	692.2	653.7	626.9	605.2	595.5	592.4	590.2	591.1	593.7	596.1
55°	667.5	628.3	591.6	566.1	550.1	543.7	536.5	537.3	535.7	537.3	537.3
57.5°	599.0	563.8	529.7	509.4	495.3	486.1	478.2	480.5	478.1	477.8	476.5
60°	554.9	516.6	489.4	471.1	455.1	447.1	439.9	441.5	439.1	437.5	434.3
62.5°	507.0	475.1	449.2	431.5	418.7	409.4	402.2	400.6	395.1	389.6	382.6
65°	437.5	411.2	388.0	371.3	359.3	352.1	346.5	341.7	329.7	317.0	310.6
67.5°	370.0	351.0	329.4	315.2	305.5	296.1	285.4	277.2	266.0	259.0	255.0
70°	326.5	308.2	289.8	276.2	265.9	257.1	245.1	239.5	231.5	228.3	224.4
72.5°	285.0	267.9	250.9	238.6	227.5	220.7	211.3	205.7	202.2	200.9	196.9
75°	222.0	208.4	195.6	184.4	175.7	170.9	166.9	162.9	161.3	154.1	150.1
77.5°	161.9	153.0	145.0	137.0	130.8	127.6	119.9	115.3	112.6	109.2	108.4
80°	126.1	119.8	111.8	107.0	98.2	95.0	91.8	91.0	90.2	89.4	88.6
82.5°	94.9	88.5	80.5	77.6	75.2	73.3	71.4	70.6	69.8	70.3	70.1
85°	47.9	44.7	44.7	43.9	43.1	42.3	41.5	41.5	40.7	41.5	40.7
87.5°	17.2	16.6	17.5	16.2	17.2	17.5	16.7	16.9	17.7	16.5	16.5
90°	6.3	6.3	10.9	10.9	12.5	14.1	13.3	14.1	14.9	15.6	15.6
92.5°	41.3	57.5	97.3	157.9	217.1	248.0	206.6	153.6	115.6	92.0	76.3
95°	64.9	97.7	165.8	294.0	480.9	637.3	655.3	579.4	458.2	353.4	277.6
97.5°	78.5	106.0	158.4	264.3	450.1	671.2	823.2	856.0	811.0	734.5	652.9
100°	89.1	114.2	160.3	248.7	408.2	628.7	828.8	943.0	958.6	920.3	862.5
102.5°	101.0	124.8	166.5	244.3	380.0	575.5	781.9	938.6	1016.2	1027.3	1003.2
105°	121.2	143.9	181.4	246.3	355.8	512.9	696.7	875.8	1011.0	1088.4	1120.5
107.5°	142.0	164.4	198.8	257.9	351.4	477.9	627.9	786.5	930.5	1039.5	1109.2
110°	156.4	177.5	211.9	266.6	352.6	466.0	593.5	732.7	867.9	981.3	1067.3



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.1	191.3	224.4	276.0	356.4	460.4	574.1	693.3	812.9	920.0	1006.0
115°	191.6	212.7	244.0	290.9	363.6	457.4	555.9	653.7	749.9	841.3	916.4
117.5°	211.3	233.2	262.9	306.0	371.3	456.6	547.8	634.3	713.9	785.8	849.5
120°	224.4	246.3	276.0	316.7	376.9	456.6	543.4	625.5	698.3	760.8	816.3
122.5°	237.5	258.8	288.5	326.7	382.5	456.0	538.4	618.0	688.2	745.2	793.8
125°	255.7	277.6	305.7	341.7	391.0	455.1	530.1	605.2	672.5	726.4	769.4
127.5°	272.4	294.5	321.7	354.7	397.7	453.4	519.0	589.6	653.8	707.6	748.5
130°	283.1	305.7	332.3	362.8	402.7	452.7	512.2	577.1	638.8	692.0	733.4
132.5°	293.1	314.5	341.1	370.9	407.1	452.1	505.9	563.9	621.9	673.9	715.3
135°	307.3	327.6	353.4	381.6	413.6	451.2	496.5	545.8	596.6	644.3	683.4
137.5°	319.3	338.7	362.8	389.1	417.5	451.0	488.4	529.4	572.4	612.6	647.9
140°	326.8	345.6	369.1	394.1	420.7	450.4	484.0	520.0	556.7	591.9	624.8
142.5°	333.7	351.9	374.7	397.8	423.2	450.4	480.3	511.2	543.6	573.8	602.2
145°	343.3	360.5	380.8	401.9	424.6	448.8	473.8	498.9	525.5	548.9	570.8
147.5°	352.5	368.0	387.1	405.5	425.4	446.0	468.1	488.7	509.8	528.6	545.8
150°	358.1	373.0	390.2	407.4	425.4	444.1	463.7	482.4	500.4	516.1	530.1
152.5°	363.8	377.4	392.7	408.6	424.1	441.0	458.7	475.6	491.0	505.4	517.0
155°	371.4	383.1	396.4	409.7	422.2	436.3	451.2	465.2	477.8	489.5	498.9
157.5°	378.6	387.8	399.1	409.7	420.2	431.5	443.5	454.1	464.6	474.5	482.0
160°	382.4	391.0	400.3	409.7	418.3	427.7	437.9	447.3	455.9	464.5	470.7
162.5°	386.1	392.8	401.6	409.7	416.5	424.0	432.9	440.4	447.7	454.5	460.1
165°	390.2	394.9	401.9	408.2	412.9	418.3	424.6	430.8	435.5	441.0	444.9
167.5°	393.0	396.6	401.8	406.3	409.1	412.7	417.1	421.6	425.2	429.6	431.9
170°	394.9	397.2	401.1	405.0	406.6	408.9	412.1	416.0	418.3	421.5	423.8
172.5°	396.1	397.8	400.5	403.8	404.1	405.2	407.7	411.0	412.7	414.6	416.3
175°	398.0	398.0	399.6	401.9	401.1	401.1	402.7	404.3	405.0	406.6	406.6
177.5°	398.0	398.0	398.6	399.9	398.6	398.6	399.2	399.9	400.5	400.5	401.1
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1891.6	1892.9	1888.4	1887.1	1888.4	1892.9	1891.6	1895.4	1896.1	1901.2	1899.3
5°	1754.9	1753.3	1749.3	1750.1	1749.3	1753.3	1754.9	1761.3	1764.5	1777.3	1775.7
7.5°	1638.0	1631.8	1633.5	1627.2	1633.5	1631.8	1638.0	1643.8	1653.5	1659.3	1672.8
10°	1566.5	1557.7	1550.5	1544.1	1550.5	1557.7	1566.5	1569.7	1583.2	1589.6	1603.2
12.5°	1468.8	1461.2	1451.5	1453.4	1451.5	1461.2	1468.8	1482.8	1500.2	1513.6	1534.9
15°	1330.1	1318.2	1299.0	1301.4	1299.0	1318.2	1330.1	1340.5	1358.1	1388.4	1402.8
17.5°	1212.8	1212.9	1204.2	1206.2	1204.2	1212.9	1212.8	1227.0	1235.9	1255.3	1277.3
20°	1152.1	1146.5	1147.3	1144.9	1147.3	1146.5	1152.1	1168.9	1178.5	1192.0	1216.0
22.5°	1109.9	1103.1	1097.5	1092.5	1097.5	1103.1	1109.9	1114.6	1127.4	1140.3	1159.8
25°	1038.7	1033.9	1026.8	1025.2	1026.8	1033.9	1038.7	1045.9	1052.3	1069.1	1081.0
27.5°	976.1	975.2	972.3	968.6	972.3	975.2	976.1	982.5	990.8	1001.5	1016.7
30°	939.7	938.1	936.5	934.1	936.5	938.1	939.7	946.1	952.5	961.3	973.3
32.5°	907.2	906.2	904.6	904.8	904.6	906.2	907.2	910.3	914.2	925.5	934.9
35°	860.7	859.9	858.3	857.5	858.3	859.9	860.7	863.9	866.3	869.5	877.5
37.5°	817.3	819.3	818.4	818.2	818.4	819.3	817.3	818.1	815.5	821.2	826.7
40°	787.2	788.0	789.6	788.8	789.6	788.0	787.2	788.0	788.0	788.0	792.8
42.5°	762.3	762.5	764.7	762.0	764.7	762.5	762.3	759.3	755.5	756.1	757.7
45°	717.8	722.6	721.8	721.8	721.8	722.6	717.8	712.2	711.4	708.2	708.2
47.5°	669.1	673.2	674.3	674.2	674.3	673.2	669.1	667.0	663.3	660.1	659.8
50°	637.1	635.5	637.9	637.1	637.9	635.5	637.1	633.1	627.5	627.5	626.0
52.5°	598.2	598.5	598.3	597.5	598.3	598.5	598.2	596.1	593.7	591.1	590.2
55°	538.1	538.9	537.3	538.1	537.3	538.9	538.1	537.3	537.3	535.7	537.3
57.5°	473.0	469.1	470.7	468.8	470.7	469.1	473.0	476.5	477.8	478.1	480.5
60°	426.4	420.0	418.4	415.2	418.4	420.0	426.4	434.3	437.5	439.1	441.5
62.5°	374.0	369.5	364.1	366.6	364.1	369.5	374.0	382.6	389.6	395.1	400.6
65°	304.2	301.0	298.6	301.8	298.6	301.0	304.2	310.6	317.0	329.7	341.7
67.5°	251.8	250.1	250.1	248.5	250.1	250.1	251.8	255.0	259.0	266.0	277.2
70°	224.4	222.0	222.0	220.4	222.0	222.0	224.4	224.4	228.3	231.5	239.5
72.5°	196.2	193.9	194.5	193.5	194.5	193.9	196.2	196.9	200.9	202.2	205.7
75°	145.3	141.3	141.3	142.1	141.3	141.3	145.3	150.1	154.1	161.3	162.9
77.5°	108.4	107.6	108.7	107.3	108.7	107.6	108.4	108.4	109.2	112.6	115.3
80°	88.6	87.8	87.0	89.4	87.0	87.8	88.6	88.6	89.4	90.2	91.0
82.5°	68.8	68.7	68.5	71.5	68.5	68.7	68.8	70.1	70.3	69.8	70.6
85°	41.5	39.9	41.5	39.9	41.5	39.9	41.5	40.7	41.5	40.7	41.5
87.5°	18.0	17.5	16.7	17.3	16.7	17.5	18.0	16.5	16.5	17.7	16.9
90°	16.4	17.2	16.4	16.4	16.4	17.2	16.4	15.6	15.6	14.9	14.1
92.5°	67.1	62.9	60.2	60.2	60.2	62.9	67.1	76.3	92.0	115.6	153.6
95°	239.3	215.0	201.0	190.8	201.0	215.0	239.3	277.6	353.4	458.2	579.4
97.5°	596.8	549.7	526.2	510.0	526.2	549.7	596.8	652.9	734.5	811.0	856.0
100°	794.4	746.7	723.3	717.0	723.3	746.7	794.4	862.5	920.3	958.6	943.0
102.5°	961.5	926.9	902.2	897.2	902.2	926.9	961.5	1003.2	1027.3	1016.2	938.6
105°	1122.1	1115.8	1104.9	1100.2	1104.9	1115.8	1122.1	1120.5	1088.4	1011.0	875.8
107.5°	1147.9	1165.7	1173.5	1175.5	1173.5	1165.7	1147.9	1109.2	1039.5	930.5	786.5
110°	1122.8	1155.7	1169.8	1176.8	1169.8	1155.7	1122.8	1067.3	981.3	867.9	732.7



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1069.0	1108.8	1128.5	1139.9	1128.5	1108.8	1069.0	1006.0	920.0	812.9	693.3
115°	978.2	1025.1	1050.1	1056.4	1050.1	1025.1	978.2	916.4	841.3	749.9	653.7
117.5°	902.2	941.6	966.9	971.8	966.9	941.6	902.2	849.5	785.8	713.9	634.3
120°	860.9	895.3	915.6	924.2	915.6	895.3	860.9	816.3	760.8	698.3	625.5
122.5°	831.5	860.9	878.1	886.7	878.1	860.9	831.5	793.8	745.2	688.2	618.0
125°	800.7	823.4	838.2	842.9	838.2	823.4	800.7	769.4	726.4	672.5	605.2
127.5°	779.9	800.1	812.6	817.3	812.6	800.1	779.9	748.5	707.6	653.8	589.6
130°	765.5	785.1	797.6	802.3	797.6	785.1	765.5	733.4	692.0	638.8	577.1
132.5°	746.7	768.8	780.7	785.4	780.7	768.8	746.7	715.3	673.9	621.9	563.9
135°	714.7	736.6	749.1	753.8	749.1	736.6	714.7	683.4	644.3	596.6	545.8
137.5°	677.1	698.7	709.0	714.7	709.0	698.7	677.1	647.9	612.6	572.4	529.4
140°	652.1	669.3	680.3	686.5	680.3	669.3	652.1	624.8	591.9	556.7	520.0
142.5°	626.5	642.4	652.1	656.5	652.1	642.4	626.5	602.2	573.8	543.6	511.2
145°	590.4	603.6	611.5	615.4	611.5	603.6	590.4	570.8	548.9	525.5	498.9
147.5°	560.2	571.6	577.5	578.9	577.5	571.6	560.2	545.8	528.6	509.8	488.7
150°	542.7	552.8	557.5	558.3	557.5	552.8	542.7	530.1	516.1	500.4	482.4
152.5°	527.6	535.9	538.7	539.5	538.7	535.9	527.6	517.0	505.4	491.0	475.6
155°	506.7	512.9	515.3	515.3	515.3	512.9	506.7	498.9	489.5	477.8	465.2
157.5°	487.9	492.6	494.0	494.0	494.0	492.6	487.9	482.0	474.5	464.6	454.1
160°	475.4	480.1	480.9	480.9	480.9	480.1	475.4	470.7	464.5	455.9	447.3
162.5°	463.5	468.2	469.0	468.4	469.0	468.2	463.5	460.1	454.5	447.7	440.4
165°	448.0	451.2	450.4	449.6	450.4	451.2	448.0	444.9	441.0	435.5	430.8
167.5°	433.5	435.5	435.4	434.7	435.4	435.5	433.5	431.9	429.6	425.2	421.6
170°	425.4	426.1	425.4	425.4	425.4	426.1	425.4	423.8	421.5	418.3	416.0
172.5°	417.2	418.0	417.2	416.0	417.2	418.0	417.2	416.3	414.6	412.7	411.0
175°	406.6	408.2	406.6	405.0	406.6	408.2	406.6	406.6	406.6	405.0	404.3
177.5°	400.5	401.1	399.9	398.6	399.9	401.1	400.5	401.1	400.5	400.5	399.9
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1895.4	1899.9	1910.1	1921.6	1931.2	1939.5	1945.9	1954.8	1963.1	1974.6	1985.5
5°	1780.5	1791.6	1807.6	1826.8	1850.7	1866.7	1886.6	1904.2	1929.8	1955.3	1980.1
7.5°	1679.5	1691.8	1715.3	1741.8	1770.2	1796.4	1820.1	1851.0	1884.9	1922.1	1963.6
10°	1614.4	1628.0	1655.9	1686.2	1719.8	1745.3	1777.3	1814.0	1852.3	1897.8	1948.9
12.5°	1555.6	1568.6	1602.2	1633.2	1668.0	1696.1	1733.2	1770.6	1821.7	1871.0	1929.1
15°	1441.1	1475.5	1513.8	1550.5	1592.0	1626.4	1671.1	1709.4	1758.1	1827.6	1893.8
17.5°	1314.0	1350.6	1398.2	1454.9	1510.6	1553.1	1598.4	1646.0	1704.0	1774.9	1851.4
20°	1239.9	1269.5	1322.2	1385.2	1449.9	1509.0	1550.5	1603.2	1663.1	1739.7	1818.8
22.5°	1184.4	1209.4	1250.6	1313.7	1383.5	1452.1	1505.2	1557.2	1623.5	1700.1	1786.2
25°	1101.0	1128.2	1164.1	1207.2	1287.0	1359.7	1429.2	1489.0	1559.3	1635.9	1731.7
27.5°	1031.7	1055.3	1088.2	1133.1	1186.8	1266.9	1351.1	1419.4	1491.4	1573.7	1669.6
30°	990.8	1010.0	1037.1	1082.6	1133.7	1205.6	1291.0	1370.9	1443.5	1529.0	1628.8
32.5°	948.0	968.5	995.0	1030.9	1085.8	1146.2	1231.6	1319.1	1396.3	1483.6	1581.5
35°	891.0	907.0	930.9	967.7	1017.2	1069.9	1145.7	1235.9	1317.4	1410.8	1504.2
37.5°	833.4	852.2	871.1	903.8	944.4	1001.0	1063.2	1155.3	1245.5	1330.8	1422.0
40°	800.8	812.0	832.7	859.1	902.2	952.5	1010.8	1101.0	1191.2	1275.9	1367.7
42.5°	764.4	776.9	794.4	820.8	859.4	908.4	965.4	1043.5	1137.6	1219.7	1303.2
45°	713.8	721.0	738.5	760.9	792.8	842.3	895.0	964.5	1053.1	1131.3	1204.8
47.5°	662.7	668.9	679.9	700.4	736.1	775.9	825.2	887.5	965.3	1043.5	1105.6
50°	627.5	633.1	643.5	662.7	694.6	733.7	782.4	838.3	907.8	982.8	1034.7
52.5°	592.4	595.5	605.2	626.9	653.7	692.2	735.8	787.2	852.2	914.5	967.0
55°	536.5	543.7	550.1	566.1	591.6	628.3	667.5	716.2	766.5	819.2	863.9
57.5°	478.2	486.1	495.3	509.4	529.7	563.8	599.0	638.4	681.4	725.1	762.6
60°	439.9	447.1	455.1	471.1	489.4	516.6	554.9	589.2	622.0	661.9	699.4
62.5°	402.2	409.4	418.7	431.5	449.2	475.1	507.0	536.9	570.9	605.7	633.6
65°	346.5	352.1	359.3	371.3	388.0	411.2	437.5	460.7	491.0	516.6	542.1
67.5°	285.4	296.1	305.5	315.2	329.4	351.0	370.0	392.2	412.8	431.8	455.1
70°	245.1	257.1	265.9	276.2	289.8	308.2	326.5	341.7	358.5	376.8	397.6
72.5°	211.3	220.7	227.5	238.6	250.9	267.9	285.0	297.6	311.2	323.8	344.0
75°	166.9	170.9	175.7	184.4	195.6	208.4	222.0	233.1	241.1	252.3	266.7
77.5°	119.9	127.6	130.8	137.0	145.0	153.0	161.9	171.3	179.0	183.0	194.0
80°	91.8	95.0	98.2	107.0	111.8	119.8	126.1	134.9	138.1	142.1	152.5
82.5°	71.4	73.3	75.2	77.6	80.5	88.5	94.9	100.4	103.6	105.1	112.9
85°	41.5	42.3	43.1	43.9	44.7	44.7	47.9	51.9	57.5	57.5	59.9
87.5°	16.7	17.5	17.2	16.2	17.5	16.6	17.2	17.1	18.8	20.3	21.9
90°	13.3	14.1	12.5	10.9	10.9	6.3	6.3	5.5	4.7	2.3	0.8
92.5°	206.6	248.0	217.1	157.9	97.3	57.5	41.3	29.9	20.3	13.0	8.9
95°	655.3	637.3	480.9	294.0	165.8	97.7	64.9	46.1	36.0	28.1	25.8
97.5°	823.2	671.2	450.1	264.3	158.4	106.0	78.5	62.4	53.0	46.3	46.3
100°	828.8	628.7	408.2	248.7	160.3	114.2	89.1	74.3	64.9	59.4	59.4
102.5°	781.9	575.5	380.0	244.3	166.5	124.8	101.0	86.8	78.0	73.2	71.9
105°	696.7	512.9	355.8	246.3	181.4	143.9	121.2	107.1	97.7	93.8	91.5
107.5°	627.9	477.9	351.4	257.9	198.8	164.4	142.0	128.5	118.5	114.6	113.1
110°	593.5	466.0	352.6	266.6	211.9	177.5	156.4	142.3	132.9	129.0	127.5



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	574.1	460.4	356.4	276.0	224.4	191.3	170.1	156.1	147.3	142.8	141.2
115°	555.9	457.4	363.6	290.9	244.0	212.7	191.6	176.7	168.9	163.4	161.1
117.5°	547.8	456.6	371.3	306.0	262.9	233.2	211.3	197.4	188.8	183.9	181.7
120°	543.4	456.6	376.9	316.7	276.0	246.3	224.4	211.1	202.5	197.0	195.5
122.5°	538.4	456.0	382.5	326.7	288.5	258.8	237.5	223.0	215.0	209.6	208.0
125°	530.1	455.1	391.0	341.7	305.7	277.6	255.7	240.8	232.2	227.5	224.4
127.5°	519.0	453.4	397.7	354.7	321.7	294.5	272.4	256.9	247.1	241.5	239.0
130°	512.2	452.7	402.7	362.8	332.3	305.7	283.1	268.2	256.5	250.2	247.1
132.5°	505.9	452.1	407.1	370.9	341.1	314.5	293.1	277.0	265.9	257.7	255.2
135°	496.5	451.2	413.6	381.6	353.4	327.6	307.3	290.9	277.6	269.8	266.6
137.5°	488.4	451.0	417.5	389.1	362.8	338.7	319.3	302.3	289.6	281.0	278.1
140°	484.0	450.4	420.7	394.1	369.1	345.6	326.8	310.4	297.1	288.5	286.2
142.5°	480.3	450.4	423.2	397.8	374.7	351.9	333.7	317.9	305.3	297.3	294.9
145°	473.8	448.8	424.6	401.9	380.8	360.5	343.3	328.4	317.5	309.6	307.3
147.5°	468.1	446.0	425.4	405.5	387.1	368.0	352.5	340.1	328.9	322.0	321.2
150°	463.7	444.1	425.4	407.4	390.2	373.0	358.1	346.4	337.0	330.8	330.0
152.5°	458.7	441.0	424.1	408.6	392.7	377.4	363.8	353.3	344.5	338.3	338.1
155°	451.2	436.3	422.2	409.7	396.4	383.1	371.4	362.8	355.0	350.3	349.5
157.5°	443.5	431.5	420.2	409.7	399.1	387.8	378.6	371.1	365.0	360.6	360.6
160°	437.9	427.7	418.3	409.7	400.3	391.0	382.4	376.1	370.6	367.5	367.5
162.5°	432.9	424.0	416.5	409.7	401.6	392.8	386.1	380.5	375.6	373.1	373.8
165°	424.6	418.3	412.9	408.2	401.9	394.9	390.2	386.3	382.4	380.8	380.8
167.5°	417.1	412.7	409.1	406.3	401.8	396.6	393.0	390.8	387.8	387.1	387.8
170°	412.1	408.9	406.6	405.0	401.1	397.2	394.9	393.3	391.0	390.2	391.0
172.5°	407.7	405.2	404.1	403.8	400.5	397.8	396.1	395.2	393.5	393.3	394.1
175°	402.7	401.1	401.1	401.9	399.6	398.0	398.0	397.2	396.4	396.4	397.2
177.5°	399.2	398.6	398.6	399.9	398.6	398.0	398.0	398.0	397.4	398.0	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1993.8	1999.5	2005.9	2018.1	2028.3	2032.8	2041.7	2048.1	2046.2	2055.1	2070.4
5°	2001.6	2023.2	2047.9	2073.5	2102.2	2126.2	2145.3	2164.5	2179.7	2198.0	2225.2
7.5°	2000.3	2038.7	2080.3	2126.2	2173.3	2214.0	2251.7	2290.0	2324.0	2361.2	2409.9
10°	1995.2	2046.3	2098.2	2158.1	2218.0	2274.7	2325.8	2373.7	2419.2	2467.9	2529.4
12.5°	1989.5	2048.2	2111.0	2183.0	2257.6	2325.8	2385.8	2454.8	2511.8	2574.6	2645.6
15°	1964.1	2043.1	2128.6	2222.0	2311.4	2403.2	2485.4	2570.1	2649.1	2724.2	2813.6
17.5°	1935.0	2026.2	2127.0	2237.3	2344.8	2456.4	2554.0	2660.6	2741.4	2842.2	2925.2
20°	1911.4	2009.6	2117.4	2241.1	2363.3	2487.0	2594.8	2703.4	2794.4	2895.8	3001.2
22.5°	1882.6	1990.4	2107.2	2235.4	2363.3	2498.5	2617.8	2725.8	2838.5	2952.7	3061.3
25°	1836.3	1948.1	2071.9	2212.4	2359.3	2497.4	2625.2	2759.3	2880.7	3004.4	3101.8
27.5°	1779.5	1896.9	2027.3	2172.3	2323.1	2464.5	2615.0	2757.9	2880.0	2999.1	3084.1
30°	1734.1	1857.9	1983.2	2130.2	2286.6	2438.3	2599.6	2742.5	2871.1	2978.1	3026.0
32.5°	1687.5	1804.9	1934.1	2082.9	2243.2	2406.4	2566.4	2712.5	2831.5	2895.7	2896.9
35°	1606.4	1716.6	1850.7	1996.8	2161.3	2338.5	2500.6	2644.3	2717.0	2722.6	2644.3
37.5°	1517.9	1619.0	1745.6	1891.9	2072.0	2248.3	2413.9	2509.7	2534.0	2452.7	2308.0
40°	1454.7	1548.1	1670.3	1820.4	1999.2	2181.3	2332.2	2402.4	2376.9	2245.1	2083.8
42.5°	1388.3	1475.3	1593.0	1741.2	1920.7	2104.6	2233.2	2270.8	2203.1	2051.0	1862.2
45°	1279.9	1359.7	1476.3	1625.6	1798.0	1970.5	2067.9	2048.7	1936.1	1755.7	1544.1
47.5°	1167.0	1244.1	1349.0	1487.1	1663.7	1812.5	1878.5	1820.7	1660.5	1462.0	1289.9
50°	1092.2	1171.3	1267.9	1399.6	1560.9	1704.6	1746.9	1659.1	1481.0	1290.2	1132.1
52.5°	1018.8	1086.3	1181.0	1308.3	1462.5	1583.9	1606.4	1505.2	1321.4	1150.3	1010.1
55°	907.0	968.5	1048.3	1168.1	1301.4	1404.4	1392.4	1262.3	1095.4	949.3	839.1
57.5°	798.9	845.2	919.0	1031.2	1148.3	1217.4	1173.7	1062.7	907.2	787.6	694.6
60°	727.4	770.5	839.1	937.3	1040.3	1079.4	1042.7	922.2	799.2	689.8	611.6
62.5°	659.6	697.7	756.7	847.9	931.1	954.3	915.0	809.7	698.9	605.5	540.7
65°	561.3	596.4	646.7	711.4	768.9	780.0	754.5	646.7	562.9	484.6	439.9
67.5°	472.0	495.0	534.3	590.2	620.7	627.2	577.9	510.2	436.3	388.2	354.5
70°	412.0	427.9	464.7	495.0	519.8	520.6	475.1	420.8	364.1	325.0	300.2
72.5°	353.9	369.2	397.0	417.7	436.7	430.5	388.8	346.0	300.2	270.7	252.3
75°	273.1	286.6	301.0	310.6	310.6	302.6	272.3	240.3	214.0	196.4	190.8
77.5°	198.5	209.7	214.5	213.0	210.1	197.7	178.5	157.6	148.2	139.9	135.7
80°	155.7	160.5	162.1	158.1	153.3	138.9	126.1	117.4	108.6	105.4	103.8
82.5°	115.4	119.6	115.4	116.6	106.0	94.2	87.2	84.2	80.5	79.2	77.6
85°	61.5	60.7	59.1	55.1	47.9	46.3	45.5	44.7	43.1	43.9	42.3
87.5°	21.5	20.1	17.7	17.2	17.2	16.9	17.5	17.8	18.1	17.3	18.8
90°	2.3	4.7	5.5	6.3	6.3	10.9	10.9	12.5	14.1	13.3	14.1
92.5°	13.0	20.3	29.9	41.3	57.5	97.3	157.9	217.1	248.0	206.6	153.6
95°	28.1	36.0	46.1	64.9	97.7	165.8	294.0	480.9	637.3	655.3	579.4
97.5°	46.3	53.0	62.4	78.5	106.0	158.4	264.3	450.1	671.2	823.2	856.0
100°	59.4	64.9	74.3	89.1	114.2	160.3	248.7	408.2	628.7	828.8	943.0
102.5°	73.2	78.0	86.8	101.0	124.8	166.5	244.3	380.0	575.5	781.9	938.6
105°	93.8	97.7	107.1	121.2	143.9	181.4	246.3	355.8	512.9	696.7	875.8
107.5°	114.6	118.5	128.5	142.0	164.4	198.8	257.9	351.4	477.9	627.9	786.5
110°	129.0	132.9	142.3	156.4	177.5	211.9	266.6	352.6	466.0	593.5	732.7



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	142.8	147.3	156.1	170.1	191.3	224.4	276.0	356.4	460.4	574.1	693.3
115°	163.4	168.9	176.7	191.6	212.7	244.0	290.9	363.6	457.4	555.9	653.7
117.5°	183.9	188.8	197.4	211.3	233.2	262.9	306.0	371.3	456.6	547.8	634.3
120°	197.0	202.5	211.1	224.4	246.3	276.0	316.7	376.9	456.6	543.4	625.5
122.5°	209.6	215.0	223.0	237.5	258.8	288.5	326.7	382.5	456.0	538.4	618.0
125°	227.5	232.2	240.8	255.7	277.6	305.7	341.7	391.0	455.1	530.1	605.2
127.5°	241.5	247.1	256.9	272.4	294.5	321.7	354.7	397.7	453.4	519.0	589.6
130°	250.2	256.5	268.2	283.1	305.7	332.3	362.8	402.7	452.7	512.2	577.1
132.5°	257.7	265.9	277.0	293.1	314.5	341.1	370.9	407.1	452.1	505.9	563.9
135°	269.8	277.6	290.9	307.3	327.6	353.4	381.6	413.6	451.2	496.5	545.8
137.5°	281.0	289.6	302.3	319.3	338.7	362.8	389.1	417.5	451.0	488.4	529.4
140°	288.5	297.1	310.4	326.8	345.6	369.1	394.1	420.7	450.4	484.0	520.0
142.5°	297.3	305.3	317.9	333.7	351.9	374.7	397.8	423.2	450.4	480.3	511.2
145°	309.6	317.5	328.4	343.3	360.5	380.8	401.9	424.6	448.8	473.8	498.9
147.5°	322.0	328.9	340.1	352.5	368.0	387.1	405.5	425.4	446.0	468.1	488.7
150°	330.8	337.0	346.4	358.1	373.0	390.2	407.4	425.4	444.1	463.7	482.4
152.5°	338.3	344.5	353.3	363.8	377.4	392.7	408.6	424.1	441.0	458.7	475.6
155°	350.3	355.0	362.8	371.4	383.1	396.4	409.7	422.2	436.3	451.2	465.2
157.5°	360.6	365.0	371.1	378.6	387.8	399.1	409.7	420.2	431.5	443.5	454.1
160°	367.5	370.6	376.1	382.4	391.0	400.3	409.7	418.3	427.7	437.9	447.3
162.5°	373.1	375.6	380.5	386.1	392.8	401.6	409.7	416.5	424.0	432.9	440.4
165°	380.8	382.4	386.3	390.2	394.9	401.9	408.2	412.9	418.3	424.6	430.8
167.5°	387.1	387.8	390.8	393.0	396.6	401.8	406.3	409.1	412.7	417.1	421.6
170°	390.2	391.0	393.3	394.9	397.2	401.1	405.0	406.6	408.9	412.1	416.0
172.5°	393.3	393.5	395.2	396.1	397.8	400.5	403.8	404.1	405.2	407.7	411.0
175°	396.4	396.4	397.2	398.0	398.0	399.6	401.9	401.1	401.1	402.7	404.3
177.5°	398.0	397.4	398.0	398.0	398.0	398.6	399.9	398.6	398.6	399.2	399.9
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2078.7	2081.3	2083.2	2089.6	2090.2	2096.0	2090.2
5°	2250.7	2261.9	2279.5	2297.0	2298.6	2309.8	2289.8
7.5°	2443.6	2469.5	2485.6	2514.0	2525.2	2532.2	2520.7
10°	2576.5	2600.4	2642.7	2663.5	2684.3	2687.4	2677.9
12.5°	2704.9	2742.9	2776.2	2815.5	2814.6	2842.7	2832.4
15°	2875.9	2915.0	2961.3	3005.2	3021.2	3021.2	3034.0
17.5°	2997.9	3069.6	3117.5	3152.0	3189.6	3196.2	3191.7
20°	3080.3	3157.7	3208.8	3253.5	3279.1	3286.3	3286.3
22.5°	3141.6	3207.5	3257.4	3297.6	3318.7	3327.1	3324.6
25°	3184.1	3240.7	3271.1	3283.1	3288.6	3287.1	3271.9
27.5°	3125.9	3123.4	3104.2	3067.5	3039.9	3023.1	3003.9
30°	3014.8	2973.3	2925.4	2872.7	2804.8	2752.9	2736.9
32.5°	2849.4	2756.1	2675.0	2587.2	2514.2	2462.3	2440.6
35°	2529.4	2381.7	2261.1	2155.7	2079.1	2031.2	2015.2
37.5°	2149.6	2006.7	1857.4	1755.2	1691.7	1643.3	1625.2
40°	1908.2	1752.5	1622.4	1526.6	1461.1	1414.0	1413.2
42.5°	1687.8	1539.2	1416.7	1347.7	1277.1	1246.0	1245.8
45°	1382.0	1263.1	1159.3	1105.0	1062.7	1037.1	1029.9
47.5°	1144.3	1045.9	976.8	933.5	899.0	882.7	872.2
50°	1010.8	924.6	869.5	831.9	812.8	792.0	790.4
52.5°	899.6	830.0	787.1	756.6	732.3	719.8	720.2
55°	756.1	701.0	670.7	647.5	628.3	618.8	614.8
57.5°	637.0	595.6	573.6	552.3	544.2	536.7	534.6
60°	562.9	534.9	514.2	497.4	485.4	483.0	482.2
62.5°	501.6	472.3	458.0	445.0	436.3	432.6	431.1
65°	413.6	392.0	379.2	368.9	365.7	360.1	359.3
67.5°	333.4	320.5	312.0	304.8	300.5	300.2	300.2
70°	284.2	277.0	269.9	265.9	263.5	261.9	261.9
72.5°	242.1	236.8	230.9	228.8	228.3	226.7	226.1
75°	184.4	178.8	179.6	175.7	172.5	168.5	166.1
77.5°	130.8	126.8	126.0	125.5	122.8	122.3	123.6
80°	101.4	97.4	96.6	97.4	96.6	94.2	94.2
82.5°	77.1	73.8	73.0	72.5	71.7	72.5	71.2
85°	41.5	39.9	39.9	39.9	41.5	40.7	39.9
87.5°	17.7	17.2	17.8	17.3	17.5	16.7	17.3
90°	14.9	15.6	15.6	16.4	17.2	16.4	16.4
92.5°	115.6	92.0	76.3	67.1	62.9	60.2	60.2
95°	458.2	353.4	277.6	239.3	215.0	201.0	190.8
97.5°	811.0	734.5	652.9	596.8	549.7	526.2	510.0
100°	958.6	920.3	862.5	794.4	746.7	723.3	717.0
102.5°	1016.2	1027.3	1003.2	961.5	926.9	902.2	897.2
105°	1011.0	1088.4	1120.5	1122.1	1115.8	1104.9	1100.2
107.5°	930.5	1039.5	1109.2	1147.9	1165.7	1173.5	1175.5
110°	867.9	981.3	1067.3	1122.8	1155.7	1169.8	1176.8



TEST NUMBER: P332999

CATALOG NUMBER: SA4XXRDIP-C1195D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	812.9	920.0	1006.0	1069.0	1108.8	1128.5	1139.9
115°	749.9	841.3	916.4	978.2	1025.1	1050.1	1056.4
117.5°	713.9	785.8	849.5	902.2	941.6	966.9	971.8
120°	698.3	760.8	816.3	860.9	895.3	915.6	924.2
122.5°	688.2	745.2	793.8	831.5	860.9	878.1	886.7
125°	672.5	726.4	769.4	800.7	823.4	838.2	842.9
127.5°	653.8	707.6	748.5	779.9	800.1	812.6	817.3
130°	638.8	692.0	733.4	765.5	785.1	797.6	802.3
132.5°	621.9	673.9	715.3	746.7	768.8	780.7	785.4
135°	596.6	644.3	683.4	714.7	736.6	749.1	753.8
137.5°	572.4	612.6	647.9	677.1	698.7	709.0	714.7
140°	556.7	591.9	624.8	652.1	669.3	680.3	686.5
142.5°	543.6	573.8	602.2	626.5	642.4	652.1	656.5
145°	525.5	548.9	570.8	590.4	603.6	611.5	615.4
147.5°	509.8	528.6	545.8	560.2	571.6	577.5	578.9
150°	500.4	516.1	530.1	542.7	552.8	557.5	558.3
152.5°	491.0	505.4	517.0	527.6	535.9	538.7	539.5
155°	477.8	489.5	498.9	506.7	512.9	515.3	515.3
157.5°	464.6	474.5	482.0	487.9	492.6	494.0	494.0
160°	455.9	464.5	470.7	475.4	480.1	480.9	480.9
162.5°	447.7	454.5	460.1	463.5	468.2	469.0	468.4
165°	435.5	441.0	444.9	448.0	451.2	450.4	449.6
167.5°	425.2	429.6	431.9	433.5	435.5	435.4	434.7
170°	418.3	421.5	423.8	425.4	426.1	425.4	425.4
172.5°	412.7	414.6	416.3	417.2	418.0	417.2	416.0
175°	405.0	406.6	406.6	406.6	408.2	406.6	405.0
177.5°	400.5	400.5	401.1	400.5	401.1	399.9	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0

(END OF REPORT)