

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332677-927

Luminaire Tested: **SA4XXDIP-C1195D365U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332677-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D365U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5056.4 lumens  
Efficiency: N/A  
Efficacy: 101.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332677-927

CATALOG NUMBER: SA4XXDIP-C1195D365U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332677-927

CATALOG NUMBER: SA4XXDIP-C1195D365U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	92	92	92	84	84	84	80
1	104	100	96	92	100	96	92	89	88	85	82	81	78	76	74	72	71	67
2	95	87	81	75	91	84	78	73	77	72	68	71	67	64	65	62	60	56
3	87	77	69	63	83	74	67	61	68	62	57	63	58	54	58	54	51	48
4	80	68	60	53	76	66	58	52	61	54	49	56	51	46	52	47	44	41
5	73	61	52	46	70	59	51	45	54	48	43	50	45	40	47	42	38	36
6	68	55	46	40	64	53	45	39	49	42	37	46	40	35	42	37	34	31
7	63	50	41	35	60	48	40	35	45	38	33	42	36	31	39	34	30	28
8	58	45	37	32	56	44	36	31	41	34	30	38	32	28	36	31	27	25
9	54	42	34	28	52	40	33	28	38	31	27	35	30	25	33	28	24	22
10	51	38	31	26	49	37	30	25	35	28	24	33	27	23	31	26	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12745	12745	12745
5°	12783	12630	12721
10°	12703	12527	12588
15°	12549	12349	12380
20°	12345	12128	12138
25°	12113	11875	11843
30°	11828	11580	11473
35°	11532	11269	11121
40°	11225	10918	10718
45°	10904	10572	10369
50°	10550	10262	9946
55°	10166	9864	9543
60°	9783	9415	9131
65°	9352	8990	8627
70°	8868	8419	8091
75°	8125	7735	7536
80°	7234	6936	6760
85°	6326	6095	5974



TEST NUMBER: P332677-927

CATALOG NUMBER: SA4XXDIP-C1195D365U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.7	2.9
10°-20°	418.9	8.3
20°-30°	616.5	12.2
30°-40°	716.7	14.2
40°-50°	716.8	14.2
50°-60°	627.0	12.4
60°-70°	465.6	9.2
70°-80°	264.5	5.2
80°-90°	77.4	1.5
90°-100°	23.9	0.5
100°-110°	70.7	1.4
110°-120°	120.0	2.4
120°-130°	158.3	3.1
130°-140°	177.8	3.5
140°-150°	174.7	3.5
150°-160°	146.9	2.9
160°-170°	97.7	1.9
170°-180°	34.2	0.7
0°-30°	1184.1	23.4
0°-40°	1900.8	37.6
0°-60°	3244.6	64.2
0°-90°	4052.2	80.1
90°-120°	214.6	4.2
90°-150°	725.3	14.3
90°-180°	1004.0	19.9
0°-180°	5056.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1579	1579	1579	1579	1579	
5°	1577	1572	1558	1571	1570	150
15°	1502	1496	1478	1484	1481	423
25°	1360	1350	1333	1334	1330	625
35°	1170	1161	1144	1135	1128	731
45°	955	946	926	913	908	736
55°	722	718	701	686	678	647
65°	490	483	471	458	452	485
75°	260	254	248	243	242	277
85°	68	68	66	66	64	75
90°	1	4	6	8	8	5
95°	17	19	21	22	22	19
105°	65	66	67	67	68	69
115°	122	122	122	121	121	120
125°	178	178	177	177	176	158
135°	229	231	231	230	230	177
145°	278	280	280	280	279	174
155°	319	319	319	320	319	147
165°	347	347	346	348	347	98
175°	361	360	360	362	360	34
180°	362	362	362	362	362	



TEST NUMBER: P332677-927

CATALOG NUMBER: SA4XXDIP-C1195D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1582.7	1582.1	1581.4	1580.7	1580.0	1578.4	1576.0	1573.5	1571.1	1568.6	1570.8
5°	1577.4	1576.3	1575.2	1574.1	1573.0	1570.8	1567.7	1564.6	1561.5	1558.5	1561.5
7.5°	1562.7	1561.6	1560.5	1559.3	1558.2	1556.0	1552.5	1549.1	1545.7	1542.2	1544.8
10°	1549.6	1548.5	1547.4	1546.2	1545.1	1542.7	1539.1	1535.4	1531.8	1528.1	1530.3
12.5°	1532.4	1531.3	1530.1	1529.0	1527.9	1525.3	1521.5	1517.7	1513.8	1509.9	1512.4
15°	1501.5	1500.4	1499.3	1498.2	1497.0	1494.4	1490.1	1485.9	1481.7	1477.5	1479.2
17.5°	1464.3	1462.9	1461.5	1460.2	1458.7	1456.0	1452.0	1448.0	1444.1	1440.0	1441.1
20°	1437.0	1435.6	1434.2	1432.8	1431.4	1428.5	1424.3	1420.1	1415.9	1411.7	1412.5
22.5°	1407.6	1405.8	1404.0	1402.1	1400.3	1397.2	1393.0	1388.8	1384.6	1380.3	1381.9
25°	1359.9	1357.9	1355.9	1353.9	1351.9	1349.0	1345.0	1341.2	1337.2	1333.2	1333.6
27.5°	1305.2	1303.1	1301.2	1299.1	1297.1	1294.3	1290.6	1287.0	1283.3	1279.6	1279.0
30°	1268.8	1266.5	1264.2	1262.0	1259.8	1256.8	1253.2	1249.5	1245.9	1242.2	1241.1
32.5°	1230.3	1228.3	1226.3	1224.2	1222.2	1219.2	1215.4	1211.5	1207.6	1203.7	1202.4
35°	1170.1	1168.2	1166.2	1164.2	1162.2	1159.3	1155.3	1151.4	1147.5	1143.5	1141.5
37.5°	1106.6	1104.8	1103.0	1101.2	1099.4	1096.4	1092.2	1088.0	1083.7	1079.5	1077.4
40°	1065.1	1062.9	1060.6	1058.4	1056.1	1052.9	1048.7	1044.4	1040.2	1036.0	1033.2
42.5°	1020.6	1019.2	1017.9	1016.5	1015.2	1012.2	1007.5	1002.8	998.1	993.5	990.2
45°	955.1	953.1	951.1	949.1	947.2	944.0	939.4	934.9	930.4	926.0	922.9
47.5°	886.5	885.1	883.8	882.4	881.1	878.4	874.2	870.1	865.9	861.7	858.3
50°	840.0	838.8	837.7	836.5	835.4	832.9	828.9	825.1	821.1	817.1	813.3
52.5°	794.4	793.1	791.7	790.4	789.0	786.2	782.1	777.9	773.8	769.6	766.1
55°	722.3	721.4	720.6	719.8	718.9	716.5	712.6	708.7	704.7	700.8	697.4
57.5°	653.5	652.5	651.6	650.6	649.7	647.2	643.3	639.4	635.6	631.7	628.5
60°	605.9	604.5	603.1	601.7	600.3	597.8	594.1	590.5	586.8	583.1	580.6
62.5°	559.4	558.2	557.0	555.8	554.7	552.2	548.3	544.4	540.5	536.6	534.3
65°	489.6	488.1	486.7	485.3	483.9	481.8	479.0	476.2	473.4	470.6	467.8
67.5°	419.2	418.0	416.6	415.3	414.1	412.0	409.3	406.6	403.9	401.2	398.5
70°	375.7	373.8	371.8	369.8	367.8	365.8	363.5	361.2	358.9	356.7	354.5
72.5°	329.2	327.2	325.2	323.2	321.3	319.4	317.6	315.8	314.0	312.2	310.4
75°	260.5	259.2	257.8	256.4	254.9	253.6	252.2	250.7	249.4	248.0	246.8
77.5°	195.0	194.4	193.8	193.2	192.6	191.6	190.4	189.2	188.0	186.7	186.4
80°	155.6	154.7	153.9	153.0	152.3	151.5	151.0	150.4	149.8	149.2	148.7
82.5°	117.2	116.8	116.4	116.0	115.6	115.3	115.2	115.1	114.9	114.9	114.5
85°	68.3	68.3	68.3	68.3	68.3	68.0	67.5	66.9	66.3	65.8	65.8
87.5°	26.5	26.4	26.3	26.2	26.1	26.0	25.9	25.7	25.7	25.5	25.6
90°	0.9	1.5	2.2	2.9	3.6	4.2	4.7	5.1	5.6	6.2	6.5
92.5°	6.0	6.8	7.5	8.3	9.1	9.7	10.1	10.4	10.8	11.1	11.3
95°	16.8	17.3	17.9	18.5	19.0	19.6	20.0	20.4	20.8	21.3	21.5
97.5°	29.3	29.8	30.3	30.7	31.1	31.6	32.1	32.6	33.1	33.7	33.9
100°	39.2	39.5	39.7	39.9	40.2	40.6	41.1	41.7	42.3	42.9	42.9
102.5°	49.5	49.6	49.7	49.8	49.9	50.2	50.7	51.3	51.7	52.2	52.4
105°	65.2	65.3	65.4	65.4	65.4	65.6	65.9	66.1	66.4	66.6	66.8
107.5°	81.8	81.8	81.9	82.0	82.1	82.1	82.1	82.1	82.2	82.2	82.4
110°	92.9	93.1	93.2	93.3	93.4	93.5	93.4	93.3	93.2	93.2	93.1



TEST NUMBER: P332677-927

CATALOG NUMBER: SA4XXDIP-C1195D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	104.6	104.6	104.6	104.6	104.6	104.6	104.5	104.4	104.3	104.2	104.2
115°	122.1	122.1	122.1	122.1	122.1	122.0	121.8	121.8	121.6	121.5	121.4
117.5°	138.5	138.6	138.6	138.6	138.7	138.7	138.6	138.6	138.4	138.3	138.2
120°	149.5	149.7	150.0	150.2	150.5	150.5	150.4	150.1	150.0	149.8	149.5
122.5°	160.9	161.0	161.1	161.2	161.3	161.3	161.2	161.1	161.1	161.0	160.7
125°	177.8	177.8	177.8	177.8	177.8	177.7	177.7	177.6	177.5	177.4	177.4
127.5°	193.1	193.2	193.5	193.6	193.8	193.8	193.8	193.6	193.5	193.5	193.3
130°	203.8	204.0	204.1	204.4	204.5	204.6	204.6	204.6	204.6	204.6	204.5
132.5°	214.8	214.9	215.0	215.2	215.3	215.3	215.3	215.2	215.2	215.2	215.0
135°	229.3	229.7	230.0	230.4	230.8	230.9	230.9	230.9	230.9	230.9	230.8
137.5°	245.0	245.3	245.4	245.6	245.7	245.9	246.0	246.1	246.2	246.3	246.1
140°	255.6	255.7	255.8	256.0	256.1	256.1	256.1	256.1	256.1	256.1	256.1
142.5°	265.2	265.3	265.5	265.5	265.7	265.8	265.7	265.6	265.6	265.5	265.5
145°	278.5	278.8	279.0	279.2	279.6	279.7	279.7	279.8	279.9	280.0	279.9
147.5°	291.8	292.1	292.3	292.6	292.9	293.0	293.0	292.9	292.9	292.9	292.8
150°	299.8	300.1	300.3	300.6	300.8	301.0	301.0	301.0	301.0	301.0	301.0
152.5°	307.4	307.6	307.7	307.8	308.0	308.1	308.2	308.2	308.2	308.3	308.5
155°	319.1	319.1	319.1	319.1	319.1	319.1	319.0	318.9	318.9	318.9	319.1
157.5°	329.0	328.8	328.8	328.7	328.5	328.4	328.4	328.4	328.4	328.4	328.6
160°	334.8	334.7	334.7	334.6	334.5	334.5	334.5	334.4	334.3	334.2	334.5
162.5°	340.2	340.0	339.8	339.7	339.5	339.5	339.4	339.3	339.2	339.1	339.5
165°	347.4	347.2	347.1	346.8	346.7	346.5	346.3	346.3	346.1	346.0	346.3
167.5°	352.9	352.7	352.4	352.1	351.9	351.7	351.8	351.8	351.8	351.8	352.2
170°	356.1	355.8	355.5	355.1	354.8	354.7	354.7	354.8	354.9	355.0	355.3
172.5°	358.3	358.1	357.7	357.5	357.3	357.1	357.1	357.2	357.2	357.2	357.6
175°	361.4	361.1	360.8	360.4	360.1	360.0	359.9	359.8	359.8	359.7	360.1
177.5°	362.4	362.2	361.9	361.6	361.4	361.3	361.3	361.3	361.3	361.3	361.6
180°	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9



TEST NUMBER: P332677-927

CATALOG NUMBER: SA4XXDIP-C1195D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1573.0	1575.3	1577.6	1578.6	1578.3	1578.1	1577.9	1577.6
5°	1564.6	1567.7	1570.8	1572.1	1571.5	1571.0	1570.4	1569.8
7.5°	1547.2	1549.7	1552.1	1553.2	1552.9	1552.5	1552.2	1551.9
10°	1532.6	1534.9	1537.1	1537.9	1537.4	1536.8	1536.2	1535.6
12.5°	1514.8	1517.3	1519.8	1520.6	1519.8	1519.0	1518.2	1517.4
15°	1480.8	1482.6	1484.2	1484.6	1483.8	1483.0	1482.1	1481.3
17.5°	1442.2	1443.3	1444.3	1444.5	1444.0	1443.4	1442.9	1442.3
20°	1413.4	1414.2	1415.1	1415.2	1414.7	1414.1	1413.6	1412.9
22.5°	1383.4	1384.9	1386.4	1386.6	1385.7	1384.7	1383.6	1382.6
25°	1333.9	1334.1	1334.4	1334.0	1332.8	1331.7	1330.6	1329.5
27.5°	1278.3	1277.6	1276.9	1275.9	1274.5	1273.1	1271.7	1270.3
30°	1239.9	1238.8	1237.7	1236.4	1235.0	1233.7	1232.2	1230.8
32.5°	1201.0	1199.7	1198.3	1197.0	1195.6	1194.1	1192.8	1191.4
35°	1139.6	1137.7	1135.7	1134.0	1132.6	1131.2	1129.7	1128.4
37.5°	1075.2	1073.1	1071.0	1069.0	1067.1	1065.2	1063.4	1061.5
40°	1030.4	1027.5	1024.8	1022.6	1021.3	1019.9	1018.4	1017.0
42.5°	987.0	983.7	980.5	978.3	977.4	976.4	975.5	974.5
45°	919.8	916.7	913.6	911.6	910.8	909.9	909.1	908.2
47.5°	854.8	851.3	847.8	844.9	842.8	840.7	838.5	836.4
50°	809.3	805.3	801.5	798.6	796.9	795.3	793.5	791.9
52.5°	762.6	759.1	755.7	752.9	750.8	748.6	746.5	744.3
55°	694.0	690.7	687.3	684.8	683.1	681.4	679.7	678.0
57.5°	625.3	622.1	618.9	616.5	614.9	613.2	611.6	610.0
60°	578.1	575.6	573.1	571.1	569.7	568.2	566.9	565.5
62.5°	532.0	529.7	527.4	525.5	524.1	522.7	521.3	519.9
65°	464.9	462.2	459.3	457.2	455.8	454.4	453.0	451.6
67.5°	395.9	393.2	390.5	388.9	388.5	388.1	387.7	387.3
70°	352.2	350.0	347.7	346.2	345.3	344.5	343.6	342.8
72.5°	308.6	306.8	305.0	303.6	302.9	302.0	301.1	300.3
75°	245.7	244.5	243.4	242.7	242.5	242.2	241.9	241.6
77.5°	186.0	185.7	185.4	184.8	184.1	183.4	182.6	181.9
80°	148.1	147.6	147.0	146.6	146.3	146.0	145.8	145.4
82.5°	114.2	113.8	113.5	113.2	112.9	112.6	112.3	112.1
85°	65.8	65.8	65.8	65.7	65.4	65.0	64.8	64.5
87.5°	25.7	25.7	25.8	25.9	25.9	25.9	25.9	26.0
90°	6.9	7.3	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	11.6	11.7	12.0	12.1	12.2	12.3	12.4	12.4
95°	21.6	21.9	22.0	22.1	22.1	22.1	22.1	22.1
97.5°	34.1	34.3	34.5	34.6	34.6	34.6	34.6	34.6
100°	43.1	43.2	43.3	43.4	43.4	43.4	43.4	43.4
102.5°	52.6	52.8	52.9	53.1	53.1	53.2	53.2	53.2
105°	67.0	67.2	67.3	67.6	67.7	68.0	68.1	68.3
107.5°	82.6	82.8	82.9	83.0	83.0	83.0	83.0	82.9
110°	93.0	92.8	92.7	92.8	92.9	93.2	93.3	93.5





TEST NUMBER: P332677-927

CATALOG NUMBER: SA4XXDIP-C1195D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	104.2	104.1	104.1	104.1	104.2	104.2	104.2	104.3
115°	121.4	121.3	121.2	121.2	121.1	121.0	121.0	121.0
117.5°	137.9	137.7	137.5	137.4	137.2	137.0	137.0	136.8
120°	149.2	148.9	148.5	148.5	148.5	148.7	148.8	148.9
122.5°	160.6	160.3	160.1	159.9	159.7	159.5	159.2	159.0
125°	177.2	177.1	177.0	176.8	176.7	176.6	176.5	176.3
127.5°	193.2	193.1	192.9	192.8	192.7	192.7	192.5	192.4
130°	204.4	204.2	204.1	203.9	203.7	203.4	203.2	203.0
132.5°	214.9	214.8	214.7	214.5	214.4	214.4	214.3	214.1
135°	230.7	230.6	230.4	230.3	230.1	229.9	229.7	229.6
137.5°	246.0	245.8	245.7	245.6	245.6	245.7	245.7	245.7
140°	256.0	256.0	255.9	255.8	255.8	255.7	255.6	255.6
142.5°	265.5	265.5	265.5	265.5	265.5	265.5	265.5	265.5
145°	279.8	279.7	279.7	279.6	279.4	279.2	279.0	278.8
147.5°	292.8	292.7	292.6	292.6	292.6	292.5	292.4	292.4
150°	301.0	301.0	301.0	300.9	300.9	300.8	300.7	300.6
152.5°	308.6	308.8	309.0	308.9	308.7	308.6	308.4	308.2
155°	319.3	319.6	319.8	319.8	319.6	319.3	319.1	318.9
157.5°	328.8	329.0	329.2	329.2	328.9	328.8	328.5	328.3
160°	334.6	334.8	335.0	334.9	334.6	334.3	334.0	333.7
162.5°	339.8	340.2	340.5	340.5	340.2	339.9	339.6	339.3
165°	346.7	347.1	347.5	347.5	347.3	347.1	346.8	346.6
167.5°	352.6	352.9	353.3	353.3	352.9	352.5	352.1	351.7
170°	355.7	356.1	356.5	356.4	356.0	355.5	355.1	354.7
172.5°	358.1	358.5	358.9	358.9	358.5	358.0	357.6	357.1
175°	360.6	361.0	361.5	361.5	361.0	360.6	360.1	359.7
177.5°	361.9	362.3	362.7	362.7	362.3	361.9	361.5	361.1
180°	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9

(END OF REPORT)