

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332883

Luminaire Tested: **SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332883  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5617.3 lumens  
Efficiency: N/A  
Efficacy: 150.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	44	43	31	30	30	23
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	56	51	48	44	41	36	33	31	24	23	22	17
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	41	58	48	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11
7	55	43	36	31	49	39	33	28	31	26	23	24	20	18	16	15	13	10
8	51	39	32	27	45	36	29	25	28	24	20	22	18	16	15	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	10	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4742	4742	4742	4742
5°	5501	4756	4204	4756
10°	6507	4736	3752	4736
15°	7516	4692	3224	4692
20°	8369	4631	2916	4631
25°	8639	4572	2707	4572
30°	7563	4501	2581	4501
35°	5887	4394	2505	4394
40°	4415	4272	2464	4272
45°	3486	4077	2442	4077
50°	2943	3852	2372	3852
55°	2564	3605	2245	3605
60°	2307	3347	1988	3347
65°	2034	3070	1710	3070
70°	1832	2783	1541	2783
75°	1535	2464	1313	2464
80°	1297	2101	1232	2101
85°	1093	1649	1093	1649



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.9	1.0
10°-20°	171.7	3.1
20°-30°	268.5	4.8
30°-40°	298.5	5.3
40°-50°	264.9	4.7
50°-60°	206.4	3.7
60°-70°	135.1	2.4
70°-80°	66.4	1.2
80°-90°	20.2	0.4
90°-100°	45.7	0.8
100°-110°	291.1	5.2
110°-120°	556.8	9.9
120°-130°	706.8	12.6
130°-140°	756.2	13.5
140°-150°	707.2	12.6
150°-160°	570.3	10.2
160°-170°	367.8	6.5
170°-180°	126.8	2.3
0°-30°	497.1	8.8
0°-40°	795.6	14.2
0°-60°	1266.9	22.6
0°-90°	1488.7	26.5
90°-120°	893.5	15.9
90°-150°	3063.7	54.5
90°-180°	4129.0	73.5
0°-180°	5617.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	587	587	587	587	587	
5°	679	587	519	587	679	69
15°	899	561	386	561	899	256
25°	970	513	304	513	970	430
35°	597	446	254	446	597	374
45°	305	357	214	357	305	242
55°	182	256	160	256	182	166
65°	106	161	90	161	106	107
75°	49	79	42	79	49	54
85°	12	18	12	18	12	14
90°	30	3	30	3	30	13
95°	29	55	29	55	29	23
105°	284	300	284	300	284	248
115°	565	561	565	561	565	559
125°	795	789	795	789	795	708
135°	985	978	985	978	985	758
145°	1134	1128	1134	1128	1134	709
155°	1236	1237	1236	1237	1236	570
165°	1299	1305	1299	1305	1299	367
175°	1327	1335	1327	1335	1327	126
180°	1335	1335	1335	1335	1335	



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	619.6	621.3	619.6	619.4	617.5	616.9	616.2	613.7	609.2	606.5	607.1
5°	678.8	684.7	681.4	680.9	675.7	670.5	667.2	659.6	651.5	646.1	641.6
7.5°	747.2	750.6	748.5	745.2	736.8	732.0	724.3	714.4	699.9	688.9	678.8
10°	793.8	796.6	795.7	789.5	783.4	770.8	763.7	749.8	731.5	717.1	703.6
12.5°	839.6	842.6	834.3	834.6	822.9	813.0	801.8	784.2	763.2	744.6	727.7
15°	899.3	895.5	895.5	890.8	877.8	864.1	852.5	834.0	807.5	785.3	761.8
17.5°	946.1	947.4	945.5	934.3	924.1	909.9	888.6	867.1	842.5	812.6	788.7
20°	974.1	974.1	972.0	964.4	951.2	936.0	913.1	889.6	858.4	828.3	801.4
22.5°	985.5	986.2	983.7	977.5	965.6	950.8	931.2	907.4	875.2	841.4	808.0
25°	969.9	974.4	974.8	973.2	969.6	960.6	943.8	919.5	890.6	853.9	817.9
27.5°	890.4	896.1	901.1	909.3	920.2	925.8	926.6	914.2	889.0	853.7	817.5
30°	811.3	816.0	831.4	851.5	867.1	881.3	893.7	897.0	882.8	851.1	813.0
32.5°	723.4	729.9	745.3	766.9	792.9	817.0	844.6	858.7	858.3	839.3	804.1
35°	597.3	602.1	616.3	639.0	670.2	706.0	749.8	783.8	807.0	805.4	783.8
37.5°	481.8	487.1	501.4	520.3	550.6	594.8	637.2	684.2	727.0	751.1	743.9
40°	418.9	419.1	433.1	452.5	480.9	519.5	565.6	617.7	665.5	704.6	712.1
42.5°	369.3	369.3	378.6	399.5	419.9	456.2	500.3	552.0	608.0	653.1	673.1
45°	305.3	307.4	315.0	327.5	343.6	374.4	409.7	457.7	520.4	573.9	607.3
47.5°	258.5	261.7	266.5	276.7	289.5	310.0	339.2	382.4	433.4	492.2	539.7
50°	234.3	234.8	240.9	246.6	257.7	274.1	299.6	335.6	382.5	439.0	491.8
52.5°	213.5	213.4	217.1	224.3	233.3	246.0	266.7	299.4	341.0	391.7	446.2
55°	182.2	183.4	186.3	191.9	198.8	207.8	224.1	248.7	281.4	324.7	374.2
57.5°	158.5	159.1	161.3	163.7	170.0	176.6	188.8	205.9	233.4	268.9	315.0
60°	142.9	143.2	143.9	147.4	152.4	158.6	166.9	181.3	204.5	236.9	273.4
62.5°	127.8	128.2	129.3	131.9	135.8	140.0	148.7	160.3	179.5	207.2	240.0
65°	106.5	106.7	108.4	109.3	112.4	116.2	122.6	130.4	143.7	166.9	191.7
67.5°	89.0	89.0	89.1	90.4	92.5	95.0	98.8	105.1	115.1	129.3	151.2
70°	77.6	77.6	78.1	78.8	80.0	82.1	84.3	89.0	96.3	107.9	124.7
72.5°	67.0	67.2	67.7	67.8	68.4	70.2	71.8	74.8	80.2	89.0	102.6
75°	49.2	49.9	51.1	52.1	53.3	53.0	54.7	56.6	58.2	63.4	71.2
77.5°	36.6	36.3	36.4	37.2	37.3	37.6	38.8	40.2	41.5	43.9	46.7
80°	27.9	27.9	28.6	28.9	28.6	28.9	30.1	30.8	31.2	32.2	34.8
82.5°	21.1	21.5	21.3	21.5	21.6	21.9	22.9	23.0	23.5	23.9	24.9
85°	11.8	12.1	12.3	11.8	11.8	11.8	12.3	12.5	13.0	12.8	13.3
87.5°	10.2	9.9	10.0	9.9	10.0	9.6	9.5	9.7	9.0	8.9	8.6
90°	29.9	29.5	29.1	28.6	28.2	27.3	26.0	24.6	23.3	22.0	20.2
92.5°	27.6	27.5	27.4	27.3	27.2	26.5	25.2	23.8	22.5	21.2	19.4
95°	28.9	28.7	28.5	28.3	28.1	27.3	26.0	24.6	23.3	22.0	21.7
97.5°	28.0	27.7	27.5	27.3	27.1	26.9	26.8	26.6	26.5	26.4	51.1
100°	28.0	27.7	27.5	27.3	27.1	28.8	32.6	36.4	40.2	43.9	74.5
102.5°	28.8	28.7	28.7	28.6	28.6	48.9	89.6	130.3	170.9	211.6	215.6
105°	284.5	292.5	300.5	308.5	316.5	319.4	317.4	315.5	313.5	311.5	310.4
107.5°	396.5	395.7	394.8	394.0	393.1	392.2	391.3	390.3	389.3	388.3	386.8
110°	445.2	444.6	443.9	443.2	442.6	442.0	441.6	441.1	440.7	440.2	438.9



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	493.9	493.1	492.3	491.4	490.6	490.2	490.3	490.4	490.5	490.5	489.9
115°	565.0	565.0	565.0	565.0	565.0	564.8	564.4	563.9	563.5	563.0	563.2
117.5°	637.3	637.4	637.5	637.6	637.7	637.7	637.8	637.9	638.0	638.1	637.6
120°	682.8	683.3	683.7	684.1	684.6	684.6	684.1	683.7	683.3	682.8	683.0
122.5°	727.5	728.0	728.4	728.9	729.3	729.4	729.1	728.9	728.6	728.3	728.0
125°	794.6	794.4	794.2	794.0	793.7	793.3	792.6	792.0	791.3	790.6	791.1
127.5°	853.5	853.7	853.9	854.1	854.2	854.4	854.5	854.7	854.8	854.9	853.9
130°	893.5	893.5	893.5	893.5	893.5	893.3	893.1	892.9	892.7	892.5	891.8
132.5°	930.2	930.4	930.5	930.7	930.9	930.9	930.7	930.4	930.2	930.0	929.1
135°	985.3	984.8	984.4	984.0	983.5	983.1	982.6	982.2	981.7	981.3	980.4
137.5°	1032.4	1032.5	1032.7	1032.8	1032.9	1032.8	1032.3	1031.8	1031.3	1030.8	1029.8
140°	1065.2	1064.9	1064.7	1064.5	1064.3	1063.8	1063.2	1062.5	1061.8	1061.2	1060.7
142.5°	1092.3	1092.3	1092.2	1092.2	1092.1	1091.9	1091.4	1090.9	1090.4	1089.9	1089.6
145°	1134.0	1133.6	1133.1	1132.7	1132.3	1131.9	1131.7	1131.5	1131.3	1131.0	1131.0
147.5°	1168.6	1168.4	1168.1	1167.9	1167.7	1167.5	1167.3	1167.1	1167.0	1166.8	1167.0
150°	1190.9	1190.7	1190.5	1190.3	1190.0	1189.9	1189.9	1189.9	1189.9	1189.9	1190.2
152.5°	1210.1	1210.2	1210.4	1210.5	1210.6	1210.5	1210.2	1209.8	1209.5	1209.1	1209.5
155°	1235.9	1236.5	1237.2	1237.9	1238.5	1238.4	1237.5	1236.6	1235.7	1234.9	1235.5
157.5°	1257.4	1258.6	1259.7	1260.9	1262.0	1262.0	1260.9	1259.7	1258.6	1257.4	1258.2
160°	1271.8	1273.1	1274.5	1275.8	1277.1	1277.1	1275.8	1274.5	1273.1	1271.8	1272.0
162.5°	1283.0	1284.5	1286.0	1287.5	1289.0	1289.1	1287.8	1286.4	1285.1	1283.8	1284.0
165°	1298.7	1300.7	1302.7	1304.7	1306.7	1306.8	1305.1	1303.3	1301.5	1299.7	1299.7
167.5°	1310.5	1312.7	1315.0	1317.2	1319.4	1319.5	1317.6	1315.6	1313.7	1311.7	1311.9
170°	1317.7	1319.9	1322.2	1324.4	1326.6	1326.8	1325.0	1323.3	1321.5	1319.7	1319.5
172.5°	1321.7	1324.1	1326.5	1328.9	1331.3	1331.6	1329.8	1328.1	1326.3	1324.5	1324.3
175°	1326.7	1329.4	1332.0	1334.7	1337.3	1337.7	1335.7	1333.7	1331.7	1329.7	1329.5
177.5°	1329.9	1332.0	1334.2	1336.3	1338.4	1338.8	1337.3	1335.9	1334.5	1333.1	1332.7
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	605.2	602.6	601.2	598.2	594.6	592.7	591.0	588.5	585.3	581.9	579.5
5°	635.9	630.2	623.1	614.6	607.1	599.7	593.3	586.9	579.6	572.0	564.5
7.5°	667.4	656.3	644.2	630.2	616.7	604.3	592.9	582.1	569.8	558.7	548.7
10°	689.4	674.3	657.5	639.7	622.0	606.6	591.4	577.7	562.6	549.1	537.7
12.5°	707.2	689.4	669.2	647.1	625.7	607.1	589.7	571.8	554.6	540.0	524.8
15°	736.7	712.4	685.2	658.6	631.0	605.6	582.2	561.4	541.7	521.1	506.7
17.5°	757.1	728.1	695.0	663.2	630.5	600.6	573.6	548.8	526.1	505.1	487.9
20°	769.2	737.2	700.5	664.3	627.6	595.7	566.6	539.1	515.7	493.0	475.2
22.5°	776.0	740.6	700.5	662.6	624.6	590.0	558.1	529.5	504.0	481.2	461.6
25°	778.2	740.3	699.4	655.8	614.2	577.5	544.3	513.3	484.9	462.2	441.4
27.5°	775.1	730.5	688.6	643.9	600.9	562.3	527.5	494.9	466.5	442.1	420.7
30°	770.6	722.8	677.8	631.4	587.9	550.7	514.0	482.8	453.2	427.9	406.4
32.5°	760.7	713.3	664.9	617.4	573.3	535.0	500.2	468.8	439.8	413.9	391.0
35°	741.2	693.2	640.7	591.9	548.6	508.8	476.2	445.9	418.2	390.5	366.4
37.5°	715.5	666.5	614.2	560.8	517.4	479.9	450.0	421.5	394.5	369.2	342.5
40°	691.3	646.6	592.6	539.6	495.1	458.9	431.2	405.4	378.2	353.1	326.4
42.5°	662.0	623.9	569.3	516.1	472.2	437.3	411.5	386.3	361.5	337.2	309.3
45°	613.0	584.1	533.0	481.9	437.6	403.0	379.4	357.1	335.4	312.2	285.9
47.5°	556.8	537.3	493.2	440.8	399.9	368.8	345.9	327.7	309.3	286.1	263.1
50°	517.8	505.3	462.7	414.9	375.8	347.2	323.8	306.7	291.3	269.1	248.5
52.5°	476.2	469.5	433.5	387.8	350.1	322.0	302.0	286.7	271.1	252.6	233.4
55°	412.7	416.3	385.8	346.2	310.7	287.1	268.9	256.1	242.8	227.2	212.3
57.5°	347.9	360.9	340.4	305.7	272.4	250.5	236.8	226.1	214.9	202.0	189.2
60°	309.1	320.0	308.4	277.8	248.7	228.4	215.6	207.3	196.2	184.4	174.7
62.5°	271.2	282.9	276.0	251.3	224.3	206.8	195.5	187.8	179.5	169.2	159.1
65°	223.7	231.2	227.9	210.9	191.7	176.8	166.4	160.7	153.1	145.6	136.6
67.5°	171.3	185.9	184.0	174.9	158.4	146.7	139.9	134.9	128.0	122.4	116.3
70°	140.8	154.3	154.1	146.7	137.7	126.9	122.1	117.9	111.7	106.3	101.3
72.5°	115.3	127.6	129.5	123.8	117.7	109.4	104.9	102.0	96.0	92.3	88.2
75°	80.7	89.7	92.1	92.1	89.2	85.0	80.9	79.0	74.8	71.5	69.1
77.5°	52.9	58.6	62.3	63.1	63.6	62.1	58.8	57.5	54.2	53.1	50.8
80°	37.4	41.2	45.4	46.9	48.0	47.6	46.2	45.2	42.1	40.9	40.0
82.5°	25.8	27.9	31.4	34.6	34.2	35.5	34.2	33.5	31.1	30.7	29.8
85°	13.5	13.7	14.2	16.3	17.5	18.0	18.2	17.8	17.0	17.0	15.4
87.5°	8.2	7.7	7.7	7.3	7.0	7.3	7.3	7.0	7.0	6.9	6.8
90°	18.4	16.6	14.9	12.8	10.3	7.9	5.4	3.0	5.4	7.9	10.3
92.5°	17.6	15.8	14.1	13.1	13.0	12.8	12.7	12.6	12.7	12.8	13.0
95°	21.5	21.3	21.1	24.7	32.3	39.8	47.4	54.9	47.4	39.8	32.3
97.5°	75.9	100.6	125.4	135.4	130.7	126.0	121.3	116.6	121.3	126.0	130.7
100°	105.2	135.8	166.4	179.7	175.7	171.7	167.7	163.7	167.7	171.7	175.7
102.5°	219.6	223.6	227.6	228.1	225.2	222.3	219.4	216.4	219.4	222.3	225.2
105°	309.2	308.1	307.0	305.8	304.5	303.1	301.8	300.5	301.8	303.1	304.5
107.5°	385.3	383.8	382.3	381.2	380.5	379.9	379.2	378.5	379.2	379.9	380.5
110°	437.6	436.2	434.9	433.9	433.2	432.6	431.9	431.3	431.9	432.6	433.2





TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	489.3	488.7	488.1	487.2	486.0	484.8	483.6	482.4	483.6	484.8	486.0
115°	563.5	563.7	563.9	563.7	563.0	562.4	561.7	561.0	561.7	562.4	563.0
117.5°	637.1	636.6	636.1	635.5	634.6	633.7	632.8	631.9	632.8	633.7	634.6
120°	683.3	683.5	683.7	683.4	682.5	681.6	680.7	679.8	680.7	681.6	682.5
122.5°	727.7	727.4	727.1	726.7	726.1	725.6	725.1	724.5	725.1	725.6	726.1
125°	791.5	792.0	792.4	792.2	791.3	790.4	789.5	788.6	789.5	790.4	791.3
127.5°	852.9	851.9	850.8	850.2	850.0	849.8	849.5	849.3	849.5	849.8	850.0
130°	891.1	890.5	889.8	889.3	889.1	888.9	888.7	888.5	888.7	888.9	889.1
132.5°	928.3	927.5	926.6	926.0	925.6	925.2	924.8	924.4	924.8	925.2	925.6
135°	979.5	978.6	977.7	977.4	977.6	977.9	978.1	978.3	978.1	977.9	977.6
137.5°	1028.9	1027.9	1026.9	1026.4	1026.3	1026.2	1026.1	1026.0	1026.1	1026.2	1026.3
140°	1060.3	1059.8	1059.4	1058.9	1058.5	1058.1	1057.6	1057.2	1057.6	1058.1	1058.5
142.5°	1089.4	1089.1	1088.8	1088.3	1087.5	1086.7	1085.9	1085.1	1085.9	1086.7	1087.5
145°	1131.0	1131.0	1131.0	1130.7	1130.0	1129.4	1128.7	1128.0	1128.7	1129.4	1130.0
147.5°	1167.2	1167.4	1167.7	1167.2	1165.9	1164.7	1163.4	1162.2	1163.4	1164.7	1165.9
150°	1190.4	1190.6	1190.8	1190.5	1189.6	1188.7	1187.8	1186.9	1187.8	1188.7	1189.6
152.5°	1209.9	1210.3	1210.7	1210.5	1209.8	1209.1	1208.4	1207.7	1208.4	1209.1	1209.8
155°	1236.2	1236.9	1237.5	1237.7	1237.5	1237.3	1237.1	1236.9	1237.1	1237.3	1237.5
157.5°	1258.9	1259.7	1260.4	1260.9	1261.0	1261.1	1261.3	1261.4	1261.3	1261.1	1261.0
160°	1272.2	1272.5	1272.7	1273.1	1273.8	1274.5	1275.1	1275.8	1275.1	1274.5	1273.8
162.5°	1284.2	1284.4	1284.7	1285.2	1286.0	1286.9	1287.7	1288.6	1287.7	1286.9	1286.0
165°	1299.7	1299.7	1299.7	1300.3	1301.4	1302.5	1303.6	1304.7	1303.6	1302.5	1301.4
167.5°	1312.0	1312.1	1312.3	1312.9	1314.1	1315.2	1316.4	1317.5	1316.4	1315.2	1314.1
170°	1319.3	1319.0	1318.8	1319.4	1320.7	1322.0	1323.4	1324.7	1323.4	1322.0	1320.7
172.5°	1324.1	1323.8	1323.6	1324.2	1325.5	1326.8	1328.2	1329.5	1328.2	1326.8	1325.5
175°	1329.3	1329.0	1328.8	1329.4	1330.7	1332.0	1333.4	1334.7	1333.4	1332.0	1330.7
177.5°	1332.4	1332.0	1331.7	1332.1	1333.4	1334.6	1335.8	1337.1	1335.8	1334.6	1333.4
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	576.8	574.9	572.5	569.6	566.2	563.2	561.8	563.0	563.6	562.0	561.8
5°	559.2	553.3	548.6	541.5	535.8	531.1	527.8	526.3	526.8	523.0	522.1
7.5°	539.5	532.5	524.7	516.3	508.5	501.5	497.9	495.9	491.8	490.1	487.2
10°	526.8	517.4	509.8	499.8	490.8	482.6	478.5	475.2	471.2	469.3	465.3
12.5°	513.8	502.8	494.4	484.1	474.9	465.0	461.1	455.0	448.7	444.7	439.5
15°	495.3	482.1	471.9	459.6	448.7	437.4	427.2	415.8	411.6	402.6	397.4
17.5°	473.8	460.4	447.8	431.3	414.5	400.3	389.5	378.6	372.1	366.4	363.7
20°	459.6	447.3	429.8	410.6	391.9	376.3	367.5	360.4	353.3	349.3	346.5
22.5°	446.2	430.4	410.1	389.4	370.7	358.5	351.1	343.8	338.0	334.2	330.4
25°	423.6	403.0	381.5	357.8	345.1	334.4	326.4	320.4	316.9	311.9	310.0
27.5°	400.5	375.5	351.8	335.9	322.6	312.8	305.8	301.4	296.9	293.7	291.2
30°	382.7	357.4	336.1	320.9	307.4	299.4	293.7	288.5	284.9	282.3	280.5
32.5°	365.1	339.8	321.9	305.6	294.9	287.1	281.0	277.1	274.3	271.0	269.8
35°	339.6	317.1	301.5	286.8	276.0	268.9	264.1	260.1	257.7	256.8	256.1
37.5°	315.1	296.7	279.9	267.9	258.2	252.6	247.0	245.0	243.4	241.7	242.5
40°	299.6	282.3	267.4	254.7	246.8	240.7	237.4	235.0	233.6	233.6	233.6
42.5°	286.2	269.3	254.7	243.3	235.5	230.3	226.6	224.6	224.1	223.9	225.1
45°	265.3	249.7	235.0	225.5	218.9	213.7	211.6	209.9	209.9	210.9	211.1
47.5°	244.6	230.0	218.2	207.6	201.5	198.3	196.4	195.6	195.7	196.6	197.7
50°	231.9	217.5	205.9	196.4	190.8	187.7	186.0	185.5	186.0	186.0	187.7
52.5°	218.1	205.2	193.8	185.8	179.4	176.5	175.6	174.9	175.2	176.0	176.7
55°	197.9	186.3	175.4	167.8	163.1	161.2	159.0	159.3	158.8	159.3	159.3
57.5°	177.5	167.1	157.0	151.0	146.8	144.1	141.8	142.4	141.7	141.6	141.2
60°	164.5	153.1	145.1	139.6	134.9	132.5	130.4	130.9	130.2	129.7	128.7
62.5°	150.3	140.8	133.1	127.9	124.1	121.4	119.2	118.8	117.1	115.5	113.4
65°	129.7	121.9	115.0	110.1	106.5	104.4	102.7	101.3	97.7	94.0	92.1
67.5°	109.7	104.0	97.6	93.4	90.5	87.8	84.6	82.2	78.9	76.8	75.6
70°	96.8	91.4	85.9	81.9	78.8	76.2	72.7	71.0	68.6	67.7	66.5
72.5°	84.5	79.4	74.4	70.7	67.5	65.4	62.6	61.0	59.9	59.5	58.4
75°	65.8	61.8	58.0	54.7	52.1	50.6	49.5	48.3	47.8	45.7	44.5
77.5°	48.0	45.3	43.0	40.6	38.8	37.8	35.5	34.2	33.4	32.4	32.1
80°	37.4	35.5	33.1	31.7	29.1	28.2	27.2	27.0	26.7	26.5	26.3
82.5°	28.1	26.2	23.9	23.0	22.3	21.7	21.2	20.9	20.7	20.8	20.8
85°	14.2	13.3	13.3	13.0	12.8	12.5	12.3	12.3	12.1	12.3	12.1
87.5°	7.3	7.5	7.9	7.8	8.4	8.7	8.8	9.1	9.5	9.4	9.6
90°	12.8	14.9	16.6	18.4	20.2	22.0	23.3	24.6	26.0	27.3	28.2
92.5°	13.1	14.1	15.8	17.6	19.4	21.2	22.5	23.8	25.2	26.5	27.2
95°	24.7	21.1	21.3	21.5	21.7	22.0	23.3	24.6	26.0	27.3	28.1
97.5°	135.4	125.4	100.6	75.9	51.1	26.4	26.5	26.6	26.8	26.9	27.1
100°	179.7	166.4	135.8	105.2	74.5	43.9	40.2	36.4	32.6	28.8	27.1
102.5°	228.1	227.6	223.6	219.6	215.6	211.6	170.9	130.3	89.6	48.9	28.6
105°	305.8	307.0	308.1	309.2	310.4	311.5	313.5	315.5	317.4	319.4	316.5
107.5°	381.2	382.3	383.8	385.3	386.8	388.3	389.3	390.3	391.3	392.2	393.1
110°	433.9	434.9	436.2	437.6	438.9	440.2	440.7	441.1	441.6	442.0	442.6



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	487.2	488.1	488.7	489.3	489.9	490.5	490.5	490.4	490.3	490.2	490.6
115°	563.7	563.9	563.7	563.5	563.2	563.0	563.5	563.9	564.4	564.8	565.0
117.5°	635.5	636.1	636.6	637.1	637.6	638.1	638.0	637.9	637.8	637.7	637.7
120°	683.4	683.7	683.5	683.3	683.0	682.8	683.3	683.7	684.1	684.6	684.6
122.5°	726.7	727.1	727.4	727.7	728.0	728.3	728.6	728.9	729.1	729.4	729.3
125°	792.2	792.4	792.0	791.5	791.1	790.6	791.3	792.0	792.6	793.3	793.7
127.5°	850.2	850.8	851.9	852.9	853.9	854.9	854.8	854.7	854.5	854.4	854.2
130°	889.3	889.8	890.5	891.1	891.8	892.5	892.7	892.9	893.1	893.3	893.5
132.5°	926.0	926.6	927.5	928.3	929.1	930.0	930.2	930.4	930.7	930.9	930.9
135°	977.4	977.7	978.6	979.5	980.4	981.3	981.7	982.2	982.6	983.1	983.5
137.5°	1026.4	1026.9	1027.9	1028.9	1029.8	1030.8	1031.3	1031.8	1032.3	1032.8	1032.9
140°	1058.9	1059.4	1059.8	1060.3	1060.7	1061.2	1061.8	1062.5	1063.2	1063.8	1064.3
142.5°	1088.3	1088.8	1089.1	1089.4	1089.6	1089.9	1090.4	1090.9	1091.4	1091.9	1092.1
145°	1130.7	1131.0	1131.0	1131.0	1131.0	1131.0	1131.3	1131.5	1131.7	1131.9	1132.3
147.5°	1167.2	1167.7	1167.4	1167.2	1167.0	1166.8	1167.0	1167.1	1167.3	1167.5	1167.7
150°	1190.5	1190.8	1190.6	1190.4	1190.2	1189.9	1189.9	1189.9	1189.9	1189.9	1190.0
152.5°	1210.5	1210.7	1210.3	1209.9	1209.5	1209.1	1209.5	1209.8	1210.2	1210.5	1210.6
155°	1237.7	1237.5	1236.9	1236.2	1235.5	1234.9	1235.7	1236.6	1237.5	1238.4	1238.5
157.5°	1260.9	1260.4	1259.7	1258.9	1258.2	1257.4	1258.6	1259.7	1260.9	1262.0	1262.0
160°	1273.1	1272.7	1272.5	1272.2	1272.0	1271.8	1273.1	1274.5	1275.8	1277.1	1277.1
162.5°	1285.2	1284.7	1284.4	1284.2	1284.0	1283.8	1285.1	1286.4	1287.8	1289.1	1289.0
165°	1300.3	1299.7	1299.7	1299.7	1299.7	1299.7	1301.5	1303.3	1305.1	1306.8	1306.7
167.5°	1312.9	1312.3	1312.1	1312.0	1311.9	1311.7	1313.7	1315.6	1317.6	1319.5	1319.4
170°	1319.4	1318.8	1319.0	1319.3	1319.5	1319.7	1321.5	1323.3	1325.0	1326.8	1326.6
172.5°	1324.2	1323.6	1323.8	1324.1	1324.3	1324.5	1326.3	1328.1	1329.8	1331.6	1331.3
175°	1329.4	1328.8	1329.0	1329.3	1329.5	1329.7	1331.7	1333.7	1335.7	1337.7	1337.3
177.5°	1332.1	1331.7	1332.0	1332.4	1332.7	1333.1	1334.5	1335.9	1337.3	1338.8	1338.4
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	560.7	561.1	559.8	559.4	559.8	561.1	560.7	561.8	562.0	563.6	563.0
5°	520.2	519.7	518.5	518.8	518.5	519.7	520.2	522.1	523.0	526.8	526.3
7.5°	485.5	483.7	484.2	482.3	484.2	483.7	485.5	487.2	490.1	491.8	495.9
10°	464.3	461.7	459.6	457.7	459.6	461.7	464.3	465.3	469.3	471.2	475.2
12.5°	435.4	433.1	430.3	430.8	430.3	433.1	435.4	439.5	444.7	448.7	455.0
15°	394.3	390.7	385.1	385.8	385.1	390.7	394.3	397.4	402.6	411.6	415.8
17.5°	359.5	359.5	356.9	357.6	356.9	359.5	359.5	363.7	366.4	372.1	378.6
20°	341.5	339.9	340.1	339.4	340.1	339.9	341.5	346.5	349.3	353.3	360.4
22.5°	329.0	327.0	325.3	323.9	325.3	327.0	329.0	330.4	334.2	338.0	343.8
25°	307.9	306.5	304.4	303.9	304.4	306.5	307.9	310.0	311.9	316.9	320.4
27.5°	289.3	289.1	288.2	287.1	288.2	289.1	289.3	291.2	293.7	296.9	301.4
30°	278.6	278.1	277.6	276.9	277.6	278.1	278.6	280.5	282.3	284.9	288.5
32.5°	268.9	268.6	268.1	268.2	268.1	268.6	268.9	269.8	271.0	274.3	277.1
35°	255.1	254.9	254.4	254.2	254.4	254.9	255.1	256.1	256.8	257.7	260.1
37.5°	242.3	242.9	242.6	242.5	242.6	242.9	242.3	242.5	241.7	243.4	245.0
40°	233.4	233.6	234.1	233.8	234.1	233.6	233.4	233.6	233.6	233.6	235.0
42.5°	226.0	226.0	226.7	225.9	226.7	226.0	226.0	225.1	223.9	224.1	224.6
45°	212.8	214.2	213.9	213.9	213.9	214.2	212.8	211.1	210.9	209.9	209.9
47.5°	198.3	199.6	199.9	199.8	199.9	199.6	198.3	197.7	196.6	195.7	195.6
50°	188.9	188.4	189.1	188.9	189.1	188.4	188.9	187.7	186.0	186.0	185.5
52.5°	177.3	177.4	177.4	177.1	177.4	177.4	177.3	176.7	176.0	175.2	174.9
55°	159.5	159.8	159.3	159.5	159.3	159.8	159.5	159.3	159.3	158.8	159.3
57.5°	140.2	139.1	139.5	139.0	139.5	139.1	140.2	141.2	141.6	141.7	142.4
60°	126.4	124.5	124.0	123.1	124.0	124.5	126.4	128.7	129.7	130.2	130.9
62.5°	110.9	109.5	107.9	108.7	107.9	109.5	110.9	113.4	115.5	117.1	118.8
65°	90.2	89.2	88.5	89.5	88.5	89.2	90.2	92.1	94.0	97.7	101.3
67.5°	74.6	74.1	74.1	73.7	74.1	74.1	74.6	75.6	76.8	78.9	82.2
70°	66.5	65.8	65.8	65.3	65.8	65.8	66.5	66.5	67.7	68.6	71.0
72.5°	58.2	57.5	57.7	57.4	57.7	57.5	58.2	58.4	59.5	59.9	61.0
75°	43.1	41.9	41.9	42.1	41.9	41.9	43.1	44.5	45.7	47.8	48.3
77.5°	32.1	31.9	32.2	31.8	32.2	31.9	32.1	32.1	32.4	33.4	34.2
80°	26.3	26.0	25.8	26.5	25.8	26.0	26.3	26.3	26.5	26.7	27.0
82.5°	20.4	20.4	20.3	21.2	20.3	20.4	20.4	20.8	20.8	20.7	20.9
85°	12.3	11.8	12.3	11.8	12.3	11.8	12.3	12.1	12.3	12.1	12.3
87.5°	10.1	10.0	9.9	10.2	9.9	10.0	10.1	9.6	9.4	9.5	9.1
90°	28.6	29.1	29.5	29.9	29.5	29.1	28.6	28.2	27.3	26.0	24.6
92.5°	27.3	27.4	27.5	27.6	27.5	27.4	27.3	27.2	26.5	25.2	23.8
95°	28.3	28.5	28.7	28.9	28.7	28.5	28.3	28.1	27.3	26.0	24.6
97.5°	27.3	27.5	27.7	28.0	27.7	27.5	27.3	27.1	26.9	26.8	26.6
100°	27.3	27.5	27.7	28.0	27.7	27.5	27.3	27.1	28.8	32.6	36.4
102.5°	28.6	28.7	28.7	28.8	28.7	28.7	28.6	28.6	48.9	89.6	130.3
105°	308.5	300.5	292.5	284.5	292.5	300.5	308.5	316.5	319.4	317.4	315.5
107.5°	394.0	394.8	395.7	396.5	395.7	394.8	394.0	393.1	392.2	391.3	390.3
110°	443.2	443.9	444.6	445.2	444.6	443.9	443.2	442.6	442.0	441.6	441.1



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	491.4	492.3	493.1	493.9	493.1	492.3	491.4	490.6	490.2	490.3	490.4
115°	565.0	565.0	565.0	565.0	565.0	565.0	565.0	565.0	564.8	564.4	563.9
117.5°	637.6	637.5	637.4	637.3	637.4	637.5	637.6	637.7	637.7	637.8	637.9
120°	684.1	683.7	683.3	682.8	683.3	683.7	684.1	684.6	684.6	684.1	683.7
122.5°	728.9	728.4	728.0	727.5	728.0	728.4	728.9	729.3	729.4	729.1	728.9
125°	794.0	794.2	794.4	794.6	794.4	794.2	794.0	793.7	793.3	792.6	792.0
127.5°	854.1	853.9	853.7	853.5	853.7	853.9	854.1	854.2	854.4	854.5	854.7
130°	893.5	893.5	893.5	893.5	893.5	893.5	893.5	893.5	893.3	893.1	892.9
132.5°	930.7	930.5	930.4	930.2	930.4	930.5	930.7	930.9	930.9	930.7	930.4
135°	984.0	984.4	984.8	985.3	984.8	984.4	984.0	983.5	983.1	982.6	982.2
137.5°	1032.8	1032.7	1032.5	1032.4	1032.5	1032.7	1032.8	1032.9	1032.8	1032.3	1031.8
140°	1064.5	1064.7	1064.9	1065.2	1064.9	1064.7	1064.5	1064.3	1063.8	1063.2	1062.5
142.5°	1092.2	1092.2	1092.3	1092.3	1092.3	1092.2	1092.2	1092.1	1091.9	1091.4	1090.9
145°	1132.7	1133.1	1133.6	1134.0	1133.6	1133.1	1132.7	1132.3	1131.9	1131.7	1131.5
147.5°	1167.9	1168.1	1168.4	1168.6	1168.4	1168.1	1167.9	1167.7	1167.5	1167.3	1167.1
150°	1190.3	1190.5	1190.7	1190.9	1190.7	1190.5	1190.3	1190.0	1189.9	1189.9	1189.9
152.5°	1210.5	1210.4	1210.2	1210.1	1210.2	1210.4	1210.5	1210.6	1210.5	1210.2	1209.8
155°	1237.9	1237.2	1236.5	1235.9	1236.5	1237.2	1237.9	1238.5	1238.4	1237.5	1236.6
157.5°	1260.9	1259.7	1258.6	1257.4	1258.6	1259.7	1260.9	1262.0	1262.0	1260.9	1259.7
160°	1275.8	1274.5	1273.1	1271.8	1273.1	1274.5	1275.8	1277.1	1277.1	1275.8	1274.5
162.5°	1287.5	1286.0	1284.5	1283.0	1284.5	1286.0	1287.5	1289.0	1289.1	1287.8	1286.4
165°	1304.7	1302.7	1300.7	1298.7	1300.7	1302.7	1304.7	1306.7	1306.8	1305.1	1303.3
167.5°	1317.2	1315.0	1312.7	1310.5	1312.7	1315.0	1317.2	1319.4	1319.5	1317.6	1315.6
170°	1324.4	1322.2	1319.9	1317.7	1319.9	1322.2	1324.4	1326.6	1326.8	1325.0	1323.3
172.5°	1328.9	1326.5	1324.1	1321.7	1324.1	1326.5	1328.9	1331.3	1331.6	1329.8	1328.1
175°	1334.7	1332.0	1329.4	1326.7	1329.4	1332.0	1334.7	1337.3	1337.7	1335.7	1333.7
177.5°	1336.3	1334.2	1332.0	1329.9	1332.0	1334.2	1336.3	1338.4	1338.8	1337.3	1335.9
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	561.8	563.2	566.2	569.6	572.5	574.9	576.8	579.5	581.9	585.3	588.5
5°	527.8	531.1	535.8	541.5	548.6	553.3	559.2	564.5	572.0	579.6	586.9
7.5°	497.9	501.5	508.5	516.3	524.7	532.5	539.5	548.7	558.7	569.8	582.1
10°	478.5	482.6	490.8	499.8	509.8	517.4	526.8	537.7	549.1	562.6	577.7
12.5°	461.1	465.0	474.9	484.1	494.4	502.8	513.8	524.8	540.0	554.6	571.8
15°	427.2	437.4	448.7	459.6	471.9	482.1	495.3	506.7	521.1	541.7	561.4
17.5°	389.5	400.3	414.5	431.3	447.8	460.4	473.8	487.9	505.1	526.1	548.8
20°	367.5	376.3	391.9	410.6	429.8	447.3	459.6	475.2	493.0	515.7	539.1
22.5°	351.1	358.5	370.7	389.4	410.1	430.4	446.2	461.6	481.2	504.0	529.5
25°	326.4	334.4	345.1	357.8	381.5	403.0	423.6	441.4	462.2	484.9	513.3
27.5°	305.8	312.8	322.6	335.9	351.8	375.5	400.5	420.7	442.1	466.5	494.9
30°	293.7	299.4	307.4	320.9	336.1	357.4	382.7	406.4	427.9	453.2	482.8
32.5°	281.0	287.1	294.9	305.6	321.9	339.8	365.1	391.0	413.9	439.8	468.8
35°	264.1	268.9	276.0	286.8	301.5	317.1	339.6	366.4	390.5	418.2	445.9
37.5°	247.0	252.6	258.2	267.9	279.9	296.7	315.1	342.5	369.2	394.5	421.5
40°	237.4	240.7	246.8	254.7	267.4	282.3	299.6	326.4	353.1	378.2	405.4
42.5°	226.6	230.3	235.5	243.3	254.7	269.3	286.2	309.3	337.2	361.5	386.3
45°	211.6	213.7	218.9	225.5	235.0	249.7	265.3	285.9	312.2	335.4	357.1
47.5°	196.4	198.3	201.5	207.6	218.2	230.0	244.6	263.1	286.1	309.3	327.7
50°	186.0	187.7	190.8	196.4	205.9	217.5	231.9	248.5	269.1	291.3	306.7
52.5°	175.6	176.5	179.4	185.8	193.8	205.2	218.1	233.4	252.6	271.1	286.7
55°	159.0	161.2	163.1	167.8	175.4	186.3	197.9	212.3	227.2	242.8	256.1
57.5°	141.8	144.1	146.8	151.0	157.0	167.1	177.5	189.2	202.0	214.9	226.1
60°	130.4	132.5	134.9	139.6	145.1	153.1	164.5	174.7	184.4	196.2	207.3
62.5°	119.2	121.4	124.1	127.9	133.1	140.8	150.3	159.1	169.2	179.5	187.8
65°	102.7	104.4	106.5	110.1	115.0	121.9	129.7	136.6	145.6	153.1	160.7
67.5°	84.6	87.8	90.5	93.4	97.6	104.0	109.7	116.3	122.4	128.0	134.9
70°	72.7	76.2	78.8	81.9	85.9	91.4	96.8	101.3	106.3	111.7	117.9
72.5°	62.6	65.4	67.5	70.7	74.4	79.4	84.5	88.2	92.3	96.0	102.0
75°	49.5	50.6	52.1	54.7	58.0	61.8	65.8	69.1	71.5	74.8	79.0
77.5°	35.5	37.8	38.8	40.6	43.0	45.3	48.0	50.8	53.1	54.2	57.5
80°	27.2	28.2	29.1	31.7	33.1	35.5	37.4	40.0	40.9	42.1	45.2
82.5°	21.2	21.7	22.3	23.0	23.9	26.2	28.1	29.8	30.7	31.1	33.5
85°	12.3	12.5	12.8	13.0	13.3	13.3	14.2	15.4	17.0	17.0	17.8
87.5°	8.8	8.7	8.4	7.8	7.9	7.5	7.3	6.8	6.9	7.0	7.0
90°	23.3	22.0	20.2	18.4	16.6	14.9	12.8	10.3	7.9	5.4	3.0
92.5°	22.5	21.2	19.4	17.6	15.8	14.1	13.1	13.0	12.8	12.7	12.6
95°	23.3	22.0	21.7	21.5	21.3	21.1	24.7	32.3	39.8	47.4	54.9
97.5°	26.5	26.4	51.1	75.9	100.6	125.4	135.4	130.7	126.0	121.3	116.6
100°	40.2	43.9	74.5	105.2	135.8	166.4	179.7	175.7	171.7	167.7	163.7
102.5°	170.9	211.6	215.6	219.6	223.6	227.6	228.1	225.2	222.3	219.4	216.4
105°	313.5	311.5	310.4	309.2	308.1	307.0	305.8	304.5	303.1	301.8	300.5
107.5°	389.3	388.3	386.8	385.3	383.8	382.3	381.2	380.5	379.9	379.2	378.5
110°	440.7	440.2	438.9	437.6	436.2	434.9	433.9	433.2	432.6	431.9	431.3



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	490.5	490.5	489.9	489.3	488.7	488.1	487.2	486.0	484.8	483.6	482.4
115°	563.5	563.0	563.2	563.5	563.7	563.9	563.7	563.0	562.4	561.7	561.0
117.5°	638.0	638.1	637.6	637.1	636.6	636.1	635.5	634.6	633.7	632.8	631.9
120°	683.3	682.8	683.0	683.3	683.5	683.7	683.4	682.5	681.6	680.7	679.8
122.5°	728.6	728.3	728.0	727.7	727.4	727.1	726.7	726.1	725.6	725.1	724.5
125°	791.3	790.6	791.1	791.5	792.0	792.4	792.2	791.3	790.4	789.5	788.6
127.5°	854.8	854.9	853.9	852.9	851.9	850.8	850.2	850.0	849.8	849.5	849.3
130°	892.7	892.5	891.8	891.1	890.5	889.8	889.3	889.1	888.9	888.7	888.5
132.5°	930.2	930.0	929.1	928.3	927.5	926.6	926.0	925.6	925.2	924.8	924.4
135°	981.7	981.3	980.4	979.5	978.6	977.7	977.4	977.6	977.9	978.1	978.3
137.5°	1031.3	1030.8	1029.8	1028.9	1027.9	1026.9	1026.4	1026.3	1026.2	1026.1	1026.0
140°	1061.8	1061.2	1060.7	1060.3	1059.8	1059.4	1058.9	1058.5	1058.1	1057.6	1057.2
142.5°	1090.4	1089.9	1089.6	1089.4	1089.1	1088.8	1088.3	1087.5	1086.7	1085.9	1085.1
145°	1131.3	1131.0	1131.0	1131.0	1131.0	1131.0	1130.7	1130.0	1129.4	1128.7	1128.0
147.5°	1167.0	1166.8	1167.0	1167.2	1167.4	1167.7	1167.2	1165.9	1164.7	1163.4	1162.2
150°	1189.9	1189.9	1190.2	1190.4	1190.6	1190.8	1190.5	1189.6	1188.7	1187.8	1186.9
152.5°	1209.5	1209.1	1209.5	1209.9	1210.3	1210.7	1210.5	1209.8	1209.1	1208.4	1207.7
155°	1235.7	1234.9	1235.5	1236.2	1236.9	1237.5	1237.7	1237.5	1237.3	1237.1	1236.9
157.5°	1258.6	1257.4	1258.2	1258.9	1259.7	1260.4	1260.9	1261.0	1261.1	1261.3	1261.4
160°	1273.1	1271.8	1272.0	1272.2	1272.5	1272.7	1273.1	1273.8	1274.5	1275.1	1275.8
162.5°	1285.1	1283.8	1284.0	1284.2	1284.4	1284.7	1285.2	1286.0	1286.9	1287.7	1288.6
165°	1301.5	1299.7	1299.7	1299.7	1299.7	1299.7	1300.3	1301.4	1302.5	1303.6	1304.7
167.5°	1313.7	1311.7	1311.9	1312.0	1312.1	1312.3	1312.9	1314.1	1315.2	1316.4	1317.5
170°	1321.5	1319.7	1319.5	1319.3	1319.0	1318.8	1319.4	1320.7	1322.0	1323.4	1324.7
172.5°	1326.3	1324.5	1324.3	1324.1	1323.8	1323.6	1324.2	1325.5	1326.8	1328.2	1329.5
175°	1331.7	1329.7	1329.5	1329.3	1329.0	1328.8	1329.4	1330.7	1332.0	1333.4	1334.7
177.5°	1334.5	1333.1	1332.7	1332.4	1332.0	1331.7	1332.1	1333.4	1334.6	1335.8	1337.1
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	591.0	592.7	594.6	598.2	601.2	602.6	605.2	607.1	606.5	609.2	613.7
5°	593.3	599.7	607.1	614.6	623.1	630.2	635.9	641.6	646.1	651.5	659.6
7.5°	592.9	604.3	616.7	630.2	644.2	656.3	667.4	678.8	688.9	699.9	714.4
10°	591.4	606.6	622.0	639.7	657.5	674.3	689.4	703.6	717.1	731.5	749.8
12.5°	589.7	607.1	625.7	647.1	669.2	689.4	707.2	727.7	744.6	763.2	784.2
15°	582.2	605.6	631.0	658.6	685.2	712.4	736.7	761.8	785.3	807.5	834.0
17.5°	573.6	600.6	630.5	663.2	695.0	728.1	757.1	788.7	812.6	842.5	867.1
20°	566.6	595.7	627.6	664.3	700.5	737.2	769.2	801.4	828.3	858.4	889.6
22.5°	558.1	590.0	624.6	662.6	700.5	740.6	776.0	808.0	841.4	875.2	907.4
25°	544.3	577.5	614.2	655.8	699.4	740.3	778.2	817.9	853.9	890.6	919.5
27.5°	527.5	562.3	600.9	643.9	688.6	730.5	775.1	817.5	853.7	889.0	914.2
30°	514.0	550.7	587.9	631.4	677.8	722.8	770.6	813.0	851.1	882.8	897.0
32.5°	500.2	535.0	573.3	617.4	664.9	713.3	760.7	804.1	839.3	858.3	858.7
35°	476.2	508.8	548.6	591.9	640.7	693.2	741.2	783.8	805.4	807.0	783.8
37.5°	450.0	479.9	517.4	560.8	614.2	666.5	715.5	743.9	751.1	727.0	684.2
40°	431.2	458.9	495.1	539.6	592.6	646.6	691.3	712.1	704.6	665.5	617.7
42.5°	411.5	437.3	472.2	516.1	569.3	623.9	662.0	673.1	653.1	608.0	552.0
45°	379.4	403.0	437.6	481.9	533.0	584.1	613.0	607.3	573.9	520.4	457.7
47.5°	345.9	368.8	399.9	440.8	493.2	537.3	556.8	539.7	492.2	433.4	382.4
50°	323.8	347.2	375.8	414.9	462.7	505.3	517.8	491.8	439.0	382.5	335.6
52.5°	302.0	322.0	350.1	387.8	433.5	469.5	476.2	446.2	391.7	341.0	299.4
55°	268.9	287.1	310.7	346.2	385.8	416.3	412.7	374.2	324.7	281.4	248.7
57.5°	236.8	250.5	272.4	305.7	340.4	360.9	347.9	315.0	268.9	233.4	205.9
60°	215.6	228.4	248.7	277.8	308.4	320.0	309.1	273.4	236.9	204.5	181.3
62.5°	195.5	206.8	224.3	251.3	276.0	282.9	271.2	240.0	207.2	179.5	160.3
65°	166.4	176.8	191.7	210.9	227.9	231.2	223.7	191.7	166.9	143.7	130.4
67.5°	139.9	146.7	158.4	174.9	184.0	185.9	171.3	151.2	129.3	115.1	105.1
70°	122.1	126.9	137.7	146.7	154.1	154.3	140.8	124.7	107.9	96.3	89.0
72.5°	104.9	109.4	117.7	123.8	129.5	127.6	115.3	102.6	89.0	80.2	74.8
75°	80.9	85.0	89.2	92.1	92.1	89.7	80.7	71.2	63.4	58.2	56.6
77.5°	58.8	62.1	63.6	63.1	62.3	58.6	52.9	46.7	43.9	41.5	40.2
80°	46.2	47.6	48.0	46.9	45.4	41.2	37.4	34.8	32.2	31.2	30.8
82.5°	34.2	35.5	34.2	34.6	31.4	27.9	25.8	24.9	23.9	23.5	23.0
85°	18.2	18.0	17.5	16.3	14.2	13.7	13.5	13.3	12.8	13.0	12.5
87.5°	7.3	7.3	7.0	7.3	7.7	7.7	8.2	8.6	8.9	9.0	9.7
90°	5.4	7.9	10.3	12.8	14.9	16.6	18.4	20.2	22.0	23.3	24.6
92.5°	12.7	12.8	13.0	13.1	14.1	15.8	17.6	19.4	21.2	22.5	23.8
95°	47.4	39.8	32.3	24.7	21.1	21.3	21.5	21.7	22.0	23.3	24.6
97.5°	121.3	126.0	130.7	135.4	125.4	100.6	75.9	51.1	26.4	26.5	26.6
100°	167.7	171.7	175.7	179.7	166.4	135.8	105.2	74.5	43.9	40.2	36.4
102.5°	219.4	222.3	225.2	228.1	227.6	223.6	219.6	215.6	211.6	170.9	130.3
105°	301.8	303.1	304.5	305.8	307.0	308.1	309.2	310.4	311.5	313.5	315.5
107.5°	379.2	379.9	380.5	381.2	382.3	383.8	385.3	386.8	388.3	389.3	390.3
110°	431.9	432.6	433.2	433.9	434.9	436.2	437.6	438.9	440.2	440.7	441.1





TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	483.6	484.8	486.0	487.2	488.1	488.7	489.3	489.9	490.5	490.5	490.4
115°	561.7	562.4	563.0	563.7	563.9	563.7	563.5	563.2	563.0	563.5	563.9
117.5°	632.8	633.7	634.6	635.5	636.1	636.6	637.1	637.6	638.1	638.0	637.9
120°	680.7	681.6	682.5	683.4	683.7	683.5	683.3	683.0	682.8	683.3	683.7
122.5°	725.1	725.6	726.1	726.7	727.1	727.4	727.7	728.0	728.3	728.6	728.9
125°	789.5	790.4	791.3	792.2	792.4	792.0	791.5	791.1	790.6	791.3	792.0
127.5°	849.5	849.8	850.0	850.2	850.8	851.9	852.9	853.9	854.9	854.8	854.7
130°	888.7	888.9	889.1	889.3	889.8	890.5	891.1	891.8	892.5	892.7	892.9
132.5°	924.8	925.2	925.6	926.0	926.6	927.5	928.3	929.1	930.0	930.2	930.4
135°	978.1	977.9	977.6	977.4	977.7	978.6	979.5	980.4	981.3	981.7	982.2
137.5°	1026.1	1026.2	1026.3	1026.4	1026.9	1027.9	1028.9	1029.8	1030.8	1031.3	1031.8
140°	1057.6	1058.1	1058.5	1058.9	1059.4	1059.8	1060.3	1060.7	1061.2	1061.8	1062.5
142.5°	1085.9	1086.7	1087.5	1088.3	1088.8	1089.1	1089.4	1089.6	1089.9	1090.4	1090.9
145°	1128.7	1129.4	1130.0	1130.7	1131.0	1131.0	1131.0	1131.0	1131.0	1131.3	1131.5
147.5°	1163.4	1164.7	1165.9	1167.2	1167.7	1167.4	1167.2	1167.0	1166.8	1167.0	1167.1
150°	1187.8	1188.7	1189.6	1190.5	1190.8	1190.6	1190.4	1190.2	1189.9	1189.9	1189.9
152.5°	1208.4	1209.1	1209.8	1210.5	1210.7	1210.3	1209.9	1209.5	1209.1	1209.5	1209.8
155°	1237.1	1237.3	1237.5	1237.7	1237.5	1236.9	1236.2	1235.5	1234.9	1235.7	1236.6
157.5°	1261.3	1261.1	1261.0	1260.9	1260.4	1259.7	1258.9	1258.2	1257.4	1258.6	1259.7
160°	1275.1	1274.5	1273.8	1273.1	1272.7	1272.5	1272.2	1272.0	1271.8	1273.1	1274.5
162.5°	1287.7	1286.9	1286.0	1285.2	1284.7	1284.4	1284.2	1284.0	1283.8	1285.1	1286.4
165°	1303.6	1302.5	1301.4	1300.3	1299.7	1299.7	1299.7	1299.7	1299.7	1301.5	1303.3
167.5°	1316.4	1315.2	1314.1	1312.9	1312.3	1312.1	1312.0	1311.9	1311.7	1313.7	1315.6
170°	1323.4	1322.0	1320.7	1319.4	1318.8	1319.0	1319.3	1319.5	1319.7	1321.5	1323.3
172.5°	1328.2	1326.8	1325.5	1324.2	1323.6	1323.8	1324.1	1324.3	1324.5	1326.3	1328.1
175°	1333.4	1332.0	1330.7	1329.4	1328.8	1329.0	1329.3	1329.5	1329.7	1331.7	1333.7
177.5°	1335.8	1334.6	1333.4	1332.1	1331.7	1332.0	1332.4	1332.7	1333.1	1334.5	1335.9
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	616.2	616.9	617.5	619.4	619.6	621.3	619.6
5°	667.2	670.5	675.7	680.9	681.4	684.7	678.8
7.5°	724.3	732.0	736.8	745.2	748.5	750.6	747.2
10°	763.7	770.8	783.4	789.5	795.7	796.6	793.8
12.5°	801.8	813.0	822.9	834.6	834.3	842.6	839.6
15°	852.5	864.1	877.8	890.8	895.5	895.5	899.3
17.5°	888.6	909.9	924.1	934.3	945.5	947.4	946.1
20°	913.1	936.0	951.2	964.4	972.0	974.1	974.1
22.5°	931.2	950.8	965.6	977.5	983.7	986.2	985.5
25°	943.8	960.6	969.6	973.2	974.8	974.4	969.9
27.5°	926.6	925.8	920.2	909.3	901.1	896.1	890.4
30°	893.7	881.3	867.1	851.5	831.4	816.0	811.3
32.5°	844.6	817.0	792.9	766.9	745.3	729.9	723.4
35°	749.8	706.0	670.2	639.0	616.3	602.1	597.3
37.5°	637.2	594.8	550.6	520.3	501.4	487.1	481.8
40°	565.6	519.5	480.9	452.5	433.1	419.1	418.9
42.5°	500.3	456.2	419.9	399.5	378.6	369.3	369.3
45°	409.7	374.4	343.6	327.5	315.0	307.4	305.3
47.5°	339.2	310.0	289.5	276.7	266.5	261.7	258.5
50°	299.6	274.1	257.7	246.6	240.9	234.8	234.3
52.5°	266.7	246.0	233.3	224.3	217.1	213.4	213.5
55°	224.1	207.8	198.8	191.9	186.3	183.4	182.2
57.5°	188.8	176.6	170.0	163.7	161.3	159.1	158.5
60°	166.9	158.6	152.4	147.4	143.9	143.2	142.9
62.5°	148.7	140.0	135.8	131.9	129.3	128.2	127.8
65°	122.6	116.2	112.4	109.3	108.4	106.7	106.5
67.5°	98.8	95.0	92.5	90.4	89.1	89.0	89.0
70°	84.3	82.1	80.0	78.8	78.1	77.6	77.6
72.5°	71.8	70.2	68.4	67.8	67.7	67.2	67.0
75°	54.7	53.0	53.3	52.1	51.1	49.9	49.2
77.5°	38.8	37.6	37.3	37.2	36.4	36.3	36.6
80°	30.1	28.9	28.6	28.9	28.6	27.9	27.9
82.5°	22.9	21.9	21.6	21.5	21.3	21.5	21.1
85°	12.3	11.8	11.8	11.8	12.3	12.1	11.8
87.5°	9.5	9.6	10.0	9.9	10.0	9.9	10.2
90°	26.0	27.3	28.2	28.6	29.1	29.5	29.9
92.5°	25.2	26.5	27.2	27.3	27.4	27.5	27.6
95°	26.0	27.3	28.1	28.3	28.5	28.7	28.9
97.5°	26.8	26.9	27.1	27.3	27.5	27.7	28.0
100°	32.6	28.8	27.1	27.3	27.5	27.7	28.0
102.5°	89.6	48.9	28.6	28.6	28.7	28.7	28.8
105°	317.4	319.4	316.5	308.5	300.5	292.5	284.5
107.5°	391.3	392.2	393.1	394.0	394.8	395.7	396.5
110°	441.6	442.0	442.6	443.2	443.9	444.6	445.2



TEST NUMBER: P332883

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	490.3	490.2	490.6	491.4	492.3	493.1	493.9
115°	564.4	564.8	565.0	565.0	565.0	565.0	565.0
117.5°	637.8	637.7	637.7	637.6	637.5	637.4	637.3
120°	684.1	684.6	684.6	684.1	683.7	683.3	682.8
122.5°	729.1	729.4	729.3	728.9	728.4	728.0	727.5
125°	792.6	793.3	793.7	794.0	794.2	794.4	794.6
127.5°	854.5	854.4	854.2	854.1	853.9	853.7	853.5
130°	893.1	893.3	893.5	893.5	893.5	893.5	893.5
132.5°	930.7	930.9	930.9	930.7	930.5	930.4	930.2
135°	982.6	983.1	983.5	984.0	984.4	984.8	985.3
137.5°	1032.3	1032.8	1032.9	1032.8	1032.7	1032.5	1032.4
140°	1063.2	1063.8	1064.3	1064.5	1064.7	1064.9	1065.2
142.5°	1091.4	1091.9	1092.1	1092.2	1092.2	1092.3	1092.3
145°	1131.7	1131.9	1132.3	1132.7	1133.1	1133.6	1134.0
147.5°	1167.3	1167.5	1167.7	1167.9	1168.1	1168.4	1168.6
150°	1189.9	1189.9	1190.0	1190.3	1190.5	1190.7	1190.9
152.5°	1210.2	1210.5	1210.6	1210.5	1210.4	1210.2	1210.1
155°	1237.5	1238.4	1238.5	1237.9	1237.2	1236.5	1235.9
157.5°	1260.9	1262.0	1262.0	1260.9	1259.7	1258.6	1257.4
160°	1275.8	1277.1	1277.1	1275.8	1274.5	1273.1	1271.8
162.5°	1287.8	1289.1	1289.0	1287.5	1286.0	1284.5	1283.0
165°	1305.1	1306.8	1306.7	1304.7	1302.7	1300.7	1298.7
167.5°	1317.6	1319.5	1319.4	1317.2	1315.0	1312.7	1310.5
170°	1325.0	1326.8	1326.6	1324.4	1322.2	1319.9	1317.7
172.5°	1329.8	1331.6	1331.3	1328.9	1326.5	1324.1	1321.7
175°	1335.7	1337.7	1337.3	1334.7	1332.0	1329.4	1326.7
177.5°	1337.3	1338.8	1338.4	1336.3	1334.2	1332.0	1329.9
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7

(END OF REPORT)