

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332888

Luminaire Tested: **SA4XXRDIP-C350D1035U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332888
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5126.7 lumens
Efficiency: N/A
Efficacy: 137.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332888
CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332888

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	58	46	45	44	32	31	30	24
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	20
3	77	68	61	56	69	61	56	51	48	44	41	36	34	31	25	24	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	21	19	15
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	35	30	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	24	19	24	19	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4991	4991	4991
5°	5002	4941	4971
10°	4970	4882	4882
15°	4914	4779	4743
20°	4835	4643	4558
25°	4735	4486	4372
30°	4638	4320	4139
35°	4529	4147	3905
40°	4400	3951	3652
45°	4280	3756	3394
50°	4143	3532	3121
55°	3997	3298	2825
60°	3836	3042	2522
65°	3689	2722	2223
70°	3474	2367	1888
75°	3203	1965	1535
80°	2794	1497	1409
85°	2371	1362	1269



TEST NUMBER: P332888

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	1.1
10°-20°	161.9	3.2
20°-30°	233.8	4.6
30°-40°	265.1	5.2
40°-50°	255.9	5.0
50°-60°	212.8	4.2
60°-70°	147.0	2.9
70°-80°	74.5	1.5
80°-90°	21.9	0.4
90°-100°	367.0	7.2
100°-110°	763.9	14.9
110°-120°	684.2	13.3
120°-130°	575.5	11.2
130°-140°	479.9	9.4
140°-150°	366.6	7.2
150°-160°	257.7	5.0
160°-170°	151.6	3.0
170°-180°	49.3	1.0
0°-30°	453.8	8.9
0°-40°	718.9	14.0
0°-60°	1187.7	23.2
0°-90°	1431.0	27.9
90°-120°	1815.1	35.4
90°-150°	3237.1	63.1
90°-180°	3696.0	72.1
0°-180°	5126.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	613	59
15°	588	583	572	571	568	166
25°	532	522	504	496	491	245
35°	460	444	421	405	396	287
45°	375	357	329	307	297	289
55°	284	264	234	211	201	254
65°	193	172	142	123	116	191
75°	103	85	63	53	49	108
85°	26	16	15	14	14	29
90°	1	8	18	20	21	3
95°	33	104	814	403	244	37
105°	117	169	655	1410	1405	125
115°	206	258	584	1122	1349	204
125°	286	340	581	955	1076	255
135°	340	405	576	848	962	263
145°	392	449	573	715	786	246
155°	446	482	557	631	658	206
165°	486	501	534	566	574	137
175°	507	508	512	519	517	48
180°	508	508	508	508	508	



TEST NUMBER: P332888

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	619.7	619.3	619.0	618.7	618.3	617.7	616.8	615.9	614.9	614.0	614.9
5°	617.2	616.8	616.4	616.0	615.5	614.7	613.4	612.2	610.9	609.7	610.7
7.5°	611.6	611.2	610.8	610.3	609.9	608.8	607.2	605.5	603.9	602.3	602.9
10°	606.3	605.8	605.3	604.8	604.2	603.0	601.1	599.2	597.3	595.5	595.9
12.5°	599.5	598.9	598.3	597.7	597.1	595.7	593.4	591.2	589.0	586.7	587.0
15°	587.9	586.9	586.0	585.0	584.1	582.3	579.7	577.0	574.4	571.8	571.6
17.5°	573.8	572.4	571.0	569.7	568.3	566.0	562.9	559.7	556.6	553.4	552.8
20°	562.8	561.4	560.1	558.7	557.3	554.9	551.3	547.7	544.1	540.5	539.7
22.5°	550.7	549.1	547.6	546.1	544.5	541.8	538.0	534.2	530.4	526.5	525.3
25°	531.6	529.7	527.8	525.9	524.0	520.9	516.6	512.3	507.9	503.6	501.8
27.5°	511.5	509.1	506.7	504.4	502.0	498.5	493.9	489.3	484.7	480.1	477.8
30°	497.5	494.8	492.2	489.6	487.0	483.2	478.2	473.3	468.3	463.4	460.8
32.5°	482.7	479.7	476.8	473.8	470.8	466.8	461.7	456.6	451.5	446.4	443.3
35°	459.6	456.2	452.9	449.5	446.1	441.8	436.6	431.3	426.1	420.8	417.2
37.5°	434.9	431.4	428.0	424.5	421.0	416.4	410.5	404.7	398.9	393.1	389.1
40°	417.5	414.0	410.5	407.1	403.6	398.9	392.9	386.9	380.9	374.9	370.5
42.5°	400.8	397.2	393.5	389.9	386.3	381.3	375.1	368.8	362.6	356.3	351.8
45°	374.9	371.0	367.1	363.2	359.3	354.2	347.9	341.6	335.3	329.0	323.8
47.5°	348.1	344.1	340.1	336.0	332.0	326.7	320.2	313.6	307.0	300.5	295.1
50°	329.9	325.8	321.7	317.6	313.5	308.1	301.4	294.6	287.9	281.2	275.9
52.5°	311.4	307.3	303.3	299.3	295.3	289.8	282.9	276.0	269.1	262.2	256.9
55°	284.0	279.8	275.6	271.4	267.2	261.6	254.8	248.0	241.1	234.3	228.8
57.5°	256.9	252.5	248.2	243.8	239.4	233.9	227.1	220.4	213.7	206.9	201.4
60°	237.6	233.4	229.2	225.0	220.8	215.3	208.6	201.8	195.1	188.4	182.9
62.5°	220.2	215.8	211.4	207.1	202.7	197.1	190.2	183.3	176.4	169.5	164.4
65°	193.1	188.6	184.1	179.6	175.0	169.4	162.7	155.9	149.2	142.5	138.0
67.5°	165.0	160.7	156.3	152.0	147.7	142.4	136.1	129.9	123.6	117.4	113.5
70°	147.2	142.8	138.4	134.0	129.5	124.3	118.3	112.3	106.3	100.3	96.9
72.5°	128.3	124.3	120.3	116.3	112.3	107.5	101.8	96.1	90.5	84.8	81.9
75°	102.7	98.8	94.9	91.0	87.1	82.7	77.8	72.8	67.9	63.0	60.5
77.5°	76.8	73.5	70.2	66.9	63.6	59.9	55.9	51.9	47.9	43.9	42.5
80°	60.1	57.1	54.0	51.0	47.9	44.8	41.7	38.5	35.3	32.2	31.9
82.5°	45.7	42.9	40.1	37.3	34.5	32.2	30.4	28.6	26.8	25.0	24.8
85°	25.6	23.5	21.4	19.2	17.1	15.9	15.6	15.3	15.0	14.7	14.5
87.5°	8.9	8.6	8.6	8.1	7.6	7.2	8.3	8.3	8.6	8.9	8.6
90°	1.0	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0
92.5°	11.4	16.6	26.0	38.1	52.7	73.5	124.2	201.7	277.1	316.7	263.8
95°	32.9	35.9	45.9	58.9	82.9	124.8	211.6	375.4	614.0	813.6	836.6
97.5°	59.1	59.1	67.7	79.7	100.2	135.4	202.3	337.4	574.6	856.9	1051.0
100°	75.9	75.9	82.9	94.8	113.8	145.8	204.7	317.5	521.1	802.6	1058.2
102.5°	91.8	93.4	99.6	110.8	129.0	159.3	212.6	311.9	485.2	734.8	998.3
105°	116.8	119.8	124.8	136.8	154.7	183.7	231.6	314.5	454.2	654.9	889.5
107.5°	144.4	146.4	151.3	164.1	181.3	209.8	253.8	329.2	448.6	610.2	801.6
110°	162.7	164.7	169.7	181.7	199.7	226.6	270.5	340.4	450.2	595.0	757.7



TEST NUMBER: P332888

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	180.3	182.3	188.1	199.3	217.2	244.2	286.5	352.4	455.0	587.8	733.0
115°	205.7	208.6	215.6	225.6	244.6	271.5	311.5	371.4	464.2	584.0	709.8
117.5°	232.0	234.8	241.0	252.0	269.7	297.7	335.6	390.7	474.0	583.0	699.4
120°	249.6	251.6	258.6	269.5	286.5	314.5	352.4	404.3	481.2	583.0	693.8
122.5°	265.6	267.5	274.5	284.7	303.3	330.4	368.4	417.1	488.4	582.2	687.4
125°	286.5	290.5	296.5	307.5	326.4	354.4	390.3	436.3	499.2	581.0	676.9
127.5°	305.1	308.3	315.5	328.0	347.8	376.0	410.7	452.8	507.7	578.8	662.7
130°	315.5	319.5	327.4	342.4	361.4	390.3	424.3	463.2	514.1	578.0	653.9
132.5°	325.8	329.0	339.4	353.6	374.2	401.5	435.5	473.6	519.7	577.2	645.9
135°	340.4	344.4	354.4	371.4	392.3	418.3	451.2	487.2	528.1	576.0	633.9
137.5°	355.0	358.8	369.8	385.9	407.7	432.5	463.2	496.8	533.1	575.8	623.5
140°	365.4	368.4	379.4	396.3	417.3	441.3	471.2	503.1	537.1	575.0	618.0
142.5°	376.6	379.6	389.7	405.9	426.1	449.2	478.4	507.9	540.3	575.0	613.2
145°	392.3	395.3	405.3	419.3	438.3	460.2	486.2	513.1	542.1	573.0	605.0
147.5°	410.1	411.1	419.9	434.3	450.0	469.8	494.2	517.7	543.1	569.4	597.6
150°	421.3	422.3	430.3	442.3	457.2	476.2	498.2	520.1	543.1	567.0	592.0
152.5°	431.7	431.9	439.9	451.0	464.4	481.8	501.4	521.7	541.5	563.0	585.6
155°	446.2	447.2	453.2	463.2	474.2	489.2	506.1	523.1	539.1	557.1	576.0
157.5°	460.4	460.4	466.0	473.8	483.4	495.2	509.5	523.1	536.5	550.9	566.2
160°	469.2	469.2	473.2	480.2	488.2	499.2	511.1	523.1	534.1	546.1	559.1
162.5°	477.2	476.4	479.6	485.8	493.0	501.6	512.7	523.1	531.7	541.3	552.7
165°	486.2	486.2	488.2	493.2	498.2	504.1	513.1	521.1	527.1	534.1	542.1
167.5°	495.2	494.2	495.2	499.0	501.8	506.3	512.9	518.7	522.3	526.9	532.5
170°	499.2	498.2	499.2	502.2	504.1	507.1	512.1	517.1	519.1	522.1	526.1
172.5°	503.1	502.2	502.3	504.5	505.7	507.9	511.3	515.5	515.9	517.3	520.5
175°	507.1	506.1	506.1	507.1	508.1	508.1	510.1	513.1	512.1	512.1	514.1
177.5°	508.9	508.1	507.3	508.1	508.1	508.1	508.9	510.5	508.9	508.9	509.7
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332888

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	615.9	616.8	617.7	618.1	618.0	618.0	617.9	617.8
5°	611.8	612.8	613.9	614.3	614.1	613.9	613.6	613.4
7.5°	603.6	604.3	605.0	605.1	604.8	604.5	604.1	603.8
10°	596.3	596.7	597.1	597.1	596.7	596.3	595.9	595.5
12.5°	587.2	587.5	587.8	587.6	587.0	586.4	585.8	585.2
15°	571.4	571.2	570.9	570.5	569.7	569.0	568.3	567.5
17.5°	552.2	551.7	551.1	550.2	549.1	548.0	546.9	545.8
20°	538.9	538.0	537.2	536.1	534.7	533.3	532.0	530.6
22.5°	524.0	522.7	521.5	520.3	519.2	518.1	517.0	515.8
25°	500.0	498.3	496.5	495.1	494.0	492.9	491.9	490.8
27.5°	475.6	473.4	471.2	469.4	467.8	466.3	464.8	463.3
30°	458.1	455.5	452.9	450.7	449.0	447.4	445.7	444.0
32.5°	440.3	437.2	434.2	431.8	430.2	428.6	427.0	425.4
35°	413.6	410.1	406.5	403.8	401.9	400.0	398.1	396.2
37.5°	385.1	381.1	377.1	374.1	372.2	370.3	368.4	366.5
40°	366.0	361.6	357.2	354.1	352.2	350.3	348.4	346.5
42.5°	347.3	342.8	338.3	335.1	333.1	331.1	329.1	327.2
45°	318.7	313.5	308.3	304.8	302.9	301.0	299.1	297.3
47.5°	289.8	284.4	279.1	275.4	273.3	271.2	269.1	267.1
50°	270.6	265.4	260.1	256.5	254.5	252.5	250.5	248.5
52.5°	251.5	246.2	240.9	237.1	235.1	233.0	230.9	228.8
55°	223.4	217.9	212.4	208.7	206.7	204.7	202.7	200.7
57.5°	195.8	190.3	184.7	181.2	179.7	178.2	176.6	175.1
60°	177.4	172.0	166.5	162.9	161.2	159.6	157.9	156.2
62.5°	159.4	154.3	149.3	146.1	144.7	143.4	142.0	140.7
65°	133.4	128.9	124.4	121.5	120.2	119.0	117.7	116.4
67.5°	109.6	105.7	101.8	99.2	97.8	96.4	95.0	93.6
70°	93.4	89.9	86.5	84.2	83.1	82.1	81.0	80.0
72.5°	78.9	75.9	73.0	71.0	70.0	69.1	68.1	67.1
75°	58.1	55.7	53.3	51.8	51.1	50.5	49.9	49.2
77.5°	41.1	39.7	38.3	37.5	37.3	37.1	36.9	36.7
80°	31.6	31.2	30.9	30.7	30.6	30.5	30.4	30.3
82.5°	24.5	24.3	24.1	23.9	23.8	23.7	23.6	23.5
85°	14.3	14.0	13.8	13.7	13.7	13.7	13.7	13.7
87.5°	8.7	8.8	9.0	9.0	9.2	9.5	9.4	9.5
90°	18.0	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	196.1	147.6	117.4	97.4	85.7	80.3	76.9	76.9
95°	739.7	585.0	451.2	354.4	305.5	274.5	256.6	243.6
97.5°	1093.0	1035.4	937.8	833.6	761.9	701.8	671.9	651.1
100°	1204.0	1223.9	1175.0	1101.1	1014.3	953.4	923.4	915.5
102.5°	1198.4	1297.4	1311.6	1280.8	1227.5	1183.4	1151.9	1145.5
105°	1118.1	1290.8	1389.6	1430.6	1432.6	1424.6	1410.6	1404.6
107.5°	1004.1	1188.0	1327.2	1416.2	1465.5	1488.3	1498.3	1500.9
110°	935.4	1108.1	1252.9	1362.7	1433.6	1475.5	1493.5	1502.5



TEST NUMBER: P332888

CATALOG NUMBER: SA4XXRDIP-C350D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	885.1	1037.8	1174.6	1284.4	1364.9	1415.6	1440.8	1455.3
115°	834.6	957.4	1074.2	1170.0	1248.9	1308.8	1340.7	1348.7
117.5°	809.8	911.5	1003.3	1084.6	1151.9	1202.2	1234.5	1240.7
120°	798.6	891.5	971.4	1042.2	1099.1	1143.1	1169.0	1180.0
122.5°	789.1	878.7	951.4	1013.5	1061.6	1099.1	1121.1	1132.1
125°	772.7	858.5	927.4	982.3	1022.3	1051.2	1070.2	1076.2
127.5°	752.7	834.8	903.5	955.6	995.7	1021.5	1037.4	1043.4
130°	736.8	815.6	883.5	936.4	977.3	1002.3	1018.3	1024.3
132.5°	720.0	794.1	860.3	913.3	953.4	981.5	996.7	1002.7
135°	696.8	761.7	822.6	872.5	912.5	940.4	956.4	962.4
137.5°	675.9	730.8	782.1	827.2	864.5	892.1	905.3	912.5
140°	663.9	710.8	755.7	797.6	832.6	854.6	868.5	876.5
142.5°	652.7	694.0	732.6	768.9	799.8	820.2	832.6	838.2
145°	636.9	670.9	700.8	728.8	753.7	770.7	780.7	785.7
147.5°	623.9	650.9	674.9	696.8	715.2	729.8	737.4	739.1
150°	616.0	638.9	658.9	676.9	692.8	705.8	711.8	712.8
152.5°	607.2	626.9	645.3	660.1	673.7	684.2	687.8	688.8
155°	594.0	610.0	624.9	636.9	646.9	654.9	657.9	657.9
157.5°	579.8	593.2	605.8	615.4	622.9	628.9	630.7	630.7
160°	571.0	582.0	593.0	601.0	607.0	613.0	614.0	614.0
162.5°	562.2	571.6	580.2	587.4	591.8	597.8	598.8	598.0
165°	550.1	556.1	563.0	568.0	572.0	576.0	575.0	574.0
167.5°	538.3	542.9	548.5	551.5	553.5	556.1	555.9	555.1
170°	531.1	534.1	538.1	541.1	543.1	544.1	543.1	543.1
172.5°	524.7	526.9	529.3	531.5	532.7	533.7	532.7	531.1
175°	516.1	517.1	519.1	519.1	519.1	521.1	519.1	517.1
177.5°	510.5	511.3	511.3	512.1	511.3	512.1	510.5	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1

(END OF REPORT)