

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332893

Luminaire Tested: **SA4XXRDIP-C350D1205U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332893
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D1205U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5600.5 lumens
Efficiency: N/A
Efficacy: 132.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332893

CATALOG NUMBER: SA4XXRDIP-C350D1205U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332893

CATALOG NUMBER: SA4XXRDIP-C350D1205U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26				
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22				
2	84	77	71	67	75	69	64	60	54	50	48	40	37	36	26	25	24	18				
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16				
4	70	60	53	47	62	54	47	43	42	38	34	31	28	26	21	19	18	14				
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12				
6	59	48	40	35	53	43	36	31	34	29	25	25	22	20	17	15	14	11				
7	55	43	35	30	49	39	32	28	31	26	22	23	20	17	16	14	12	9				
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	14	12	11	8				
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8				
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4991	4991	4991
5°	5002	4941	4971
10°	4970	4882	4882
15°	4914	4779	4743
20°	4835	4643	4558
25°	4735	4486	4372
30°	4638	4320	4139
35°	4529	4147	3905
40°	4400	3951	3652
45°	4280	3756	3394
50°	4143	3532	3121
55°	3997	3298	2825
60°	3836	3042	2522
65°	3689	2722	2223
70°	3474	2367	1888
75°	3203	1965	1535
80°	2794	1497	1409
85°	2371	1362	1269



TEST NUMBER: P332893

CATALOG NUMBER: SA4XXRDIP-C350D1205U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	1.0
10°-20°	161.9	2.9
20°-30°	233.8	4.2
30°-40°	265.1	4.7
40°-50°	255.9	4.6
50°-60°	212.8	3.8
60°-70°	147.0	2.6
70°-80°	74.5	1.3
80°-90°	23.6	0.4
90°-100°	99.1	1.8
100°-110°	293.5	5.2
110°-120°	498.2	8.9
120°-130°	656.9	11.7
130°-140°	737.7	13.2
140°-150°	724.9	12.9
150°-160°	609.7	10.9
160°-170°	405.7	7.2
170°-180°	142.1	2.5
0°-30°	453.8	8.1
0°-40°	718.9	12.8
0°-60°	1187.7	21.2
0°-90°	1432.7	25.6
90°-120°	890.8	15.9
90°-150°	3010.3	53.8
90°-180°	4168.0	74.4
0°-180°	5600.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	613	59
15°	588	583	572	571	568	166
25°	532	522	504	496	491	245
35°	460	444	421	405	396	287
45°	375	357	329	307	297	289
55°	284	264	234	211	201	254
65°	193	172	142	123	116	191
75°	103	85	63	53	49	108
85°	26	16	15	14	14	29
90°	4	16	26	32	35	6
95°	70	80	88	92	92	78
105°	271	272	276	280	284	287
115°	506	506	504	503	502	499
125°	738	738	737	734	732	657
135°	952	958	958	956	953	736
145°	1156	1160	1162	1160	1157	723
155°	1324	1324	1323	1327	1323	609
165°	1442	1438	1436	1442	1438	406
175°	1500	1494	1493	1500	1493	142
180°	1502	1502	1502	1502	1502	



TEST NUMBER: P332893

CATALOG NUMBER: SA4XXRDIP-C350D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	619.7	619.3	619.0	618.7	618.3	617.7	616.8	615.9	614.9	614.0	614.9
5°	617.2	616.8	616.4	616.0	615.5	614.7	613.4	612.2	610.9	609.7	610.7
7.5°	611.6	611.2	610.8	610.3	609.9	608.8	607.2	605.5	603.9	602.3	602.9
10°	606.3	605.8	605.3	604.8	604.2	603.0	601.1	599.2	597.3	595.5	595.9
12.5°	599.5	598.9	598.3	597.7	597.1	595.7	593.4	591.2	589.0	586.7	587.0
15°	587.9	586.9	586.0	585.0	584.1	582.3	579.7	577.0	574.4	571.8	571.6
17.5°	573.8	572.4	571.0	569.7	568.3	566.0	562.9	559.7	556.6	553.4	552.8
20°	562.8	561.4	560.1	558.7	557.3	554.9	551.3	547.7	544.1	540.5	539.7
22.5°	550.7	549.1	547.6	546.1	544.5	541.8	538.0	534.2	530.4	526.5	525.3
25°	531.6	529.7	527.8	525.9	524.0	520.9	516.6	512.3	507.9	503.6	501.8
27.5°	511.5	509.1	506.7	504.4	502.0	498.5	493.9	489.3	484.7	480.1	477.8
30°	497.5	494.8	492.2	489.6	487.0	483.2	478.2	473.3	468.3	463.4	460.8
32.5°	482.7	479.7	476.8	473.8	470.8	466.8	461.7	456.6	451.5	446.4	443.3
35°	459.6	456.2	452.9	449.5	446.1	441.8	436.6	431.3	426.1	420.8	417.2
37.5°	434.9	431.4	428.0	424.5	421.0	416.4	410.5	404.7	398.9	393.1	389.1
40°	417.5	414.0	410.5	407.1	403.6	398.9	392.9	386.9	380.9	374.9	370.5
42.5°	400.8	397.2	393.5	389.9	386.3	381.3	375.1	368.8	362.6	356.3	351.8
45°	374.9	371.0	367.1	363.2	359.3	354.2	347.9	341.6	335.3	329.0	323.8
47.5°	348.1	344.1	340.1	336.0	332.0	326.7	320.2	313.6	307.0	300.5	295.1
50°	329.9	325.8	321.7	317.6	313.5	308.1	301.4	294.6	287.9	281.2	275.9
52.5°	311.4	307.3	303.3	299.3	295.3	289.8	282.9	276.0	269.1	262.2	256.9
55°	284.0	279.8	275.6	271.4	267.2	261.6	254.8	248.0	241.1	234.3	228.8
57.5°	256.9	252.5	248.2	243.8	239.4	233.9	227.1	220.4	213.7	206.9	201.4
60°	237.6	233.4	229.2	225.0	220.8	215.3	208.6	201.8	195.1	188.4	182.9
62.5°	220.2	215.8	211.4	207.1	202.7	197.1	190.2	183.3	176.4	169.5	164.4
65°	193.1	188.6	184.1	179.6	175.0	169.4	162.7	155.9	149.2	142.5	138.0
67.5°	165.0	160.7	156.3	152.0	147.7	142.4	136.1	129.9	123.6	117.4	113.5
70°	147.2	142.8	138.4	134.0	129.5	124.3	118.3	112.3	106.3	100.3	96.9
72.5°	128.3	124.3	120.3	116.3	112.3	107.5	101.8	96.1	90.5	84.8	81.9
75°	102.7	98.8	94.9	91.0	87.1	82.7	77.8	72.8	67.9	63.0	60.5
77.5°	76.8	73.5	70.2	66.9	63.6	59.9	55.9	51.9	47.9	43.9	42.5
80°	60.1	57.1	54.0	51.0	47.9	44.8	41.7	38.5	35.3	32.2	31.9
82.5°	45.7	42.9	40.1	37.3	34.5	32.2	30.4	28.6	26.8	25.0	24.8
85°	25.6	23.5	21.4	19.2	17.1	15.9	15.6	15.3	15.0	14.7	14.5
87.5°	9.4	9.3	9.2	9.1	9.0	9.1	9.4	9.8	10.1	10.4	10.6
90°	3.5	6.3	9.2	12.0	14.8	17.3	19.4	21.4	23.5	25.6	27.1
92.5°	24.9	28.1	31.4	34.6	37.9	40.2	41.7	43.1	44.6	46.0	46.9
95°	69.7	72.0	74.4	76.7	79.0	81.1	82.9	84.7	86.5	88.3	89.1
97.5°	121.8	123.6	125.5	127.3	129.2	131.2	133.3	135.4	137.5	139.6	140.6
100°	162.7	163.7	164.7	165.7	166.8	168.5	170.8	173.1	175.4	177.8	178.3
102.5°	205.4	205.8	206.2	206.6	207.1	208.3	210.4	212.6	214.7	216.8	217.5
105°	270.7	271.0	271.2	271.5	271.7	272.4	273.4	274.4	275.5	276.5	277.3
107.5°	339.2	339.6	339.9	340.2	340.5	340.7	340.9	341.0	341.2	341.3	342.1
110°	385.7	386.2	386.7	387.3	387.8	387.9	387.7	387.4	387.1	386.9	386.4



TEST NUMBER: P332893

CATALOG NUMBER: SA4XXRDIP-C350D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	434.0	434.2	434.3	434.4	434.5	434.3	433.8	433.4	432.9	432.4	432.3
115°	506.5	506.5	506.5	506.5	506.5	506.3	505.8	505.3	504.7	504.2	504.0
117.5°	574.9	575.1	575.3	575.5	575.7	575.6	575.2	574.9	574.5	574.2	573.3
120°	620.4	621.4	622.5	623.5	624.5	624.7	623.9	623.1	622.3	621.6	620.3
122.5°	667.8	668.2	668.6	669.0	669.5	669.5	669.1	668.8	668.4	668.0	667.2
125°	737.7	737.7	737.7	737.7	737.7	737.6	737.4	737.1	736.8	736.6	736.1
127.5°	801.2	802.0	802.7	803.5	804.3	804.5	804.0	803.6	803.2	802.8	802.3
130°	845.8	846.6	847.3	848.1	848.9	849.3	849.3	849.3	849.3	849.3	848.8
132.5°	891.3	891.9	892.5	893.0	893.6	893.8	893.6	893.4	893.2	893.0	892.4
135°	951.5	953.1	954.6	956.2	957.7	958.5	958.5	958.5	958.5	958.5	958.0
137.5°	1017.0	1017.8	1018.5	1019.2	1019.9	1020.5	1020.9	1021.3	1021.7	1022.1	1021.5
140°	1060.7	1061.2	1061.8	1062.3	1062.8	1063.0	1063.0	1063.0	1063.0	1063.0	1062.8
142.5°	1100.7	1101.2	1101.7	1102.2	1102.8	1102.9	1102.7	1102.5	1102.3	1102.1	1102.0
145°	1156.0	1157.0	1158.1	1159.1	1160.1	1160.8	1161.0	1161.3	1161.5	1161.8	1161.5
147.5°	1210.8	1212.1	1213.3	1214.5	1215.8	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3
150°	1244.3	1245.3	1246.4	1247.4	1248.4	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9
152.5°	1275.9	1276.5	1277.1	1277.7	1278.4	1278.8	1279.0	1279.2	1279.4	1279.6	1280.2
155°	1324.4	1324.4	1324.4	1324.4	1324.4	1324.3	1324.1	1323.8	1323.5	1323.3	1324.3
157.5°	1365.3	1364.9	1364.4	1364.0	1363.5	1363.2	1363.2	1363.1	1363.1	1363.0	1363.8
160°	1389.5	1389.3	1389.0	1388.7	1388.5	1388.2	1388.0	1387.7	1387.4	1387.2	1388.0
162.5°	1411.8	1411.1	1410.5	1409.8	1409.1	1408.7	1408.4	1408.2	1407.9	1407.6	1409.0
165°	1441.8	1441.0	1440.2	1439.5	1438.7	1438.0	1437.5	1437.0	1436.5	1436.0	1437.5
167.5°	1464.8	1463.7	1462.6	1461.5	1460.5	1459.9	1460.0	1460.0	1460.1	1460.1	1461.7
170°	1477.8	1476.5	1475.2	1473.9	1472.6	1472.1	1472.4	1472.6	1472.9	1473.2	1474.7
172.5°	1487.1	1486.0	1484.9	1483.8	1482.8	1482.2	1482.3	1482.4	1482.4	1482.5	1484.2
175°	1499.9	1498.6	1497.3	1496.0	1494.7	1493.9	1493.7	1493.4	1493.2	1492.9	1494.7
177.5°	1504.1	1503.0	1502.0	1501.0	1499.9	1499.4	1499.4	1499.4	1499.4	1499.4	1500.9
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2



TEST NUMBER: P332893

CATALOG NUMBER: SA4XXRDIP-C350D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	615.9	616.8	617.7	618.1	618.0	618.0	617.9	617.8
5°	611.8	612.8	613.9	614.3	614.1	613.9	613.6	613.4
7.5°	603.6	604.3	605.0	605.1	604.8	604.5	604.1	603.8
10°	596.3	596.7	597.1	597.1	596.7	596.3	595.9	595.5
12.5°	587.2	587.5	587.8	587.6	587.0	586.4	585.8	585.2
15°	571.4	571.2	570.9	570.5	569.7	569.0	568.3	567.5
17.5°	552.2	551.7	551.1	550.2	549.1	548.0	546.9	545.8
20°	538.9	538.0	537.2	536.1	534.7	533.3	532.0	530.6
22.5°	524.0	522.7	521.5	520.3	519.2	518.1	517.0	515.8
25°	500.0	498.3	496.5	495.1	494.0	492.9	491.9	490.8
27.5°	475.6	473.4	471.2	469.4	467.8	466.3	464.8	463.3
30°	458.1	455.5	452.9	450.7	449.0	447.4	445.7	444.0
32.5°	440.3	437.2	434.2	431.8	430.2	428.6	427.0	425.4
35°	413.6	410.1	406.5	403.8	401.9	400.0	398.1	396.2
37.5°	385.1	381.1	377.1	374.1	372.2	370.3	368.4	366.5
40°	366.0	361.6	357.2	354.1	352.2	350.3	348.4	346.5
42.5°	347.3	342.8	338.3	335.1	333.1	331.1	329.1	327.2
45°	318.7	313.5	308.3	304.8	302.9	301.0	299.1	297.3
47.5°	289.8	284.4	279.1	275.4	273.3	271.2	269.1	267.1
50°	270.6	265.4	260.1	256.5	254.5	252.5	250.5	248.5
52.5°	251.5	246.2	240.9	237.1	235.1	233.0	230.9	228.8
55°	223.4	217.9	212.4	208.7	206.7	204.7	202.7	200.7
57.5°	195.8	190.3	184.7	181.2	179.7	178.2	176.6	175.1
60°	177.4	172.0	166.5	162.9	161.2	159.6	157.9	156.2
62.5°	159.4	154.3	149.3	146.1	144.7	143.4	142.0	140.7
65°	133.4	128.9	124.4	121.5	120.2	119.0	117.7	116.4
67.5°	109.6	105.7	101.8	99.2	97.8	96.4	95.0	93.6
70°	93.4	89.9	86.5	84.2	83.1	82.1	81.0	80.0
72.5°	78.9	75.9	73.0	71.0	70.0	69.1	68.1	67.1
75°	58.1	55.7	53.3	51.8	51.1	50.5	49.9	49.2
77.5°	41.1	39.7	38.3	37.5	37.3	37.1	36.9	36.7
80°	31.6	31.2	30.9	30.7	30.6	30.5	30.4	30.3
82.5°	24.5	24.3	24.1	23.9	23.8	23.7	23.6	23.5
85°	14.3	14.0	13.8	13.7	13.7	13.7	13.7	13.7
87.5°	10.9	11.1	11.3	11.5	11.7	11.9	12.1	12.3
90°	28.7	30.2	31.8	32.8	33.3	33.8	34.3	34.9
92.5°	47.9	48.8	49.7	50.3	50.7	51.0	51.3	51.6
95°	89.8	90.6	91.4	91.8	91.8	91.8	91.8	91.8
97.5°	141.5	142.4	143.4	143.8	143.8	143.8	143.8	143.8
100°	178.8	179.3	179.8	180.1	180.1	180.1	180.1	180.1
102.5°	218.2	219.0	219.7	220.1	220.4	220.6	220.8	221.0
105°	278.1	278.8	279.6	280.4	281.2	281.9	282.7	283.5
107.5°	342.8	343.5	344.2	344.6	344.5	344.5	344.4	344.4
110°	385.8	385.3	384.8	384.9	385.7	386.5	387.3	388.0



TEST NUMBER: P332893

CATALOG NUMBER: SA4XXRDIP-C350D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.2	432.1	432.0	432.0	432.2	432.3	432.5	432.7
115°	503.7	503.4	503.2	502.9	502.7	502.4	502.2	501.9
117.5°	572.4	571.5	570.6	570.0	569.4	568.9	568.4	567.9
120°	619.0	617.7	616.4	616.0	616.5	617.0	617.6	618.1
122.5°	666.3	665.4	664.5	663.6	662.7	661.8	660.8	659.9
125°	735.5	735.0	734.5	734.0	733.5	733.0	732.4	731.9
127.5°	801.8	801.3	800.7	800.3	799.9	799.4	799.0	798.6
130°	848.2	847.7	847.2	846.4	845.4	844.4	843.3	842.3
132.5°	891.9	891.4	890.9	890.4	890.0	889.6	889.2	888.8
135°	957.5	956.9	956.4	955.8	955.0	954.2	953.4	952.7
137.5°	1020.8	1020.1	1019.5	1019.2	1019.4	1019.5	1019.7	1019.8
140°	1062.5	1062.3	1062.0	1061.8	1061.5	1061.2	1061.0	1060.7
142.5°	1102.0	1101.9	1101.9	1101.8	1101.8	1101.7	1101.7	1101.6
145°	1161.3	1161.0	1160.8	1160.2	1159.5	1158.7	1157.9	1157.2
147.5°	1215.1	1214.9	1214.6	1214.4	1214.2	1213.9	1213.6	1213.4
150°	1248.9	1248.9	1248.9	1248.8	1248.5	1248.3	1248.0	1247.8
152.5°	1280.8	1281.5	1282.1	1282.1	1281.4	1280.7	1280.0	1279.4
155°	1325.4	1326.4	1327.4	1327.4	1326.4	1325.4	1324.3	1323.3
157.5°	1364.6	1365.3	1366.1	1366.1	1365.2	1364.3	1363.4	1362.6
160°	1388.7	1389.5	1390.3	1390.0	1388.7	1387.4	1386.2	1384.9
162.5°	1410.4	1411.8	1413.2	1413.3	1412.0	1410.7	1409.4	1408.1
165°	1439.1	1440.6	1442.2	1442.4	1441.4	1440.4	1439.3	1438.3
167.5°	1463.2	1464.8	1466.3	1466.3	1464.7	1463.1	1461.5	1459.9
170°	1476.3	1477.8	1479.4	1479.2	1477.4	1475.6	1473.8	1472.0
172.5°	1486.0	1487.7	1489.5	1489.5	1487.6	1485.8	1484.0	1482.2
175°	1496.5	1498.3	1500.1	1500.1	1498.3	1496.5	1494.7	1492.9
177.5°	1502.3	1503.8	1505.2	1505.1	1503.4	1501.8	1500.1	1498.5
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2

(END OF REPORT)