

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332898

Luminaire Tested: **SA4XXRDIP-C575D365U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332898
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D365U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3811.0 lumens
Efficiency: N/A
Efficacy: 138.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332898

CATALOG NUMBER: SA4XXRDIP-C575D365U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332898

CATALOG NUMBER: SA4XXRDIP-C575D365U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62				
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	60	58	57	53				
2	92	85	79	73	86	80	74	70	70	66	62	61	58	55	53	51	49	45				
3	84	75	67	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38				
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	42	39	36	33				
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	35	32	29				
6	66	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25				
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23				
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	23	20				
9	53	40	33	28	49	38	31	27	34	29	25	31	26	22	27	23	20	18				
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8205	8205	8205
5°	8223	8122	8173
10°	8171	8025	8025
15°	8078	7856	7798
20°	7948	7635	7494
25°	7784	7375	7187
30°	7623	7101	6804
35°	7447	6818	6419
40°	7233	6495	6003
45°	7036	6174	5579
50°	6812	5805	5130
55°	6572	5422	4643
60°	6307	5000	4146
65°	6065	4474	3656
70°	5712	3895	3104
75°	5268	3228	2523
80°	4593	2459	2315
85°	3890	2232	2093



TEST NUMBER: P332898

CATALOG NUMBER: SA4XXRDIP-C575D365U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	2.5
10°-20°	266.2	7.0
20°-30°	384.4	10.1
30°-40°	435.7	11.4
40°-50°	420.8	11.0
50°-60°	349.9	9.2
60°-70°	241.6	6.3
70°-80°	122.5	3.2
80°-90°	32.8	0.9
90°-100°	16.2	0.4
100°-110°	103.0	2.7
110°-120°	197.1	5.2
120°-130°	250.2	6.6
130°-140°	267.7	7.0
140°-150°	250.4	6.6
150°-160°	201.9	5.3
160°-170°	130.2	3.4
170°-180°	44.9	1.2
0°-30°	746.1	19.6
0°-40°	1181.8	31.0
0°-60°	1952.5	51.2
0°-90°	2349.4	61.6
90°-120°	316.3	8.3
90°-150°	1084.6	28.5
90°-180°	1462.0	38.4
0°-180°	3811.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1015	1011	1002	1010	1008	96
15°	966	959	940	938	933	272
25°	874	859	828	815	807	402
35°	756	730	692	666	651	472
45°	616	586	541	504	489	475
55°	467	435	385	346	330	418
65°	318	283	234	202	191	313
75°	169	140	104	86	81	178
85°	42	27	24	23	23	47
90°	1	5	8	10	11	3
95°	19	8	8	10	10	25
105°	106	108	110	113	101	111
115°	199	200	199	200	200	195
125°	279	280	280	281	281	249
135°	346	346	347	348	349	267
145°	399	400	400	401	402	249
155°	438	438	437	438	438	202
165°	462	460	460	463	460	130
175°	472	470	471	474	470	45
180°	472	472	472	472	472	



TEST NUMBER: P332898

CATALOG NUMBER: SA4XXRDIP-C575D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1018.8	1018.2	1017.7	1017.1	1016.6	1015.5	1014.0	1012.5	1010.9	1009.4	1010.9
5°	1014.7	1014.0	1013.3	1012.6	1012.0	1010.6	1008.5	1006.4	1004.3	1002.3	1004.0
7.5°	1005.5	1004.8	1004.1	1003.4	1002.6	1000.9	998.2	995.5	992.8	990.1	991.2
10°	996.8	996.0	995.1	994.2	993.4	991.4	988.3	985.1	982.0	978.9	979.6
12.5°	985.6	984.6	983.6	982.6	981.6	979.3	975.6	971.9	968.3	964.6	965.0
15°	966.5	964.9	963.4	961.8	960.2	957.3	953.0	948.7	944.3	940.0	939.7
17.5°	943.3	941.0	938.8	936.5	934.3	930.6	925.4	920.2	915.0	909.8	908.9
20°	925.2	923.0	920.7	918.5	916.2	912.2	906.3	900.4	894.5	888.7	887.3
22.5°	905.3	902.8	900.3	897.7	895.2	890.8	884.5	878.2	871.9	865.6	863.5
25°	873.9	870.8	867.6	864.5	861.4	856.3	849.2	842.1	835.0	828.0	825.0
27.5°	840.9	837.0	833.1	829.2	825.2	819.5	811.9	804.4	796.8	789.2	785.6
30°	817.8	813.5	809.2	804.9	800.6	794.3	786.2	778.1	769.9	761.8	757.5
32.5°	793.6	788.7	783.8	778.9	774.1	767.4	759.0	750.6	742.2	733.8	728.8
35°	755.6	750.1	744.5	739.0	733.5	726.4	717.7	709.1	700.4	691.8	685.9
37.5°	715.0	709.3	703.6	697.9	692.1	684.5	674.9	665.3	655.8	646.2	639.6
40°	686.3	680.6	674.9	669.2	663.5	655.7	645.9	636.0	626.2	616.3	609.0
42.5°	658.9	653.0	647.0	641.0	635.0	626.9	616.6	606.3	596.1	585.8	578.4
45°	616.3	609.9	603.5	597.1	590.7	582.3	571.9	561.6	551.2	540.8	532.3
47.5°	572.3	565.7	559.0	552.4	545.8	537.1	526.3	515.6	504.8	494.0	485.2
50°	542.4	535.6	528.9	522.1	515.4	506.5	495.4	484.4	473.3	462.2	453.6
52.5°	511.9	505.3	498.7	492.1	485.4	476.5	465.1	453.8	442.4	431.1	422.3
55°	466.9	460.0	453.1	446.1	439.2	430.1	418.9	407.7	396.4	385.2	376.2
57.5°	422.4	415.2	408.0	400.8	393.6	384.5	373.4	362.3	351.3	340.2	331.1
60°	390.6	383.7	376.8	369.9	363.0	354.0	342.9	331.8	320.8	309.7	300.7
62.5°	362.0	354.8	347.6	340.4	333.2	324.0	312.6	301.3	289.9	278.6	270.3
65°	317.5	310.1	302.6	295.2	287.7	278.5	267.4	256.4	245.3	234.2	226.8
67.5°	271.3	264.1	257.0	249.9	242.8	234.1	223.8	213.5	203.3	193.0	186.6
70°	242.0	234.7	227.5	220.2	213.0	204.4	194.5	184.7	174.8	165.0	159.3
72.5°	210.9	204.3	197.7	191.2	184.6	176.7	167.4	158.1	148.7	139.4	134.6
75°	168.9	162.5	156.1	149.7	143.3	136.0	127.9	119.7	111.6	103.5	99.5
77.5°	126.2	120.8	115.4	109.9	104.5	98.5	91.9	85.4	78.8	72.2	69.9
80°	98.8	93.8	88.8	83.8	78.8	73.7	68.5	63.3	58.1	52.9	52.4
82.5°	75.2	70.6	66.0	61.4	56.8	53.0	50.0	47.0	44.1	41.1	40.7
85°	42.0	38.6	35.1	31.6	28.2	26.2	25.7	25.2	24.6	24.1	23.8
87.5°	14.5	13.6	12.7	11.7	10.8	10.3	10.3	10.3	10.3	10.3	10.2
90°	1.1	1.9	2.8	3.7	4.5	5.3	5.9	6.5	7.1	7.8	8.2
92.5°	4.5	4.5	4.5	4.6	4.6	5.0	5.6	6.2	6.9	7.5	8.0
95°	19.4	16.8	14.1	11.4	8.8	7.5	7.5	7.6	7.7	7.8	8.2
97.5°	41.3	42.9	44.6	46.3	47.9	44.4	35.6	26.9	18.1	9.3	9.4
100°	58.0	59.4	60.8	62.2	63.6	58.9	48.1	37.2	26.4	15.6	14.2
102.5°	76.6	77.7	78.7	79.7	80.8	80.6	79.2	77.8	76.3	74.9	60.5
105°	106.4	106.8	107.3	107.8	108.3	108.7	109.1	109.5	109.9	110.3	111.0
107.5°	134.0	134.2	134.5	134.7	135.0	135.3	135.9	136.4	136.9	137.5	137.8
110°	152.7	152.9	153.1	153.4	153.6	154.0	154.4	154.9	155.4	155.9	156.0



TEST NUMBER: P332898

CATALOG NUMBER: SA4XXRDIP-C575D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.8	171.2	171.6	172.0	172.5	172.8	173.0	173.2	173.4	173.7	173.6
115°	198.6	198.9	199.1	199.3	199.6	199.6	199.6	199.5	199.4	199.3	199.5
117.5°	223.7	224.0	224.3	224.7	225.0	225.2	225.4	225.6	225.7	225.9	225.9
120°	240.7	241.0	241.3	241.6	241.9	242.0	242.0	241.9	241.8	241.7	241.9
122.5°	256.5	256.7	256.9	257.1	257.3	257.4	257.5	257.6	257.7	257.9	257.9
125°	279.2	279.5	279.8	280.1	280.5	280.5	280.4	280.2	280.1	279.9	280.1
127.5°	300.7	300.8	300.8	300.9	301.0	301.2	301.6	301.9	302.3	302.7	302.6
130°	314.5	314.6	314.7	314.8	314.9	315.0	315.2	315.5	315.7	316.0	316.0
132.5°	327.3	327.4	327.5	327.7	327.8	328.0	328.3	328.6	328.9	329.2	329.3
135°	346.3	346.3	346.2	346.1	346.0	346.1	346.5	346.8	347.1	347.4	347.6
137.5°	363.2	363.3	363.3	363.3	363.4	363.6	363.9	364.2	364.6	364.9	365.1
140°	374.3	374.4	374.6	374.7	374.9	375.0	375.2	375.4	375.5	375.7	375.9
142.5°	384.2	384.4	384.7	385.0	385.3	385.5	385.6	385.7	385.8	385.9	386.0
145°	399.4	399.6	399.8	400.1	400.3	400.4	400.4	400.4	400.4	400.4	400.5
147.5°	411.4	411.9	412.3	412.8	413.2	413.4	413.3	413.2	413.1	413.1	413.1
150°	420.2	420.5	420.8	421.2	421.5	421.6	421.5	421.4	421.3	421.3	421.3
152.5°	427.6	427.8	428.1	428.3	428.6	428.6	428.5	428.3	428.2	428.1	428.2
155°	437.9	438.0	438.0	438.1	438.2	438.1	437.9	437.6	437.4	437.2	437.5
157.5°	446.6	446.5	446.5	446.4	446.4	446.2	446.0	445.7	445.4	445.2	445.6
160°	451.7	451.4	451.2	451.0	450.7	450.6	450.5	450.4	450.3	450.2	450.7
162.5°	456.2	455.9	455.6	455.3	455.0	454.8	454.7	454.6	454.6	454.5	455.0
165°	461.9	461.5	461.1	460.7	460.3	460.1	460.1	460.1	460.1	460.1	460.8
167.5°	466.4	466.0	465.6	465.2	464.8	464.6	464.5	464.5	464.4	464.4	465.1
170°	469.0	468.5	468.0	467.6	467.1	466.9	467.0	467.1	467.1	467.2	467.8
172.5°	470.7	470.2	469.7	469.3	468.8	468.6	468.7	468.8	468.8	468.9	469.5
175°	472.5	472.0	471.6	471.1	470.6	470.4	470.5	470.6	470.7	470.7	471.5
177.5°	473.4	472.9	472.5	472.0	471.6	471.4	471.6	471.7	471.8	471.9	472.5
180°	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5



TEST NUMBER: P332898

CATALOG NUMBER: SA4XXRDIP-C575D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1012.5	1014.0	1015.5	1016.2	1016.1	1015.9	1015.8	1015.7
5°	1005.7	1007.5	1009.2	1009.9	1009.5	1009.2	1008.8	1008.5
7.5°	992.3	993.4	994.6	994.8	994.3	993.7	993.2	992.6
10°	980.3	981.0	981.7	981.7	981.0	980.3	979.6	978.9
12.5°	965.4	965.8	966.3	966.0	965.0	964.1	963.1	962.1
15°	939.3	939.0	938.6	937.9	936.6	935.4	934.2	933.0
17.5°	907.9	906.9	905.9	904.5	902.7	900.9	899.0	897.2
20°	885.9	884.5	883.1	881.3	879.1	876.8	874.6	872.3
22.5°	861.5	859.4	857.3	855.4	853.5	851.7	849.9	848.0
25°	822.1	819.1	816.2	813.9	812.1	810.4	808.7	806.9
27.5°	781.9	778.3	774.7	771.6	769.1	766.6	764.2	761.7
30°	753.2	748.8	744.5	741.0	738.2	735.4	732.7	729.9
32.5°	723.8	718.8	713.7	709.9	707.3	704.7	702.0	699.4
35°	680.0	674.1	668.3	663.8	660.7	657.5	654.4	651.3
37.5°	633.0	626.5	619.9	615.1	611.9	608.8	605.7	602.6
40°	601.8	594.5	587.2	582.1	578.9	575.8	572.7	569.6
42.5°	571.0	563.6	556.2	550.9	547.6	544.4	541.1	537.9
45°	523.9	515.4	506.9	501.1	498.0	494.9	491.8	488.7
47.5°	476.4	467.6	458.8	452.7	449.3	445.9	442.5	439.0
50°	444.9	436.3	427.6	421.7	418.4	415.1	411.8	408.5
52.5°	413.5	404.7	396.0	389.9	386.4	383.0	379.6	376.2
55°	367.2	358.2	349.2	343.1	339.8	336.5	333.2	329.9
57.5°	321.9	312.8	303.7	297.9	295.4	292.9	290.4	287.9
60°	291.7	282.7	273.7	267.9	265.1	262.3	259.6	256.8
62.5°	262.0	253.7	245.4	240.1	237.9	235.7	233.5	231.3
65°	219.4	211.9	204.5	199.7	197.7	195.6	193.5	191.4
67.5°	180.2	173.8	167.4	163.1	160.8	158.5	156.2	153.9
70°	153.6	147.9	142.1	138.4	136.7	135.0	133.2	131.5
72.5°	129.7	124.8	119.9	116.7	115.1	113.5	111.9	110.3
75°	95.5	91.6	87.6	85.1	84.0	83.0	82.0	80.9
77.5°	67.6	65.3	62.9	61.6	61.3	61.0	60.7	60.4
80°	51.9	51.4	50.8	50.5	50.3	50.1	50.0	49.8
82.5°	40.3	39.9	39.6	39.3	39.1	38.9	38.8	38.6
85°	23.4	23.1	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	10.2	10.1	10.1	10.2	10.3	10.5	10.7	10.8
90°	8.7	9.2	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	8.4	8.9	9.4	9.6	9.7	9.7	9.7	9.8
95°	8.7	9.2	9.7	9.9	10.0	10.1	10.2	10.2
97.5°	9.4	9.5	9.5	9.6	9.7	9.7	9.8	9.9
100°	12.9	11.5	10.2	9.6	9.7	9.7	9.8	9.9
102.5°	46.1	31.7	17.3	10.1	10.1	10.1	10.2	10.2
105°	111.7	112.4	113.1	112.0	109.2	106.4	103.5	100.7
107.5°	138.2	138.5	138.9	139.2	139.5	139.8	140.1	140.4
110°	156.2	156.3	156.5	156.7	156.9	157.2	157.4	157.6



TEST NUMBER: P332898

CATALOG NUMBER: SA4XXRDIP-C575D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	173.6	173.6	173.5	173.7	174.0	174.3	174.6	174.9
115°	199.6	199.8	200.0	200.0	200.0	200.0	200.0	200.0
117.5°	225.8	225.8	225.8	225.7	225.7	225.7	225.7	225.6
120°	242.0	242.2	242.4	242.4	242.2	242.0	241.9	241.7
122.5°	258.0	258.1	258.2	258.2	258.0	257.9	257.7	257.6
125°	280.4	280.6	280.8	281.0	281.1	281.2	281.2	281.3
127.5°	302.6	302.5	302.5	302.4	302.4	302.3	302.2	302.2
130°	316.1	316.2	316.3	316.3	316.3	316.3	316.3	316.3
132.5°	329.4	329.5	329.6	329.6	329.5	329.4	329.4	329.3
135°	347.7	347.9	348.0	348.2	348.3	348.5	348.7	348.8
137.5°	365.3	365.5	365.6	365.7	365.6	365.6	365.5	365.5
140°	376.1	376.4	376.6	376.8	376.9	376.9	377.0	377.1
142.5°	386.2	386.4	386.5	386.6	386.7	386.7	386.7	386.7
145°	400.6	400.7	400.7	400.8	401.0	401.2	401.3	401.5
147.5°	413.2	413.3	413.3	413.4	413.5	413.5	413.6	413.7
150°	421.3	421.3	421.3	421.3	421.4	421.5	421.5	421.6
152.5°	428.3	428.4	428.6	428.6	428.5	428.5	428.5	428.4
155°	437.8	438.1	438.4	438.5	438.2	438.0	437.8	437.5
157.5°	446.0	446.4	446.8	446.8	446.4	446.0	445.6	445.2
160°	451.2	451.7	452.1	452.1	451.7	451.2	450.7	450.2
162.5°	455.4	455.9	456.4	456.3	455.8	455.3	454.7	454.2
165°	461.4	462.0	462.7	462.6	461.9	461.2	460.5	459.8
167.5°	465.8	466.5	467.1	467.1	466.3	465.5	464.7	464.0
170°	468.5	469.1	469.7	469.6	468.9	468.1	467.3	466.5
172.5°	470.2	470.8	471.4	471.3	470.5	469.6	468.8	467.9
175°	472.2	472.9	473.6	473.5	472.5	471.6	470.6	469.7
177.5°	473.0	473.5	474.0	473.8	473.1	472.3	471.6	470.8
180°	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5

(END OF REPORT)