

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332951

Luminaire Tested: **SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332951  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7641.6 lumens  
Efficiency: N/A  
Efficacy: 134.3 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				
1	97	93	89	86	88	85	82	79	71	68	66	57	56	54	45	44	43	38				
2	88	81	75	71	81	75	70	65	62	59	56	51	48	46	40	39	37	32				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24				
5	68	57	49	43	62	53	46	40	44	39	35	36	33	30	29	27	24	21				
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17				
8	54	42	34	29	49	39	32	28	33	28	24	28	24	21	22	20	17	15				
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	23	20	17	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10656	10656	10656	10656
5°	12361	10689	9447	10689
10°	14623	10642	8432	10642
15°	16891	10543	7245	10543
20°	18806	10408	6552	10408
25°	19414	10276	6083	10276
30°	16995	10113	5800	10113
35°	13230	9875	5629	9875
40°	9921	9601	5538	9601
45°	7833	9162	5489	9162
50°	6612	8657	5330	8657
55°	5764	8099	5046	8099
60°	5186	7522	4466	7522
65°	4571	6898	3840	6898
70°	4116	6253	3465	6253
75°	3450	5540	2954	5540
80°	2920	4723	2771	4723
85°	2464	3696	2464	3696



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.9	1.7
10°-20°	385.8	5.0
20°-30°	603.4	7.9
30°-40°	670.8	8.8
40°-50°	595.2	7.8
50°-60°	463.8	6.1
60°-70°	303.6	4.0
70°-80°	149.3	2.0
80°-90°	40.1	0.5
90°-100°	427.2	5.6
100°-110°	889.1	11.6
110°-120°	796.4	10.4
120°-130°	669.9	8.8
130°-140°	558.5	7.3
140°-150°	426.7	5.6
150°-160°	299.9	3.9
160°-170°	176.4	2.3
170°-180°	57.4	0.8
0°-30°	1117.1	14.6
0°-40°	1787.9	23.4
0°-60°	2846.9	37.3
0°-90°	3340.0	43.7
90°-120°	2112.7	27.6
90°-150°	3767.8	49.3
90°-180°	4302.0	56.3
0°-180°	7641.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1320	1320	1320	1320	1320	
5°	1525	1319	1166	1319	1525	154
15°	2021	1262	867	1262	2021	575
25°	2180	1154	683	1154	2180	967
35°	1342	1002	571	1002	1342	841
45°	686	802	481	802	686	543
55°	410	575	358	575	410	372
65°	239	361	201	361	239	241
75°	111	178	95	178	111	122
85°	27	40	27	40	27	31
90°	24	1	24	1	24	21
95°	284	38	284	38	284	440
105°	1635	136	1635	136	1635	1616
115°	1570	239	1570	239	1570	1558
125°	1253	334	1253	334	1253	1138
135°	1120	396	1120	396	1120	865
145°	914	457	914	457	914	580
155°	766	519	766	519	766	357
165°	668	566	668	566	668	191
175°	602	590	602	590	602	59
180°	592	592	592	592	592	



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1392.3	1396.2	1392.3	1391.9	1387.7	1386.4	1384.7	1379.2	1368.9	1363.0	1364.3
5°	1525.3	1538.6	1531.2	1530.1	1518.4	1506.7	1499.2	1482.2	1464.1	1451.9	1441.8
7.5°	1679.1	1686.8	1682.1	1674.6	1655.7	1645.0	1627.7	1605.3	1572.9	1548.1	1525.4
10°	1783.8	1790.2	1788.0	1774.2	1760.4	1732.2	1716.2	1684.9	1643.9	1611.5	1581.2
12.5°	1886.7	1893.6	1874.8	1875.5	1849.3	1827.1	1801.8	1762.3	1715.0	1673.2	1635.2
15°	2021.0	2012.5	2012.5	2001.8	1972.6	1941.7	1915.7	1874.2	1814.6	1764.6	1712.0
17.5°	2126.1	2129.0	2124.7	2099.6	2076.6	2044.7	1996.9	1948.5	1893.2	1826.1	1772.3
20°	2189.0	2189.0	2184.3	2167.2	2137.5	2103.4	2051.8	1999.2	1929.0	1861.4	1800.8
22.5°	2214.6	2216.3	2210.6	2196.6	2169.8	2136.6	2092.7	2039.2	1966.8	1890.8	1815.7
25°	2179.5	2189.6	2190.6	2186.9	2178.9	2158.7	2121.0	2066.2	2001.3	1918.9	1838.0
27.5°	2001.0	2013.7	2024.9	2043.3	2067.8	2080.5	2082.2	2054.4	1997.8	1918.4	1837.1
30°	1823.1	1833.8	1868.3	1913.5	1948.7	1980.6	2008.2	2015.7	1983.8	1912.5	1826.9
32.5°	1625.7	1640.2	1674.8	1723.4	1781.9	1835.9	1898.0	1929.7	1928.9	1886.1	1806.9
35°	1342.4	1353.0	1384.9	1436.0	1506.2	1586.5	1684.9	1761.4	1813.6	1809.8	1761.4
37.5°	1082.6	1094.6	1126.9	1169.2	1237.3	1336.7	1431.9	1537.4	1633.8	1687.9	1671.8
40°	941.4	941.9	973.3	1016.9	1080.7	1167.4	1271.1	1388.1	1495.5	1583.3	1600.3
42.5°	829.9	830.0	850.7	897.7	943.7	1025.3	1124.3	1240.5	1366.2	1467.6	1512.7
45°	686.1	690.9	707.9	736.1	772.2	841.4	920.6	1028.6	1169.5	1289.7	1364.7
47.5°	581.0	588.0	598.8	621.8	650.6	696.7	762.2	859.2	973.9	1106.1	1212.8
50°	526.5	527.6	541.4	554.2	579.2	615.9	673.3	754.1	859.4	986.6	1105.2
52.5°	479.7	479.5	487.8	504.0	524.3	552.9	599.3	672.9	766.3	880.2	1002.6
55°	409.5	412.2	418.6	431.3	446.7	467.0	503.6	559.0	632.4	729.7	840.8
57.5°	356.1	357.5	362.5	367.9	382.1	396.8	424.3	462.7	524.6	604.3	707.9
60°	321.2	321.8	323.4	331.3	342.5	356.3	374.9	407.4	459.5	532.4	614.3
62.5°	287.2	288.1	290.6	296.4	305.1	314.6	334.1	360.2	403.3	465.6	539.4
65°	239.3	239.9	243.6	245.7	252.6	261.1	275.5	293.0	322.8	374.9	430.8
67.5°	200.0	200.0	200.2	203.1	207.8	213.5	222.1	236.1	258.6	290.6	339.8
70°	174.4	174.4	175.5	177.1	179.8	184.5	189.3	200.0	216.5	242.5	280.3
72.5°	150.6	151.0	152.1	152.4	153.8	157.7	161.3	168.1	180.3	200.0	230.5
75°	110.6	112.2	114.9	117.0	119.7	119.1	122.9	127.1	130.8	142.5	160.1
77.5°	82.3	81.5	81.8	83.6	83.9	84.5	87.1	90.4	93.2	98.7	105.0
80°	62.8	62.8	64.4	64.9	64.4	64.9	67.5	69.1	70.2	72.3	78.2
82.5°	47.4	48.3	47.8	48.3	48.6	49.1	51.4	51.7	52.8	53.6	56.1
85°	26.6	27.1	27.7	26.6	26.6	26.6	27.7	28.2	29.3	28.7	29.8
87.5°	14.2	13.8	14.5	14.2	14.4	14.0	14.2	14.8	13.7	14.4	13.9
90°	24.4	24.4	25.6	24.4	23.2	23.2	22.1	20.9	19.8	20.9	18.6
92.5°	89.5	89.5	93.4	99.7	113.4	136.7	171.7	228.2	307.0	368.6	322.6
95°	283.5	298.6	319.6	355.6	412.5	525.2	680.9	861.0	973.8	947.0	714.6
97.5°	757.9	782.0	816.9	886.8	970.3	1091.6	1205.2	1272.2	1223.4	997.5	668.8
100°	1065.6	1074.9	1109.7	1180.6	1281.7	1367.7	1424.6	1401.4	1231.7	934.2	606.6
102.5°	1333.3	1340.7	1377.4	1428.8	1490.8	1526.6	1510.1	1394.9	1162.0	855.2	564.7
105°	1634.9	1641.9	1658.2	1667.5	1665.1	1617.5	1502.5	1301.4	1035.3	762.3	528.7
107.5°	1747.0	1743.9	1732.3	1705.8	1648.4	1544.8	1382.8	1168.7	933.1	710.2	522.2
110°	1748.8	1738.4	1717.4	1668.6	1586.1	1458.3	1289.8	1088.8	882.0	692.6	524.1



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1694.0	1677.0	1647.7	1588.7	1495.0	1367.2	1208.0	1030.2	853.1	684.2	529.6
115°	1569.9	1560.6	1523.4	1453.7	1361.9	1250.3	1114.4	971.4	826.2	679.8	540.3
117.5°	1444.1	1436.9	1399.3	1340.7	1262.4	1167.8	1060.9	942.6	814.1	678.6	551.7
120°	1373.5	1360.7	1330.5	1279.4	1213.1	1130.6	1037.7	929.6	807.6	678.6	560.1
122.5°	1317.7	1304.9	1279.4	1235.7	1179.7	1107.4	1022.8	918.4	800.2	677.7	568.5
125°	1252.6	1245.7	1223.6	1189.9	1143.4	1079.5	999.3	899.4	787.8	676.3	581.0
127.5°	1214.5	1207.6	1189.0	1159.0	1112.3	1051.6	971.7	876.1	771.3	673.7	591.0
130°	1192.2	1185.2	1166.6	1137.6	1090.0	1028.4	949.4	857.6	761.1	672.8	598.4
132.5°	1167.1	1160.1	1142.5	1109.7	1063.0	1001.4	924.3	838.0	751.8	671.9	604.9
135°	1120.2	1113.2	1094.6	1062.1	1015.6	957.5	886.6	811.1	737.9	670.5	614.7
137.5°	1062.1	1053.7	1038.4	1006.3	962.8	910.3	850.6	786.7	725.8	670.2	620.5
140°	1020.2	1010.9	994.7	969.1	928.4	879.6	827.3	772.7	719.3	669.3	625.2
142.5°	975.6	969.1	954.7	931.0	895.0	852.7	807.8	759.7	713.7	669.3	628.9
145°	914.5	908.7	897.1	877.3	848.3	815.7	780.9	741.4	704.2	667.0	631.0
147.5°	860.3	858.3	849.4	832.5	811.1	785.5	757.6	726.3	695.6	662.8	632.1
150°	829.7	828.5	821.5	806.4	787.8	766.9	743.7	717.0	689.1	660.0	632.1
152.5°	801.8	800.6	796.4	784.1	768.3	751.1	729.7	706.7	681.6	655.4	630.3
155°	765.8	765.8	762.3	753.0	741.4	727.4	710.0	691.4	670.5	648.4	627.5
157.5°	734.2	734.2	732.1	725.1	716.3	705.1	690.5	674.9	659.1	641.2	624.5
160°	714.6	714.6	713.5	706.5	699.5	690.2	677.4	664.7	650.7	635.6	621.7
162.5°	696.0	697.0	695.8	688.8	683.7	675.4	665.4	654.4	643.3	630.0	618.9
165°	668.2	669.3	670.5	665.8	661.2	655.4	647.2	640.3	631.0	621.7	613.5
167.5°	646.1	647.0	647.2	644.2	641.9	638.4	631.9	626.6	619.8	613.3	608.0
170°	632.1	632.1	633.3	632.1	629.8	626.3	621.7	618.2	612.4	607.7	604.2
172.5°	618.2	620.0	621.2	620.0	618.6	616.1	613.3	610.7	605.9	602.1	600.5
175°	601.9	604.2	606.6	604.2	604.2	604.2	601.9	600.8	598.4	596.1	596.1
177.5°	592.4	594.2	596.1	595.2	596.1	595.2	595.2	594.2	593.3	592.4	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1360.0	1354.1	1351.1	1344.3	1336.2	1331.9	1328.1	1322.6	1315.3	1307.7	1302.1
5°	1429.0	1416.3	1400.3	1381.2	1364.2	1347.7	1333.3	1319.0	1302.5	1285.4	1268.4
7.5°	1499.9	1474.8	1447.7	1416.3	1385.8	1358.0	1332.5	1308.0	1280.3	1255.6	1233.0
10°	1549.2	1515.2	1477.4	1437.6	1397.7	1363.1	1329.1	1298.2	1264.2	1233.9	1208.3
12.5°	1589.2	1549.2	1503.8	1454.1	1406.2	1364.4	1325.2	1285.0	1246.3	1213.4	1179.4
15°	1655.6	1600.8	1539.7	1480.1	1417.9	1361.0	1308.3	1261.5	1217.4	1171.1	1138.7
17.5°	1701.2	1636.2	1561.9	1490.3	1416.8	1349.7	1289.0	1233.2	1182.3	1135.0	1096.4
20°	1728.5	1656.7	1574.2	1492.9	1410.4	1338.6	1273.2	1211.5	1158.9	1107.8	1067.9
22.5°	1743.8	1664.3	1574.2	1489.0	1403.6	1325.9	1254.1	1189.8	1132.5	1081.4	1037.3
25°	1748.7	1663.6	1571.6	1473.7	1380.1	1297.7	1223.2	1153.6	1089.7	1038.7	991.9
27.5°	1741.9	1641.7	1547.4	1447.0	1350.4	1263.5	1185.4	1112.2	1048.3	993.5	945.5
30°	1731.7	1624.2	1523.2	1418.9	1321.1	1237.6	1155.1	1084.9	1018.5	961.6	913.2
32.5°	1709.5	1603.0	1494.2	1387.5	1288.3	1202.3	1124.1	1053.5	988.3	930.1	878.7
35°	1665.7	1557.8	1439.7	1330.1	1232.8	1143.4	1070.1	1002.0	939.8	877.5	823.3
37.5°	1608.0	1497.7	1380.2	1260.2	1162.8	1078.5	1011.1	947.2	886.5	829.7	769.6
40°	1553.5	1453.0	1331.7	1212.6	1112.6	1031.2	969.0	911.0	849.9	793.5	733.4
42.5°	1487.5	1401.9	1279.4	1159.8	1061.1	982.7	924.8	868.1	812.4	757.8	695.1
45°	1377.5	1312.6	1197.7	1082.8	983.4	905.7	852.5	802.5	753.6	701.5	642.5
47.5°	1251.3	1207.4	1108.2	990.6	898.6	828.7	777.3	736.5	695.1	643.0	591.2
50°	1163.7	1135.5	1039.7	932.3	844.6	780.2	727.6	689.3	654.7	604.7	558.4
52.5°	1070.1	1055.1	974.2	871.5	786.7	723.6	678.6	644.2	609.2	567.7	524.4
55°	927.5	935.5	866.9	778.1	698.3	645.1	604.2	575.4	545.7	510.6	477.1
57.5°	781.8	810.9	764.9	686.9	612.1	563.0	532.2	508.0	483.0	453.9	425.3
60°	694.6	719.0	693.0	624.4	559.0	513.2	484.5	465.9	440.9	414.3	392.5
62.5°	609.5	635.7	620.2	564.8	504.1	464.7	439.4	422.1	403.5	380.3	357.6
65°	502.6	519.6	512.2	473.9	430.8	397.3	373.9	361.1	344.1	327.1	306.9
67.5°	384.9	417.8	413.5	393.1	355.9	329.7	314.4	303.1	287.6	275.0	261.2
70°	316.4	346.8	346.2	329.7	309.5	285.1	274.4	264.9	251.0	238.8	227.6
72.5°	259.0	286.8	290.9	278.3	264.4	245.9	235.7	229.1	215.7	207.3	198.3
75°	181.4	201.6	206.9	206.9	200.5	190.9	181.9	177.6	168.1	160.6	155.3
77.5°	118.9	131.7	140.0	141.9	142.9	139.7	132.2	129.2	121.9	119.2	114.1
80°	84.0	92.5	102.1	105.3	108.0	106.9	103.7	101.6	94.7	92.0	89.9
82.5°	58.1	62.8	70.6	77.6	76.9	79.7	76.9	75.2	70.0	69.0	66.9
85°	30.3	30.8	31.9	36.7	39.4	40.4	41.0	39.9	38.3	38.3	34.6
87.5°	13.5	13.0	12.5	12.5	12.7	14.2	14.7	14.7	13.9	13.3	12.3
90°	16.3	16.3	9.3	9.3	8.1	7.0	3.5	1.2	3.5	7.0	8.1
92.5°	234.7	144.6	85.5	61.4	44.4	30.2	19.3	13.2	19.3	30.2	44.4
95°	436.9	246.3	145.3	96.4	68.6	53.5	41.8	38.3	41.8	53.5	68.6
97.5°	392.8	235.4	157.6	116.7	92.7	78.8	68.8	68.8	68.8	78.8	92.7
100°	369.5	238.2	169.7	132.5	110.4	96.4	88.3	88.3	88.3	96.4	110.4
102.5°	363.0	247.5	185.5	150.1	129.0	116.0	108.8	106.9	108.8	116.0	129.0
105°	366.0	269.6	213.8	180.1	159.2	145.3	139.4	136.0	139.4	145.3	159.2
107.5°	383.2	295.4	244.3	211.0	191.0	176.2	170.3	168.0	170.3	176.2	191.0
110°	396.2	314.9	263.8	232.4	211.5	197.5	191.7	189.4	191.7	197.5	211.5





TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	410.2	333.5	284.2	252.9	231.9	218.9	212.2	209.9	212.2	218.9	231.9
115°	432.3	362.5	316.1	284.7	262.6	251.0	242.9	239.4	242.9	251.0	262.6
117.5°	454.8	390.7	346.5	314.0	293.3	280.5	273.3	270.0	273.3	280.5	293.3
120°	470.6	410.2	366.0	333.5	313.7	301.0	292.8	290.5	292.8	301.0	313.7
122.5°	485.5	428.8	384.6	353.0	331.4	319.6	311.4	309.1	311.4	319.6	331.4
125°	507.8	454.3	412.5	380.0	357.9	345.1	338.1	333.5	338.1	345.1	357.9
127.5°	527.1	478.0	437.6	404.8	381.8	367.2	358.8	355.1	358.8	367.2	381.8
130°	539.2	493.9	454.3	420.6	398.6	381.1	371.8	367.2	371.8	381.1	398.6
132.5°	551.3	506.9	467.4	435.5	411.6	395.1	383.0	379.3	383.0	395.1	411.6
135°	567.1	525.2	486.9	456.7	432.3	412.5	400.9	396.2	400.9	412.5	432.3
137.5°	578.2	539.2	503.4	474.6	449.2	430.4	417.6	413.2	417.6	430.4	449.2
140°	585.6	548.5	513.6	485.7	461.3	441.6	428.8	425.3	428.8	441.6	461.3
142.5°	591.2	556.8	522.9	495.9	472.5	453.6	441.8	438.3	441.8	453.6	472.5
145°	597.3	565.9	535.7	510.1	488.0	471.8	460.2	456.7	460.2	471.8	488.0
147.5°	602.6	575.2	546.8	523.8	505.5	488.7	478.5	477.3	478.5	488.7	505.5
150°	605.4	579.8	554.3	532.2	514.8	500.8	491.5	490.4	491.5	500.8	514.8
152.5°	607.3	583.6	560.8	540.6	525.0	512.0	502.7	502.4	502.7	512.0	525.0
155°	608.9	589.1	569.4	552.0	539.2	527.5	520.6	519.4	520.6	527.5	539.2
157.5°	608.9	593.1	576.4	562.6	551.5	542.4	535.9	535.9	535.9	542.4	551.5
160°	608.9	594.9	581.0	568.2	558.9	550.8	546.1	546.1	546.1	550.8	558.9
162.5°	608.9	596.8	583.8	573.8	565.4	558.2	554.5	555.4	554.5	558.2	565.4
165°	606.6	597.3	586.8	579.8	574.0	568.2	565.9	565.9	565.9	568.2	574.0
167.5°	603.8	597.0	589.4	584.0	580.8	576.4	575.2	576.4	575.2	576.4	580.8
170°	601.9	596.1	590.3	586.8	584.5	581.0	579.8	581.0	579.8	581.0	584.5
172.5°	600.1	595.2	591.2	588.7	587.3	584.7	584.5	585.6	584.5	584.7	587.3
175°	597.3	593.8	591.5	591.5	590.3	589.1	589.1	590.3	589.1	589.1	590.3
177.5°	594.2	592.4	591.5	591.5	591.5	590.5	591.5	592.4	591.5	590.5	591.5
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1296.2	1291.9	1286.4	1280.0	1272.4	1265.6	1262.6	1265.1	1266.4	1263.0	1262.6
5°	1256.7	1243.4	1232.8	1216.8	1204.1	1193.4	1186.0	1182.8	1183.9	1175.4	1173.2
7.5°	1212.4	1196.6	1179.2	1160.3	1142.6	1127.0	1118.8	1114.3	1105.3	1101.4	1094.9
10°	1183.9	1162.6	1145.6	1123.2	1103.0	1084.4	1075.4	1067.9	1058.9	1054.6	1045.6
12.5°	1154.5	1129.8	1111.1	1087.9	1067.3	1044.8	1036.2	1022.4	1008.3	999.3	987.7
15°	1113.1	1083.4	1060.5	1032.8	1008.4	982.8	960.0	934.4	924.9	904.7	893.0
17.5°	1064.7	1034.5	1006.2	969.1	931.4	899.7	875.3	850.8	836.2	823.3	817.3
20°	1032.8	1005.2	965.8	922.7	880.7	845.6	825.9	810.0	794.0	785.0	778.6
22.5°	1002.6	967.3	921.6	875.1	833.1	805.6	788.9	772.5	759.6	751.0	742.4
25°	952.0	905.7	857.3	804.1	775.4	751.5	733.4	720.1	712.1	701.0	696.7
27.5°	900.0	843.9	790.5	754.8	724.9	703.0	687.2	677.2	667.1	660.0	654.5
30°	860.0	803.1	755.2	721.2	690.9	672.8	660.0	648.3	640.3	634.5	630.2
32.5°	820.4	763.5	723.3	686.7	662.8	645.1	631.5	622.8	616.5	609.0	606.4
35°	763.2	712.7	677.6	644.6	620.1	604.2	593.5	584.5	579.2	577.0	575.4
37.5°	708.2	666.8	629.1	602.0	580.2	567.7	555.1	550.7	547.0	543.2	544.9
40°	673.3	634.5	601.0	572.3	554.7	540.9	533.4	528.1	524.9	524.9	524.9
42.5°	643.1	605.1	572.5	546.7	529.2	517.5	509.2	504.7	503.6	503.2	505.8
45°	596.2	561.1	528.1	506.8	491.9	480.2	475.5	471.7	471.7	473.9	474.4
47.5°	549.7	516.8	490.4	466.5	452.9	445.6	441.4	439.5	439.7	441.9	444.3
50°	521.2	488.8	462.7	441.4	428.7	421.7	418.0	417.0	418.0	418.0	421.7
52.5°	490.1	461.1	435.5	417.6	403.1	396.6	394.6	393.1	393.8	395.5	397.1
55°	444.6	418.6	394.1	377.1	366.4	362.2	357.4	357.9	356.9	357.9	357.9
57.5°	399.0	375.6	352.8	339.3	330.0	323.8	318.6	320.1	318.5	318.3	317.4
60°	369.6	344.1	326.0	313.8	303.1	297.8	293.0	294.1	292.5	291.4	289.3
62.5°	337.7	316.4	299.2	287.4	278.9	272.7	267.9	266.9	263.2	259.5	254.9
65°	291.4	273.9	258.5	247.3	239.3	234.5	230.8	227.6	219.6	211.1	206.9
67.5°	246.5	233.8	219.4	210.0	203.5	197.2	190.1	184.7	177.2	172.5	169.9
70°	217.5	205.3	193.1	184.0	177.1	171.3	163.3	159.6	154.2	152.1	149.4
72.5°	189.9	178.5	167.1	158.9	151.6	147.0	140.7	137.0	134.7	133.8	131.2
75°	147.9	138.8	130.3	122.9	117.0	113.8	111.2	108.5	107.4	102.6	100.0
77.5°	107.9	101.9	96.6	91.3	87.1	85.0	79.9	76.8	75.0	72.8	72.2
80°	84.0	79.8	74.5	71.3	65.4	63.3	61.2	60.6	60.1	59.6	59.0
82.5°	63.2	58.9	53.6	51.7	50.1	48.8	47.5	47.0	46.5	46.8	46.7
85°	31.9	29.8	29.8	29.3	28.7	28.2	27.7	27.7	27.1	27.7	27.1
87.5°	12.5	12.1	13.5	12.6	13.5	14.0	13.3	13.5	14.2	13.6	13.6
90°	9.3	9.3	16.3	16.3	18.6	20.9	19.8	20.9	22.1	23.2	23.2
92.5°	61.4	85.5	144.6	234.7	322.6	368.6	307.0	228.2	171.7	136.7	113.4
95°	96.4	145.3	246.3	436.9	714.6	947.0	973.8	861.0	680.9	525.2	412.5
97.5°	116.7	157.6	235.4	392.8	668.8	997.5	1223.4	1272.2	1205.2	1091.6	970.3
100°	132.5	169.7	238.2	369.5	606.6	934.2	1231.7	1401.4	1424.6	1367.7	1281.7
102.5°	150.1	185.5	247.5	363.0	564.7	855.2	1162.0	1394.9	1510.1	1526.6	1490.8
105°	180.1	213.8	269.6	366.0	528.7	762.3	1035.3	1301.4	1502.5	1617.5	1665.1
107.5°	211.0	244.3	295.4	383.2	522.2	710.2	933.1	1168.7	1382.8	1544.8	1648.4
110°	232.4	263.8	314.9	396.2	524.1	692.6	882.0	1088.8	1289.8	1458.3	1586.1



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	252.9	284.2	333.5	410.2	529.6	684.2	853.1	1030.2	1208.0	1367.2	1495.0
115°	284.7	316.1	362.5	432.3	540.3	679.8	826.2	971.4	1114.4	1250.3	1361.9
117.5°	314.0	346.5	390.7	454.8	551.7	678.6	814.1	942.6	1060.9	1167.8	1262.4
120°	333.5	366.0	410.2	470.6	560.1	678.6	807.6	929.6	1037.7	1130.6	1213.1
122.5°	353.0	384.6	428.8	485.5	568.5	677.7	800.2	918.4	1022.8	1107.4	1179.7
125°	380.0	412.5	454.3	507.8	581.0	676.3	787.8	899.4	999.3	1079.5	1143.4
127.5°	404.8	437.6	478.0	527.1	591.0	673.7	771.3	876.1	971.7	1051.6	1112.3
130°	420.6	454.3	493.9	539.2	598.4	672.8	761.1	857.6	949.4	1028.4	1090.0
132.5°	435.5	467.4	506.9	551.3	604.9	671.9	751.8	838.0	924.3	1001.4	1063.0
135°	456.7	486.9	525.2	567.1	614.7	670.5	737.9	811.1	886.6	957.5	1015.6
137.5°	474.6	503.4	539.2	578.2	620.5	670.2	725.8	786.7	850.6	910.3	962.8
140°	485.7	513.6	548.5	585.6	625.2	669.3	719.3	772.7	827.3	879.6	928.4
142.5°	495.9	522.9	556.8	591.2	628.9	669.3	713.7	759.7	807.8	852.7	895.0
145°	510.1	535.7	565.9	597.3	631.0	667.0	704.2	741.4	780.9	815.7	848.3
147.5°	523.8	546.8	575.2	602.6	632.1	662.8	695.6	726.3	757.6	785.5	811.1
150°	532.2	554.3	579.8	605.4	632.1	660.0	689.1	717.0	743.7	766.9	787.8
152.5°	540.6	560.8	583.6	607.3	630.3	655.4	681.6	706.7	729.7	751.1	768.3
155°	552.0	569.4	589.1	608.9	627.5	648.4	670.5	691.4	710.0	727.4	741.4
157.5°	562.6	576.4	593.1	608.9	624.5	641.2	659.1	674.9	690.5	705.1	716.3
160°	568.2	581.0	594.9	608.9	621.7	635.6	650.7	664.7	677.4	690.2	699.5
162.5°	573.8	583.8	596.8	608.9	618.9	630.0	643.3	654.4	665.4	675.4	683.7
165°	579.8	586.8	597.3	606.6	613.5	621.7	631.0	640.3	647.2	655.4	661.2
167.5°	584.0	589.4	597.0	603.8	608.0	613.3	619.8	626.6	631.9	638.4	641.9
170°	586.8	590.3	596.1	601.9	604.2	607.7	612.4	618.2	621.7	626.3	629.8
172.5°	588.7	591.2	595.2	600.1	600.5	602.1	605.9	610.7	613.3	616.1	618.6
175°	591.5	591.5	593.8	597.3	596.1	596.1	598.4	600.8	601.9	604.2	604.2
177.5°	591.5	591.5	592.4	594.2	592.4	592.4	593.3	594.2	595.2	595.2	596.1
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1260.0	1260.9	1257.9	1257.0	1257.9	1260.9	1260.0	1262.6	1263.0	1266.4	1265.1
5°	1169.0	1167.9	1165.3	1165.8	1165.3	1167.9	1169.0	1173.2	1175.4	1183.9	1182.8
7.5°	1091.1	1087.0	1088.1	1083.9	1088.1	1087.0	1091.1	1094.9	1101.4	1105.3	1114.3
10°	1043.5	1037.6	1032.8	1028.6	1032.8	1037.6	1043.5	1045.6	1054.6	1058.9	1067.9
12.5°	978.4	973.4	966.9	968.2	966.9	973.4	978.4	987.7	999.3	1008.3	1022.4
15°	886.0	878.1	865.3	866.9	865.3	878.1	886.0	893.0	904.7	924.9	934.4
17.5°	807.9	808.0	802.1	803.5	802.1	808.0	807.9	817.3	823.3	836.2	850.8
20°	767.4	763.7	764.2	762.7	764.2	763.7	767.4	778.6	785.0	794.0	810.0
22.5°	739.4	734.8	731.1	727.8	731.1	734.8	739.4	742.4	751.0	759.6	772.5
25°	691.9	688.7	683.9	682.9	683.9	688.7	691.9	696.7	701.0	712.1	720.1
27.5°	650.2	649.6	647.7	645.2	647.7	649.6	650.2	654.5	660.0	667.1	677.2
30°	626.0	624.9	623.8	622.2	623.8	624.9	626.0	630.2	634.5	640.3	648.3
32.5°	604.3	603.6	602.6	602.7	602.6	603.6	604.3	606.4	609.0	616.5	622.8
35°	573.3	572.8	571.7	571.2	571.7	572.8	573.3	575.4	577.0	579.2	584.5
37.5°	544.4	545.8	545.1	545.0	545.1	545.8	544.4	544.9	543.2	547.0	550.7
40°	524.4	524.9	526.0	525.5	526.0	524.9	524.4	524.9	524.9	524.9	528.1
42.5°	507.8	507.9	509.4	507.6	509.4	507.9	507.8	505.8	503.2	503.6	504.7
45°	478.1	481.3	480.8	480.8	480.8	481.3	478.1	474.4	473.9	471.7	471.7
47.5°	445.7	448.4	449.2	449.1	449.2	448.4	445.7	444.3	441.9	439.7	439.5
50°	424.4	423.3	424.9	424.4	424.9	423.3	424.4	421.7	418.0	418.0	417.0
52.5°	398.5	398.7	398.6	398.0	398.6	398.7	398.5	397.1	395.5	393.8	393.1
55°	358.5	359.0	357.9	358.5	357.9	359.0	358.5	357.9	357.9	356.9	357.9
57.5°	315.1	312.5	313.6	312.3	313.6	312.5	315.1	317.4	318.3	318.5	320.1
60°	284.0	279.7	278.7	276.6	278.7	279.7	284.0	289.3	291.4	292.5	294.1
62.5°	249.1	246.1	242.5	244.2	242.5	246.1	249.1	254.9	259.5	263.2	266.9
65°	202.6	200.5	198.9	201.0	198.9	200.5	202.6	206.9	211.1	219.6	227.6
67.5°	167.7	166.6	166.6	165.5	166.6	166.6	167.7	169.9	172.5	177.2	184.7
70°	149.4	147.9	147.9	146.8	147.9	147.9	149.4	149.4	152.1	154.2	159.6
72.5°	130.7	129.1	129.6	128.9	129.6	129.1	130.7	131.2	133.8	134.7	137.0
75°	96.8	94.1	94.1	94.7	94.1	94.1	96.8	100.0	102.6	107.4	108.5
77.5°	72.2	71.7	72.4	71.5	72.4	71.7	72.2	72.2	72.8	75.0	76.8
80°	59.0	58.5	58.0	59.6	58.0	58.5	59.0	59.0	59.6	60.1	60.6
82.5°	45.8	45.7	45.6	47.7	45.6	45.7	45.8	46.7	46.8	46.5	47.0
85°	27.7	26.6	27.7	26.6	27.7	26.6	27.7	27.1	27.7	27.1	27.7
87.5°	14.7	14.5	13.8	14.2	13.8	14.5	14.7	13.6	13.6	14.2	13.5
90°	24.4	25.6	24.4	24.4	24.4	25.6	24.4	23.2	23.2	22.1	20.9
92.5°	99.7	93.4	89.5	89.5	89.5	93.4	99.7	113.4	136.7	171.7	228.2
95°	355.6	319.6	298.6	283.5	298.6	319.6	355.6	412.5	525.2	680.9	861.0
97.5°	886.8	816.9	782.0	757.9	782.0	816.9	886.8	970.3	1091.6	1205.2	1272.2
100°	1180.6	1109.7	1074.9	1065.6	1074.9	1109.7	1180.6	1281.7	1367.7	1424.6	1401.4
102.5°	1428.8	1377.4	1340.7	1333.3	1340.7	1377.4	1428.8	1490.8	1526.6	1510.1	1394.9
105°	1667.5	1658.2	1641.9	1634.9	1641.9	1658.2	1667.5	1665.1	1617.5	1502.5	1301.4
107.5°	1705.8	1732.3	1743.9	1747.0	1743.9	1732.3	1705.8	1648.4	1544.8	1382.8	1168.7
110°	1668.6	1717.4	1738.4	1748.8	1738.4	1717.4	1668.6	1586.1	1458.3	1289.8	1088.8



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1588.7	1647.7	1677.0	1694.0	1677.0	1647.7	1588.7	1495.0	1367.2	1208.0	1030.2
115°	1453.7	1523.4	1560.6	1569.9	1560.6	1523.4	1453.7	1361.9	1250.3	1114.4	971.4
117.5°	1340.7	1399.3	1436.9	1444.1	1436.9	1399.3	1340.7	1262.4	1167.8	1060.9	942.6
120°	1279.4	1330.5	1360.7	1373.5	1360.7	1330.5	1279.4	1213.1	1130.6	1037.7	929.6
122.5°	1235.7	1279.4	1304.9	1317.7	1304.9	1279.4	1235.7	1179.7	1107.4	1022.8	918.4
125°	1189.9	1223.6	1245.7	1252.6	1245.7	1223.6	1189.9	1143.4	1079.5	999.3	899.4
127.5°	1159.0	1189.0	1207.6	1214.5	1207.6	1189.0	1159.0	1112.3	1051.6	971.7	876.1
130°	1137.6	1166.6	1185.2	1192.2	1185.2	1166.6	1137.6	1090.0	1028.4	949.4	857.6
132.5°	1109.7	1142.5	1160.1	1167.1	1160.1	1142.5	1109.7	1063.0	1001.4	924.3	838.0
135°	1062.1	1094.6	1113.2	1120.2	1113.2	1094.6	1062.1	1015.6	957.5	886.6	811.1
137.5°	1006.3	1038.4	1053.7	1062.1	1053.7	1038.4	1006.3	962.8	910.3	850.6	786.7
140°	969.1	994.7	1010.9	1020.2	1010.9	994.7	969.1	928.4	879.6	827.3	772.7
142.5°	931.0	954.7	969.1	975.6	969.1	954.7	931.0	895.0	852.7	807.8	759.7
145°	877.3	897.1	908.7	914.5	908.7	897.1	877.3	848.3	815.7	780.9	741.4
147.5°	832.5	849.4	858.3	860.3	858.3	849.4	832.5	811.1	785.5	757.6	726.3
150°	806.4	821.5	828.5	829.7	828.5	821.5	806.4	787.8	766.9	743.7	717.0
152.5°	784.1	796.4	800.6	801.8	800.6	796.4	784.1	768.3	751.1	729.7	706.7
155°	753.0	762.3	765.8	765.8	765.8	762.3	753.0	741.4	727.4	710.0	691.4
157.5°	725.1	732.1	734.2	734.2	734.2	732.1	725.1	716.3	705.1	690.5	674.9
160°	706.5	713.5	714.6	714.6	714.6	713.5	706.5	699.5	690.2	677.4	664.7
162.5°	688.8	695.8	697.0	696.0	697.0	695.8	688.8	683.7	675.4	665.4	654.4
165°	665.8	670.5	669.3	668.2	669.3	670.5	665.8	661.2	655.4	647.2	640.3
167.5°	644.2	647.2	647.0	646.1	647.0	647.2	644.2	641.9	638.4	631.9	626.6
170°	632.1	633.3	632.1	632.1	632.1	633.3	632.1	629.8	626.3	621.7	618.2
172.5°	620.0	621.2	620.0	618.2	620.0	621.2	620.0	618.6	616.1	613.3	610.7
175°	604.2	606.6	604.2	601.9	604.2	606.6	604.2	604.2	604.2	601.9	600.8
177.5°	595.2	596.1	594.2	592.4	594.2	596.1	595.2	596.1	595.2	595.2	594.2
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1262.6	1265.6	1272.4	1280.0	1286.4	1291.9	1296.2	1302.1	1307.7	1315.3	1322.6
5°	1186.0	1193.4	1204.1	1216.8	1232.8	1243.4	1256.7	1268.4	1285.4	1302.5	1319.0
7.5°	1118.8	1127.0	1142.6	1160.3	1179.2	1196.6	1212.4	1233.0	1255.6	1280.3	1308.0
10°	1075.4	1084.4	1103.0	1123.2	1145.6	1162.6	1183.9	1208.3	1233.9	1264.2	1298.2
12.5°	1036.2	1044.8	1067.3	1087.9	1111.1	1129.8	1154.5	1179.4	1213.4	1246.3	1285.0
15°	960.0	982.8	1008.4	1032.8	1060.5	1083.4	1113.1	1138.7	1171.1	1217.4	1261.5
17.5°	875.3	899.7	931.4	969.1	1006.2	1034.5	1064.7	1096.4	1135.0	1182.3	1233.2
20°	825.9	845.6	880.7	922.7	965.8	1005.2	1032.8	1067.9	1107.8	1158.9	1211.5
22.5°	788.9	805.6	833.1	875.1	921.6	967.3	1002.6	1037.3	1081.4	1132.5	1189.8
25°	733.4	751.5	775.4	804.1	857.3	905.7	952.0	991.9	1038.7	1089.7	1153.6
27.5°	687.2	703.0	724.9	754.8	790.5	843.9	900.0	945.5	993.5	1048.3	1112.2
30°	660.0	672.8	690.9	721.2	755.2	803.1	860.0	913.2	961.6	1018.5	1084.9
32.5°	631.5	645.1	662.8	686.7	723.3	763.5	820.4	878.7	930.1	988.3	1053.5
35°	593.5	604.2	620.1	644.6	677.6	712.7	763.2	823.3	877.5	939.8	1002.0
37.5°	555.1	567.7	580.2	602.0	629.1	666.8	708.2	769.6	829.7	886.5	947.2
40°	533.4	540.9	554.7	572.3	601.0	634.5	673.3	733.4	793.5	849.9	911.0
42.5°	509.2	517.5	529.2	546.7	572.5	605.1	643.1	695.1	757.8	812.4	868.1
45°	475.5	480.2	491.9	506.8	528.1	561.1	596.2	642.5	701.5	753.6	802.5
47.5°	441.4	445.6	452.9	466.5	490.4	516.8	549.7	591.2	643.0	695.1	736.5
50°	418.0	421.7	428.7	441.4	462.7	488.8	521.2	558.4	604.7	654.7	689.3
52.5°	394.6	396.6	403.1	417.6	435.5	461.1	490.1	524.4	567.7	609.2	644.2
55°	357.4	362.2	366.4	377.1	394.1	418.6	444.6	477.1	510.6	545.7	575.4
57.5°	318.6	323.8	330.0	339.3	352.8	375.6	399.0	425.3	453.9	483.0	508.0
60°	293.0	297.8	303.1	313.8	326.0	344.1	369.6	392.5	414.3	440.9	465.9
62.5°	267.9	272.7	278.9	287.4	299.2	316.4	337.7	357.6	380.3	403.5	422.1
65°	230.8	234.5	239.3	247.3	258.5	273.9	291.4	306.9	327.1	344.1	361.1
67.5°	190.1	197.2	203.5	210.0	219.4	233.8	246.5	261.2	275.0	287.6	303.1
70°	163.3	171.3	177.1	184.0	193.1	205.3	217.5	227.6	238.8	251.0	264.9
72.5°	140.7	147.0	151.6	158.9	167.1	178.5	189.9	198.3	207.3	215.7	229.1
75°	111.2	113.8	117.0	122.9	130.3	138.8	147.9	155.3	160.6	168.1	177.6
77.5°	79.9	85.0	87.1	91.3	96.6	101.9	107.9	114.1	119.2	121.9	129.2
80°	61.2	63.3	65.4	71.3	74.5	79.8	84.0	89.9	92.0	94.7	101.6
82.5°	47.5	48.8	50.1	51.7	53.6	58.9	63.2	66.9	69.0	70.0	75.2
85°	27.7	28.2	28.7	29.3	29.8	29.8	31.9	34.6	38.3	38.3	39.9
87.5°	13.3	14.0	13.5	12.6	13.5	12.1	12.5	12.3	13.3	13.9	14.7
90°	19.8	20.9	18.6	16.3	16.3	9.3	9.3	8.1	7.0	3.5	1.2
92.5°	307.0	368.6	322.6	234.7	144.6	85.5	61.4	44.4	30.2	19.3	13.2
95°	973.8	947.0	714.6	436.9	246.3	145.3	96.4	68.6	53.5	41.8	38.3
97.5°	1223.4	997.5	668.8	392.8	235.4	157.6	116.7	92.7	78.8	68.8	68.8
100°	1231.7	934.2	606.6	369.5	238.2	169.7	132.5	110.4	96.4	88.3	88.3
102.5°	1162.0	855.2	564.7	363.0	247.5	185.5	150.1	129.0	116.0	108.8	106.9
105°	1035.3	762.3	528.7	366.0	269.6	213.8	180.1	159.2	145.3	139.4	136.0
107.5°	933.1	710.2	522.2	383.2	295.4	244.3	211.0	191.0	176.2	170.3	168.0
110°	882.0	692.6	524.1	396.2	314.9	263.8	232.4	211.5	197.5	191.7	189.4



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	853.1	684.2	529.6	410.2	333.5	284.2	252.9	231.9	218.9	212.2	209.9
115°	826.2	679.8	540.3	432.3	362.5	316.1	284.7	262.6	251.0	242.9	239.4
117.5°	814.1	678.6	551.7	454.8	390.7	346.5	314.0	293.3	280.5	273.3	270.0
120°	807.6	678.6	560.1	470.6	410.2	366.0	333.5	313.7	301.0	292.8	290.5
122.5°	800.2	677.7	568.5	485.5	428.8	384.6	353.0	331.4	319.6	311.4	309.1
125°	787.8	676.3	581.0	507.8	454.3	412.5	380.0	357.9	345.1	338.1	333.5
127.5°	771.3	673.7	591.0	527.1	478.0	437.6	404.8	381.8	367.2	358.8	355.1
130°	761.1	672.8	598.4	539.2	493.9	454.3	420.6	398.6	381.1	371.8	367.2
132.5°	751.8	671.9	604.9	551.3	506.9	467.4	435.5	411.6	395.1	383.0	379.3
135°	737.9	670.5	614.7	567.1	525.2	486.9	456.7	432.3	412.5	400.9	396.2
137.5°	725.8	670.2	620.5	578.2	539.2	503.4	474.6	449.2	430.4	417.6	413.2
140°	719.3	669.3	625.2	585.6	548.5	513.6	485.7	461.3	441.6	428.8	425.3
142.5°	713.7	669.3	628.9	591.2	556.8	522.9	495.9	472.5	453.6	441.8	438.3
145°	704.2	667.0	631.0	597.3	565.9	535.7	510.1	488.0	471.8	460.2	456.7
147.5°	695.6	662.8	632.1	602.6	575.2	546.8	523.8	505.5	488.7	478.5	477.3
150°	689.1	660.0	632.1	605.4	579.8	554.3	532.2	514.8	500.8	491.5	490.4
152.5°	681.6	655.4	630.3	607.3	583.6	560.8	540.6	525.0	512.0	502.7	502.4
155°	670.5	648.4	627.5	608.9	589.1	569.4	552.0	539.2	527.5	520.6	519.4
157.5°	659.1	641.2	624.5	608.9	593.1	576.4	562.6	551.5	542.4	535.9	535.9
160°	650.7	635.6	621.7	608.9	594.9	581.0	568.2	558.9	550.8	546.1	546.1
162.5°	643.3	630.0	618.9	608.9	596.8	583.8	573.8	565.4	558.2	554.5	555.4
165°	631.0	621.7	613.5	606.6	597.3	586.8	579.8	574.0	568.2	565.9	565.9
167.5°	619.8	613.3	608.0	603.8	597.0	589.4	584.0	580.8	576.4	575.2	576.4
170°	612.4	607.7	604.2	601.9	596.1	590.3	586.8	584.5	581.0	579.8	581.0
172.5°	605.9	602.1	600.5	600.1	595.2	591.2	588.7	587.3	584.7	584.5	585.6
175°	598.4	596.1	596.1	597.3	593.8	591.5	591.5	590.3	589.1	589.1	590.3
177.5°	593.3	592.4	592.4	594.2	592.4	591.5	591.5	591.5	590.5	591.5	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1328.1	1331.9	1336.2	1344.3	1351.1	1354.1	1360.0	1364.3	1363.0	1368.9	1379.2
5°	1333.3	1347.7	1364.2	1381.2	1400.3	1416.3	1429.0	1441.8	1451.9	1464.1	1482.2
7.5°	1332.5	1358.0	1385.8	1416.3	1447.7	1474.8	1499.9	1525.4	1548.1	1572.9	1605.3
10°	1329.1	1363.1	1397.7	1437.6	1477.4	1515.2	1549.2	1581.2	1611.5	1643.9	1684.9
12.5°	1325.2	1364.4	1406.2	1454.1	1503.8	1549.2	1589.2	1635.2	1673.2	1715.0	1762.3
15°	1308.3	1361.0	1417.9	1480.1	1539.7	1600.8	1655.6	1712.0	1764.6	1814.6	1874.2
17.5°	1289.0	1349.7	1416.8	1490.3	1561.9	1636.2	1701.2	1772.3	1826.1	1893.2	1948.5
20°	1273.2	1338.6	1410.4	1492.9	1574.2	1656.7	1728.5	1800.8	1861.4	1929.0	1999.2
22.5°	1254.1	1325.9	1403.6	1489.0	1574.2	1664.3	1743.8	1815.7	1890.8	1966.8	2039.2
25°	1223.2	1297.7	1380.1	1473.7	1571.6	1663.6	1748.7	1838.0	1918.9	2001.3	2066.2
27.5°	1185.4	1263.5	1350.4	1447.0	1547.4	1641.7	1741.9	1837.1	1918.4	1997.8	2054.4
30°	1155.1	1237.6	1321.1	1418.9	1523.2	1624.2	1731.7	1826.9	1912.5	1983.8	2015.7
32.5°	1124.1	1202.3	1288.3	1387.5	1494.2	1603.0	1709.5	1806.9	1886.1	1928.9	1929.7
35°	1070.1	1143.4	1232.8	1330.1	1439.7	1557.8	1665.7	1761.4	1809.8	1813.6	1761.4
37.5°	1011.1	1078.5	1162.8	1260.2	1380.2	1497.7	1608.0	1671.8	1687.9	1633.8	1537.4
40°	969.0	1031.2	1112.6	1212.6	1331.7	1453.0	1553.5	1600.3	1583.3	1495.5	1388.1
42.5°	924.8	982.7	1061.1	1159.8	1279.4	1401.9	1487.5	1512.7	1467.6	1366.2	1240.5
45°	852.5	905.7	983.4	1082.8	1197.7	1312.6	1377.5	1364.7	1289.7	1169.5	1028.6
47.5°	777.3	828.7	898.6	990.6	1108.2	1207.4	1251.3	1212.8	1106.1	973.9	859.2
50°	727.6	780.2	844.6	932.3	1039.7	1135.5	1163.7	1105.2	986.6	859.4	754.1
52.5°	678.6	723.6	786.7	871.5	974.2	1055.1	1070.1	1002.6	880.2	766.3	672.9
55°	604.2	645.1	698.3	778.1	866.9	935.5	927.5	840.8	729.7	632.4	559.0
57.5°	532.2	563.0	612.1	686.9	764.9	810.9	781.8	707.9	604.3	524.6	462.7
60°	484.5	513.2	559.0	624.4	693.0	719.0	694.6	614.3	532.4	459.5	407.4
62.5°	439.4	464.7	504.1	564.8	620.2	635.7	609.5	539.4	465.6	403.3	360.2
65°	373.9	397.3	430.8	473.9	512.2	519.6	502.6	430.8	374.9	322.8	293.0
67.5°	314.4	329.7	355.9	393.1	413.5	417.8	384.9	339.8	290.6	258.6	236.1
70°	274.4	285.1	309.5	329.7	346.2	346.8	316.4	280.3	242.5	216.5	200.0
72.5°	235.7	245.9	264.4	278.3	290.9	286.8	259.0	230.5	200.0	180.3	168.1
75°	181.9	190.9	200.5	206.9	206.9	201.6	181.4	160.1	142.5	130.8	127.1
77.5°	132.2	139.7	142.9	141.9	140.0	131.7	118.9	105.0	98.7	93.2	90.4
80°	103.7	106.9	108.0	105.3	102.1	92.5	84.0	78.2	72.3	70.2	69.1
82.5°	76.9	79.7	76.9	77.6	70.6	62.8	58.1	56.1	53.6	52.8	51.7
85°	41.0	40.4	39.4	36.7	31.9	30.8	30.3	29.8	28.7	29.3	28.2
87.5°	14.7	14.2	12.7	12.5	12.5	13.0	13.5	13.9	14.4	13.7	14.8
90°	3.5	7.0	8.1	9.3	9.3	16.3	16.3	18.6	20.9	19.8	20.9
92.5°	19.3	30.2	44.4	61.4	85.5	144.6	234.7	322.6	368.6	307.0	228.2
95°	41.8	53.5	68.6	96.4	145.3	246.3	436.9	714.6	947.0	973.8	861.0
97.5°	68.8	78.8	92.7	116.7	157.6	235.4	392.8	668.8	997.5	1223.4	1272.2
100°	88.3	96.4	110.4	132.5	169.7	238.2	369.5	606.6	934.2	1231.7	1401.4
102.5°	108.8	116.0	129.0	150.1	185.5	247.5	363.0	564.7	855.2	1162.0	1394.9
105°	139.4	145.3	159.2	180.1	213.8	269.6	366.0	528.7	762.3	1035.3	1301.4
107.5°	170.3	176.2	191.0	211.0	244.3	295.4	383.2	522.2	710.2	933.1	1168.7
110°	191.7	197.5	211.5	232.4	263.8	314.9	396.2	524.1	692.6	882.0	1088.8





TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	212.2	218.9	231.9	252.9	284.2	333.5	410.2	529.6	684.2	853.1	1030.2
115°	242.9	251.0	262.6	284.7	316.1	362.5	432.3	540.3	679.8	826.2	971.4
117.5°	273.3	280.5	293.3	314.0	346.5	390.7	454.8	551.7	678.6	814.1	942.6
120°	292.8	301.0	313.7	333.5	366.0	410.2	470.6	560.1	678.6	807.6	929.6
122.5°	311.4	319.6	331.4	353.0	384.6	428.8	485.5	568.5	677.7	800.2	918.4
125°	338.1	345.1	357.9	380.0	412.5	454.3	507.8	581.0	676.3	787.8	899.4
127.5°	358.8	367.2	381.8	404.8	437.6	478.0	527.1	591.0	673.7	771.3	876.1
130°	371.8	381.1	398.6	420.6	454.3	493.9	539.2	598.4	672.8	761.1	857.6
132.5°	383.0	395.1	411.6	435.5	467.4	506.9	551.3	604.9	671.9	751.8	838.0
135°	400.9	412.5	432.3	456.7	486.9	525.2	567.1	614.7	670.5	737.9	811.1
137.5°	417.6	430.4	449.2	474.6	503.4	539.2	578.2	620.5	670.2	725.8	786.7
140°	428.8	441.6	461.3	485.7	513.6	548.5	585.6	625.2	669.3	719.3	772.7
142.5°	441.8	453.6	472.5	495.9	522.9	556.8	591.2	628.9	669.3	713.7	759.7
145°	460.2	471.8	488.0	510.1	535.7	565.9	597.3	631.0	667.0	704.2	741.4
147.5°	478.5	488.7	505.5	523.8	546.8	575.2	602.6	632.1	662.8	695.6	726.3
150°	491.5	500.8	514.8	532.2	554.3	579.8	605.4	632.1	660.0	689.1	717.0
152.5°	502.7	512.0	525.0	540.6	560.8	583.6	607.3	630.3	655.4	681.6	706.7
155°	520.6	527.5	539.2	552.0	569.4	589.1	608.9	627.5	648.4	670.5	691.4
157.5°	535.9	542.4	551.5	562.6	576.4	593.1	608.9	624.5	641.2	659.1	674.9
160°	546.1	550.8	558.9	568.2	581.0	594.9	608.9	621.7	635.6	650.7	664.7
162.5°	554.5	558.2	565.4	573.8	583.8	596.8	608.9	618.9	630.0	643.3	654.4
165°	565.9	568.2	574.0	579.8	586.8	597.3	606.6	613.5	621.7	631.0	640.3
167.5°	575.2	576.4	580.8	584.0	589.4	597.0	603.8	608.0	613.3	619.8	626.6
170°	579.8	581.0	584.5	586.8	590.3	596.1	601.9	604.2	607.7	612.4	618.2
172.5°	584.5	584.7	587.3	588.7	591.2	595.2	600.1	600.5	602.1	605.9	610.7
175°	589.1	589.1	590.3	591.5	591.5	593.8	597.3	596.1	596.1	598.4	600.8
177.5°	591.5	590.5	591.5	591.5	591.5	592.4	594.2	592.4	592.4	593.3	594.2
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1384.7	1386.4	1387.7	1391.9	1392.3	1396.2	1392.3
5°	1499.2	1506.7	1518.4	1530.1	1531.2	1538.6	1525.3
7.5°	1627.7	1645.0	1655.7	1674.6	1682.1	1686.8	1679.1
10°	1716.2	1732.2	1760.4	1774.2	1788.0	1790.2	1783.8
12.5°	1801.8	1827.1	1849.3	1875.5	1874.8	1893.6	1886.7
15°	1915.7	1941.7	1972.6	2001.8	2012.5	2012.5	2021.0
17.5°	1996.9	2044.7	2076.6	2099.6	2124.7	2129.0	2126.1
20°	2051.8	2103.4	2137.5	2167.2	2184.3	2189.0	2189.0
22.5°	2092.7	2136.6	2169.8	2196.6	2210.6	2216.3	2214.6
25°	2121.0	2158.7	2178.9	2186.9	2190.6	2189.6	2179.5
27.5°	2082.2	2080.5	2067.8	2043.3	2024.9	2013.7	2001.0
30°	2008.2	1980.6	1948.7	1913.5	1868.3	1833.8	1823.1
32.5°	1898.0	1835.9	1781.9	1723.4	1674.8	1640.2	1625.7
35°	1684.9	1586.5	1506.2	1436.0	1384.9	1353.0	1342.4
37.5°	1431.9	1336.7	1237.3	1169.2	1126.9	1094.6	1082.6
40°	1271.1	1167.4	1080.7	1016.9	973.3	941.9	941.4
42.5°	1124.3	1025.3	943.7	897.7	850.7	830.0	829.9
45°	920.6	841.4	772.2	736.1	707.9	690.9	686.1
47.5°	762.2	696.7	650.6	621.8	598.8	588.0	581.0
50°	673.3	615.9	579.2	554.2	541.4	527.6	526.5
52.5°	599.3	552.9	524.3	504.0	487.8	479.5	479.7
55°	503.6	467.0	446.7	431.3	418.6	412.2	409.5
57.5°	424.3	396.8	382.1	367.9	362.5	357.5	356.1
60°	374.9	356.3	342.5	331.3	323.4	321.8	321.2
62.5°	334.1	314.6	305.1	296.4	290.6	288.1	287.2
65°	275.5	261.1	252.6	245.7	243.6	239.9	239.3
67.5°	222.1	213.5	207.8	203.1	200.2	200.0	200.0
70°	189.3	184.5	179.8	177.1	175.5	174.4	174.4
72.5°	161.3	157.7	153.8	152.4	152.1	151.0	150.6
75°	122.9	119.1	119.7	117.0	114.9	112.2	110.6
77.5°	87.1	84.5	83.9	83.6	81.8	81.5	82.3
80°	67.5	64.9	64.4	64.9	64.4	62.8	62.8
82.5°	51.4	49.1	48.6	48.3	47.8	48.3	47.4
85°	27.7	26.6	26.6	26.6	27.7	27.1	26.6
87.5°	14.2	14.0	14.4	14.2	14.5	13.8	14.2
90°	22.1	23.2	23.2	24.4	25.6	24.4	24.4
92.5°	171.7	136.7	113.4	99.7	93.4	89.5	89.5
95°	680.9	525.2	412.5	355.6	319.6	298.6	283.5
97.5°	1205.2	1091.6	970.3	886.8	816.9	782.0	757.9
100°	1424.6	1367.7	1281.7	1180.6	1109.7	1074.9	1065.6
102.5°	1510.1	1526.6	1490.8	1428.8	1377.4	1340.7	1333.3
105°	1502.5	1617.5	1665.1	1667.5	1658.2	1641.9	1634.9
107.5°	1382.8	1544.8	1648.4	1705.8	1732.3	1743.9	1747.0
110°	1289.8	1458.3	1586.1	1668.6	1717.4	1738.4	1748.8



TEST NUMBER: P332951

CATALOG NUMBER: SA4XXRDIP-C795D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1208.0	1367.2	1495.0	1588.7	1647.7	1677.0	1694.0
115°	1114.4	1250.3	1361.9	1453.7	1523.4	1560.6	1569.9
117.5°	1060.9	1167.8	1262.4	1340.7	1399.3	1436.9	1444.1
120°	1037.7	1130.6	1213.1	1279.4	1330.5	1360.7	1373.5
122.5°	1022.8	1107.4	1179.7	1235.7	1279.4	1304.9	1317.7
125°	999.3	1079.5	1143.4	1189.9	1223.6	1245.7	1252.6
127.5°	971.7	1051.6	1112.3	1159.0	1189.0	1207.6	1214.5
130°	949.4	1028.4	1090.0	1137.6	1166.6	1185.2	1192.2
132.5°	924.3	1001.4	1063.0	1109.7	1142.5	1160.1	1167.1
135°	886.6	957.5	1015.6	1062.1	1094.6	1113.2	1120.2
137.5°	850.6	910.3	962.8	1006.3	1038.4	1053.7	1062.1
140°	827.3	879.6	928.4	969.1	994.7	1010.9	1020.2
142.5°	807.8	852.7	895.0	931.0	954.7	969.1	975.6
145°	780.9	815.7	848.3	877.3	897.1	908.7	914.5
147.5°	757.6	785.5	811.1	832.5	849.4	858.3	860.3
150°	743.7	766.9	787.8	806.4	821.5	828.5	829.7
152.5°	729.7	751.1	768.3	784.1	796.4	800.6	801.8
155°	710.0	727.4	741.4	753.0	762.3	765.8	765.8
157.5°	690.5	705.1	716.3	725.1	732.1	734.2	734.2
160°	677.4	690.2	699.5	706.5	713.5	714.6	714.6
162.5°	665.4	675.4	683.7	688.8	695.8	697.0	696.0
165°	647.2	655.4	661.2	665.8	670.5	669.3	668.2
167.5°	631.9	638.4	641.9	644.2	647.2	647.0	646.1
170°	621.7	626.3	629.8	632.1	633.3	632.1	632.1
172.5°	613.3	616.1	618.6	620.0	621.2	620.0	618.2
175°	601.9	604.2	604.2	604.2	606.6	604.2	601.9
177.5°	595.2	595.2	596.1	595.2	596.1	594.2	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5

(END OF REPORT)