

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332942

Luminaire Tested: **SA4XXRDIP-C795D810U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332942  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C795D810U835-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6106.3 lumens  
Efficiency: N/A  
Efficacy: 133.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332942  
CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332942

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38
3	82	73	66	60	76	68	62	56	58	54	50	49	46	43	41	39	36	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	33	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	25	22
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11215	11215	11215
5°	11240	11102	11171
10°	11170	10969	10969
15°	11041	10739	10659
20°	10865	10436	10244
25°	10640	10081	9825
30°	10421	9707	9300
35°	10178	9319	8774
40°	9887	8878	8205
45°	9618	8440	7626
50°	9311	7935	7013
55°	8983	7410	6348
60°	8622	6835	5667
65°	8290	6117	4999
70°	7808	5323	4244
75°	7199	4414	3450
80°	6281	3361	3166
85°	5317	3057	2853



TEST NUMBER: P332942

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.5	2.1
10°-20°	363.9	6.0
20°-30°	525.5	8.6
30°-40°	595.6	9.8
40°-50°	575.2	9.4
50°-60°	478.3	7.8
60°-70°	330.3	5.4
70°-80°	167.4	2.7
80°-90°	45.1	0.7
90°-100°	287.5	4.7
100°-110°	598.3	9.8
110°-120°	535.9	8.8
120°-130°	450.8	7.4
130°-140°	375.9	6.2
140°-150°	287.1	4.7
150°-160°	201.8	3.3
160°-170°	118.7	1.9
170°-180°	38.6	0.6
0°-30°	1019.8	16.7
0°-40°	1615.5	26.5
0°-60°	2668.9	43.7
0°-90°	3211.7	52.6
90°-120°	1421.6	23.3
90°-150°	2535.4	41.5
90°-180°	2895.0	47.4
0°-180°	6106.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1387	1382	1370	1380	1378	132
15°	1321	1311	1285	1282	1275	372
25°	1194	1174	1132	1114	1103	550
35°	1033	998	946	910	890	645
45°	842	802	739	689	668	649
55°	638	594	526	473	451	571
65°	434	387	320	276	262	428
75°	231	191	142	118	111	244
85°	57	37	33	31	31	65
90°	1	6	14	16	16	4
95°	26	81	637	316	191	29
105°	92	133	513	1104	1100	98
115°	161	202	457	879	1056	160
125°	224	267	455	748	843	200
135°	267	317	451	664	754	206
145°	307	352	449	560	615	193
155°	350	377	436	494	515	161
165°	381	393	418	443	450	107
175°	397	398	401	407	405	38
180°	398	398	398	398	398	



TEST NUMBER: P332942

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1392.6	1391.8	1391.0	1390.3	1389.5	1388.1	1386.0	1384.0	1381.9	1379.8	1381.9
5°	1387.0	1386.1	1385.1	1384.2	1383.2	1381.4	1378.5	1375.7	1372.8	1370.0	1372.4
7.5°	1374.5	1373.5	1372.5	1371.5	1370.5	1368.2	1364.5	1360.8	1357.1	1353.4	1354.9
10°	1362.6	1361.4	1360.2	1359.0	1357.8	1355.1	1350.9	1346.6	1342.4	1338.1	1339.0
12.5°	1347.2	1345.9	1344.5	1343.1	1341.8	1338.6	1333.6	1328.5	1323.5	1318.5	1319.1
15°	1321.1	1319.0	1316.8	1314.7	1312.6	1308.6	1302.6	1296.7	1290.8	1284.9	1284.4
17.5°	1289.4	1286.3	1283.2	1280.2	1277.1	1272.0	1264.9	1257.8	1250.7	1243.6	1242.3
20°	1264.7	1261.6	1258.6	1255.5	1252.4	1246.9	1238.8	1230.8	1222.7	1214.7	1212.8
22.5°	1237.5	1234.0	1230.6	1227.1	1223.7	1217.6	1209.0	1200.4	1191.8	1183.2	1180.4
25°	1194.5	1190.2	1186.0	1181.7	1177.5	1170.5	1160.8	1151.1	1141.4	1131.7	1127.7
27.5°	1149.4	1144.1	1138.7	1133.4	1128.0	1120.2	1109.8	1099.5	1089.1	1078.8	1073.8
30°	1117.9	1112.0	1106.1	1100.2	1094.3	1085.8	1074.7	1063.6	1052.4	1041.3	1035.4
32.5°	1084.7	1078.1	1071.4	1064.7	1058.1	1049.0	1037.5	1026.0	1014.5	1003.0	996.2
35°	1032.8	1025.3	1017.7	1010.1	1002.6	992.9	981.1	969.2	957.4	945.6	937.6
37.5°	977.3	969.5	961.7	953.9	946.1	935.7	922.6	909.5	896.4	883.3	874.3
40°	938.2	930.4	922.6	914.8	907.0	896.3	882.8	869.4	855.9	842.4	832.5
42.5°	900.7	892.5	884.4	876.2	868.0	856.9	842.9	828.8	814.8	800.7	790.6
45°	842.4	833.7	824.9	816.2	807.4	796.0	781.8	767.6	753.4	739.3	727.7
47.5°	782.2	773.2	764.2	755.1	746.1	734.2	719.5	704.7	690.0	675.2	663.2
50°	741.4	732.2	722.9	713.7	704.5	692.3	677.2	662.1	646.9	631.8	620.0
52.5°	699.7	690.7	681.6	672.6	663.6	651.3	635.8	620.3	604.8	589.3	577.3
55°	638.2	628.7	619.3	609.8	600.4	588.0	572.6	557.2	541.9	526.5	514.2
57.5°	577.4	567.5	557.7	547.9	538.0	525.5	510.4	495.3	480.2	465.0	452.6
60°	534.0	524.5	515.1	505.6	496.1	483.9	468.7	453.6	438.5	423.3	411.0
62.5°	494.8	485.0	475.2	465.3	455.5	442.8	427.3	411.8	396.3	380.8	369.4
65°	434.0	423.8	413.6	403.5	393.3	380.7	365.5	350.4	335.3	320.2	310.0
67.5°	370.8	361.1	351.3	341.6	331.8	320.0	305.9	291.9	277.8	263.8	255.0
70°	330.8	320.9	310.9	301.0	291.1	279.4	265.9	252.4	239.0	225.5	217.7
72.5°	288.3	279.3	270.3	261.3	252.3	241.5	228.8	216.0	203.3	190.6	183.9
75°	230.8	222.1	213.3	204.6	195.8	185.9	174.8	163.7	152.6	141.5	136.0
77.5°	172.5	165.1	157.7	150.3	142.8	134.6	125.7	116.7	107.7	98.7	95.5
80°	135.1	128.2	121.4	114.5	107.7	100.7	93.6	86.5	79.4	72.3	71.6
82.5°	102.8	96.5	90.2	83.9	77.6	72.4	68.4	64.3	60.2	56.2	55.6
85°	57.4	52.7	48.0	43.3	38.5	35.8	35.1	34.4	33.7	33.0	32.5
87.5°	19.7	18.5	17.5	16.1	14.8	13.9	14.7	14.5	14.6	14.7	14.4
90°	0.8	2.3	4.7	5.5	6.3	6.3	10.9	10.9	12.5	14.1	13.3
92.5°	8.9	13.0	20.3	29.9	41.3	57.5	97.3	157.9	217.1	248.0	206.6
95°	25.8	28.1	36.0	46.1	64.9	97.7	165.8	294.0	480.9	637.3	655.3
97.5°	46.3	46.3	53.0	62.4	78.5	106.0	158.4	264.3	450.1	671.2	823.2
100°	59.4	59.4	64.9	74.3	89.1	114.2	160.3	248.7	408.2	628.7	828.8
102.5°	71.9	73.2	78.0	86.8	101.0	124.8	166.5	244.3	380.0	575.5	781.9
105°	91.5	93.8	97.7	107.1	121.2	143.9	181.4	246.3	355.8	512.9	696.7
107.5°	113.1	114.6	118.5	128.5	142.0	164.4	198.8	257.9	351.4	477.9	627.9
110°	127.5	129.0	132.9	142.3	156.4	177.5	211.9	266.6	352.6	466.0	593.5



TEST NUMBER: P332942

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	141.2	142.8	147.3	156.1	170.1	191.3	224.4	276.0	356.4	460.4	574.1
115°	161.1	163.4	168.9	176.7	191.6	212.7	244.0	290.9	363.6	457.4	555.9
117.5°	181.7	183.9	188.8	197.4	211.3	233.2	262.9	306.0	371.3	456.6	547.8
120°	195.5	197.0	202.5	211.1	224.4	246.3	276.0	316.7	376.9	456.6	543.4
122.5°	208.0	209.6	215.0	223.0	237.5	258.8	288.5	326.7	382.5	456.0	538.4
125°	224.4	227.5	232.2	240.8	255.7	277.6	305.7	341.7	391.0	455.1	530.1
127.5°	239.0	241.5	247.1	256.9	272.4	294.5	321.7	354.7	397.7	453.4	519.0
130°	247.1	250.2	256.5	268.2	283.1	305.7	332.3	362.8	402.7	452.7	512.2
132.5°	255.2	257.7	265.9	277.0	293.1	314.5	341.1	370.9	407.1	452.1	505.9
135°	266.6	269.8	277.6	290.9	307.3	327.6	353.4	381.6	413.6	451.2	496.5
137.5°	278.1	281.0	289.6	302.3	319.3	338.7	362.8	389.1	417.5	451.0	488.4
140°	286.2	288.5	297.1	310.4	326.8	345.6	369.1	394.1	420.7	450.4	484.0
142.5°	294.9	297.3	305.3	317.9	333.7	351.9	374.7	397.8	423.2	450.4	480.3
145°	307.3	309.6	317.5	328.4	343.3	360.5	380.8	401.9	424.6	448.8	473.8
147.5°	321.2	322.0	328.9	340.1	352.5	368.0	387.1	405.5	425.4	446.0	468.1
150°	330.0	330.8	337.0	346.4	358.1	373.0	390.2	407.4	425.4	444.1	463.7
152.5°	338.1	338.3	344.5	353.3	363.8	377.4	392.7	408.6	424.1	441.0	458.7
155°	349.5	350.3	355.0	362.8	371.4	383.1	396.4	409.7	422.2	436.3	451.2
157.5°	360.6	360.6	365.0	371.1	378.6	387.8	399.1	409.7	420.2	431.5	443.5
160°	367.5	367.5	370.6	376.1	382.4	391.0	400.3	409.7	418.3	427.7	437.9
162.5°	373.8	373.1	375.6	380.5	386.1	392.8	401.6	409.7	416.5	424.0	432.9
165°	380.8	380.8	382.4	386.3	390.2	394.9	401.9	408.2	412.9	418.3	424.6
167.5°	387.8	387.1	387.8	390.8	393.0	396.6	401.8	406.3	409.1	412.7	417.1
170°	391.0	390.2	391.0	393.3	394.9	397.2	401.1	405.0	406.6	408.9	412.1
172.5°	394.1	393.3	393.5	395.2	396.1	397.8	400.5	403.8	404.1	405.2	407.7
175°	397.2	396.4	396.4	397.2	398.0	398.0	399.6	401.9	401.1	401.1	402.7
177.5°	398.6	398.0	397.4	398.0	398.0	398.0	398.6	399.9	398.6	398.6	399.2
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332942

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1384.0	1386.0	1388.1	1389.1	1388.9	1388.7	1388.5	1388.3
5°	1374.7	1377.1	1379.5	1380.4	1379.9	1379.5	1379.0	1378.5
7.5°	1356.4	1358.0	1359.5	1359.8	1359.1	1358.3	1357.6	1356.8
10°	1340.0	1340.9	1341.9	1341.9	1340.9	1340.0	1339.0	1338.1
12.5°	1319.7	1320.2	1320.8	1320.4	1319.1	1317.8	1316.4	1315.1
15°	1284.0	1283.5	1283.0	1282.0	1280.3	1278.6	1277.0	1275.3
17.5°	1241.0	1239.7	1238.3	1236.4	1233.9	1231.4	1228.9	1226.4
20°	1210.9	1209.0	1207.1	1204.7	1201.6	1198.5	1195.4	1192.4
22.5°	1177.6	1174.7	1171.9	1169.2	1166.7	1164.2	1161.7	1159.2
25°	1123.7	1119.7	1115.7	1112.5	1110.1	1107.8	1105.4	1103.0
27.5°	1068.8	1063.9	1058.9	1054.7	1051.3	1047.9	1044.5	1041.1
30°	1029.5	1023.6	1017.7	1012.8	1009.1	1005.3	1001.5	997.7
32.5°	989.3	982.5	975.6	970.4	966.8	963.2	959.6	956.0
35°	929.5	921.5	913.5	907.3	903.1	898.8	894.5	890.3
37.5°	865.3	856.3	847.3	840.7	836.5	832.2	828.0	823.7
40°	822.6	812.6	802.7	795.6	791.4	787.1	782.9	778.6
42.5°	780.5	770.4	760.3	753.0	748.5	744.1	739.7	735.2
45°	716.1	704.5	692.9	685.0	680.7	676.5	672.2	668.0
47.5°	651.2	639.2	627.2	618.8	614.2	609.5	604.8	600.1
50°	608.2	596.4	584.5	576.4	571.9	567.4	562.9	558.4
52.5°	565.3	553.3	541.2	532.9	528.2	523.5	518.9	514.2
55°	501.9	489.6	477.4	469.0	464.5	460.0	455.5	451.0
57.5°	440.1	427.6	415.1	407.2	403.8	400.4	397.0	393.6
60°	398.8	386.5	374.2	366.1	362.4	358.6	354.8	351.0
62.5°	358.1	346.8	335.4	328.2	325.2	322.2	319.1	316.1
65°	299.8	289.7	279.5	273.0	270.2	267.3	264.5	261.7
67.5°	246.3	237.6	228.8	222.9	219.8	216.6	213.5	210.4
70°	209.9	202.1	194.3	189.2	186.9	184.5	182.1	179.8
72.5°	177.3	170.6	163.9	159.5	157.4	155.2	153.0	150.8
75°	130.6	125.2	119.7	116.3	114.9	113.5	112.0	110.6
77.5°	92.4	89.2	86.0	84.2	83.8	83.4	83.0	82.5
80°	70.9	70.2	69.5	69.0	68.8	68.5	68.3	68.1
82.5°	55.1	54.6	54.1	53.7	53.5	53.2	53.0	52.8
85°	32.0	31.6	31.1	30.8	30.8	30.8	30.8	30.8
87.5°	14.3	14.3	14.3	14.3	14.6	15.0	15.0	15.2
90°	14.1	14.9	15.6	15.6	16.4	17.2	16.4	16.4
92.5°	153.6	115.6	92.0	76.3	67.1	62.9	60.2	60.2
95°	579.4	458.2	353.4	277.6	239.3	215.0	201.0	190.8
97.5°	856.0	811.0	734.5	652.9	596.8	549.7	526.2	510.0
100°	943.0	958.6	920.3	862.5	794.4	746.7	723.3	717.0
102.5°	938.6	1016.2	1027.3	1003.2	961.5	926.9	902.2	897.2
105°	875.8	1011.0	1088.4	1120.5	1122.1	1115.8	1104.9	1100.2
107.5°	786.5	930.5	1039.5	1109.2	1147.9	1165.7	1173.5	1175.5
110°	732.7	867.9	981.3	1067.3	1122.8	1155.7	1169.8	1176.8





TEST NUMBER: P332942

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	693.3	812.9	920.0	1006.0	1069.0	1108.8	1128.5	1139.9
115°	653.7	749.9	841.3	916.4	978.2	1025.1	1050.1	1056.4
117.5°	634.3	713.9	785.8	849.5	902.2	941.6	966.9	971.8
120°	625.5	698.3	760.8	816.3	860.9	895.3	915.6	924.2
122.5°	618.0	688.2	745.2	793.8	831.5	860.9	878.1	886.7
125°	605.2	672.5	726.4	769.4	800.7	823.4	838.2	842.9
127.5°	589.6	653.8	707.6	748.5	779.9	800.1	812.6	817.3
130°	577.1	638.8	692.0	733.4	765.5	785.1	797.6	802.3
132.5°	563.9	621.9	673.9	715.3	746.7	768.8	780.7	785.4
135°	545.8	596.6	644.3	683.4	714.7	736.6	749.1	753.8
137.5°	529.4	572.4	612.6	647.9	677.1	698.7	709.0	714.7
140°	520.0	556.7	591.9	624.8	652.1	669.3	680.3	686.5
142.5°	511.2	543.6	573.8	602.2	626.5	642.4	652.1	656.5
145°	498.9	525.5	548.9	570.8	590.4	603.6	611.5	615.4
147.5°	488.7	509.8	528.6	545.8	560.2	571.6	577.5	578.9
150°	482.4	500.4	516.1	530.1	542.7	552.8	557.5	558.3
152.5°	475.6	491.0	505.4	517.0	527.6	535.9	538.7	539.5
155°	465.2	477.8	489.5	498.9	506.7	512.9	515.3	515.3
157.5°	454.1	464.6	474.5	482.0	487.9	492.6	494.0	494.0
160°	447.3	455.9	464.5	470.7	475.4	480.1	480.9	480.9
162.5°	440.4	447.7	454.5	460.1	463.5	468.2	469.0	468.4
165°	430.8	435.5	441.0	444.9	448.0	451.2	450.4	449.6
167.5°	421.6	425.2	429.6	431.9	433.5	435.5	435.4	434.7
170°	416.0	418.3	421.5	423.8	425.4	426.1	425.4	425.4
172.5°	411.0	412.7	414.6	416.3	417.2	418.0	417.2	416.0
175°	404.3	405.0	406.6	406.6	406.6	408.2	406.6	405.0
177.5°	399.9	400.5	400.5	401.1	400.5	401.1	399.9	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0

(END OF REPORT)