

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332604-927

Luminaire Tested: **SA4XXDIP-C795D810U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332604-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D810U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5262.6 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332604-927
CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332604-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43	43	43	43	
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	42	41	36	36	36	36	
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31	31	31	31	
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26	26	26	26	
5	68	57	49	43	63	53	45	40	45	40	35	38	34	31	32	29	26	23	23	23	23	
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20	20	20	20	
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18	18	18	18	
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16	16	
9	50	38	31	25	46	36	29	24	31	25	22	27	22	19	22	19	16	14	14	14	14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13	13	13	13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8490	8490	8490
5°	8515	8413	8474
10°	8461	8344	8385
15°	8359	8226	8247
20°	8223	8079	8086
25°	8068	7911	7888
30°	7879	7713	7643
35°	7681	7508	7407
40°	7477	7273	7140
45°	7263	7042	6907
50°	7027	6836	6625
55°	6773	6570	6356
60°	6516	6273	6082
65°	6229	5989	5746
70°	5908	5611	5391
75°	5415	5153	5022
80°	4816	4621	4505
85°	4215	4057	3974



TEST NUMBER: P332604-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.0	1.9
10°-20°	279.0	5.3
20°-30°	410.7	7.8
30°-40°	477.4	9.1
40°-50°	477.5	9.1
50°-60°	417.6	7.9
60°-70°	310.2	5.9
70°-80°	176.2	3.3
80°-90°	53.2	1.0
90°-100°	28.3	0.5
100°-110°	180.6	3.4
110°-120°	345.5	6.6
120°-130°	438.6	8.3
130°-140°	469.2	8.9
140°-150°	438.8	8.3
150°-160°	353.8	6.7
160°-170°	228.2	4.3
170°-180°	78.7	1.5
0°-30°	788.7	15.0
0°-40°	1266.2	24.1
0°-60°	2161.3	41.1
0°-90°	2700.9	51.3
90°-120°	554.4	10.5
90°-150°	1901.0	36.1
90°-180°	2562.0	48.7
0°-180°	5262.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1052	1052	1052	1052	1052	
5°	1051	1047	1038	1047	1046	100
15°	1000	996	984	989	987	282
25°	906	900	888	889	886	417
35°	779	773	762	756	752	487
45°	636	630	617	608	605	490
55°	481	478	467	457	452	431
65°	326	322	314	305	301	323
75°	174	169	165	162	161	184
85°	46	45	44	44	43	50
90°	2	9	14	17	19	4
95°	34	14	14	17	18	44
105°	186	190	193	197	176	195
115°	348	350	349	351	351	342
125°	489	492	491	492	493	437
135°	607	607	609	610	611	467
145°	700	702	702	702	704	437
155°	768	768	766	768	767	354
165°	810	807	806	811	806	229
175°	828	825	825	830	823	79
180°	828	828	828	828	828	



TEST NUMBER: P332604-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1054.3	1053.8	1053.4	1053.0	1052.5	1051.5	1049.8	1048.1	1046.5	1044.9	1046.3
5°	1050.8	1050.0	1049.2	1048.5	1047.7	1046.3	1044.3	1042.2	1040.1	1038.1	1040.1
7.5°	1041.0	1040.2	1039.5	1038.7	1038.0	1036.5	1034.2	1031.9	1029.6	1027.3	1029.0
10°	1032.2	1031.5	1030.7	1030.0	1029.2	1027.6	1025.2	1022.8	1020.3	1017.9	1019.4
12.5°	1020.7	1020.0	1019.2	1018.5	1017.8	1016.1	1013.5	1010.9	1008.4	1005.8	1007.4
15°	1000.2	999.4	998.7	997.9	997.2	995.5	992.6	989.8	987.0	984.2	985.3
17.5°	975.4	974.5	973.5	972.6	971.7	969.9	967.3	964.6	961.9	959.3	960.0
20°	957.2	956.2	955.4	954.4	953.5	951.6	948.8	945.9	943.2	940.4	941.0
22.5°	937.7	936.4	935.2	934.0	932.7	930.7	927.9	925.1	922.3	919.5	920.5
25°	905.8	904.5	903.2	901.9	900.6	898.6	896.0	893.3	890.7	888.1	888.3
27.5°	869.4	868.1	866.7	865.4	864.0	862.1	859.7	857.3	854.8	852.4	851.9
30°	845.2	843.7	842.2	840.7	839.2	837.2	834.7	832.3	829.9	827.4	826.7
32.5°	819.5	818.2	816.8	815.5	814.1	812.1	809.6	807.0	804.5	801.8	801.0
35°	779.4	778.1	776.8	775.5	774.2	772.2	769.6	767.0	764.4	761.8	760.4
37.5°	737.1	735.9	734.7	733.6	732.3	730.3	727.5	724.7	721.9	719.1	717.6
40°	709.5	708.0	706.5	705.0	703.5	701.3	698.5	695.7	692.9	690.1	688.2
42.5°	679.9	678.9	678.0	677.2	676.2	674.2	671.1	668.0	664.9	661.8	659.7
45°	636.2	634.9	633.6	632.2	631.0	628.8	625.8	622.8	619.8	616.8	614.7
47.5°	590.5	589.6	588.7	587.8	586.9	585.1	582.3	579.6	576.8	574.0	571.6
50°	559.5	558.7	558.0	557.2	556.5	554.8	552.2	549.6	546.9	544.3	541.7
52.5°	529.2	528.3	527.4	526.5	525.5	523.7	520.9	518.2	515.4	512.6	510.3
55°	481.2	480.5	480.0	479.4	478.9	477.3	474.7	472.1	469.4	466.8	464.5
57.5°	435.3	434.7	434.0	433.4	432.8	431.1	428.6	426.0	423.4	420.8	418.7
60°	403.6	402.7	401.7	400.8	399.9	398.2	395.8	393.3	390.9	388.5	386.7
62.5°	372.6	371.9	371.1	370.3	369.5	367.8	365.2	362.6	360.0	357.4	355.9
65°	326.1	325.2	324.2	323.3	322.3	320.9	319.1	317.2	315.3	313.5	311.6
67.5°	279.2	278.4	277.5	276.6	275.8	274.5	272.7	270.8	269.1	267.3	265.5
70°	250.3	249.0	247.6	246.3	245.0	243.6	242.1	240.6	239.1	237.7	236.1
72.5°	219.3	217.9	216.7	215.3	214.0	212.8	211.6	210.3	209.1	207.9	206.8
75°	173.6	172.6	171.7	170.8	169.8	168.9	167.9	167.0	166.1	165.2	164.4
77.5°	129.9	129.5	129.1	128.7	128.3	127.7	126.8	126.0	125.2	124.4	124.1
80°	103.6	103.1	102.5	102.0	101.4	100.9	100.5	100.2	99.8	99.4	99.0
82.5°	78.0	77.8	77.5	77.2	77.0	76.8	76.8	76.7	76.6	76.5	76.3
85°	45.5	45.5	45.5	45.5	45.5	45.3	44.9	44.6	44.2	43.8	43.8
87.5°	17.9	18.1	18.2	18.4	18.5	18.6	18.7	18.8	18.9	18.9	19.1
90°	1.8	3.4	4.9	6.4	7.9	9.2	10.3	11.4	12.5	13.6	14.4
92.5°	7.8	7.9	8.0	8.1	8.2	8.7	9.8	10.9	12.0	13.2	13.9
95°	34.1	29.4	24.7	20.0	15.4	13.1	13.2	13.4	13.5	13.6	14.4
97.5°	72.3	75.3	78.2	81.1	84.1	77.8	62.4	47.1	31.7	16.3	16.4
100°	101.6	104.1	106.5	109.0	111.5	103.2	84.2	65.3	46.3	27.3	24.9
102.5°	134.3	136.1	137.9	139.7	141.6	141.2	138.7	136.3	133.8	131.3	106.1
105°	186.4	187.3	188.1	188.9	189.7	190.5	191.2	191.9	192.6	193.2	194.5
107.5°	234.9	235.3	235.7	236.1	236.5	237.2	238.1	239.1	240.0	241.0	241.5
110°	267.6	268.0	268.4	268.8	269.3	269.8	270.7	271.5	272.4	273.1	273.5



TEST NUMBER: P332604-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	299.3	300.0	300.8	301.5	302.3	302.9	303.2	303.6	304.0	304.4	304.4
115°	348.1	348.5	349.0	349.4	349.7	349.9	349.7	349.6	349.5	349.4	349.6
117.5°	392.1	392.6	393.2	393.7	394.3	394.7	395.0	395.3	395.6	395.9	395.9
120°	421.8	422.4	422.9	423.5	424.0	424.2	424.1	424.0	423.8	423.7	424.0
122.5°	449.6	449.9	450.2	450.5	450.9	451.1	451.3	451.5	451.7	451.9	452.1
125°	489.3	489.9	490.4	491.0	491.5	491.6	491.4	491.2	490.8	490.6	491.0
127.5°	527.0	527.1	527.3	527.4	527.5	527.9	528.5	529.2	529.8	530.4	530.4
130°	551.3	551.4	551.5	551.7	551.8	552.1	552.5	552.9	553.3	553.7	553.9
132.5°	573.5	573.8	574.1	574.3	574.6	575.0	575.4	576.0	576.5	577.0	577.2
135°	607.0	606.9	606.7	606.6	606.5	606.7	607.2	607.8	608.3	608.9	609.1
137.5°	636.6	636.7	636.8	636.8	636.8	637.2	637.8	638.4	639.0	639.6	639.9
140°	655.9	656.2	656.5	656.8	657.0	657.4	657.6	657.9	658.1	658.4	658.9
142.5°	673.3	673.8	674.3	674.8	675.3	675.6	675.7	676.0	676.1	676.3	676.6
145°	699.9	700.4	700.8	701.2	701.6	701.8	701.8	701.8	701.8	701.8	702.0
147.5°	721.1	721.9	722.6	723.4	724.2	724.5	724.4	724.2	724.1	724.0	724.1
150°	736.5	737.0	737.6	738.2	738.6	738.9	738.7	738.6	738.5	738.3	738.3
152.5°	749.3	749.8	750.2	750.7	751.1	751.2	751.0	750.8	750.4	750.2	750.4
155°	767.5	767.5	767.7	767.9	768.0	767.9	767.5	767.0	766.6	766.2	766.8
157.5°	782.7	782.6	782.5	782.4	782.4	782.0	781.6	781.2	780.7	780.2	780.9
160°	791.6	791.2	790.8	790.4	790.0	789.6	789.6	789.4	789.3	789.1	790.0
162.5°	799.5	799.0	798.4	798.0	797.4	797.1	796.9	796.9	796.7	796.5	797.4
165°	809.5	808.9	808.2	807.5	806.8	806.4	806.4	806.4	806.4	806.4	807.6
167.5°	817.5	816.7	816.0	815.3	814.6	814.2	814.1	814.0	814.0	813.9	815.1
170°	822.0	821.1	820.3	819.4	818.6	818.3	818.4	818.6	818.7	818.9	819.9
172.5°	824.9	824.1	823.2	822.4	821.7	821.3	821.4	821.6	821.7	821.8	822.9
175°	828.1	827.3	826.5	825.7	824.8	824.5	824.7	824.7	824.9	825.1	826.2
177.5°	829.7	828.9	828.1	827.3	826.6	826.2	826.5	826.7	827.0	827.1	828.0
180°	828.1	828.1	828.1	828.1	828.1	828.1	828.1	828.1	828.1	828.1	828.1



TEST NUMBER: P332604-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1047.8	1049.3	1050.8	1051.5	1051.4	1051.2	1051.1	1050.9
5°	1042.2	1044.3	1046.3	1047.2	1046.8	1046.5	1046.1	1045.7
7.5°	1030.6	1032.3	1033.9	1034.6	1034.4	1034.2	1034.0	1033.7
10°	1020.9	1022.4	1023.9	1024.5	1024.1	1023.7	1023.3	1022.9
12.5°	1009.1	1010.7	1012.3	1012.9	1012.4	1011.9	1011.3	1010.8
15°	986.4	987.5	988.6	989.0	988.4	987.9	987.3	986.7
17.5°	960.7	961.4	962.1	962.3	961.9	961.5	961.2	960.8
20°	941.5	942.1	942.6	942.7	942.3	942.0	941.6	941.2
22.5°	921.5	922.5	923.5	923.7	923.0	922.3	921.6	921.0
25°	888.5	888.7	888.9	888.6	887.9	887.1	886.4	885.6
27.5°	851.5	851.0	850.6	849.9	849.0	848.0	847.1	846.1
30°	825.9	825.2	824.4	823.6	822.7	821.7	820.8	819.9
32.5°	800.0	799.2	798.3	797.3	796.4	795.4	794.5	793.6
35°	759.1	757.8	756.5	755.3	754.4	753.5	752.6	751.6
37.5°	716.2	714.8	713.4	712.1	710.8	709.6	708.4	707.1
40°	686.3	684.5	682.6	681.2	680.2	679.4	678.4	677.5
42.5°	657.4	655.3	653.1	651.7	651.1	650.5	649.8	649.2
45°	612.7	610.6	608.6	607.3	606.7	606.1	605.5	605.0
47.5°	569.3	567.0	564.7	562.8	561.4	560.0	558.6	557.1
50°	539.1	536.5	533.9	532.0	530.8	529.7	528.6	527.5
52.5°	508.0	505.6	503.4	501.5	500.1	498.7	497.3	495.8
55°	462.3	460.1	457.8	456.1	455.0	453.9	452.7	451.6
57.5°	416.5	414.4	412.3	410.7	409.6	408.4	407.4	406.3
60°	385.1	383.4	381.7	380.4	379.5	378.5	377.6	376.7
62.5°	354.3	352.8	351.3	350.1	349.1	348.2	347.3	346.3
65°	309.7	307.8	305.9	304.6	303.6	302.7	301.7	300.8
67.5°	263.7	261.9	260.1	259.0	258.8	258.6	258.3	258.0
70°	234.6	233.1	231.6	230.6	230.0	229.5	228.9	228.4
72.5°	205.6	204.4	203.2	202.3	201.7	201.1	200.6	200.0
75°	163.7	162.9	162.2	161.7	161.5	161.3	161.1	161.0
77.5°	123.9	123.7	123.5	123.1	122.6	122.2	121.7	121.2
80°	98.7	98.3	97.9	97.7	97.4	97.3	97.1	96.9
82.5°	76.0	75.8	75.6	75.4	75.3	75.0	74.9	74.6
85°	43.8	43.8	43.8	43.7	43.6	43.3	43.2	42.9
87.5°	19.3	19.4	19.6	19.6	19.7	19.8	19.8	19.9
90°	15.3	16.1	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	14.8	15.6	16.4	16.9	17.0	17.0	17.0	17.1
95°	15.3	16.1	17.0	17.4	17.6	17.7	17.8	18.0
97.5°	16.6	16.6	16.7	16.8	17.0	17.0	17.2	17.3
100°	22.6	20.2	17.9	16.8	17.0	17.0	17.2	17.3
102.5°	80.8	55.6	30.3	17.7	17.7	17.7	17.8	17.8
105°	195.7	196.9	198.2	196.4	191.4	186.4	181.5	176.5
107.5°	242.2	242.7	243.4	243.9	244.5	244.9	245.5	246.1
110°	273.7	274.0	274.3	274.6	275.0	275.4	275.8	276.2



TEST NUMBER: P332604-927

CATALOG NUMBER: SA4XXDIP-C795D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	304.3	304.2	304.1	304.4	304.9	305.5	305.9	306.5
115°	349.9	350.1	350.5	350.6	350.6	350.6	350.6	350.6
117.5°	395.8	395.8	395.7	395.6	395.6	395.5	395.5	395.5
120°	424.2	424.5	424.8	424.8	424.5	424.2	424.0	423.7
122.5°	452.3	452.4	452.6	452.5	452.3	451.9	451.7	451.4
125°	491.4	491.8	492.2	492.5	492.7	492.7	492.9	493.1
127.5°	530.3	530.2	530.1	530.0	529.9	529.8	529.7	529.6
130°	554.1	554.1	554.3	554.4	554.4	554.4	554.4	554.4
132.5°	577.3	577.4	577.6	577.6	577.5	577.3	577.3	577.2
135°	609.4	609.7	610.0	610.2	610.5	610.8	611.1	611.3
137.5°	640.2	640.5	640.8	640.9	640.8	640.7	640.6	640.6
140°	659.3	659.7	660.0	660.4	660.5	660.6	660.8	660.9
142.5°	676.8	677.2	677.5	677.6	677.6	677.7	677.7	677.7
145°	702.0	702.2	702.3	702.5	702.8	703.1	703.4	703.6
147.5°	724.2	724.3	724.4	724.5	724.7	724.8	724.9	725.1
150°	738.3	738.3	738.3	738.4	738.6	738.6	738.8	738.9
152.5°	750.7	750.9	751.1	751.1	751.1	751.0	750.9	750.8
155°	767.3	767.9	768.4	768.5	768.0	767.6	767.2	766.8
157.5°	781.6	782.4	783.1	783.1	782.4	781.6	780.9	780.2
160°	790.8	791.6	792.4	792.4	791.6	790.8	790.0	789.1
162.5°	798.2	799.0	799.9	799.8	798.8	797.9	797.0	796.1
165°	808.7	809.8	810.9	810.8	809.5	808.3	807.1	805.8
167.5°	816.3	817.5	818.7	818.6	817.3	815.9	814.5	813.2
170°	821.0	822.1	823.2	823.1	821.7	820.4	819.0	817.6
172.5°	824.0	825.1	826.2	826.0	824.6	823.1	821.6	820.1
175°	827.5	828.8	830.0	829.8	828.1	826.5	824.8	823.2
177.5°	828.9	829.8	830.7	830.4	829.1	827.8	826.5	825.1
180°	828.1	828.1	828.1	828.1	828.1	828.1	828.1	828.1

(END OF REPORT)