

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332977-927

Luminaire Tested: **SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332977-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6144.5 lumens  
Efficiency: N/A  
Efficacy: 101.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332977-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332977-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	66	62	59	56	54	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	33	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11548	11548	11548
5°	11574	11432	11503
10°	11501	11294	11294
15°	11369	11058	10975
20°	11188	10746	10548
25°	10956	10381	10117
30°	10730	9996	9577
35°	10481	9596	9034
40°	10181	9141	8450
45°	9903	8691	7854
50°	9588	8171	7222
55°	9250	7631	6536
60°	8879	7038	5837
65°	8537	6298	5146
70°	8039	5481	4369
75°	7414	4545	3553
80°	6467	3464	3259
85°	5483	3149	2946



TEST NUMBER: P332977-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.4	2.2
10°-20°	374.7	6.1
20°-30°	541.1	8.8
30°-40°	613.3	10.0
40°-50°	592.3	9.6
50°-60°	492.5	8.0
60°-70°	340.1	5.5
70°-80°	172.4	2.8
80°-90°	47.3	0.8
90°-100°	67.4	1.1
100°-110°	199.8	3.3
110°-120°	339.1	5.5
120°-130°	447.1	7.3
130°-140°	502.1	8.2
140°-150°	493.4	8.0
150°-160°	415.0	6.8
160°-170°	276.1	4.5
170°-180°	96.7	1.6
0°-30°	1050.1	17.1
0°-40°	1663.5	27.1
0°-60°	2748.2	44.7
0°-90°	3307.9	53.8
90°-120°	606.3	9.9
90°-150°	2048.8	33.3
90°-180°	2837.0	46.2
0°-180°	6144.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1430	1430	1430	1430	1430	
5°	1428	1423	1411	1421	1420	135
15°	1360	1349	1323	1321	1313	383
25°	1230	1209	1165	1147	1136	566
35°	1064	1027	974	937	917	664
45°	867	826	761	709	688	669
55°	657	612	542	487	464	588
65°	447	398	330	284	269	441
75°	238	197	146	122	114	251
85°	59	38	34	32	32	67
90°	2	11	17	22	24	6
95°	48	54	60	62	62	53
105°	184	185	188	191	193	196
115°	345	345	343	342	342	340
125°	502	502	501	500	498	447
135°	648	652	652	651	648	501
145°	787	790	791	790	788	492
155°	901	901	901	903	901	415
165°	981	979	977	982	979	276
175°	1021	1017	1016	1021	1016	97
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332977-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1433.9	1433.1	1432.3	1431.6	1430.8	1429.3	1427.2	1425.1	1422.9	1420.8	1422.9
5°	1428.2	1427.3	1426.3	1425.3	1424.3	1422.4	1419.5	1416.6	1413.6	1410.7	1413.2
7.5°	1415.3	1414.3	1413.3	1412.2	1411.2	1408.8	1405.0	1401.2	1397.4	1393.6	1395.2
10°	1403.0	1401.8	1400.6	1399.4	1398.2	1395.3	1391.0	1386.6	1382.2	1377.8	1378.8
12.5°	1387.3	1385.8	1384.4	1383.1	1381.6	1378.3	1373.2	1368.0	1362.9	1357.7	1358.3
15°	1360.3	1358.1	1356.0	1353.8	1351.5	1347.4	1341.3	1335.2	1329.2	1323.1	1322.6
17.5°	1327.7	1324.5	1321.4	1318.2	1315.0	1309.8	1302.5	1295.2	1287.9	1280.6	1279.2
20°	1302.3	1299.1	1295.9	1292.8	1289.6	1283.9	1275.7	1267.3	1259.1	1250.8	1248.9
22.5°	1274.2	1270.7	1267.1	1263.6	1260.0	1253.8	1245.0	1236.1	1227.2	1218.4	1215.4
25°	1230.0	1225.6	1221.2	1216.9	1212.4	1205.3	1195.3	1185.3	1175.4	1165.4	1161.3
27.5°	1183.5	1178.1	1172.6	1167.0	1161.6	1153.5	1142.8	1132.2	1121.5	1110.8	1105.7
30°	1151.1	1145.0	1139.0	1132.9	1126.8	1118.0	1106.6	1095.1	1083.7	1072.3	1066.2
32.5°	1117.0	1110.1	1103.2	1096.4	1089.5	1080.1	1068.3	1056.5	1044.7	1032.8	1025.8
35°	1063.5	1055.7	1047.9	1040.1	1032.4	1022.4	1010.2	998.1	985.9	973.7	965.4
37.5°	1006.3	998.3	990.3	982.2	974.2	963.5	950.0	936.5	923.0	909.5	900.2
40°	966.1	958.0	950.0	941.9	933.9	923.0	909.1	895.2	881.3	867.4	857.2
42.5°	927.5	919.1	910.6	902.2	893.8	882.3	867.9	853.4	839.0	824.5	814.1
45°	867.4	858.5	849.5	840.4	831.4	819.6	805.0	790.4	775.8	761.2	749.3
47.5°	805.5	796.1	786.9	777.6	768.3	756.1	740.8	725.6	710.4	695.3	682.9
50°	763.4	753.9	744.4	734.9	725.4	712.9	697.4	681.8	666.1	650.6	638.4
52.5°	720.5	711.1	701.9	692.6	683.3	670.7	654.7	638.7	622.7	606.8	594.5
55°	657.2	647.5	637.7	628.0	618.2	605.5	589.6	573.8	558.0	542.2	529.5
57.5°	594.5	584.4	574.3	564.1	554.1	541.1	525.6	510.0	494.4	478.9	466.0
60°	549.9	540.1	530.4	520.6	510.9	498.2	482.7	467.1	451.5	435.9	423.3
62.5°	509.5	499.4	489.3	479.1	469.1	456.0	440.0	424.1	408.1	392.1	380.4
65°	446.9	436.4	426.0	415.5	405.0	392.0	376.4	360.8	345.2	329.7	319.2
67.5°	381.8	371.8	361.8	351.7	341.7	329.5	315.0	300.6	286.1	271.6	262.6
70°	340.6	330.4	320.2	310.0	299.8	287.7	273.9	259.9	246.1	232.2	224.2
72.5°	296.8	287.6	278.3	269.1	259.8	248.7	235.6	222.4	209.4	196.3	189.4
75°	237.7	228.7	219.7	210.6	201.7	191.4	180.0	168.6	157.1	145.7	140.1
77.5°	177.7	170.0	162.4	154.7	147.1	138.6	129.4	120.2	110.9	101.6	98.4
80°	139.1	132.1	125.0	118.0	110.9	103.7	96.4	89.1	81.8	74.5	73.8
82.5°	105.8	99.3	92.8	86.3	79.9	74.5	70.4	66.2	62.0	57.8	57.3
85°	59.2	54.3	49.4	44.5	39.7	36.8	36.1	35.4	34.7	34.0	33.4
87.5°	20.6	19.5	18.3	17.1	15.9	15.4	15.4	15.6	15.7	15.8	15.8
90°	2.4	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5
92.5°	17.0	19.2	21.3	23.5	25.7	27.4	28.4	29.3	30.3	31.3	31.9
95°	47.5	49.0	50.6	52.2	53.8	55.1	56.4	57.7	58.9	60.1	60.6
97.5°	82.9	84.1	85.4	86.7	87.9	89.3	90.7	92.1	93.6	95.1	95.7
100°	110.7	111.4	112.1	112.8	113.5	114.6	116.2	117.8	119.4	121.0	121.4
102.5°	139.8	140.1	140.4	140.6	140.9	141.8	143.2	144.7	146.1	147.6	148.1
105°	184.3	184.4	184.6	184.7	185.0	185.4	186.1	186.8	187.5	188.2	188.7
107.5°	230.9	231.1	231.3	231.6	231.7	231.9	232.0	232.1	232.2	232.3	232.8
110°	262.5	262.8	263.2	263.6	264.0	264.0	263.8	263.6	263.5	263.3	262.9



TEST NUMBER: P332977-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.4	295.5	295.6	295.6	295.7	295.6	295.2	294.9	294.6	294.3	294.2
115°	344.8	344.8	344.8	344.8	344.8	344.6	344.2	343.9	343.5	343.2	343.0
117.5°	391.3	391.4	391.5	391.7	391.8	391.7	391.5	391.3	391.0	390.8	390.1
120°	422.2	422.9	423.7	424.4	425.1	425.2	424.6	424.1	423.6	423.0	422.2
122.5°	454.5	454.8	455.0	455.3	455.6	455.7	455.4	455.1	454.9	454.6	454.1
125°	502.1	502.1	502.1	502.1	502.1	502.0	501.8	501.7	501.5	501.3	501.0
127.5°	545.3	545.8	546.3	546.8	547.4	547.5	547.2	546.9	546.7	546.4	546.1
130°	575.6	576.2	576.7	577.2	577.7	578.0	578.0	578.0	578.0	578.0	577.7
132.5°	606.7	607.0	607.4	607.8	608.2	608.3	608.2	608.0	607.8	607.8	607.4
135°	647.6	648.6	649.7	650.8	651.8	652.4	652.4	652.4	652.4	652.4	652.0
137.5°	692.2	692.7	693.2	693.6	694.2	694.5	694.8	695.1	695.4	695.7	695.2
140°	721.9	722.2	722.6	722.9	723.3	723.5	723.5	723.5	723.5	723.5	723.3
142.5°	749.1	749.5	749.8	750.2	750.5	750.6	750.5	750.4	750.2	750.0	750.0
145°	786.7	787.4	788.1	788.9	789.6	790.0	790.2	790.4	790.5	790.7	790.5
147.5°	824.1	824.9	825.8	826.6	827.4	827.8	827.7	827.5	827.4	827.3	827.1
150°	846.8	847.6	848.3	849.0	849.7	850.0	850.0	850.0	850.0	850.0	850.0
152.5°	868.4	868.8	869.2	869.7	870.1	870.3	870.4	870.6	870.8	870.8	871.3
155°	901.4	901.4	901.4	901.4	901.4	901.3	901.1	900.9	900.8	900.6	901.3
157.5°	929.2	928.9	928.6	928.3	928.0	927.8	927.7	927.7	927.7	927.6	928.2
160°	945.7	945.5	945.3	945.2	945.0	944.8	944.6	944.4	944.3	944.1	944.6
162.5°	960.8	960.4	960.0	959.5	959.0	958.7	958.5	958.4	958.2	958.0	958.9
165°	981.3	980.7	980.2	979.7	979.1	978.7	978.3	978.0	977.6	977.3	978.3
167.5°	997.0	996.2	995.5	994.7	994.0	993.6	993.6	993.7	993.7	993.8	994.8
170°	1005.8	1004.9	1004.0	1003.1	1002.3	1001.9	1002.1	1002.3	1002.4	1002.6	1003.7
172.5°	1012.1	1011.4	1010.7	1009.9	1009.2	1008.8	1008.8	1008.8	1008.9	1008.9	1010.1
175°	1020.8	1019.9	1019.1	1018.2	1017.3	1016.8	1016.6	1016.4	1016.2	1016.1	1017.3
177.5°	1023.7	1022.9	1022.2	1021.5	1020.8	1020.5	1020.5	1020.5	1020.5	1020.5	1021.4
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332977-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1425.1	1427.2	1429.3	1430.4	1430.1	1430.0	1429.7	1429.6
5°	1415.6	1418.0	1420.5	1421.4	1420.9	1420.5	1420.0	1419.5
7.5°	1396.8	1398.3	1399.9	1400.3	1399.5	1398.7	1397.9	1397.1
10°	1379.8	1380.8	1381.7	1381.7	1380.8	1379.8	1378.8	1377.8
12.5°	1358.8	1359.5	1360.0	1359.6	1358.3	1356.9	1355.6	1354.2
15°	1322.2	1321.6	1321.1	1320.0	1318.3	1316.6	1314.9	1313.2
17.5°	1277.9	1276.5	1275.2	1273.2	1270.6	1268.0	1265.4	1262.8
20°	1246.9	1245.0	1243.0	1240.5	1237.3	1234.1	1231.0	1227.8
22.5°	1212.5	1209.6	1206.7	1204.0	1201.3	1198.8	1196.2	1193.7
25°	1157.1	1152.9	1148.8	1145.5	1143.1	1140.7	1138.2	1135.8
27.5°	1100.6	1095.5	1090.4	1086.1	1082.6	1079.0	1075.5	1072.1
30°	1060.1	1054.0	1047.9	1042.9	1039.0	1035.1	1031.3	1027.4
32.5°	1018.7	1011.7	1004.6	999.3	995.5	991.8	988.2	984.4
35°	957.1	948.9	940.6	934.3	929.9	925.5	921.1	916.7
37.5°	891.0	881.8	872.5	865.7	861.3	856.9	852.5	848.2
40°	847.0	836.8	826.6	819.3	814.9	810.5	806.1	801.8
42.5°	803.7	793.3	782.8	775.4	770.8	766.2	761.6	757.1
45°	737.4	725.4	713.5	705.4	701.0	696.6	692.2	687.9
47.5°	670.6	658.2	645.8	637.2	632.4	627.6	622.7	618.0
50°	626.2	614.1	601.9	593.5	588.9	584.2	579.6	575.0
52.5°	582.0	569.7	557.3	548.7	543.9	539.1	534.2	529.5
55°	516.8	504.2	491.5	482.9	478.2	473.6	469.1	464.4
57.5°	453.1	440.3	427.5	419.3	415.7	412.3	408.8	405.3
60°	410.6	397.9	385.3	377.0	373.1	369.2	365.4	361.5
62.5°	368.8	357.0	345.4	337.9	334.9	331.8	328.6	325.5
65°	308.7	298.3	287.8	281.1	278.2	275.3	272.4	269.4
67.5°	253.6	244.6	235.6	229.5	226.2	223.1	219.8	216.7
70°	216.1	208.1	200.1	194.8	192.4	190.0	187.5	185.1
72.5°	182.5	175.7	168.8	164.3	162.0	159.8	157.6	155.3
75°	134.5	128.9	123.3	119.8	118.3	116.8	115.3	113.9
77.5°	95.1	91.9	88.6	86.7	86.3	85.9	85.4	85.0
80°	73.0	72.3	71.5	71.1	70.8	70.6	70.3	70.1
82.5°	56.7	56.2	55.7	55.3	55.1	54.8	54.6	54.3
85°	33.0	32.5	32.0	31.8	31.8	31.8	31.8	31.8
87.5°	15.8	15.8	15.8	15.9	16.2	16.5	16.7	17.0
90°	19.5	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	32.6	33.2	33.8	34.3	34.5	34.7	34.9	35.1
95°	61.2	61.7	62.2	62.5	62.5	62.5	62.5	62.5
97.5°	96.3	97.0	97.6	97.9	97.9	97.9	97.9	97.9
100°	121.7	122.0	122.4	122.6	122.6	122.6	122.6	122.6
102.5°	148.5	149.0	149.5	149.8	150.0	150.1	150.3	150.4
105°	189.3	189.8	190.3	190.8	191.3	191.9	192.4	192.9
107.5°	233.3	233.8	234.2	234.5	234.5	234.4	234.4	234.3
110°	262.6	262.2	261.9	262.0	262.5	263.0	263.6	264.1





TEST NUMBER: P332977-927

CATALOG NUMBER: SA4XXRDIP-C1020D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	294.1	294.1	294.1	294.1	294.1	294.2	294.4	294.5
115°	342.8	342.6	342.5	342.3	342.1	341.9	341.7	341.6
117.5°	389.6	389.0	388.4	387.9	387.5	387.2	386.8	386.5
120°	421.3	420.4	419.5	419.2	419.6	419.9	420.3	420.6
122.5°	453.4	452.9	452.3	451.6	451.0	450.4	449.7	449.1
125°	500.6	500.3	499.9	499.6	499.2	498.8	498.5	498.1
127.5°	545.7	545.3	544.9	544.6	544.4	544.1	543.8	543.5
130°	577.3	576.9	576.6	576.1	575.4	574.6	573.9	573.2
132.5°	607.0	606.7	606.3	606.0	605.7	605.5	605.1	604.9
135°	651.6	651.3	650.9	650.5	650.0	649.4	648.9	648.4
137.5°	694.7	694.3	693.9	693.6	693.8	693.9	694.0	694.1
140°	723.2	722.9	722.8	722.6	722.5	722.2	722.1	721.9
142.5°	750.0	750.0	750.0	749.9	749.9	749.8	749.8	749.7
145°	790.4	790.2	790.0	789.6	789.1	788.6	788.1	787.5
147.5°	827.0	826.8	826.6	826.5	826.3	826.2	826.0	825.9
150°	850.0	850.0	850.0	849.9	849.8	849.5	849.4	849.2
152.5°	871.7	872.1	872.6	872.6	872.1	871.6	871.2	870.7
155°	902.1	902.7	903.4	903.4	902.7	902.1	901.3	900.6
157.5°	928.7	929.2	929.8	929.7	929.2	928.5	928.0	927.3
160°	945.2	945.7	946.2	946.0	945.2	944.3	943.4	942.5
162.5°	959.9	960.8	961.8	961.9	961.0	960.1	959.3	958.3
165°	979.5	980.5	981.5	981.7	981.0	980.3	979.6	978.9
167.5°	995.9	997.0	998.0	998.0	996.9	995.8	994.7	993.6
170°	1004.7	1005.8	1006.9	1006.7	1005.5	1004.2	1003.1	1001.8
172.5°	1011.3	1012.5	1013.8	1013.7	1012.5	1011.2	1010.0	1008.8
175°	1018.5	1019.8	1021.0	1021.0	1019.8	1018.5	1017.3	1016.1
177.5°	1022.5	1023.4	1024.5	1024.4	1023.3	1022.1	1021.0	1019.9
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4

(END OF REPORT)