

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332641-935

Luminaire Tested: **SA4XXDIP-C1020D590U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332641-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D590U935-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5576.0 lumens  
Efficiency: N/A  
Efficacy: 114.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332641-935  
CATALOG NUMBER: SA4XXDIP-C1020D590U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332641-935

CATALOG NUMBER: SA4XXDIP-C1020D590U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	64	63	62	58
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48
3	85	75	67	61	80	71	64	59	63	58	54	57	52	49	50	47	44	41
4	78	66	58	52	73	63	56	50	56	50	46	51	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	41	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26	24
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19
10	49	37	29	25	47	35	28	24	32	26	22	29	24	21	27	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11994	11994	11994
5°	12030	11885	11972
10°	11954	11788	11847
15°	11810	11621	11651
20°	11618	11413	11424
25°	11399	11176	11144
30°	11130	10897	10797
35°	10852	10606	10465
40°	10564	10275	10086
45°	10261	9949	9758
50°	9928	9658	9359
55°	9568	9282	8981
60°	9206	8861	8591
65°	8800	8458	8118
70°	8344	7924	7615
75°	7648	7277	7093
80°	6811	6527	6365
85°	5956	5734	5622



TEST NUMBER: P332641-935

CATALOG NUMBER: SA4XXDIP-C1020D590U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.9	2.5
10°-20°	394.2	7.1
20°-30°	580.2	10.4
30°-40°	674.5	12.1
40°-50°	674.5	12.1
50°-60°	590.0	10.6
60°-70°	438.2	7.9
70°-80°	248.9	4.5
80°-90°	73.7	1.3
90°-100°	41.9	0.8
100°-110°	124.1	2.2
110°-120°	210.6	3.8
120°-130°	277.7	5.0
130°-140°	311.8	5.6
140°-150°	306.4	5.5
150°-160°	257.7	4.6
160°-170°	171.5	3.1
170°-180°	60.0	1.1
0°-30°	1114.3	20.0
0°-40°	1788.8	32.1
0°-60°	3053.4	54.8
0°-90°	3814.3	68.4
90°-120°	376.5	6.8
90°-150°	1272.4	22.8
90°-180°	1762.0	31.6
0°-180°	5576.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1486	1486	1486	1486	1486	
5°	1484	1479	1467	1479	1477	141
15°	1413	1408	1390	1397	1394	398
25°	1280	1271	1255	1256	1251	588
35°	1101	1092	1076	1068	1062	688
45°	899	890	871	859	855	693
55°	680	675	660	646	638	609
65°	461	454	443	431	425	456
75°	245	239	233	229	227	261
85°	64	64	62	62	61	71
90°	2	7	11	14	15	5
95°	29	34	37	39	39	33
105°	114	115	117	118	120	121
115°	214	214	213	213	212	211
125°	312	312	311	310	309	278
135°	402	405	405	404	403	311
145°	489	490	491	490	489	306
155°	560	560	559	561	559	257
165°	609	608	607	610	608	172
175°	634	632	631	634	631	60
180°	635	635	635	635	635	



TEST NUMBER: P332641-935

CATALOG NUMBER: SA4XXDIP-C1020D590U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1489.4	1488.8	1488.2	1487.5	1486.9	1485.4	1483.1	1480.7	1478.4	1476.1	1478.3
5°	1484.5	1483.4	1482.4	1481.3	1480.2	1478.3	1475.3	1472.4	1469.6	1466.6	1469.6
7.5°	1470.7	1469.6	1468.5	1467.5	1466.5	1464.3	1461.0	1457.8	1454.6	1451.4	1453.7
10°	1458.3	1457.2	1456.1	1455.1	1454.1	1451.8	1448.4	1444.9	1441.5	1438.0	1440.1
12.5°	1442.1	1441.1	1439.9	1438.9	1437.9	1435.5	1431.8	1428.2	1424.5	1420.9	1423.2
15°	1413.1	1412.0	1410.9	1409.9	1408.8	1406.3	1402.3	1398.4	1394.4	1390.4	1392.0
17.5°	1378.0	1376.7	1375.4	1374.1	1372.8	1370.2	1366.4	1362.7	1358.9	1355.2	1356.2
20°	1352.3	1351.0	1349.7	1348.3	1347.0	1344.4	1340.4	1336.4	1332.5	1328.5	1329.3
22.5°	1324.7	1322.9	1321.2	1319.5	1317.8	1314.8	1310.9	1306.9	1303.0	1299.0	1300.5
25°	1279.7	1277.9	1276.0	1274.1	1272.3	1269.5	1265.8	1262.1	1258.4	1254.7	1255.0
27.5°	1228.3	1226.4	1224.4	1222.5	1220.6	1218.0	1214.5	1211.1	1207.6	1204.2	1203.6
30°	1194.0	1191.9	1189.7	1187.7	1185.5	1182.8	1179.3	1175.9	1172.4	1169.0	1167.9
32.5°	1157.8	1155.9	1154.0	1152.1	1150.2	1147.4	1143.8	1140.1	1136.4	1132.8	1131.5
35°	1101.1	1099.3	1097.4	1095.6	1093.7	1091.0	1087.3	1083.6	1079.9	1076.2	1074.3
37.5°	1041.4	1039.7	1038.0	1036.3	1034.6	1031.8	1027.8	1023.8	1019.9	1015.9	1013.9
40°	1002.4	1000.2	998.1	996.0	993.9	990.8	986.9	982.9	979.0	975.0	972.3
42.5°	960.4	959.2	957.9	956.7	955.4	952.5	948.1	943.7	939.4	935.0	931.9
45°	898.8	896.9	895.1	893.2	891.4	888.3	884.1	879.9	875.6	871.4	868.5
47.5°	834.2	833.0	831.7	830.4	829.1	826.6	822.7	818.7	814.9	810.9	807.6
50°	790.5	789.4	788.3	787.3	786.2	783.9	780.2	776.4	772.7	769.0	765.3
52.5°	747.6	746.3	745.0	743.8	742.5	739.9	736.0	732.1	728.1	724.3	721.0
55°	679.8	678.9	678.1	677.3	676.6	674.3	670.6	666.9	663.2	659.5	656.3
57.5°	615.0	614.1	613.2	612.3	611.4	609.1	605.5	601.8	598.1	594.5	591.5
60°	570.2	568.9	567.6	566.3	564.9	562.6	559.1	555.7	552.2	548.8	546.4
62.5°	526.4	525.3	524.2	523.1	521.9	519.6	515.9	512.3	508.6	505.0	502.8
65°	460.7	459.3	458.1	456.8	455.4	453.4	450.7	448.2	445.5	442.8	440.2
67.5°	394.5	393.3	392.1	390.9	389.6	387.8	385.2	382.7	380.1	377.6	375.1
70°	353.5	351.7	349.8	348.0	346.1	344.1	342.1	339.9	337.9	335.7	333.6
72.5°	309.8	307.9	306.1	304.2	302.4	300.6	298.9	297.2	295.5	293.8	292.1
75°	245.2	243.9	242.5	241.3	240.0	238.6	237.3	236.0	234.6	233.3	232.3
77.5°	183.6	183.0	182.4	181.8	181.2	180.4	179.2	178.1	176.8	175.7	175.4
80°	146.5	145.6	144.8	144.0	143.3	142.6	142.1	141.5	141.0	140.4	139.9
82.5°	110.2	109.9	109.5	109.1	108.7	108.5	108.4	108.3	108.2	108.1	107.8
85°	64.3	64.3	64.3	64.3	64.3	64.1	63.5	62.9	62.4	61.9	61.9
87.5°	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1
90°	1.5	2.7	3.9	5.1	6.3	7.3	8.2	9.0	9.9	10.8	11.5
92.5°	10.5	11.9	13.3	14.6	16.0	17.0	17.7	18.3	18.9	19.5	19.8
95°	29.4	30.5	31.4	32.4	33.4	34.3	35.0	35.8	36.6	37.3	37.6
97.5°	51.5	52.3	53.0	53.8	54.6	55.4	56.3	57.3	58.1	59.1	59.4
100°	68.7	69.2	69.7	70.1	70.5	71.2	72.2	73.2	74.1	75.2	75.3
102.5°	86.8	87.0	87.1	87.3	87.5	88.1	88.9	89.8	90.7	91.6	92.0
105°	114.4	114.5	114.6	114.8	114.9	115.1	115.5	116.0	116.4	116.8	117.2
107.5°	143.4	143.5	143.6	143.8	144.0	144.0	144.0	144.1	144.2	144.3	144.6
110°	163.1	163.2	163.5	163.7	163.9	163.9	163.8	163.8	163.7	163.5	163.3



TEST NUMBER: P332641-935

CATALOG NUMBER: SA4XXDIP-C1020D590U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	183.5	183.5	183.6	183.6	183.7	183.6	183.4	183.1	183.0	182.8	182.7
115°	214.1	214.1	214.1	214.1	214.1	214.0	213.8	213.5	213.4	213.1	213.0
117.5°	243.0	243.1	243.1	243.2	243.3	243.3	243.1	243.0	242.8	242.7	242.3
120°	262.3	262.7	263.1	263.6	264.0	264.1	263.7	263.4	263.0	262.7	262.2
122.5°	282.2	282.4	282.6	282.8	282.9	283.0	282.8	282.7	282.5	282.4	282.0
125°	311.9	311.9	311.9	311.9	311.9	311.8	311.7	311.6	311.4	311.3	311.1
127.5°	338.6	339.0	339.3	339.7	339.9	340.0	339.8	339.7	339.5	339.3	339.1
130°	357.5	357.8	358.2	358.5	358.8	359.0	359.0	359.0	359.0	359.0	358.8
132.5°	376.8	377.0	377.2	377.5	377.7	377.8	377.7	377.6	377.5	377.5	377.2
135°	402.2	402.9	403.5	404.2	404.8	405.1	405.1	405.1	405.1	405.1	404.9
137.5°	429.9	430.2	430.5	430.8	431.1	431.4	431.5	431.7	431.9	432.0	431.8
140°	448.3	448.6	448.8	449.0	449.2	449.4	449.4	449.4	449.4	449.4	449.2
142.5°	465.2	465.5	465.7	465.9	466.1	466.1	466.1	466.0	465.9	465.8	465.8
145°	488.6	489.0	489.5	489.9	490.3	490.6	490.8	490.9	490.9	491.0	490.9
147.5°	511.8	512.3	512.8	513.3	513.9	514.1	514.0	513.9	513.8	513.8	513.7
150°	525.9	526.4	526.8	527.3	527.7	527.9	527.9	527.9	527.9	527.9	527.9
152.5°	539.3	539.6	539.8	540.1	540.4	540.5	540.6	540.7	540.8	540.9	541.1
155°	559.8	559.8	559.8	559.8	559.8	559.7	559.6	559.6	559.5	559.3	559.7
157.5°	577.1	576.9	576.7	576.5	576.4	576.2	576.2	576.2	576.2	576.1	576.4
160°	587.3	587.2	587.1	587.0	586.9	586.8	586.7	586.6	586.4	586.3	586.7
162.5°	596.8	596.5	596.2	595.9	595.6	595.4	595.3	595.2	595.1	595.0	595.6
165°	609.4	609.1	608.7	608.5	608.1	607.9	607.6	607.4	607.2	607.0	607.6
167.5°	619.1	618.7	618.2	617.8	617.3	617.1	617.1	617.2	617.2	617.2	617.9
170°	624.7	624.1	623.5	623.0	622.4	622.2	622.3	622.4	622.6	622.7	623.4
172.5°	628.5	628.1	627.7	627.2	626.7	626.5	626.5	626.5	626.5	626.6	627.3
175°	634.0	633.4	632.9	632.3	631.8	631.5	631.4	631.3	631.1	631.0	631.8
177.5°	635.8	635.3	634.9	634.5	634.0	633.8	633.8	633.8	633.8	633.8	634.4
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0



TEST NUMBER: P332641-935

CATALOG NUMBER: SA4XXDIP-C1020D590U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1480.3	1482.5	1484.6	1485.6	1485.3	1485.1	1484.9	1484.7
5°	1472.4	1475.3	1478.3	1479.5	1478.9	1478.3	1477.8	1477.3
7.5°	1456.0	1458.4	1460.7	1461.7	1461.4	1461.0	1460.7	1460.4
10°	1442.3	1444.4	1446.5	1447.3	1446.7	1446.2	1445.7	1445.2
12.5°	1425.6	1427.9	1430.2	1431.0	1430.3	1429.5	1428.7	1428.1
15°	1393.6	1395.2	1396.8	1397.1	1396.4	1395.6	1394.8	1394.0
17.5°	1357.2	1358.2	1359.2	1359.4	1358.9	1358.4	1357.9	1357.3
20°	1330.1	1330.9	1331.7	1331.8	1331.3	1330.8	1330.2	1329.7
22.5°	1301.8	1303.3	1304.7	1304.9	1304.0	1303.0	1302.1	1301.1
25°	1255.3	1255.5	1255.8	1255.3	1254.3	1253.3	1252.2	1251.1
27.5°	1203.0	1202.3	1201.7	1200.8	1199.4	1198.1	1196.7	1195.4
30°	1166.9	1165.8	1164.8	1163.6	1162.3	1160.9	1159.6	1158.3
32.5°	1130.2	1129.0	1127.7	1126.4	1125.1	1123.8	1122.5	1121.1
35°	1072.5	1070.6	1068.8	1067.1	1065.8	1064.5	1063.2	1061.9
37.5°	1011.8	1009.9	1007.9	1006.0	1004.3	1002.5	1000.7	999.0
40°	969.7	967.0	964.4	962.4	961.0	959.8	958.5	957.1
42.5°	928.8	925.7	922.6	920.7	919.8	918.9	918.0	917.1
45°	865.6	862.6	859.7	857.9	857.1	856.4	855.5	854.7
47.5°	804.3	801.1	797.8	795.1	793.2	791.1	789.1	787.1
50°	761.6	757.9	754.2	751.6	749.9	748.4	746.8	745.2
52.5°	717.7	714.4	711.1	708.5	706.5	704.5	702.5	700.4
55°	653.2	650.0	646.8	644.5	642.8	641.3	639.6	638.1
57.5°	588.5	585.5	582.5	580.1	578.6	577.1	575.6	574.0
60°	544.1	541.7	539.2	537.4	536.1	534.8	533.5	532.1
62.5°	500.7	498.4	496.3	494.6	493.3	491.9	490.6	489.3
65°	437.6	434.9	432.2	430.2	429.0	427.7	426.3	425.0
67.5°	372.6	370.0	367.5	366.0	365.6	365.2	364.9	364.5
70°	331.5	329.3	327.3	325.8	325.0	324.2	323.4	322.6
72.5°	290.4	288.7	287.1	285.8	285.0	284.2	283.4	282.6
75°	231.2	230.1	229.1	228.4	228.2	227.9	227.6	227.4
77.5°	175.0	174.8	174.4	173.9	173.2	172.5	171.9	171.2
80°	139.4	138.9	138.4	137.9	137.7	137.4	137.2	136.9
82.5°	107.5	107.1	106.9	106.5	106.2	106.0	105.7	105.5
85°	61.9	61.9	61.9	61.7	61.5	61.2	61.0	60.7
87.5°	25.3	25.4	25.6	25.7	25.7	25.7	25.7	25.8
90°	12.1	12.7	13.4	13.9	14.1	14.3	14.6	14.7
92.5°	20.2	20.7	21.0	21.3	21.4	21.5	21.7	21.8
95°	38.0	38.3	38.7	38.8	38.8	38.8	38.8	38.8
97.5°	59.8	60.2	60.6	60.8	60.8	60.8	60.8	60.8
100°	75.6	75.8	76.0	76.1	76.1	76.1	76.1	76.1
102.5°	92.2	92.6	92.8	93.1	93.2	93.2	93.3	93.4
105°	117.5	117.9	118.2	118.5	118.8	119.2	119.5	119.9
107.5°	144.9	145.2	145.5	145.7	145.6	145.6	145.6	145.6
110°	163.1	162.9	162.6	162.7	163.1	163.3	163.7	164.0





TEST NUMBER: P332641-935

CATALOG NUMBER: SA4XXDIP-C1020D590U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	182.7	182.6	182.6	182.6	182.7	182.7	182.8	182.9
115°	212.9	212.8	212.7	212.6	212.5	212.3	212.2	212.2
117.5°	241.9	241.6	241.2	240.9	240.6	240.5	240.2	240.0
120°	261.7	261.1	260.5	260.4	260.6	260.8	261.1	261.2
122.5°	281.6	281.3	280.9	280.5	280.1	279.7	279.3	279.0
125°	310.9	310.6	310.5	310.2	310.0	309.8	309.6	309.4
127.5°	338.9	338.7	338.5	338.3	338.1	337.9	337.8	337.6
130°	358.5	358.3	358.1	357.7	357.3	356.9	356.5	356.0
132.5°	377.0	376.8	376.6	376.3	376.2	376.0	375.8	375.7
135°	404.7	404.5	404.2	404.0	403.6	403.3	403.0	402.7
137.5°	431.4	431.2	430.9	430.8	430.8	430.9	431.0	431.1
140°	449.1	449.0	448.9	448.8	448.7	448.6	448.5	448.3
142.5°	465.8	465.8	465.7	465.7	465.7	465.7	465.6	465.6
145°	490.9	490.8	490.6	490.4	490.1	489.7	489.4	489.1
147.5°	513.6	513.5	513.4	513.3	513.2	513.1	513.0	512.9
150°	527.9	527.9	527.9	527.9	527.7	527.6	527.5	527.4
152.5°	541.4	541.7	541.9	541.9	541.7	541.3	541.1	540.8
155°	560.2	560.6	561.1	561.1	560.6	560.2	559.7	559.3
157.5°	576.8	577.1	577.5	577.4	577.0	576.7	576.3	575.9
160°	587.0	587.3	587.6	587.5	587.0	586.4	585.9	585.4
162.5°	596.2	596.8	597.4	597.4	596.8	596.2	595.7	595.2
165°	608.3	608.9	609.6	609.7	609.2	608.8	608.4	608.0
167.5°	618.5	619.1	619.8	619.7	619.1	618.5	617.8	617.1
170°	624.0	624.7	625.3	625.3	624.5	623.7	622.9	622.2
172.5°	628.1	628.9	629.6	629.6	628.8	628.0	627.2	626.5
175°	632.6	633.4	634.0	634.0	633.4	632.6	631.8	631.0
177.5°	635.0	635.6	636.2	636.2	635.5	634.8	634.0	633.4
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0

(END OF REPORT)