

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332706-935

Luminaire Tested: **SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332706-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8719.9 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332706-935
CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	53
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	71	83	77	71	67	66	62	58	55	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13397	13397	13397	13397
5°	15776	13431	11854	13431
10°	18889	13373	10673	13373
15°	22349	13237	9802	13237
20°	24887	13099	9024	13099
25°	25289	12896	8487	12896
30°	21519	12701	8318	12701
35°	16544	12384	8319	12384
40°	12896	12012	8476	12012
45°	10752	11451	8617	11451
50°	9463	10766	8911	10766
55°	8670	9947	9270	9947
60°	8125	9213	9700	9213
65°	7564	8392	10059	8392
70°	6911	7579	10286	7579
75°	6173	6669	10162	6669
80°	5174	5463	9842	5463
85°	3816	3946	9429	3946



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.7	1.9
10°-20°	498.3	5.7
20°-30°	790.2	9.1
30°-40°	879.4	10.1
40°-50°	800.5	9.2
50°-60°	654.1	7.5
60°-70°	467.0	5.4
70°-80°	257.1	2.9
80°-90°	74.1	0.8
90°-100°	45.8	0.5
100°-110°	291.7	3.3
110°-120°	558.0	6.4
120°-130°	708.4	8.1
130°-140°	757.9	8.7
140°-150°	708.7	8.1
150°-160°	571.5	6.6
160°-170°	368.6	4.2
170°-180°	127.0	1.5
0°-30°	1450.2	16.6
0°-40°	2329.6	26.7
0°-60°	3784.2	43.4
0°-90°	4582.4	52.6
90°-120°	895.4	10.3
90°-150°	3070.4	35.2
90°-180°	4138.0	47.5
0°-180°	8719.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1660	1660	1660	1660	1660	
5°	1947	1657	1463	1657	1947	198
15°	2674	1584	1173	1584	2674	756
25°	2839	1448	953	1448	2839	1252
35°	1679	1257	844	1257	1679	1066
45°	942	1003	755	1003	942	742
55°	616	707	659	707	616	556
65°	396	439	527	439	396	392
75°	198	214	326	214	198	210
85°	41	43	102	43	41	51
90°	30	3	30	3	30	14
95°	29	55	29	55	29	23
105°	285	301	285	301	285	249
115°	566	562	566	562	566	561
125°	796	790	796	790	796	709
135°	987	980	987	980	987	760
145°	1136	1130	1136	1130	1136	710
155°	1238	1240	1238	1240	1238	571
165°	1302	1308	1302	1308	1302	368
175°	1330	1338	1330	1338	1330	127
180°	1338	1338	1338	1338	1338	



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1766.2	1765.6	1760.1	1759.0	1755.1	1750.2	1749.1	1740.3	1722.7	1714.4	1712.3
5°	1946.8	1960.6	1942.7	1939.2	1937.2	1914.5	1902.8	1889.0	1857.4	1838.9	1824.5
7.5°	2162.4	2164.0	2156.2	2149.9	2132.4	2112.6	2082.9	2051.3	2013.6	1974.4	1944.9
10°	2304.3	2309.8	2300.9	2299.5	2264.4	2242.4	2198.4	2161.3	2118.7	2071.2	2027.9
12.5°	2453.8	2446.2	2441.6	2412.2	2405.7	2365.6	2314.5	2276.2	2210.5	2155.9	2098.3
15°	2674.1	2659.0	2649.4	2608.8	2588.9	2533.1	2478.9	2437.0	2351.0	2269.3	2207.3
17.5°	2803.3	2818.5	2796.2	2779.6	2728.0	2689.0	2633.5	2545.5	2478.2	2376.6	2298.5
20°	2896.8	2898.2	2885.8	2868.7	2828.1	2778.6	2718.1	2621.8	2541.4	2440.4	2333.1
22.5°	2922.1	2922.4	2917.2	2901.1	2870.4	2830.3	2769.2	2689.0	2591.5	2481.7	2374.4
25°	2839.1	2836.3	2842.5	2860.4	2848.7	2836.3	2801.3	2741.5	2650.8	2534.5	2419.1
27.5°	2530.6	2549.5	2584.5	2628.5	2670.8	2703.1	2712.2	2699.9	2643.7	2548.2	2427.2
30°	2308.4	2331.8	2357.9	2401.8	2487.2	2535.9	2589.5	2630.1	2607.5	2531.2	2418.4
32.5°	2064.2	2070.0	2108.8	2158.8	2236.9	2330.8	2415.8	2498.1	2525.5	2485.4	2391.4
35°	1678.7	1688.3	1730.3	1779.8	1875.3	1990.1	2118.0	2232.1	2326.2	2364.0	2315.9
37.5°	1369.9	1397.6	1427.1	1480.3	1564.4	1667.8	1800.7	1948.4	2088.7	2182.7	2198.6
40°	1223.7	1240.8	1262.1	1302.7	1374.2	1475.9	1590.0	1759.1	1908.3	2043.1	2087.1
42.5°	1108.1	1118.2	1131.3	1167.9	1222.4	1323.6	1427.8	1576.6	1726.3	1887.4	1961.1
45°	941.8	952.1	974.0	995.4	1036.6	1106.7	1203.7	1326.0	1476.6	1631.9	1768.1
47.5°	821.7	828.2	841.3	864.1	899.1	945.4	1024.2	1126.4	1266.0	1416.8	1561.9
50°	753.5	758.9	769.2	789.9	816.7	857.9	922.6	1018.0	1127.4	1279.3	1421.6
52.5°	699.6	701.7	709.3	723.3	744.6	779.3	832.3	911.4	1013.0	1148.4	1290.2
55°	616.0	618.7	625.6	635.8	654.4	676.4	717.0	776.1	864.8	982.3	1105.4
57.5°	547.2	549.1	554.9	558.9	574.1	592.0	623.2	665.5	732.6	832.3	942.2
60°	503.2	501.8	508.7	512.1	522.5	537.6	561.6	602.2	660.6	741.1	842.1
62.5°	460.3	458.4	464.2	468.7	474.6	487.5	507.2	539.0	586.3	659.1	746.4
65°	396.0	393.2	396.7	402.2	407.7	414.5	429.0	457.1	495.0	547.2	613.9
67.5°	331.3	334.2	334.8	337.5	340.7	350.1	359.9	379.9	406.6	448.3	504.9
70°	292.8	293.5	296.3	296.3	298.3	306.6	314.9	326.5	352.7	391.2	437.2
72.5°	254.3	257.3	256.1	258.3	259.8	265.4	271.4	282.5	304.8	333.4	372.3
75°	197.9	200.0	200.0	200.7	202.8	204.8	209.7	217.9	233.8	255.0	281.8
77.5°	144.4	144.6	145.6	148.1	148.1	151.4	155.0	161.5	169.4	184.0	200.4
80°	111.3	112.7	112.0	113.4	113.4	116.1	117.5	125.8	129.2	138.9	151.9
82.5°	81.7	83.0	82.9	84.8	85.9	86.4	88.4	91.7	95.1	103.7	109.0
85°	41.2	42.6	41.2	42.6	44.7	45.4	47.4	48.1	50.9	53.0	57.8
87.5°	18.1	19.6	19.5	20.1	21.0	21.4	21.7	20.9	22.8	23.1	25.0
90°	30.0	29.5	29.1	28.7	28.2	27.4	26.0	24.7	23.3	22.0	20.2
92.5°	27.6	27.6	27.5	27.4	27.3	26.5	25.2	23.8	22.6	21.2	19.5
95°	29.0	28.8	28.6	28.3	28.2	27.4	26.0	24.7	23.3	22.0	21.8
97.5°	28.0	27.8	27.6	27.4	27.1	26.9	26.8	26.7	26.5	26.4	51.2
100°	28.0	27.8	27.6	27.4	27.1	28.9	32.7	36.4	40.2	44.0	74.7
102.5°	28.8	28.8	28.8	28.7	28.7	49.0	89.8	130.5	171.3	212.1	216.1
105°	285.2	293.2	301.1	309.1	317.1	320.1	318.1	316.2	314.2	312.1	311.0
107.5°	397.4	396.5	395.7	394.9	394.0	393.0	392.1	391.2	390.1	389.2	387.6
110°	446.2	445.6	444.9	444.2	443.5	443.0	442.6	442.1	441.6	441.2	439.9



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	495.0	494.2	493.4	492.5	491.6	491.3	491.4	491.5	491.5	491.6	491.0
115°	566.3	566.3	566.3	566.3	566.3	566.0	565.6	565.2	564.7	564.2	564.5
117.5°	638.7	638.8	638.9	638.9	639.0	639.1	639.2	639.3	639.4	639.5	639.0
120°	684.3	684.8	685.2	685.6	686.0	686.0	685.6	685.2	684.8	684.3	684.5
122.5°	729.1	729.5	730.0	730.5	730.9	731.0	730.7	730.5	730.2	730.0	729.6
125°	796.3	796.2	795.9	795.7	795.5	795.0	794.4	793.7	793.0	792.4	792.8
127.5°	855.4	855.6	855.7	855.9	856.1	856.3	856.4	856.5	856.6	856.8	855.7
130°	895.4	895.4	895.4	895.4	895.4	895.3	895.1	894.8	894.6	894.4	893.7
132.5°	932.2	932.4	932.5	932.7	932.9	932.9	932.7	932.5	932.2	932.0	931.2
135°	987.4	987.0	986.5	986.1	985.7	985.2	984.7	984.3	983.9	983.4	982.6
137.5°	1034.7	1034.7	1034.9	1035.1	1035.2	1035.0	1034.5	1034.1	1033.5	1033.0	1032.1
140°	1067.5	1067.2	1067.0	1066.8	1066.6	1066.2	1065.5	1064.8	1064.1	1063.5	1063.0
142.5°	1094.7	1094.7	1094.6	1094.6	1094.5	1094.2	1093.7	1093.3	1092.8	1092.3	1092.0
145°	1136.5	1136.1	1135.6	1135.1	1134.7	1134.4	1134.2	1133.9	1133.8	1133.5	1133.5
147.5°	1171.1	1170.9	1170.7	1170.4	1170.2	1170.0	1169.8	1169.7	1169.5	1169.3	1169.5
150°	1193.5	1193.3	1193.1	1192.8	1192.7	1192.5	1192.5	1192.5	1192.5	1192.5	1192.7
152.5°	1212.7	1212.9	1213.0	1213.1	1213.2	1213.1	1212.8	1212.5	1212.1	1211.8	1212.1
155°	1238.5	1239.2	1239.8	1240.5	1241.2	1241.1	1240.2	1239.3	1238.5	1237.5	1238.2
157.5°	1260.2	1261.3	1262.5	1263.6	1264.8	1264.8	1263.6	1262.5	1261.3	1260.2	1260.9
160°	1274.5	1275.9	1277.2	1278.6	1279.9	1279.9	1278.6	1277.2	1275.9	1274.5	1274.8
162.5°	1285.7	1287.3	1288.8	1290.3	1291.8	1291.9	1290.6	1289.3	1287.9	1286.6	1286.8
165°	1301.6	1303.6	1305.5	1307.6	1309.6	1309.7	1307.9	1306.1	1304.3	1302.6	1302.6
167.5°	1313.4	1315.6	1317.8	1320.1	1322.2	1322.4	1320.4	1318.5	1316.6	1314.6	1314.7
170°	1320.6	1322.8	1325.0	1327.2	1329.5	1329.7	1327.9	1326.1	1324.4	1322.6	1322.3
172.5°	1324.6	1327.0	1329.4	1331.8	1334.2	1334.5	1332.7	1330.9	1329.1	1327.4	1327.1
175°	1329.6	1332.2	1334.9	1337.6	1340.2	1340.6	1338.6	1336.6	1334.6	1332.6	1332.4
177.5°	1332.8	1334.9	1337.0	1339.2	1341.4	1341.7	1340.2	1338.9	1337.4	1336.0	1335.7
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332706-935
 CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1712.8	1705.1	1699.6	1695.2	1683.1	1675.9	1670.4	1662.8	1654.0	1644.6	1633.1
5°	1810.0	1786.7	1769.4	1743.4	1718.6	1698.0	1676.6	1657.4	1634.0	1608.6	1590.0
7.5°	1912.2	1877.4	1832.8	1794.2	1750.8	1713.0	1679.1	1644.5	1608.4	1573.6	1541.5
10°	1977.0	1932.3	1882.8	1824.5	1769.4	1720.6	1675.2	1631.3	1588.6	1546.0	1509.6
12.5°	2046.9	1991.2	1918.0	1849.8	1788.1	1722.9	1668.1	1614.2	1562.8	1518.0	1475.5
15°	2140.7	2060.2	1975.7	1884.2	1803.1	1726.8	1651.9	1583.8	1526.1	1467.0	1425.7
17.5°	2198.3	2098.8	2002.1	1906.5	1808.4	1712.1	1631.3	1552.8	1480.5	1421.8	1369.8
20°	2236.2	2137.3	2016.9	1921.4	1804.5	1705.6	1612.1	1524.7	1449.1	1386.6	1332.9
22.5°	2269.3	2154.8	2034.5	1908.8	1792.4	1687.4	1585.1	1497.2	1420.0	1354.1	1302.7
25°	2287.1	2155.8	2025.2	1900.1	1768.1	1643.6	1550.8	1447.8	1365.2	1295.8	1240.8
27.5°	2289.1	2148.6	2000.9	1861.8	1725.6	1609.7	1492.5	1400.4	1314.7	1241.4	1188.6
30°	2282.9	2136.6	1977.7	1827.2	1690.4	1564.6	1462.8	1362.5	1275.2	1202.3	1147.3
32.5°	2263.7	2111.3	1948.0	1788.7	1646.9	1523.9	1418.8	1323.4	1238.4	1166.6	1108.8
35°	2208.0	2057.4	1883.5	1717.9	1572.9	1448.5	1353.6	1256.6	1171.4	1103.4	1047.7
37.5°	2121.0	1984.9	1808.1	1636.7	1494.2	1369.2	1275.2	1187.6	1110.8	1041.6	984.6
40°	2045.1	1925.5	1748.2	1581.1	1427.1	1308.2	1220.2	1139.8	1063.4	998.2	943.8
42.5°	1957.7	1853.5	1689.9	1512.9	1364.4	1244.9	1159.2	1086.9	1015.0	954.7	900.4
45°	1801.7	1733.0	1579.1	1415.4	1260.8	1148.0	1066.2	1003.0	942.5	883.4	838.0
47.5°	1622.5	1588.4	1458.7	1303.4	1156.5	1045.4	974.5	916.1	863.0	813.0	772.9
50°	1502.0	1485.6	1373.5	1223.7	1083.4	978.9	907.4	857.2	811.8	767.8	730.0
52.5°	1383.3	1382.7	1281.7	1144.4	1014.7	914.0	843.1	796.2	756.9	721.1	687.2
55°	1201.6	1220.9	1141.9	1019.4	903.3	812.5	748.6	706.7	679.2	649.6	624.2
57.5°	1034.8	1066.8	1001.6	893.8	796.9	713.3	657.6	626.1	596.8	578.9	560.4
60°	926.0	956.2	905.3	814.6	723.2	651.7	598.7	570.6	545.1	532.8	519.7
62.5°	829.1	856.1	818.5	734.3	655.0	586.3	541.6	514.4	497.3	483.8	475.2
65°	690.9	713.6	681.2	620.1	552.0	497.1	460.5	439.3	422.8	417.2	407.7
67.5°	558.4	579.1	561.6	509.6	455.0	413.5	385.0	364.5	354.7	349.9	343.0
70°	479.8	500.4	481.9	436.5	394.6	359.6	332.7	321.1	310.7	308.7	299.0
72.5°	413.3	427.3	408.7	373.2	337.4	307.8	287.1	274.8	269.5	265.8	260.5
75°	310.0	322.4	310.0	282.5	257.1	236.5	218.6	213.8	207.6	205.5	202.1
77.5°	219.5	230.1	220.7	203.5	184.5	168.6	158.9	152.7	151.4	147.8	149.5
80°	167.7	174.6	165.7	153.9	138.9	127.9	121.0	117.5	113.4	112.0	114.8
82.5°	120.5	123.5	118.9	111.1	99.8	92.6	88.0	84.0	83.2	83.4	83.4
85°	62.6	61.9	61.2	54.3	50.9	46.1	43.3	42.6	41.9	43.3	44.7
87.5°	24.6	24.8	23.8	21.3	19.1	17.0	15.9	14.9	15.9	17.0	18.0
90°	18.4	16.7	14.9	12.7	10.3	7.9	5.4	3.0	5.4	7.9	10.3
92.5°	17.7	15.8	14.1	13.2	13.0	12.9	12.7	12.6	12.7	12.9	13.0
95°	21.5	21.4	21.1	24.8	32.4	39.9	47.4	55.0	47.4	39.9	32.4
97.5°	76.0	100.8	125.6	135.7	131.0	126.3	121.6	116.8	121.6	126.3	131.0
100°	105.4	136.0	166.8	180.1	176.1	172.1	168.1	164.1	168.1	172.1	176.1
102.5°	220.1	224.1	228.1	228.6	225.7	222.7	219.8	216.9	219.8	222.7	225.7
105°	309.9	308.8	307.7	306.4	305.1	303.8	302.5	301.1	302.5	303.8	305.1
107.5°	386.2	384.6	383.1	382.0	381.3	380.7	380.0	379.4	380.0	380.7	381.3
110°	438.5	437.2	435.8	434.9	434.2	433.5	432.8	432.2	432.8	433.5	434.2



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	490.3	489.7	489.1	488.2	487.0	485.8	484.7	483.5	484.7	485.8	487.0
115°	564.7	564.9	565.2	564.9	564.2	563.6	562.9	562.2	562.9	563.6	564.2
117.5°	638.5	638.0	637.5	636.8	635.9	635.1	634.1	633.3	634.1	635.1	635.9
120°	684.8	685.0	685.2	684.8	684.0	683.1	682.2	681.3	682.2	683.1	684.0
122.5°	729.3	729.0	728.7	728.2	727.7	727.2	726.7	726.1	726.7	727.2	727.7
125°	793.2	793.7	794.1	793.9	793.0	792.1	791.3	790.3	791.3	792.1	793.0
127.5°	854.7	853.7	852.6	852.0	851.9	851.6	851.4	851.2	851.4	851.6	851.9
130°	893.0	892.4	891.7	891.3	891.0	890.9	890.6	890.4	890.6	890.9	891.0
132.5°	930.3	929.4	928.7	928.0	927.6	927.2	926.8	926.4	926.8	927.2	927.6
135°	981.6	980.8	979.9	979.6	979.7	980.0	980.2	980.4	980.2	980.0	979.7
137.5°	1031.1	1030.1	1029.2	1028.6	1028.6	1028.5	1028.4	1028.3	1028.4	1028.5	1028.6
140°	1062.6	1062.1	1061.7	1061.3	1060.8	1060.3	1059.9	1059.5	1059.9	1060.3	1060.8
142.5°	1091.7	1091.5	1091.2	1090.7	1089.9	1089.1	1088.3	1087.4	1088.3	1089.1	1089.9
145°	1133.5	1133.5	1133.5	1133.2	1132.5	1131.9	1131.2	1130.5	1131.2	1131.9	1132.5
147.5°	1169.8	1170.0	1170.2	1169.7	1168.5	1167.2	1166.0	1164.7	1166.0	1167.2	1168.5
150°	1193.0	1193.2	1193.4	1193.1	1192.2	1191.3	1190.4	1189.6	1190.4	1191.3	1192.2
152.5°	1212.5	1213.0	1213.3	1213.1	1212.5	1211.8	1211.1	1210.3	1211.1	1211.8	1212.5
155°	1238.9	1239.6	1240.2	1240.4	1240.2	1240.0	1239.8	1239.6	1239.8	1240.0	1240.2
157.5°	1261.7	1262.4	1263.2	1263.6	1263.8	1263.9	1264.0	1264.1	1264.0	1263.9	1263.8
160°	1275.0	1275.2	1275.5	1275.9	1276.6	1277.2	1277.9	1278.6	1277.9	1277.2	1276.6
162.5°	1287.0	1287.2	1287.5	1288.0	1288.8	1289.7	1290.6	1291.3	1290.6	1289.7	1288.8
165°	1302.6	1302.6	1302.6	1303.1	1304.2	1305.4	1306.5	1307.6	1306.5	1305.4	1304.2
167.5°	1314.8	1315.0	1315.1	1315.8	1316.9	1318.1	1319.2	1320.3	1319.2	1318.1	1316.9
170°	1322.2	1321.9	1321.7	1322.2	1323.6	1324.9	1326.3	1327.6	1326.3	1324.9	1323.6
172.5°	1327.0	1326.7	1326.5	1327.1	1328.4	1329.7	1331.0	1332.4	1331.0	1329.7	1328.4
175°	1332.1	1331.9	1331.7	1332.2	1333.6	1334.9	1336.3	1337.6	1336.3	1334.9	1333.6
177.5°	1335.2	1334.9	1334.6	1335.0	1336.3	1337.5	1338.8	1340.0	1338.8	1337.5	1336.3
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1627.5	1622.6	1615.5	1605.6	1597.3	1588.5	1586.3	1583.0	1589.6	1584.2	1582.4
5°	1574.3	1559.8	1541.2	1519.9	1507.5	1489.7	1486.3	1479.4	1472.5	1471.8	1464.9
7.5°	1517.7	1496.5	1472.2	1450.4	1430.4	1410.9	1398.1	1395.3	1385.2	1379.2	1372.3
10°	1481.4	1455.3	1427.1	1406.5	1383.1	1362.5	1348.1	1339.8	1332.9	1325.3	1318.5
12.5°	1438.6	1410.7	1387.5	1365.2	1337.5	1321.8	1298.0	1283.8	1282.4	1282.5	1264.6
15°	1388.6	1361.2	1325.3	1293.7	1278.6	1248.4	1235.3	1218.8	1208.5	1198.2	1190.0
17.5°	1331.5	1297.4	1269.4	1233.1	1204.3	1180.2	1163.0	1153.1	1137.6	1123.0	1112.4
20°	1295.8	1259.4	1229.9	1191.3	1159.7	1130.1	1115.7	1102.0	1090.3	1077.9	1066.2
22.5°	1259.5	1221.4	1185.3	1147.9	1118.4	1087.3	1073.3	1054.6	1043.5	1036.6	1024.9
25°	1202.3	1161.1	1119.8	1084.1	1053.9	1026.3	1007.8	993.3	980.9	975.4	967.9
27.5°	1140.1	1099.2	1059.4	1018.7	984.4	964.5	949.6	938.7	931.6	924.3	920.9
30°	1100.6	1058.0	1015.4	977.5	945.9	926.0	912.2	904.7	899.1	895.7	892.3
32.5°	1060.4	1018.4	973.5	939.0	910.7	892.9	882.5	874.9	872.2	871.0	869.8
35°	996.1	953.5	912.2	881.3	854.5	847.6	838.7	834.6	833.2	838.0	840.1
37.5°	933.8	894.2	856.3	826.3	808.7	798.7	795.7	795.7	800.7	804.9	809.9
40°	893.6	855.1	819.4	793.3	776.8	770.6	769.2	772.7	778.2	783.0	788.5
42.5°	854.6	816.7	784.2	759.7	748.2	742.5	743.4	746.8	754.5	760.4	768.7
45°	794.0	762.3	730.7	710.8	701.2	702.6	702.6	708.8	716.3	725.2	734.2
47.5°	736.9	705.1	679.1	662.3	657.3	656.1	660.0	668.0	678.9	689.9	702.4
50°	698.4	668.2	645.5	630.3	624.9	627.0	632.4	640.0	653.1	666.8	679.8
52.5°	659.4	631.9	610.9	596.8	593.0	596.7	602.2	614.2	625.6	640.4	656.3
55°	598.7	575.4	558.9	548.5	547.2	549.2	555.4	568.5	585.0	603.6	618.7
57.5°	538.4	518.8	503.8	496.6	497.3	499.2	509.4	525.0	542.5	562.3	581.9
60°	497.7	479.8	467.4	461.9	462.6	466.7	479.1	493.6	515.6	534.9	555.4
62.5°	459.2	443.5	431.7	426.8	425.8	434.9	446.7	461.7	483.7	505.1	527.4
65°	397.4	385.0	375.3	372.6	374.6	381.5	396.7	416.6	435.1	457.8	481.2
67.5°	336.8	326.7	320.0	321.3	323.8	334.0	346.6	363.8	384.9	408.4	431.4
70°	298.3	288.7	283.2	283.9	288.0	300.4	311.4	328.6	351.3	375.3	394.6
72.5°	258.7	252.4	247.5	250.4	254.5	263.0	276.7	293.9	313.9	336.3	356.6
75°	198.6	198.6	195.9	197.9	204.1	212.4	222.7	240.6	260.5	278.4	294.9
77.5°	147.4	145.9	147.7	150.2	153.7	163.5	175.3	188.0	203.1	220.9	234.5
80°	112.7	113.4	116.8	121.0	122.3	129.9	142.3	153.9	165.7	180.8	193.9
82.5°	84.7	85.4	87.1	92.4	93.8	101.9	109.9	121.6	132.2	142.3	153.2
85°	46.1	46.1	49.5	51.6	55.0	60.5	65.3	72.2	81.8	88.7	99.0
87.5°	20.1	20.6	23.2	24.6	26.6	29.7	31.1	37.4	39.9	42.9	48.0
90°	12.7	14.9	16.7	18.4	20.2	22.0	23.3	24.7	26.0	27.4	28.2
92.5°	13.2	14.1	15.8	17.7	19.5	21.2	22.6	23.8	25.2	26.5	27.3
95°	24.8	21.1	21.4	21.5	21.8	22.0	23.3	24.7	26.0	27.4	28.2
97.5°	135.7	125.6	100.8	76.0	51.2	26.4	26.5	26.7	26.8	26.9	27.1
100°	180.1	166.8	136.0	105.4	74.7	44.0	40.2	36.4	32.7	28.9	27.1
102.5°	228.6	228.1	224.1	220.1	216.1	212.1	171.3	130.5	89.8	49.0	28.7
105°	306.4	307.7	308.8	309.9	311.0	312.1	314.2	316.2	318.1	320.1	317.1
107.5°	382.0	383.1	384.6	386.2	387.6	389.2	390.1	391.2	392.1	393.0	394.0
110°	434.9	435.8	437.2	438.5	439.9	441.2	441.6	442.1	442.6	443.0	443.5



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	488.2	489.1	489.7	490.3	491.0	491.6	491.5	491.5	491.4	491.3	491.6
115°	564.9	565.2	564.9	564.7	564.5	564.2	564.7	565.2	565.6	566.0	566.3
117.5°	636.8	637.5	638.0	638.5	639.0	639.5	639.4	639.3	639.2	639.1	639.0
120°	684.8	685.2	685.0	684.8	684.5	684.3	684.8	685.2	685.6	686.0	686.0
122.5°	728.2	728.7	729.0	729.3	729.6	730.0	730.2	730.5	730.7	731.0	730.9
125°	793.9	794.1	793.7	793.2	792.8	792.4	793.0	793.7	794.4	795.0	795.5
127.5°	852.0	852.6	853.7	854.7	855.7	856.8	856.6	856.5	856.4	856.3	856.1
130°	891.3	891.7	892.4	893.0	893.7	894.4	894.6	894.8	895.1	895.3	895.4
132.5°	928.0	928.7	929.4	930.3	931.2	932.0	932.2	932.5	932.7	932.9	932.9
135°	979.6	979.9	980.8	981.6	982.6	983.4	983.9	984.3	984.7	985.2	985.7
137.5°	1028.6	1029.2	1030.1	1031.1	1032.1	1033.0	1033.5	1034.1	1034.5	1035.0	1035.2
140°	1061.3	1061.7	1062.1	1062.6	1063.0	1063.5	1064.1	1064.8	1065.5	1066.2	1066.6
142.5°	1090.7	1091.2	1091.5	1091.7	1092.0	1092.3	1092.8	1093.3	1093.7	1094.2	1094.5
145°	1133.2	1133.5	1133.5	1133.5	1133.5	1133.5	1133.8	1133.9	1134.2	1134.4	1134.7
147.5°	1169.7	1170.2	1170.0	1169.8	1169.5	1169.3	1169.5	1169.7	1169.8	1170.0	1170.2
150°	1193.1	1193.4	1193.2	1193.0	1192.7	1192.5	1192.5	1192.5	1192.5	1192.5	1192.7
152.5°	1213.1	1213.3	1213.0	1212.5	1212.1	1211.8	1212.1	1212.5	1212.8	1213.1	1213.2
155°	1240.4	1240.2	1239.6	1238.9	1238.2	1237.5	1238.5	1239.3	1240.2	1241.1	1241.2
157.5°	1263.6	1263.2	1262.4	1261.7	1260.9	1260.2	1261.3	1262.5	1263.6	1264.8	1264.8
160°	1275.9	1275.5	1275.2	1275.0	1274.8	1274.5	1275.9	1277.2	1278.6	1279.9	1279.9
162.5°	1288.0	1287.5	1287.2	1287.0	1286.8	1286.6	1287.9	1289.3	1290.6	1291.9	1291.8
165°	1303.1	1302.6	1302.6	1302.6	1302.6	1302.6	1304.3	1306.1	1307.9	1309.7	1309.6
167.5°	1315.8	1315.1	1315.0	1314.8	1314.7	1314.6	1316.6	1318.5	1320.4	1322.4	1322.2
170°	1322.2	1321.7	1321.9	1322.2	1322.3	1322.6	1324.4	1326.1	1327.9	1329.7	1329.5
172.5°	1327.1	1326.5	1326.7	1327.0	1327.1	1327.4	1329.1	1330.9	1332.7	1334.5	1334.2
175°	1332.2	1331.7	1331.9	1332.1	1332.4	1332.6	1334.6	1336.6	1338.6	1340.6	1340.2
177.5°	1335.0	1334.6	1334.9	1335.2	1335.7	1336.0	1337.4	1338.9	1340.2	1341.7	1341.4
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1581.4	1580.3	1576.4	1575.9	1576.4	1580.3	1581.4	1582.4	1584.2	1589.6	1583.0
5°	1460.8	1457.3	1455.3	1462.8	1455.3	1457.3	1460.8	1464.9	1471.8	1472.5	1479.4
7.5°	1369.9	1367.2	1361.2	1359.2	1361.2	1367.2	1369.9	1372.3	1379.2	1385.2	1395.3
10°	1311.6	1308.9	1303.4	1302.0	1303.4	1308.9	1311.6	1318.5	1325.3	1332.9	1339.8
12.5°	1255.5	1250.0	1249.0	1250.3	1249.0	1250.0	1255.5	1264.6	1282.5	1282.4	1283.8
15°	1181.0	1178.3	1170.7	1172.8	1170.7	1178.3	1181.0	1190.0	1198.2	1208.5	1218.8
17.5°	1107.6	1104.3	1095.1	1103.2	1095.1	1104.3	1107.6	1112.4	1123.0	1137.6	1153.1
20°	1061.4	1055.9	1051.1	1050.4	1051.1	1055.9	1061.4	1066.2	1077.9	1090.3	1102.0
22.5°	1017.4	1012.4	1012.0	1007.5	1012.0	1012.4	1017.4	1024.9	1036.6	1043.5	1054.6
25°	962.4	957.6	956.2	952.8	956.2	957.6	962.4	967.9	975.4	980.9	993.3
27.5°	920.2	917.8	915.4	916.4	915.4	917.8	920.2	920.9	924.3	931.6	938.7
30°	894.3	893.6	892.3	892.3	892.3	893.6	894.3	892.3	895.7	899.1	904.7
32.5°	872.9	872.8	873.6	873.6	873.6	872.8	872.9	869.8	871.0	872.2	874.9
35°	842.8	844.8	846.2	844.1	846.2	844.8	842.8	840.1	838.0	833.2	834.6
37.5°	815.5	817.6	819.6	821.9	819.6	817.6	815.5	809.9	804.9	800.7	795.7
40°	794.7	799.5	800.8	804.3	800.8	799.5	794.7	788.5	783.0	778.2	772.7
42.5°	774.9	780.2	783.8	784.5	783.8	780.2	774.9	768.7	760.4	754.5	746.8
45°	744.5	750.0	754.8	754.8	754.8	750.0	744.5	734.2	725.2	716.3	708.8
47.5°	713.0	721.0	725.8	727.0	725.8	721.0	713.0	702.4	689.9	678.9	668.0
50°	691.6	701.2	706.0	709.5	706.0	701.2	691.6	679.8	666.8	653.1	640.0
52.5°	670.6	680.3	686.7	688.5	686.7	680.3	670.6	656.3	640.4	625.6	614.2
55°	634.5	648.2	655.8	658.6	655.8	648.2	634.5	618.7	603.6	585.0	568.5
57.5°	600.4	613.0	621.8	623.9	621.8	613.0	600.4	581.9	562.3	542.5	525.0
60°	574.0	587.7	598.7	600.8	598.7	587.7	574.0	555.4	534.9	515.6	493.6
62.5°	547.1	561.4	571.3	576.6	571.3	561.4	547.1	527.4	505.1	483.7	461.7
65°	500.4	514.9	524.5	526.6	524.5	514.9	500.4	481.2	457.8	435.1	416.6
67.5°	449.6	464.0	470.4	474.3	470.4	464.0	449.6	431.4	408.4	384.9	363.8
70°	413.8	425.5	432.4	435.8	432.4	425.5	413.8	394.6	375.3	351.3	328.6
72.5°	373.2	385.4	393.4	394.0	393.4	385.4	373.2	356.6	336.3	313.9	293.9
75°	310.7	321.8	325.8	325.8	325.8	321.8	310.7	294.9	278.4	260.5	240.6
77.5°	246.0	251.6	256.8	258.0	256.8	251.6	246.0	234.5	220.9	203.1	188.0
80°	204.1	207.6	211.7	211.7	211.7	207.6	204.1	193.9	180.8	165.7	153.9
82.5°	161.3	164.2	168.3	167.7	168.3	164.2	161.3	153.2	142.3	132.2	121.6
85°	97.6	103.8	103.1	101.8	103.1	103.8	97.6	99.0	88.7	81.8	72.2
87.5°	49.8	50.4	52.1	53.3	52.1	50.4	49.8	48.0	42.9	39.9	37.4
90°	28.7	29.1	29.5	30.0	29.5	29.1	28.7	28.2	27.4	26.0	24.7
92.5°	27.4	27.5	27.6	27.6	27.6	27.5	27.4	27.3	26.5	25.2	23.8
95°	28.3	28.6	28.8	29.0	28.8	28.6	28.3	28.2	27.4	26.0	24.7
97.5°	27.4	27.6	27.8	28.0	27.8	27.6	27.4	27.1	26.9	26.8	26.7
100°	27.4	27.6	27.8	28.0	27.8	27.6	27.4	27.1	28.9	32.7	36.4
102.5°	28.7	28.8	28.8	28.8	28.8	28.8	28.7	28.7	49.0	89.8	130.5
105°	309.1	301.1	293.2	285.2	293.2	301.1	309.1	317.1	320.1	318.1	316.2
107.5°	394.9	395.7	396.5	397.4	396.5	395.7	394.9	394.0	393.0	392.1	391.2
110°	444.2	444.9	445.6	446.2	445.6	444.9	444.2	443.5	443.0	442.6	442.1



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.5	493.4	494.2	495.0	494.2	493.4	492.5	491.6	491.3	491.4	491.5
115°	566.3	566.3	566.3	566.3	566.3	566.3	566.3	566.3	566.0	565.6	565.2
117.5°	638.9	638.9	638.8	638.7	638.8	638.9	638.9	639.0	639.1	639.2	639.3
120°	685.6	685.2	684.8	684.3	684.8	685.2	685.6	686.0	686.0	685.6	685.2
122.5°	730.5	730.0	729.5	729.1	729.5	730.0	730.5	730.9	731.0	730.7	730.5
125°	795.7	795.9	796.2	796.3	796.2	795.9	795.7	795.5	795.0	794.4	793.7
127.5°	855.9	855.7	855.6	855.4	855.6	855.7	855.9	856.1	856.3	856.4	856.5
130°	895.4	895.4	895.4	895.4	895.4	895.4	895.4	895.4	895.3	895.1	894.8
132.5°	932.7	932.5	932.4	932.2	932.4	932.5	932.7	932.9	932.9	932.7	932.5
135°	986.1	986.5	987.0	987.4	987.0	986.5	986.1	985.7	985.2	984.7	984.3
137.5°	1035.1	1034.9	1034.7	1034.7	1034.7	1034.9	1035.1	1035.2	1035.0	1034.5	1034.1
140°	1066.8	1067.0	1067.2	1067.5	1067.2	1067.0	1066.8	1066.6	1066.2	1065.5	1064.8
142.5°	1094.6	1094.6	1094.7	1094.7	1094.7	1094.6	1094.6	1094.5	1094.2	1093.7	1093.3
145°	1135.1	1135.6	1136.1	1136.5	1136.1	1135.6	1135.1	1134.7	1134.4	1134.2	1133.9
147.5°	1170.4	1170.7	1170.9	1171.1	1170.9	1170.7	1170.4	1170.2	1170.0	1169.8	1169.7
150°	1192.8	1193.1	1193.3	1193.5	1193.3	1193.1	1192.8	1192.7	1192.5	1192.5	1192.5
152.5°	1213.1	1213.0	1212.9	1212.7	1212.9	1213.0	1213.1	1213.2	1213.1	1212.8	1212.5
155°	1240.5	1239.8	1239.2	1238.5	1239.2	1239.8	1240.5	1241.2	1241.1	1240.2	1239.3
157.5°	1263.6	1262.5	1261.3	1260.2	1261.3	1262.5	1263.6	1264.8	1264.8	1263.6	1262.5
160°	1278.6	1277.2	1275.9	1274.5	1275.9	1277.2	1278.6	1279.9	1279.9	1278.6	1277.2
162.5°	1290.3	1288.8	1287.3	1285.7	1287.3	1288.8	1290.3	1291.8	1291.9	1290.6	1289.3
165°	1307.6	1305.5	1303.6	1301.6	1303.6	1305.5	1307.6	1309.6	1309.7	1307.9	1306.1
167.5°	1320.1	1317.8	1315.6	1313.4	1315.6	1317.8	1320.1	1322.2	1322.4	1320.4	1318.5
170°	1327.2	1325.0	1322.8	1320.6	1322.8	1325.0	1327.2	1329.5	1329.7	1327.9	1326.1
172.5°	1331.8	1329.4	1327.0	1324.6	1327.0	1329.4	1331.8	1334.2	1334.5	1332.7	1330.9
175°	1337.6	1334.9	1332.2	1329.6	1332.2	1334.9	1337.6	1340.2	1340.6	1338.6	1336.6
177.5°	1339.2	1337.0	1334.9	1332.8	1334.9	1337.0	1339.2	1341.4	1341.7	1340.2	1338.9
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1586.3	1588.5	1597.3	1605.6	1615.5	1622.6	1627.5	1633.1	1644.6	1654.0	1662.8
5°	1486.3	1489.7	1507.5	1519.9	1541.2	1559.8	1574.3	1590.0	1608.6	1634.0	1657.4
7.5°	1398.1	1410.9	1430.4	1450.4	1472.2	1496.5	1517.7	1541.5	1573.6	1608.4	1644.5
10°	1348.1	1362.5	1383.1	1406.5	1427.1	1455.3	1481.4	1509.6	1546.0	1588.6	1631.3
12.5°	1298.0	1321.8	1337.5	1365.2	1387.5	1410.7	1438.6	1475.5	1518.0	1562.8	1614.2
15°	1235.3	1248.4	1278.6	1293.7	1325.3	1361.2	1388.6	1425.7	1467.0	1526.1	1583.8
17.5°	1163.0	1180.2	1204.3	1233.1	1269.4	1297.4	1331.5	1369.8	1421.8	1480.5	1552.8
20°	1115.7	1130.1	1159.7	1191.3	1229.9	1259.4	1295.8	1332.9	1386.6	1449.1	1524.7
22.5°	1073.3	1087.3	1118.4	1147.9	1185.3	1221.4	1259.5	1302.7	1354.1	1420.0	1497.2
25°	1007.8	1026.3	1053.9	1084.1	1119.8	1161.1	1202.3	1240.8	1295.8	1365.2	1447.8
27.5°	949.6	964.5	984.4	1018.7	1059.4	1099.2	1140.1	1188.6	1241.4	1314.7	1400.4
30°	912.2	926.0	945.9	977.5	1015.4	1058.0	1100.6	1147.3	1202.3	1275.2	1362.5
32.5°	882.5	892.9	910.7	939.0	973.5	1018.4	1060.4	1108.8	1166.6	1238.4	1323.4
35°	838.7	847.6	854.5	881.3	912.2	953.5	996.1	1047.7	1103.4	1171.4	1256.6
37.5°	795.7	798.7	808.7	826.3	856.3	894.2	933.8	984.6	1041.6	1110.8	1187.6
40°	769.2	770.6	776.8	793.3	819.4	855.1	893.6	943.8	998.2	1063.4	1139.8
42.5°	743.4	742.5	748.2	759.7	784.2	816.7	854.6	900.4	954.7	1015.0	1086.9
45°	702.6	702.6	701.2	710.8	730.7	762.3	794.0	838.0	883.4	942.5	1003.0
47.5°	660.0	656.1	657.3	662.3	679.1	705.1	736.9	772.9	813.0	863.0	916.1
50°	632.4	627.0	624.9	630.3	645.5	668.2	698.4	730.0	767.8	811.8	857.2
52.5°	602.2	596.7	593.0	596.8	610.9	631.9	659.4	687.2	721.1	756.9	796.2
55°	555.4	549.2	547.2	548.5	558.9	575.4	598.7	624.2	649.6	679.2	706.7
57.5°	509.4	499.2	497.3	496.6	503.8	518.8	538.4	560.4	578.9	596.8	626.1
60°	479.1	466.7	462.6	461.9	467.4	479.8	497.7	519.7	532.8	545.1	570.6
62.5°	446.7	434.9	425.8	426.8	431.7	443.5	459.2	475.2	483.8	497.3	514.4
65°	396.7	381.5	374.6	372.6	375.3	385.0	397.4	407.7	417.2	422.8	439.3
67.5°	346.6	334.0	323.8	321.3	320.0	326.7	336.8	343.0	349.9	354.7	364.5
70°	311.4	300.4	288.0	283.9	283.2	288.7	298.3	299.0	308.7	310.7	321.1
72.5°	276.7	263.0	254.5	250.4	247.5	252.4	258.7	260.5	265.8	269.5	274.8
75°	222.7	212.4	204.1	197.9	195.9	198.6	198.6	202.1	205.5	207.6	213.8
77.5°	175.3	163.5	153.7	150.2	147.7	145.9	147.4	149.5	147.8	151.4	152.7
80°	142.3	129.9	122.3	121.0	116.8	113.4	112.7	114.8	112.0	113.4	117.5
82.5°	109.9	101.9	93.8	92.4	87.1	85.4	84.7	83.4	83.4	83.2	84.0
85°	65.3	60.5	55.0	51.6	49.5	46.1	46.1	44.7	43.3	41.9	42.6
87.5°	31.1	29.7	26.6	24.6	23.2	20.6	20.1	18.0	17.0	15.9	14.9
90°	23.3	22.0	20.2	18.4	16.7	14.9	12.7	10.3	7.9	5.4	3.0
92.5°	22.6	21.2	19.5	17.7	15.8	14.1	13.2	13.0	12.9	12.7	12.6
95°	23.3	22.0	21.8	21.5	21.4	21.1	24.8	32.4	39.9	47.4	55.0
97.5°	26.5	26.4	51.2	76.0	100.8	125.6	135.7	131.0	126.3	121.6	116.8
100°	40.2	44.0	74.7	105.4	136.0	166.8	180.1	176.1	172.1	168.1	164.1
102.5°	171.3	212.1	216.1	220.1	224.1	228.1	228.6	225.7	222.7	219.8	216.9
105°	314.2	312.1	311.0	309.9	308.8	307.7	306.4	305.1	303.8	302.5	301.1
107.5°	390.1	389.2	387.6	386.2	384.6	383.1	382.0	381.3	380.7	380.0	379.4
110°	441.6	441.2	439.9	438.5	437.2	435.8	434.9	434.2	433.5	432.8	432.2



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	491.5	491.6	491.0	490.3	489.7	489.1	488.2	487.0	485.8	484.7	483.5
115°	564.7	564.2	564.5	564.7	564.9	565.2	564.9	564.2	563.6	562.9	562.2
117.5°	639.4	639.5	639.0	638.5	638.0	637.5	636.8	635.9	635.1	634.1	633.3
120°	684.8	684.3	684.5	684.8	685.0	685.2	684.8	684.0	683.1	682.2	681.3
122.5°	730.2	730.0	729.6	729.3	729.0	728.7	728.2	727.7	727.2	726.7	726.1
125°	793.0	792.4	792.8	793.2	793.7	794.1	793.9	793.0	792.1	791.3	790.3
127.5°	856.6	856.8	855.7	854.7	853.7	852.6	852.0	851.9	851.6	851.4	851.2
130°	894.6	894.4	893.7	893.0	892.4	891.7	891.3	891.0	890.9	890.6	890.4
132.5°	932.2	932.0	931.2	930.3	929.4	928.7	928.0	927.6	927.2	926.8	926.4
135°	983.9	983.4	982.6	981.6	980.8	979.9	979.6	979.7	980.0	980.2	980.4
137.5°	1033.5	1033.0	1032.1	1031.1	1030.1	1029.2	1028.6	1028.6	1028.5	1028.4	1028.3
140°	1064.1	1063.5	1063.0	1062.6	1062.1	1061.7	1061.3	1060.8	1060.3	1059.9	1059.5
142.5°	1092.8	1092.3	1092.0	1091.7	1091.5	1091.2	1090.7	1089.9	1089.1	1088.3	1087.4
145°	1133.8	1133.5	1133.5	1133.5	1133.5	1133.5	1133.2	1132.5	1131.9	1131.2	1130.5
147.5°	1169.5	1169.3	1169.5	1169.8	1170.0	1170.2	1169.7	1168.5	1167.2	1166.0	1164.7
150°	1192.5	1192.5	1192.7	1193.0	1193.2	1193.4	1193.1	1192.2	1191.3	1190.4	1189.6
152.5°	1212.1	1211.8	1212.1	1212.5	1213.0	1213.3	1213.1	1212.5	1211.8	1211.1	1210.3
155°	1238.5	1237.5	1238.2	1238.9	1239.6	1240.2	1240.4	1240.2	1240.0	1239.8	1239.6
157.5°	1261.3	1260.2	1260.9	1261.7	1262.4	1263.2	1263.6	1263.8	1263.9	1264.0	1264.1
160°	1275.9	1274.5	1274.8	1275.0	1275.2	1275.5	1275.9	1276.6	1277.2	1277.9	1278.6
162.5°	1287.9	1286.6	1286.8	1287.0	1287.2	1287.5	1288.0	1288.8	1289.7	1290.6	1291.3
165°	1304.3	1302.6	1302.6	1302.6	1302.6	1302.6	1303.1	1304.2	1305.4	1306.5	1307.6
167.5°	1316.6	1314.6	1314.7	1314.8	1315.0	1315.1	1315.8	1316.9	1318.1	1319.2	1320.3
170°	1324.4	1322.6	1322.3	1322.2	1321.9	1321.7	1322.2	1323.6	1324.9	1326.3	1327.6
172.5°	1329.1	1327.4	1327.1	1327.0	1326.7	1326.5	1327.1	1328.4	1329.7	1331.0	1332.4
175°	1334.6	1332.6	1332.4	1332.1	1331.9	1331.7	1332.2	1333.6	1334.9	1336.3	1337.6
177.5°	1337.4	1336.0	1335.7	1335.2	1334.9	1334.6	1335.0	1336.3	1337.5	1338.8	1340.0
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1670.4	1675.9	1683.1	1695.2	1699.6	1705.1	1712.8	1712.3	1714.4	1722.7	1740.3
5°	1676.6	1698.0	1718.6	1743.4	1769.4	1786.7	1810.0	1824.5	1838.9	1857.4	1889.0
7.5°	1679.1	1713.0	1750.8	1794.2	1832.8	1877.4	1912.2	1944.9	1974.4	2013.6	2051.3
10°	1675.2	1720.6	1769.4	1824.5	1882.8	1932.3	1977.0	2027.9	2071.2	2118.7	2161.3
12.5°	1668.1	1722.9	1788.1	1849.8	1918.0	1991.2	2046.9	2098.3	2155.9	2210.5	2276.2
15°	1651.9	1726.8	1803.1	1884.2	1975.7	2060.2	2140.7	2207.3	2269.3	2351.0	2437.0
17.5°	1631.3	1712.1	1808.4	1906.5	2002.1	2098.8	2198.3	2298.5	2376.6	2478.2	2545.5
20°	1612.1	1705.6	1804.5	1921.4	2016.9	2137.3	2236.2	2333.1	2440.4	2541.4	2621.8
22.5°	1585.1	1687.4	1792.4	1908.8	2034.5	2154.8	2269.3	2374.4	2481.7	2591.5	2689.0
25°	1550.8	1643.6	1768.1	1900.1	2025.2	2155.8	2287.1	2419.1	2534.5	2650.8	2741.5
27.5°	1492.5	1609.7	1725.6	1861.8	2000.9	2148.6	2289.1	2427.2	2548.2	2643.7	2699.9
30°	1462.8	1564.6	1690.4	1827.2	1977.7	2136.6	2282.9	2418.4	2531.2	2607.5	2630.1
32.5°	1418.8	1523.9	1646.9	1788.7	1948.0	2111.3	2263.7	2391.4	2485.4	2525.5	2498.1
35°	1353.6	1448.5	1572.9	1717.9	1883.5	2057.4	2208.0	2315.9	2364.0	2326.2	2232.1
37.5°	1275.2	1369.2	1494.2	1636.7	1808.1	1984.9	2121.0	2198.6	2182.7	2088.7	1948.4
40°	1220.2	1308.2	1427.1	1581.1	1748.2	1925.5	2045.1	2087.1	2043.1	1908.3	1759.1
42.5°	1159.2	1244.9	1364.4	1512.9	1689.9	1853.5	1957.7	1961.1	1887.4	1726.3	1576.6
45°	1066.2	1148.0	1260.8	1415.4	1579.1	1733.0	1801.7	1768.1	1631.9	1476.6	1326.0
47.5°	974.5	1045.4	1156.5	1303.4	1458.7	1588.4	1622.5	1561.9	1416.8	1266.0	1126.4
50°	907.4	978.9	1083.4	1223.7	1373.5	1485.6	1502.0	1421.6	1279.3	1127.4	1018.0
52.5°	843.1	914.0	1014.7	1144.4	1281.7	1382.7	1383.3	1290.2	1148.4	1013.0	911.4
55°	748.6	812.5	903.3	1019.4	1141.9	1220.9	1201.6	1105.4	982.3	864.8	776.1
57.5°	657.6	713.3	796.9	893.8	1001.6	1066.8	1034.8	942.2	832.3	732.6	665.5
60°	598.7	651.7	723.2	814.6	905.3	956.2	926.0	842.1	741.1	660.6	602.2
62.5°	541.6	586.3	655.0	734.3	818.5	856.1	829.1	746.4	659.1	586.3	539.0
65°	460.5	497.1	552.0	620.1	681.2	713.6	690.9	613.9	547.2	495.0	457.1
67.5°	385.0	413.5	455.0	509.6	561.6	579.1	558.4	504.9	448.3	406.6	379.9
70°	332.7	359.6	394.6	436.5	481.9	500.4	479.8	437.2	391.2	352.7	326.5
72.5°	287.1	307.8	337.4	373.2	408.7	427.3	413.3	372.3	333.4	304.8	282.5
75°	218.6	236.5	257.1	282.5	310.0	322.4	310.0	281.8	255.0	233.8	217.9
77.5°	158.9	168.6	184.5	203.5	220.7	230.1	219.5	200.4	184.0	169.4	161.5
80°	121.0	127.9	138.9	153.9	165.7	174.6	167.7	151.9	138.9	129.2	125.8
82.5°	88.0	92.6	99.8	111.1	118.9	123.5	120.5	109.0	103.7	95.1	91.7
85°	43.3	46.1	50.9	54.3	61.2	61.9	62.6	57.8	53.0	50.9	48.1
87.5°	15.9	17.0	19.1	21.3	23.8	24.8	24.6	25.0	23.1	22.8	20.9
90°	5.4	7.9	10.3	12.7	14.9	16.7	18.4	20.2	22.0	23.3	24.7
92.5°	12.7	12.9	13.0	13.2	14.1	15.8	17.7	19.5	21.2	22.6	23.8
95°	47.4	39.9	32.4	24.8	21.1	21.4	21.5	21.8	22.0	23.3	24.7
97.5°	121.6	126.3	131.0	135.7	125.6	100.8	76.0	51.2	26.4	26.5	26.7
100°	168.1	172.1	176.1	180.1	166.8	136.0	105.4	74.7	44.0	40.2	36.4
102.5°	219.8	222.7	225.7	228.6	228.1	224.1	220.1	216.1	212.1	171.3	130.5
105°	302.5	303.8	305.1	306.4	307.7	308.8	309.9	311.0	312.1	314.2	316.2
107.5°	380.0	380.7	381.3	382.0	383.1	384.6	386.2	387.6	389.2	390.1	391.2
110°	432.8	433.5	434.2	434.9	435.8	437.2	438.5	439.9	441.2	441.6	442.1



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.7	485.8	487.0	488.2	489.1	489.7	490.3	491.0	491.6	491.5	491.5
115°	562.9	563.6	564.2	564.9	565.2	564.9	564.7	564.5	564.2	564.7	565.2
117.5°	634.1	635.1	635.9	636.8	637.5	638.0	638.5	639.0	639.5	639.4	639.3
120°	682.2	683.1	684.0	684.8	685.2	685.0	684.8	684.5	684.3	684.8	685.2
122.5°	726.7	727.2	727.7	728.2	728.7	729.0	729.3	729.6	730.0	730.2	730.5
125°	791.3	792.1	793.0	793.9	794.1	793.7	793.2	792.8	792.4	793.0	793.7
127.5°	851.4	851.6	851.9	852.0	852.6	853.7	854.7	855.7	856.8	856.6	856.5
130°	890.6	890.9	891.0	891.3	891.7	892.4	893.0	893.7	894.4	894.6	894.8
132.5°	926.8	927.2	927.6	928.0	928.7	929.4	930.3	931.2	932.0	932.2	932.5
135°	980.2	980.0	979.7	979.6	979.9	980.8	981.6	982.6	983.4	983.9	984.3
137.5°	1028.4	1028.5	1028.6	1028.6	1029.2	1030.1	1031.1	1032.1	1033.0	1033.5	1034.1
140°	1059.9	1060.3	1060.8	1061.3	1061.7	1062.1	1062.6	1063.0	1063.5	1064.1	1064.8
142.5°	1088.3	1089.1	1089.9	1090.7	1091.2	1091.5	1091.7	1092.0	1092.3	1092.8	1093.3
145°	1131.2	1131.9	1132.5	1133.2	1133.5	1133.5	1133.5	1133.5	1133.5	1133.8	1133.9
147.5°	1166.0	1167.2	1168.5	1169.7	1170.2	1170.0	1169.8	1169.5	1169.3	1169.5	1169.7
150°	1190.4	1191.3	1192.2	1193.1	1193.4	1193.2	1193.0	1192.7	1192.5	1192.5	1192.5
152.5°	1211.1	1211.8	1212.5	1213.1	1213.3	1213.0	1212.5	1212.1	1211.8	1212.1	1212.5
155°	1239.8	1240.0	1240.2	1240.4	1240.2	1239.6	1238.9	1238.2	1237.5	1238.5	1239.3
157.5°	1264.0	1263.9	1263.8	1263.6	1263.2	1262.4	1261.7	1260.9	1260.2	1261.3	1262.5
160°	1277.9	1277.2	1276.6	1275.9	1275.5	1275.2	1275.0	1274.8	1274.5	1275.9	1277.2
162.5°	1290.6	1289.7	1288.8	1288.0	1287.5	1287.2	1287.0	1286.8	1286.6	1287.9	1289.3
165°	1306.5	1305.4	1304.2	1303.1	1302.6	1302.6	1302.6	1302.6	1302.6	1304.3	1306.1
167.5°	1319.2	1318.1	1316.9	1315.8	1315.1	1315.0	1314.8	1314.7	1314.6	1316.6	1318.5
170°	1326.3	1324.9	1323.6	1322.2	1321.7	1321.9	1322.2	1322.3	1322.6	1324.4	1326.1
172.5°	1331.0	1329.7	1328.4	1327.1	1326.5	1326.7	1327.0	1327.1	1327.4	1329.1	1330.9
175°	1336.3	1334.9	1333.6	1332.2	1331.7	1331.9	1332.1	1332.4	1332.6	1334.6	1336.6
177.5°	1338.8	1337.5	1336.3	1335.0	1334.6	1334.9	1335.2	1335.7	1336.0	1337.4	1338.9
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1749.1	1750.2	1755.1	1759.0	1760.1	1765.6	1766.2
5°	1902.8	1914.5	1937.2	1939.2	1942.7	1960.6	1946.8
7.5°	2082.9	2112.6	2132.4	2149.9	2156.2	2164.0	2162.4
10°	2198.4	2242.4	2264.4	2299.5	2300.9	2309.8	2304.3
12.5°	2314.5	2365.6	2405.7	2412.2	2441.6	2446.2	2453.8
15°	2478.9	2533.1	2588.9	2608.8	2649.4	2659.0	2674.1
17.5°	2633.5	2689.0	2728.0	2779.6	2796.2	2818.5	2803.3
20°	2718.1	2778.6	2828.1	2868.7	2885.8	2898.2	2896.8
22.5°	2769.2	2830.3	2870.4	2901.1	2917.2	2922.4	2922.1
25°	2801.3	2836.3	2848.7	2860.4	2842.5	2836.3	2839.1
27.5°	2712.2	2703.1	2670.8	2628.5	2584.5	2549.5	2530.6
30°	2589.5	2535.9	2487.2	2401.8	2357.9	2331.8	2308.4
32.5°	2415.8	2330.8	2236.9	2158.8	2108.8	2070.0	2064.2
35°	2118.0	1990.1	1875.3	1779.8	1730.3	1688.3	1678.7
37.5°	1800.7	1667.8	1564.4	1480.3	1427.1	1397.6	1369.9
40°	1590.0	1475.9	1374.2	1302.7	1262.1	1240.8	1223.7
42.5°	1427.8	1323.6	1222.4	1167.9	1131.3	1118.2	1108.1
45°	1203.7	1106.7	1036.6	995.4	974.0	952.1	941.8
47.5°	1024.2	945.4	899.1	864.1	841.3	828.2	821.7
50°	922.6	857.9	816.7	789.9	769.2	758.9	753.5
52.5°	832.3	779.3	744.6	723.3	709.3	701.7	699.6
55°	717.0	676.4	654.4	635.8	625.6	618.7	616.0
57.5°	623.2	592.0	574.1	558.9	554.9	549.1	547.2
60°	561.6	537.6	522.5	512.1	508.7	501.8	503.2
62.5°	507.2	487.5	474.6	468.7	464.2	458.4	460.3
65°	429.0	414.5	407.7	402.2	396.7	393.2	396.0
67.5°	359.9	350.1	340.7	337.5	334.8	334.2	331.3
70°	314.9	306.6	298.3	296.3	296.3	293.5	292.8
72.5°	271.4	265.4	259.8	258.3	256.1	257.3	254.3
75°	209.7	204.8	202.8	200.7	200.0	200.0	197.9
77.5°	155.0	151.4	148.1	148.1	145.6	144.6	144.4
80°	117.5	116.1	113.4	113.4	112.0	112.7	111.3
82.5°	88.4	86.4	85.9	84.8	82.9	83.0	81.7
85°	47.4	45.4	44.7	42.6	41.2	42.6	41.2
87.5°	21.7	21.4	21.0	20.1	19.5	19.6	18.1
90°	26.0	27.4	28.2	28.7	29.1	29.5	30.0
92.5°	25.2	26.5	27.3	27.4	27.5	27.6	27.6
95°	26.0	27.4	28.2	28.3	28.6	28.8	29.0
97.5°	26.8	26.9	27.1	27.4	27.6	27.8	28.0
100°	32.7	28.9	27.1	27.4	27.6	27.8	28.0
102.5°	89.8	49.0	28.7	28.7	28.8	28.8	28.8
105°	318.1	320.1	317.1	309.1	301.1	293.2	285.2
107.5°	392.1	393.0	394.0	394.9	395.7	396.5	397.4
110°	442.6	443.0	443.5	444.2	444.9	445.6	446.2



TEST NUMBER: P332706-935

CATALOG NUMBER: SA4XXDIP-C1195D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	491.4	491.3	491.6	492.5	493.4	494.2	495.0
115°	565.6	566.0	566.3	566.3	566.3	566.3	566.3
117.5°	639.2	639.1	639.0	638.9	638.9	638.8	638.7
120°	685.6	686.0	686.0	685.6	685.2	684.8	684.3
122.5°	730.7	731.0	730.9	730.5	730.0	729.5	729.1
125°	794.4	795.0	795.5	795.7	795.9	796.2	796.3
127.5°	856.4	856.3	856.1	855.9	855.7	855.6	855.4
130°	895.1	895.3	895.4	895.4	895.4	895.4	895.4
132.5°	932.7	932.9	932.9	932.7	932.5	932.4	932.2
135°	984.7	985.2	985.7	986.1	986.5	987.0	987.4
137.5°	1034.5	1035.0	1035.2	1035.1	1034.9	1034.7	1034.7
140°	1065.5	1066.2	1066.6	1066.8	1067.0	1067.2	1067.5
142.5°	1093.7	1094.2	1094.5	1094.6	1094.6	1094.7	1094.7
145°	1134.2	1134.4	1134.7	1135.1	1135.6	1136.1	1136.5
147.5°	1169.8	1170.0	1170.2	1170.4	1170.7	1170.9	1171.1
150°	1192.5	1192.5	1192.7	1192.8	1193.1	1193.3	1193.5
152.5°	1212.8	1213.1	1213.2	1213.1	1213.0	1212.9	1212.7
155°	1240.2	1241.1	1241.2	1240.5	1239.8	1239.2	1238.5
157.5°	1263.6	1264.8	1264.8	1263.6	1262.5	1261.3	1260.2
160°	1278.6	1279.9	1279.9	1278.6	1277.2	1275.9	1274.5
162.5°	1290.6	1291.9	1291.8	1290.3	1288.8	1287.3	1285.7
165°	1307.9	1309.7	1309.6	1307.6	1305.5	1303.6	1301.6
167.5°	1320.4	1322.4	1322.2	1320.1	1317.8	1315.6	1313.4
170°	1327.9	1329.7	1329.5	1327.2	1325.0	1322.8	1320.6
172.5°	1332.7	1334.5	1334.2	1331.8	1329.4	1327.0	1324.6
175°	1338.6	1340.6	1340.2	1337.6	1334.9	1332.2	1329.6
177.5°	1340.2	1341.7	1341.4	1339.2	1337.0	1334.9	1332.8
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6

(END OF REPORT)