

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332681-935

Luminaire Tested: **SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332681-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6398.1 lumens  
Efficiency: N/A  
Efficacy: 116.1 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332681-935  
CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	72	72	72	72	
1	103	99	95	91	97	94	90	87	84	82	79	76	74	72	68	66	65	61	61	61	61	
2	94	87	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55	52	52	52	52	
3	86	76	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44	44	44	44	
4	79	68	60	54	75	65	57	52	59	53	48	53	48	45	48	44	41	38	38	38	38	
5	73	61	53	46	69	58	50	45	53	47	42	48	43	39	43	39	36	33	33	33	33	
6	67	55	46	41	63	52	45	39	48	41	37	43	38	34	39	35	32	29	29	29	29	
7	62	50	42	36	59	48	40	35	43	37	33	40	34	30	36	32	28	26	26	26	26	
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	26	23	23	23	23	
9	54	41	34	29	51	40	33	28	37	31	26	34	28	25	31	26	23	21	21	21	21	
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	29	24	21	19	19	19	19	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13397	13397	13397	13397
5°	15776	13431	11854	13431
10°	18889	13373	10673	13373
15°	22349	13237	9802	13237
20°	24887	13099	9024	13099
25°	25289	12896	8487	12896
30°	21519	12701	8318	12701
35°	16544	12384	8319	12384
40°	12896	12012	8476	12012
45°	10752	11451	8617	11451
50°	9463	10766	8911	10766
55°	8670	9947	9270	9947
60°	8125	9213	9700	9213
65°	7564	8392	10059	8392
70°	6911	7579	10286	7579
75°	6173	6669	10162	6669
80°	5174	5463	9842	5463
85°	3816	3946	9429	3946



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.7	2.5
10°-20°	498.3	7.8
20°-30°	790.2	12.4
30°-40°	879.4	13.7
40°-50°	800.5	12.5
50°-60°	654.1	10.2
60°-70°	467.0	7.3
70°-80°	257.1	4.0
80°-90°	71.6	1.1
90°-100°	180.6	2.8
100°-110°	375.8	5.9
110°-120°	336.6	5.3
120°-130°	283.1	4.4
130°-140°	236.1	3.7
140°-150°	180.4	2.8
150°-160°	126.8	2.0
160°-170°	74.6	1.2
170°-180°	24.3	0.4
0°-30°	1450.2	22.7
0°-40°	2329.6	36.4
0°-60°	3784.2	59.1
0°-90°	4579.9	71.6
90°-120°	893.0	14.0
90°-150°	1592.6	24.9
90°-180°	1818.0	28.4
0°-180°	6398.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1660	1660	1660	1660	1660	
5°	1947	1657	1463	1657	1947	198
15°	2674	1584	1173	1584	2674	756
25°	2839	1448	953	1448	2839	1252
35°	1679	1257	844	1257	1679	1066
45°	942	1003	755	1003	942	742
55°	616	707	659	707	616	556
65°	396	439	527	439	396	392
75°	198	214	326	214	198	210
85°	41	43	102	43	41	50
90°	10	0	10	0	10	10
95°	120	16	120	16	120	186
105°	691	57	691	57	691	683
115°	664	101	664	101	664	659
125°	529	141	529	141	529	481
135°	474	168	474	168	474	365
145°	386	193	386	193	386	245
155°	324	220	324	220	324	151
165°	282	239	282	239	282	81
175°	254	250	254	250	254	25
180°	250	250	250	250	250	



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1766.2	1765.6	1760.1	1759.0	1755.1	1750.2	1749.1	1740.3	1722.7	1714.4	1712.3
5°	1946.8	1960.6	1942.7	1939.2	1937.2	1914.5	1902.8	1889.0	1857.4	1838.9	1824.5
7.5°	2162.4	2164.0	2156.2	2149.9	2132.4	2112.6	2082.9	2051.3	2013.6	1974.4	1944.9
10°	2304.3	2309.8	2300.9	2299.5	2264.4	2242.4	2198.4	2161.3	2118.7	2071.2	2027.9
12.5°	2453.8	2446.2	2441.6	2412.2	2405.7	2365.6	2314.5	2276.2	2210.5	2155.9	2098.3
15°	2674.1	2659.0	2649.4	2608.8	2588.9	2533.1	2478.9	2437.0	2351.0	2269.3	2207.3
17.5°	2803.3	2818.5	2796.2	2779.6	2728.0	2689.0	2633.5	2545.5	2478.2	2376.6	2298.5
20°	2896.8	2898.2	2885.8	2868.7	2828.1	2778.6	2718.1	2621.8	2541.4	2440.4	2333.1
22.5°	2922.1	2922.4	2917.2	2901.1	2870.4	2830.3	2769.2	2689.0	2591.5	2481.7	2374.4
25°	2839.1	2836.3	2842.5	2860.4	2848.7	2836.3	2801.3	2741.5	2650.8	2534.5	2419.1
27.5°	2530.6	2549.5	2584.5	2628.5	2670.8	2703.1	2712.2	2699.9	2643.7	2548.2	2427.2
30°	2308.4	2331.8	2357.9	2401.8	2487.2	2535.9	2589.5	2630.1	2607.5	2531.2	2418.4
32.5°	2064.2	2070.0	2108.8	2158.8	2236.9	2330.8	2415.8	2498.1	2525.5	2485.4	2391.4
35°	1678.7	1688.3	1730.3	1779.8	1875.3	1990.1	2118.0	2232.1	2326.2	2364.0	2315.9
37.5°	1369.9	1397.6	1427.1	1480.3	1564.4	1667.8	1800.7	1948.4	2088.7	2182.7	2198.6
40°	1223.7	1240.8	1262.1	1302.7	1374.2	1475.9	1590.0	1759.1	1908.3	2043.1	2087.1
42.5°	1108.1	1118.2	1131.3	1167.9	1222.4	1323.6	1427.8	1576.6	1726.3	1887.4	1961.1
45°	941.8	952.1	974.0	995.4	1036.6	1106.7	1203.7	1326.0	1476.6	1631.9	1768.1
47.5°	821.7	828.2	841.3	864.1	899.1	945.4	1024.2	1126.4	1266.0	1416.8	1561.9
50°	753.5	758.9	769.2	789.9	816.7	857.9	922.6	1018.0	1127.4	1279.3	1421.6
52.5°	699.6	701.7	709.3	723.3	744.6	779.3	832.3	911.4	1013.0	1148.4	1290.2
55°	616.0	618.7	625.6	635.8	654.4	676.4	717.0	776.1	864.8	982.3	1105.4
57.5°	547.2	549.1	554.9	558.9	574.1	592.0	623.2	665.5	732.6	832.3	942.2
60°	503.2	501.8	508.7	512.1	522.5	537.6	561.6	602.2	660.6	741.1	842.1
62.5°	460.3	458.4	464.2	468.7	474.6	487.5	507.2	539.0	586.3	659.1	746.4
65°	396.0	393.2	396.7	402.2	407.7	414.5	429.0	457.1	495.0	547.2	613.9
67.5°	331.3	334.2	334.8	337.5	340.7	350.1	359.9	379.9	406.6	448.3	504.9
70°	292.8	293.5	296.3	296.3	298.3	306.6	314.9	326.5	352.7	391.2	437.2
72.5°	254.3	257.3	256.1	258.3	259.8	265.4	271.4	282.5	304.8	333.4	372.3
75°	197.9	200.0	200.0	200.7	202.8	204.8	209.7	217.9	233.8	255.0	281.8
77.5°	144.4	144.6	145.6	148.1	148.1	151.4	155.0	161.5	169.4	184.0	200.4
80°	111.3	112.7	112.0	113.4	113.4	116.1	117.5	125.8	129.2	138.9	151.9
82.5°	81.7	83.0	82.9	84.8	85.9	86.4	88.4	91.7	95.1	103.7	109.0
85°	41.2	42.6	41.2	42.6	44.7	45.4	47.4	48.1	50.9	53.0	57.8
87.5°	14.1	15.8	15.9	16.4	17.4	17.9	18.3	17.7	19.8	20.5	22.5
90°	10.3	10.3	10.8	10.3	9.8	9.8	9.3	8.9	8.4	8.9	7.8
92.5°	37.8	37.8	39.5	42.1	48.0	57.8	72.6	96.4	129.8	155.8	136.4
95°	119.9	126.2	135.1	150.3	174.4	222.0	287.8	363.9	411.6	400.3	302.0
97.5°	320.3	330.5	345.3	374.9	410.1	461.4	509.5	537.7	517.1	421.6	282.8
100°	450.4	454.3	469.1	499.0	541.7	578.1	602.2	592.4	520.6	394.9	256.4
102.5°	563.5	566.7	582.2	603.9	630.2	645.3	638.3	589.6	491.1	361.5	238.7
105°	691.0	694.0	700.9	704.8	703.9	683.7	635.1	550.1	437.6	322.2	223.5
107.5°	738.4	737.1	732.2	721.0	696.7	653.0	584.4	494.0	394.4	300.2	220.8
110°	739.2	734.8	725.9	705.3	670.5	616.4	545.2	460.2	372.8	292.7	221.5



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	716.0	708.9	696.5	671.5	631.9	577.9	510.6	435.5	360.6	289.2	223.9
115°	663.6	659.6	643.9	614.4	575.7	528.5	471.1	410.6	349.2	287.3	228.4
117.5°	610.4	607.3	591.4	566.7	533.6	493.6	448.4	398.4	344.1	286.8	233.2
120°	580.6	575.1	562.4	540.8	512.7	477.9	438.6	393.0	341.4	286.8	236.8
122.5°	557.0	551.6	540.8	522.3	498.6	468.0	432.3	388.2	338.2	286.5	240.3
125°	529.4	526.5	517.2	502.9	483.3	456.2	422.4	380.1	333.0	285.9	245.6
127.5°	513.3	510.4	502.6	489.9	470.1	444.5	410.7	370.3	326.1	284.7	249.8
130°	503.9	501.0	493.1	480.9	460.7	434.6	401.3	362.5	321.7	284.4	253.0
132.5°	493.4	490.3	482.9	469.1	449.3	423.3	390.6	354.2	317.8	284.0	255.7
135°	473.5	470.5	462.7	448.9	429.3	404.7	374.8	342.9	311.9	283.4	259.8
137.5°	448.9	445.4	438.9	425.3	407.0	384.8	359.6	332.5	306.8	283.3	262.3
140°	431.3	427.3	420.4	409.7	392.4	371.8	349.7	326.6	304.0	282.9	264.2
142.5°	412.3	409.7	403.6	393.5	378.3	360.4	341.5	321.2	301.7	282.9	265.8
145°	386.5	384.1	379.2	370.8	358.5	344.8	330.0	313.3	297.6	281.9	266.7
147.5°	363.7	362.7	359.0	351.9	342.9	332.0	320.2	306.9	294.0	280.2	267.2
150°	350.7	350.2	347.2	340.9	333.0	324.2	314.4	303.1	291.3	279.0	267.2
152.5°	338.9	338.4	336.7	331.4	324.8	317.5	308.4	298.7	288.1	277.0	266.4
155°	323.6	323.6	322.2	318.3	313.3	307.5	300.1	292.2	283.4	274.1	265.2
157.5°	310.3	310.3	309.4	306.5	302.7	298.0	291.9	285.2	278.6	271.0	264.0
160°	302.0	302.0	301.6	298.6	295.7	291.7	286.4	280.9	275.1	268.6	262.8
162.5°	294.2	294.6	294.1	291.2	289.0	285.4	281.2	276.6	271.9	266.3	261.6
165°	282.4	282.9	283.4	281.5	279.5	277.0	273.5	270.6	266.7	262.8	259.3
167.5°	273.1	273.5	273.5	272.3	271.3	269.8	267.1	264.8	262.0	259.2	257.0
170°	267.2	267.2	267.7	267.2	266.2	264.8	262.8	261.3	258.8	256.8	255.4
172.5°	261.3	262.1	262.6	262.1	261.5	260.5	259.2	258.1	256.1	254.5	253.8
175°	254.4	255.4	256.4	255.4	255.4	255.4	254.4	253.9	253.0	251.9	251.9
177.5°	250.4	251.2	251.9	251.6	251.9	251.6	251.6	251.2	250.8	250.4	250.4
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1712.8	1705.1	1699.6	1695.2	1683.1	1675.9	1670.4	1662.8	1654.0	1644.6	1633.1
5°	1810.0	1786.7	1769.4	1743.4	1718.6	1698.0	1676.6	1657.4	1634.0	1608.6	1590.0
7.5°	1912.2	1877.4	1832.8	1794.2	1750.8	1713.0	1679.1	1644.5	1608.4	1573.6	1541.5
10°	1977.0	1932.3	1882.8	1824.5	1769.4	1720.6	1675.2	1631.3	1588.6	1546.0	1509.6
12.5°	2046.9	1991.2	1918.0	1849.8	1788.1	1722.9	1668.1	1614.2	1562.8	1518.0	1475.5
15°	2140.7	2060.2	1975.7	1884.2	1803.1	1726.8	1651.9	1583.8	1526.1	1467.0	1425.7
17.5°	2198.3	2098.8	2002.1	1906.5	1808.4	1712.1	1631.3	1552.8	1480.5	1421.8	1369.8
20°	2236.2	2137.3	2016.9	1921.4	1804.5	1705.6	1612.1	1524.7	1449.1	1386.6	1332.9
22.5°	2269.3	2154.8	2034.5	1908.8	1792.4	1687.4	1585.1	1497.2	1420.0	1354.1	1302.7
25°	2287.1	2155.8	2025.2	1900.1	1768.1	1643.6	1550.8	1447.8	1365.2	1295.8	1240.8
27.5°	2289.1	2148.6	2000.9	1861.8	1725.6	1609.7	1492.5	1400.4	1314.7	1241.4	1188.6
30°	2282.9	2136.6	1977.7	1827.2	1690.4	1564.6	1462.8	1362.5	1275.2	1202.3	1147.3
32.5°	2263.7	2111.3	1948.0	1788.7	1646.9	1523.9	1418.8	1323.4	1238.4	1166.6	1108.8
35°	2208.0	2057.4	1883.5	1717.9	1572.9	1448.5	1353.6	1256.6	1171.4	1103.4	1047.7
37.5°	2121.0	1984.9	1808.1	1636.7	1494.2	1369.2	1275.2	1187.6	1110.8	1041.6	984.6
40°	2045.1	1925.5	1748.2	1581.1	1427.1	1308.2	1220.2	1139.8	1063.4	998.2	943.8
42.5°	1957.7	1853.5	1689.9	1512.9	1364.4	1244.9	1159.2	1086.9	1015.0	954.7	900.4
45°	1801.7	1733.0	1579.1	1415.4	1260.8	1148.0	1066.2	1003.0	942.5	883.4	838.0
47.5°	1622.5	1588.4	1458.7	1303.4	1156.5	1045.4	974.5	916.1	863.0	813.0	772.9
50°	1502.0	1485.6	1373.5	1223.7	1083.4	978.9	907.4	857.2	811.8	767.8	730.0
52.5°	1383.3	1382.7	1281.7	1144.4	1014.7	914.0	843.1	796.2	756.9	721.1	687.2
55°	1201.6	1220.9	1141.9	1019.4	903.3	812.5	748.6	706.7	679.2	649.6	624.2
57.5°	1034.8	1066.8	1001.6	893.8	796.9	713.3	657.6	626.1	596.8	578.9	560.4
60°	926.0	956.2	905.3	814.6	723.2	651.7	598.7	570.6	545.1	532.8	519.7
62.5°	829.1	856.1	818.5	734.3	655.0	586.3	541.6	514.4	497.3	483.8	475.2
65°	690.9	713.6	681.2	620.1	552.0	497.1	460.5	439.3	422.8	417.2	407.7
67.5°	558.4	579.1	561.6	509.6	455.0	413.5	385.0	364.5	354.7	349.9	343.0
70°	479.8	500.4	481.9	436.5	394.6	359.6	332.7	321.1	310.7	308.7	299.0
72.5°	413.3	427.3	408.7	373.2	337.4	307.8	287.1	274.8	269.5	265.8	260.5
75°	310.0	322.4	310.0	282.5	257.1	236.5	218.6	213.8	207.6	205.5	202.1
77.5°	219.5	230.1	220.7	203.5	184.5	168.6	158.9	152.7	151.4	147.8	149.5
80°	167.7	174.6	165.7	153.9	138.9	127.9	121.0	117.5	113.4	112.0	114.8
82.5°	120.5	123.5	118.9	111.1	99.8	92.6	88.0	84.0	83.2	83.4	83.4
85°	62.6	61.9	61.2	54.3	50.9	46.1	43.3	42.6	41.9	43.3	44.7
87.5°	22.3	22.8	21.7	19.5	17.7	16.0	15.2	14.4	15.2	16.0	16.6
90°	6.9	6.9	4.0	4.0	3.4	2.9	1.5	0.5	1.5	2.9	3.4
92.5°	99.2	61.1	36.2	25.9	18.8	12.7	8.2	5.6	8.2	12.7	18.8
95°	184.7	104.1	61.4	40.7	29.0	22.6	17.7	16.2	17.7	22.6	29.0
97.5°	166.0	99.5	66.6	49.3	39.2	33.3	29.1	29.1	29.1	33.3	39.2
100°	156.2	100.7	71.7	56.0	46.7	40.7	37.4	37.4	37.4	40.7	46.7
102.5°	153.4	104.6	78.4	63.5	54.5	49.0	46.0	45.2	46.0	49.0	54.5
105°	154.7	113.9	90.4	76.1	67.3	61.4	59.0	57.4	59.0	61.4	67.3
107.5°	162.0	124.8	103.2	89.2	80.8	74.5	72.0	71.0	72.0	74.5	80.8
110°	167.5	133.1	111.5	98.2	89.4	83.5	81.0	80.1	81.0	83.5	89.4





TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	173.4	140.9	120.1	106.9	98.1	92.6	89.7	88.7	89.7	92.6	98.1
115°	182.7	153.3	133.6	120.4	111.0	106.1	102.6	101.2	102.6	106.1	111.0
117.5°	192.3	165.1	146.5	132.7	124.0	118.6	115.5	114.2	115.5	118.6	124.0
120°	198.9	173.4	154.7	140.9	132.6	127.2	123.8	122.8	123.8	127.2	132.6
122.5°	205.2	181.2	162.6	149.2	140.1	135.1	131.6	130.6	131.6	135.1	140.1
125°	214.6	192.0	174.4	160.6	151.3	145.9	142.9	140.9	142.9	145.9	151.3
127.5°	222.8	202.1	184.9	171.1	161.4	155.2	151.7	150.1	151.7	155.2	161.4
130°	227.9	208.7	192.0	177.8	168.5	161.1	157.1	155.2	157.1	161.1	168.5
132.5°	233.0	214.2	197.5	184.1	174.0	167.0	161.9	160.3	161.9	167.0	174.0
135°	239.7	222.0	205.8	193.0	182.7	174.4	169.4	167.5	169.4	174.4	182.7
137.5°	244.4	227.9	212.8	200.6	189.9	181.9	176.5	174.7	176.5	181.9	189.9
140°	247.5	231.9	217.1	205.3	195.0	186.7	181.2	179.8	181.2	186.7	195.0
142.5°	249.9	235.4	221.0	209.7	199.7	191.7	186.8	185.3	186.8	191.7	199.7
145°	252.4	239.2	226.4	215.6	206.3	199.4	194.5	193.0	194.5	199.4	206.3
147.5°	254.7	243.1	231.2	221.4	213.6	206.6	202.2	201.7	202.2	206.6	213.6
150°	255.9	245.1	234.3	225.0	217.6	211.7	207.8	207.2	207.8	211.7	217.6
152.5°	256.7	246.7	237.0	228.5	221.9	216.4	212.5	212.4	212.5	216.4	221.9
155°	257.4	249.0	240.6	233.3	227.9	223.0	220.1	219.6	220.1	223.0	227.9
157.5°	257.4	250.7	243.6	237.8	233.1	229.3	226.5	226.5	226.5	229.3	233.1
160°	257.4	251.5	245.6	240.1	236.3	232.8	230.8	230.8	230.8	232.8	236.3
162.5°	257.4	252.3	246.8	242.5	239.0	235.9	234.4	234.8	234.4	235.9	239.0
165°	256.4	252.4	248.1	245.1	242.6	240.1	239.2	239.2	239.2	240.1	242.6
167.5°	255.2	252.4	249.1	246.8	245.5	243.6	243.1	243.6	243.1	243.6	245.5
170°	254.4	251.9	249.5	248.1	247.0	245.6	245.1	245.6	245.1	245.6	247.0
172.5°	253.7	251.6	249.9	248.8	248.2	247.1	247.0	247.5	247.0	247.1	248.2
175°	252.4	251.0	250.0	250.0	249.5	249.0	249.0	249.5	249.0	249.0	249.5
177.5°	251.2	250.4	250.0	250.0	250.0	249.6	250.0	250.4	250.0	249.6	250.0
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1627.5	1622.6	1615.5	1605.6	1597.3	1588.5	1586.3	1583.0	1589.6	1584.2	1582.4
5°	1574.3	1559.8	1541.2	1519.9	1507.5	1489.7	1486.3	1479.4	1472.5	1471.8	1464.9
7.5°	1517.7	1496.5	1472.2	1450.4	1430.4	1410.9	1398.1	1395.3	1385.2	1379.2	1372.3
10°	1481.4	1455.3	1427.1	1406.5	1383.1	1362.5	1348.1	1339.8	1332.9	1325.3	1318.5
12.5°	1438.6	1410.7	1387.5	1365.2	1337.5	1321.8	1298.0	1283.8	1282.4	1282.5	1264.6
15°	1388.6	1361.2	1325.3	1293.7	1278.6	1248.4	1235.3	1218.8	1208.5	1198.2	1190.0
17.5°	1331.5	1297.4	1269.4	1233.1	1204.3	1180.2	1163.0	1153.1	1137.6	1123.0	1112.4
20°	1295.8	1259.4	1229.9	1191.3	1159.7	1130.1	1115.7	1102.0	1090.3	1077.9	1066.2
22.5°	1259.5	1221.4	1185.3	1147.9	1118.4	1087.3	1073.3	1054.6	1043.5	1036.6	1024.9
25°	1202.3	1161.1	1119.8	1084.1	1053.9	1026.3	1007.8	993.3	980.9	975.4	967.9
27.5°	1140.1	1099.2	1059.4	1018.7	984.4	964.5	949.6	938.7	931.6	924.3	920.9
30°	1100.6	1058.0	1015.4	977.5	945.9	926.0	912.2	904.7	899.1	895.7	892.3
32.5°	1060.4	1018.4	973.5	939.0	910.7	892.9	882.5	874.9	872.2	871.0	869.8
35°	996.1	953.5	912.2	881.3	854.5	847.6	838.7	834.6	833.2	838.0	840.1
37.5°	933.8	894.2	856.3	826.3	808.7	798.7	795.7	795.7	800.7	804.9	809.9
40°	893.6	855.1	819.4	793.3	776.8	770.6	769.2	772.7	778.2	783.0	788.5
42.5°	854.6	816.7	784.2	759.7	748.2	742.5	743.4	746.8	754.5	760.4	768.7
45°	794.0	762.3	730.7	710.8	701.2	702.6	702.6	708.8	716.3	725.2	734.2
47.5°	736.9	705.1	679.1	662.3	657.3	656.1	660.0	668.0	678.9	689.9	702.4
50°	698.4	668.2	645.5	630.3	624.9	627.0	632.4	640.0	653.1	666.8	679.8
52.5°	659.4	631.9	610.9	596.8	593.0	596.7	602.2	614.2	625.6	640.4	656.3
55°	598.7	575.4	558.9	548.5	547.2	549.2	555.4	568.5	585.0	603.6	618.7
57.5°	538.4	518.8	503.8	496.6	497.3	499.2	509.4	525.0	542.5	562.3	581.9
60°	497.7	479.8	467.4	461.9	462.6	466.7	479.1	493.6	515.6	534.9	555.4
62.5°	459.2	443.5	431.7	426.8	425.8	434.9	446.7	461.7	483.7	505.1	527.4
65°	397.4	385.0	375.3	372.6	374.6	381.5	396.7	416.6	435.1	457.8	481.2
67.5°	336.8	326.7	320.0	321.3	323.8	334.0	346.6	363.8	384.9	408.4	431.4
70°	298.3	288.7	283.2	283.9	288.0	300.4	311.4	328.6	351.3	375.3	394.6
72.5°	258.7	252.4	247.5	250.4	254.5	263.0	276.7	293.9	313.9	336.3	356.6
75°	198.6	198.6	195.9	197.9	204.1	212.4	222.7	240.6	260.5	278.4	294.9
77.5°	147.4	145.9	147.7	150.2	153.7	163.5	175.3	188.0	203.1	220.9	234.5
80°	112.7	113.4	116.8	121.0	122.3	129.9	142.3	153.9	165.7	180.8	193.9
82.5°	84.7	85.4	87.1	92.4	93.8	101.9	109.9	121.6	132.2	142.3	153.2
85°	46.1	46.1	49.5	51.6	55.0	60.5	65.3	72.2	81.8	88.7	99.0
87.5°	18.4	18.4	21.2	22.3	24.1	27.0	28.1	34.2	36.5	39.3	44.3
90°	4.0	4.0	6.9	6.9	7.8	8.9	8.4	8.9	9.3	9.8	9.8
92.5°	25.9	36.2	61.1	99.2	136.4	155.8	129.8	96.4	72.6	57.8	48.0
95°	40.7	61.4	104.1	184.7	302.0	400.3	411.6	363.9	287.8	222.0	174.4
97.5°	49.3	66.6	99.5	166.0	282.8	421.6	517.1	537.7	509.5	461.4	410.1
100°	56.0	71.7	100.7	156.2	256.4	394.9	520.6	592.4	602.2	578.1	541.7
102.5°	63.5	78.4	104.6	153.4	238.7	361.5	491.1	589.6	638.3	645.3	630.2
105°	76.1	90.4	113.9	154.7	223.5	322.2	437.6	550.1	635.1	683.7	703.9
107.5°	89.2	103.2	124.8	162.0	220.8	300.2	394.4	494.0	584.4	653.0	696.7
110°	98.2	111.5	133.1	167.5	221.5	292.7	372.8	460.2	545.2	616.4	670.5



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	106.9	120.1	140.9	173.4	223.9	289.2	360.6	435.5	510.6	577.9	631.9
115°	120.4	133.6	153.3	182.7	228.4	287.3	349.2	410.6	471.1	528.5	575.7
117.5°	132.7	146.5	165.1	192.3	233.2	286.8	344.1	398.4	448.4	493.6	533.6
120°	140.9	154.7	173.4	198.9	236.8	286.8	341.4	393.0	438.6	477.9	512.7
122.5°	149.2	162.6	181.2	205.2	240.3	286.5	338.2	388.2	432.3	468.0	498.6
125°	160.6	174.4	192.0	214.6	245.6	285.9	333.0	380.1	422.4	456.2	483.3
127.5°	171.1	184.9	202.1	222.8	249.8	284.7	326.1	370.3	410.7	444.5	470.1
130°	177.8	192.0	208.7	227.9	253.0	284.4	321.7	362.5	401.3	434.6	460.7
132.5°	184.1	197.5	214.2	233.0	255.7	284.0	317.8	354.2	390.6	423.3	449.3
135°	193.0	205.8	222.0	239.7	259.8	283.4	311.9	342.9	374.8	404.7	429.3
137.5°	200.6	212.8	227.9	244.4	262.3	283.3	306.8	332.5	359.6	384.8	407.0
140°	205.3	217.1	231.9	247.5	264.2	282.9	304.0	326.6	349.7	371.8	392.4
142.5°	209.7	221.0	235.4	249.9	265.8	282.9	301.7	321.2	341.5	360.4	378.3
145°	215.6	226.4	239.2	252.4	266.7	281.9	297.6	313.3	330.0	344.8	358.5
147.5°	221.4	231.2	243.1	254.7	267.2	280.2	294.0	306.9	320.2	332.0	342.9
150°	225.0	234.3	245.1	255.9	267.2	279.0	291.3	303.1	314.4	324.2	333.0
152.5°	228.5	237.0	246.7	256.7	266.4	277.0	288.1	298.7	308.4	317.5	324.8
155°	233.3	240.6	249.0	257.4	265.2	274.1	283.4	292.2	300.1	307.5	313.3
157.5°	237.8	243.6	250.7	257.4	264.0	271.0	278.6	285.2	291.9	298.0	302.7
160°	240.1	245.6	251.5	257.4	262.8	268.6	275.1	280.9	286.4	291.7	295.7
162.5°	242.5	246.8	252.3	257.4	261.6	266.3	271.9	276.6	281.2	285.4	289.0
165°	245.1	248.1	252.4	256.4	259.3	262.8	266.7	270.6	273.5	277.0	279.5
167.5°	246.8	249.1	252.4	255.2	257.0	259.2	262.0	264.8	267.1	269.8	271.3
170°	248.1	249.5	251.9	254.4	255.4	256.8	258.8	261.3	262.8	264.8	266.2
172.5°	248.8	249.9	251.6	253.7	253.8	254.5	256.1	258.1	259.2	260.5	261.5
175°	250.0	250.0	251.0	252.4	251.9	251.9	253.0	253.9	254.4	255.4	255.4
177.5°	250.0	250.0	250.4	251.2	250.4	250.4	250.8	251.2	251.6	251.6	251.9
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1581.4	1580.3	1576.4	1575.9	1576.4	1580.3	1581.4	1582.4	1584.2	1589.6	1583.0
5°	1460.8	1457.3	1455.3	1462.8	1455.3	1457.3	1460.8	1464.9	1471.8	1472.5	1479.4
7.5°	1369.9	1367.2	1361.2	1359.2	1361.2	1367.2	1369.9	1372.3	1379.2	1385.2	1395.3
10°	1311.6	1308.9	1303.4	1302.0	1303.4	1308.9	1311.6	1318.5	1325.3	1332.9	1339.8
12.5°	1255.5	1250.0	1249.0	1250.3	1249.0	1250.0	1255.5	1264.6	1282.5	1282.4	1283.8
15°	1181.0	1178.3	1170.7	1172.8	1170.7	1178.3	1181.0	1190.0	1198.2	1208.5	1218.8
17.5°	1107.6	1104.3	1095.1	1103.2	1095.1	1104.3	1107.6	1112.4	1123.0	1137.6	1153.1
20°	1061.4	1055.9	1051.1	1050.4	1051.1	1055.9	1061.4	1066.2	1077.9	1090.3	1102.0
22.5°	1017.4	1012.4	1012.0	1007.5	1012.0	1012.4	1017.4	1024.9	1036.6	1043.5	1054.6
25°	962.4	957.6	956.2	952.8	956.2	957.6	962.4	967.9	975.4	980.9	993.3
27.5°	920.2	917.8	915.4	916.4	915.4	917.8	920.2	920.9	924.3	931.6	938.7
30°	894.3	893.6	892.3	892.3	892.3	893.6	894.3	892.3	895.7	899.1	904.7
32.5°	872.9	872.8	873.6	873.6	873.6	872.8	872.9	869.8	871.0	872.2	874.9
35°	842.8	844.8	846.2	844.1	846.2	844.8	842.8	840.1	838.0	833.2	834.6
37.5°	815.5	817.6	819.6	821.9	819.6	817.6	815.5	809.9	804.9	800.7	795.7
40°	794.7	799.5	800.8	804.3	800.8	799.5	794.7	788.5	783.0	778.2	772.7
42.5°	774.9	780.2	783.8	784.5	783.8	780.2	774.9	768.7	760.4	754.5	746.8
45°	744.5	750.0	754.8	754.8	754.8	750.0	744.5	734.2	725.2	716.3	708.8
47.5°	713.0	721.0	725.8	727.0	725.8	721.0	713.0	702.4	689.9	678.9	668.0
50°	691.6	701.2	706.0	709.5	706.0	701.2	691.6	679.8	666.8	653.1	640.0
52.5°	670.6	680.3	686.7	688.5	686.7	680.3	670.6	656.3	640.4	625.6	614.2
55°	634.5	648.2	655.8	658.6	655.8	648.2	634.5	618.7	603.6	585.0	568.5
57.5°	600.4	613.0	621.8	623.9	621.8	613.0	600.4	581.9	562.3	542.5	525.0
60°	574.0	587.7	598.7	600.8	598.7	587.7	574.0	555.4	534.9	515.6	493.6
62.5°	547.1	561.4	571.3	576.6	571.3	561.4	547.1	527.4	505.1	483.7	461.7
65°	500.4	514.9	524.5	526.6	524.5	514.9	500.4	481.2	457.8	435.1	416.6
67.5°	449.6	464.0	470.4	474.3	470.4	464.0	449.6	431.4	408.4	384.9	363.8
70°	413.8	425.5	432.4	435.8	432.4	425.5	413.8	394.6	375.3	351.3	328.6
72.5°	373.2	385.4	393.4	394.0	393.4	385.4	373.2	356.6	336.3	313.9	293.9
75°	310.7	321.8	325.8	325.8	325.8	321.8	310.7	294.9	278.4	260.5	240.6
77.5°	246.0	251.6	256.8	258.0	256.8	251.6	246.0	234.5	220.9	203.1	188.0
80°	204.1	207.6	211.7	211.7	211.7	207.6	204.1	193.9	180.8	165.7	153.9
82.5°	161.3	164.2	168.3	167.7	168.3	164.2	161.3	153.2	142.3	132.2	121.6
85°	97.6	103.8	103.1	101.8	103.1	103.8	97.6	99.0	88.7	81.8	72.2
87.5°	46.1	46.7	48.2	49.3	48.2	46.7	46.1	44.3	39.3	36.5	34.2
90°	10.3	10.8	10.3	10.3	10.3	10.8	10.3	9.8	9.8	9.3	8.9
92.5°	42.1	39.5	37.8	37.8	37.8	39.5	42.1	48.0	57.8	72.6	96.4
95°	150.3	135.1	126.2	119.9	126.2	135.1	150.3	174.4	222.0	287.8	363.9
97.5°	374.9	345.3	330.5	320.3	330.5	345.3	374.9	410.1	461.4	509.5	537.7
100°	499.0	469.1	454.3	450.4	454.3	469.1	499.0	541.7	578.1	602.2	592.4
102.5°	603.9	582.2	566.7	563.5	566.7	582.2	603.9	630.2	645.3	638.3	589.6
105°	704.8	700.9	694.0	691.0	694.0	700.9	704.8	703.9	683.7	635.1	550.1
107.5°	721.0	732.2	737.1	738.4	737.1	732.2	721.0	696.7	653.0	584.4	494.0
110°	705.3	725.9	734.8	739.2	734.8	725.9	705.3	670.5	616.4	545.2	460.2



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	671.5	696.5	708.9	716.0	708.9	696.5	671.5	631.9	577.9	510.6	435.5
115°	614.4	643.9	659.6	663.6	659.6	643.9	614.4	575.7	528.5	471.1	410.6
117.5°	566.7	591.4	607.3	610.4	607.3	591.4	566.7	533.6	493.6	448.4	398.4
120°	540.8	562.4	575.1	580.6	575.1	562.4	540.8	512.7	477.9	438.6	393.0
122.5°	522.3	540.8	551.6	557.0	551.6	540.8	522.3	498.6	468.0	432.3	388.2
125°	502.9	517.2	526.5	529.4	526.5	517.2	502.9	483.3	456.2	422.4	380.1
127.5°	489.9	502.6	510.4	513.3	510.4	502.6	489.9	470.1	444.5	410.7	370.3
130°	480.9	493.1	501.0	503.9	501.0	493.1	480.9	460.7	434.6	401.3	362.5
132.5°	469.1	482.9	490.3	493.4	490.3	482.9	469.1	449.3	423.3	390.6	354.2
135°	448.9	462.7	470.5	473.5	470.5	462.7	448.9	429.3	404.7	374.8	342.9
137.5°	425.3	438.9	445.4	448.9	445.4	438.9	425.3	407.0	384.8	359.6	332.5
140°	409.7	420.4	427.3	431.3	427.3	420.4	409.7	392.4	371.8	349.7	326.6
142.5°	393.5	403.6	409.7	412.3	409.7	403.6	393.5	378.3	360.4	341.5	321.2
145°	370.8	379.2	384.1	386.5	384.1	379.2	370.8	358.5	344.8	330.0	313.3
147.5°	351.9	359.0	362.7	363.7	362.7	359.0	351.9	342.9	332.0	320.2	306.9
150°	340.9	347.2	350.2	350.7	350.2	347.2	340.9	333.0	324.2	314.4	303.1
152.5°	331.4	336.7	338.4	338.9	338.4	336.7	331.4	324.8	317.5	308.4	298.7
155°	318.3	322.2	323.6	323.6	323.6	322.2	318.3	313.3	307.5	300.1	292.2
157.5°	306.5	309.4	310.3	310.3	310.3	309.4	306.5	302.7	298.0	291.9	285.2
160°	298.6	301.6	302.0	302.0	302.0	301.6	298.6	295.7	291.7	286.4	280.9
162.5°	291.2	294.1	294.6	294.2	294.6	294.1	291.2	289.0	285.4	281.2	276.6
165°	281.5	283.4	282.9	282.4	282.9	283.4	281.5	279.5	277.0	273.5	270.6
167.5°	272.3	273.5	273.5	273.1	273.5	273.5	272.3	271.3	269.8	267.1	264.8
170°	267.2	267.7	267.2	267.2	267.2	267.7	267.2	266.2	264.8	262.8	261.3
172.5°	262.1	262.6	262.1	261.3	262.1	262.6	262.1	261.5	260.5	259.2	258.1
175°	255.4	256.4	255.4	254.4	255.4	256.4	255.4	255.4	255.4	254.4	253.9
177.5°	251.6	251.9	251.2	250.4	251.2	251.9	251.6	251.9	251.6	251.6	251.2
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1586.3	1588.5	1597.3	1605.6	1615.5	1622.6	1627.5	1633.1	1644.6	1654.0	1662.8
5°	1486.3	1489.7	1507.5	1519.9	1541.2	1559.8	1574.3	1590.0	1608.6	1634.0	1657.4
7.5°	1398.1	1410.9	1430.4	1450.4	1472.2	1496.5	1517.7	1541.5	1573.6	1608.4	1644.5
10°	1348.1	1362.5	1383.1	1406.5	1427.1	1455.3	1481.4	1509.6	1546.0	1588.6	1631.3
12.5°	1298.0	1321.8	1337.5	1365.2	1387.5	1410.7	1438.6	1475.5	1518.0	1562.8	1614.2
15°	1235.3	1248.4	1278.6	1293.7	1325.3	1361.2	1388.6	1425.7	1467.0	1526.1	1583.8
17.5°	1163.0	1180.2	1204.3	1233.1	1269.4	1297.4	1331.5	1369.8	1421.8	1480.5	1552.8
20°	1115.7	1130.1	1159.7	1191.3	1229.9	1259.4	1295.8	1332.9	1386.6	1449.1	1524.7
22.5°	1073.3	1087.3	1118.4	1147.9	1185.3	1221.4	1259.5	1302.7	1354.1	1420.0	1497.2
25°	1007.8	1026.3	1053.9	1084.1	1119.8	1161.1	1202.3	1240.8	1295.8	1365.2	1447.8
27.5°	949.6	964.5	984.4	1018.7	1059.4	1099.2	1140.1	1188.6	1241.4	1314.7	1400.4
30°	912.2	926.0	945.9	977.5	1015.4	1058.0	1100.6	1147.3	1202.3	1275.2	1362.5
32.5°	882.5	892.9	910.7	939.0	973.5	1018.4	1060.4	1108.8	1166.6	1238.4	1323.4
35°	838.7	847.6	854.5	881.3	912.2	953.5	996.1	1047.7	1103.4	1171.4	1256.6
37.5°	795.7	798.7	808.7	826.3	856.3	894.2	933.8	984.6	1041.6	1110.8	1187.6
40°	769.2	770.6	776.8	793.3	819.4	855.1	893.6	943.8	998.2	1063.4	1139.8
42.5°	743.4	742.5	748.2	759.7	784.2	816.7	854.6	900.4	954.7	1015.0	1086.9
45°	702.6	702.6	701.2	710.8	730.7	762.3	794.0	838.0	883.4	942.5	1003.0
47.5°	660.0	656.1	657.3	662.3	679.1	705.1	736.9	772.9	813.0	863.0	916.1
50°	632.4	627.0	624.9	630.3	645.5	668.2	698.4	730.0	767.8	811.8	857.2
52.5°	602.2	596.7	593.0	596.8	610.9	631.9	659.4	687.2	721.1	756.9	796.2
55°	555.4	549.2	547.2	548.5	558.9	575.4	598.7	624.2	649.6	679.2	706.7
57.5°	509.4	499.2	497.3	496.6	503.8	518.8	538.4	560.4	578.9	596.8	626.1
60°	479.1	466.7	462.6	461.9	467.4	479.8	497.7	519.7	532.8	545.1	570.6
62.5°	446.7	434.9	425.8	426.8	431.7	443.5	459.2	475.2	483.8	497.3	514.4
65°	396.7	381.5	374.6	372.6	375.3	385.0	397.4	407.7	417.2	422.8	439.3
67.5°	346.6	334.0	323.8	321.3	320.0	326.7	336.8	343.0	349.9	354.7	364.5
70°	311.4	300.4	288.0	283.9	283.2	288.7	298.3	299.0	308.7	310.7	321.1
72.5°	276.7	263.0	254.5	250.4	247.5	252.4	258.7	260.5	265.8	269.5	274.8
75°	222.7	212.4	204.1	197.9	195.9	198.6	198.6	202.1	205.5	207.6	213.8
77.5°	175.3	163.5	153.7	150.2	147.7	145.9	147.4	149.5	147.8	151.4	152.7
80°	142.3	129.9	122.3	121.0	116.8	113.4	112.7	114.8	112.0	113.4	117.5
82.5°	109.9	101.9	93.8	92.4	87.1	85.4	84.7	83.4	83.4	83.2	84.0
85°	65.3	60.5	55.0	51.6	49.5	46.1	46.1	44.7	43.3	41.9	42.6
87.5°	28.1	27.0	24.1	22.3	21.2	18.4	18.4	16.6	16.0	15.2	14.4
90°	8.4	8.9	7.8	6.9	6.9	4.0	4.0	3.4	2.9	1.5	0.5
92.5°	129.8	155.8	136.4	99.2	61.1	36.2	25.9	18.8	12.7	8.2	5.6
95°	411.6	400.3	302.0	184.7	104.1	61.4	40.7	29.0	22.6	17.7	16.2
97.5°	517.1	421.6	282.8	166.0	99.5	66.6	49.3	39.2	33.3	29.1	29.1
100°	520.6	394.9	256.4	156.2	100.7	71.7	56.0	46.7	40.7	37.4	37.4
102.5°	491.1	361.5	238.7	153.4	104.6	78.4	63.5	54.5	49.0	46.0	45.2
105°	437.6	322.2	223.5	154.7	113.9	90.4	76.1	67.3	61.4	59.0	57.4
107.5°	394.4	300.2	220.8	162.0	124.8	103.2	89.2	80.8	74.5	72.0	71.0
110°	372.8	292.7	221.5	167.5	133.1	111.5	98.2	89.4	83.5	81.0	80.1



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	360.6	289.2	223.9	173.4	140.9	120.1	106.9	98.1	92.6	89.7	88.7
115°	349.2	287.3	228.4	182.7	153.3	133.6	120.4	111.0	106.1	102.6	101.2
117.5°	344.1	286.8	233.2	192.3	165.1	146.5	132.7	124.0	118.6	115.5	114.2
120°	341.4	286.8	236.8	198.9	173.4	154.7	140.9	132.6	127.2	123.8	122.8
122.5°	338.2	286.5	240.3	205.2	181.2	162.6	149.2	140.1	135.1	131.6	130.6
125°	333.0	285.9	245.6	214.6	192.0	174.4	160.6	151.3	145.9	142.9	140.9
127.5°	326.1	284.7	249.8	222.8	202.1	184.9	171.1	161.4	155.2	151.7	150.1
130°	321.7	284.4	253.0	227.9	208.7	192.0	177.8	168.5	161.1	157.1	155.2
132.5°	317.8	284.0	255.7	233.0	214.2	197.5	184.1	174.0	167.0	161.9	160.3
135°	311.9	283.4	259.8	239.7	222.0	205.8	193.0	182.7	174.4	169.4	167.5
137.5°	306.8	283.3	262.3	244.4	227.9	212.8	200.6	189.9	181.9	176.5	174.7
140°	304.0	282.9	264.2	247.5	231.9	217.1	205.3	195.0	186.7	181.2	179.8
142.5°	301.7	282.9	265.8	249.9	235.4	221.0	209.7	199.7	191.7	186.8	185.3
145°	297.6	281.9	266.7	252.4	239.2	226.4	215.6	206.3	199.4	194.5	193.0
147.5°	294.0	280.2	267.2	254.7	243.1	231.2	221.4	213.6	206.6	202.2	201.7
150°	291.3	279.0	267.2	255.9	245.1	234.3	225.0	217.6	211.7	207.8	207.2
152.5°	288.1	277.0	266.4	256.7	246.7	237.0	228.5	221.9	216.4	212.5	212.4
155°	283.4	274.1	265.2	257.4	249.0	240.6	233.3	227.9	223.0	220.1	219.6
157.5°	278.6	271.0	264.0	257.4	250.7	243.6	237.8	233.1	229.3	226.5	226.5
160°	275.1	268.6	262.8	257.4	251.5	245.6	240.1	236.3	232.8	230.8	230.8
162.5°	271.9	266.3	261.6	257.4	252.3	246.8	242.5	239.0	235.9	234.4	234.8
165°	266.7	262.8	259.3	256.4	252.4	248.1	245.1	242.6	240.1	239.2	239.2
167.5°	262.0	259.2	257.0	255.2	252.4	249.1	246.8	245.5	243.6	243.1	243.6
170°	258.8	256.8	255.4	254.4	251.9	249.5	248.1	247.0	245.6	245.1	245.6
172.5°	256.1	254.5	253.8	253.7	251.6	249.9	248.8	248.2	247.1	247.0	247.5
175°	253.0	251.9	251.9	252.4	251.0	250.0	250.0	249.5	249.0	249.0	249.5
177.5°	250.8	250.4	250.4	251.2	250.4	250.0	250.0	250.0	249.6	250.0	250.4
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1670.4	1675.9	1683.1	1695.2	1699.6	1705.1	1712.8	1712.3	1714.4	1722.7	1740.3
5°	1676.6	1698.0	1718.6	1743.4	1769.4	1786.7	1810.0	1824.5	1838.9	1857.4	1889.0
7.5°	1679.1	1713.0	1750.8	1794.2	1832.8	1877.4	1912.2	1944.9	1974.4	2013.6	2051.3
10°	1675.2	1720.6	1769.4	1824.5	1882.8	1932.3	1977.0	2027.9	2071.2	2118.7	2161.3
12.5°	1668.1	1722.9	1788.1	1849.8	1918.0	1991.2	2046.9	2098.3	2155.9	2210.5	2276.2
15°	1651.9	1726.8	1803.1	1884.2	1975.7	2060.2	2140.7	2207.3	2269.3	2351.0	2437.0
17.5°	1631.3	1712.1	1808.4	1906.5	2002.1	2098.8	2198.3	2298.5	2376.6	2478.2	2545.5
20°	1612.1	1705.6	1804.5	1921.4	2016.9	2137.3	2236.2	2333.1	2440.4	2541.4	2621.8
22.5°	1585.1	1687.4	1792.4	1908.8	2034.5	2154.8	2269.3	2374.4	2481.7	2591.5	2689.0
25°	1550.8	1643.6	1768.1	1900.1	2025.2	2155.8	2287.1	2419.1	2534.5	2650.8	2741.5
27.5°	1492.5	1609.7	1725.6	1861.8	2000.9	2148.6	2289.1	2427.2	2548.2	2643.7	2699.9
30°	1462.8	1564.6	1690.4	1827.2	1977.7	2136.6	2282.9	2418.4	2531.2	2607.5	2630.1
32.5°	1418.8	1523.9	1646.9	1788.7	1948.0	2111.3	2263.7	2391.4	2485.4	2525.5	2498.1
35°	1353.6	1448.5	1572.9	1717.9	1883.5	2057.4	2208.0	2315.9	2364.0	2326.2	2232.1
37.5°	1275.2	1369.2	1494.2	1636.7	1808.1	1984.9	2121.0	2198.6	2182.7	2088.7	1948.4
40°	1220.2	1308.2	1427.1	1581.1	1748.2	1925.5	2045.1	2087.1	2043.1	1908.3	1759.1
42.5°	1159.2	1244.9	1364.4	1512.9	1689.9	1853.5	1957.7	1961.1	1887.4	1726.3	1576.6
45°	1066.2	1148.0	1260.8	1415.4	1579.1	1733.0	1801.7	1768.1	1631.9	1476.6	1326.0
47.5°	974.5	1045.4	1156.5	1303.4	1458.7	1588.4	1622.5	1561.9	1416.8	1266.0	1126.4
50°	907.4	978.9	1083.4	1223.7	1373.5	1485.6	1502.0	1421.6	1279.3	1127.4	1018.0
52.5°	843.1	914.0	1014.7	1144.4	1281.7	1382.7	1383.3	1290.2	1148.4	1013.0	911.4
55°	748.6	812.5	903.3	1019.4	1141.9	1220.9	1201.6	1105.4	982.3	864.8	776.1
57.5°	657.6	713.3	796.9	893.8	1001.6	1066.8	1034.8	942.2	832.3	732.6	665.5
60°	598.7	651.7	723.2	814.6	905.3	956.2	926.0	842.1	741.1	660.6	602.2
62.5°	541.6	586.3	655.0	734.3	818.5	856.1	829.1	746.4	659.1	586.3	539.0
65°	460.5	497.1	552.0	620.1	681.2	713.6	690.9	613.9	547.2	495.0	457.1
67.5°	385.0	413.5	455.0	509.6	561.6	579.1	558.4	504.9	448.3	406.6	379.9
70°	332.7	359.6	394.6	436.5	481.9	500.4	479.8	437.2	391.2	352.7	326.5
72.5°	287.1	307.8	337.4	373.2	408.7	427.3	413.3	372.3	333.4	304.8	282.5
75°	218.6	236.5	257.1	282.5	310.0	322.4	310.0	281.8	255.0	233.8	217.9
77.5°	158.9	168.6	184.5	203.5	220.7	230.1	219.5	200.4	184.0	169.4	161.5
80°	121.0	127.9	138.9	153.9	165.7	174.6	167.7	151.9	138.9	129.2	125.8
82.5°	88.0	92.6	99.8	111.1	118.9	123.5	120.5	109.0	103.7	95.1	91.7
85°	43.3	46.1	50.9	54.3	61.2	61.9	62.6	57.8	53.0	50.9	48.1
87.5°	15.2	16.0	17.7	19.5	21.7	22.8	22.3	22.5	20.5	19.8	17.7
90°	1.5	2.9	3.4	4.0	4.0	6.9	6.9	7.8	8.9	8.4	8.9
92.5°	8.2	12.7	18.8	25.9	36.2	61.1	99.2	136.4	155.8	129.8	96.4
95°	17.7	22.6	29.0	40.7	61.4	104.1	184.7	302.0	400.3	411.6	363.9
97.5°	29.1	33.3	39.2	49.3	66.6	99.5	166.0	282.8	421.6	517.1	537.7
100°	37.4	40.7	46.7	56.0	71.7	100.7	156.2	256.4	394.9	520.6	592.4
102.5°	46.0	49.0	54.5	63.5	78.4	104.6	153.4	238.7	361.5	491.1	589.6
105°	59.0	61.4	67.3	76.1	90.4	113.9	154.7	223.5	322.2	437.6	550.1
107.5°	72.0	74.5	80.8	89.2	103.2	124.8	162.0	220.8	300.2	394.4	494.0
110°	81.0	83.5	89.4	98.2	111.5	133.1	167.5	221.5	292.7	372.8	460.2





TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	89.7	92.6	98.1	106.9	120.1	140.9	173.4	223.9	289.2	360.6	435.5
115°	102.6	106.1	111.0	120.4	133.6	153.3	182.7	228.4	287.3	349.2	410.6
117.5°	115.5	118.6	124.0	132.7	146.5	165.1	192.3	233.2	286.8	344.1	398.4
120°	123.8	127.2	132.6	140.9	154.7	173.4	198.9	236.8	286.8	341.4	393.0
122.5°	131.6	135.1	140.1	149.2	162.6	181.2	205.2	240.3	286.5	338.2	388.2
125°	142.9	145.9	151.3	160.6	174.4	192.0	214.6	245.6	285.9	333.0	380.1
127.5°	151.7	155.2	161.4	171.1	184.9	202.1	222.8	249.8	284.7	326.1	370.3
130°	157.1	161.1	168.5	177.8	192.0	208.7	227.9	253.0	284.4	321.7	362.5
132.5°	161.9	167.0	174.0	184.1	197.5	214.2	233.0	255.7	284.0	317.8	354.2
135°	169.4	174.4	182.7	193.0	205.8	222.0	239.7	259.8	283.4	311.9	342.9
137.5°	176.5	181.9	189.9	200.6	212.8	227.9	244.4	262.3	283.3	306.8	332.5
140°	181.2	186.7	195.0	205.3	217.1	231.9	247.5	264.2	282.9	304.0	326.6
142.5°	186.8	191.7	199.7	209.7	221.0	235.4	249.9	265.8	282.9	301.7	321.2
145°	194.5	199.4	206.3	215.6	226.4	239.2	252.4	266.7	281.9	297.6	313.3
147.5°	202.2	206.6	213.6	221.4	231.2	243.1	254.7	267.2	280.2	294.0	306.9
150°	207.8	211.7	217.6	225.0	234.3	245.1	255.9	267.2	279.0	291.3	303.1
152.5°	212.5	216.4	221.9	228.5	237.0	246.7	256.7	266.4	277.0	288.1	298.7
155°	220.1	223.0	227.9	233.3	240.6	249.0	257.4	265.2	274.1	283.4	292.2
157.5°	226.5	229.3	233.1	237.8	243.6	250.7	257.4	264.0	271.0	278.6	285.2
160°	230.8	232.8	236.3	240.1	245.6	251.5	257.4	262.8	268.6	275.1	280.9
162.5°	234.4	235.9	239.0	242.5	246.8	252.3	257.4	261.6	266.3	271.9	276.6
165°	239.2	240.1	242.6	245.1	248.1	252.4	256.4	259.3	262.8	266.7	270.6
167.5°	243.1	243.6	245.5	246.8	249.1	252.4	255.2	257.0	259.2	262.0	264.8
170°	245.1	245.6	247.0	248.1	249.5	251.9	254.4	255.4	256.8	258.8	261.3
172.5°	247.0	247.1	248.2	248.8	249.9	251.6	253.7	253.8	254.5	256.1	258.1
175°	249.0	249.0	249.5	250.0	250.0	251.0	252.4	251.9	251.9	253.0	253.9
177.5°	250.0	249.6	250.0	250.0	250.0	250.4	251.2	250.4	250.4	250.8	251.2
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332681-935  
 CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5	1659.5
2.5°	1749.1	1750.2	1755.1	1759.0	1760.1	1765.6	1766.2
5°	1902.8	1914.5	1937.2	1939.2	1942.7	1960.6	1946.8
7.5°	2082.9	2112.6	2132.4	2149.9	2156.2	2164.0	2162.4
10°	2198.4	2242.4	2264.4	2299.5	2300.9	2309.8	2304.3
12.5°	2314.5	2365.6	2405.7	2412.2	2441.6	2446.2	2453.8
15°	2478.9	2533.1	2588.9	2608.8	2649.4	2659.0	2674.1
17.5°	2633.5	2689.0	2728.0	2779.6	2796.2	2818.5	2803.3
20°	2718.1	2778.6	2828.1	2868.7	2885.8	2898.2	2896.8
22.5°	2769.2	2830.3	2870.4	2901.1	2917.2	2922.4	2922.1
25°	2801.3	2836.3	2848.7	2860.4	2842.5	2836.3	2839.1
27.5°	2712.2	2703.1	2670.8	2628.5	2584.5	2549.5	2530.6
30°	2589.5	2535.9	2487.2	2401.8	2357.9	2331.8	2308.4
32.5°	2415.8	2330.8	2236.9	2158.8	2108.8	2070.0	2064.2
35°	2118.0	1990.1	1875.3	1779.8	1730.3	1688.3	1678.7
37.5°	1800.7	1667.8	1564.4	1480.3	1427.1	1397.6	1369.9
40°	1590.0	1475.9	1374.2	1302.7	1262.1	1240.8	1223.7
42.5°	1427.8	1323.6	1222.4	1167.9	1131.3	1118.2	1108.1
45°	1203.7	1106.7	1036.6	995.4	974.0	952.1	941.8
47.5°	1024.2	945.4	899.1	864.1	841.3	828.2	821.7
50°	922.6	857.9	816.7	789.9	769.2	758.9	753.5
52.5°	832.3	779.3	744.6	723.3	709.3	701.7	699.6
55°	717.0	676.4	654.4	635.8	625.6	618.7	616.0
57.5°	623.2	592.0	574.1	558.9	554.9	549.1	547.2
60°	561.6	537.6	522.5	512.1	508.7	501.8	503.2
62.5°	507.2	487.5	474.6	468.7	464.2	458.4	460.3
65°	429.0	414.5	407.7	402.2	396.7	393.2	396.0
67.5°	359.9	350.1	340.7	337.5	334.8	334.2	331.3
70°	314.9	306.6	298.3	296.3	296.3	293.5	292.8
72.5°	271.4	265.4	259.8	258.3	256.1	257.3	254.3
75°	209.7	204.8	202.8	200.7	200.0	200.0	197.9
77.5°	155.0	151.4	148.1	148.1	145.6	144.6	144.4
80°	117.5	116.1	113.4	113.4	112.0	112.7	111.3
82.5°	88.4	86.4	85.9	84.8	82.9	83.0	81.7
85°	47.4	45.4	44.7	42.6	41.2	42.6	41.2
87.5°	18.3	17.9	17.4	16.4	15.9	15.8	14.1
90°	9.3	9.8	9.8	10.3	10.8	10.3	10.3
92.5°	72.6	57.8	48.0	42.1	39.5	37.8	37.8
95°	287.8	222.0	174.4	150.3	135.1	126.2	119.9
97.5°	509.5	461.4	410.1	374.9	345.3	330.5	320.3
100°	602.2	578.1	541.7	499.0	469.1	454.3	450.4
102.5°	638.3	645.3	630.2	603.9	582.2	566.7	563.5
105°	635.1	683.7	703.9	704.8	700.9	694.0	691.0
107.5°	584.4	653.0	696.7	721.0	732.2	737.1	738.4
110°	545.2	616.4	670.5	705.3	725.9	734.8	739.2



TEST NUMBER: P332681-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	510.6	577.9	631.9	671.5	696.5	708.9	716.0
115°	471.1	528.5	575.7	614.4	643.9	659.6	663.6
117.5°	448.4	493.6	533.6	566.7	591.4	607.3	610.4
120°	438.6	477.9	512.7	540.8	562.4	575.1	580.6
122.5°	432.3	468.0	498.6	522.3	540.8	551.6	557.0
125°	422.4	456.2	483.3	502.9	517.2	526.5	529.4
127.5°	410.7	444.5	470.1	489.9	502.6	510.4	513.3
130°	401.3	434.6	460.7	480.9	493.1	501.0	503.9
132.5°	390.6	423.3	449.3	469.1	482.9	490.3	493.4
135°	374.8	404.7	429.3	448.9	462.7	470.5	473.5
137.5°	359.6	384.8	407.0	425.3	438.9	445.4	448.9
140°	349.7	371.8	392.4	409.7	420.4	427.3	431.3
142.5°	341.5	360.4	378.3	393.5	403.6	409.7	412.3
145°	330.0	344.8	358.5	370.8	379.2	384.1	386.5
147.5°	320.2	332.0	342.9	351.9	359.0	362.7	363.7
150°	314.4	324.2	333.0	340.9	347.2	350.2	350.7
152.5°	308.4	317.5	324.8	331.4	336.7	338.4	338.9
155°	300.1	307.5	313.3	318.3	322.2	323.6	323.6
157.5°	291.9	298.0	302.7	306.5	309.4	310.3	310.3
160°	286.4	291.7	295.7	298.6	301.6	302.0	302.0
162.5°	281.2	285.4	289.0	291.2	294.1	294.6	294.2
165°	273.5	277.0	279.5	281.5	283.4	282.9	282.4
167.5°	267.1	269.8	271.3	272.3	273.5	273.5	273.1
170°	262.8	264.8	266.2	267.2	267.7	267.2	267.2
172.5°	259.2	260.5	261.5	262.1	262.6	262.1	261.3
175°	254.4	255.4	255.4	255.4	256.4	255.4	254.4
177.5°	251.6	251.6	251.9	251.6	251.9	251.2	250.4
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0

(END OF REPORT)