

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332686-935

Luminaire Tested: **SA4XXDIP-C1195D590U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332686-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D590U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6166.6 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332686-935
CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332686-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	43
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	47	40	35	42	37	33	38	34	30	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	30	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	41	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13852	13852	13852
5°	13893	13726	13827
10°	13806	13615	13682
15°	13639	13422	13456
20°	13418	13181	13193
25°	13165	12908	12871
30°	12855	12585	12470
35°	12534	12249	12086
40°	12199	11866	11649
45°	11851	11490	11270
50°	11465	11154	10810
55°	11050	10719	10372
60°	10634	10233	9923
65°	10164	9769	9377
70°	9640	9151	8795
75°	8833	8406	8191
80°	7861	7541	7350
85°	6873	6623	6493



TEST NUMBER: P332686-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	2.6
10°-20°	455.3	7.4
20°-30°	670.1	10.9
30°-40°	779.0	12.6
40°-50°	779.1	12.6
50°-60°	681.5	11.1
60°-70°	506.1	8.2
70°-80°	287.5	4.7
80°-90°	84.9	1.4
90°-100°	41.9	0.7
100°-110°	124.1	2.0
110°-120°	210.6	3.4
120°-130°	277.7	4.5
130°-140°	311.8	5.1
140°-150°	306.4	5.0
150°-160°	257.7	4.2
160°-170°	171.5	2.8
170°-180°	60.0	1.0
0°-30°	1287.0	20.9
0°-40°	2066.0	33.5
0°-60°	3526.5	57.2
0°-90°	4405.0	71.4
90°-120°	376.5	6.1
90°-150°	1272.4	20.6
90°-180°	1762.0	28.6
0°-180°	6166.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1714	1708	1694	1708	1706	163
15°	1632	1626	1606	1613	1610	460
25°	1478	1468	1449	1450	1445	680
35°	1272	1262	1243	1233	1226	795
45°	1038	1028	1006	992	987	800
55°	785	780	762	746	737	703
65°	532	525	511	498	491	527
75°	283	276	270	264	263	301
85°	74	74	72	71	70	82
90°	2	7	11	14	15	6
95°	29	34	37	39	39	33
105°	114	115	117	118	120	121
115°	214	214	213	213	212	211
125°	312	312	311	310	309	278
135°	402	405	405	404	403	311
145°	489	490	491	490	489	306
155°	560	560	559	561	559	257
165°	609	608	607	610	608	172
175°	634	632	631	634	631	60
180°	635	635	635	635	635	



TEST NUMBER: P332686-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1720.2	1719.5	1718.7	1718.0	1717.3	1715.5	1712.9	1710.2	1707.5	1704.9	1707.3
5°	1714.4	1713.2	1712.0	1710.8	1709.6	1707.3	1703.9	1700.6	1697.2	1693.8	1697.2
7.5°	1698.5	1697.3	1696.1	1694.8	1693.6	1691.2	1687.4	1683.7	1680.0	1676.2	1679.0
10°	1684.2	1683.0	1681.8	1680.5	1679.3	1676.7	1672.8	1668.8	1664.8	1660.9	1663.3
12.5°	1665.5	1664.3	1663.0	1661.8	1660.6	1657.9	1653.7	1649.5	1645.3	1641.1	1643.7
15°	1631.9	1630.7	1629.5	1628.3	1627.0	1624.2	1619.5	1615.0	1610.4	1605.9	1607.7
17.5°	1591.6	1590.0	1588.5	1587.0	1585.4	1582.5	1578.1	1573.8	1569.5	1565.1	1566.3
20°	1561.9	1560.3	1558.8	1557.3	1555.7	1552.6	1548.1	1543.5	1539.0	1534.3	1535.2
22.5°	1529.9	1527.9	1526.0	1523.9	1521.9	1518.5	1514.0	1509.4	1504.9	1500.2	1501.9
25°	1478.0	1475.8	1473.7	1471.5	1469.4	1466.2	1461.9	1457.7	1453.4	1449.1	1449.4
27.5°	1418.6	1416.3	1414.2	1412.0	1409.8	1406.7	1402.7	1398.8	1394.8	1390.8	1390.1
30°	1379.0	1376.6	1374.1	1371.7	1369.2	1366.0	1362.0	1358.1	1354.1	1350.1	1348.9
32.5°	1337.2	1335.0	1332.8	1330.6	1328.4	1325.2	1320.9	1316.7	1312.5	1308.3	1306.8
35°	1271.8	1269.6	1267.5	1265.3	1263.2	1260.0	1255.7	1251.5	1247.2	1242.9	1240.7
37.5°	1202.7	1200.8	1198.9	1196.9	1194.9	1191.6	1187.1	1182.5	1177.8	1173.3	1171.0
40°	1157.6	1155.2	1152.7	1150.3	1147.9	1144.4	1139.8	1135.1	1130.6	1126.0	1122.9
42.5°	1109.2	1107.8	1106.3	1104.8	1103.4	1100.1	1095.0	1089.9	1084.9	1079.8	1076.2
45°	1038.0	1035.9	1033.7	1031.6	1029.5	1026.0	1021.1	1016.2	1011.2	1006.4	1003.1
47.5°	963.5	962.0	960.5	959.1	957.6	954.7	950.1	945.6	941.1	936.6	932.8
50°	912.9	911.7	910.4	909.2	908.0	905.3	901.0	896.7	892.4	888.1	883.9
52.5°	863.4	861.9	860.5	859.0	857.6	854.5	850.1	845.5	841.0	836.5	832.7
55°	785.1	784.1	783.3	782.3	781.4	778.8	774.5	770.3	765.9	761.6	758.0
57.5°	710.2	709.2	708.2	707.1	706.1	703.4	699.2	695.0	690.8	686.6	683.1
60°	658.6	657.0	655.5	654.0	652.5	649.7	645.8	641.8	637.7	633.8	631.0
62.5°	608.0	606.7	605.4	604.1	602.9	600.1	595.9	591.7	587.5	583.2	580.7
65°	532.1	530.5	529.0	527.4	526.0	523.7	520.6	517.5	514.5	511.4	508.4
67.5°	455.6	454.3	452.8	451.4	450.0	447.8	444.9	442.0	439.0	436.1	433.2
70°	408.4	406.2	404.1	401.9	399.8	397.5	395.0	392.6	390.1	387.7	385.3
72.5°	357.7	355.6	353.4	351.3	349.2	347.2	345.2	343.2	341.3	339.3	337.3
75°	283.2	281.7	280.2	278.6	277.1	275.6	274.1	272.5	271.0	269.5	268.3
77.5°	212.0	211.3	210.7	210.0	209.3	208.3	207.0	205.6	204.3	202.9	202.6
80°	169.1	168.2	167.3	166.3	165.5	164.7	164.1	163.4	162.8	162.2	161.6
82.5°	127.3	126.9	126.5	126.1	125.6	125.4	125.2	125.1	124.9	124.8	124.5
85°	74.2	74.2	74.2	74.2	74.2	74.0	73.4	72.8	72.1	71.5	71.5
87.5°	28.9	28.9	28.8	28.8	28.8	28.8	28.8	28.7	28.6	28.6	28.7
90°	1.5	2.7	3.9	5.1	6.3	7.3	8.2	9.0	9.9	10.8	11.5
92.5°	10.5	11.9	13.3	14.6	16.0	17.0	17.7	18.3	18.9	19.5	19.8
95°	29.4	30.5	31.4	32.4	33.4	34.3	35.0	35.8	36.6	37.3	37.6
97.5°	51.5	52.3	53.0	53.8	54.6	55.4	56.3	57.3	58.1	59.1	59.4
100°	68.7	69.2	69.7	70.1	70.5	71.2	72.2	73.2	74.1	75.2	75.3
102.5°	86.8	87.0	87.1	87.3	87.5	88.1	88.9	89.8	90.7	91.6	92.0
105°	114.4	114.5	114.6	114.8	114.9	115.1	115.5	116.0	116.4	116.8	117.2
107.5°	143.4	143.5	143.6	143.8	144.0	144.0	144.0	144.1	144.2	144.3	144.6
110°	163.1	163.2	163.5	163.7	163.9	163.9	163.8	163.8	163.7	163.5	163.3



TEST NUMBER: P332686-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	183.5	183.5	183.6	183.6	183.7	183.6	183.4	183.1	183.0	182.8	182.7
115°	214.1	214.1	214.1	214.1	214.1	214.0	213.8	213.5	213.4	213.1	213.0
117.5°	243.0	243.1	243.1	243.2	243.3	243.3	243.1	243.0	242.8	242.7	242.3
120°	262.3	262.7	263.1	263.6	264.0	264.1	263.7	263.4	263.0	262.7	262.2
122.5°	282.2	282.4	282.6	282.8	282.9	283.0	282.8	282.7	282.5	282.4	282.0
125°	311.9	311.9	311.9	311.9	311.9	311.8	311.7	311.6	311.4	311.3	311.1
127.5°	338.6	339.0	339.3	339.7	339.9	340.0	339.8	339.7	339.5	339.3	339.1
130°	357.5	357.8	358.2	358.5	358.8	359.0	359.0	359.0	359.0	359.0	358.8
132.5°	376.8	377.0	377.2	377.5	377.7	377.8	377.7	377.6	377.5	377.5	377.2
135°	402.2	402.9	403.5	404.2	404.8	405.1	405.1	405.1	405.1	405.1	404.9
137.5°	429.9	430.2	430.5	430.8	431.1	431.4	431.5	431.7	431.9	432.0	431.8
140°	448.3	448.6	448.8	449.0	449.2	449.4	449.4	449.4	449.4	449.4	449.2
142.5°	465.2	465.5	465.7	465.9	466.1	466.1	466.1	466.0	465.9	465.8	465.8
145°	488.6	489.0	489.5	489.9	490.3	490.6	490.8	490.9	490.9	491.0	490.9
147.5°	511.8	512.3	512.8	513.3	513.9	514.1	514.0	513.9	513.8	513.8	513.7
150°	525.9	526.4	526.8	527.3	527.7	527.9	527.9	527.9	527.9	527.9	527.9
152.5°	539.3	539.6	539.8	540.1	540.4	540.5	540.6	540.7	540.8	540.9	541.1
155°	559.8	559.8	559.8	559.8	559.8	559.7	559.6	559.6	559.5	559.3	559.7
157.5°	577.1	576.9	576.7	576.5	576.4	576.2	576.2	576.2	576.2	576.1	576.4
160°	587.3	587.2	587.1	587.0	586.9	586.8	586.7	586.6	586.4	586.3	586.7
162.5°	596.8	596.5	596.2	595.9	595.6	595.4	595.3	595.2	595.1	595.0	595.6
165°	609.4	609.1	608.7	608.5	608.1	607.9	607.6	607.4	607.2	607.0	607.6
167.5°	619.1	618.7	618.2	617.8	617.3	617.1	617.1	617.2	617.2	617.2	617.9
170°	624.7	624.1	623.5	623.0	622.4	622.2	622.3	622.4	622.6	622.7	623.4
172.5°	628.5	628.1	627.7	627.2	626.7	626.5	626.5	626.5	626.5	626.6	627.3
175°	634.0	633.4	632.9	632.3	631.8	631.5	631.4	631.3	631.1	631.0	631.8
177.5°	635.8	635.3	634.9	634.5	634.0	633.8	633.8	633.8	633.8	633.8	634.4
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0



TEST NUMBER: P332686-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1709.7	1712.2	1714.6	1715.7	1715.5	1715.2	1714.9	1714.7
5°	1700.6	1703.9	1707.3	1708.7	1708.1	1707.4	1706.8	1706.2
7.5°	1681.6	1684.3	1687.0	1688.2	1687.8	1687.4	1687.0	1686.7
10°	1665.7	1668.2	1670.6	1671.5	1670.9	1670.3	1669.7	1669.0
12.5°	1646.4	1649.1	1651.8	1652.7	1651.8	1651.0	1650.1	1649.2
15°	1609.5	1611.4	1613.2	1613.6	1612.7	1611.8	1610.8	1610.0
17.5°	1567.5	1568.7	1569.8	1570.0	1569.4	1568.8	1568.2	1567.6
20°	1536.2	1537.1	1538.0	1538.2	1537.6	1537.0	1536.4	1535.7
22.5°	1503.6	1505.2	1506.8	1507.1	1506.1	1504.9	1503.8	1502.7
25°	1449.8	1450.0	1450.4	1449.8	1448.6	1447.4	1446.2	1445.0
27.5°	1389.3	1388.6	1387.8	1386.7	1385.2	1383.7	1382.2	1380.6
30°	1347.6	1346.4	1345.2	1343.8	1342.3	1340.8	1339.3	1337.7
32.5°	1305.4	1303.9	1302.4	1301.0	1299.4	1297.9	1296.4	1294.9
35°	1238.6	1236.5	1234.3	1232.5	1231.0	1229.4	1227.9	1226.4
37.5°	1168.6	1166.3	1164.0	1161.8	1159.9	1157.8	1155.8	1153.7
40°	1119.9	1116.8	1113.8	1111.5	1110.0	1108.5	1106.9	1105.4
42.5°	1072.7	1069.2	1065.7	1063.3	1062.3	1061.3	1060.2	1059.2
45°	999.7	996.3	993.0	990.8	989.9	988.9	988.1	987.1
47.5°	929.0	925.2	921.4	918.3	916.0	913.7	911.4	909.0
50°	879.6	875.3	871.1	868.0	866.2	864.4	862.5	860.7
52.5°	828.9	825.1	821.3	818.3	816.0	813.6	811.3	809.0
55°	754.3	750.7	747.0	744.2	742.4	740.6	738.7	736.9
57.5°	679.7	676.1	672.7	670.0	668.3	666.5	664.7	663.0
60°	628.3	625.6	622.8	620.7	619.1	617.6	616.1	614.6
62.5°	578.2	575.7	573.2	571.2	569.6	568.1	566.6	565.1
65°	505.3	502.3	499.2	497.0	495.4	493.9	492.3	490.9
67.5°	430.2	427.3	424.4	422.7	422.2	421.8	421.4	420.9
70°	382.8	380.4	377.9	376.3	375.3	374.4	373.5	372.6
72.5°	335.4	333.5	331.5	330.0	329.2	328.2	327.3	326.4
75°	267.0	265.8	264.6	263.8	263.6	263.2	262.9	262.6
77.5°	202.2	201.8	201.5	200.9	200.1	199.3	198.5	197.7
80°	161.0	160.4	159.8	159.4	159.0	158.7	158.4	158.1
82.5°	124.1	123.7	123.4	123.0	122.7	122.4	122.1	121.8
85°	71.5	71.5	71.5	71.4	71.0	70.7	70.4	70.1
87.5°	28.8	28.9	29.1	29.2	29.2	29.3	29.3	29.4
90°	12.1	12.7	13.4	13.9	14.1	14.3	14.6	14.7
92.5°	20.2	20.7	21.0	21.3	21.4	21.5	21.7	21.8
95°	38.0	38.3	38.7	38.8	38.8	38.8	38.8	38.8
97.5°	59.8	60.2	60.6	60.8	60.8	60.8	60.8	60.8
100°	75.6	75.8	76.0	76.1	76.1	76.1	76.1	76.1
102.5°	92.2	92.6	92.8	93.1	93.2	93.2	93.3	93.4
105°	117.5	117.9	118.2	118.5	118.8	119.2	119.5	119.9
107.5°	144.9	145.2	145.5	145.7	145.6	145.6	145.6	145.6
110°	163.1	162.9	162.6	162.7	163.1	163.3	163.7	164.0



TEST NUMBER: P332686-935

CATALOG NUMBER: SA4XXDIP-C1195D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	182.7	182.6	182.6	182.6	182.7	182.7	182.8	182.9
115°	212.9	212.8	212.7	212.6	212.5	212.3	212.2	212.2
117.5°	241.9	241.6	241.2	240.9	240.6	240.5	240.2	240.0
120°	261.7	261.1	260.5	260.4	260.6	260.8	261.1	261.2
122.5°	281.6	281.3	280.9	280.5	280.1	279.7	279.3	279.0
125°	310.9	310.6	310.5	310.2	310.0	309.8	309.6	309.4
127.5°	338.9	338.7	338.5	338.3	338.1	337.9	337.8	337.6
130°	358.5	358.3	358.1	357.7	357.3	356.9	356.5	356.0
132.5°	377.0	376.8	376.6	376.3	376.2	376.0	375.8	375.7
135°	404.7	404.5	404.2	404.0	403.6	403.3	403.0	402.7
137.5°	431.4	431.2	430.9	430.8	430.8	430.9	431.0	431.1
140°	449.1	449.0	448.9	448.8	448.7	448.6	448.5	448.3
142.5°	465.8	465.8	465.7	465.7	465.7	465.7	465.6	465.6
145°	490.9	490.8	490.6	490.4	490.1	489.7	489.4	489.1
147.5°	513.6	513.5	513.4	513.3	513.2	513.1	513.0	512.9
150°	527.9	527.9	527.9	527.9	527.7	527.6	527.5	527.4
152.5°	541.4	541.7	541.9	541.9	541.7	541.3	541.1	540.8
155°	560.2	560.6	561.1	561.1	560.6	560.2	559.7	559.3
157.5°	576.8	577.1	577.5	577.4	577.0	576.7	576.3	575.9
160°	587.0	587.3	587.6	587.5	587.0	586.4	585.9	585.4
162.5°	596.2	596.8	597.4	597.4	596.8	596.2	595.7	595.2
165°	608.3	608.9	609.6	609.7	609.2	608.8	608.4	608.0
167.5°	618.5	619.1	619.8	619.7	619.1	618.5	617.8	617.1
170°	624.0	624.7	625.3	625.3	624.5	623.7	622.9	622.2
172.5°	628.1	628.9	629.6	629.6	628.8	628.0	627.2	626.5
175°	632.6	633.4	634.0	634.0	633.4	632.6	631.8	631.0
177.5°	635.0	635.6	636.2	636.2	635.5	634.8	634.0	633.4
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0

(END OF REPORT)