

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332569-935

Luminaire Tested: **SA4XXDIP-C575D1035U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332569-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5232.0 lumens  
Efficiency: N/A  
Efficacy: 117.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332569-935  
CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332569-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	91	88	84	87	83	80	77	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	35	34	29
3	79	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	25	22	19	20	17	15	13
9	49	37	29	24	45	34	27	23	29	23	20	23	20	17	19	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332569-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.7	1.5
10°-20°	221.9	4.2
20°-30°	326.6	6.2
30°-40°	379.6	7.3
40°-50°	379.6	7.3
50°-60°	332.1	6.3
60°-70°	246.6	4.7
70°-80°	140.1	2.7
80°-90°	43.8	0.8
90°-100°	73.3	1.4
100°-110°	217.1	4.1
110°-120°	368.5	7.0
120°-130°	485.9	9.3
130°-140°	545.7	10.4
140°-150°	536.2	10.2
150°-160°	451.0	8.6
160°-170°	300.1	5.7
170°-180°	105.1	2.0
0°-30°	627.2	12.0
0°-40°	1006.8	19.2
0°-60°	1718.5	32.8
0°-90°	2149.0	41.1
90°-120°	658.9	12.6
90°-150°	2226.8	42.6
90°-180°	3083.0	58.9
0°-180°	5232.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	3	12	19	24	26	5
95°	52	59	65	68	68	57
105°	200	201	205	207	210	213
115°	375	375	373	372	371	369
125°	546	546	545	543	541	486
135°	704	709	709	707	705	544
145°	855	858	859	858	856	535
155°	980	980	979	982	979	451
165°	1066	1064	1062	1067	1064	301
175°	1110	1105	1104	1110	1104	105
180°	1111	1111	1111	1111	1111	



TEST NUMBER: P332569-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.5	14.7	15.1	15.3	15.7	15.9	16.1	16.3	16.4	16.6	16.9
90°	2.6	4.6	6.8	8.9	11.0	12.8	14.3	15.8	17.4	18.9	20.1
92.5°	18.4	20.8	23.2	25.6	28.0	29.8	30.8	31.9	33.0	34.0	34.7
95°	51.6	53.3	55.0	56.7	58.5	59.9	61.3	62.7	64.0	65.3	65.9
97.5°	90.1	91.4	92.8	94.2	95.6	97.0	98.6	100.1	101.8	103.3	104.0
100°	120.3	121.1	121.8	122.6	123.4	124.6	126.3	128.0	129.8	131.5	131.9
102.5°	152.0	152.2	152.6	152.8	153.2	154.1	155.7	157.2	158.8	160.4	160.9
105°	200.3	200.4	200.6	200.8	201.0	201.5	202.2	203.0	203.8	204.6	205.1
107.5°	251.0	251.2	251.4	251.7	251.8	252.0	252.2	252.3	252.4	252.5	253.0
110°	285.3	285.7	286.1	286.5	286.9	287.0	286.7	286.5	286.4	286.2	285.8



TEST NUMBER: P332569-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	321.1	321.2	321.2	321.3	321.4	321.2	320.9	320.6	320.2	319.9	319.8
115°	374.7	374.7	374.7	374.7	374.7	374.5	374.1	373.8	373.3	373.0	372.8
117.5°	425.2	425.4	425.5	425.7	425.9	425.8	425.5	425.2	425.0	424.7	424.0
120°	458.9	459.7	460.5	461.2	462.0	462.1	461.5	460.9	460.4	459.8	458.8
122.5°	494.0	494.3	494.6	494.9	495.2	495.2	495.0	494.6	494.4	494.1	493.5
125°	545.7	545.7	545.7	545.7	545.7	545.6	545.4	545.3	545.0	544.8	544.5
127.5°	592.6	593.2	593.7	594.3	595.0	595.0	594.8	594.4	594.2	593.8	593.5
130°	625.6	626.2	626.8	627.3	627.9	628.2	628.2	628.2	628.2	628.2	627.8
132.5°	659.4	659.8	660.1	660.6	661.0	661.2	661.0	660.8	660.6	660.6	660.1
135°	703.9	705.0	706.1	707.3	708.4	709.0	709.0	709.0	709.0	709.0	708.6
137.5°	752.3	752.9	753.4	753.9	754.5	754.8	755.2	755.5	755.8	756.1	755.6
140°	784.6	785.0	785.4	785.7	786.2	786.4	786.4	786.4	786.4	786.4	786.2
142.5°	814.2	814.6	814.9	815.4	815.7	815.8	815.7	815.5	815.4	815.2	815.2
145°	855.1	855.8	856.6	857.4	858.2	858.6	858.8	859.0	859.2	859.4	859.2
147.5°	895.7	896.6	897.5	898.5	899.3	899.7	899.6	899.4	899.2	899.1	899.0
150°	920.4	921.2	922.0	922.7	923.5	923.9	923.9	923.9	923.9	923.9	923.9
152.5°	943.8	944.3	944.7	945.2	945.6	945.9	946.1	946.2	946.4	946.5	947.0
155°	979.7	979.7	979.7	979.7	979.7	979.6	979.4	979.2	979.0	978.9	979.6
157.5°	1010.0	1009.6	1009.3	1008.9	1008.6	1008.4	1008.3	1008.3	1008.3	1008.2	1008.8
160°	1027.9	1027.6	1027.4	1027.3	1027.1	1026.9	1026.7	1026.5	1026.3	1026.1	1026.7
162.5°	1044.3	1043.9	1043.4	1042.8	1042.3	1042.0	1041.8	1041.6	1041.5	1041.2	1042.2
165°	1066.5	1065.9	1065.4	1064.8	1064.2	1063.8	1063.3	1063.0	1062.6	1062.2	1063.3
167.5°	1083.6	1082.7	1081.9	1081.2	1080.3	1080.0	1080.0	1080.0	1080.0	1080.1	1081.2
170°	1093.1	1092.2	1091.2	1090.3	1089.3	1088.9	1089.2	1089.3	1089.5	1089.7	1090.9
172.5°	1100.0	1099.2	1098.5	1097.6	1096.8	1096.4	1096.5	1096.5	1096.6	1096.6	1097.9
175°	1109.5	1108.5	1107.6	1106.6	1105.7	1105.1	1104.9	1104.7	1104.5	1104.3	1105.7
177.5°	1112.6	1111.8	1111.0	1110.3	1109.5	1109.1	1109.1	1109.1	1109.1	1109.1	1110.2
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332569-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	17.1	17.3	17.6	17.7	17.8	17.9	17.9	18.0
90°	21.2	22.4	23.5	24.3	24.6	25.1	25.4	25.7
92.5°	35.4	36.1	36.8	37.3	37.5	37.7	38.0	38.1
95°	66.5	67.1	67.6	67.9	67.9	67.9	67.9	67.9
97.5°	104.7	105.4	106.1	106.4	106.4	106.4	106.4	106.4
100°	132.2	132.6	133.0	133.2	133.2	133.2	133.2	133.2
102.5°	161.4	162.0	162.5	162.8	163.0	163.2	163.3	163.4
105°	205.7	206.3	206.8	207.4	207.9	208.5	209.1	209.7
107.5°	253.6	254.1	254.6	254.9	254.9	254.8	254.8	254.7
110°	285.4	285.0	284.6	284.7	285.3	285.9	286.5	287.1





TEST NUMBER: P332569-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	319.7	319.6	319.6	319.6	319.7	319.8	319.9	320.0
115°	372.6	372.4	372.2	372.0	371.9	371.6	371.4	371.3
117.5°	423.4	422.8	422.1	421.6	421.2	420.9	420.4	420.1
120°	457.9	456.9	456.0	455.6	456.1	456.4	456.8	457.2
122.5°	492.8	492.2	491.5	490.9	490.2	489.5	488.8	488.1
125°	544.1	543.7	543.3	542.9	542.6	542.2	541.8	541.4
127.5°	593.1	592.7	592.3	591.9	591.7	591.3	591.1	590.7
130°	627.5	627.1	626.7	626.1	625.3	624.6	623.8	623.0
132.5°	659.8	659.4	659.0	658.7	658.3	658.1	657.7	657.5
135°	708.3	707.8	707.5	707.0	706.5	705.8	705.2	704.7
137.5°	755.1	754.6	754.1	753.9	754.1	754.1	754.2	754.4
140°	786.0	785.7	785.6	785.4	785.2	785.0	784.8	784.6
142.5°	815.1	815.1	815.1	815.0	815.0	814.9	814.9	814.9
145°	859.0	858.8	858.6	858.2	857.6	857.1	856.5	855.9
147.5°	898.8	898.6	898.5	898.3	898.1	897.9	897.8	897.6
150°	923.9	923.9	923.9	923.8	923.6	923.3	923.2	923.0
152.5°	947.4	947.9	948.4	948.4	947.9	947.4	946.8	946.3
155°	980.4	981.1	981.9	981.9	981.1	980.4	979.6	978.9
157.5°	1009.4	1010.0	1010.6	1010.5	1009.9	1009.2	1008.6	1007.9
160°	1027.3	1027.9	1028.4	1028.2	1027.3	1026.3	1025.4	1024.4
162.5°	1043.3	1044.3	1045.3	1045.4	1044.5	1043.5	1042.6	1041.6
165°	1064.5	1065.7	1066.8	1067.0	1066.3	1065.5	1064.7	1063.9
167.5°	1082.4	1083.6	1084.7	1084.7	1083.5	1082.3	1081.1	1080.0
170°	1092.0	1093.1	1094.3	1094.2	1092.9	1091.5	1090.2	1088.8
172.5°	1099.2	1100.4	1101.8	1101.7	1100.4	1099.1	1097.8	1096.4
175°	1107.0	1108.4	1109.7	1109.7	1108.4	1107.0	1105.7	1104.3
177.5°	1111.3	1112.3	1113.4	1113.4	1112.2	1110.9	1109.7	1108.5
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2

(END OF REPORT)