

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332910-927

Luminaire Tested: **SA4XXRDIP-C575D810U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332910-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D810U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4424.1 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332910-927

CATALOG NUMBER: SA4XXRDIP-C575D810U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332910-927

CATALOG NUMBER: SA4XXRDIP-C575D810U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	44	43	42	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	39	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	25	23	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	13
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6500	6500	6500
5°	6514	6434	6474
10°	6473	6357	6357
15°	6399	6224	6177
20°	6296	6048	5936
25°	6167	5842	5694
30°	6039	5626	5390
35°	5899	5401	5084
40°	5730	5145	4755
45°	5574	4891	4419
50°	5397	4598	4064
55°	5206	4294	3678
60°	4996	3961	3284
65°	4804	3543	2896
70°	4525	3085	2460
75°	4173	2558	1999
80°	3640	1948	1836
85°	3084	1769	1658



TEST NUMBER: P332910-927

CATALOG NUMBER: SA4XXRDIP-C575D810U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	1.7
10°-20°	210.9	4.8
20°-30°	304.5	6.9
30°-40°	345.2	7.8
40°-50°	333.3	7.5
50°-60°	277.2	6.3
60°-70°	191.4	4.3
70°-80°	97.0	2.2
80°-90°	27.3	0.6
90°-100°	28.3	0.6
100°-110°	180.6	4.1
110°-120°	345.5	7.8
120°-130°	438.6	9.9
130°-140°	469.2	10.6
140°-150°	438.8	9.9
150°-160°	353.8	8.0
160°-170°	228.2	5.2
170°-180°	78.7	1.8
0°-30°	591.0	13.4
0°-40°	936.2	21.2
0°-60°	1546.7	35.0
0°-90°	1862.4	42.1
90°-120°	554.4	12.5
90°-150°	1901.0	43.0
90°-180°	2562.0	57.9
0°-180°	4424.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	805	805	805	805	805	
5°	804	801	794	800	799	76
15°	766	760	745	743	739	216
25°	692	680	656	646	639	319
35°	599	578	548	528	516	374
45°	488	465	428	399	387	376
55°	370	344	305	274	261	331
65°	252	224	186	160	152	248
75°	134	111	82	68	64	141
85°	33	22	19	18	18	37
90°	2	9	14	17	19	3
95°	34	14	14	17	18	44
105°	186	190	193	197	176	195
115°	348	350	349	351	351	342
125°	489	492	491	492	493	437
135°	607	607	609	610	611	467
145°	700	702	702	702	704	437
155°	768	768	766	768	767	354
165°	810	807	806	811	806	229
175°	828	825	825	830	823	79
180°	828	828	828	828	828	



TEST NUMBER: P332910-927

CATALOG NUMBER: SA4XXRDIP-C575D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	807.1	806.6	806.2	805.7	805.3	804.5	803.3	802.1	800.8	799.6	800.8
5°	803.8	803.3	802.7	802.2	801.7	800.6	798.9	797.3	795.6	794.0	795.4
7.5°	796.5	796.0	795.4	794.9	794.2	792.9	790.8	788.6	786.5	784.3	785.2
10°	789.6	789.0	788.3	787.6	787.0	785.4	782.9	780.4	777.9	775.5	776.0
12.5°	780.8	780.0	779.2	778.4	777.6	775.8	772.9	769.9	767.1	764.1	764.5
15°	765.6	764.4	763.2	761.9	760.7	758.4	754.9	751.5	748.1	744.7	744.4
17.5°	747.3	745.4	743.7	741.9	740.1	737.2	733.1	729.0	724.8	720.7	720.0
20°	732.9	731.2	729.4	727.6	725.8	722.6	718.0	713.3	708.6	704.0	702.9
22.5°	717.2	715.2	713.2	711.1	709.2	705.7	700.7	695.7	690.7	685.7	684.0
25°	692.3	689.8	687.3	684.8	682.4	678.3	672.7	667.1	661.5	655.9	653.6
27.5°	666.1	663.1	660.0	656.9	653.7	649.2	643.2	637.2	631.2	625.2	622.3
30°	647.8	644.4	641.0	637.6	634.2	629.2	622.8	616.4	609.9	603.5	600.1
32.5°	628.7	624.8	620.9	617.0	613.2	607.9	601.3	594.6	588.0	581.3	577.3
35°	598.6	594.2	589.8	585.4	581.1	575.4	568.5	561.7	554.8	548.0	543.4
37.5°	566.4	561.9	557.4	552.9	548.3	542.2	534.6	527.0	519.5	511.9	506.7
40°	543.7	539.2	534.6	530.1	525.6	519.4	511.7	503.8	496.1	488.2	482.4
42.5°	522.0	517.3	512.5	507.8	503.0	496.6	488.5	480.3	472.2	464.1	458.2
45°	488.2	483.2	478.1	473.0	467.9	461.3	453.0	444.9	436.7	428.4	421.7
47.5°	453.4	448.1	442.8	437.6	432.4	425.5	416.9	408.4	399.9	391.3	384.4
50°	429.7	424.3	419.0	413.6	408.3	401.2	392.4	383.7	374.9	366.1	359.3
52.5°	405.5	400.3	395.1	389.8	384.5	377.5	368.4	359.5	350.5	341.5	334.5
55°	369.9	364.4	358.9	353.4	347.9	340.7	331.8	323.0	314.0	305.1	298.0
57.5°	334.6	328.9	323.2	317.5	311.8	304.6	295.8	287.0	278.3	269.5	262.3
60°	309.4	304.0	298.5	293.0	287.6	280.4	271.6	262.8	254.1	245.3	238.2
62.5°	286.8	281.1	275.4	269.7	264.0	256.7	247.6	238.7	229.7	220.7	214.1
65°	251.5	245.7	239.7	233.9	227.9	220.6	211.8	203.1	194.3	185.5	179.7
67.5°	214.9	209.2	203.6	198.0	192.3	185.4	177.3	169.1	161.1	152.9	147.8
70°	191.7	185.9	180.2	174.4	168.7	161.9	154.1	146.3	138.5	130.7	126.2
72.5°	167.1	161.8	156.6	151.5	146.2	140.0	132.6	125.2	117.8	110.4	106.6
75°	133.8	128.7	123.7	118.6	113.5	107.7	101.3	94.8	88.4	82.0	78.8
77.5°	100.0	95.7	91.4	87.1	82.8	78.0	72.8	67.7	62.4	57.2	55.4
80°	78.3	74.3	70.3	66.4	62.4	58.4	54.3	50.1	46.0	41.9	41.5
82.5°	59.6	55.9	52.3	48.6	45.0	42.0	39.6	37.2	34.9	32.6	32.2
85°	33.3	30.6	27.8	25.0	22.3	20.8	20.4	20.0	19.5	19.1	18.9
87.5°	11.7	11.2	10.5	10.0	9.4	9.2	9.3	9.4	9.5	9.7	9.7
90°	1.8	3.4	4.9	6.4	7.9	9.2	10.3	11.4	12.5	13.6	14.4
92.5°	7.8	7.9	8.0	8.1	8.2	8.7	9.8	10.9	12.0	13.2	13.9
95°	34.1	29.4	24.7	20.0	15.4	13.1	13.2	13.4	13.5	13.6	14.4
97.5°	72.3	75.3	78.2	81.1	84.1	77.8	62.4	47.1	31.7	16.3	16.4
100°	101.6	104.1	106.5	109.0	111.5	103.2	84.2	65.3	46.3	27.3	24.9
102.5°	134.3	136.1	137.9	139.7	141.6	141.2	138.7	136.3	133.8	131.3	106.1
105°	186.4	187.3	188.1	188.9	189.7	190.5	191.2	191.9	192.6	193.2	194.5
107.5°	234.9	235.3	235.7	236.1	236.5	237.2	238.1	239.1	240.0	241.0	241.5
110°	267.6	268.0	268.4	268.8	269.3	269.8	270.7	271.5	272.4	273.1	273.5



TEST NUMBER: P332910-927

CATALOG NUMBER: SA4XXRDIP-C575D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	299.3	300.0	300.8	301.5	302.3	302.9	303.2	303.6	304.0	304.4	304.4
115°	348.1	348.5	349.0	349.4	349.7	349.9	349.7	349.6	349.5	349.4	349.6
117.5°	392.1	392.6	393.2	393.7	394.3	394.7	395.0	395.3	395.6	395.9	395.9
120°	421.8	422.4	422.9	423.5	424.0	424.2	424.1	424.0	423.8	423.7	424.0
122.5°	449.6	449.9	450.2	450.5	450.9	451.1	451.3	451.5	451.7	451.9	452.1
125°	489.3	489.9	490.4	491.0	491.5	491.6	491.4	491.2	490.8	490.6	491.0
127.5°	527.0	527.1	527.3	527.4	527.5	527.9	528.5	529.2	529.8	530.4	530.4
130°	551.3	551.4	551.5	551.7	551.8	552.1	552.5	552.9	553.3	553.7	553.9
132.5°	573.5	573.8	574.1	574.3	574.6	575.0	575.4	576.0	576.5	577.0	577.2
135°	607.0	606.9	606.7	606.6	606.5	606.7	607.2	607.8	608.3	608.9	609.1
137.5°	636.6	636.7	636.8	636.8	636.8	637.2	637.8	638.4	639.0	639.6	639.9
140°	655.9	656.2	656.5	656.8	657.0	657.4	657.6	657.9	658.1	658.4	658.9
142.5°	673.3	673.8	674.3	674.8	675.3	675.6	675.7	676.0	676.1	676.3	676.6
145°	699.9	700.4	700.8	701.2	701.6	701.8	701.8	701.8	701.8	701.8	702.0
147.5°	721.1	721.9	722.6	723.4	724.2	724.5	724.4	724.2	724.1	724.0	724.1
150°	736.5	737.0	737.6	738.2	738.6	738.9	738.7	738.6	738.5	738.3	738.3
152.5°	749.3	749.8	750.2	750.7	751.1	751.2	751.0	750.8	750.4	750.2	750.4
155°	767.5	767.5	767.7	767.9	768.0	767.9	767.5	767.0	766.6	766.2	766.8
157.5°	782.7	782.6	782.5	782.4	782.4	782.0	781.6	781.2	780.7	780.2	780.9
160°	791.6	791.2	790.8	790.4	790.0	789.6	789.6	789.4	789.3	789.1	790.0
162.5°	799.5	799.0	798.4	798.0	797.4	797.1	796.9	796.9	796.7	796.5	797.4
165°	809.5	808.9	808.2	807.5	806.8	806.4	806.4	806.4	806.4	806.4	807.6
167.5°	817.5	816.7	816.0	815.3	814.6	814.2	814.1	814.0	814.0	813.9	815.1
170°	822.0	821.1	820.3	819.4	818.6	818.3	818.4	818.6	818.7	818.9	819.9
172.5°	824.9	824.1	823.2	822.4	821.7	821.3	821.4	821.6	821.7	821.8	822.9
175°	828.1	827.3	826.5	825.7	824.8	824.5	824.7	824.7	824.9	825.1	826.2
177.5°	829.7	828.9	828.1	827.3	826.6	826.2	826.5	826.7	827.0	827.1	828.0
180°	828.1	828.1	828.1	828.1	828.1	828.1	828.1	828.1	828.1	828.1	828.1



TEST NUMBER: P332910-927

CATALOG NUMBER: SA4XXRDIP-C575D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	802.1	803.3	804.5	805.0	804.9	804.8	804.7	804.6
5°	796.7	798.1	799.5	800.0	799.7	799.5	799.2	798.9
7.5°	786.1	787.0	787.9	788.1	787.7	787.2	786.8	786.3
10°	776.6	777.1	777.7	777.7	777.1	776.6	776.0	775.5
12.5°	764.8	765.1	765.5	765.2	764.5	763.7	763.0	762.2
15°	744.1	743.9	743.5	743.0	742.0	741.0	740.1	739.1
17.5°	719.2	718.4	717.6	716.5	715.1	713.7	712.2	710.7
20°	701.8	700.7	699.6	698.2	696.4	694.6	692.8	691.0
22.5°	682.5	680.8	679.1	677.6	676.1	674.7	673.3	671.8
25°	651.3	648.9	646.6	644.8	643.3	642.0	640.6	639.2
27.5°	619.4	616.6	613.7	611.2	609.3	607.3	605.4	603.4
30°	596.7	593.2	589.8	587.0	584.8	582.6	580.4	578.2
32.5°	573.4	569.4	565.4	562.4	560.3	558.3	556.1	554.1
35°	538.7	534.0	529.4	525.9	523.4	520.9	518.4	515.9
37.5°	501.5	496.3	491.1	487.3	484.7	482.3	479.8	477.4
40°	476.7	471.0	465.2	461.1	458.6	456.1	453.7	451.2
42.5°	452.3	446.5	440.6	436.4	433.8	431.3	428.6	426.1
45°	415.0	408.3	401.6	397.0	394.5	392.1	389.6	387.1
47.5°	377.4	370.4	363.5	358.6	355.9	353.2	350.5	347.8
50°	352.4	345.6	338.7	334.1	331.4	328.8	326.2	323.6
52.5°	327.6	320.6	313.7	308.9	306.1	303.4	300.7	298.0
55°	290.9	283.8	276.6	271.8	269.2	266.6	264.0	261.3
57.5°	255.0	247.8	240.6	236.0	234.0	232.0	230.0	228.1
60°	231.1	223.9	216.8	212.2	210.0	207.8	205.7	203.4
62.5°	207.6	201.0	194.4	190.2	188.5	186.7	185.0	183.2
65°	173.8	167.9	162.0	158.2	156.6	155.0	153.3	151.6
67.5°	142.8	137.7	132.6	129.2	127.4	125.6	123.7	121.9
70°	121.7	117.2	112.6	109.6	108.3	106.9	105.5	104.2
72.5°	102.7	98.9	95.0	92.4	91.2	89.9	88.6	87.4
75°	75.7	72.6	69.4	67.4	66.5	65.8	65.0	64.1
77.5°	53.6	51.7	49.8	48.8	48.6	48.3	48.1	47.8
80°	41.1	40.7	40.2	40.0	39.8	39.7	39.6	39.5
82.5°	31.9	31.6	31.4	31.1	31.0	30.8	30.7	30.6
85°	18.5	18.3	18.0	17.9	17.9	17.9	17.9	17.9
87.5°	9.7	9.8	9.8	10.0	10.1	10.3	10.5	10.6
90°	15.3	16.1	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	14.8	15.6	16.4	16.9	17.0	17.0	17.0	17.1
95°	15.3	16.1	17.0	17.4	17.6	17.7	17.8	18.0
97.5°	16.6	16.6	16.7	16.8	17.0	17.0	17.2	17.3
100°	22.6	20.2	17.9	16.8	17.0	17.0	17.2	17.3
102.5°	80.8	55.6	30.3	17.7	17.7	17.7	17.8	17.8
105°	195.7	196.9	198.2	196.4	191.4	186.4	181.5	176.5
107.5°	242.2	242.7	243.4	243.9	244.5	244.9	245.5	246.1
110°	273.7	274.0	274.3	274.6	275.0	275.4	275.8	276.2



TEST NUMBER: P332910-927

CATALOG NUMBER: SA4XXRDIP-C575D810U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	304.3	304.2	304.1	304.4	304.9	305.5	305.9	306.5
115°	349.9	350.1	350.5	350.6	350.6	350.6	350.6	350.6
117.5°	395.8	395.8	395.7	395.6	395.6	395.5	395.5	395.5
120°	424.2	424.5	424.8	424.8	424.5	424.2	424.0	423.7
122.5°	452.3	452.4	452.6	452.5	452.3	451.9	451.7	451.4
125°	491.4	491.8	492.2	492.5	492.7	492.7	492.9	493.1
127.5°	530.3	530.2	530.1	530.0	529.9	529.8	529.7	529.6
130°	554.1	554.1	554.3	554.4	554.4	554.4	554.4	554.4
132.5°	577.3	577.4	577.6	577.6	577.5	577.3	577.3	577.2
135°	609.4	609.7	610.0	610.2	610.5	610.8	611.1	611.3
137.5°	640.2	640.5	640.8	640.9	640.8	640.7	640.6	640.6
140°	659.3	659.7	660.0	660.4	660.5	660.6	660.8	660.9
142.5°	676.8	677.2	677.5	677.6	677.6	677.7	677.7	677.7
145°	702.0	702.2	702.3	702.5	702.8	703.1	703.4	703.6
147.5°	724.2	724.3	724.4	724.5	724.7	724.8	724.9	725.1
150°	738.3	738.3	738.3	738.4	738.6	738.6	738.8	738.9
152.5°	750.7	750.9	751.1	751.1	751.1	751.0	750.9	750.8
155°	767.3	767.9	768.4	768.5	768.0	767.6	767.2	766.8
157.5°	781.6	782.4	783.1	783.1	782.4	781.6	780.9	780.2
160°	790.8	791.6	792.4	792.4	791.6	790.8	790.0	789.1
162.5°	798.2	799.0	799.9	799.8	798.8	797.9	797.0	796.1
165°	808.7	809.8	810.9	810.8	809.5	808.3	807.1	805.8
167.5°	816.3	817.5	818.7	818.6	817.3	815.9	814.5	813.2
170°	821.0	822.1	823.2	823.1	821.7	820.4	819.0	817.6
172.5°	824.0	825.1	826.2	826.0	824.6	823.1	821.6	820.1
175°	827.5	828.8	830.0	829.8	828.1	826.5	824.8	823.2
177.5°	828.9	829.8	830.7	830.4	829.1	827.8	826.5	825.1
180°	828.1	828.1	828.1	828.1	828.1	828.1	828.1	828.1

(END OF REPORT)