

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332578-935

Luminaire Tested: **SA4XXDIP-C575D1205U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332578-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5738.0 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332578-935
CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332578-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	95	91	87	83	86	82	79	76	67	65	62	53	51	50	39	38	38	31
2	86	79	73	68	78	72	67	62	58	55	52	46	44	41	35	33	32	26
3	79	70	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	22	41	31	24	20	25	21	17	21	17	14	16	13	12	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332578-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	1.4
10°-20°	221.9	3.9
20°-30°	326.6	5.7
30°-40°	379.6	6.6
40°-50°	379.6	6.6
50°-60°	332.1	5.8
60°-70°	246.6	4.3
70°-80°	140.1	2.4
80°-90°	44.3	0.8
90°-100°	85.3	1.5
100°-110°	252.7	4.4
110°-120°	428.9	7.5
120°-130°	565.6	9.9
130°-140°	635.2	11.1
140°-150°	624.2	10.9
150°-160°	525.0	9.1
160°-170°	349.3	6.1
170°-180°	122.3	2.1
0°-30°	627.2	10.9
0°-40°	1006.8	17.5
0°-60°	1718.5	29.9
0°-90°	2149.6	37.5
90°-120°	767.0	13.4
90°-150°	2591.9	45.2
90°-180°	3588.0	62.5
0°-180°	5738.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	3	14	22	28	30	6
95°	60	69	76	79	79	67
105°	233	234	238	241	244	247
115°	436	436	434	433	432	430
125°	635	635	634	632	630	566
135°	819	825	825	823	820	634
145°	995	999	1000	999	996	623
155°	1140	1140	1139	1143	1139	524
165°	1241	1238	1236	1242	1238	350
175°	1291	1287	1285	1292	1285	123
180°	1293	1293	1293	1293	1293	



TEST NUMBER: P332578-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.6	14.9	15.2	15.7	16.0	16.4	16.5	16.8	17.0	17.3	17.6
90°	3.0	5.4	7.9	10.3	12.7	14.9	16.7	18.4	20.2	22.0	23.3
92.5°	21.4	24.2	27.0	29.8	32.6	34.6	35.9	37.1	38.4	39.6	40.4
95°	60.0	62.0	64.1	66.0	68.0	69.8	71.4	72.9	74.5	76.0	76.7
97.5°	104.9	106.4	108.1	109.6	111.2	113.0	114.8	116.6	118.4	120.2	121.1
100°	140.1	140.9	141.8	142.7	143.6	145.1	147.1	149.0	151.0	153.1	153.5
102.5°	176.8	177.2	177.5	177.9	178.3	179.3	181.2	183.0	184.9	186.7	187.3
105°	233.1	233.3	233.5	233.8	233.9	234.5	235.4	236.3	237.2	238.1	238.8
107.5°	292.1	292.4	292.7	292.9	293.2	293.3	293.5	293.6	293.8	293.9	294.5
110°	332.1	332.5	332.9	333.5	333.9	334.0	333.8	333.6	333.3	333.1	332.7



TEST NUMBER: P332578-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	373.7	373.8	373.9	374.0	374.1	373.9	373.5	373.2	372.7	372.3	372.2
115°	436.1	436.1	436.1	436.1	436.1	435.9	435.5	435.1	434.5	434.1	433.9
117.5°	495.0	495.2	495.3	495.5	495.7	495.6	495.2	495.0	494.6	494.4	493.6
120°	534.2	535.0	536.0	536.8	537.7	537.9	537.2	536.5	535.8	535.2	534.1
122.5°	575.0	575.3	575.7	576.0	576.4	576.4	576.1	575.8	575.5	575.1	574.5
125°	635.2	635.2	635.2	635.2	635.2	635.1	634.9	634.6	634.4	634.2	633.8
127.5°	689.8	690.5	691.1	691.8	692.5	692.7	692.2	691.9	691.6	691.2	690.8
130°	728.2	728.9	729.5	730.2	730.9	731.2	731.2	731.2	731.2	731.2	730.8
132.5°	767.4	767.9	768.4	768.9	769.4	769.6	769.4	769.2	769.0	768.9	768.4
135°	819.2	820.6	821.9	823.3	824.6	825.3	825.3	825.3	825.3	825.3	824.8
137.5°	875.6	876.3	876.9	877.5	878.1	878.7	879.0	879.3	879.7	880.0	879.5
140°	913.3	913.7	914.2	914.6	915.1	915.2	915.2	915.2	915.2	915.2	915.1
142.5°	947.7	948.1	948.6	949.0	949.5	949.6	949.4	949.3	949.1	948.9	948.8
145°	995.3	996.2	997.1	998.0	998.8	999.4	999.6	999.9	1000.1	1000.3	1000.1
147.5°	1042.5	1043.6	1044.7	1045.7	1046.8	1047.2	1047.1	1046.9	1046.7	1046.5	1046.4
150°	1071.3	1072.2	1073.2	1074.0	1074.9	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3
152.5°	1098.5	1099.1	1099.6	1100.1	1100.7	1101.0	1101.2	1101.4	1101.6	1101.7	1102.3
155°	1140.3	1140.3	1140.3	1140.3	1140.3	1140.2	1140.1	1139.8	1139.5	1139.4	1140.2
157.5°	1175.5	1175.2	1174.7	1174.4	1174.0	1173.7	1173.7	1173.6	1173.6	1173.5	1174.2
160°	1196.4	1196.2	1195.9	1195.7	1195.5	1195.2	1195.1	1194.8	1194.6	1194.4	1195.1
162.5°	1215.6	1215.0	1214.4	1213.8	1213.2	1212.9	1212.6	1212.5	1212.2	1211.9	1213.1
165°	1241.4	1240.7	1240.0	1239.4	1238.7	1238.1	1237.7	1237.3	1236.8	1236.4	1237.7
167.5°	1261.2	1260.2	1259.3	1258.4	1257.5	1257.0	1257.1	1257.1	1257.1	1257.1	1258.5
170°	1272.4	1271.3	1270.1	1269.0	1267.9	1267.5	1267.7	1267.9	1268.2	1268.4	1269.7
172.5°	1280.4	1279.4	1278.5	1277.6	1276.7	1276.2	1276.3	1276.3	1276.3	1276.4	1277.9
175°	1291.4	1290.3	1289.2	1288.1	1286.9	1286.2	1286.1	1285.8	1285.6	1285.4	1286.9
177.5°	1295.0	1294.1	1293.2	1292.4	1291.4	1291.0	1291.0	1291.0	1291.0	1291.0	1292.3
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4



TEST NUMBER: P332578-935
 CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	17.8	18.1	18.3	18.5	18.6	18.7	18.8	18.9
90°	24.7	26.0	27.4	28.2	28.7	29.1	29.5	30.0
92.5°	41.2	42.0	42.8	43.3	43.7	43.9	44.2	44.4
95°	77.3	78.0	78.7	79.0	79.0	79.0	79.0	79.0
97.5°	121.8	122.6	123.5	123.8	123.8	123.8	123.8	123.8
100°	153.9	154.4	154.8	155.1	155.1	155.1	155.1	155.1
102.5°	187.9	188.6	189.2	189.5	189.8	189.9	190.1	190.3
105°	239.4	240.0	240.7	241.4	242.1	242.7	243.4	244.1
107.5°	295.2	295.8	296.4	296.7	296.6	296.6	296.5	296.5
110°	332.2	331.7	331.3	331.4	332.1	332.8	333.5	334.1



TEST NUMBER: P332578-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	372.1	372.0	372.0	372.0	372.1	372.2	372.4	372.6
115°	433.7	433.4	433.3	433.0	432.8	432.6	432.4	432.1
117.5°	492.8	492.1	491.3	490.8	490.3	489.8	489.4	489.0
120°	533.0	531.8	530.7	530.4	530.8	531.2	531.8	532.2
122.5°	573.7	572.9	572.1	571.4	570.6	569.8	568.9	568.2
125°	633.3	632.8	632.4	632.0	631.5	631.1	630.6	630.2
127.5°	690.3	689.9	689.4	689.1	688.7	688.3	687.9	687.6
130°	730.3	729.9	729.4	728.8	727.9	727.0	726.1	725.2
132.5°	767.9	767.5	767.1	766.6	766.3	765.9	765.6	765.3
135°	824.4	823.9	823.5	822.9	822.3	821.6	820.9	820.3
137.5°	878.9	878.3	877.8	877.5	877.7	877.8	878.0	878.0
140°	914.8	914.6	914.4	914.2	914.0	913.7	913.5	913.3
142.5°	948.8	948.7	948.7	948.6	948.6	948.6	948.6	948.5
145°	999.9	999.6	999.4	998.9	998.3	997.6	997.0	996.3
147.5°	1046.2	1046.0	1045.8	1045.6	1045.4	1045.2	1044.9	1044.7
150°	1075.3	1075.3	1075.3	1075.2	1075.0	1074.8	1074.5	1074.4
152.5°	1102.8	1103.4	1103.9	1103.9	1103.3	1102.7	1102.1	1101.6
155°	1141.2	1142.0	1142.9	1142.9	1142.0	1141.2	1140.2	1139.4
157.5°	1174.9	1175.5	1176.2	1176.2	1175.4	1174.7	1173.9	1173.2
160°	1195.7	1196.4	1197.0	1196.8	1195.7	1194.6	1193.5	1192.4
162.5°	1214.4	1215.6	1216.8	1216.9	1215.7	1214.6	1213.5	1212.4
165°	1239.1	1240.4	1241.7	1241.9	1241.0	1240.2	1239.2	1238.4
167.5°	1259.8	1261.2	1262.5	1262.5	1261.1	1259.7	1258.4	1257.0
170°	1271.1	1272.4	1273.8	1273.6	1272.0	1270.5	1268.9	1267.4
172.5°	1279.4	1280.9	1282.5	1282.5	1280.8	1279.3	1277.7	1276.2
175°	1288.5	1290.0	1291.6	1291.6	1290.0	1288.5	1286.9	1285.4
177.5°	1293.5	1294.8	1296.0	1295.9	1294.4	1293.0	1291.6	1290.2
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4

(END OF REPORT)