

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332579-935

Luminaire Tested: **SA4XXDIP-C575D1205U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332579-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5852.2 lumens  
Efficiency: N/A  
Efficacy: 118.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332579-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332579-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	83	86	82	79	76	66	64	62	52	51	49	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	51	46	43	41	34	33	31	26
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	61	54	48	65	56	49	44	46	41	37	36	32	30	27	25	23	19
5	66	55	47	41	59	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17	14
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12	10
10	45	33	26	21	41	31	24	20	25	20	17	20	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332579-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.7	1.3
10°-20°	221.9	3.8
20°-30°	326.6	5.6
30°-40°	379.6	6.5
40°-50°	379.6	6.5
50°-60°	332.1	5.7
60°-70°	246.6	4.2
70°-80°	140.1	2.4
80°-90°	43.2	0.7
90°-100°	367.8	6.3
100°-110°	765.5	13.1
110°-120°	685.7	11.7
120°-130°	576.8	9.9
130°-140°	480.9	8.2
140°-150°	367.4	6.3
150°-160°	258.2	4.4
160°-170°	151.9	2.6
170°-180°	49.4	0.8
0°-30°	627.2	10.7
0°-40°	1006.8	17.2
0°-60°	1718.5	29.4
0°-90°	2148.5	36.7
90°-120°	1819.0	31.1
90°-150°	3244.1	55.4
90°-180°	3704.0	63.3
0°-180°	5852.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	1	8	18	20	21	4
95°	33	104	815	404	244	37
105°	117	170	656	1413	1408	125
115°	206	259	585	1125	1352	204
125°	287	341	582	957	1078	256
135°	341	406	577	849	964	264
145°	393	450	574	716	787	247
155°	447	483	558	632	659	206
165°	487	502	535	567	575	138
175°	508	509	513	520	518	48
180°	509	509	509	509	509	



TEST NUMBER: P332579-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.1	14.4	14.9	15.0	15.1	15.0	16.0	15.9	16.2	16.4	16.3
90°	1.0	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0
92.5°	11.4	16.6	26.0	38.2	52.9	73.6	124.5	202.1	277.8	317.4	264.3
95°	33.0	36.0	46.1	59.1	83.0	125.1	212.1	376.2	615.3	815.4	838.4
97.5°	59.2	59.2	67.8	79.8	100.5	135.7	202.7	338.2	575.8	858.8	1053.3
100°	76.0	76.0	83.0	95.1	114.1	146.1	205.1	318.1	522.3	804.3	1060.5
102.5°	92.0	93.7	99.9	111.1	129.2	159.7	213.1	312.5	486.2	736.3	1000.5
105°	117.1	120.0	125.1	137.1	155.1	184.1	232.1	315.1	455.2	656.3	891.4
107.5°	144.6	146.6	151.7	164.5	181.7	210.3	254.3	329.9	449.6	611.5	803.4
110°	163.1	165.1	170.0	182.1	200.1	227.1	271.1	341.1	451.3	596.3	759.4



TEST NUMBER: P332579-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	180.7	182.7	188.5	199.7	217.7	244.7	287.1	353.2	456.0	589.1	734.5
115°	206.1	209.1	216.1	226.1	245.1	272.2	312.1	372.2	465.2	585.3	711.4
117.5°	232.5	235.3	241.5	252.5	270.4	298.3	336.4	391.6	475.0	584.3	700.9
120°	250.1	252.1	259.2	270.1	287.1	315.1	353.2	405.2	482.2	584.3	695.3
122.5°	266.1	268.1	275.2	285.3	303.9	331.1	369.2	418.0	489.5	583.5	689.0
125°	287.1	291.1	297.1	308.2	327.2	355.2	391.2	437.2	500.2	582.3	678.3
127.5°	305.7	308.9	316.2	328.7	348.5	376.8	411.6	453.8	508.9	580.1	664.1
130°	316.2	320.1	328.1	343.2	362.1	391.2	425.2	464.3	515.2	579.3	655.3
132.5°	326.6	329.8	340.2	354.4	375.0	402.4	436.4	474.7	520.8	578.5	647.3
135°	341.1	345.2	355.2	372.2	393.2	419.2	452.2	488.3	529.3	577.3	635.3
137.5°	355.8	359.6	370.6	386.8	408.6	433.4	464.3	497.8	534.3	577.0	624.9
140°	366.2	369.2	380.2	397.2	418.2	442.2	472.3	504.2	538.3	576.3	619.3
142.5°	377.4	380.4	390.5	406.8	427.0	450.2	479.4	509.0	541.5	576.3	614.5
145°	393.2	396.2	406.2	420.2	439.2	461.2	487.2	514.3	543.3	574.3	606.3
147.5°	411.0	412.0	420.8	435.2	451.0	470.8	495.2	518.8	544.2	570.7	598.9
150°	422.2	423.2	431.2	443.2	458.2	477.3	499.2	521.2	544.2	568.3	593.3
152.5°	432.6	432.8	440.8	452.0	465.5	482.8	502.5	522.9	542.7	564.3	586.9
155°	447.2	448.2	454.2	464.3	475.3	490.3	507.2	524.3	540.3	558.3	577.3
157.5°	461.4	461.4	467.0	474.8	484.4	496.3	510.7	524.3	537.7	552.1	567.5
160°	470.2	470.2	474.2	481.2	489.2	500.2	512.2	524.3	535.3	547.3	560.3
162.5°	478.2	477.4	480.6	486.8	494.0	502.7	513.8	524.3	532.9	542.4	553.9
165°	487.2	487.2	489.2	494.2	499.2	505.2	514.3	522.3	528.2	535.3	543.3
167.5°	496.3	495.2	496.3	500.1	502.8	507.5	514.0	519.9	523.5	528.1	533.6
170°	500.2	499.2	500.2	503.3	505.2	508.2	513.2	518.2	520.2	523.2	527.3
172.5°	504.2	503.3	503.4	505.7	506.9	509.0	512.5	516.7	517.0	518.4	521.7
175°	508.2	507.2	507.2	508.2	509.3	509.3	511.3	514.3	513.2	513.2	515.2
177.5°	510.1	509.3	508.4	509.3	509.3	509.3	510.1	511.6	510.1	510.1	510.8
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332579-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	16.4	16.7	16.9	16.9	17.0	17.3	17.0	17.0
90°	18.0	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	196.5	147.8	117.7	97.6	85.8	80.4	77.1	77.1
95°	741.3	586.3	452.2	355.2	306.2	275.2	257.1	244.1
97.5°	1095.4	1037.7	939.9	835.4	763.5	703.4	673.3	652.6
100°	1206.6	1226.6	1177.6	1103.5	1016.5	955.5	925.5	917.5
102.5°	1201.0	1300.2	1314.4	1283.6	1230.2	1185.9	1154.3	1148.0
105°	1120.5	1293.7	1392.7	1433.7	1435.7	1427.7	1413.7	1407.6
107.5°	1006.3	1190.6	1330.1	1419.3	1468.7	1491.5	1501.5	1504.2
110°	937.5	1110.5	1255.6	1365.6	1436.7	1478.7	1496.8	1505.7





TEST NUMBER: P332579-935

CATALOG NUMBER: SA4XXDIP-C575D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	887.0	1040.1	1177.2	1287.2	1367.9	1418.7	1443.9	1458.5
115°	836.4	959.5	1076.5	1172.6	1251.6	1311.6	1343.7	1351.7
117.5°	811.6	913.4	1005.5	1086.9	1154.3	1204.8	1237.2	1243.4
120°	800.4	893.5	973.4	1044.5	1101.6	1145.6	1171.6	1182.6
122.5°	790.7	880.6	953.5	1015.7	1063.9	1101.6	1123.5	1134.5
125°	774.4	860.4	929.4	984.5	1024.5	1053.5	1072.5	1078.5
127.5°	754.3	836.6	905.4	957.7	997.9	1023.7	1039.7	1045.7
130°	738.4	817.4	885.5	938.5	979.5	1004.4	1020.5	1026.5
132.5°	721.5	795.8	862.2	915.2	955.5	983.7	998.8	1004.9
135°	698.4	763.4	824.4	874.4	914.5	942.5	958.5	964.5
137.5°	677.3	732.4	783.8	829.0	866.4	894.1	907.2	914.5
140°	665.3	712.3	757.3	799.4	834.4	856.4	870.4	878.4
142.5°	654.1	695.5	734.2	770.6	801.6	822.0	834.4	840.0
145°	638.3	672.4	702.3	730.4	755.4	772.4	782.4	787.4
147.5°	625.3	652.3	676.3	698.4	716.8	731.3	739.0	740.7
150°	617.3	640.3	660.3	678.3	694.3	707.3	713.3	714.4
152.5°	608.5	628.3	646.7	661.5	675.1	685.7	689.3	690.3
155°	595.3	611.3	626.3	638.3	648.3	656.3	659.4	659.4
157.5°	581.1	594.5	607.1	616.7	624.3	630.3	632.1	632.1
160°	572.3	583.2	594.3	602.3	608.3	614.3	615.3	615.3
162.5°	563.4	572.9	581.5	588.7	593.1	599.1	600.1	599.3
165°	551.3	557.2	564.3	569.3	573.3	577.3	576.3	575.3
167.5°	539.5	544.1	549.7	552.7	554.7	557.2	557.1	556.3
170°	532.3	535.3	539.2	542.3	544.2	545.3	544.2	544.2
172.5°	525.8	528.1	530.5	532.6	533.8	534.9	533.8	532.3
175°	517.3	518.2	520.2	520.2	520.2	522.3	520.2	518.2
177.5°	511.6	512.5	512.5	513.2	512.5	513.2	511.6	510.1
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3

(END OF REPORT)