

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332930-927

Luminaire Tested: **SA4XXRDIP-C795D365U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332930-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3579.8 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332930-927  
CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332930-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71				
1	103	99	95	91	97	94	90	87	84	81	79	75	73	72	67	66	65	61				
2	94	87	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55	51				
3	86	76	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44				
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38				
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33				
6	67	55	47	41	63	52	45	39	48	41	37	43	38	34	39	35	32	29				
7	62	50	42	36	59	48	40	35	44	37	33	40	34	31	36	32	28	26				
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	26	23				
9	54	42	34	29	51	40	33	28	37	31	26	34	28	25	31	26	23	21				
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21	19				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8884	8884	8884
5°	8904	8795	8849
10°	8848	8689	8689
15°	8747	8507	8444
20°	8607	8267	8115
25°	8429	7986	7783
30°	8255	7690	7368
35°	8064	7383	6951
40°	7832	7032	6500
45°	7618	6687	6042
50°	7376	6286	5556
55°	7116	5871	5029
60°	6830	5414	4490
65°	6567	4846	3960
70°	6187	4216	3361
75°	5702	3497	2732
80°	4974	2664	2506
85°	4215	2418	2260



TEST NUMBER: P332930-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.4	2.9
10°-20°	288.3	8.1
20°-30°	416.3	11.6
30°-40°	471.8	13.2
40°-50°	455.6	12.7
50°-60°	378.9	10.6
60°-70°	261.6	7.3
70°-80°	132.6	3.7
80°-90°	34.8	1.0
90°-100°	102.9	2.9
100°-110°	214.2	6.0
110°-120°	191.9	5.4
120°-130°	161.4	4.5
130°-140°	134.6	3.8
140°-150°	102.8	2.9
150°-160°	72.3	2.0
160°-170°	42.5	1.2
170°-180°	13.8	0.4
0°-30°	807.9	22.6
0°-40°	1279.7	35.7
0°-60°	2114.3	59.1
0°-90°	2543.3	71.0
90°-120°	509.0	14.2
90°-150°	907.8	25.4
90°-180°	1036.0	28.9
0°-180°	3579.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1099	1095	1085	1093	1092	104
15°	1047	1038	1018	1016	1010	295
25°	946	930	896	883	874	436
35°	818	790	749	721	705	511
45°	667	635	586	546	529	514
55°	506	471	417	375	357	452
65°	344	307	254	219	207	339
75°	183	151	112	93	88	193
85°	46	29	26	24	24	51
90°	0	2	5	6	6	3
95°	9	29	228	113	68	10
105°	33	47	184	396	394	35
115°	58	72	164	315	378	57
125°	80	96	163	268	302	72
135°	96	114	162	238	270	74
145°	110	126	161	200	220	69
155°	125	135	156	177	184	58
165°	136	141	150	159	161	38
175°	142	142	144	146	145	13
180°	142	142	142	142	142	



TEST NUMBER: P332930-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1103.2	1102.6	1101.9	1101.4	1100.7	1099.6	1098.0	1096.4	1094.7	1093.1	1094.7
5°	1098.8	1098.0	1097.3	1096.5	1095.7	1094.3	1092.0	1089.8	1087.5	1085.3	1087.2
7.5°	1088.9	1088.1	1087.3	1086.5	1085.7	1083.9	1080.9	1078.0	1075.1	1072.1	1073.3
10°	1079.4	1078.5	1077.5	1076.6	1075.6	1073.5	1070.2	1066.8	1063.4	1060.0	1060.7
12.5°	1067.2	1066.2	1065.1	1064.0	1063.0	1060.4	1056.5	1052.4	1048.5	1044.5	1045.0
15°	1046.6	1044.9	1043.1	1041.5	1039.8	1036.6	1031.9	1027.2	1022.5	1017.9	1017.5
17.5°	1021.4	1019.0	1016.5	1014.2	1011.7	1007.7	1002.0	996.4	990.8	985.2	984.1
20°	1001.9	999.4	997.0	994.6	992.1	987.8	981.4	975.0	968.6	962.3	960.8
22.5°	980.3	977.6	974.9	972.1	969.4	964.6	957.7	950.9	944.1	937.3	935.1
25°	946.3	942.9	939.5	936.1	932.8	927.2	919.6	911.9	904.2	896.5	893.3
27.5°	910.5	906.3	902.1	897.9	893.6	887.4	879.2	871.0	862.8	854.6	850.6
30°	885.6	880.9	876.2	871.6	866.9	860.2	851.4	842.6	833.7	824.9	820.2
32.5°	859.3	854.1	848.7	843.4	838.2	831.0	821.9	812.8	803.7	794.6	789.2
35°	818.2	812.2	806.2	800.2	794.2	786.6	777.2	767.8	758.4	749.1	742.8
37.5°	774.2	768.0	761.8	755.7	749.5	741.2	730.9	720.5	710.1	699.7	692.6
40°	743.2	737.0	730.9	724.7	718.5	710.0	699.3	688.7	678.0	667.3	659.5
42.5°	713.5	707.0	700.6	694.1	687.6	678.8	667.7	656.6	645.5	634.3	626.3
45°	667.3	660.4	653.5	646.6	639.6	630.6	619.3	608.1	596.8	585.7	576.5
47.5°	619.6	612.5	605.4	598.2	591.0	581.6	570.0	558.3	546.6	534.9	525.4
50°	587.3	580.0	572.7	565.4	558.1	548.4	536.5	524.5	512.5	500.5	491.2
52.5°	554.3	547.2	540.0	532.8	525.7	515.9	503.7	491.4	479.1	466.8	457.3
55°	505.6	498.0	490.6	483.1	475.6	465.8	453.6	441.4	429.3	417.1	407.3
57.5°	457.4	449.6	441.8	434.0	426.2	416.3	404.3	392.4	380.4	368.4	358.5
60°	423.0	415.5	408.1	400.5	393.0	383.3	371.3	359.3	347.4	335.3	325.6
62.5°	392.0	384.2	376.4	368.6	360.8	350.8	338.5	326.2	313.9	301.7	292.6
65°	343.8	335.7	327.6	319.6	311.6	301.6	289.5	277.6	265.6	253.7	245.6
67.5°	293.7	286.1	278.3	270.6	262.8	253.5	242.3	231.2	220.1	209.0	202.0
70°	262.1	254.2	246.3	238.4	230.6	221.3	210.6	199.9	189.3	178.6	172.5
72.5°	228.4	221.3	214.1	207.0	199.9	191.3	181.3	171.1	161.1	151.0	145.7
75°	182.8	175.9	169.0	162.1	155.1	147.3	138.5	129.7	120.9	112.1	107.7
77.5°	136.7	130.8	124.9	119.1	113.1	106.6	99.6	92.4	85.3	78.2	75.7
80°	107.0	101.6	96.2	90.7	85.3	79.8	74.1	68.5	62.9	57.3	56.7
82.5°	81.4	76.4	71.5	66.5	61.5	57.4	54.2	50.9	47.7	44.5	44.0
85°	45.5	41.7	38.0	34.3	30.5	28.4	27.8	27.3	26.7	26.1	25.7
87.5°	15.5	14.5	13.5	12.3	11.2	10.5	10.7	10.5	10.5	10.5	10.2
90°	0.3	0.9	1.7	2.0	2.2	2.2	3.9	3.9	4.5	5.1	4.8
92.5°	3.2	4.7	7.3	10.7	14.8	20.6	34.9	56.6	77.7	88.8	74.0
95°	9.3	10.1	12.9	16.6	23.2	35.0	59.3	105.3	172.2	228.1	234.6
97.5°	16.6	16.6	19.0	22.3	28.1	37.9	56.7	94.7	161.1	240.3	294.8
100°	21.3	21.3	23.2	26.6	31.9	40.9	57.4	89.0	146.2	225.1	296.8
102.5°	25.7	26.2	28.0	31.1	36.2	44.7	59.7	87.5	136.1	206.0	280.0
105°	32.8	33.6	35.0	38.3	43.4	51.5	65.0	88.2	127.4	183.6	249.5
107.5°	40.5	41.0	42.5	46.0	50.9	58.9	71.1	92.4	125.8	171.1	224.8
110°	45.6	46.2	47.6	50.9	56.0	63.5	75.9	95.5	126.3	166.8	212.5



TEST NUMBER: P332930-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	50.5	51.1	52.8	55.8	60.9	68.4	80.3	98.9	127.6	164.9	205.6
115°	57.7	58.5	60.4	63.3	68.6	76.1	87.4	104.2	130.2	163.8	199.1
117.5°	65.0	65.8	67.6	70.7	75.7	83.5	94.1	109.6	132.9	163.5	196.1
120°	70.0	70.6	72.5	75.6	80.3	88.2	98.9	113.4	135.0	163.5	194.6
122.5°	74.5	75.0	77.0	79.9	85.1	92.7	103.3	117.0	137.0	163.3	192.8
125°	80.3	81.4	83.2	86.3	91.6	99.4	109.5	122.3	140.0	163.0	189.8
127.5°	85.6	86.4	88.5	92.0	97.5	105.4	115.2	127.0	142.4	162.3	185.8
130°	88.5	89.6	91.8	96.0	101.3	109.5	119.0	129.9	144.2	162.1	183.4
132.5°	91.4	92.3	95.2	99.2	105.0	112.6	122.2	132.8	145.8	161.9	181.2
135°	95.5	96.6	99.4	104.2	110.0	117.3	126.5	136.7	148.1	161.5	177.8
137.5°	99.6	100.6	103.7	108.2	114.3	121.3	129.9	139.3	149.5	161.5	174.9
140°	102.5	103.3	106.4	111.1	117.0	123.7	132.1	141.1	150.6	161.3	173.3
142.5°	105.6	106.5	109.3	113.8	119.5	126.0	134.2	142.4	151.5	161.3	172.0
145°	110.0	110.9	113.7	117.6	122.9	129.0	136.3	143.9	152.0	160.7	169.7
147.5°	115.0	115.3	117.8	121.8	126.2	131.7	138.6	145.2	152.3	159.7	167.6
150°	118.1	118.4	120.6	124.1	128.3	133.6	139.7	145.8	152.3	159.0	166.0
152.5°	121.0	121.1	123.3	126.5	130.2	135.1	140.6	146.3	151.9	157.9	164.2
155°	125.2	125.4	127.1	129.9	133.0	137.2	142.0	146.7	151.2	156.2	161.5
157.5°	129.1	129.1	130.7	132.8	135.5	138.9	142.9	146.7	150.4	154.5	158.8
160°	131.6	131.6	132.7	134.7	136.9	140.0	143.4	146.7	149.8	153.1	156.8
162.5°	133.8	133.6	134.5	136.3	138.2	140.7	143.8	146.7	149.1	151.8	155.0
165°	136.3	136.3	136.9	138.3	139.7	141.4	143.9	146.2	147.8	149.8	152.0
167.5°	138.9	138.6	138.9	139.9	140.7	142.0	143.9	145.4	146.5	147.7	149.3
170°	140.0	139.7	140.0	140.9	141.4	142.2	143.6	145.0	145.6	146.4	147.6
172.5°	141.1	140.9	140.9	141.5	141.8	142.4	143.4	144.6	144.7	145.0	146.0
175°	142.2	142.0	142.0	142.2	142.5	142.5	143.1	143.9	143.6	143.6	144.2
177.5°	142.8	142.5	142.3	142.5	142.5	142.5	142.8	143.1	142.8	142.8	143.0
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332930-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1096.4	1098.0	1099.6	1100.4	1100.3	1100.1	1099.9	1099.8
5°	1089.0	1090.9	1092.8	1093.5	1093.1	1092.8	1092.4	1092.0
7.5°	1074.5	1075.8	1077.0	1077.2	1076.7	1076.0	1075.5	1074.8
10°	1061.5	1062.2	1063.0	1063.0	1062.2	1061.5	1060.7	1060.0
12.5°	1045.4	1045.8	1046.3	1046.0	1045.0	1043.9	1042.8	1041.8
15°	1017.2	1016.8	1016.4	1015.6	1014.2	1012.9	1011.6	1010.3
17.5°	983.1	982.1	981.0	979.5	977.5	975.5	973.5	971.5
20°	959.3	957.7	956.2	954.3	951.9	949.4	947.0	944.6
22.5°	932.9	930.6	928.4	926.2	924.2	922.3	920.3	918.3
25°	890.2	887.0	883.8	881.3	879.4	877.6	875.7	873.8
27.5°	846.7	842.8	838.8	835.5	832.8	830.1	827.4	824.7
30°	815.6	810.9	806.2	802.3	799.4	796.4	793.4	790.4
32.5°	783.7	778.3	772.9	768.7	765.9	763.0	760.2	757.3
35°	736.3	730.0	723.7	718.7	715.4	712.0	708.6	705.3
37.5°	685.5	678.3	671.2	666.0	662.7	659.3	655.9	652.5
40°	651.6	643.7	635.9	630.3	626.9	623.5	620.2	616.8
42.5°	618.3	610.3	602.3	596.5	592.9	589.5	586.0	582.4
45°	567.3	558.1	548.9	542.6	539.2	535.9	532.5	529.2
47.5°	515.9	506.4	496.9	490.2	486.6	482.8	479.1	475.4
50°	481.8	472.5	463.0	456.6	453.0	449.5	445.9	442.4
52.5°	447.8	438.3	428.7	422.2	418.4	414.7	411.1	407.3
55°	397.6	387.9	378.2	371.5	368.0	364.4	360.8	357.3
57.5°	348.6	338.7	328.8	322.6	319.9	317.2	314.5	311.8
60°	315.9	306.2	296.4	290.0	287.1	284.1	281.1	278.1
62.5°	283.7	274.7	265.7	260.0	257.6	255.2	252.8	250.4
65°	237.5	229.5	221.4	216.3	214.0	211.8	209.5	207.3
67.5°	195.1	188.2	181.3	176.6	174.1	171.6	169.1	166.7
70°	166.3	160.1	153.9	149.9	148.1	146.2	144.3	142.4
72.5°	140.5	135.1	129.8	126.4	124.7	122.9	121.2	119.5
75°	103.5	99.2	94.8	92.1	91.0	89.9	88.7	87.6
77.5°	73.2	70.7	68.1	66.7	66.4	66.1	65.8	65.4
80°	56.2	55.6	55.1	54.7	54.5	54.3	54.1	53.9
82.5°	43.6	43.3	42.9	42.5	42.4	42.1	42.0	41.8
85°	25.3	25.0	24.6	24.4	24.4	24.4	24.4	24.4
87.5°	10.1	10.1	10.0	10.0	10.1	10.4	10.5	10.6
90°	5.1	5.3	5.6	5.6	5.9	6.2	5.9	5.9
92.5°	55.0	41.4	33.0	27.3	24.0	22.5	21.5	21.5
95°	207.5	164.1	126.5	99.4	85.6	77.0	71.9	68.3
97.5°	306.5	290.4	263.0	233.8	213.7	196.9	188.5	182.6
100°	337.6	343.3	329.5	308.8	284.5	267.4	259.0	256.7
102.5°	336.1	363.8	367.8	359.2	344.3	331.9	323.1	321.2
105°	313.5	362.0	389.8	401.2	401.8	399.5	395.6	394.0
107.5°	281.6	333.2	372.2	397.2	411.0	417.4	420.2	420.9
110°	262.4	310.8	351.4	382.1	402.0	413.8	418.8	421.4





TEST NUMBER: P332930-927

CATALOG NUMBER: SA4XXRDIP-C795D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	248.2	291.0	329.4	360.2	382.8	397.0	404.1	408.1
115°	234.1	268.5	301.3	328.1	350.2	367.0	376.0	378.3
117.5°	227.1	255.6	281.4	304.2	323.1	337.2	346.2	347.9
120°	223.9	250.0	272.4	292.3	308.2	320.6	327.9	331.0
122.5°	221.3	246.4	266.8	284.2	297.7	308.2	314.4	317.5
125°	216.7	240.7	260.1	275.5	286.7	294.9	300.2	301.8
127.5°	211.1	234.1	253.4	268.0	279.2	286.5	291.0	292.6
130°	206.6	228.8	247.8	262.6	274.1	281.1	285.6	287.2
132.5°	201.9	222.7	241.3	256.1	267.4	275.3	279.6	281.2
135°	195.4	213.7	230.7	244.7	255.9	263.7	268.2	269.9
137.5°	189.6	204.9	219.4	232.0	242.5	250.2	253.9	255.9
140°	186.2	199.3	211.9	223.7	233.5	239.6	243.6	245.8
142.5°	183.1	194.6	205.4	215.6	224.3	230.0	233.5	235.0
145°	178.6	188.1	196.5	204.4	211.4	216.1	219.0	220.3
147.5°	175.0	182.5	189.3	195.4	200.6	204.7	206.8	207.3
150°	172.8	179.2	184.8	189.8	194.3	198.0	199.6	199.9
152.5°	170.3	175.9	181.0	185.1	188.9	191.9	192.9	193.2
155°	166.6	171.0	175.2	178.6	181.4	183.6	184.5	184.5
157.5°	162.6	166.4	169.9	172.6	174.7	176.4	176.9	176.9
160°	160.2	163.2	166.3	168.6	170.2	171.9	172.2	172.2
162.5°	157.7	160.3	162.7	164.8	166.0	167.6	167.9	167.7
165°	154.2	156.0	157.9	159.3	160.4	161.5	161.3	161.0
167.5°	151.0	152.3	153.8	154.6	155.2	156.0	155.9	155.7
170°	148.9	149.8	150.9	151.8	152.3	152.6	152.3	152.3
172.5°	147.2	147.7	148.5	149.1	149.4	149.6	149.4	148.9
175°	144.7	145.0	145.6	145.6	145.6	146.2	145.6	145.0
177.5°	143.1	143.4	143.4	143.6	143.4	143.6	143.1	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5

(END OF REPORT)