

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332542-935

Luminaire Tested: **SA4XXDIP-C575D365U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332542-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D365U935-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3238.3 lumens  
Efficiency: N/A  
Efficacy: 117.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332542-935  
CATALOG NUMBER: SA4XXDIP-C575D365U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332542-935

CATALOG NUMBER: SA4XXDIP-C575D365U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66						
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56						
2	92	85	78	73	87	80	74	70	71	67	63	63	59	57	55	53	50	47						
3	84	74	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	40						
4	77	66	58	52	72	62	55	49	56	50	45	50	45	41	44	40	37	34						
5	71	59	50	44	66	56	48	43	50	44	39	45	40	36	39	35	32	29						
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	28	26						
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23						
8	56	44	36	30	53	41	34	29	37	31	27	34	29	25	30	26	23	21						
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19						
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17						

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332542-935

CATALOG NUMBER: SA4XXDIP-C575D365U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.7	2.4
10°-20°	221.9	6.9
20°-30°	326.6	10.1
30°-40°	379.6	11.7
40°-50°	379.6	11.7
50°-60°	332.1	10.3
60°-70°	246.6	7.6
70°-80°	140.1	4.3
80°-90°	41.6	1.3
90°-100°	25.9	0.8
100°-110°	76.9	2.4
110°-120°	130.5	4.0
120°-130°	172.0	5.3
130°-140°	193.2	6.0
140°-150°	189.8	5.9
150°-160°	159.7	4.9
160°-170°	106.2	3.3
170°-180°	37.2	1.1
0°-30°	627.2	19.4
0°-40°	1006.8	31.1
0°-60°	1718.5	53.1
0°-90°	2146.9	66.3
90°-120°	233.3	7.2
90°-150°	788.3	24.3
90°-180°	1091.0	33.7
0°-180°	3238.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	1	4	7	8	9	3
95°	18	21	23	24	24	20
105°	71	71	72	73	74	75
115°	133	133	132	132	132	131
125°	193	193	193	192	192	172
135°	249	251	251	250	250	193
145°	303	304	304	304	303	189
155°	347	347	347	348	347	160
165°	378	377	376	378	377	106
175°	393	391	391	393	391	37
180°	393	393	393	393	393	



TEST NUMBER: P332542-935

CATALOG NUMBER: SA4XXDIP-C575D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.1	14.1	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.3
90°	0.9	1.6	2.4	3.2	3.9	4.6	5.1	5.6	6.1	6.7	7.1
92.5°	6.5	7.4	8.2	9.0	9.9	10.5	10.9	11.3	11.7	12.1	12.3
95°	18.3	18.9	19.5	20.1	20.7	21.3	21.7	22.2	22.6	23.2	23.3
97.5°	31.9	32.4	32.9	33.3	33.8	34.4	34.9	35.5	36.0	36.6	36.9
100°	42.6	42.9	43.1	43.4	43.7	44.1	44.7	45.4	46.0	46.6	46.7
102.5°	53.8	53.9	54.0	54.2	54.2	54.6	55.1	55.7	56.2	56.7	57.0
105°	70.9	70.9	71.0	71.1	71.1	71.3	71.6	71.9	72.2	72.4	72.6
107.5°	88.9	88.9	89.0	89.1	89.2	89.2	89.3	89.3	89.4	89.4	89.5
110°	101.0	101.2	101.3	101.4	101.5	101.6	101.5	101.4	101.3	101.3	101.2



TEST NUMBER: P332542-935

CATALOG NUMBER: SA4XXDIP-C575D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	113.7	113.7	113.7	113.7	113.7	113.7	113.6	113.5	113.4	113.2	113.2
115°	132.7	132.7	132.7	132.7	132.7	132.6	132.4	132.3	132.2	132.1	132.0
117.5°	150.5	150.6	150.7	150.7	150.8	150.8	150.7	150.6	150.4	150.3	150.2
120°	162.5	162.7	163.0	163.2	163.6	163.6	163.4	163.2	163.0	162.8	162.5
122.5°	174.9	175.0	175.1	175.2	175.3	175.3	175.2	175.1	175.0	175.0	174.7
125°	193.2	193.2	193.2	193.2	193.2	193.1	193.1	193.0	193.0	192.9	192.8
127.5°	209.8	210.0	210.3	210.4	210.6	210.7	210.6	210.4	210.3	210.3	210.1
130°	221.5	221.7	221.9	222.1	222.3	222.4	222.4	222.4	222.4	222.4	222.3
132.5°	233.4	233.6	233.7	233.8	234.0	234.0	234.0	233.9	233.9	233.8	233.7
135°	249.2	249.6	249.9	250.4	250.8	251.0	251.0	251.0	251.0	251.0	250.9
137.5°	266.3	266.6	266.7	266.9	267.1	267.3	267.3	267.4	267.6	267.7	267.5
140°	277.8	277.9	278.0	278.2	278.4	278.4	278.4	278.4	278.4	278.4	278.4
142.5°	288.3	288.3	288.5	288.6	288.8	288.9	288.8	288.7	288.7	288.6	288.6
145°	302.7	303.0	303.2	303.5	303.8	304.0	304.0	304.1	304.2	304.3	304.2
147.5°	317.1	317.5	317.7	318.1	318.4	318.5	318.5	318.4	318.4	318.3	318.2
150°	325.9	326.1	326.4	326.7	326.9	327.1	327.1	327.1	327.1	327.1	327.1
152.5°	334.2	334.3	334.4	334.6	334.8	334.8	334.9	335.0	335.0	335.1	335.3
155°	346.8	346.8	346.8	346.8	346.8	346.8	346.7	346.6	346.6	346.6	346.8
157.5°	357.6	357.4	357.3	357.2	357.1	357.0	357.0	357.0	357.0	357.0	357.1
160°	363.9	363.8	363.8	363.7	363.6	363.5	363.5	363.4	363.3	363.3	363.5
162.5°	369.7	369.5	369.4	369.2	369.0	368.9	368.9	368.8	368.7	368.6	369.0
165°	377.5	377.4	377.2	376.9	376.8	376.6	376.4	376.3	376.2	376.1	376.4
167.5°	383.6	383.3	383.1	382.7	382.5	382.3	382.4	382.4	382.4	382.4	382.8
170°	387.0	386.7	386.3	386.0	385.6	385.6	385.6	385.6	385.7	385.8	386.2
172.5°	389.4	389.2	388.8	388.6	388.3	388.1	388.1	388.2	388.2	388.2	388.7
175°	392.8	392.4	392.1	391.8	391.4	391.2	391.2	391.1	391.1	391.0	391.4
177.5°	393.9	393.6	393.3	393.0	392.8	392.7	392.7	392.7	392.7	392.7	393.0
180°	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4



TEST NUMBER: P332542-935

CATALOG NUMBER: SA4XXDIP-C575D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	14.4	14.5	14.6	14.6	14.6	14.6	14.6	14.7
90°	7.5	7.9	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	12.6	12.7	13.0	13.2	13.3	13.3	13.4	13.5
95°	23.5	23.8	23.9	24.0	24.0	24.0	24.0	24.0
97.5°	37.0	37.3	37.5	37.6	37.6	37.6	37.6	37.6
100°	46.8	46.9	47.1	47.2	47.2	47.2	47.2	47.2
102.5°	57.2	57.3	57.5	57.7	57.7	57.8	57.8	57.9
105°	72.8	73.0	73.2	73.4	73.6	73.9	74.0	74.2
107.5°	89.8	90.0	90.1	90.2	90.2	90.2	90.2	90.1
110°	101.1	100.9	100.7	100.8	101.0	101.3	101.4	101.6





TEST NUMBER: P332542-935

CATALOG NUMBER: SA4XXDIP-C575D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	113.2	113.1	113.1	113.1	113.2	113.2	113.2	113.3
115°	131.9	131.8	131.7	131.7	131.6	131.6	131.5	131.5
117.5°	149.9	149.6	149.5	149.3	149.1	149.0	148.9	148.7
120°	162.1	161.8	161.4	161.4	161.4	161.6	161.7	161.9
122.5°	174.5	174.3	174.0	173.7	173.6	173.3	173.1	172.8
125°	192.6	192.5	192.3	192.2	192.1	191.9	191.8	191.7
127.5°	210.0	209.8	209.7	209.6	209.5	209.4	209.2	209.1
130°	222.1	222.0	221.9	221.6	221.4	221.1	220.8	220.6
132.5°	233.6	233.4	233.3	233.2	233.1	233.0	232.9	232.7
135°	250.7	250.6	250.5	250.3	250.1	249.9	249.7	249.5
137.5°	267.3	267.2	267.0	266.9	266.9	267.0	267.0	267.1
140°	278.3	278.2	278.1	278.0	278.0	277.9	277.8	277.8
142.5°	288.6	288.6	288.5	288.5	288.5	288.5	288.5	288.5
145°	304.1	304.0	304.0	303.8	303.7	303.4	303.2	303.1
147.5°	318.2	318.1	318.1	318.1	318.0	317.9	317.8	317.8
150°	327.1	327.1	327.1	327.0	327.0	326.9	326.8	326.7
152.5°	335.4	335.6	335.8	335.7	335.5	335.4	335.2	335.0
155°	347.1	347.3	347.6	347.6	347.3	347.1	346.8	346.6
157.5°	357.3	357.6	357.7	357.7	357.5	357.3	357.1	356.8
160°	363.7	363.9	364.1	364.0	363.7	363.3	363.0	362.7
162.5°	369.4	369.7	370.1	370.1	369.8	369.5	369.1	368.8
165°	376.9	377.3	377.6	377.7	377.5	377.2	376.9	376.7
167.5°	383.2	383.6	384.0	384.0	383.6	383.1	382.7	382.3
170°	386.6	387.0	387.4	387.4	386.9	386.4	386.0	385.5
172.5°	389.2	389.6	390.0	390.0	389.6	389.1	388.7	388.1
175°	391.9	392.4	392.9	392.9	392.4	391.9	391.4	391.0
177.5°	393.4	393.8	394.2	394.2	393.7	393.3	392.9	392.4
180°	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4

(END OF REPORT)