

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332934-927

Luminaire Tested: **SA4XXRDIP-C795D590U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332934-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D590U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4413.1 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332934-927

CATALOG NUMBER: SA4XXRDIP-C795D590U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332934-927

CATALOG NUMBER: SA4XXRDIP-C795D590U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46	42
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	42	39	36
4	76	66	58	52	71	62	55	49	54	48	44	47	42	39	40	37	34	31
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8884	8884	8884
5°	8904	8795	8849
10°	8848	8689	8689
15°	8747	8507	8444
20°	8607	8267	8115
25°	8429	7986	7783
30°	8255	7690	7368
35°	8064	7383	6951
40°	7832	7032	6500
45°	7618	6687	6042
50°	7376	6286	5556
55°	7116	5871	5029
60°	6830	5414	4490
65°	6567	4846	3960
70°	6187	4216	3361
75°	5702	3497	2732
80°	4974	2664	2506
85°	4215	2418	2260



TEST NUMBER: P332934-927

CATALOG NUMBER: SA4XXRDIP-C795D590U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.4	2.3
10°-20°	288.3	6.5
20°-30°	416.3	9.4
30°-40°	471.8	10.7
40°-50°	455.6	10.3
50°-60°	378.9	8.6
60°-70°	261.6	5.9
70°-80°	132.6	3.0
80°-90°	35.8	0.8
90°-100°	20.7	0.5
100°-110°	131.7	3.0
110°-120°	252.0	5.7
120°-130°	319.9	7.2
130°-140°	342.3	7.8
140°-150°	320.1	7.3
150°-160°	258.1	5.8
160°-170°	166.5	3.8
170°-180°	57.4	1.3
0°-30°	807.9	18.3
0°-40°	1279.7	29.0
0°-60°	2114.3	47.9
0°-90°	2544.3	57.7
90°-120°	404.5	9.2
90°-150°	1386.8	31.4
90°-180°	1869.0	42.4
0°-180°	4413.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1099	1095	1085	1093	1092	104
15°	1047	1038	1018	1016	1010	295
25°	946	930	896	883	874	436
35°	818	790	749	721	705	511
45°	667	635	586	546	529	514
55°	506	471	417	375	357	452
65°	344	307	254	219	207	339
75°	183	151	112	93	88	193
85°	46	29	26	24	24	51
90°	1	6	10	13	14	3
95°	25	10	10	13	13	32
105°	136	139	141	144	129	142
115°	254	255	255	256	256	250
125°	357	359	358	359	360	319
135°	443	442	444	445	446	341
145°	511	512	512	512	513	319
155°	560	560	559	561	559	258
165°	591	588	588	592	588	167
175°	604	602	602	605	601	58
180°	604	604	604	604	604	



TEST NUMBER: P332934-927

CATALOG NUMBER: SA4XXRDIP-C795D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1103.2	1102.6	1101.9	1101.4	1100.7	1099.6	1098.0	1096.4	1094.7	1093.1	1094.7
5°	1098.8	1098.0	1097.3	1096.5	1095.7	1094.3	1092.0	1089.8	1087.5	1085.3	1087.2
7.5°	1088.9	1088.1	1087.3	1086.5	1085.7	1083.9	1080.9	1078.0	1075.1	1072.1	1073.3
10°	1079.4	1078.5	1077.5	1076.6	1075.6	1073.5	1070.2	1066.8	1063.4	1060.0	1060.7
12.5°	1067.2	1066.2	1065.1	1064.0	1063.0	1060.4	1056.5	1052.4	1048.5	1044.5	1045.0
15°	1046.6	1044.9	1043.1	1041.5	1039.8	1036.6	1031.9	1027.2	1022.5	1017.9	1017.5
17.5°	1021.4	1019.0	1016.5	1014.2	1011.7	1007.7	1002.0	996.4	990.8	985.2	984.1
20°	1001.9	999.4	997.0	994.6	992.1	987.8	981.4	975.0	968.6	962.3	960.8
22.5°	980.3	977.6	974.9	972.1	969.4	964.6	957.7	950.9	944.1	937.3	935.1
25°	946.3	942.9	939.5	936.1	932.8	927.2	919.6	911.9	904.2	896.5	893.3
27.5°	910.5	906.3	902.1	897.9	893.6	887.4	879.2	871.0	862.8	854.6	850.6
30°	885.6	880.9	876.2	871.6	866.9	860.2	851.4	842.6	833.7	824.9	820.2
32.5°	859.3	854.1	848.7	843.4	838.2	831.0	821.9	812.8	803.7	794.6	789.2
35°	818.2	812.2	806.2	800.2	794.2	786.6	777.2	767.8	758.4	749.1	742.8
37.5°	774.2	768.0	761.8	755.7	749.5	741.2	730.9	720.5	710.1	699.7	692.6
40°	743.2	737.0	730.9	724.7	718.5	710.0	699.3	688.7	678.0	667.3	659.5
42.5°	713.5	707.0	700.6	694.1	687.6	678.8	667.7	656.6	645.5	634.3	626.3
45°	667.3	660.4	653.5	646.6	639.6	630.6	619.3	608.1	596.8	585.7	576.5
47.5°	619.6	612.5	605.4	598.2	591.0	581.6	570.0	558.3	546.6	534.9	525.4
50°	587.3	580.0	572.7	565.4	558.1	548.4	536.5	524.5	512.5	500.5	491.2
52.5°	554.3	547.2	540.0	532.8	525.7	515.9	503.7	491.4	479.1	466.8	457.3
55°	505.6	498.0	490.6	483.1	475.6	465.8	453.6	441.4	429.3	417.1	407.3
57.5°	457.4	449.6	441.8	434.0	426.2	416.3	404.3	392.4	380.4	368.4	358.5
60°	423.0	415.5	408.1	400.5	393.0	383.3	371.3	359.3	347.4	335.3	325.6
62.5°	392.0	384.2	376.4	368.6	360.8	350.8	338.5	326.2	313.9	301.7	292.6
65°	343.8	335.7	327.6	319.6	311.6	301.6	289.5	277.6	265.6	253.7	245.6
67.5°	293.7	286.1	278.3	270.6	262.8	253.5	242.3	231.2	220.1	209.0	202.0
70°	262.1	254.2	246.3	238.4	230.6	221.3	210.6	199.9	189.3	178.6	172.5
72.5°	228.4	221.3	214.1	207.0	199.9	191.3	181.3	171.1	161.1	151.0	145.7
75°	182.8	175.9	169.0	162.1	155.1	147.3	138.5	129.7	120.9	112.1	107.7
77.5°	136.7	130.8	124.9	119.1	113.1	106.6	99.6	92.4	85.3	78.2	75.7
80°	107.0	101.6	96.2	90.7	85.3	79.8	74.1	68.5	62.9	57.3	56.7
82.5°	81.4	76.4	71.5	66.5	61.5	57.4	54.2	50.9	47.7	44.5	44.0
85°	45.5	41.7	38.0	34.3	30.5	28.4	27.8	27.3	26.7	26.1	25.7
87.5°	15.8	14.8	13.8	12.8	11.9	11.4	11.4	11.4	11.4	11.4	11.4
90°	1.3	2.5	3.6	4.7	5.8	6.7	7.5	8.3	9.1	9.9	10.5
92.5°	5.7	5.8	5.8	5.9	5.9	6.3	7.2	8.0	8.8	9.6	10.2
95°	24.9	21.5	18.1	14.6	11.2	9.5	9.7	9.7	9.8	9.9	10.5
97.5°	52.8	54.9	57.0	59.2	61.3	56.7	45.6	34.4	23.1	12.0	12.0
100°	74.1	75.9	77.7	79.5	81.4	75.3	61.5	47.6	33.7	19.9	18.1
102.5°	98.0	99.3	100.6	102.0	103.3	103.1	101.2	99.4	97.6	95.8	77.4
105°	136.0	136.7	137.2	137.8	138.4	138.9	139.5	140.0	140.5	141.0	141.9
107.5°	171.3	171.7	172.0	172.2	172.5	173.0	173.7	174.4	175.1	175.8	176.3
110°	195.2	195.5	195.8	196.1	196.4	196.9	197.5	198.0	198.7	199.3	199.5



TEST NUMBER: P332934-927

CATALOG NUMBER: SA4XXRDIP-C795D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.3	218.9	219.4	220.0	220.5	220.9	221.2	221.5	221.8	222.0	222.0
115°	254.0	254.3	254.5	254.8	255.2	255.2	255.2	255.1	254.9	254.8	255.1
117.5°	286.1	286.5	286.8	287.2	287.6	288.0	288.2	288.4	288.6	288.8	288.8
120°	307.8	308.2	308.6	309.0	309.3	309.5	309.4	309.3	309.2	309.1	309.3
122.5°	328.0	328.2	328.4	328.7	328.9	329.2	329.3	329.4	329.5	329.7	329.8
125°	357.0	357.4	357.8	358.2	358.6	358.7	358.5	358.3	358.1	357.9	358.2
127.5°	384.4	384.5	384.7	384.8	384.8	385.2	385.6	386.0	386.5	387.0	386.9
130°	402.2	402.3	402.3	402.5	402.6	402.7	403.1	403.4	403.7	404.0	404.1
132.5°	418.4	418.6	418.8	419.0	419.1	419.5	419.9	420.2	420.6	421.0	421.0
135°	442.8	442.8	442.7	442.5	442.4	442.6	443.0	443.4	443.8	444.2	444.4
137.5°	464.5	464.5	464.5	464.5	464.6	464.9	465.2	465.7	466.2	466.6	466.8
140°	478.6	478.7	479.0	479.1	479.3	479.5	479.7	480.0	480.1	480.4	480.6
142.5°	491.2	491.5	491.9	492.3	492.7	492.9	493.0	493.1	493.2	493.4	493.6
145°	510.6	511.0	511.2	511.5	511.8	512.0	512.0	512.0	512.0	512.0	512.1
147.5°	526.1	526.6	527.2	527.8	528.3	528.5	528.5	528.4	528.2	528.1	528.2
150°	537.3	537.7	538.1	538.5	538.9	539.1	538.9	538.8	538.8	538.6	538.6
152.5°	546.7	547.0	547.3	547.6	548.0	548.0	547.9	547.7	547.5	547.3	547.5
155°	559.9	560.0	560.1	560.2	560.3	560.2	559.9	559.6	559.3	559.0	559.4
157.5°	571.0	570.9	570.8	570.8	570.8	570.5	570.2	569.9	569.5	569.2	569.7
160°	577.5	577.2	576.9	576.6	576.3	576.1	576.0	575.9	575.8	575.7	576.3
162.5°	583.3	582.9	582.5	582.2	581.8	581.5	581.4	581.3	581.2	581.1	581.7
165°	590.6	590.1	589.6	589.1	588.6	588.4	588.4	588.4	588.4	588.4	589.1
167.5°	596.4	595.9	595.3	594.8	594.3	594.0	594.0	593.9	593.8	593.7	594.7
170°	599.7	599.0	598.4	597.9	597.2	597.0	597.1	597.1	597.3	597.4	598.2
172.5°	601.8	601.2	600.6	600.0	599.4	599.1	599.3	599.4	599.4	599.5	600.4
175°	604.2	603.6	602.9	602.4	601.7	601.5	601.6	601.7	601.8	601.9	602.8
177.5°	605.2	604.7	604.1	603.6	603.0	602.8	602.9	603.1	603.2	603.4	604.1
180°	604.2	604.2	604.2	604.2	604.2	604.2	604.2	604.2	604.2	604.2	604.2



TEST NUMBER: P332934-927

CATALOG NUMBER: SA4XXRDIP-C795D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1096.4	1098.0	1099.6	1100.4	1100.3	1100.1	1099.9	1099.8
5°	1089.0	1090.9	1092.8	1093.5	1093.1	1092.8	1092.4	1092.0
7.5°	1074.5	1075.8	1077.0	1077.2	1076.7	1076.0	1075.5	1074.8
10°	1061.5	1062.2	1063.0	1063.0	1062.2	1061.5	1060.7	1060.0
12.5°	1045.4	1045.8	1046.3	1046.0	1045.0	1043.9	1042.8	1041.8
15°	1017.2	1016.8	1016.4	1015.6	1014.2	1012.9	1011.6	1010.3
17.5°	983.1	982.1	981.0	979.5	977.5	975.5	973.5	971.5
20°	959.3	957.7	956.2	954.3	951.9	949.4	947.0	944.6
22.5°	932.9	930.6	928.4	926.2	924.2	922.3	920.3	918.3
25°	890.2	887.0	883.8	881.3	879.4	877.6	875.7	873.8
27.5°	846.7	842.8	838.8	835.5	832.8	830.1	827.4	824.7
30°	815.6	810.9	806.2	802.3	799.4	796.4	793.4	790.4
32.5°	783.7	778.3	772.9	768.7	765.9	763.0	760.2	757.3
35°	736.3	730.0	723.7	718.7	715.4	712.0	708.6	705.3
37.5°	685.5	678.3	671.2	666.0	662.7	659.3	655.9	652.5
40°	651.6	643.7	635.9	630.3	626.9	623.5	620.2	616.8
42.5°	618.3	610.3	602.3	596.5	592.9	589.5	586.0	582.4
45°	567.3	558.1	548.9	542.6	539.2	535.9	532.5	529.2
47.5°	515.9	506.4	496.9	490.2	486.6	482.8	479.1	475.4
50°	481.8	472.5	463.0	456.6	453.0	449.5	445.9	442.4
52.5°	447.8	438.3	428.7	422.2	418.4	414.7	411.1	407.3
55°	397.6	387.9	378.2	371.5	368.0	364.4	360.8	357.3
57.5°	348.6	338.7	328.8	322.6	319.9	317.2	314.5	311.8
60°	315.9	306.2	296.4	290.0	287.1	284.1	281.1	278.1
62.5°	283.7	274.7	265.7	260.0	257.6	255.2	252.8	250.4
65°	237.5	229.5	221.4	216.3	214.0	211.8	209.5	207.3
67.5°	195.1	188.2	181.3	176.6	174.1	171.6	169.1	166.7
70°	166.3	160.1	153.9	149.9	148.1	146.2	144.3	142.4
72.5°	140.5	135.1	129.8	126.4	124.7	122.9	121.2	119.5
75°	103.5	99.2	94.8	92.1	91.0	89.9	88.7	87.6
77.5°	73.2	70.7	68.1	66.7	66.4	66.1	65.8	65.4
80°	56.2	55.6	55.1	54.7	54.5	54.3	54.1	53.9
82.5°	43.6	43.3	42.9	42.5	42.4	42.1	42.0	41.8
85°	25.3	25.0	24.6	24.4	24.4	24.4	24.4	24.4
87.5°	11.3	11.3	11.3	11.4	11.6	11.8	12.0	12.1
90°	11.2	11.7	12.4	12.8	13.0	13.2	13.4	13.5
92.5°	10.8	11.4	12.0	12.3	12.4	12.4	12.4	12.4
95°	11.2	11.7	12.4	12.7	12.8	12.9	13.0	13.1
97.5°	12.0	12.1	12.2	12.3	12.4	12.4	12.5	12.7
100°	16.5	14.7	13.1	12.3	12.4	12.4	12.5	12.7
102.5°	58.9	40.6	22.1	12.9	13.0	13.0	13.0	13.0
105°	142.8	143.7	144.6	143.2	139.7	136.0	132.4	128.8
107.5°	176.7	177.1	177.5	177.9	178.3	178.7	179.1	179.5
110°	199.7	199.9	200.1	200.3	200.7	200.9	201.2	201.5



TEST NUMBER: P332934-927

CATALOG NUMBER: SA4XXRDIP-C795D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	222.0	222.0	221.9	222.0	222.4	222.8	223.2	223.6
115°	255.2	255.5	255.6	255.8	255.8	255.8	255.8	255.8
117.5°	288.8	288.8	288.7	288.7	288.6	288.6	288.5	288.5
120°	309.5	309.7	309.9	309.9	309.7	309.5	309.3	309.1
122.5°	329.9	330.0	330.2	330.1	329.9	329.7	329.5	329.3
125°	358.5	358.8	359.1	359.3	359.4	359.5	359.6	359.7
127.5°	386.9	386.8	386.7	386.7	386.6	386.5	386.4	386.3
130°	404.2	404.3	404.4	404.4	404.4	404.4	404.4	404.4
132.5°	421.2	421.3	421.4	421.4	421.3	421.2	421.1	421.0
135°	444.6	444.8	445.0	445.2	445.4	445.6	445.8	446.0
137.5°	467.1	467.3	467.5	467.5	467.5	467.5	467.4	467.3
140°	480.9	481.3	481.6	481.7	481.9	482.0	482.0	482.1
142.5°	493.8	494.0	494.2	494.4	494.4	494.4	494.4	494.5
145°	512.1	512.3	512.4	512.5	512.7	512.9	513.2	513.3
147.5°	528.3	528.4	528.5	528.5	528.7	528.8	528.9	528.9
150°	538.6	538.6	538.6	538.7	538.8	538.9	539.0	539.1
152.5°	547.6	547.8	548.0	548.0	548.0	547.9	547.8	547.8
155°	559.8	560.2	560.5	560.6	560.3	560.0	559.8	559.4
157.5°	570.2	570.8	571.2	571.2	570.8	570.2	569.7	569.2
160°	576.9	577.5	578.1	578.1	577.5	576.9	576.3	575.7
162.5°	582.3	582.9	583.5	583.5	582.8	582.1	581.5	580.7
165°	589.9	590.7	591.6	591.5	590.6	589.7	588.8	587.9
167.5°	595.6	596.4	597.3	597.2	596.3	595.2	594.2	593.3
170°	599.0	599.8	600.6	600.5	599.5	598.5	597.5	596.5
172.5°	601.2	602.0	602.8	602.6	601.6	600.5	599.4	598.3
175°	603.7	604.6	605.5	605.4	604.2	602.9	601.7	600.6
177.5°	604.8	605.4	606.0	605.9	604.9	604.0	602.9	602.0
180°	604.2	604.2	604.2	604.2	604.2	604.2	604.2	604.2

(END OF REPORT)