

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332941-927

Luminaire Tested: **SA4XXRDIP-C795D810U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332941-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4766.6 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332941-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332941-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53	53	53	53	
1	99	95	91	87	91	88	85	82	75	73	71	64	62	60	53	52	51	46	46	46	46	
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39	39	39	39	
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33	33	33	33	
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	37	34	32	29	29	29	29	
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28	25	25	25	25	
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25	22	22	22	22	
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20	20	20	20	
8	55	43	35	30	51	40	33	28	35	30	26	30	26	23	26	22	20	18	18	18	18	
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18	16	16	16	16	
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15	15	15	15	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8884	8884	8884
5°	8904	8795	8849
10°	8848	8689	8689
15°	8747	8507	8444
20°	8607	8267	8115
25°	8429	7986	7783
30°	8255	7690	7368
35°	8064	7383	6951
40°	7832	7032	6500
45°	7618	6687	6042
50°	7376	6286	5556
55°	7116	5871	5029
60°	6830	5414	4490
65°	6567	4846	3960
70°	6187	4216	3361
75°	5702	3497	2732
80°	4974	2664	2506
85°	4215	2418	2260



TEST NUMBER: P332941-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.4	2.2
10°-20°	288.3	6.0
20°-30°	416.3	8.7
30°-40°	471.8	9.9
40°-50°	455.6	9.6
50°-60°	378.9	7.9
60°-70°	261.6	5.5
70°-80°	132.6	2.8
80°-90°	36.4	0.8
90°-100°	52.8	1.1
100°-110°	156.5	3.3
110°-120°	265.6	5.6
120°-130°	350.2	7.3
130°-140°	393.3	8.3
140°-150°	386.4	8.1
150°-160°	325.0	6.8
160°-170°	216.2	4.5
170°-180°	75.7	1.6
0°-30°	807.9	16.9
0°-40°	1279.7	26.8
0°-60°	2114.3	44.4
0°-90°	2544.9	53.4
90°-120°	474.9	10.0
90°-150°	1604.7	33.7
90°-180°	2222.0	46.6
0°-180°	4766.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1099	1095	1085	1093	1092	104
15°	1047	1038	1018	1016	1010	295
25°	946	930	896	883	874	436
35°	818	790	749	721	705	511
45°	667	635	586	546	529	514
55°	506	471	417	375	357	452
65°	344	307	254	219	207	339
75°	183	151	112	93	88	193
85°	46	29	26	24	24	51
90°	2	9	14	17	19	4
95°	37	43	47	49	49	41
105°	144	145	147	149	151	153
115°	270	270	269	268	268	266
125°	393	393	393	391	390	350
135°	507	511	511	510	508	392
145°	616	619	619	619	617	386
155°	706	706	705	708	705	325
165°	769	767	766	769	767	217
175°	800	797	796	800	796	76
180°	801	801	801	801	801	



TEST NUMBER: P332941-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1103.2	1102.6	1101.9	1101.4	1100.7	1099.6	1098.0	1096.4	1094.7	1093.1	1094.7
5°	1098.8	1098.0	1097.3	1096.5	1095.7	1094.3	1092.0	1089.8	1087.5	1085.3	1087.2
7.5°	1088.9	1088.1	1087.3	1086.5	1085.7	1083.9	1080.9	1078.0	1075.1	1072.1	1073.3
10°	1079.4	1078.5	1077.5	1076.6	1075.6	1073.5	1070.2	1066.8	1063.4	1060.0	1060.7
12.5°	1067.2	1066.2	1065.1	1064.0	1063.0	1060.4	1056.5	1052.4	1048.5	1044.5	1045.0
15°	1046.6	1044.9	1043.1	1041.5	1039.8	1036.6	1031.9	1027.2	1022.5	1017.9	1017.5
17.5°	1021.4	1019.0	1016.5	1014.2	1011.7	1007.7	1002.0	996.4	990.8	985.2	984.1
20°	1001.9	999.4	997.0	994.6	992.1	987.8	981.4	975.0	968.6	962.3	960.8
22.5°	980.3	977.6	974.9	972.1	969.4	964.6	957.7	950.9	944.1	937.3	935.1
25°	946.3	942.9	939.5	936.1	932.8	927.2	919.6	911.9	904.2	896.5	893.3
27.5°	910.5	906.3	902.1	897.9	893.6	887.4	879.2	871.0	862.8	854.6	850.6
30°	885.6	880.9	876.2	871.6	866.9	860.2	851.4	842.6	833.7	824.9	820.2
32.5°	859.3	854.1	848.7	843.4	838.2	831.0	821.9	812.8	803.7	794.6	789.2
35°	818.2	812.2	806.2	800.2	794.2	786.6	777.2	767.8	758.4	749.1	742.8
37.5°	774.2	768.0	761.8	755.7	749.5	741.2	730.9	720.5	710.1	699.7	692.6
40°	743.2	737.0	730.9	724.7	718.5	710.0	699.3	688.7	678.0	667.3	659.5
42.5°	713.5	707.0	700.6	694.1	687.6	678.8	667.7	656.6	645.5	634.3	626.3
45°	667.3	660.4	653.5	646.6	639.6	630.6	619.3	608.1	596.8	585.7	576.5
47.5°	619.6	612.5	605.4	598.2	591.0	581.6	570.0	558.3	546.6	534.9	525.4
50°	587.3	580.0	572.7	565.4	558.1	548.4	536.5	524.5	512.5	500.5	491.2
52.5°	554.3	547.2	540.0	532.8	525.7	515.9	503.7	491.4	479.1	466.8	457.3
55°	505.6	498.0	490.6	483.1	475.6	465.8	453.6	441.4	429.3	417.1	407.3
57.5°	457.4	449.6	441.8	434.0	426.2	416.3	404.3	392.4	380.4	368.4	358.5
60°	423.0	415.5	408.1	400.5	393.0	383.3	371.3	359.3	347.4	335.3	325.6
62.5°	392.0	384.2	376.4	368.6	360.8	350.8	338.5	326.2	313.9	301.7	292.6
65°	343.8	335.7	327.6	319.6	311.6	301.6	289.5	277.6	265.6	253.7	245.6
67.5°	293.7	286.1	278.3	270.6	262.8	253.5	242.3	231.2	220.1	209.0	202.0
70°	262.1	254.2	246.3	238.4	230.6	221.3	210.6	199.9	189.3	178.6	172.5
72.5°	228.4	221.3	214.1	207.0	199.9	191.3	181.3	171.1	161.1	151.0	145.7
75°	182.8	175.9	169.0	162.1	155.1	147.3	138.5	129.7	120.9	112.1	107.7
77.5°	136.7	130.8	124.9	119.1	113.1	106.6	99.6	92.4	85.3	78.2	75.7
80°	107.0	101.6	96.2	90.7	85.3	79.8	74.1	68.5	62.9	57.3	56.7
82.5°	81.4	76.4	71.5	66.5	61.5	57.4	54.2	50.9	47.7	44.5	44.0
85°	45.5	41.7	38.0	34.3	30.5	28.4	27.8	27.3	26.7	26.1	25.7
87.5°	15.8	15.0	14.1	13.2	12.3	11.9	12.0	12.0	12.1	12.2	12.2
90°	1.8	3.4	4.9	6.4	7.9	9.2	10.3	11.4	12.5	13.6	14.4
92.5°	13.2	15.0	16.7	18.5	20.2	21.5	22.2	23.0	23.8	24.6	25.0
95°	37.2	38.4	39.6	40.9	42.1	43.3	44.2	45.2	46.1	47.1	47.5
97.5°	64.9	65.9	66.9	67.9	68.8	69.9	71.1	72.2	73.3	74.5	74.9
100°	86.7	87.2	87.8	88.3	88.9	89.8	91.0	92.3	93.5	94.7	95.1
102.5°	109.5	109.7	110.0	110.2	110.4	111.1	112.2	113.3	114.5	115.6	116.0
105°	144.3	144.4	144.6	144.7	144.9	145.2	145.8	146.3	146.9	147.4	147.8
107.5°	180.9	181.0	181.2	181.3	181.5	181.6	181.7	181.8	181.9	182.0	182.4
110°	205.7	205.9	206.1	206.4	206.7	206.8	206.7	206.5	206.4	206.2	206.0



TEST NUMBER: P332941-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.4	231.4	231.5	231.6	231.6	231.5	231.2	231.0	230.8	230.5	230.4
115°	270.1	270.1	270.1	270.1	270.1	269.9	269.6	269.3	269.0	268.8	268.6
117.5°	306.4	306.6	306.7	306.7	306.9	306.8	306.7	306.4	306.3	306.1	305.6
120°	330.7	331.3	331.8	332.4	333.0	333.0	332.6	332.2	331.8	331.4	330.7
122.5°	356.0	356.2	356.4	356.6	356.9	356.9	356.7	356.5	356.3	356.1	355.6
125°	393.2	393.2	393.2	393.2	393.2	393.2	393.1	392.9	392.8	392.7	392.4
127.5°	427.1	427.5	427.9	428.3	428.7	428.8	428.6	428.4	428.2	427.9	427.7
130°	450.8	451.3	451.7	452.1	452.5	452.7	452.7	452.7	452.7	452.7	452.4
132.5°	475.2	475.5	475.8	476.0	476.3	476.4	476.3	476.3	476.1	476.0	475.7
135°	507.2	508.0	508.9	509.7	510.6	511.0	511.0	511.0	511.0	511.0	510.6
137.5°	542.2	542.6	542.9	543.3	543.7	544.0	544.2	544.5	544.6	544.9	544.5
140°	565.5	565.7	566.0	566.3	566.6	566.6	566.6	566.6	566.6	566.6	566.6
142.5°	586.8	587.0	587.3	587.6	587.9	588.0	587.8	587.7	587.6	587.5	587.5
145°	616.2	616.8	617.3	617.9	618.5	618.8	618.9	619.0	619.2	619.3	619.2
147.5°	645.5	646.1	646.7	647.5	648.1	648.4	648.2	648.2	648.0	647.9	647.8
150°	663.3	663.8	664.4	665.0	665.5	665.7	665.7	665.7	665.7	665.7	665.7
152.5°	680.2	680.5	680.8	681.1	681.4	681.7	681.8	681.9	682.0	682.1	682.5
155°	706.0	706.0	706.0	706.0	706.0	705.9	705.8	705.7	705.5	705.4	705.9
157.5°	727.9	727.5	727.3	727.1	726.8	726.7	726.7	726.7	726.6	726.6	727.0
160°	740.7	740.5	740.5	740.3	740.1	740.0	739.9	739.7	739.6	739.5	739.9
162.5°	752.6	752.3	751.9	751.5	751.1	750.9	750.8	750.7	750.5	750.4	751.1
165°	768.6	768.2	767.8	767.3	766.9	766.6	766.3	766.0	765.7	765.5	766.3
167.5°	780.9	780.2	779.7	779.1	778.6	778.2	778.2	778.3	778.3	778.3	779.2
170°	787.7	787.1	786.4	785.7	785.1	784.7	784.9	785.1	785.1	785.3	786.1
172.5°	792.7	792.2	791.5	791.0	790.4	790.1	790.2	790.2	790.2	790.3	791.2
175°	799.5	798.8	798.1	797.5	796.8	796.4	796.2	796.1	796.0	795.8	796.8
177.5°	801.8	801.2	800.7	800.1	799.5	799.3	799.3	799.3	799.3	799.3	800.0
180°	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7



TEST NUMBER: P332941-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1096.4	1098.0	1099.6	1100.4	1100.3	1100.1	1099.9	1099.8
5°	1089.0	1090.9	1092.8	1093.5	1093.1	1092.8	1092.4	1092.0
7.5°	1074.5	1075.8	1077.0	1077.2	1076.7	1076.0	1075.5	1074.8
10°	1061.5	1062.2	1063.0	1063.0	1062.2	1061.5	1060.7	1060.0
12.5°	1045.4	1045.8	1046.3	1046.0	1045.0	1043.9	1042.8	1041.8
15°	1017.2	1016.8	1016.4	1015.6	1014.2	1012.9	1011.6	1010.3
17.5°	983.1	982.1	981.0	979.5	977.5	975.5	973.5	971.5
20°	959.3	957.7	956.2	954.3	951.9	949.4	947.0	944.6
22.5°	932.9	930.6	928.4	926.2	924.2	922.3	920.3	918.3
25°	890.2	887.0	883.8	881.3	879.4	877.6	875.7	873.8
27.5°	846.7	842.8	838.8	835.5	832.8	830.1	827.4	824.7
30°	815.6	810.9	806.2	802.3	799.4	796.4	793.4	790.4
32.5°	783.7	778.3	772.9	768.7	765.9	763.0	760.2	757.3
35°	736.3	730.0	723.7	718.7	715.4	712.0	708.6	705.3
37.5°	685.5	678.3	671.2	666.0	662.7	659.3	655.9	652.5
40°	651.6	643.7	635.9	630.3	626.9	623.5	620.2	616.8
42.5°	618.3	610.3	602.3	596.5	592.9	589.5	586.0	582.4
45°	567.3	558.1	548.9	542.6	539.2	535.9	532.5	529.2
47.5°	515.9	506.4	496.9	490.2	486.6	482.8	479.1	475.4
50°	481.8	472.5	463.0	456.6	453.0	449.5	445.9	442.4
52.5°	447.8	438.3	428.7	422.2	418.4	414.7	411.1	407.3
55°	397.6	387.9	378.2	371.5	368.0	364.4	360.8	357.3
57.5°	348.6	338.7	328.8	322.6	319.9	317.2	314.5	311.8
60°	315.9	306.2	296.4	290.0	287.1	284.1	281.1	278.1
62.5°	283.7	274.7	265.7	260.0	257.6	255.2	252.8	250.4
65°	237.5	229.5	221.4	216.3	214.0	211.8	209.5	207.3
67.5°	195.1	188.2	181.3	176.6	174.1	171.6	169.1	166.7
70°	166.3	160.1	153.9	149.9	148.1	146.2	144.3	142.4
72.5°	140.5	135.1	129.8	126.4	124.7	122.9	121.2	119.5
75°	103.5	99.2	94.8	92.1	91.0	89.9	88.7	87.6
77.5°	73.2	70.7	68.1	66.7	66.4	66.1	65.8	65.4
80°	56.2	55.6	55.1	54.7	54.5	54.3	54.1	53.9
82.5°	43.6	43.3	42.9	42.5	42.4	42.1	42.0	41.8
85°	25.3	25.0	24.6	24.4	24.4	24.4	24.4	24.4
87.5°	12.2	12.2	12.2	12.4	12.5	12.8	12.9	13.2
90°	15.3	16.1	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	25.5	26.0	26.5	26.9	27.0	27.2	27.3	27.5
95°	47.9	48.3	48.7	49.0	49.0	49.0	49.0	49.0
97.5°	75.4	75.9	76.4	76.7	76.7	76.7	76.7	76.7
100°	95.3	95.6	95.9	96.0	96.0	96.0	96.0	96.0
102.5°	116.4	116.7	117.1	117.3	117.5	117.6	117.7	117.8
105°	148.2	148.6	149.0	149.5	149.9	150.3	150.7	151.1
107.5°	182.8	183.1	183.5	183.7	183.6	183.6	183.6	183.5
110°	205.7	205.4	205.1	205.2	205.7	206.0	206.4	206.8



TEST NUMBER: P332941-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	230.4	230.4	230.3	230.3	230.4	230.4	230.5	230.6
115°	268.5	268.4	268.2	268.1	268.0	267.8	267.7	267.5
117.5°	305.1	304.7	304.2	303.8	303.6	303.2	303.0	302.7
120°	329.9	329.2	328.6	328.4	328.7	328.9	329.2	329.5
122.5°	355.1	354.7	354.3	353.8	353.2	352.8	352.3	351.8
125°	392.1	391.8	391.6	391.3	391.0	390.7	390.5	390.1
127.5°	427.4	427.1	426.8	426.6	426.4	426.2	426.0	425.7
130°	452.2	451.9	451.6	451.2	450.7	450.1	449.6	449.0
132.5°	475.5	475.2	474.9	474.7	474.4	474.2	474.0	473.8
135°	510.4	510.1	509.8	509.5	509.1	508.7	508.3	507.9
137.5°	544.2	543.8	543.4	543.3	543.4	543.4	543.5	543.7
140°	566.4	566.3	566.1	566.0	565.9	565.7	565.5	565.5
142.5°	587.4	587.4	587.4	587.3	587.3	587.3	587.2	587.2
145°	619.0	618.9	618.8	618.5	618.1	617.7	617.3	616.9
147.5°	647.7	647.6	647.5	647.4	647.2	647.1	647.0	646.8
150°	665.7	665.7	665.7	665.7	665.6	665.4	665.3	665.1
152.5°	682.8	683.1	683.4	683.4	683.1	682.7	682.4	682.0
155°	706.5	707.0	707.6	707.6	707.0	706.5	705.9	705.4
157.5°	727.4	727.9	728.3	728.2	727.8	727.3	726.8	726.4
160°	740.3	740.7	741.1	741.0	740.3	739.6	738.9	738.2
162.5°	751.9	752.6	753.4	753.4	752.7	752.0	751.3	750.6
165°	767.1	767.9	768.8	768.9	768.3	767.8	767.2	766.8
167.5°	780.0	780.9	781.6	781.6	780.8	779.9	779.1	778.2
170°	787.0	787.7	788.6	788.5	787.6	786.6	785.6	784.7
172.5°	792.1	793.1	794.0	794.0	793.1	792.0	791.1	790.1
175°	797.7	798.7	799.7	799.7	798.7	797.7	796.8	795.8
177.5°	800.8	801.6	802.4	802.3	801.5	800.6	799.7	798.8
180°	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7

(END OF REPORT)