

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332942-927

Luminaire Tested: **SA4XXRDIP-C795D810U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332942-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4837.3 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332942-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332942-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38
3	82	73	66	60	76	68	62	56	58	54	50	49	46	43	41	39	36	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	33	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	25	22
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8884	8884	8884
5°	8904	8795	8849
10°	8848	8689	8689
15°	8747	8507	8444
20°	8607	8267	8115
25°	8429	7986	7783
30°	8255	7690	7368
35°	8064	7383	6951
40°	7832	7032	6500
45°	7618	6687	6042
50°	7376	6286	5556
55°	7116	5871	5029
60°	6830	5414	4490
65°	6567	4846	3960
70°	6187	4216	3361
75°	5702	3497	2732
80°	4974	2664	2506
85°	4215	2418	2260



TEST NUMBER: P332942-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.4	2.1
10°-20°	288.3	6.0
20°-30°	416.3	8.6
30°-40°	471.8	9.8
40°-50°	455.6	9.4
50°-60°	378.9	7.8
60°-70°	261.6	5.4
70°-80°	132.6	2.7
80°-90°	35.8	0.7
90°-100°	227.7	4.7
100°-110°	474.0	9.8
110°-120°	424.5	8.8
120°-130°	357.1	7.4
130°-140°	297.7	6.2
140°-150°	227.5	4.7
150°-160°	159.9	3.3
160°-170°	94.0	1.9
170°-180°	30.6	0.6
0°-30°	807.9	16.7
0°-40°	1279.7	26.5
0°-60°	2114.3	43.7
0°-90°	2544.3	52.6
90°-120°	1126.2	23.3
90°-150°	2008.5	41.5
90°-180°	2293.0	47.4
0°-180°	4837.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1099	1095	1085	1093	1092	104
15°	1047	1038	1018	1016	1010	295
25°	946	930	896	883	874	436
35°	818	790	749	721	705	511
45°	667	635	586	546	529	514
55°	506	471	417	375	357	452
65°	344	307	254	219	207	339
75°	183	151	112	93	88	193
85°	46	29	26	24	24	51
90°	1	5	11	12	13	3
95°	20	64	505	250	151	23
105°	72	105	406	875	872	77
115°	128	160	362	696	837	127
125°	178	211	360	592	668	158
135°	211	251	357	526	597	163
145°	243	279	356	444	488	153
155°	277	299	346	392	408	128
165°	302	311	331	351	356	85
175°	315	315	318	322	321	30
180°	315	315	315	315	315	



TEST NUMBER: P332942-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1103.2	1102.6	1101.9	1101.4	1100.7	1099.6	1098.0	1096.4	1094.7	1093.1	1094.7
5°	1098.8	1098.0	1097.3	1096.5	1095.7	1094.3	1092.0	1089.8	1087.5	1085.3	1087.2
7.5°	1088.9	1088.1	1087.3	1086.5	1085.7	1083.9	1080.9	1078.0	1075.1	1072.1	1073.3
10°	1079.4	1078.5	1077.5	1076.6	1075.6	1073.5	1070.2	1066.8	1063.4	1060.0	1060.7
12.5°	1067.2	1066.2	1065.1	1064.0	1063.0	1060.4	1056.5	1052.4	1048.5	1044.5	1045.0
15°	1046.6	1044.9	1043.1	1041.5	1039.8	1036.6	1031.9	1027.2	1022.5	1017.9	1017.5
17.5°	1021.4	1019.0	1016.5	1014.2	1011.7	1007.7	1002.0	996.4	990.8	985.2	984.1
20°	1001.9	999.4	997.0	994.6	992.1	987.8	981.4	975.0	968.6	962.3	960.8
22.5°	980.3	977.6	974.9	972.1	969.4	964.6	957.7	950.9	944.1	937.3	935.1
25°	946.3	942.9	939.5	936.1	932.8	927.2	919.6	911.9	904.2	896.5	893.3
27.5°	910.5	906.3	902.1	897.9	893.6	887.4	879.2	871.0	862.8	854.6	850.6
30°	885.6	880.9	876.2	871.6	866.9	860.2	851.4	842.6	833.7	824.9	820.2
32.5°	859.3	854.1	848.7	843.4	838.2	831.0	821.9	812.8	803.7	794.6	789.2
35°	818.2	812.2	806.2	800.2	794.2	786.6	777.2	767.8	758.4	749.1	742.8
37.5°	774.2	768.0	761.8	755.7	749.5	741.2	730.9	720.5	710.1	699.7	692.6
40°	743.2	737.0	730.9	724.7	718.5	710.0	699.3	688.7	678.0	667.3	659.5
42.5°	713.5	707.0	700.6	694.1	687.6	678.8	667.7	656.6	645.5	634.3	626.3
45°	667.3	660.4	653.5	646.6	639.6	630.6	619.3	608.1	596.8	585.7	576.5
47.5°	619.6	612.5	605.4	598.2	591.0	581.6	570.0	558.3	546.6	534.9	525.4
50°	587.3	580.0	572.7	565.4	558.1	548.4	536.5	524.5	512.5	500.5	491.2
52.5°	554.3	547.2	540.0	532.8	525.7	515.9	503.7	491.4	479.1	466.8	457.3
55°	505.6	498.0	490.6	483.1	475.6	465.8	453.6	441.4	429.3	417.1	407.3
57.5°	457.4	449.6	441.8	434.0	426.2	416.3	404.3	392.4	380.4	368.4	358.5
60°	423.0	415.5	408.1	400.5	393.0	383.3	371.3	359.3	347.4	335.3	325.6
62.5°	392.0	384.2	376.4	368.6	360.8	350.8	338.5	326.2	313.9	301.7	292.6
65°	343.8	335.7	327.6	319.6	311.6	301.6	289.5	277.6	265.6	253.7	245.6
67.5°	293.7	286.1	278.3	270.6	262.8	253.5	242.3	231.2	220.1	209.0	202.0
70°	262.1	254.2	246.3	238.4	230.6	221.3	210.6	199.9	189.3	178.6	172.5
72.5°	228.4	221.3	214.1	207.0	199.9	191.3	181.3	171.1	161.1	151.0	145.7
75°	182.8	175.9	169.0	162.1	155.1	147.3	138.5	129.7	120.9	112.1	107.7
77.5°	136.7	130.8	124.9	119.1	113.1	106.6	99.6	92.4	85.3	78.2	75.7
80°	107.0	101.6	96.2	90.7	85.3	79.8	74.1	68.5	62.9	57.3	56.7
82.5°	81.4	76.4	71.5	66.5	61.5	57.4	54.2	50.9	47.7	44.5	44.0
85°	45.5	41.7	38.0	34.3	30.5	28.4	27.8	27.3	26.7	26.1	25.7
87.5°	15.6	14.7	13.9	12.8	11.7	11.0	11.6	11.5	11.6	11.6	11.4
90°	0.6	1.8	3.7	4.4	5.0	5.0	8.6	8.6	9.9	11.2	10.5
92.5°	7.1	10.3	16.1	23.7	32.7	45.6	77.1	125.1	172.0	196.5	163.7
95°	20.4	22.3	28.5	36.5	51.4	77.4	131.3	232.9	381.0	504.9	519.1
97.5°	36.7	36.7	42.0	49.4	62.2	84.0	125.5	209.4	356.6	531.7	652.1
100°	47.1	47.1	51.4	58.9	70.6	90.5	127.0	197.0	323.4	498.0	656.6
102.5°	57.0	58.0	61.8	68.8	80.0	98.9	131.9	193.5	301.0	455.9	619.4
105°	72.5	74.3	77.4	84.8	96.0	114.0	143.7	195.1	281.9	406.3	551.9
107.5°	89.6	90.8	93.9	101.8	112.5	130.2	157.5	204.3	278.4	378.6	497.4
110°	101.0	102.2	105.3	112.7	123.9	140.6	167.9	211.2	279.3	369.2	470.2



TEST NUMBER: P332942-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	111.9	113.1	116.7	123.7	134.8	151.5	177.8	218.6	282.3	364.7	454.8
115°	127.6	129.4	133.8	140.0	151.8	168.5	193.3	230.4	288.0	362.3	440.4
117.5°	143.9	145.7	149.6	156.4	167.4	184.7	208.3	242.4	294.1	361.7	434.0
120°	154.9	156.1	160.4	167.2	177.8	195.1	218.6	250.9	298.6	361.7	430.5
122.5°	164.8	166.0	170.3	176.7	188.1	205.0	228.5	258.8	303.0	361.2	426.5
125°	177.8	180.2	183.9	190.8	202.6	219.9	242.2	270.7	309.7	360.5	419.9
127.5°	189.3	191.3	195.7	203.5	215.8	233.3	254.8	281.0	315.1	359.2	411.1
130°	195.7	198.2	203.2	212.5	224.3	242.2	263.2	287.4	319.0	358.6	405.8
132.5°	202.2	204.1	210.6	219.4	232.2	249.1	270.2	293.8	322.5	358.1	400.8
135°	211.2	213.7	219.9	230.4	243.4	259.5	280.0	302.3	327.6	357.4	393.3
137.5°	220.3	222.6	229.4	239.5	252.9	268.3	287.4	308.2	330.7	357.3	386.9
140°	226.7	228.5	235.4	245.9	258.9	273.8	292.4	312.2	333.3	356.8	383.4
142.5°	233.6	235.5	241.9	251.8	264.4	278.8	296.8	315.1	335.3	356.8	380.5
145°	243.4	245.3	251.5	260.2	272.0	285.6	301.7	318.4	336.4	355.5	375.3
147.5°	254.4	255.1	260.5	269.4	279.2	291.5	306.7	321.2	337.0	353.3	370.8
150°	261.4	262.1	267.0	274.4	283.7	295.5	309.1	322.7	337.0	351.8	367.3
152.5°	267.8	268.0	272.9	279.9	288.2	299.0	311.1	323.7	336.0	349.4	363.4
155°	276.9	277.5	281.2	287.4	294.2	303.5	314.0	324.6	334.5	345.6	357.4
157.5°	285.7	285.7	289.1	294.0	299.9	307.2	316.2	324.6	332.9	341.8	351.3
160°	291.1	291.1	293.6	297.9	302.9	309.7	317.1	324.6	331.4	338.8	346.9
162.5°	296.1	295.6	297.5	301.4	305.9	311.2	318.1	324.6	329.9	335.9	342.9
165°	301.7	301.7	302.9	306.0	309.1	312.8	318.4	323.4	327.1	331.4	336.4
167.5°	307.2	306.7	307.2	309.6	311.3	314.2	318.3	321.9	324.1	326.9	330.4
170°	309.7	309.1	309.7	311.6	312.8	314.7	317.7	320.8	322.1	323.9	326.5
172.5°	312.2	311.6	311.7	313.1	313.8	315.1	317.3	319.9	320.1	321.0	323.0
175°	314.7	314.0	314.0	314.7	315.3	315.3	316.6	318.4	317.7	317.7	319.0
177.5°	315.8	315.3	314.8	315.3	315.3	315.3	315.8	316.8	315.8	315.8	316.2
180°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3



TEST NUMBER: P332942-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1096.4	1098.0	1099.6	1100.4	1100.3	1100.1	1099.9	1099.8
5°	1089.0	1090.9	1092.8	1093.5	1093.1	1092.8	1092.4	1092.0
7.5°	1074.5	1075.8	1077.0	1077.2	1076.7	1076.0	1075.5	1074.8
10°	1061.5	1062.2	1063.0	1063.0	1062.2	1061.5	1060.7	1060.0
12.5°	1045.4	1045.8	1046.3	1046.0	1045.0	1043.9	1042.8	1041.8
15°	1017.2	1016.8	1016.4	1015.6	1014.2	1012.9	1011.6	1010.3
17.5°	983.1	982.1	981.0	979.5	977.5	975.5	973.5	971.5
20°	959.3	957.7	956.2	954.3	951.9	949.4	947.0	944.6
22.5°	932.9	930.6	928.4	926.2	924.2	922.3	920.3	918.3
25°	890.2	887.0	883.8	881.3	879.4	877.6	875.7	873.8
27.5°	846.7	842.8	838.8	835.5	832.8	830.1	827.4	824.7
30°	815.6	810.9	806.2	802.3	799.4	796.4	793.4	790.4
32.5°	783.7	778.3	772.9	768.7	765.9	763.0	760.2	757.3
35°	736.3	730.0	723.7	718.7	715.4	712.0	708.6	705.3
37.5°	685.5	678.3	671.2	666.0	662.7	659.3	655.9	652.5
40°	651.6	643.7	635.9	630.3	626.9	623.5	620.2	616.8
42.5°	618.3	610.3	602.3	596.5	592.9	589.5	586.0	582.4
45°	567.3	558.1	548.9	542.6	539.2	535.9	532.5	529.2
47.5°	515.9	506.4	496.9	490.2	486.6	482.8	479.1	475.4
50°	481.8	472.5	463.0	456.6	453.0	449.5	445.9	442.4
52.5°	447.8	438.3	428.7	422.2	418.4	414.7	411.1	407.3
55°	397.6	387.9	378.2	371.5	368.0	364.4	360.8	357.3
57.5°	348.6	338.7	328.8	322.6	319.9	317.2	314.5	311.8
60°	315.9	306.2	296.4	290.0	287.1	284.1	281.1	278.1
62.5°	283.7	274.7	265.7	260.0	257.6	255.2	252.8	250.4
65°	237.5	229.5	221.4	216.3	214.0	211.8	209.5	207.3
67.5°	195.1	188.2	181.3	176.6	174.1	171.6	169.1	166.7
70°	166.3	160.1	153.9	149.9	148.1	146.2	144.3	142.4
72.5°	140.5	135.1	129.8	126.4	124.7	122.9	121.2	119.5
75°	103.5	99.2	94.8	92.1	91.0	89.9	88.7	87.6
77.5°	73.2	70.7	68.1	66.7	66.4	66.1	65.8	65.4
80°	56.2	55.6	55.1	54.7	54.5	54.3	54.1	53.9
82.5°	43.6	43.3	42.9	42.5	42.4	42.1	42.0	41.8
85°	25.3	25.0	24.6	24.4	24.4	24.4	24.4	24.4
87.5°	11.3	11.3	11.3	11.3	11.6	11.9	11.9	12.0
90°	11.2	11.8	12.4	12.4	13.0	13.6	13.0	13.0
92.5°	121.7	91.6	72.9	60.4	53.2	49.8	47.7	47.7
95°	459.0	363.0	280.0	219.9	189.6	170.3	159.2	151.1
97.5°	678.1	642.5	581.9	517.2	472.8	435.5	416.8	404.0
100°	747.0	759.4	729.0	683.3	629.3	591.5	573.0	568.0
102.5°	743.5	805.0	813.8	794.7	761.7	734.3	714.7	710.7
105°	693.8	800.9	862.2	887.6	888.9	883.9	875.3	871.6
107.5°	623.1	737.1	823.5	878.7	909.3	923.4	929.6	931.2
110°	580.4	687.5	777.4	845.5	889.5	915.5	926.7	932.2



TEST NUMBER: P332942-927

CATALOG NUMBER: SA4XXRDIP-C795D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	549.2	644.0	728.8	796.9	846.8	878.4	894.0	903.0
115°	517.8	594.1	666.5	726.0	774.9	812.1	831.9	836.9
117.5°	502.5	565.5	622.5	673.0	714.7	745.9	766.0	769.8
120°	495.5	553.2	602.7	646.7	682.0	709.2	725.3	732.1
122.5°	489.6	545.2	590.3	628.8	658.7	682.0	695.6	702.4
125°	479.4	532.7	575.4	609.5	634.3	652.3	664.0	667.7
127.5°	467.1	517.9	560.5	592.9	617.8	633.8	643.7	647.5
130°	457.2	506.0	548.2	581.0	606.4	621.9	631.8	635.6
132.5°	446.7	492.7	533.9	566.6	591.5	609.0	618.5	622.2
135°	432.4	472.6	510.4	541.4	566.2	583.5	593.4	597.1
137.5°	419.4	453.4	485.3	513.3	536.4	553.5	561.7	566.2
140°	411.9	441.0	468.9	495.0	516.6	530.2	538.9	543.8
142.5°	405.0	430.6	454.6	477.1	496.3	508.9	516.6	520.1
145°	395.2	416.3	434.8	452.2	467.7	478.2	484.4	487.5
147.5°	387.1	403.9	418.7	432.4	443.8	452.8	457.5	458.6
150°	382.1	396.4	408.8	419.9	429.9	437.9	441.6	442.3
152.5°	376.8	389.0	400.4	409.6	418.0	424.5	426.7	427.4
155°	368.5	378.5	387.8	395.2	401.4	406.3	408.2	408.2
157.5°	359.7	368.0	375.9	381.8	386.5	390.2	391.3	391.3
160°	354.3	361.2	368.0	372.9	376.6	380.3	381.0	381.0
162.5°	348.9	354.7	360.0	364.5	367.2	370.9	371.5	371.1
165°	341.3	345.0	349.4	352.4	354.9	357.4	356.8	356.2
167.5°	334.0	336.8	340.3	342.1	343.4	345.0	344.9	344.4
170°	329.5	331.4	333.9	335.7	337.0	337.5	337.0	337.0
172.5°	325.6	326.9	328.4	329.8	330.5	331.1	330.5	329.5
175°	320.3	320.8	322.1	322.1	322.1	323.4	322.1	320.8
177.5°	316.8	317.3	317.3	317.7	317.3	317.7	316.8	315.8
180°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3

(END OF REPORT)