

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332659-830

Luminaire Tested: **SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332659-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7552.0 lumens
Efficiency: N/A
Efficacy: 124.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332659-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332659-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	53	51	46
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	38	34	32	28
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13130	13130	13130
5°	13169	13011	13105
10°	13086	12904	12969
15°	12929	12721	12754
20°	12718	12494	12506
25°	12479	12235	12200
30°	12185	11929	11820
35°	11880	11610	11456
40°	11564	11248	11041
45°	11233	10891	10683
50°	10868	10574	10246
55°	10473	10162	9831
60°	10078	9700	9405
65°	9635	9259	8886
70°	9135	8674	8337
75°	8372	7966	7764
80°	7452	7146	6969
85°	6521	6280	6150



TEST NUMBER: P332659-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	2.0
10°-20°	431.5	5.7
20°-30°	635.2	8.4
30°-40°	738.4	9.8
40°-50°	738.4	9.8
50°-60°	645.9	8.6
60°-70°	479.7	6.4
70°-80°	272.5	3.6
80°-90°	82.3	1.1
90°-100°	80.2	1.1
100°-110°	237.7	3.1
110°-120°	403.4	5.3
120°-130°	531.9	7.0
130°-140°	597.4	7.9
140°-150°	587.0	7.8
150°-160°	493.7	6.5
160°-170°	328.5	4.3
170°-180°	115.0	1.5
0°-30°	1219.8	16.2
0°-40°	1958.2	25.9
0°-60°	3342.6	44.3
0°-90°	4177.1	55.3
90°-120°	721.3	9.6
90°-150°	2437.7	32.3
90°-180°	3375.0	44.7
0°-180°	7552.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1626	1626	1626	1626	1626	
5°	1625	1619	1606	1619	1617	154
15°	1547	1541	1522	1529	1526	436
25°	1401	1391	1374	1374	1370	644
35°	1205	1196	1178	1169	1162	753
45°	984	974	954	940	936	758
55°	744	739	722	707	698	666
65°	504	497	485	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	3	13	21	26	28	7
95°	56	65	72	74	74	63
105°	219	220	224	227	230	233
115°	410	410	408	407	406	404
125°	597	597	596	595	593	532
135°	770	776	776	774	772	596
145°	936	940	941	940	937	586
155°	1072	1072	1072	1075	1072	493
165°	1168	1165	1163	1168	1165	329
175°	1215	1210	1209	1215	1209	115
180°	1216	1216	1216	1216	1216	



TEST NUMBER: P332659-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1630.5	1629.8	1629.1	1628.4	1627.8	1626.1	1623.5	1621.0	1618.4	1615.9	1618.3
5°	1625.0	1623.9	1622.8	1621.6	1620.4	1618.3	1615.0	1611.8	1608.7	1605.5	1608.7
7.5°	1610.0	1608.7	1607.6	1606.5	1605.3	1603.0	1599.4	1595.9	1592.3	1588.8	1591.4
10°	1596.4	1595.3	1594.0	1592.9	1591.8	1589.3	1585.5	1581.8	1578.0	1574.2	1576.5
12.5°	1578.7	1577.5	1576.3	1575.2	1574.0	1571.4	1567.4	1563.5	1559.4	1555.5	1558.0
15°	1546.9	1545.7	1544.5	1543.4	1542.2	1539.5	1535.1	1530.8	1526.4	1522.1	1523.8
17.5°	1508.5	1507.1	1505.6	1504.2	1502.8	1500.0	1495.8	1491.8	1487.6	1483.6	1484.6
20°	1480.4	1478.9	1477.5	1476.0	1474.6	1471.7	1467.4	1463.0	1458.7	1454.3	1455.2
22.5°	1450.2	1448.2	1446.3	1444.4	1442.6	1439.4	1435.0	1430.7	1426.3	1422.0	1423.6
25°	1400.9	1398.9	1396.8	1394.8	1392.8	1389.8	1385.7	1381.7	1377.6	1373.6	1373.9
27.5°	1344.6	1342.6	1340.4	1338.3	1336.2	1333.3	1329.6	1325.8	1322.0	1318.2	1317.6
30°	1307.1	1304.8	1302.4	1300.1	1297.8	1294.8	1291.0	1287.2	1283.5	1279.7	1278.6
32.5°	1267.4	1265.4	1263.3	1261.2	1259.1	1256.0	1252.1	1248.1	1244.1	1240.1	1238.7
35°	1205.4	1203.4	1201.4	1199.4	1197.3	1194.3	1190.2	1186.2	1182.1	1178.1	1176.0
37.5°	1140.0	1138.1	1136.3	1134.4	1132.6	1129.5	1125.1	1120.8	1116.4	1112.1	1109.9
40°	1097.3	1095.0	1092.6	1090.3	1088.0	1084.7	1080.3	1076.0	1071.7	1067.3	1064.4
42.5°	1051.4	1050.0	1048.6	1047.3	1045.8	1042.7	1037.9	1033.1	1028.3	1023.5	1020.1
45°	983.9	981.8	979.9	977.8	975.8	972.4	967.8	963.2	958.6	953.9	950.7
47.5°	913.2	911.9	910.5	909.1	907.7	904.8	900.6	896.3	892.0	887.7	884.1
50°	865.3	864.1	863.0	861.9	860.6	858.1	854.0	850.0	845.9	841.9	837.8
52.5°	818.4	817.0	815.6	814.3	812.8	810.0	805.7	801.4	797.1	792.9	789.3
55°	744.1	743.2	742.3	741.5	740.6	738.2	734.1	730.1	726.0	722.0	718.5
57.5°	673.3	672.2	671.3	670.2	669.3	666.8	662.8	658.8	654.8	650.8	647.5
60°	624.2	622.7	621.3	619.9	618.4	615.9	612.1	608.3	604.5	600.8	598.1
62.5°	576.3	575.0	573.8	572.6	571.4	568.8	564.8	560.8	556.8	552.8	550.4
65°	504.4	502.8	501.4	500.0	498.5	496.3	493.4	490.6	487.7	484.7	481.9
67.5°	431.9	430.6	429.2	427.9	426.5	424.5	421.7	419.0	416.1	413.4	410.6
70°	387.0	385.0	383.0	381.0	378.9	376.7	374.5	372.1	369.9	367.5	365.1
72.5°	339.1	337.1	335.1	333.0	331.0	329.0	327.2	325.4	323.5	321.6	319.8
75°	268.4	267.0	265.5	264.1	262.7	261.2	259.8	258.4	256.8	255.4	254.3
77.5°	201.0	200.3	199.6	199.1	198.4	197.5	196.1	194.9	193.6	192.4	192.0
80°	160.3	159.4	158.5	157.7	156.8	156.1	155.5	155.0	154.4	153.7	153.2
82.5°	120.6	120.3	119.9	119.4	119.0	118.8	118.7	118.6	118.5	118.3	118.0
85°	70.4	70.4	70.4	70.4	70.4	70.1	69.5	68.9	68.3	67.8	67.8
87.5°	27.7	27.9	28.1	28.4	28.6	28.7	28.8	28.9	29.0	29.1	29.4
90°	2.8	5.1	7.4	9.7	12.1	14.0	15.6	17.3	19.0	20.7	22.0
92.5°	20.2	22.8	25.4	28.0	30.6	32.6	33.7	34.9	36.1	37.2	38.0
95°	56.5	58.3	60.2	62.1	64.0	65.6	67.1	68.6	70.0	71.5	72.1
97.5°	98.6	100.1	101.6	103.1	104.6	106.2	107.9	109.6	111.4	113.1	113.9
100°	131.7	132.5	133.4	134.2	135.1	136.4	138.3	140.2	142.0	143.9	144.4
102.5°	166.4	166.6	167.0	167.3	167.7	168.7	170.4	172.1	173.8	175.6	176.2
105°	219.2	219.4	219.6	219.8	220.1	220.6	221.4	222.3	223.1	223.9	224.5
107.5°	274.8	274.9	275.2	275.5	275.7	275.9	276.1	276.2	276.3	276.4	277.0
110°	312.4	312.7	313.2	313.6	314.1	314.1	313.9	313.7	313.5	313.3	312.8



TEST NUMBER: P332659-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.5	351.6	351.7	351.8	351.9	351.7	351.3	350.9	350.5	350.2	350.1
115°	410.2	410.2	410.2	410.2	410.2	410.0	409.5	409.2	408.7	408.3	408.1
117.5°	465.5	465.7	465.8	466.0	466.2	466.1	465.8	465.5	465.2	465.0	464.2
120°	502.4	503.2	504.1	504.9	505.8	505.9	505.2	504.5	504.0	503.3	502.3
122.5°	540.7	541.1	541.4	541.8	542.1	542.2	541.9	541.5	541.2	540.9	540.3
125°	597.4	597.4	597.4	597.4	597.4	597.3	597.1	596.9	596.6	596.4	596.1
127.5°	648.8	649.4	650.0	650.6	651.3	651.4	651.1	650.7	650.4	650.1	649.7
130°	684.9	685.5	686.2	686.7	687.4	687.7	687.7	687.7	687.7	687.7	687.3
132.5°	721.8	722.3	722.6	723.1	723.6	723.8	723.6	723.4	723.2	723.1	722.6
135°	770.5	771.8	773.0	774.3	775.5	776.2	776.2	776.2	776.2	776.2	775.7
137.5°	823.6	824.2	824.7	825.3	826.0	826.3	826.7	827.1	827.4	827.7	827.2
140°	858.9	859.3	859.8	860.2	860.6	860.8	860.8	860.8	860.8	860.8	860.6
142.5°	891.3	891.7	892.1	892.6	893.0	893.1	893.0	892.8	892.6	892.4	892.4
145°	936.0	936.9	937.7	938.6	939.4	939.9	940.2	940.4	940.6	940.8	940.6
147.5°	980.5	981.5	982.5	983.5	984.5	985.0	984.8	984.6	984.4	984.3	984.1
150°	1007.6	1008.4	1009.3	1010.1	1011.0	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3
152.5°	1033.2	1033.7	1034.2	1034.7	1035.2	1035.5	1035.7	1035.9	1036.0	1036.1	1036.7
155°	1072.5	1072.5	1072.5	1072.5	1072.5	1072.4	1072.1	1072.0	1071.8	1071.6	1072.4
157.5°	1105.6	1105.2	1104.8	1104.5	1104.1	1103.9	1103.8	1103.8	1103.8	1103.7	1104.4
160°	1125.2	1124.9	1124.7	1124.5	1124.4	1124.2	1123.9	1123.7	1123.5	1123.3	1123.9
162.5°	1143.2	1142.7	1142.2	1141.6	1141.0	1140.7	1140.5	1140.3	1140.1	1139.8	1140.9
165°	1167.5	1166.9	1166.3	1165.6	1165.0	1164.5	1164.0	1163.7	1163.2	1162.8	1164.0
167.5°	1186.2	1185.2	1184.4	1183.6	1182.6	1182.2	1182.2	1182.3	1182.3	1182.4	1183.6
170°	1196.7	1195.6	1194.6	1193.5	1192.5	1192.0	1192.3	1192.5	1192.7	1192.9	1194.2
172.5°	1204.2	1203.3	1202.5	1201.6	1200.7	1200.2	1200.3	1200.3	1200.4	1200.4	1201.8
175°	1214.6	1213.5	1212.5	1211.4	1210.4	1209.8	1209.6	1209.3	1209.1	1208.9	1210.4
177.5°	1218.0	1217.1	1216.3	1215.4	1214.6	1214.2	1214.2	1214.2	1214.2	1214.2	1215.3
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4



TEST NUMBER: P332659-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1620.5	1622.9	1625.2	1626.3	1626.0	1625.8	1625.5	1625.3
5°	1611.8	1615.0	1618.3	1619.6	1619.0	1618.3	1617.8	1617.2
7.5°	1593.9	1596.5	1599.0	1600.2	1599.8	1599.4	1599.0	1598.7
10°	1578.9	1581.2	1583.5	1584.3	1583.8	1583.2	1582.6	1582.1
12.5°	1560.6	1563.1	1565.7	1566.5	1565.8	1564.9	1564.1	1563.3
15°	1525.6	1527.3	1529.1	1529.5	1528.6	1527.8	1526.9	1526.0
17.5°	1485.7	1486.9	1487.9	1488.2	1487.6	1487.0	1486.5	1485.8
20°	1456.0	1457.0	1457.8	1457.9	1457.4	1456.8	1456.2	1455.7
22.5°	1425.1	1426.7	1428.2	1428.5	1427.5	1426.4	1425.4	1424.4
25°	1374.1	1374.4	1374.7	1374.2	1373.1	1372.0	1370.7	1369.6
27.5°	1316.9	1316.2	1315.5	1314.5	1313.0	1311.5	1310.0	1308.6
30°	1277.4	1276.2	1275.1	1273.8	1272.3	1270.8	1269.4	1268.0
32.5°	1237.3	1236.0	1234.5	1233.1	1231.6	1230.2	1228.8	1227.3
35°	1174.0	1172.0	1170.0	1168.2	1166.8	1165.4	1163.9	1162.4
37.5°	1107.7	1105.5	1103.3	1101.3	1099.4	1097.4	1095.5	1093.6
40°	1061.5	1058.6	1055.7	1053.6	1052.1	1050.7	1049.2	1047.7
42.5°	1016.8	1013.4	1010.0	1007.9	1006.9	1005.9	1004.9	1004.0
45°	947.5	944.3	941.1	939.1	938.3	937.5	936.5	935.7
47.5°	880.5	876.9	873.4	870.4	868.3	866.0	863.8	861.7
50°	833.8	829.7	825.7	822.7	821.0	819.3	817.6	815.8
52.5°	785.7	782.0	778.4	775.6	773.4	771.2	769.0	766.8
55°	715.0	711.5	708.0	705.5	703.7	702.0	700.2	698.5
57.5°	644.2	640.9	637.6	635.1	633.4	631.8	630.1	628.4
60°	595.6	593.0	590.3	588.3	586.8	585.4	584.0	582.5
62.5°	548.1	545.6	543.3	541.4	540.0	538.5	537.1	535.6
65°	479.0	476.1	473.2	471.0	469.6	468.2	466.7	465.2
67.5°	407.8	405.0	402.3	400.7	400.2	399.8	399.4	399.1
70°	362.9	360.5	358.3	356.7	355.8	354.9	354.0	353.2
72.5°	317.9	316.0	314.2	312.8	312.0	311.1	310.3	309.3
75°	253.1	251.9	250.8	250.1	249.8	249.5	249.2	248.9
77.5°	191.6	191.3	191.0	190.4	189.6	188.9	188.1	187.4
80°	152.6	152.0	151.5	151.0	150.7	150.4	150.1	149.9
82.5°	117.6	117.3	117.0	116.6	116.3	116.0	115.7	115.5
85°	67.8	67.8	67.8	67.6	67.3	67.0	66.7	66.4
87.5°	29.7	29.9	30.2	30.3	30.4	30.5	30.5	30.6
90°	23.2	24.5	25.7	26.6	27.0	27.4	27.8	28.2
92.5°	38.7	39.5	40.2	40.8	41.0	41.3	41.6	41.8
95°	72.8	73.4	74.0	74.4	74.4	74.4	74.4	74.4
97.5°	114.6	115.4	116.1	116.5	116.5	116.5	116.5	116.5
100°	144.8	145.2	145.6	145.8	145.8	145.8	145.8	145.8
102.5°	176.7	177.3	177.9	178.2	178.4	178.6	178.8	178.9
105°	225.2	225.8	226.4	227.1	227.6	228.3	228.9	229.5
107.5°	277.6	278.1	278.7	279.0	279.0	278.9	278.9	278.8
110°	312.5	312.0	311.6	311.7	312.4	312.9	313.6	314.2



TEST NUMBER: P332659-830

CATALOG NUMBER: SA4XXDIP-C1020D1035U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	350.0	349.9	349.9	349.9	350.0	350.1	350.2	350.3
115°	407.8	407.6	407.5	407.3	407.1	406.8	406.6	406.4
117.5°	463.5	462.8	462.1	461.6	461.1	460.7	460.2	459.9
120°	501.2	500.2	499.2	498.8	499.3	499.6	500.1	500.5
122.5°	539.5	538.9	538.1	537.3	536.6	535.8	535.1	534.3
125°	595.6	595.2	594.7	594.4	594.0	593.5	593.1	592.7
127.5°	649.2	648.8	648.4	648.0	647.7	647.3	647.1	646.7
130°	686.9	686.5	686.1	685.4	684.6	683.7	682.9	682.0
132.5°	722.3	721.8	721.4	721.0	720.7	720.4	720.0	719.7
135°	775.3	774.9	774.5	773.9	773.4	772.7	772.0	771.5
137.5°	826.6	826.0	825.6	825.3	825.5	825.6	825.7	825.9
140°	860.4	860.2	860.0	859.8	859.6	859.3	859.1	858.9
142.5°	892.3	892.3	892.3	892.2	892.2	892.1	892.1	892.0
145°	940.4	940.2	939.9	939.5	938.9	938.3	937.6	937.0
147.5°	983.9	983.7	983.5	983.4	983.2	983.0	982.8	982.6
150°	1011.3	1011.3	1011.3	1011.3	1011.1	1010.8	1010.6	1010.4
152.5°	1037.2	1037.6	1038.2	1038.2	1037.6	1037.1	1036.5	1035.9
155°	1073.3	1074.0	1074.9	1074.9	1074.0	1073.3	1072.4	1071.6
157.5°	1104.9	1105.6	1106.3	1106.2	1105.5	1104.8	1104.1	1103.3
160°	1124.5	1125.2	1125.8	1125.6	1124.5	1123.5	1122.5	1121.4
162.5°	1142.1	1143.2	1144.3	1144.4	1143.4	1142.4	1141.3	1140.2
165°	1165.4	1166.6	1167.8	1168.0	1167.2	1166.4	1165.5	1164.7
167.5°	1184.9	1186.2	1187.4	1187.4	1186.1	1184.8	1183.5	1182.2
170°	1195.4	1196.7	1198.0	1197.8	1196.4	1194.9	1193.4	1191.9
172.5°	1203.2	1204.7	1206.2	1206.1	1204.7	1203.2	1201.7	1200.2
175°	1211.8	1213.3	1214.7	1214.7	1213.3	1211.8	1210.4	1208.9
177.5°	1216.5	1217.7	1218.9	1218.8	1217.5	1216.1	1214.7	1213.4
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4

(END OF REPORT)