

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332627-830

Luminaire Tested: **SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332627-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5573.9 lumens
Efficiency: N/A
Efficacy: 128.1 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332627-830
CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10	0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																			
0	114	114	114	114	109	109	109	109	99	99	99	99	90	90	90	82	82	82	78
1	104	100	96	92	99	96	92	89	87	85	82	82	80	78	76	73	71	70	66
2	95	88	82	76	91	84	78	74	77	73	69	69	71	67	64	65	62	59	56
3	87	78	70	64	83	74	68	62	68	63	58	58	63	58	54	58	54	51	48
4	80	69	61	55	76	66	59	53	61	55	50	50	56	51	47	52	48	44	41
5	74	62	53	47	70	59	52	46	55	48	44	44	51	45	41	47	42	39	36
6	68	56	47	41	65	54	46	40	50	43	38	38	46	40	36	43	38	34	32
7	63	51	42	37	60	49	41	36	45	39	34	34	42	36	32	39	34	31	28
8	59	46	38	33	56	45	37	32	41	35	30	30	39	33	29	36	31	28	25
9	55	42	35	29	52	41	34	29	38	32	27	27	36	30	26	33	28	25	23
10	52	39	32	27	49	38	31	26	35	29	25	25	33	28	24	31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12698	12698	12698	12698
5°	14954	12730	11237	12730
10°	17905	12675	10117	12675
15°	21184	12547	9290	12547
20°	23589	12416	8553	12416
25°	23971	12223	8044	12223
30°	20396	12039	7883	12039
35°	15682	11739	7885	11739
40°	12223	11385	8033	11385
45°	10192	10853	8169	10853
50°	8970	10206	8445	10206
55°	8217	9429	8785	9429
60°	7700	8732	9195	8732
65°	7169	7952	9534	7952
70°	6552	7183	9751	7183
75°	5855	6319	9635	6319
80°	4909	5179	9331	5179
85°	3622	3742	8929	3742



TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	2.7
10°-20°	472.3	8.5
20°-30°	749.0	13.4
30°-40°	833.5	15.0
40°-50°	758.7	13.6
50°-60°	620.0	11.1
60°-70°	442.6	7.9
70°-80°	243.7	4.4
80°-90°	67.5	1.2
90°-100°	122.5	2.2
100°-110°	254.9	4.6
110°-120°	228.3	4.1
120°-130°	192.0	3.4
130°-140°	160.1	2.9
140°-150°	122.3	2.2
150°-160°	86.0	1.5
160°-170°	50.6	0.9
170°-180°	16.5	0.3
0°-30°	1374.6	24.7
0°-40°	2208.1	39.6
0°-60°	3586.8	64.4
0°-90°	4340.7	77.9
90°-120°	605.7	10.9
90°-150°	1080.2	19.4
90°-180°	1233.0	22.1
0°-180°	5573.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1573	1573	1573	1573	1573	
5°	1845	1571	1387	1571	1845	188
15°	2535	1501	1112	1501	2535	716
25°	2691	1372	903	1372	2691	1186
35°	1591	1191	800	1191	1591	1010
45°	893	951	716	951	893	703
55°	584	670	624	670	584	527
65°	375	416	499	416	375	372
75°	188	203	309	203	188	200
85°	39	40	96	40	39	48
90°	7	0	7	0	7	7
95°	81	11	81	11	81	126
105°	469	39	469	39	469	463
115°	450	69	450	69	450	447
125°	359	96	359	96	359	326
135°	321	114	321	114	321	248
145°	262	131	262	131	262	166
155°	220	149	220	149	220	102
165°	192	162	192	162	192	55
175°	173	169	173	169	173	17
180°	170	170	170	170	170	



TEST NUMBER: P332627-830
 CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9
2.5°	1674.0	1673.6	1668.3	1667.3	1663.6	1659.0	1657.9	1649.5	1632.9	1625.0	1623.0
5°	1845.3	1858.3	1841.4	1838.1	1836.2	1814.7	1803.6	1790.5	1760.6	1742.9	1729.3
7.5°	2049.7	2051.2	2043.8	2037.8	2021.2	2002.4	1974.3	1944.4	1908.6	1871.5	1843.4
10°	2184.2	2189.3	2180.9	2179.5	2146.4	2125.4	2083.8	2048.6	2008.2	1963.2	1922.2
12.5°	2325.9	2318.6	2314.3	2286.4	2280.3	2242.2	2193.8	2157.6	2095.3	2043.5	1988.9
15°	2534.7	2520.4	2511.2	2472.8	2453.9	2401.1	2349.6	2309.9	2228.5	2150.9	2092.3
17.5°	2657.1	2671.5	2650.4	2634.6	2585.8	2548.7	2496.1	2412.7	2349.0	2252.7	2178.7
20°	2745.8	2747.0	2735.4	2719.0	2680.6	2633.7	2576.3	2485.1	2409.0	2313.1	2211.5
22.5°	2769.8	2770.0	2765.0	2749.8	2720.7	2682.7	2624.9	2548.7	2456.4	2352.2	2250.6
25°	2691.1	2688.4	2694.4	2711.2	2700.2	2688.4	2655.2	2598.5	2512.5	2402.4	2292.9
27.5°	2398.6	2416.6	2449.7	2491.4	2531.6	2562.2	2570.8	2559.2	2505.8	2415.3	2300.7
30°	2188.0	2210.2	2235.0	2276.6	2357.4	2403.7	2454.6	2492.9	2471.4	2399.1	2292.3
32.5°	1956.6	1962.1	1998.8	2046.3	2120.2	2209.2	2289.8	2367.9	2393.8	2355.9	2266.7
35°	1591.2	1600.2	1640.0	1687.0	1777.5	1886.3	2007.5	2115.7	2205.0	2240.8	2195.2
37.5°	1298.4	1324.6	1352.7	1403.2	1482.9	1580.8	1706.8	1846.7	1979.8	2068.9	2084.1
40°	1159.8	1176.1	1196.3	1234.7	1302.5	1398.9	1507.1	1667.5	1808.8	1936.5	1978.2
42.5°	1050.4	1059.9	1072.2	1107.0	1158.7	1254.5	1353.3	1494.3	1636.3	1788.9	1858.9
45°	892.7	902.5	923.3	943.5	982.6	1049.0	1140.9	1256.9	1399.6	1546.9	1675.8
47.5°	778.7	785.0	797.4	819.1	852.2	896.1	970.8	1067.7	1200.0	1342.9	1480.4
50°	714.2	719.3	729.2	748.7	774.1	813.1	874.4	965.0	1068.6	1212.6	1347.5
52.5°	663.1	665.2	672.3	685.6	705.8	738.7	788.9	863.8	960.2	1088.5	1222.9
55°	583.8	586.4	593.0	602.8	620.3	641.1	679.6	735.7	819.7	931.1	1047.7
57.5°	518.7	520.5	525.9	529.7	544.2	561.2	590.7	630.7	694.5	788.9	893.1
60°	476.9	475.7	482.2	485.4	495.2	509.5	532.3	570.8	626.1	702.4	798.1
62.5°	436.3	434.5	440.0	444.2	449.9	462.1	480.7	510.9	555.8	624.7	707.5
65°	375.3	372.7	376.0	381.2	386.3	392.9	406.6	433.3	469.1	518.7	581.8
67.5°	314.1	316.8	317.4	319.9	322.9	331.8	341.2	360.1	385.3	425.0	478.5
70°	277.6	278.2	280.9	280.9	282.8	290.6	298.4	309.5	334.2	370.8	414.4
72.5°	241.1	243.8	242.8	244.9	246.3	251.5	257.2	267.8	288.9	316.0	352.9
75°	187.7	189.6	189.6	190.3	192.2	194.2	198.7	206.5	221.5	241.8	267.1
77.5°	136.9	137.1	138.0	140.3	140.3	143.5	146.8	153.2	160.5	174.4	189.8
80°	105.6	106.9	106.2	107.5	107.5	110.1	111.4	119.2	122.5	131.6	144.0
82.5°	77.4	78.7	78.6	80.4	81.4	82.0	83.8	86.9	90.2	98.2	103.3
85°	39.1	40.4	39.1	40.4	42.3	43.0	45.0	45.6	48.3	50.1	54.8
87.5°	12.9	14.4	14.5	15.0	15.9	16.5	16.9	16.3	18.4	18.9	20.8
90°	7.0	7.0	7.4	7.0	6.7	6.7	6.3	6.0	5.7	6.0	5.4
92.5°	25.6	25.6	26.8	28.6	32.5	39.2	49.2	65.4	88.0	105.7	92.5
95°	81.2	85.6	91.6	101.9	118.3	150.5	195.2	246.9	279.2	271.5	204.9
97.5°	217.3	224.2	234.2	254.2	278.1	312.9	345.5	364.7	350.7	286.0	191.7
100°	305.5	308.1	318.1	338.5	367.4	392.1	408.4	401.7	353.1	267.9	173.9
102.5°	382.2	384.4	394.9	409.6	427.3	437.6	432.9	399.9	333.1	245.2	161.9
105°	468.7	470.7	475.3	478.1	477.4	463.7	430.7	373.1	296.8	218.5	151.6
107.5°	500.8	499.9	496.6	489.0	472.6	442.8	396.4	335.1	267.5	203.6	149.7
110°	501.3	498.3	492.4	478.3	454.7	418.1	369.8	312.2	252.9	198.5	150.2



TEST NUMBER: P332627-830
 CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.6	480.8	472.4	455.4	428.6	391.9	346.3	295.3	244.6	196.1	151.8
115°	450.1	447.4	436.7	416.7	390.4	358.4	319.4	278.5	236.9	194.9	154.9
117.5°	414.0	411.9	401.1	384.4	361.9	334.8	304.2	270.2	233.4	194.5	158.2
120°	393.8	390.1	381.4	366.7	347.8	324.1	297.5	266.5	231.5	194.5	160.6
122.5°	377.8	374.1	366.7	354.2	338.2	317.4	293.2	263.3	229.4	194.3	163.0
125°	359.1	357.1	350.8	341.1	327.8	309.4	286.4	257.9	225.8	193.9	166.5
127.5°	348.2	346.2	340.8	332.2	318.9	301.5	278.5	251.2	221.1	193.1	169.5
130°	341.8	339.8	334.4	326.1	312.5	294.8	272.2	245.8	218.2	192.8	171.5
132.5°	334.6	332.6	327.5	318.1	304.7	287.1	264.9	240.3	215.6	192.7	173.4
135°	321.1	319.1	313.8	304.4	291.2	274.5	254.2	232.5	211.5	192.2	176.3
137.5°	304.4	302.1	297.7	288.5	276.0	261.0	243.8	225.6	208.1	192.2	177.9
140°	292.5	289.8	285.1	277.9	266.2	252.1	237.1	221.5	206.2	191.9	179.2
142.5°	279.7	277.9	273.7	266.9	256.6	244.4	231.6	217.8	204.6	191.9	180.3
145°	262.1	260.5	257.1	251.5	243.2	233.8	223.9	212.5	201.9	191.2	180.9
147.5°	246.7	246.0	243.6	238.7	232.5	225.2	217.2	208.2	199.4	190.0	181.3
150°	237.8	237.5	235.5	231.2	225.8	219.9	213.2	205.6	197.6	189.2	181.3
152.5°	229.9	229.5	228.3	224.8	220.3	215.4	209.2	202.6	195.4	187.8	180.7
155°	219.5	219.5	218.5	215.8	212.5	208.5	203.5	198.2	192.2	185.9	179.9
157.5°	210.5	210.5	209.9	207.8	205.4	202.2	197.9	193.5	189.0	183.8	179.0
160°	204.9	204.9	204.5	202.6	200.6	197.8	194.2	190.6	186.5	182.2	178.2
162.5°	199.5	199.8	199.4	197.5	196.0	193.6	190.8	187.7	184.5	180.6	177.4
165°	191.5	191.9	192.2	190.9	189.5	187.8	185.6	183.5	180.9	178.2	175.9
167.5°	185.2	185.5	185.6	184.6	184.0	183.0	181.2	179.6	177.7	175.8	174.3
170°	181.3	181.3	181.5	181.3	180.6	179.6	178.2	177.2	175.6	174.2	173.2
172.5°	177.2	177.8	178.0	177.8	177.4	176.6	175.8	175.1	173.7	172.6	172.2
175°	172.6	173.2	173.9	173.2	173.2	173.2	172.6	172.2	171.5	170.9	170.9
177.5°	169.8	170.3	170.9	170.6	170.9	170.6	170.6	170.3	170.1	169.8	169.8
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6



TEST NUMBER: P332627-830
 CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9
2.5°	1623.5	1616.2	1611.0	1606.8	1595.3	1588.6	1583.4	1576.0	1567.7	1558.9	1547.9
5°	1715.6	1693.5	1677.2	1652.5	1629.0	1609.4	1589.2	1570.9	1548.8	1524.8	1507.1
7.5°	1812.4	1779.5	1737.3	1700.6	1659.4	1623.6	1591.6	1558.7	1524.6	1491.5	1461.1
10°	1874.0	1831.6	1784.7	1729.3	1677.2	1630.9	1587.9	1546.2	1505.8	1465.4	1430.9
12.5°	1940.1	1887.3	1818.1	1753.3	1694.9	1633.0	1581.1	1530.0	1481.3	1438.8	1398.5
15°	2029.0	1952.8	1872.6	1786.0	1709.1	1636.8	1565.8	1501.3	1446.5	1390.4	1351.4
17.5°	2083.7	1989.3	1897.7	1807.1	1714.0	1622.9	1546.2	1471.8	1403.3	1347.6	1298.4
20°	2119.6	2025.8	1911.8	1821.2	1710.4	1616.6	1528.0	1445.2	1373.6	1314.3	1263.4
22.5°	2150.9	2042.5	1928.4	1809.2	1698.9	1599.4	1502.4	1419.2	1346.0	1283.5	1234.7
25°	2167.8	2043.3	1919.6	1801.0	1675.8	1557.9	1470.0	1372.2	1294.0	1228.2	1176.1
27.5°	2169.6	2036.6	1896.5	1764.7	1635.6	1525.8	1414.8	1327.4	1246.2	1176.7	1126.6
30°	2163.9	2025.1	1874.6	1731.9	1602.2	1483.0	1386.6	1291.5	1208.7	1139.6	1087.5
32.5°	2145.7	2001.1	1846.4	1695.4	1561.0	1444.4	1344.9	1254.4	1173.7	1105.7	1051.0
35°	2092.9	1950.2	1785.4	1628.3	1490.8	1372.9	1283.0	1191.1	1110.3	1045.8	993.1
37.5°	2010.4	1881.4	1713.8	1551.3	1416.3	1297.8	1208.7	1125.7	1052.8	987.3	933.2
40°	1938.4	1825.0	1657.0	1498.6	1352.7	1240.0	1156.6	1080.3	1008.0	946.1	894.7
42.5°	1855.6	1756.8	1601.8	1434.0	1293.3	1180.1	1098.7	1030.3	962.1	904.9	853.5
45°	1707.8	1642.7	1496.7	1341.6	1195.0	1088.2	1010.6	950.6	893.3	837.3	794.3
47.5°	1537.9	1505.5	1382.7	1235.4	1096.3	990.9	923.7	868.3	818.0	770.5	732.6
50°	1423.7	1408.1	1301.8	1159.8	1026.9	927.8	860.1	812.6	769.5	727.8	692.0
52.5°	1311.1	1310.6	1214.8	1084.8	961.8	866.4	799.1	754.7	717.4	683.5	651.3
55°	1139.0	1157.3	1082.3	966.3	856.2	770.2	709.5	669.9	643.8	615.8	591.6
57.5°	980.9	1011.2	949.3	847.2	755.4	676.1	623.3	593.4	565.7	548.7	531.2
60°	877.7	906.3	858.2	772.1	685.5	617.7	567.5	540.8	516.7	505.0	492.6
62.5°	786.0	811.5	775.8	696.1	620.9	555.6	513.3	487.7	471.4	458.5	450.3
65°	654.9	676.4	645.7	587.8	523.2	471.1	436.6	416.3	400.8	395.5	386.3
67.5°	529.3	548.9	532.3	483.1	431.3	391.9	364.9	345.4	336.2	331.7	325.2
70°	454.8	474.4	456.8	413.8	374.0	340.8	315.4	304.3	294.5	292.6	283.4
72.5°	391.7	405.0	387.5	353.8	319.8	291.8	272.1	260.5	255.4	251.9	246.9
75°	293.9	305.6	293.9	267.8	243.6	224.1	207.2	202.6	196.8	194.8	191.5
77.5°	208.0	218.1	209.2	192.8	174.8	159.8	150.6	144.8	143.5	140.1	141.7
80°	159.0	165.5	157.0	146.0	131.6	121.2	114.7	111.4	107.5	106.2	108.8
82.5°	114.1	117.1	112.7	105.3	94.6	87.8	83.4	79.6	78.8	79.1	79.1
85°	59.3	58.6	58.0	51.5	48.3	43.6	41.1	40.4	39.8	41.1	42.3
87.5°	20.7	21.3	20.4	18.3	16.6	15.0	14.2	13.6	14.2	15.0	15.6
90°	4.6	4.6	2.6	2.6	2.4	2.0	1.0	0.4	1.0	2.0	2.4
92.5°	67.3	41.5	24.5	17.6	12.7	8.7	5.6	3.8	5.6	8.7	12.7
95°	125.3	70.6	41.7	27.6	19.7	15.4	12.0	11.0	12.0	15.4	19.7
97.5°	112.6	67.5	45.1	33.5	26.6	22.6	19.7	19.7	19.7	22.6	26.6
100°	105.9	68.3	48.6	38.0	31.7	27.6	25.4	25.4	25.4	27.6	31.7
102.5°	104.1	71.0	53.2	43.1	36.9	33.3	31.2	30.6	31.2	33.3	36.9
105°	104.9	77.3	61.3	51.7	45.6	41.7	40.0	39.0	40.0	41.7	45.6
107.5°	109.9	84.6	70.0	60.5	54.8	50.5	48.8	48.2	48.8	50.5	54.8
110°	113.6	90.3	75.6	66.6	60.6	56.6	55.0	54.3	55.0	56.6	60.6



TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	117.6	95.6	81.4	72.5	66.4	62.8	60.8	60.1	60.8	62.8	66.4
115°	123.9	104.0	90.6	81.6	75.3	71.9	69.7	68.6	69.7	71.9	75.3
117.5°	130.4	112.0	99.3	90.0	84.1	80.4	78.3	77.4	78.3	80.4	84.1
120°	134.9	117.6	104.9	95.6	89.9	86.2	84.0	83.3	84.0	86.2	89.9
122.5°	139.2	122.9	110.3	101.2	95.0	91.6	89.3	88.6	89.3	91.6	95.0
125°	145.5	130.3	118.3	109.0	102.6	99.0	96.9	95.6	96.9	99.0	102.6
127.5°	151.1	137.0	125.5	116.0	109.4	105.3	102.8	101.8	102.8	105.3	109.4
130°	154.6	141.6	130.3	120.6	114.2	109.2	106.6	105.3	106.6	109.2	114.2
132.5°	158.1	145.3	133.9	124.9	118.0	113.3	109.8	108.8	109.8	113.3	118.0
135°	162.6	150.5	139.6	130.9	123.9	118.3	114.9	113.6	114.9	118.3	123.9
137.5°	165.8	154.6	144.3	136.0	128.8	123.4	119.7	118.5	119.7	123.4	128.8
140°	167.9	157.2	147.2	139.2	132.2	126.6	122.9	122.0	122.9	126.6	132.2
142.5°	169.5	159.7	149.9	142.1	135.4	130.1	126.7	125.6	126.7	130.1	135.4
145°	171.3	162.2	153.5	146.3	139.9	135.3	132.0	130.9	132.0	135.3	139.9
147.5°	172.8	164.9	156.7	150.1	144.9	140.2	137.1	136.9	137.1	140.2	144.9
150°	173.5	166.3	158.9	152.6	147.6	143.5	140.9	140.5	140.9	143.5	147.6
152.5°	174.1	167.3	160.8	155.0	150.5	146.8	144.1	144.0	144.1	146.8	150.5
155°	174.6	168.9	163.2	158.3	154.6	151.3	149.2	148.9	149.2	151.3	154.6
157.5°	174.6	170.0	165.2	161.3	158.1	155.5	153.6	153.6	153.6	155.5	158.1
160°	174.6	170.6	166.5	162.9	160.2	157.9	156.6	156.6	156.6	157.9	160.2
162.5°	174.6	171.1	167.4	164.5	162.1	160.0	159.0	159.2	159.0	160.0	162.1
165°	173.9	171.3	168.2	166.3	164.6	162.9	162.2	162.2	162.2	162.9	164.6
167.5°	173.1	171.2	169.0	167.4	166.5	165.2	164.9	165.2	164.9	165.2	166.5
170°	172.6	170.9	169.2	168.2	167.6	166.5	166.3	166.5	166.3	166.5	167.6
172.5°	172.0	170.6	169.5	168.7	168.3	167.6	167.6	167.9	167.6	167.6	168.3
175°	171.3	170.2	169.6	169.6	169.2	168.9	168.9	169.2	168.9	168.9	169.2
177.5°	170.3	169.8	169.6	169.6	169.6	169.3	169.6	169.8	169.6	169.3	169.6
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6



TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9
2.5°	1542.7	1538.0	1531.3	1521.8	1514.0	1505.7	1503.6	1500.4	1506.7	1501.5	1500.0
5°	1492.1	1478.5	1460.8	1440.7	1428.9	1412.0	1408.7	1402.2	1395.7	1395.1	1388.6
7.5°	1438.6	1418.5	1395.4	1374.9	1355.8	1337.3	1325.2	1322.6	1313.0	1307.3	1300.8
10°	1404.2	1379.4	1352.7	1333.1	1311.0	1291.5	1277.8	1270.0	1263.4	1256.2	1249.7
12.5°	1363.5	1337.2	1315.1	1294.0	1267.7	1252.8	1230.3	1216.7	1215.5	1215.6	1198.6
15°	1316.2	1290.2	1256.2	1226.2	1211.9	1183.3	1170.9	1155.3	1145.5	1135.7	1127.9
17.5°	1262.2	1229.6	1203.2	1168.8	1141.4	1118.6	1102.4	1093.0	1078.3	1064.4	1054.4
20°	1228.2	1193.7	1165.6	1129.2	1099.2	1071.2	1057.5	1044.5	1033.4	1021.7	1010.6
22.5°	1193.8	1157.7	1123.4	1088.0	1060.2	1030.6	1017.4	999.7	989.1	982.6	971.5
25°	1139.6	1100.5	1061.4	1027.6	998.9	972.8	955.3	941.5	929.8	924.6	917.5
27.5°	1080.7	1041.9	1004.1	965.6	933.1	914.2	900.1	889.8	883.1	876.1	872.9
30°	1043.2	1002.8	962.4	926.5	896.5	877.7	864.7	857.5	852.2	849.0	845.7
32.5°	1005.1	965.3	922.7	890.0	863.2	846.4	836.5	829.3	826.7	825.6	824.3
35°	944.1	903.7	864.7	835.4	809.9	803.4	794.9	791.0	789.8	794.3	796.3
37.5°	885.1	847.6	811.6	783.2	766.6	757.1	754.1	754.3	758.9	763.0	767.7
40°	847.1	810.6	776.7	752.0	736.3	730.5	729.2	732.4	737.6	742.2	747.3
42.5°	810.0	774.1	743.3	720.1	709.2	703.8	704.6	707.8	715.2	720.8	728.6
45°	752.6	722.6	692.7	673.7	664.6	665.9	665.9	671.8	678.9	687.4	695.9
47.5°	698.5	668.3	643.7	627.7	623.0	621.9	625.6	633.2	643.5	653.9	665.8
50°	662.0	633.3	611.8	597.5	592.3	594.3	599.5	606.6	619.0	632.1	644.4
52.5°	625.0	598.9	579.0	565.7	562.0	565.6	570.8	582.1	593.0	607.0	622.0
55°	567.5	545.4	529.7	520.0	518.7	520.7	526.5	538.9	554.5	572.1	586.4
57.5°	510.3	491.8	477.5	470.7	471.4	473.2	482.9	497.6	514.3	533.0	551.5
60°	471.7	454.8	443.1	437.9	438.5	442.4	454.1	467.9	488.7	506.9	526.5
62.5°	435.3	420.4	409.2	404.5	403.6	412.2	423.4	437.6	458.5	478.8	499.9
65°	376.6	364.9	355.8	353.2	355.2	361.7	376.0	394.8	412.5	433.9	456.1
67.5°	319.2	309.6	303.4	304.5	306.9	316.5	328.6	344.8	364.8	387.0	409.0
70°	282.8	273.6	268.4	269.1	273.1	284.7	295.2	311.4	333.0	355.8	374.0
72.5°	245.2	239.2	234.6	237.3	241.2	249.3	262.3	278.6	297.6	318.8	338.0
75°	188.3	188.3	185.7	187.7	193.5	201.3	211.1	228.1	246.9	263.9	279.6
77.5°	139.7	138.3	140.0	142.3	145.7	155.0	166.2	178.2	192.5	209.4	222.3
80°	106.9	107.5	110.7	114.7	116.0	123.2	134.9	146.0	157.0	171.4	183.7
82.5°	80.3	81.0	82.7	87.6	88.9	96.6	104.2	115.2	125.3	134.9	145.2
85°	43.6	43.6	46.9	48.8	52.1	57.3	61.9	68.4	77.6	84.1	93.8
87.5°	17.2	17.2	19.7	20.7	22.4	25.2	26.1	32.0	34.1	36.8	41.5
90°	2.6	2.6	4.6	4.6	5.4	6.0	5.7	6.0	6.3	6.7	6.7
92.5°	17.6	24.5	41.5	67.3	92.5	105.7	88.0	65.4	49.2	39.2	32.5
95°	27.6	41.7	70.6	125.3	204.9	271.5	279.2	246.9	195.2	150.5	118.3
97.5°	33.5	45.1	67.5	112.6	191.7	286.0	350.7	364.7	345.5	312.9	278.1
100°	38.0	48.6	68.3	105.9	173.9	267.9	353.1	401.7	408.4	392.1	367.4
102.5°	43.1	53.2	71.0	104.1	161.9	245.2	333.1	399.9	432.9	437.6	427.3
105°	51.7	61.3	77.3	104.9	151.6	218.5	296.8	373.1	430.7	463.7	477.4
107.5°	60.5	70.0	84.6	109.9	149.7	203.6	267.5	335.1	396.4	442.8	472.6
110°	66.6	75.6	90.3	113.6	150.2	198.5	252.9	312.2	369.8	418.1	454.7



TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	72.5	81.4	95.6	117.6	151.8	196.1	244.6	295.3	346.3	391.9	428.6
115°	81.6	90.6	104.0	123.9	154.9	194.9	236.9	278.5	319.4	358.4	390.4
117.5°	90.0	99.3	112.0	130.4	158.2	194.5	233.4	270.2	304.2	334.8	361.9
120°	95.6	104.9	117.6	134.9	160.6	194.5	231.5	266.5	297.5	324.1	347.8
122.5°	101.2	110.3	122.9	139.2	163.0	194.3	229.4	263.3	293.2	317.4	338.2
125°	109.0	118.3	130.3	145.5	166.5	193.9	225.8	257.9	286.4	309.4	327.8
127.5°	116.0	125.5	137.0	151.1	169.5	193.1	221.1	251.2	278.5	301.5	318.9
130°	120.6	130.3	141.6	154.6	171.5	192.8	218.2	245.8	272.2	294.8	312.5
132.5°	124.9	133.9	145.3	158.1	173.4	192.7	215.6	240.3	264.9	287.1	304.7
135°	130.9	139.6	150.5	162.6	176.3	192.2	211.5	232.5	254.2	274.5	291.2
137.5°	136.0	144.3	154.6	165.8	177.9	192.2	208.1	225.6	243.8	261.0	276.0
140°	139.2	147.2	157.2	167.9	179.2	191.9	206.2	221.5	237.1	252.1	266.2
142.5°	142.1	149.9	159.7	169.5	180.3	191.9	204.6	217.8	231.6	244.4	256.6
145°	146.3	153.5	162.2	171.3	180.9	191.2	201.9	212.5	223.9	233.8	243.2
147.5°	150.1	156.7	164.9	172.8	181.3	190.0	199.4	208.2	217.2	225.2	232.5
150°	152.6	158.9	166.3	173.5	181.3	189.2	197.6	205.6	213.2	219.9	225.8
152.5°	155.0	160.8	167.3	174.1	180.7	187.8	195.4	202.6	209.2	215.4	220.3
155°	158.3	163.2	168.9	174.6	179.9	185.9	192.2	198.2	203.5	208.5	212.5
157.5°	161.3	165.2	170.0	174.6	179.0	183.8	189.0	193.5	197.9	202.2	205.4
160°	162.9	166.5	170.6	174.6	178.2	182.2	186.5	190.6	194.2	197.8	200.6
162.5°	164.5	167.4	171.1	174.6	177.4	180.6	184.5	187.7	190.8	193.6	196.0
165°	166.3	168.2	171.3	173.9	175.9	178.2	180.9	183.5	185.6	187.8	189.5
167.5°	167.4	169.0	171.2	173.1	174.3	175.8	177.7	179.6	181.2	183.0	184.0
170°	168.2	169.2	170.9	172.6	173.2	174.2	175.6	177.2	178.2	179.6	180.6
172.5°	168.7	169.5	170.6	172.0	172.2	172.6	173.7	175.1	175.8	176.6	177.4
175°	169.6	169.6	170.2	171.3	170.9	170.9	171.5	172.2	172.6	173.2	173.2
177.5°	169.6	169.6	169.8	170.3	169.8	169.8	170.1	170.3	170.6	170.6	170.9
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6



TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9
2.5°	1498.9	1497.9	1494.2	1493.7	1494.2	1497.9	1498.9	1500.0	1501.5	1506.7	1500.4
5°	1384.6	1381.4	1379.4	1386.6	1379.4	1381.4	1384.6	1388.6	1395.1	1395.7	1402.2
7.5°	1298.4	1295.9	1290.2	1288.4	1290.2	1295.9	1298.4	1300.8	1307.3	1313.0	1322.6
10°	1243.2	1240.6	1235.4	1234.1	1235.4	1240.6	1243.2	1249.7	1256.2	1263.4	1270.0
12.5°	1190.1	1184.9	1183.8	1185.1	1183.8	1184.9	1190.1	1198.6	1215.6	1215.5	1216.7
15°	1119.5	1116.8	1109.7	1111.6	1109.7	1116.8	1119.5	1127.9	1135.7	1145.5	1155.3
17.5°	1049.8	1046.7	1038.0	1045.7	1038.0	1046.7	1049.8	1054.4	1064.4	1078.3	1093.0
20°	1006.1	1000.8	996.3	995.6	996.3	1000.8	1006.1	1010.6	1021.7	1033.4	1044.5
22.5°	964.3	959.7	959.2	955.0	959.2	959.7	964.3	971.5	982.6	989.1	999.7
25°	912.2	907.7	906.3	903.1	906.3	907.7	912.2	917.5	924.6	929.8	941.5
27.5°	872.2	870.0	867.6	868.6	867.6	870.0	872.2	872.9	876.1	883.1	889.8
30°	847.7	847.1	845.7	845.7	845.7	847.1	847.7	845.7	849.0	852.2	857.5
32.5°	827.4	827.3	828.0	828.0	828.0	827.3	827.4	824.3	825.6	826.7	829.3
35°	798.8	800.8	802.1	800.1	802.1	800.8	798.8	796.3	794.3	789.8	791.0
37.5°	773.1	775.0	776.8	779.0	776.8	775.0	773.1	767.7	763.0	758.9	754.3
40°	753.2	757.8	759.1	762.3	759.1	757.8	753.2	747.3	742.2	737.6	732.4
42.5°	734.4	739.5	742.9	743.6	742.9	739.5	734.4	728.6	720.8	715.2	707.8
45°	705.7	710.9	715.5	715.5	715.5	710.9	705.7	695.9	687.4	678.9	671.8
47.5°	675.8	683.3	688.0	689.1	688.0	683.3	675.8	665.8	653.9	643.5	633.2
50°	655.5	664.6	669.2	672.4	669.2	664.6	655.5	644.4	632.1	619.0	606.6
52.5°	635.7	644.8	650.9	652.6	650.9	644.8	635.7	622.0	607.0	593.0	582.1
55°	601.4	614.4	621.6	624.2	621.6	614.4	601.4	586.4	572.1	554.5	538.9
57.5°	569.1	581.1	589.5	591.4	589.5	581.1	569.1	551.5	533.0	514.3	497.6
60°	544.0	557.1	567.5	569.5	567.5	557.1	544.0	526.5	506.9	488.7	467.9
62.5°	518.5	532.1	541.5	546.6	541.5	532.1	518.5	499.9	478.8	458.5	437.6
65°	474.4	488.0	497.2	499.1	497.2	488.0	474.4	456.1	433.9	412.5	394.8
67.5°	426.1	439.8	445.8	449.6	445.8	439.8	426.1	409.0	387.0	364.8	344.8
70°	392.3	403.3	409.8	413.1	409.8	403.3	392.3	374.0	355.8	333.0	311.4
72.5°	353.6	365.2	372.9	373.5	372.9	365.2	353.6	338.0	318.8	297.6	278.6
75°	294.5	304.9	308.9	308.9	308.9	304.9	294.5	279.6	263.9	246.9	228.1
77.5°	233.1	238.5	243.5	244.5	243.5	238.5	233.1	222.3	209.4	192.5	178.2
80°	193.5	196.8	200.7	200.7	200.7	196.8	193.5	183.7	171.4	157.0	146.0
82.5°	152.9	155.6	159.5	159.0	159.5	155.6	152.9	145.2	134.9	125.3	115.2
85°	92.6	98.4	97.7	96.4	97.7	98.4	92.6	93.8	84.1	77.6	68.4
87.5°	43.1	43.7	45.1	46.2	45.1	43.7	43.1	41.5	36.8	34.1	32.0
90°	7.0	7.4	7.0	7.0	7.0	7.4	7.0	6.7	6.7	6.3	6.0
92.5°	28.6	26.8	25.6	25.6	25.6	26.8	28.6	32.5	39.2	49.2	65.4
95°	101.9	91.6	85.6	81.2	85.6	91.6	101.9	118.3	150.5	195.2	246.9
97.5°	254.2	234.2	224.2	217.3	224.2	234.2	254.2	278.1	312.9	345.5	364.7
100°	338.5	318.1	308.1	305.5	308.1	318.1	338.5	367.4	392.1	408.4	401.7
102.5°	409.6	394.9	384.4	382.2	384.4	394.9	409.6	427.3	437.6	432.9	399.9
105°	478.1	475.3	470.7	468.7	470.7	475.3	478.1	477.4	463.7	430.7	373.1
107.5°	489.0	496.6	499.9	500.8	499.9	496.6	489.0	472.6	442.8	396.4	335.1
110°	478.3	492.4	498.3	501.3	498.3	492.4	478.3	454.7	418.1	369.8	312.2



TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	455.4	472.4	480.8	485.6	480.8	472.4	455.4	428.6	391.9	346.3	295.3
115°	416.7	436.7	447.4	450.1	447.4	436.7	416.7	390.4	358.4	319.4	278.5
117.5°	384.4	401.1	411.9	414.0	411.9	401.1	384.4	361.9	334.8	304.2	270.2
120°	366.7	381.4	390.1	393.8	390.1	381.4	366.7	347.8	324.1	297.5	266.5
122.5°	354.2	366.7	374.1	377.8	374.1	366.7	354.2	338.2	317.4	293.2	263.3
125°	341.1	350.8	357.1	359.1	357.1	350.8	341.1	327.8	309.4	286.4	257.9
127.5°	332.2	340.8	346.2	348.2	346.2	340.8	332.2	318.9	301.5	278.5	251.2
130°	326.1	334.4	339.8	341.8	339.8	334.4	326.1	312.5	294.8	272.2	245.8
132.5°	318.1	327.5	332.6	334.6	332.6	327.5	318.1	304.7	287.1	264.9	240.3
135°	304.4	313.8	319.1	321.1	319.1	313.8	304.4	291.2	274.5	254.2	232.5
137.5°	288.5	297.7	302.1	304.4	302.1	297.7	288.5	276.0	261.0	243.8	225.6
140°	277.9	285.1	289.8	292.5	289.8	285.1	277.9	266.2	252.1	237.1	221.5
142.5°	266.9	273.7	277.9	279.7	277.9	273.7	266.9	256.6	244.4	231.6	217.8
145°	251.5	257.1	260.5	262.1	260.5	257.1	251.5	243.2	233.8	223.9	212.5
147.5°	238.7	243.6	246.0	246.7	246.0	243.6	238.7	232.5	225.2	217.2	208.2
150°	231.2	235.5	237.5	237.8	237.5	235.5	231.2	225.8	219.9	213.2	205.6
152.5°	224.8	228.3	229.5	229.9	229.5	228.3	224.8	220.3	215.4	209.2	202.6
155°	215.8	218.5	219.5	219.5	219.5	218.5	215.8	212.5	208.5	203.5	198.2
157.5°	207.8	209.9	210.5	210.5	210.5	209.9	207.8	205.4	202.2	197.9	193.5
160°	202.6	204.5	204.9	204.9	204.9	204.5	202.6	200.6	197.8	194.2	190.6
162.5°	197.5	199.4	199.8	199.5	199.8	199.4	197.5	196.0	193.6	190.8	187.7
165°	190.9	192.2	191.9	191.5	191.9	192.2	190.9	189.5	187.8	185.6	183.5
167.5°	184.6	185.6	185.5	185.2	185.5	185.6	184.6	184.0	183.0	181.2	179.6
170°	181.3	181.5	181.3	181.3	181.3	181.5	181.3	180.6	179.6	178.2	177.2
172.5°	177.8	178.0	177.8	177.2	177.8	178.0	177.8	177.4	176.6	175.8	175.1
175°	173.2	173.9	173.2	172.6	173.2	173.9	173.2	173.2	173.2	172.6	172.2
177.5°	170.6	170.9	170.3	169.8	170.3	170.9	170.6	170.9	170.6	170.6	170.3
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6



TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9
2.5°	1503.6	1505.7	1514.0	1521.8	1531.3	1538.0	1542.7	1547.9	1558.9	1567.7	1576.0
5°	1408.7	1412.0	1428.9	1440.7	1460.8	1478.5	1492.1	1507.1	1524.8	1548.8	1570.9
7.5°	1325.2	1337.3	1355.8	1374.9	1395.4	1418.5	1438.6	1461.1	1491.5	1524.6	1558.7
10°	1277.8	1291.5	1311.0	1333.1	1352.7	1379.4	1404.2	1430.9	1465.4	1505.8	1546.2
12.5°	1230.3	1252.8	1267.7	1294.0	1315.1	1337.2	1363.5	1398.5	1438.8	1481.3	1530.0
15°	1170.9	1183.3	1211.9	1226.2	1256.2	1290.2	1316.2	1351.4	1390.4	1446.5	1501.3
17.5°	1102.4	1118.6	1141.4	1168.8	1203.2	1229.6	1262.2	1298.4	1347.6	1403.3	1471.8
20°	1057.5	1071.2	1099.2	1129.2	1165.6	1193.7	1228.2	1263.4	1314.3	1373.6	1445.2
22.5°	1017.4	1030.6	1060.2	1088.0	1123.4	1157.7	1193.8	1234.7	1283.5	1346.0	1419.2
25°	955.3	972.8	998.9	1027.6	1061.4	1100.5	1139.6	1176.1	1228.2	1294.0	1372.2
27.5°	900.1	914.2	933.1	965.6	1004.1	1041.9	1080.7	1126.6	1176.7	1246.2	1327.4
30°	864.7	877.7	896.5	926.5	962.4	1002.8	1043.2	1087.5	1139.6	1208.7	1291.5
32.5°	836.5	846.4	863.2	890.0	922.7	965.3	1005.1	1051.0	1105.7	1173.7	1254.4
35°	794.9	803.4	809.9	835.4	864.7	903.7	944.1	993.1	1045.8	1110.3	1191.1
37.5°	754.1	757.1	766.6	783.2	811.6	847.6	885.1	933.2	987.3	1052.8	1125.7
40°	729.2	730.5	736.3	752.0	776.7	810.6	847.1	894.7	946.1	1008.0	1080.3
42.5°	704.6	703.8	709.2	720.1	743.3	774.1	810.0	853.5	904.9	962.1	1030.3
45°	665.9	665.9	664.6	673.7	692.7	722.6	752.6	794.3	837.3	893.3	950.6
47.5°	625.6	621.9	623.0	627.7	643.7	668.3	698.5	732.6	770.5	818.0	868.3
50°	599.5	594.3	592.3	597.5	611.8	633.3	662.0	692.0	727.8	769.5	812.6
52.5°	570.8	565.6	562.0	565.7	579.0	598.9	625.0	651.3	683.5	717.4	754.7
55°	526.5	520.7	518.7	520.0	529.7	545.4	567.5	591.6	615.8	643.8	669.9
57.5°	482.9	473.2	471.4	470.7	477.5	491.8	510.3	531.2	548.7	565.7	593.4
60°	454.1	442.4	438.5	437.9	443.1	454.8	471.7	492.6	505.0	516.7	540.8
62.5°	423.4	412.2	403.6	404.5	409.2	420.4	435.3	450.3	458.5	471.4	487.7
65°	376.0	361.7	355.2	353.2	355.8	364.9	376.6	386.3	395.5	400.8	416.3
67.5°	328.6	316.5	306.9	304.5	303.4	309.6	319.2	325.2	331.7	336.2	345.4
70°	295.2	284.7	273.1	269.1	268.4	273.6	282.8	283.4	292.6	294.5	304.3
72.5°	262.3	249.3	241.2	237.3	234.6	239.2	245.2	246.9	251.9	255.4	260.5
75°	211.1	201.3	193.5	187.7	185.7	188.3	188.3	191.5	194.8	196.8	202.6
77.5°	166.2	155.0	145.7	142.3	140.0	138.3	139.7	141.7	140.1	143.5	144.8
80°	134.9	123.2	116.0	114.7	110.7	107.5	106.9	108.8	106.2	107.5	111.4
82.5°	104.2	96.6	88.9	87.6	82.7	81.0	80.3	79.1	79.1	78.8	79.6
85°	61.9	57.3	52.1	48.8	46.9	43.6	43.6	42.3	41.1	39.8	40.4
87.5°	26.1	25.2	22.4	20.7	19.7	17.2	17.2	15.6	15.0	14.2	13.6
90°	5.7	6.0	5.4	4.6	4.6	2.6	2.6	2.4	2.0	1.0	0.4
92.5°	88.0	105.7	92.5	67.3	41.5	24.5	17.6	12.7	8.7	5.6	3.8
95°	279.2	271.5	204.9	125.3	70.6	41.7	27.6	19.7	15.4	12.0	11.0
97.5°	350.7	286.0	191.7	112.6	67.5	45.1	33.5	26.6	22.6	19.7	19.7
100°	353.1	267.9	173.9	105.9	68.3	48.6	38.0	31.7	27.6	25.4	25.4
102.5°	333.1	245.2	161.9	104.1	71.0	53.2	43.1	36.9	33.3	31.2	30.6
105°	296.8	218.5	151.6	104.9	77.3	61.3	51.7	45.6	41.7	40.0	39.0
107.5°	267.5	203.6	149.7	109.9	84.6	70.0	60.5	54.8	50.5	48.8	48.2
110°	252.9	198.5	150.2	113.6	90.3	75.6	66.6	60.6	56.6	55.0	54.3



TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	244.6	196.1	151.8	117.6	95.6	81.4	72.5	66.4	62.8	60.8	60.1
115°	236.9	194.9	154.9	123.9	104.0	90.6	81.6	75.3	71.9	69.7	68.6
117.5°	233.4	194.5	158.2	130.4	112.0	99.3	90.0	84.1	80.4	78.3	77.4
120°	231.5	194.5	160.6	134.9	117.6	104.9	95.6	89.9	86.2	84.0	83.3
122.5°	229.4	194.3	163.0	139.2	122.9	110.3	101.2	95.0	91.6	89.3	88.6
125°	225.8	193.9	166.5	145.5	130.3	118.3	109.0	102.6	99.0	96.9	95.6
127.5°	221.1	193.1	169.5	151.1	137.0	125.5	116.0	109.4	105.3	102.8	101.8
130°	218.2	192.8	171.5	154.6	141.6	130.3	120.6	114.2	109.2	106.6	105.3
132.5°	215.6	192.7	173.4	158.1	145.3	133.9	124.9	118.0	113.3	109.8	108.8
135°	211.5	192.2	176.3	162.6	150.5	139.6	130.9	123.9	118.3	114.9	113.6
137.5°	208.1	192.2	177.9	165.8	154.6	144.3	136.0	128.8	123.4	119.7	118.5
140°	206.2	191.9	179.2	167.9	157.2	147.2	139.2	132.2	126.6	122.9	122.0
142.5°	204.6	191.9	180.3	169.5	159.7	149.9	142.1	135.4	130.1	126.7	125.6
145°	201.9	191.2	180.9	171.3	162.2	153.5	146.3	139.9	135.3	132.0	130.9
147.5°	199.4	190.0	181.3	172.8	164.9	156.7	150.1	144.9	140.2	137.1	136.9
150°	197.6	189.2	181.3	173.5	166.3	158.9	152.6	147.6	143.5	140.9	140.5
152.5°	195.4	187.8	180.7	174.1	167.3	160.8	155.0	150.5	146.8	144.1	144.0
155°	192.2	185.9	179.9	174.6	168.9	163.2	158.3	154.6	151.3	149.2	148.9
157.5°	189.0	183.8	179.0	174.6	170.0	165.2	161.3	158.1	155.5	153.6	153.6
160°	186.5	182.2	178.2	174.6	170.6	166.5	162.9	160.2	157.9	156.6	156.6
162.5°	184.5	180.6	177.4	174.6	171.1	167.4	164.5	162.1	160.0	159.0	159.2
165°	180.9	178.2	175.9	173.9	171.3	168.2	166.3	164.6	162.9	162.2	162.2
167.5°	177.7	175.8	174.3	173.1	171.2	169.0	167.4	166.5	165.2	164.9	165.2
170°	175.6	174.2	173.2	172.6	170.9	169.2	168.2	167.6	166.5	166.3	166.5
172.5°	173.7	172.6	172.2	172.0	170.6	169.5	168.7	168.3	167.6	167.6	167.9
175°	171.5	170.9	170.9	171.3	170.2	169.6	169.6	169.2	168.9	168.9	169.2
177.5°	170.1	169.8	169.8	170.3	169.8	169.6	169.6	169.6	169.3	169.6	169.8
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6



TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9
2.5°	1583.4	1588.6	1595.3	1606.8	1611.0	1616.2	1623.5	1623.0	1625.0	1632.9	1649.5
5°	1589.2	1609.4	1629.0	1652.5	1677.2	1693.5	1715.6	1729.3	1742.9	1760.6	1790.5
7.5°	1591.6	1623.6	1659.4	1700.6	1737.3	1779.5	1812.4	1843.4	1871.5	1908.6	1944.4
10°	1587.9	1630.9	1677.2	1729.3	1784.7	1831.6	1874.0	1922.2	1963.2	2008.2	2048.6
12.5°	1581.1	1633.0	1694.9	1753.3	1818.1	1887.3	1940.1	1988.9	2043.5	2095.3	2157.6
15°	1565.8	1636.8	1709.1	1786.0	1872.6	1952.8	2029.0	2092.3	2150.9	2228.5	2309.9
17.5°	1546.2	1622.9	1714.0	1807.1	1897.7	1989.3	2083.7	2178.7	2252.7	2349.0	2412.7
20°	1528.0	1616.6	1710.4	1821.2	1911.8	2025.8	2119.6	2211.5	2313.1	2409.0	2485.1
22.5°	1502.4	1599.4	1698.9	1809.2	1928.4	2042.5	2150.9	2250.6	2352.2	2456.4	2548.7
25°	1470.0	1557.9	1675.8	1801.0	1919.6	2043.3	2167.8	2292.9	2402.4	2512.5	2598.5
27.5°	1414.8	1525.8	1635.6	1764.7	1896.5	2036.6	2169.6	2300.7	2415.3	2505.8	2559.2
30°	1386.6	1483.0	1602.2	1731.9	1874.6	2025.1	2163.9	2292.3	2399.1	2471.4	2492.9
32.5°	1344.9	1444.4	1561.0	1695.4	1846.4	2001.1	2145.7	2266.7	2355.9	2393.8	2367.9
35°	1283.0	1372.9	1490.8	1628.3	1785.4	1950.2	2092.9	2195.2	2240.8	2205.0	2115.7
37.5°	1208.7	1297.8	1416.3	1551.3	1713.8	1881.4	2010.4	2084.1	2068.9	1979.8	1846.7
40°	1156.6	1240.0	1352.7	1498.6	1657.0	1825.0	1938.4	1978.2	1936.5	1808.8	1667.5
42.5°	1098.7	1180.1	1293.3	1434.0	1601.8	1756.8	1855.6	1858.9	1788.9	1636.3	1494.3
45°	1010.6	1088.2	1195.0	1341.6	1496.7	1642.7	1707.8	1675.8	1546.9	1399.6	1256.9
47.5°	923.7	990.9	1096.3	1235.4	1382.7	1505.5	1537.9	1480.4	1342.9	1200.0	1067.7
50°	860.1	927.8	1026.9	1159.8	1301.8	1408.1	1423.7	1347.5	1212.6	1068.6	965.0
52.5°	799.1	866.4	961.8	1084.8	1214.8	1310.6	1311.1	1222.9	1088.5	960.2	863.8
55°	709.5	770.2	856.2	966.3	1082.3	1157.3	1139.0	1047.7	931.1	819.7	735.7
57.5°	623.3	676.1	755.4	847.2	949.3	1011.2	980.9	893.1	788.9	694.5	630.7
60°	567.5	617.7	685.5	772.1	858.2	906.3	877.7	798.1	702.4	626.1	570.8
62.5°	513.3	555.6	620.9	696.1	775.8	811.5	786.0	707.5	624.7	555.8	510.9
65°	436.6	471.1	523.2	587.8	645.7	676.4	654.9	581.8	518.7	469.1	433.3
67.5°	364.9	391.9	431.3	483.1	532.3	548.9	529.3	478.5	425.0	385.3	360.1
70°	315.4	340.8	374.0	413.8	456.8	474.4	454.8	414.4	370.8	334.2	309.5
72.5°	272.1	291.8	319.8	353.8	387.5	405.0	391.7	352.9	316.0	288.9	267.8
75°	207.2	224.1	243.6	267.8	293.9	305.6	293.9	267.1	241.8	221.5	206.5
77.5°	150.6	159.8	174.8	192.8	209.2	218.1	208.0	189.8	174.4	160.5	153.2
80°	114.7	121.2	131.6	146.0	157.0	165.5	159.0	144.0	131.6	122.5	119.2
82.5°	83.4	87.8	94.6	105.3	112.7	117.1	114.1	103.3	98.2	90.2	86.9
85°	41.1	43.6	48.3	51.5	58.0	58.6	59.3	54.8	50.1	48.3	45.6
87.5°	14.2	15.0	16.6	18.3	20.4	21.3	20.7	20.8	18.9	18.4	16.3
90°	1.0	2.0	2.4	2.6	2.6	4.6	4.6	5.4	6.0	5.7	6.0
92.5°	5.6	8.7	12.7	17.6	24.5	41.5	67.3	92.5	105.7	88.0	65.4
95°	12.0	15.4	19.7	27.6	41.7	70.6	125.3	204.9	271.5	279.2	246.9
97.5°	19.7	22.6	26.6	33.5	45.1	67.5	112.6	191.7	286.0	350.7	364.7
100°	25.4	27.6	31.7	38.0	48.6	68.3	105.9	173.9	267.9	353.1	401.7
102.5°	31.2	33.3	36.9	43.1	53.2	71.0	104.1	161.9	245.2	333.1	399.9
105°	40.0	41.7	45.6	51.7	61.3	77.3	104.9	151.6	218.5	296.8	373.1
107.5°	48.8	50.5	54.8	60.5	70.0	84.6	109.9	149.7	203.6	267.5	335.1
110°	55.0	56.6	60.6	66.6	75.6	90.3	113.6	150.2	198.5	252.9	312.2



TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	60.8	62.8	66.4	72.5	81.4	95.6	117.6	151.8	196.1	244.6	295.3
115°	69.7	71.9	75.3	81.6	90.6	104.0	123.9	154.9	194.9	236.9	278.5
117.5°	78.3	80.4	84.1	90.0	99.3	112.0	130.4	158.2	194.5	233.4	270.2
120°	84.0	86.2	89.9	95.6	104.9	117.6	134.9	160.6	194.5	231.5	266.5
122.5°	89.3	91.6	95.0	101.2	110.3	122.9	139.2	163.0	194.3	229.4	263.3
125°	96.9	99.0	102.6	109.0	118.3	130.3	145.5	166.5	193.9	225.8	257.9
127.5°	102.8	105.3	109.4	116.0	125.5	137.0	151.1	169.5	193.1	221.1	251.2
130°	106.6	109.2	114.2	120.6	130.3	141.6	154.6	171.5	192.8	218.2	245.8
132.5°	109.8	113.3	118.0	124.9	133.9	145.3	158.1	173.4	192.7	215.6	240.3
135°	114.9	118.3	123.9	130.9	139.6	150.5	162.6	176.3	192.2	211.5	232.5
137.5°	119.7	123.4	128.8	136.0	144.3	154.6	165.8	177.9	192.2	208.1	225.6
140°	122.9	126.6	132.2	139.2	147.2	157.2	167.9	179.2	191.9	206.2	221.5
142.5°	126.7	130.1	135.4	142.1	149.9	159.7	169.5	180.3	191.9	204.6	217.8
145°	132.0	135.3	139.9	146.3	153.5	162.2	171.3	180.9	191.2	201.9	212.5
147.5°	137.1	140.2	144.9	150.1	156.7	164.9	172.8	181.3	190.0	199.4	208.2
150°	140.9	143.5	147.6	152.6	158.9	166.3	173.5	181.3	189.2	197.6	205.6
152.5°	144.1	146.8	150.5	155.0	160.8	167.3	174.1	180.7	187.8	195.4	202.6
155°	149.2	151.3	154.6	158.3	163.2	168.9	174.6	179.9	185.9	192.2	198.2
157.5°	153.6	155.5	158.1	161.3	165.2	170.0	174.6	179.0	183.8	189.0	193.5
160°	156.6	157.9	160.2	162.9	166.5	170.6	174.6	178.2	182.2	186.5	190.6
162.5°	159.0	160.0	162.1	164.5	167.4	171.1	174.6	177.4	180.6	184.5	187.7
165°	162.2	162.9	164.6	166.3	168.2	171.3	173.9	175.9	178.2	180.9	183.5
167.5°	164.9	165.2	166.5	167.4	169.0	171.2	173.1	174.3	175.8	177.7	179.6
170°	166.3	166.5	167.6	168.2	169.2	170.9	172.6	173.2	174.2	175.6	177.2
172.5°	167.6	167.6	168.3	168.7	169.5	170.6	172.0	172.2	172.6	173.7	175.1
175°	168.9	168.9	169.2	169.6	169.6	170.2	171.3	170.9	170.9	171.5	172.2
177.5°	169.6	169.3	169.6	169.6	169.6	169.8	170.3	169.8	169.8	170.1	170.3
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6



TEST NUMBER: P332627-830
 CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9	1572.9
2.5°	1657.9	1659.0	1663.6	1667.3	1668.3	1673.6	1674.0
5°	1803.6	1814.7	1836.2	1838.1	1841.4	1858.3	1845.3
7.5°	1974.3	2002.4	2021.2	2037.8	2043.8	2051.2	2049.7
10°	2083.8	2125.4	2146.4	2179.5	2180.9	2189.3	2184.2
12.5°	2193.8	2242.2	2280.3	2286.4	2314.3	2318.6	2325.9
15°	2349.6	2401.1	2453.9	2472.8	2511.2	2520.4	2534.7
17.5°	2496.1	2548.7	2585.8	2634.6	2650.4	2671.5	2657.1
20°	2576.3	2633.7	2680.6	2719.0	2735.4	2747.0	2745.8
22.5°	2624.9	2682.7	2720.7	2749.8	2765.0	2770.0	2769.8
25°	2655.2	2688.4	2700.2	2711.2	2694.4	2688.4	2691.1
27.5°	2570.8	2562.2	2531.6	2491.4	2449.7	2416.6	2398.6
30°	2454.6	2403.7	2357.4	2276.6	2235.0	2210.2	2188.0
32.5°	2289.8	2209.2	2120.2	2046.3	1998.8	1962.1	1956.6
35°	2007.5	1886.3	1777.5	1687.0	1640.0	1600.2	1591.2
37.5°	1706.8	1580.8	1482.9	1403.2	1352.7	1324.6	1298.4
40°	1507.1	1398.9	1302.5	1234.7	1196.3	1176.1	1159.8
42.5°	1353.3	1254.5	1158.7	1107.0	1072.2	1059.9	1050.4
45°	1140.9	1049.0	982.6	943.5	923.3	902.5	892.7
47.5°	970.8	896.1	852.2	819.1	797.4	785.0	778.7
50°	874.4	813.1	774.1	748.7	729.2	719.3	714.2
52.5°	788.9	738.7	705.8	685.6	672.3	665.2	663.1
55°	679.6	641.1	620.3	602.8	593.0	586.4	583.8
57.5°	590.7	561.2	544.2	529.7	525.9	520.5	518.7
60°	532.3	509.5	495.2	485.4	482.2	475.7	476.9
62.5°	480.7	462.1	449.9	444.2	440.0	434.5	436.3
65°	406.6	392.9	386.3	381.2	376.0	372.7	375.3
67.5°	341.2	331.8	322.9	319.9	317.4	316.8	314.1
70°	298.4	290.6	282.8	280.9	280.9	278.2	277.6
72.5°	257.2	251.5	246.3	244.9	242.8	243.8	241.1
75°	198.7	194.2	192.2	190.3	189.6	189.6	187.7
77.5°	146.8	143.5	140.3	140.3	138.0	137.1	136.9
80°	111.4	110.1	107.5	107.5	106.2	106.9	105.6
82.5°	83.8	82.0	81.4	80.4	78.6	78.7	77.4
85°	45.0	43.0	42.3	40.4	39.1	40.4	39.1
87.5°	16.9	16.5	15.9	15.0	14.5	14.4	12.9
90°	6.3	6.7	6.7	7.0	7.4	7.0	7.0
92.5°	49.2	39.2	32.5	28.6	26.8	25.6	25.6
95°	195.2	150.5	118.3	101.9	91.6	85.6	81.2
97.5°	345.5	312.9	278.1	254.2	234.2	224.2	217.3
100°	408.4	392.1	367.4	338.5	318.1	308.1	305.5
102.5°	432.9	437.6	427.3	409.6	394.9	384.4	382.2
105°	430.7	463.7	477.4	478.1	475.3	470.7	468.7
107.5°	396.4	442.8	472.6	489.0	496.6	499.9	500.8
110°	369.8	418.1	454.7	478.3	492.4	498.3	501.3



TEST NUMBER: P332627-830

CATALOG NUMBER: SA4XXDIP-C1020D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	346.3	391.9	428.6	455.4	472.4	480.8	485.6
115°	319.4	358.4	390.4	416.7	436.7	447.4	450.1
117.5°	304.2	334.8	361.9	384.4	401.1	411.9	414.0
120°	297.5	324.1	347.8	366.7	381.4	390.1	393.8
122.5°	293.2	317.4	338.2	354.2	366.7	374.1	377.8
125°	286.4	309.4	327.8	341.1	350.8	357.1	359.1
127.5°	278.5	301.5	318.9	332.2	340.8	346.2	348.2
130°	272.2	294.8	312.5	326.1	334.4	339.8	341.8
132.5°	264.9	287.1	304.7	318.1	327.5	332.6	334.6
135°	254.2	274.5	291.2	304.4	313.8	319.1	321.1
137.5°	243.8	261.0	276.0	288.5	297.7	302.1	304.4
140°	237.1	252.1	266.2	277.9	285.1	289.8	292.5
142.5°	231.6	244.4	256.6	266.9	273.7	277.9	279.7
145°	223.9	233.8	243.2	251.5	257.1	260.5	262.1
147.5°	217.2	225.2	232.5	238.7	243.6	246.0	246.7
150°	213.2	219.9	225.8	231.2	235.5	237.5	237.8
152.5°	209.2	215.4	220.3	224.8	228.3	229.5	229.9
155°	203.5	208.5	212.5	215.8	218.5	219.5	219.5
157.5°	197.9	202.2	205.4	207.8	209.9	210.5	210.5
160°	194.2	197.8	200.6	202.6	204.5	204.9	204.9
162.5°	190.8	193.6	196.0	197.5	199.4	199.8	199.5
165°	185.6	187.8	189.5	190.9	192.2	191.9	191.5
167.5°	181.2	183.0	184.0	184.6	185.6	185.5	185.2
170°	178.2	179.6	180.6	181.3	181.5	181.3	181.3
172.5°	175.8	176.6	177.4	177.8	178.0	177.8	177.2
175°	172.6	173.2	173.2	173.2	173.9	173.2	172.6
177.5°	170.6	170.6	170.9	170.6	170.9	170.3	169.8
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6

(END OF REPORT)