

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332640-830

Luminaire Tested: **SA4XXDIP-C1020D590U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332640-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D590U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6399.1 lumens
Efficiency: N/A
Efficacy: 131.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332640-830
CATALOG NUMBER: SA4XXDIP-C1020D590U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332640-830

CATALOG NUMBER: SA4XXDIP-C1020D590U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	61	59	55
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	39
4	77	66	58	51	72	62	55	49	55	50	45	49	44	41	43	40	37	33
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28	25
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13130	13130	13130
5°	13169	13011	13105
10°	13086	12904	12969
15°	12929	12721	12754
20°	12718	12494	12506
25°	12479	12235	12200
30°	12185	11929	11820
35°	11880	11610	11456
40°	11564	11248	11041
45°	11233	10891	10683
50°	10868	10574	10246
55°	10473	10162	9831
60°	10078	9700	9405
65°	9635	9259	8886
70°	9135	8674	8337
75°	8372	7966	7764
80°	7452	7146	6969
85°	6521	6280	6150



TEST NUMBER: P332640-830

CATALOG NUMBER: SA4XXDIP-C1020D590U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	2.4
10°-20°	431.5	6.7
20°-30°	635.2	9.9
30°-40°	738.4	11.5
40°-50°	738.4	11.5
50°-60°	645.9	10.1
60°-70°	479.7	7.5
70°-80°	272.5	4.3
80°-90°	80.7	1.3
90°-100°	24.6	0.4
100°-110°	156.8	2.4
110°-120°	299.9	4.7
120°-130°	380.7	5.9
130°-140°	407.3	6.4
140°-150°	380.9	6.0
150°-160°	307.1	4.8
160°-170°	198.1	3.1
170°-180°	68.3	1.1
0°-30°	1219.8	19.1
0°-40°	1958.2	30.6
0°-60°	3342.6	52.2
0°-90°	4175.5	65.3
90°-120°	481.2	7.5
90°-150°	1650.1	25.8
90°-180°	2224.0	34.8
0°-180°	6399.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1626	1626	1626	1626	1626	
5°	1625	1619	1606	1619	1617	154
15°	1547	1541	1522	1529	1526	436
25°	1401	1391	1374	1374	1370	644
35°	1205	1196	1178	1169	1162	753
45°	984	974	954	940	936	758
55°	744	739	722	707	698	666
65°	504	497	485	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	2	7	12	15	16	5
95°	30	12	12	15	16	38
105°	162	165	168	171	153	169
115°	302	304	303	304	304	297
125°	425	427	426	427	428	379
135°	527	526	528	530	531	406
145°	608	609	609	610	611	380
155°	666	667	665	667	666	307
165°	703	700	700	704	700	198
175°	719	716	716	720	714	68
180°	719	719	719	719	719	



TEST NUMBER: P332640-830

CATALOG NUMBER: SA4XXDIP-C1020D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1630.5	1629.8	1629.1	1628.4	1627.8	1626.1	1623.5	1621.0	1618.4	1615.9	1618.3
5°	1625.0	1623.9	1622.8	1621.6	1620.4	1618.3	1615.0	1611.8	1608.7	1605.5	1608.7
7.5°	1610.0	1608.7	1607.6	1606.5	1605.3	1603.0	1599.4	1595.9	1592.3	1588.8	1591.4
10°	1596.4	1595.3	1594.0	1592.9	1591.8	1589.3	1585.5	1581.8	1578.0	1574.2	1576.5
12.5°	1578.7	1577.5	1576.3	1575.2	1574.0	1571.4	1567.4	1563.5	1559.4	1555.5	1558.0
15°	1546.9	1545.7	1544.5	1543.4	1542.2	1539.5	1535.1	1530.8	1526.4	1522.1	1523.8
17.5°	1508.5	1507.1	1505.6	1504.2	1502.8	1500.0	1495.8	1491.8	1487.6	1483.6	1484.6
20°	1480.4	1478.9	1477.5	1476.0	1474.6	1471.7	1467.4	1463.0	1458.7	1454.3	1455.2
22.5°	1450.2	1448.2	1446.3	1444.4	1442.6	1439.4	1435.0	1430.7	1426.3	1422.0	1423.6
25°	1400.9	1398.9	1396.8	1394.8	1392.8	1389.8	1385.7	1381.7	1377.6	1373.6	1373.9
27.5°	1344.6	1342.6	1340.4	1338.3	1336.2	1333.3	1329.6	1325.8	1322.0	1318.2	1317.6
30°	1307.1	1304.8	1302.4	1300.1	1297.8	1294.8	1291.0	1287.2	1283.5	1279.7	1278.6
32.5°	1267.4	1265.4	1263.3	1261.2	1259.1	1256.0	1252.1	1248.1	1244.1	1240.1	1238.7
35°	1205.4	1203.4	1201.4	1199.4	1197.3	1194.3	1190.2	1186.2	1182.1	1178.1	1176.0
37.5°	1140.0	1138.1	1136.3	1134.4	1132.6	1129.5	1125.1	1120.8	1116.4	1112.1	1109.9
40°	1097.3	1095.0	1092.6	1090.3	1088.0	1084.7	1080.3	1076.0	1071.7	1067.3	1064.4
42.5°	1051.4	1050.0	1048.6	1047.3	1045.8	1042.7	1037.9	1033.1	1028.3	1023.5	1020.1
45°	983.9	981.8	979.9	977.8	975.8	972.4	967.8	963.2	958.6	953.9	950.7
47.5°	913.2	911.9	910.5	909.1	907.7	904.8	900.6	896.3	892.0	887.7	884.1
50°	865.3	864.1	863.0	861.9	860.6	858.1	854.0	850.0	845.9	841.9	837.8
52.5°	818.4	817.0	815.6	814.3	812.8	810.0	805.7	801.4	797.1	792.9	789.3
55°	744.1	743.2	742.3	741.5	740.6	738.2	734.1	730.1	726.0	722.0	718.5
57.5°	673.3	672.2	671.3	670.2	669.3	666.8	662.8	658.8	654.8	650.8	647.5
60°	624.2	622.7	621.3	619.9	618.4	615.9	612.1	608.3	604.5	600.8	598.1
62.5°	576.3	575.0	573.8	572.6	571.4	568.8	564.8	560.8	556.8	552.8	550.4
65°	504.4	502.8	501.4	500.0	498.5	496.3	493.4	490.6	487.7	484.7	481.9
67.5°	431.9	430.6	429.2	427.9	426.5	424.5	421.7	419.0	416.1	413.4	410.6
70°	387.0	385.0	383.0	381.0	378.9	376.7	374.5	372.1	369.9	367.5	365.1
72.5°	339.1	337.1	335.1	333.0	331.0	329.0	327.2	325.4	323.5	321.6	319.8
75°	268.4	267.0	265.5	264.1	262.7	261.2	259.8	258.4	256.8	255.4	254.3
77.5°	201.0	200.3	199.6	199.1	198.4	197.5	196.1	194.9	193.6	192.4	192.0
80°	160.3	159.4	158.5	157.7	156.8	156.1	155.5	155.0	154.4	153.7	153.2
82.5°	120.6	120.3	119.9	119.4	119.0	118.8	118.7	118.6	118.5	118.3	118.0
85°	70.4	70.4	70.4	70.4	70.4	70.1	69.5	68.9	68.3	67.8	67.8
87.5°	27.4	27.4	27.5	27.5	27.5	27.5	27.5	27.4	27.4	27.4	27.5
90°	1.6	2.9	4.2	5.6	6.9	8.0	9.0	9.9	10.8	11.8	12.5
92.5°	6.8	6.9	6.9	7.0	7.1	7.5	8.6	9.5	10.5	11.4	12.2
95°	29.6	25.5	21.5	17.3	13.3	11.3	11.5	11.6	11.7	11.8	12.5
97.5°	62.8	65.3	67.9	70.4	73.0	67.5	54.2	40.9	27.5	14.2	14.2
100°	88.1	90.3	92.5	94.6	96.8	89.6	73.1	56.6	40.2	23.7	21.6
102.5°	116.6	118.1	119.7	121.3	122.9	122.6	120.5	118.3	116.1	114.0	92.1
105°	161.8	162.6	163.2	164.0	164.7	165.3	166.0	166.5	167.1	167.8	168.8
107.5°	203.9	204.2	204.6	204.9	205.3	205.9	206.7	207.5	208.3	209.2	209.7
110°	232.2	232.6	233.0	233.4	233.7	234.2	235.0	235.6	236.4	237.1	237.3



TEST NUMBER: P332640-830

CATALOG NUMBER: SA4XXDIP-C1020D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	259.8	260.4	261.1	261.7	262.4	262.9	263.2	263.5	263.9	264.2	264.2
115°	302.2	302.6	302.8	303.2	303.6	303.7	303.6	303.5	303.3	303.2	303.5
117.5°	340.4	340.8	341.3	341.8	342.2	342.6	342.9	343.2	343.4	343.7	343.7
120°	366.2	366.6	367.1	367.6	368.1	368.3	368.2	368.0	367.9	367.8	368.0
122.5°	390.2	390.5	390.8	391.1	391.3	391.6	391.8	391.9	392.1	392.3	392.4
125°	424.7	425.2	425.7	426.2	426.7	426.8	426.5	426.3	426.0	425.8	426.2
127.5°	457.4	457.5	457.7	457.8	457.9	458.3	458.8	459.3	459.9	460.4	460.3
130°	478.5	478.6	478.7	478.9	479.0	479.2	479.6	479.9	480.3	480.7	480.8
132.5°	497.9	498.0	498.3	498.5	498.7	499.1	499.5	499.9	500.4	500.9	501.0
135°	526.9	526.8	526.7	526.5	526.4	526.6	527.1	527.5	528.0	528.5	528.8
137.5°	552.6	552.6	552.7	552.7	552.8	553.1	553.6	554.1	554.7	555.2	555.4
140°	569.4	569.6	569.9	570.0	570.3	570.5	570.8	571.1	571.3	571.6	571.8
142.5°	584.5	584.8	585.3	585.7	586.2	586.4	586.5	586.7	586.8	587.0	587.3
145°	607.6	607.9	608.2	608.6	609.0	609.2	609.2	609.2	609.2	609.2	609.3
147.5°	625.9	626.6	627.3	627.9	628.6	628.9	628.8	628.7	628.5	628.4	628.5
150°	639.2	639.7	640.3	640.7	641.2	641.4	641.2	641.1	641.0	640.8	640.8
152.5°	650.4	650.8	651.2	651.6	652.0	652.1	651.9	651.7	651.4	651.2	651.4
155°	666.2	666.3	666.4	666.5	666.7	666.5	666.2	665.8	665.4	665.1	665.5
157.5°	679.4	679.3	679.2	679.2	679.1	678.8	678.4	678.1	677.6	677.2	677.9
160°	687.1	686.7	686.4	686.1	685.7	685.4	685.3	685.2	685.0	684.9	685.7
162.5°	694.0	693.5	693.1	692.7	692.2	691.9	691.7	691.6	691.5	691.4	692.1
165°	702.7	702.1	701.5	700.9	700.3	700.0	700.0	700.0	700.0	700.0	701.0
167.5°	709.5	709.0	708.3	707.8	707.1	706.7	706.7	706.6	706.5	706.4	707.6
170°	713.5	712.8	712.0	711.3	710.6	710.3	710.4	710.5	710.7	710.8	711.7
172.5°	716.0	715.3	714.6	713.9	713.2	712.8	713.0	713.1	713.2	713.3	714.4
175°	718.9	718.1	717.4	716.7	716.0	715.7	715.8	716.0	716.0	716.1	717.2
177.5°	720.1	719.4	718.8	718.1	717.5	717.2	717.4	717.6	717.7	717.9	718.8
180°	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9



TEST NUMBER: P332640-830

CATALOG NUMBER: SA4XXDIP-C1020D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1620.5	1622.9	1625.2	1626.3	1626.0	1625.8	1625.5	1625.3
5°	1611.8	1615.0	1618.3	1619.6	1619.0	1618.3	1617.8	1617.2
7.5°	1593.9	1596.5	1599.0	1600.2	1599.8	1599.4	1599.0	1598.7
10°	1578.9	1581.2	1583.5	1584.3	1583.8	1583.2	1582.6	1582.1
12.5°	1560.6	1563.1	1565.7	1566.5	1565.8	1564.9	1564.1	1563.3
15°	1525.6	1527.3	1529.1	1529.5	1528.6	1527.8	1526.9	1526.0
17.5°	1485.7	1486.9	1487.9	1488.2	1487.6	1487.0	1486.5	1485.8
20°	1456.0	1457.0	1457.8	1457.9	1457.4	1456.8	1456.2	1455.7
22.5°	1425.1	1426.7	1428.2	1428.5	1427.5	1426.4	1425.4	1424.4
25°	1374.1	1374.4	1374.7	1374.2	1373.1	1372.0	1370.7	1369.6
27.5°	1316.9	1316.2	1315.5	1314.5	1313.0	1311.5	1310.0	1308.6
30°	1277.4	1276.2	1275.1	1273.8	1272.3	1270.8	1269.4	1268.0
32.5°	1237.3	1236.0	1234.5	1233.1	1231.6	1230.2	1228.8	1227.3
35°	1174.0	1172.0	1170.0	1168.2	1166.8	1165.4	1163.9	1162.4
37.5°	1107.7	1105.5	1103.3	1101.3	1099.4	1097.4	1095.5	1093.6
40°	1061.5	1058.6	1055.7	1053.6	1052.1	1050.7	1049.2	1047.7
42.5°	1016.8	1013.4	1010.0	1007.9	1006.9	1005.9	1004.9	1004.0
45°	947.5	944.3	941.1	939.1	938.3	937.5	936.5	935.7
47.5°	880.5	876.9	873.4	870.4	868.3	866.0	863.8	861.7
50°	833.8	829.7	825.7	822.7	821.0	819.3	817.6	815.8
52.5°	785.7	782.0	778.4	775.6	773.4	771.2	769.0	766.8
55°	715.0	711.5	708.0	705.5	703.7	702.0	700.2	698.5
57.5°	644.2	640.9	637.6	635.1	633.4	631.8	630.1	628.4
60°	595.6	593.0	590.3	588.3	586.8	585.4	584.0	582.5
62.5°	548.1	545.6	543.3	541.4	540.0	538.5	537.1	535.6
65°	479.0	476.1	473.2	471.0	469.6	468.2	466.7	465.2
67.5°	407.8	405.0	402.3	400.7	400.2	399.8	399.4	399.1
70°	362.9	360.5	358.3	356.7	355.8	354.9	354.0	353.2
72.5°	317.9	316.0	314.2	312.8	312.0	311.1	310.3	309.3
75°	253.1	251.9	250.8	250.1	249.8	249.5	249.2	248.9
77.5°	191.6	191.3	191.0	190.4	189.6	188.9	188.1	187.4
80°	152.6	152.0	151.5	151.0	150.7	150.4	150.1	149.9
82.5°	117.6	117.3	117.0	116.6	116.3	116.0	115.7	115.5
85°	67.8	67.8	67.8	67.6	67.3	67.0	66.7	66.4
87.5°	27.7	27.8	28.0	28.1	28.1	28.2	28.2	28.3
90°	13.3	13.9	14.7	15.2	15.5	15.6	15.9	16.1
92.5°	12.8	13.6	14.2	14.6	14.7	14.7	14.8	14.8
95°	13.3	13.9	14.7	15.1	15.3	15.4	15.5	15.6
97.5°	14.3	14.4	14.5	14.6	14.7	14.8	14.9	15.1
100°	19.6	17.5	15.6	14.6	14.7	14.8	14.9	15.1
102.5°	70.1	48.3	26.3	15.4	15.5	15.5	15.5	15.5
105°	169.9	171.0	172.0	170.4	166.2	161.8	157.5	153.3
107.5°	210.2	210.8	211.2	211.7	212.2	212.6	213.1	213.6
110°	237.6	237.8	238.1	238.4	238.7	239.0	239.4	239.8



TEST NUMBER: P332640-830

CATALOG NUMBER: SA4XXDIP-C1020D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	264.1	264.1	264.0	264.2	264.7	265.1	265.6	266.0
115°	303.7	304.0	304.2	304.3	304.3	304.3	304.3	304.3
117.5°	343.6	343.6	343.5	343.5	343.4	343.4	343.3	343.3
120°	368.3	368.4	368.7	368.7	368.4	368.3	368.0	367.8
122.5°	392.6	392.7	392.9	392.8	392.6	392.3	392.1	391.8
125°	426.5	426.9	427.3	427.5	427.6	427.7	427.8	428.0
127.5°	460.3	460.2	460.1	460.1	460.0	459.9	459.8	459.7
130°	480.9	481.0	481.2	481.2	481.2	481.2	481.2	481.2
132.5°	501.1	501.2	501.3	501.3	501.2	501.1	501.1	501.0
135°	529.0	529.2	529.4	529.7	529.9	530.2	530.5	530.7
137.5°	555.7	556.0	556.2	556.3	556.3	556.2	556.1	556.0
140°	572.2	572.6	573.0	573.2	573.3	573.4	573.5	573.6
142.5°	587.5	587.8	588.1	588.2	588.2	588.2	588.2	588.3
145°	609.4	609.5	609.6	609.8	610.0	610.3	610.6	610.8
147.5°	628.6	628.7	628.8	628.9	629.1	629.1	629.2	629.3
150°	640.8	640.8	640.8	640.9	641.0	641.2	641.3	641.4
152.5°	651.6	651.8	652.0	652.1	652.0	651.9	651.8	651.8
155°	666.0	666.5	666.9	667.0	666.7	666.3	666.0	665.6
157.5°	678.4	679.1	679.7	679.7	679.1	678.4	677.9	677.2
160°	686.4	687.1	687.9	687.9	687.1	686.4	685.7	684.9
162.5°	692.9	693.5	694.3	694.3	693.4	692.6	691.8	691.0
165°	701.9	702.9	703.9	703.8	702.7	701.6	700.6	699.5
167.5°	708.6	709.6	710.7	710.6	709.5	708.2	707.0	705.9
170°	712.7	713.6	714.6	714.4	713.3	712.1	710.9	709.7
172.5°	715.3	716.2	717.2	717.0	715.8	714.4	713.1	711.8
175°	718.3	719.3	720.5	720.3	718.9	717.4	716.0	714.5
177.5°	719.5	720.3	721.0	720.9	719.7	718.6	717.4	716.2
180°	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9

(END OF REPORT)