

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333006-935

Luminaire Tested: **SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P333006-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7706.5 lumens  
Efficiency: N/A  
Efficacy: 115.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333006-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333006-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	66	62	59	56	54	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	33	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14495	14495	14495
5°	14528	14350	14439
10°	14437	14178	14178
15°	14271	13881	13778
20°	14044	13489	13241
25°	13752	13030	12699
30°	13470	12547	12021
35°	13157	12046	11340
40°	12779	11475	10606
45°	12432	10909	9857
50°	12036	10257	9065
55°	11610	9578	8204
60°	11144	8835	7325
65°	10714	7904	6460
70°	10093	6878	5486
75°	9304	5705	4460
80°	8117	4347	4091
85°	6873	3946	3696



TEST NUMBER: P333006-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.7	2.2
10°-20°	470.4	6.1
20°-30°	679.2	8.8
30°-40°	769.9	10.0
40°-50°	743.4	9.6
50°-60°	618.2	8.0
60°-70°	426.9	5.5
70°-80°	216.4	2.8
80°-90°	58.8	0.8
90°-100°	39.3	0.5
100°-110°	250.6	3.3
110°-120°	479.4	6.2
120°-130°	608.6	7.9
130°-140°	651.1	8.4
140°-150°	608.9	7.9
150°-160°	491.0	6.4
160°-170°	316.7	4.1
170°-180°	109.2	1.4
0°-30°	1318.2	17.1
0°-40°	2088.1	27.1
0°-60°	3449.7	44.8
0°-90°	4151.8	53.9
90°-120°	769.3	10.0
90°-150°	2637.9	34.2
90°-180°	3555.0	46.1
0°-180°	7706.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1796	1796	1796	1796	1796	
5°	1793	1787	1771	1784	1782	170
15°	1708	1694	1661	1658	1648	481
25°	1544	1517	1463	1440	1426	711
35°	1335	1290	1222	1177	1151	834
45°	1089	1036	956	890	863	839
55°	825	768	680	612	583	738
65°	561	500	414	357	338	554
75°	298	247	183	152	143	315
85°	74	48	43	40	40	84
90°	3	12	19	24	26	6
95°	47	20	19	24	25	61
105°	259	264	268	274	245	271
115°	483	485	485	486	486	475
125°	679	682	681	683	684	606
135°	842	842	845	847	848	649
145°	971	974	974	975	976	607
155°	1065	1066	1063	1066	1064	491
165°	1123	1119	1119	1125	1118	317
175°	1149	1144	1145	1152	1142	109
180°	1149	1149	1149	1149	1149	



TEST NUMBER: P333006-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1799.9	1799.0	1798.0	1797.0	1796.0	1794.2	1791.6	1788.8	1786.1	1783.5	1786.1
5°	1792.8	1791.6	1790.4	1789.2	1788.0	1785.5	1781.8	1778.1	1774.5	1770.8	1773.8
7.5°	1776.6	1775.3	1774.0	1772.7	1771.4	1768.4	1763.7	1758.9	1754.1	1749.4	1751.4
10°	1761.2	1759.6	1758.2	1756.6	1755.1	1751.5	1746.1	1740.6	1735.1	1729.6	1730.8
12.5°	1741.4	1739.7	1737.8	1736.0	1734.3	1730.2	1723.7	1717.3	1710.7	1704.3	1705.0
15°	1707.5	1704.8	1702.1	1699.4	1696.6	1691.3	1683.8	1676.1	1668.4	1660.8	1660.2
17.5°	1666.6	1662.6	1658.6	1654.7	1650.7	1644.2	1635.0	1625.8	1616.6	1607.5	1605.8
20°	1634.7	1630.7	1626.8	1622.8	1618.9	1611.6	1601.3	1590.9	1580.5	1570.1	1567.6
22.5°	1599.5	1595.1	1590.6	1586.1	1581.7	1573.9	1562.7	1551.6	1540.5	1529.4	1525.7
25°	1543.9	1538.4	1532.9	1527.5	1522.0	1512.9	1500.5	1487.9	1475.4	1462.8	1457.7
27.5°	1485.7	1478.8	1471.9	1465.0	1458.0	1447.9	1434.5	1421.2	1407.7	1394.4	1387.9
30°	1445.0	1437.4	1429.7	1422.0	1414.5	1403.4	1389.1	1374.7	1360.4	1346.0	1338.3
32.5°	1402.1	1393.4	1384.8	1376.2	1367.6	1355.9	1341.0	1326.2	1311.3	1296.5	1287.6
35°	1335.0	1325.2	1315.4	1305.6	1295.9	1283.3	1268.1	1252.8	1237.5	1222.3	1211.9
37.5°	1263.3	1253.1	1243.0	1233.0	1222.9	1209.4	1192.5	1175.5	1158.6	1141.7	1130.1
40°	1212.6	1202.6	1192.5	1182.4	1172.3	1158.6	1141.2	1123.7	1106.3	1088.9	1076.1
42.5°	1164.2	1153.7	1143.1	1132.5	1122.0	1107.6	1089.4	1071.3	1053.2	1035.0	1021.9
45°	1088.9	1077.5	1066.3	1055.0	1043.7	1028.8	1010.6	992.2	973.9	955.5	940.6
47.5°	1011.1	999.4	987.7	976.0	964.4	949.0	930.0	910.9	891.8	872.8	857.2
50°	958.3	946.3	934.4	922.6	910.6	894.8	875.3	855.7	836.2	816.7	801.4
52.5°	904.4	892.7	881.1	869.4	857.7	841.8	821.8	801.8	781.7	761.6	746.1
55°	824.9	812.7	800.5	788.2	776.0	760.0	740.1	720.3	700.4	680.5	664.7
57.5°	746.2	733.6	720.8	708.2	695.4	679.3	659.8	640.2	620.6	601.1	585.0
60°	690.2	678.0	665.7	653.5	641.3	625.4	605.9	586.3	566.7	547.2	531.3
62.5°	639.6	626.9	614.2	601.5	588.8	572.4	552.3	532.3	512.2	492.2	477.5
65°	560.9	547.8	534.7	521.5	508.4	492.1	472.5	453.0	433.4	413.8	400.7
67.5°	479.2	466.7	454.1	441.5	429.0	413.5	395.4	377.3	359.1	341.0	329.7
70°	427.6	414.7	401.9	389.1	376.3	361.1	343.7	326.3	308.9	291.4	281.4
72.5°	372.6	361.0	349.4	337.8	326.1	312.1	295.7	279.2	262.8	246.3	237.7
75°	298.3	287.1	275.7	264.4	253.1	240.3	225.9	211.5	197.3	182.9	175.8
77.5°	223.0	213.4	203.8	194.2	184.6	174.0	162.4	150.8	139.2	127.6	123.5
80°	174.6	165.7	156.9	148.0	139.1	130.2	121.0	111.8	102.6	93.5	92.6
82.5°	132.9	124.7	116.6	108.4	100.3	93.6	88.3	83.1	77.8	72.6	71.9
85°	74.2	68.1	62.0	55.9	49.8	46.3	45.4	44.4	43.6	42.6	42.0
87.5°	25.8	24.3	22.7	21.2	19.6	18.9	19.0	19.0	19.1	19.2	19.2
90°	2.6	4.6	6.8	8.9	11.0	12.8	14.3	15.8	17.4	18.9	20.1
92.5°	10.8	10.9	11.0	11.2	11.3	12.1	13.6	15.2	16.7	18.3	19.4
95°	47.3	40.8	34.3	27.8	21.3	18.2	18.3	18.5	18.7	18.9	20.1
97.5°	100.4	104.4	108.5	112.5	116.6	108.0	86.6	65.3	44.0	22.7	22.8
100°	140.9	144.4	147.8	151.3	154.7	143.3	116.9	90.6	64.1	37.8	34.6
102.5°	186.3	188.9	191.4	193.9	196.4	196.0	192.5	189.1	185.6	182.2	147.1
105°	258.7	259.8	261.0	262.2	263.3	264.3	265.3	266.2	267.3	268.2	269.9
107.5°	325.9	326.5	327.1	327.6	328.2	329.2	330.5	331.7	333.0	334.3	335.2
110°	371.3	371.9	372.5	373.0	373.6	374.4	375.6	376.8	377.9	379.0	379.4



TEST NUMBER: P333006-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.3	416.4	417.4	418.4	419.5	420.3	420.8	421.3	421.8	422.3	422.3
115°	483.0	483.6	484.2	484.7	485.3	485.5	485.3	485.2	484.9	484.7	485.2
117.5°	544.1	544.8	545.6	546.4	547.2	547.7	548.1	548.5	549.0	549.4	549.3
120°	585.3	586.1	586.9	587.6	588.4	588.7	588.5	588.3	588.1	587.9	588.3
122.5°	623.8	624.3	624.7	625.2	625.7	626.0	626.3	626.5	626.8	627.1	627.3
125°	679.0	679.8	680.5	681.3	682.1	682.3	681.9	681.5	681.1	680.7	681.3
127.5°	731.2	731.4	731.7	731.8	732.0	732.5	733.5	734.3	735.2	736.1	736.0
130°	765.0	765.2	765.3	765.5	765.7	766.1	766.7	767.2	767.8	768.4	768.6
132.5°	795.9	796.3	796.6	796.9	797.3	797.8	798.6	799.3	800.0	800.7	800.9
135°	842.3	842.1	842.0	841.7	841.5	841.8	842.6	843.3	844.1	844.9	845.2
137.5°	883.4	883.5	883.6	883.6	883.7	884.2	885.0	885.9	886.7	887.5	887.9
140°	910.2	910.6	911.0	911.4	911.7	912.1	912.5	912.9	913.3	913.7	914.2
142.5°	934.3	935.0	935.6	936.3	937.0	937.5	937.7	938.0	938.1	938.4	938.8
145°	971.2	971.8	972.4	972.9	973.5	973.8	973.8	973.8	973.8	973.8	974.0
147.5°	1000.7	1001.7	1002.8	1003.8	1005.0	1005.4	1005.1	1005.0	1004.8	1004.6	1004.8
150°	1021.9	1022.7	1023.5	1024.2	1025.0	1025.3	1025.1	1024.9	1024.8	1024.5	1024.5
152.5°	1039.8	1040.4	1041.0	1041.6	1042.2	1042.4	1042.1	1041.7	1041.4	1041.0	1041.4
155°	1065.0	1065.1	1065.3	1065.5	1065.7	1065.5	1065.0	1064.4	1063.8	1063.2	1063.9
157.5°	1086.1	1086.0	1085.8	1085.7	1085.6	1085.2	1084.6	1083.9	1083.3	1082.6	1083.7
160°	1098.5	1097.9	1097.3	1096.7	1096.1	1095.8	1095.6	1095.4	1095.2	1095.0	1096.1
162.5°	1109.5	1108.7	1108.0	1107.2	1106.6	1106.1	1105.9	1105.7	1105.5	1105.4	1106.5
165°	1123.3	1122.4	1121.5	1120.5	1119.6	1119.0	1119.0	1119.0	1119.0	1119.0	1120.6
167.5°	1134.4	1133.4	1132.4	1131.4	1130.4	1129.9	1129.7	1129.6	1129.5	1129.4	1131.1
170°	1140.6	1139.4	1138.2	1137.1	1136.0	1135.5	1135.7	1135.9	1136.1	1136.3	1137.8
172.5°	1144.7	1143.6	1142.4	1141.3	1140.1	1139.6	1139.8	1140.1	1140.2	1140.4	1141.9
175°	1149.2	1148.1	1146.9	1145.7	1144.6	1144.1	1144.3	1144.5	1144.7	1144.9	1146.6
177.5°	1151.2	1150.1	1149.1	1148.1	1146.9	1146.6	1146.9	1147.2	1147.5	1147.8	1149.0
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2



TEST NUMBER: P333006-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1788.8	1791.6	1794.2	1795.4	1795.2	1794.9	1794.7	1794.5
5°	1776.9	1779.9	1783.0	1784.3	1783.6	1783.0	1782.4	1781.8
7.5°	1753.3	1755.2	1757.2	1757.6	1756.7	1755.8	1754.7	1753.8
10°	1732.0	1733.2	1734.5	1734.5	1733.2	1732.0	1730.8	1729.6
12.5°	1705.7	1706.5	1707.2	1706.7	1705.0	1703.3	1701.6	1699.9
15°	1659.6	1659.0	1658.4	1657.0	1654.8	1652.7	1650.6	1648.5
17.5°	1604.0	1602.3	1600.6	1598.2	1594.9	1591.6	1588.5	1585.2
20°	1565.2	1562.7	1560.3	1557.1	1553.2	1549.2	1545.2	1541.2
22.5°	1522.1	1518.4	1514.8	1511.3	1508.0	1504.8	1501.6	1498.3
25°	1452.4	1447.3	1442.1	1438.0	1434.9	1431.8	1428.7	1425.7
27.5°	1381.6	1375.1	1368.7	1363.3	1358.9	1354.5	1350.1	1345.7
30°	1330.7	1323.1	1315.4	1309.2	1304.2	1299.4	1294.5	1289.6
32.5°	1278.8	1269.9	1261.0	1254.3	1249.7	1245.0	1240.4	1235.7
35°	1201.4	1191.1	1180.7	1172.8	1167.3	1161.7	1156.2	1150.7
37.5°	1118.4	1106.8	1095.3	1086.7	1081.2	1075.6	1070.2	1064.7
40°	1063.2	1050.4	1037.6	1028.4	1022.9	1017.4	1011.9	1006.4
42.5°	1008.8	995.7	982.7	973.3	967.5	961.8	956.1	950.3
45°	925.6	910.6	895.6	885.4	879.9	874.4	868.9	863.4
47.5°	841.7	826.2	810.7	799.9	793.8	787.8	781.7	775.7
50°	786.1	770.9	755.5	745.0	739.3	733.4	727.6	721.8
52.5°	730.6	715.1	699.6	688.8	682.8	676.7	670.6	664.6
55°	648.8	632.9	617.0	606.1	600.4	594.5	588.8	582.9
57.5°	568.9	552.7	536.6	526.3	521.9	517.5	513.1	508.7
60°	515.4	499.6	483.6	473.3	468.4	463.5	458.6	453.7
62.5°	462.9	448.2	433.5	424.2	420.3	416.5	412.5	408.6
65°	387.5	374.4	361.3	352.8	349.2	345.5	341.9	338.2
67.5°	318.4	307.0	295.8	288.1	284.0	280.0	276.0	271.9
70°	271.3	261.2	251.2	244.6	241.5	238.5	235.4	232.4
72.5°	229.1	220.5	211.9	206.2	203.4	200.6	197.8	194.9
75°	168.8	161.8	154.7	150.3	148.5	146.6	144.8	143.0
77.5°	119.4	115.3	111.2	108.9	108.3	107.8	107.3	106.7
80°	91.7	90.7	89.8	89.2	88.9	88.6	88.3	88.0
82.5°	71.3	70.6	69.9	69.4	69.1	68.8	68.5	68.2
85°	41.4	40.8	40.2	39.9	39.9	39.9	39.9	39.9
87.5°	19.1	19.1	19.1	19.3	19.6	19.9	20.2	20.6
90°	21.2	22.4	23.5	24.3	24.6	25.1	25.4	25.7
92.5°	20.5	21.7	22.8	23.4	23.5	23.6	23.7	23.8
95°	21.2	22.4	23.5	24.2	24.4	24.5	24.7	24.9
97.5°	22.9	23.1	23.2	23.3	23.5	23.7	23.8	24.1
100°	31.3	28.1	24.8	23.3	23.5	23.7	23.8	24.1
102.5°	112.2	77.1	42.1	24.6	24.6	24.7	24.7	24.8
105°	271.6	273.3	275.0	272.5	265.6	258.7	251.8	245.0
107.5°	336.0	336.9	337.7	338.5	339.2	339.9	340.7	341.4
110°	379.8	380.2	380.6	381.1	381.6	382.2	382.8	383.3





TEST NUMBER: P333006-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	422.2	422.1	422.1	422.4	423.1	423.9	424.6	425.2
115°	485.5	485.9	486.3	486.5	486.5	486.5	486.5	486.5
117.5°	549.2	549.1	549.1	549.1	549.0	548.9	548.8	548.7
120°	588.7	589.0	589.4	589.4	589.0	588.7	588.3	587.9
122.5°	627.6	627.8	628.0	627.9	627.6	627.2	626.8	626.4
125°	681.9	682.4	683.0	683.4	683.6	683.8	684.0	684.2
127.5°	735.9	735.7	735.6	735.5	735.4	735.2	735.0	734.9
130°	768.8	769.0	769.1	769.3	769.3	769.3	769.3	769.3
132.5°	801.1	801.3	801.5	801.5	801.3	801.2	801.1	800.9
135°	845.7	846.0	846.4	846.8	847.2	847.6	847.9	848.3
137.5°	888.4	888.8	889.2	889.3	889.2	889.2	889.0	888.9
140°	914.8	915.4	915.9	916.4	916.5	916.7	916.9	917.1
142.5°	939.3	939.7	940.1	940.3	940.4	940.4	940.5	940.5
145°	974.2	974.4	974.6	974.9	975.3	975.6	976.0	976.4
147.5°	1004.9	1005.0	1005.2	1005.4	1005.6	1005.7	1006.0	1006.2
150°	1024.5	1024.5	1024.5	1024.6	1024.8	1025.0	1025.2	1025.4
152.5°	1041.6	1042.0	1042.2	1042.3	1042.2	1042.2	1042.0	1041.9
155°	1064.7	1065.5	1066.3	1066.3	1065.8	1065.2	1064.6	1064.1
157.5°	1084.6	1085.6	1086.6	1086.6	1085.6	1084.6	1083.7	1082.6
160°	1097.3	1098.5	1099.6	1099.6	1098.5	1097.3	1096.1	1095.0
162.5°	1107.6	1108.8	1109.9	1109.8	1108.5	1107.2	1106.0	1104.7
165°	1122.1	1123.7	1125.2	1125.1	1123.3	1121.6	1119.9	1118.2
167.5°	1132.7	1134.5	1136.1	1136.0	1134.1	1132.2	1130.2	1128.3
170°	1139.4	1140.8	1142.4	1142.2	1140.3	1138.4	1136.4	1134.5
172.5°	1143.5	1145.0	1146.5	1146.2	1144.2	1142.1	1140.1	1138.0
175°	1148.3	1150.0	1151.8	1151.4	1149.2	1146.9	1144.6	1142.3
177.5°	1150.2	1151.4	1152.7	1152.4	1150.6	1148.7	1146.9	1145.0
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2

(END OF REPORT)