

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332988-935

Luminaire Tested: **SA4XXRDIP-C1195D365U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332988-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D365U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5408.1 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332988-935
CATALOG NUMBER: SA4XXRDIP-C1195D365U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332988-935

CATALOG NUMBER: SA4XXRDIP-C1195D365U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77				77
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69				66	
2	95	88	82	76	91	84	78	74	77	72	68	70	67	63	64	61	59				56	
3	87	78	70	64	83	74	67	62	68	63	58	62	58	54	57	53	50				47	
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	51	47	44				41	
5	74	62	53	47	70	59	52	46	55	48	43	50	45	41	46	42	38				36	
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	42	38	34				32	
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	39	34	30				28	
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	36	31	27				25	
9	55	42	35	29	52	41	34	29	38	32	27	35	30	26	33	28	25				23	
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23				21	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14495	14495	14495
5°	14528	14350	14439
10°	14437	14178	14178
15°	14271	13881	13778
20°	14044	13489	13241
25°	13752	13030	12699
30°	13470	12547	12021
35°	13157	12046	11340
40°	12779	11475	10606
45°	12432	10909	9857
50°	12036	10257	9065
55°	11610	9578	8204
60°	11144	8835	7325
65°	10714	7904	6460
70°	10093	6878	5486
75°	9304	5705	4460
80°	8117	4347	4091
85°	6873	3946	3696



TEST NUMBER: P332988-935

CATALOG NUMBER: SA4XXRDIP-C1195D365U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.7	3.1
10°-20°	470.4	8.7
20°-30°	679.2	12.6
30°-40°	769.9	14.2
40°-50°	743.4	13.7
50°-60°	618.2	11.4
60°-70°	426.9	7.9
70°-80°	216.4	4.0
80°-90°	56.7	1.0
90°-100°	13.9	0.3
100°-110°	88.7	1.6
110°-120°	169.7	3.1
120°-130°	215.4	4.0
130°-140°	230.5	4.3
140°-150°	215.6	4.0
150°-160°	173.8	3.2
160°-170°	112.1	2.1
170°-180°	38.6	0.7
0°-30°	1318.2	24.4
0°-40°	2088.1	38.6
0°-60°	3449.7	63.8
0°-90°	4149.7	76.7
90°-120°	272.4	5.0
90°-150°	933.9	17.3
90°-180°	1258.0	23.3
0°-180°	5408.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1796	1796	1796	1796	1796	
5°	1793	1787	1771	1784	1782	170
15°	1708	1694	1661	1658	1648	481
25°	1544	1517	1463	1440	1426	711
35°	1335	1290	1222	1177	1151	834
45°	1089	1036	956	890	863	839
55°	825	768	680	612	583	738
65°	561	500	414	357	338	554
75°	298	247	183	152	143	315
85°	74	48	43	40	40	84
90°	1	4	7	8	9	4
95°	17	7	7	8	9	22
105°	92	93	95	97	87	96
115°	171	172	172	172	172	168
125°	240	242	241	242	242	215
135°	298	298	299	300	300	230
145°	344	345	345	345	346	215
155°	377	377	376	378	377	174
165°	398	396	396	398	396	112
175°	407	405	405	408	404	39
180°	407	407	407	407	407	



TEST NUMBER: P332988-935

CATALOG NUMBER: SA4XXRDIP-C1195D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1799.9	1799.0	1798.0	1797.0	1796.0	1794.2	1791.6	1788.8	1786.1	1783.5	1786.1
5°	1792.8	1791.6	1790.4	1789.2	1788.0	1785.5	1781.8	1778.1	1774.5	1770.8	1773.8
7.5°	1776.6	1775.3	1774.0	1772.7	1771.4	1768.4	1763.7	1758.9	1754.1	1749.4	1751.4
10°	1761.2	1759.6	1758.2	1756.6	1755.1	1751.5	1746.1	1740.6	1735.1	1729.6	1730.8
12.5°	1741.4	1739.7	1737.8	1736.0	1734.3	1730.2	1723.7	1717.3	1710.7	1704.3	1705.0
15°	1707.5	1704.8	1702.1	1699.4	1696.6	1691.3	1683.8	1676.1	1668.4	1660.8	1660.2
17.5°	1666.6	1662.6	1658.6	1654.7	1650.7	1644.2	1635.0	1625.8	1616.6	1607.5	1605.8
20°	1634.7	1630.7	1626.8	1622.8	1618.9	1611.6	1601.3	1590.9	1580.5	1570.1	1567.6
22.5°	1599.5	1595.1	1590.6	1586.1	1581.7	1573.9	1562.7	1551.6	1540.5	1529.4	1525.7
25°	1543.9	1538.4	1532.9	1527.5	1522.0	1512.9	1500.5	1487.9	1475.4	1462.8	1457.7
27.5°	1485.7	1478.8	1471.9	1465.0	1458.0	1447.9	1434.5	1421.2	1407.7	1394.4	1387.9
30°	1445.0	1437.4	1429.7	1422.0	1414.5	1403.4	1389.1	1374.7	1360.4	1346.0	1338.3
32.5°	1402.1	1393.4	1384.8	1376.2	1367.6	1355.9	1341.0	1326.2	1311.3	1296.5	1287.6
35°	1335.0	1325.2	1315.4	1305.6	1295.9	1283.3	1268.1	1252.8	1237.5	1222.3	1211.9
37.5°	1263.3	1253.1	1243.0	1233.0	1222.9	1209.4	1192.5	1175.5	1158.6	1141.7	1130.1
40°	1212.6	1202.6	1192.5	1182.4	1172.3	1158.6	1141.2	1123.7	1106.3	1088.9	1076.1
42.5°	1164.2	1153.7	1143.1	1132.5	1122.0	1107.6	1089.4	1071.3	1053.2	1035.0	1021.9
45°	1088.9	1077.5	1066.3	1055.0	1043.7	1028.8	1010.6	992.2	973.9	955.5	940.6
47.5°	1011.1	999.4	987.7	976.0	964.4	949.0	930.0	910.9	891.8	872.8	857.2
50°	958.3	946.3	934.4	922.6	910.6	894.8	875.3	855.7	836.2	816.7	801.4
52.5°	904.4	892.7	881.1	869.4	857.7	841.8	821.8	801.8	781.7	761.6	746.1
55°	824.9	812.7	800.5	788.2	776.0	760.0	740.1	720.3	700.4	680.5	664.7
57.5°	746.2	733.6	720.8	708.2	695.4	679.3	659.8	640.2	620.6	601.1	585.0
60°	690.2	678.0	665.7	653.5	641.3	625.4	605.9	586.3	566.7	547.2	531.3
62.5°	639.6	626.9	614.2	601.5	588.8	572.4	552.3	532.3	512.2	492.2	477.5
65°	560.9	547.8	534.7	521.5	508.4	492.1	472.5	453.0	433.4	413.8	400.7
67.5°	479.2	466.7	454.1	441.5	429.0	413.5	395.4	377.3	359.1	341.0	329.7
70°	427.6	414.7	401.9	389.1	376.3	361.1	343.7	326.3	308.9	291.4	281.4
72.5°	372.6	361.0	349.4	337.8	326.1	312.1	295.7	279.2	262.8	246.3	237.7
75°	298.3	287.1	275.7	264.4	253.1	240.3	225.9	211.5	197.3	182.9	175.8
77.5°	223.0	213.4	203.8	194.2	184.6	174.0	162.4	150.8	139.2	127.6	123.5
80°	174.6	165.7	156.9	148.0	139.1	130.2	121.0	111.8	102.6	93.5	92.6
82.5°	132.9	124.7	116.6	108.4	100.3	93.6	88.3	83.1	77.8	72.6	71.9
85°	74.2	68.1	62.0	55.9	49.8	46.3	45.4	44.4	43.6	42.6	42.0
87.5°	25.5	23.7	21.9	20.1	18.3	17.3	17.1	17.0	16.9	16.7	16.5
90°	0.9	1.6	2.4	3.2	3.9	4.6	5.1	5.6	6.1	6.7	7.1
92.5°	3.9	3.9	3.9	4.0	4.0	4.3	4.8	5.3	5.9	6.5	6.9
95°	16.7	14.5	12.1	9.8	7.6	6.5	6.5	6.5	6.6	6.7	7.1
97.5°	35.6	36.9	38.4	39.9	41.2	38.2	30.7	23.2	15.6	8.0	8.1
100°	49.9	51.1	52.3	53.6	54.8	50.7	41.4	32.0	22.7	13.4	12.2
102.5°	66.0	66.9	67.8	68.6	69.6	69.4	68.2	67.0	65.7	64.5	52.1
105°	91.6	92.0	92.4	92.8	93.2	93.6	93.9	94.3	94.6	95.0	95.6
107.5°	115.4	115.5	115.8	116.0	116.2	116.5	117.0	117.4	117.9	118.4	118.6
110°	131.5	131.6	131.8	132.1	132.2	132.6	132.9	133.4	133.8	134.2	134.3



TEST NUMBER: P332988-935

CATALOG NUMBER: SA4XXRDIP-C1195D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.1	147.4	147.7	148.1	148.5	148.8	149.0	149.1	149.3	149.6	149.5
115°	171.0	171.3	171.4	171.6	171.9	171.9	171.9	171.8	171.7	171.6	171.8
117.5°	192.6	192.9	193.1	193.5	193.7	193.9	194.1	194.2	194.3	194.5	194.5
120°	207.2	207.5	207.8	208.0	208.3	208.4	208.4	208.3	208.2	208.1	208.3
122.5°	220.8	221.0	221.2	221.4	221.5	221.6	221.7	221.8	221.9	222.1	222.1
125°	240.4	240.6	240.9	241.2	241.5	241.5	241.4	241.3	241.2	241.0	241.2
127.5°	258.9	259.0	259.0	259.1	259.2	259.3	259.7	259.9	260.3	260.6	260.5
130°	270.8	270.9	271.0	271.0	271.1	271.2	271.4	271.6	271.8	272.1	272.1
132.5°	281.8	281.9	282.0	282.1	282.2	282.4	282.7	282.9	283.2	283.4	283.5
135°	298.2	298.2	298.1	298.0	297.9	298.0	298.3	298.6	298.9	299.1	299.3
137.5°	312.7	312.8	312.8	312.8	312.9	313.1	313.3	313.6	313.9	314.2	314.4
140°	322.3	322.4	322.5	322.6	322.8	322.9	323.0	323.2	323.3	323.5	323.6
142.5°	330.8	331.0	331.2	331.5	331.7	331.9	332.0	332.1	332.2	332.3	332.3
145°	343.9	344.1	344.2	344.5	344.7	344.7	344.7	344.7	344.7	344.7	344.8
147.5°	354.2	354.6	355.0	355.4	355.8	355.9	355.9	355.8	355.7	355.7	355.7
150°	361.8	362.1	362.3	362.7	362.9	363.0	362.9	362.8	362.7	362.7	362.7
152.5°	368.2	368.3	368.6	368.8	369.0	369.0	368.9	368.8	368.7	368.6	368.7
155°	377.0	377.1	377.1	377.2	377.3	377.2	377.0	376.8	376.6	376.4	376.7
157.5°	384.5	384.4	384.4	384.4	384.4	384.2	384.0	383.7	383.5	383.3	383.7
160°	388.9	388.7	388.5	388.3	388.1	388.0	387.9	387.8	387.7	387.6	388.1
162.5°	392.8	392.5	392.3	392.0	391.8	391.6	391.5	391.4	391.4	391.3	391.8
165°	397.7	397.4	397.0	396.7	396.3	396.1	396.1	396.1	396.1	396.1	396.7
167.5°	401.6	401.2	400.9	400.5	400.2	400.0	399.9	399.9	399.8	399.8	400.5
170°	403.8	403.4	402.9	402.6	402.2	402.0	402.1	402.2	402.2	402.3	402.8
172.5°	405.3	404.8	404.4	404.1	403.6	403.5	403.6	403.6	403.6	403.7	404.2
175°	406.8	406.4	406.0	405.6	405.2	405.0	405.1	405.2	405.3	405.3	406.0
177.5°	407.6	407.2	406.8	406.4	406.0	405.9	406.0	406.1	406.2	406.3	406.8
180°	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8



TEST NUMBER: P332988-935

CATALOG NUMBER: SA4XXRDIP-C1195D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1788.8	1791.6	1794.2	1795.4	1795.2	1794.9	1794.7	1794.5
5°	1776.9	1779.9	1783.0	1784.3	1783.6	1783.0	1782.4	1781.8
7.5°	1753.3	1755.2	1757.2	1757.6	1756.7	1755.8	1754.7	1753.8
10°	1732.0	1733.2	1734.5	1734.5	1733.2	1732.0	1730.8	1729.6
12.5°	1705.7	1706.5	1707.2	1706.7	1705.0	1703.3	1701.6	1699.9
15°	1659.6	1659.0	1658.4	1657.0	1654.8	1652.7	1650.6	1648.5
17.5°	1604.0	1602.3	1600.6	1598.2	1594.9	1591.6	1588.5	1585.2
20°	1565.2	1562.7	1560.3	1557.1	1553.2	1549.2	1545.2	1541.2
22.5°	1522.1	1518.4	1514.8	1511.3	1508.0	1504.8	1501.6	1498.3
25°	1452.4	1447.3	1442.1	1438.0	1434.9	1431.8	1428.7	1425.7
27.5°	1381.6	1375.1	1368.7	1363.3	1358.9	1354.5	1350.1	1345.7
30°	1330.7	1323.1	1315.4	1309.2	1304.2	1299.4	1294.5	1289.6
32.5°	1278.8	1269.9	1261.0	1254.3	1249.7	1245.0	1240.4	1235.7
35°	1201.4	1191.1	1180.7	1172.8	1167.3	1161.7	1156.2	1150.7
37.5°	1118.4	1106.8	1095.3	1086.7	1081.2	1075.6	1070.2	1064.7
40°	1063.2	1050.4	1037.6	1028.4	1022.9	1017.4	1011.9	1006.4
42.5°	1008.8	995.7	982.7	973.3	967.5	961.8	956.1	950.3
45°	925.6	910.6	895.6	885.4	879.9	874.4	868.9	863.4
47.5°	841.7	826.2	810.7	799.9	793.8	787.8	781.7	775.7
50°	786.1	770.9	755.5	745.0	739.3	733.4	727.6	721.8
52.5°	730.6	715.1	699.6	688.8	682.8	676.7	670.6	664.6
55°	648.8	632.9	617.0	606.1	600.4	594.5	588.8	582.9
57.5°	568.9	552.7	536.6	526.3	521.9	517.5	513.1	508.7
60°	515.4	499.6	483.6	473.3	468.4	463.5	458.6	453.7
62.5°	462.9	448.2	433.5	424.2	420.3	416.5	412.5	408.6
65°	387.5	374.4	361.3	352.8	349.2	345.5	341.9	338.2
67.5°	318.4	307.0	295.8	288.1	284.0	280.0	276.0	271.9
70°	271.3	261.2	251.2	244.6	241.5	238.5	235.4	232.4
72.5°	229.1	220.5	211.9	206.2	203.4	200.6	197.8	194.9
75°	168.8	161.8	154.7	150.3	148.5	146.6	144.8	143.0
77.5°	119.4	115.3	111.2	108.9	108.3	107.8	107.3	106.7
80°	91.7	90.7	89.8	89.2	88.9	88.6	88.3	88.0
82.5°	71.3	70.6	69.9	69.4	69.1	68.8	68.5	68.2
85°	41.4	40.8	40.2	39.9	39.9	39.9	39.9	39.9
87.5°	16.4	16.3	16.1	16.1	16.4	16.7	17.0	17.2
90°	7.5	7.9	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	7.2	7.7	8.1	8.3	8.4	8.4	8.4	8.4
95°	7.5	7.9	8.4	8.5	8.6	8.7	8.8	8.8
97.5°	8.1	8.2	8.2	8.3	8.4	8.4	8.4	8.5
100°	11.1	9.9	8.8	8.3	8.4	8.4	8.4	8.5
102.5°	39.7	27.3	14.9	8.7	8.7	8.7	8.8	8.8
105°	96.2	96.8	97.4	96.4	94.0	91.6	89.1	86.7
107.5°	119.0	119.2	119.6	119.9	120.1	120.4	120.6	120.9
110°	134.5	134.6	134.7	134.9	135.1	135.3	135.5	135.7



TEST NUMBER: P332988-935

CATALOG NUMBER: SA4XXRDIP-C1195D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	149.5	149.5	149.4	149.6	149.8	150.1	150.3	150.6
115°	171.9	172.0	172.2	172.2	172.2	172.2	172.2	172.2
117.5°	194.4	194.4	194.4	194.3	194.3	194.3	194.3	194.2
120°	208.4	208.5	208.7	208.7	208.5	208.4	208.3	208.1
122.5°	222.1	222.2	222.3	222.3	222.1	222.1	221.9	221.8
125°	241.4	241.6	241.8	241.9	242.0	242.1	242.1	242.2
127.5°	260.5	260.5	260.5	260.4	260.4	260.3	260.2	260.2
130°	272.2	272.2	272.3	272.3	272.3	272.3	272.3	272.3
132.5°	283.6	283.7	283.8	283.8	283.7	283.6	283.6	283.5
135°	299.4	299.5	299.6	299.8	299.9	300.1	300.2	300.3
137.5°	314.5	314.7	314.8	314.9	314.8	314.8	314.7	314.7
140°	323.8	324.1	324.3	324.4	324.5	324.5	324.6	324.7
142.5°	332.5	332.7	332.8	332.9	332.9	332.9	332.9	332.9
145°	344.9	345.0	345.0	345.1	345.3	345.4	345.5	345.7
147.5°	355.8	355.9	355.9	355.9	356.0	356.0	356.1	356.2
150°	362.7	362.7	362.7	362.7	362.8	362.9	362.9	363.0
152.5°	368.8	368.9	369.0	369.0	368.9	368.9	368.9	368.9
155°	376.9	377.2	377.5	377.5	377.3	377.1	376.9	376.7
157.5°	384.0	384.4	384.7	384.7	384.4	384.0	383.7	383.3
160°	388.5	388.9	389.3	389.3	388.9	388.5	388.1	387.6
162.5°	392.1	392.5	393.0	392.9	392.4	392.0	391.5	391.1
165°	397.3	397.8	398.4	398.3	397.7	397.1	396.5	395.9
167.5°	401.1	401.7	402.2	402.2	401.5	400.8	400.1	399.5
170°	403.4	403.9	404.4	404.3	403.7	403.0	402.3	401.7
172.5°	404.8	405.4	405.9	405.8	405.1	404.3	403.6	402.9
175°	406.6	407.2	407.8	407.7	406.8	406.0	405.2	404.4
177.5°	407.3	407.7	408.1	407.9	407.3	406.7	406.0	405.4
180°	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8

(END OF REPORT)