

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332996-935

Luminaire Tested: **SA4XXRDIP-C1195D590U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332996-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D590U935-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5968.1 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332996-935
CATALOG NUMBER: SA4XXRDIP-C1195D590U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332996-935

CATALOG NUMBER: SA4XXRDIP-C1195D590U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70				
1	103	98	94	91	97	93	90	87	83	81	78	74	72	71	66	65	63	59				
2	94	86	80	75	88	82	76	72	73	69	65	66	62	60	59	56	54	50				
3	86	76	69	63	81	72	66	60	65	60	56	58	54	51	52	49	46	43				
4	79	68	60	54	74	64	57	52	58	52	48	52	48	44	47	43	40	37				
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35	32				
6	67	55	46	40	63	52	45	39	47	41	36	43	38	34	39	34	31	29				
7	62	50	41	36	59	47	40	35	43	37	32	39	34	30	35	31	28	26				
8	58	45	37	32	55	43	36	31	39	33	29	36	31	27	33	28	25	23				
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23	21				
10	50	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14495	14495	14495
5°	14528	14350	14439
10°	14437	14178	14178
15°	14271	13881	13778
20°	14044	13489	13241
25°	13752	13030	12699
30°	13470	12547	12021
35°	13157	12046	11340
40°	12779	11475	10606
45°	12432	10909	9857
50°	12036	10257	9065
55°	11610	9578	8204
60°	11144	8835	7325
65°	10714	7904	6460
70°	10093	6878	5486
75°	9304	5705	4460
80°	8117	4347	4091
85°	6873	3946	3696



TEST NUMBER: P332996-935

CATALOG NUMBER: SA4XXRDIP-C1195D590U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.7	2.8
10°-20°	470.4	7.9
20°-30°	679.2	11.4
30°-40°	769.9	12.9
40°-50°	743.4	12.5
50°-60°	618.2	10.4
60°-70°	426.9	7.2
70°-80°	216.4	3.6
80°-90°	56.9	1.0
90°-100°	180.6	3.0
100°-110°	375.8	6.3
110°-120°	336.6	5.6
120°-130°	283.1	4.7
130°-140°	236.1	4.0
140°-150°	180.4	3.0
150°-160°	126.8	2.1
160°-170°	74.6	1.2
170°-180°	24.3	0.4
0°-30°	1318.2	22.1
0°-40°	2088.1	35.0
0°-60°	3449.7	57.8
0°-90°	4149.9	69.5
90°-120°	893.0	15.0
90°-150°	1592.6	26.7
90°-180°	1818.0	30.5
0°-180°	5968.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1796	1796	1796	1796	1796	
5°	1793	1787	1771	1784	1782	170
15°	1708	1694	1661	1658	1648	481
25°	1544	1517	1463	1440	1426	711
35°	1335	1290	1222	1177	1151	834
45°	1089	1036	956	890	863	839
55°	825	768	680	612	583	738
65°	561	500	414	357	338	554
75°	298	247	183	152	143	315
85°	74	48	43	40	40	83
90°	0	4	9	10	10	4
95°	16	51	400	198	120	18
105°	57	83	322	694	691	61
115°	101	127	287	552	664	100
125°	141	168	286	470	529	125
135°	168	199	283	417	474	129
145°	193	221	282	352	386	121
155°	220	237	274	310	324	101
165°	239	247	263	278	282	68
175°	250	250	252	255	254	24
180°	250	250	250	250	250	



TEST NUMBER: P332996-935

CATALOG NUMBER: SA4XXRDIP-C1195D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1799.9	1799.0	1798.0	1797.0	1796.0	1794.2	1791.6	1788.8	1786.1	1783.5	1786.1
5°	1792.8	1791.6	1790.4	1789.2	1788.0	1785.5	1781.8	1778.1	1774.5	1770.8	1773.8
7.5°	1776.6	1775.3	1774.0	1772.7	1771.4	1768.4	1763.7	1758.9	1754.1	1749.4	1751.4
10°	1761.2	1759.6	1758.2	1756.6	1755.1	1751.5	1746.1	1740.6	1735.1	1729.6	1730.8
12.5°	1741.4	1739.7	1737.8	1736.0	1734.3	1730.2	1723.7	1717.3	1710.7	1704.3	1705.0
15°	1707.5	1704.8	1702.1	1699.4	1696.6	1691.3	1683.8	1676.1	1668.4	1660.8	1660.2
17.5°	1666.6	1662.6	1658.6	1654.7	1650.7	1644.2	1635.0	1625.8	1616.6	1607.5	1605.8
20°	1634.7	1630.7	1626.8	1622.8	1618.9	1611.6	1601.3	1590.9	1580.5	1570.1	1567.6
22.5°	1599.5	1595.1	1590.6	1586.1	1581.7	1573.9	1562.7	1551.6	1540.5	1529.4	1525.7
25°	1543.9	1538.4	1532.9	1527.5	1522.0	1512.9	1500.5	1487.9	1475.4	1462.8	1457.7
27.5°	1485.7	1478.8	1471.9	1465.0	1458.0	1447.9	1434.5	1421.2	1407.7	1394.4	1387.9
30°	1445.0	1437.4	1429.7	1422.0	1414.5	1403.4	1389.1	1374.7	1360.4	1346.0	1338.3
32.5°	1402.1	1393.4	1384.8	1376.2	1367.6	1355.9	1341.0	1326.2	1311.3	1296.5	1287.6
35°	1335.0	1325.2	1315.4	1305.6	1295.9	1283.3	1268.1	1252.8	1237.5	1222.3	1211.9
37.5°	1263.3	1253.1	1243.0	1233.0	1222.9	1209.4	1192.5	1175.5	1158.6	1141.7	1130.1
40°	1212.6	1202.6	1192.5	1182.4	1172.3	1158.6	1141.2	1123.7	1106.3	1088.9	1076.1
42.5°	1164.2	1153.7	1143.1	1132.5	1122.0	1107.6	1089.4	1071.3	1053.2	1035.0	1021.9
45°	1088.9	1077.5	1066.3	1055.0	1043.7	1028.8	1010.6	992.2	973.9	955.5	940.6
47.5°	1011.1	999.4	987.7	976.0	964.4	949.0	930.0	910.9	891.8	872.8	857.2
50°	958.3	946.3	934.4	922.6	910.6	894.8	875.3	855.7	836.2	816.7	801.4
52.5°	904.4	892.7	881.1	869.4	857.7	841.8	821.8	801.8	781.7	761.6	746.1
55°	824.9	812.7	800.5	788.2	776.0	760.0	740.1	720.3	700.4	680.5	664.7
57.5°	746.2	733.6	720.8	708.2	695.4	679.3	659.8	640.2	620.6	601.1	585.0
60°	690.2	678.0	665.7	653.5	641.3	625.4	605.9	586.3	566.7	547.2	531.3
62.5°	639.6	626.9	614.2	601.5	588.8	572.4	552.3	532.3	512.2	492.2	477.5
65°	560.9	547.8	534.7	521.5	508.4	492.1	472.5	453.0	433.4	413.8	400.7
67.5°	479.2	466.7	454.1	441.5	429.0	413.5	395.4	377.3	359.1	341.0	329.7
70°	427.6	414.7	401.9	389.1	376.3	361.1	343.7	326.3	308.9	291.4	281.4
72.5°	372.6	361.0	349.4	337.8	326.1	312.1	295.7	279.2	262.8	246.3	237.7
75°	298.3	287.1	275.7	264.4	253.1	240.3	225.9	211.5	197.3	182.9	175.8
77.5°	223.0	213.4	203.8	194.2	184.6	174.0	162.4	150.8	139.2	127.6	123.5
80°	174.6	165.7	156.9	148.0	139.1	130.2	121.0	111.8	102.6	93.5	92.6
82.5°	132.9	124.7	116.6	108.4	100.3	93.6	88.3	83.1	77.8	72.6	71.9
85°	74.2	68.1	62.0	55.9	49.8	46.3	45.4	44.4	43.6	42.6	42.0
87.5°	25.4	23.7	22.0	20.1	18.3	17.1	17.5	17.2	17.2	17.1	16.8
90°	0.5	1.5	2.9	3.4	4.0	4.0	6.9	6.9	7.8	8.9	8.4
92.5°	5.6	8.2	12.7	18.8	25.9	36.2	61.1	99.2	136.4	155.8	129.8
95°	16.2	17.7	22.6	29.0	40.7	61.4	104.1	184.7	302.0	400.3	411.6
97.5°	29.1	29.1	33.3	39.2	49.3	66.6	99.5	166.0	282.8	421.6	517.1
100°	37.4	37.4	40.7	46.7	56.0	71.7	100.7	156.2	256.4	394.9	520.6
102.5°	45.2	46.0	49.0	54.5	63.5	78.4	104.6	153.4	238.7	361.5	491.1
105°	57.4	59.0	61.4	67.3	76.1	90.4	113.9	154.7	223.5	322.2	437.6
107.5°	71.0	72.0	74.5	80.8	89.2	103.2	124.8	162.0	220.8	300.2	394.4
110°	80.1	81.0	83.5	89.4	98.2	111.5	133.1	167.5	221.5	292.7	372.8



TEST NUMBER: P332996-935

CATALOG NUMBER: SA4XXRDIP-C1195D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	88.7	89.7	92.6	98.1	106.9	120.1	140.9	173.4	223.9	289.2	360.6
115°	101.2	102.6	106.1	111.0	120.4	133.6	153.3	182.7	228.4	287.3	349.2
117.5°	114.2	115.5	118.6	124.0	132.7	146.5	165.1	192.3	233.2	286.8	344.1
120°	122.8	123.8	127.2	132.6	140.9	154.7	173.4	198.9	236.8	286.8	341.4
122.5°	130.6	131.6	135.1	140.1	149.2	162.6	181.2	205.2	240.3	286.5	338.2
125°	140.9	142.9	145.9	151.3	160.6	174.4	192.0	214.6	245.6	285.9	333.0
127.5°	150.1	151.7	155.2	161.4	171.1	184.9	202.1	222.8	249.8	284.7	326.1
130°	155.2	157.1	161.1	168.5	177.8	192.0	208.7	227.9	253.0	284.4	321.7
132.5°	160.3	161.9	167.0	174.0	184.1	197.5	214.2	233.0	255.7	284.0	317.8
135°	167.5	169.4	174.4	182.7	193.0	205.8	222.0	239.7	259.8	283.4	311.9
137.5°	174.7	176.5	181.9	189.9	200.6	212.8	227.9	244.4	262.3	283.3	306.8
140°	179.8	181.2	186.7	195.0	205.3	217.1	231.9	247.5	264.2	282.9	304.0
142.5°	185.3	186.8	191.7	199.7	209.7	221.0	235.4	249.9	265.8	282.9	301.7
145°	193.0	194.5	199.4	206.3	215.6	226.4	239.2	252.4	266.7	281.9	297.6
147.5°	201.7	202.2	206.6	213.6	221.4	231.2	243.1	254.7	267.2	280.2	294.0
150°	207.2	207.8	211.7	217.6	225.0	234.3	245.1	255.9	267.2	279.0	291.3
152.5°	212.4	212.5	216.4	221.9	228.5	237.0	246.7	256.7	266.4	277.0	288.1
155°	219.6	220.1	223.0	227.9	233.3	240.6	249.0	257.4	265.2	274.1	283.4
157.5°	226.5	226.5	229.3	233.1	237.8	243.6	250.7	257.4	264.0	271.0	278.6
160°	230.8	230.8	232.8	236.3	240.1	245.6	251.5	257.4	262.8	268.6	275.1
162.5°	234.8	234.4	235.9	239.0	242.5	246.8	252.3	257.4	261.6	266.3	271.9
165°	239.2	239.2	240.1	242.6	245.1	248.1	252.4	256.4	259.3	262.8	266.7
167.5°	243.6	243.1	243.6	245.5	246.8	249.1	252.4	255.2	257.0	259.2	262.0
170°	245.6	245.1	245.6	247.0	248.1	249.5	251.9	254.4	255.4	256.8	258.8
172.5°	247.5	247.0	247.1	248.2	248.8	249.9	251.6	253.7	253.8	254.5	256.1
175°	249.5	249.0	249.0	249.5	250.0	250.0	251.0	252.4	251.9	251.9	253.0
177.5°	250.4	250.0	249.6	250.0	250.0	250.0	250.4	251.2	250.4	250.4	250.8
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332996-935

CATALOG NUMBER: SA4XXRDIP-C1195D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1788.8	1791.6	1794.2	1795.4	1795.2	1794.9	1794.7	1794.5
5°	1776.9	1779.9	1783.0	1784.3	1783.6	1783.0	1782.4	1781.8
7.5°	1753.3	1755.2	1757.2	1757.6	1756.7	1755.8	1754.7	1753.8
10°	1732.0	1733.2	1734.5	1734.5	1733.2	1732.0	1730.8	1729.6
12.5°	1705.7	1706.5	1707.2	1706.7	1705.0	1703.3	1701.6	1699.9
15°	1659.6	1659.0	1658.4	1657.0	1654.8	1652.7	1650.6	1648.5
17.5°	1604.0	1602.3	1600.6	1598.2	1594.9	1591.6	1588.5	1585.2
20°	1565.2	1562.7	1560.3	1557.1	1553.2	1549.2	1545.2	1541.2
22.5°	1522.1	1518.4	1514.8	1511.3	1508.0	1504.8	1501.6	1498.3
25°	1452.4	1447.3	1442.1	1438.0	1434.9	1431.8	1428.7	1425.7
27.5°	1381.6	1375.1	1368.7	1363.3	1358.9	1354.5	1350.1	1345.7
30°	1330.7	1323.1	1315.4	1309.2	1304.2	1299.4	1294.5	1289.6
32.5°	1278.8	1269.9	1261.0	1254.3	1249.7	1245.0	1240.4	1235.7
35°	1201.4	1191.1	1180.7	1172.8	1167.3	1161.7	1156.2	1150.7
37.5°	1118.4	1106.8	1095.3	1086.7	1081.2	1075.6	1070.2	1064.7
40°	1063.2	1050.4	1037.6	1028.4	1022.9	1017.4	1011.9	1006.4
42.5°	1008.8	995.7	982.7	973.3	967.5	961.8	956.1	950.3
45°	925.6	910.6	895.6	885.4	879.9	874.4	868.9	863.4
47.5°	841.7	826.2	810.7	799.9	793.8	787.8	781.7	775.7
50°	786.1	770.9	755.5	745.0	739.3	733.4	727.6	721.8
52.5°	730.6	715.1	699.6	688.8	682.8	676.7	670.6	664.6
55°	648.8	632.9	617.0	606.1	600.4	594.5	588.8	582.9
57.5°	568.9	552.7	536.6	526.3	521.9	517.5	513.1	508.7
60°	515.4	499.6	483.6	473.3	468.4	463.5	458.6	453.7
62.5°	462.9	448.2	433.5	424.2	420.3	416.5	412.5	408.6
65°	387.5	374.4	361.3	352.8	349.2	345.5	341.9	338.2
67.5°	318.4	307.0	295.8	288.1	284.0	280.0	276.0	271.9
70°	271.3	261.2	251.2	244.6	241.5	238.5	235.4	232.4
72.5°	229.1	220.5	211.9	206.2	203.4	200.6	197.8	194.9
75°	168.8	161.8	154.7	150.3	148.5	146.6	144.8	143.0
77.5°	119.4	115.3	111.2	108.9	108.3	107.8	107.3	106.7
80°	91.7	90.7	89.8	89.2	88.9	88.6	88.3	88.0
82.5°	71.3	70.6	69.9	69.4	69.1	68.8	68.5	68.2
85°	41.4	40.8	40.2	39.9	39.9	39.9	39.9	39.9
87.5°	16.7	16.5	16.4	16.4	16.7	17.0	17.2	17.5
90°	8.9	9.3	9.8	9.8	10.3	10.8	10.3	10.3
92.5°	96.4	72.6	57.8	48.0	42.1	39.5	37.8	37.8
95°	363.9	287.8	222.0	174.4	150.3	135.1	126.2	119.9
97.5°	537.7	509.5	461.4	410.1	374.9	345.3	330.5	320.3
100°	592.4	602.2	578.1	541.7	499.0	469.1	454.3	450.4
102.5°	589.6	638.3	645.3	630.2	603.9	582.2	566.7	563.5
105°	550.1	635.1	683.7	703.9	704.8	700.9	694.0	691.0
107.5°	494.0	584.4	653.0	696.7	721.0	732.2	737.1	738.4
110°	460.2	545.2	616.4	670.5	705.3	725.9	734.8	739.2



TEST NUMBER: P332996-935

CATALOG NUMBER: SA4XXRDIP-C1195D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	435.5	510.6	577.9	631.9	671.5	696.5	708.9	716.0
115°	410.6	471.1	528.5	575.7	614.4	643.9	659.6	663.6
117.5°	398.4	448.4	493.6	533.6	566.7	591.4	607.3	610.4
120°	393.0	438.6	477.9	512.7	540.8	562.4	575.1	580.6
122.5°	388.2	432.3	468.0	498.6	522.3	540.8	551.6	557.0
125°	380.1	422.4	456.2	483.3	502.9	517.2	526.5	529.4
127.5°	370.3	410.7	444.5	470.1	489.9	502.6	510.4	513.3
130°	362.5	401.3	434.6	460.7	480.9	493.1	501.0	503.9
132.5°	354.2	390.6	423.3	449.3	469.1	482.9	490.3	493.4
135°	342.9	374.8	404.7	429.3	448.9	462.7	470.5	473.5
137.5°	332.5	359.6	384.8	407.0	425.3	438.9	445.4	448.9
140°	326.6	349.7	371.8	392.4	409.7	420.4	427.3	431.3
142.5°	321.2	341.5	360.4	378.3	393.5	403.6	409.7	412.3
145°	313.3	330.0	344.8	358.5	370.8	379.2	384.1	386.5
147.5°	306.9	320.2	332.0	342.9	351.9	359.0	362.7	363.7
150°	303.1	314.4	324.2	333.0	340.9	347.2	350.2	350.7
152.5°	298.7	308.4	317.5	324.8	331.4	336.7	338.4	338.9
155°	292.2	300.1	307.5	313.3	318.3	322.2	323.6	323.6
157.5°	285.2	291.9	298.0	302.7	306.5	309.4	310.3	310.3
160°	280.9	286.4	291.7	295.7	298.6	301.6	302.0	302.0
162.5°	276.6	281.2	285.4	289.0	291.2	294.1	294.6	294.2
165°	270.6	273.5	277.0	279.5	281.5	283.4	282.9	282.4
167.5°	264.8	267.1	269.8	271.3	272.3	273.5	273.5	273.1
170°	261.3	262.8	264.8	266.2	267.2	267.7	267.2	267.2
172.5°	258.1	259.2	260.5	261.5	262.1	262.6	262.1	261.3
175°	253.9	254.4	255.4	255.4	255.4	256.4	255.4	254.4
177.5°	251.2	251.6	251.6	251.9	251.6	251.9	251.2	250.4
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0

(END OF REPORT)