

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332999-935

Luminaire Tested: **SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332999-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6807.0 lumens  
Efficiency: N/A  
Efficacy: 112.1 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	61	60	59	55
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	53	51	47
3	85	76	69	63	80	71	65	60	63	58	54	56	52	49	49	46	44	40
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35
5	72	60	52	46	67	57	50	44	51	45	41	45	41	37	40	36	33	31
6	66	54	46	41	62	52	44	39	46	40	36	41	36	33	36	33	30	27
7	62	49	41	36	58	47	40	34	42	36	32	38	33	29	33	30	27	24
8	57	45	37	32	54	43	36	31	38	33	28	35	30	26	31	27	24	22
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	25	22	20
10	50	38	31	26	47	36	29	25	33	27	23	29	25	21	26	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13774	13774	13774	13774
5°	15977	13816	12211	13816
10°	18901	13755	10899	13755
15°	21833	13628	9365	13628
20°	24308	13454	8469	13454
25°	25093	13281	7863	13281
30°	21967	13073	7498	13073
35°	17100	12764	7276	12764
40°	12823	12410	7158	12410
45°	10123	11843	7096	11843
50°	8547	11189	6889	11189
55°	7450	10469	6521	10469
60°	6704	9723	5772	9723
65°	5910	8915	4963	8915
70°	5323	8080	4480	8080
75°	4460	7162	3815	7162
80°	3770	6104	3580	6104
85°	3186	4780	3186	4780



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.3	2.4
10°-20°	498.7	7.3
20°-30°	780.0	11.5
30°-40°	867.1	12.7
40°-50°	769.3	11.3
50°-60°	599.5	8.8
60°-70°	392.5	5.8
70°-80°	193.0	2.8
80°-90°	49.5	0.7
90°-100°	247.5	3.6
100°-110°	515.1	7.6
110°-120°	461.4	6.8
120°-130°	388.1	5.7
130°-140°	323.6	4.8
140°-150°	247.2	3.6
150°-160°	173.8	2.6
160°-170°	102.2	1.5
170°-180°	33.3	0.5
0°-30°	1444.0	21.2
0°-40°	2311.0	34.0
0°-60°	3679.8	54.1
0°-90°	4314.8	63.4
90°-120°	1224.0	18.0
90°-150°	2183.0	32.1
90°-180°	2492.0	36.6
0°-180°	6807.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1706	1706	1706	1706	1706	
5°	1972	1705	1507	1705	1972	199
15°	2612	1631	1120	1631	2612	743
25°	2817	1491	883	1491	2817	1250
35°	1735	1295	738	1295	1735	1088
45°	887	1037	622	1037	887	702
55°	529	744	463	744	529	481
65°	309	467	260	467	309	311
75°	143	230	122	230	143	157
85°	34	52	34	52	34	39
90°	14	1	14	1	14	13
95°	164	22	164	22	164	255
105°	947	79	947	79	947	937
115°	910	139	910	139	910	903
125°	726	193	726	193	726	659
135°	649	230	649	230	649	501
145°	530	265	530	265	530	336
155°	444	301	444	301	444	207
165°	387	328	387	328	387	111
175°	349	342	349	342	349	34
180°	343	343	343	343	343	



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1799.7	1804.7	1799.7	1799.1	1793.6	1792.0	1789.8	1782.6	1769.4	1761.8	1763.4
5°	1971.5	1988.7	1979.1	1977.7	1962.6	1947.5	1937.9	1915.9	1892.5	1876.7	1863.6
7.5°	2170.3	2180.2	2174.2	2164.6	2140.1	2126.2	2103.9	2074.9	2033.0	2001.0	1971.7
10°	2305.7	2313.9	2311.2	2293.3	2275.4	2238.9	2218.4	2177.8	2124.9	2082.9	2043.8
12.5°	2438.7	2447.6	2423.4	2424.1	2390.3	2361.6	2328.9	2277.9	2216.7	2162.7	2113.6
15°	2612.3	2601.3	2601.3	2587.5	2549.7	2509.8	2476.1	2422.5	2345.5	2280.9	2212.9
17.5°	2748.1	2751.9	2746.2	2713.9	2684.2	2642.9	2581.2	2518.6	2447.1	2360.3	2290.8
20°	2829.5	2829.5	2823.3	2801.3	2762.8	2718.8	2652.1	2584.0	2493.3	2406.0	2327.6
22.5°	2862.5	2864.6	2857.4	2839.2	2804.6	2761.7	2704.9	2635.8	2542.3	2443.9	2346.9
25°	2817.1	2830.2	2831.5	2826.7	2816.4	2790.2	2741.5	2670.6	2586.8	2480.3	2375.8
27.5°	2586.4	2602.9	2617.4	2641.1	2672.7	2689.2	2691.4	2655.4	2582.2	2479.7	2374.6
30°	2356.5	2370.2	2414.9	2473.4	2518.8	2560.0	2595.7	2605.4	2564.1	2472.0	2361.3
32.5°	2101.4	2120.0	2164.7	2227.6	2303.2	2373.0	2453.3	2494.2	2493.2	2437.9	2335.5
35°	1735.1	1748.9	1790.1	1856.1	1946.8	2050.6	2177.8	2276.7	2344.2	2339.3	2276.7
37.5°	1399.3	1414.9	1456.6	1511.2	1599.2	1727.8	1850.8	1987.2	2111.8	2181.8	2160.9
40°	1216.8	1217.5	1258.0	1314.4	1396.9	1508.9	1643.0	1794.2	1933.0	2046.5	2068.5
42.5°	1072.6	1072.8	1099.6	1160.4	1219.8	1325.3	1453.2	1603.4	1765.9	1896.9	1955.2
45°	886.7	892.9	915.0	951.4	998.2	1087.5	1189.9	1329.5	1511.7	1667.0	1763.9
47.5°	751.0	760.0	774.0	803.7	841.0	900.5	985.2	1110.6	1258.8	1429.7	1567.6
50°	680.5	681.9	699.8	716.3	748.6	796.1	870.3	974.7	1110.9	1275.1	1428.5
52.5°	620.1	619.7	630.5	651.4	677.7	714.6	774.6	869.7	990.4	1137.7	1296.0
55°	529.3	532.8	541.0	557.5	577.5	603.6	651.0	722.5	817.3	943.1	1086.8
57.5°	460.3	462.1	468.6	475.5	493.9	512.8	548.5	598.1	678.1	781.1	915.0
60°	415.2	415.9	417.9	428.3	442.7	460.5	484.7	526.6	593.9	688.1	794.0
62.5°	371.2	372.5	375.7	383.1	394.3	406.7	431.9	465.5	521.3	601.8	697.2
65°	309.4	310.0	314.9	317.6	326.5	337.5	356.1	378.8	417.2	484.7	556.8
67.5°	258.5	258.5	258.7	262.4	268.6	276.0	287.1	305.2	334.2	375.7	439.3
70°	225.5	225.5	226.9	228.9	232.4	238.5	244.7	258.5	279.8	313.5	362.3
72.5°	194.7	195.2	196.6	197.0	198.8	203.9	208.4	217.2	233.1	258.5	297.9
75°	143.0	145.1	148.5	151.3	154.6	153.9	158.8	164.3	169.1	184.3	206.9
77.5°	106.4	105.3	105.7	108.1	108.5	109.2	112.6	116.8	120.5	127.6	135.7
80°	81.1	81.1	83.2	83.9	83.2	83.9	87.3	89.4	90.7	93.5	101.1
82.5°	61.3	62.4	61.7	62.4	62.9	63.5	66.4	66.8	68.2	69.3	72.5
85°	34.4	35.0	35.7	34.4	34.4	34.4	35.7	36.4	37.8	37.1	38.5
87.5°	14.9	14.4	15.1	14.9	15.3	14.8	15.2	16.2	14.9	15.6	15.3
90°	14.1	14.1	14.8	14.1	13.4	13.4	12.8	12.1	11.5	12.1	10.8
92.5°	51.8	51.8	54.2	57.8	65.7	79.2	99.5	132.2	177.9	213.5	186.9
95°	164.3	173.1	185.1	206.0	239.0	304.3	394.5	498.9	564.2	548.7	414.1
97.5°	439.1	453.1	473.3	513.8	562.1	632.4	698.3	737.0	708.8	577.9	387.5
100°	617.3	622.8	642.9	684.0	742.6	792.4	825.4	811.9	713.6	541.3	351.5
102.5°	772.5	776.8	798.1	827.9	863.8	884.5	874.9	808.1	673.2	495.5	327.2
105°	947.3	951.3	960.7	966.1	964.8	937.1	870.5	754.1	599.9	441.6	306.3
107.5°	1012.1	1010.4	1003.7	988.3	955.0	895.0	801.2	677.2	540.6	411.5	302.6
110°	1013.2	1007.2	995.1	966.7	918.9	844.9	747.3	630.9	511.0	401.2	303.6



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	981.5	971.6	954.7	920.4	866.2	792.1	699.9	596.9	494.3	396.4	306.9
115°	909.6	904.1	882.6	842.2	789.0	724.4	645.7	562.8	478.6	393.8	313.1
117.5°	836.7	832.5	810.7	776.8	731.4	676.6	614.7	546.1	471.7	393.1	319.7
120°	795.7	788.3	770.9	741.2	702.8	655.0	601.2	538.6	467.9	393.1	324.5
122.5°	763.4	756.0	741.2	715.9	683.5	641.6	592.5	532.1	463.6	392.6	329.3
125°	725.7	721.7	708.9	689.4	662.5	625.4	579.0	521.1	456.4	391.8	336.7
127.5°	703.7	699.6	688.9	671.5	644.5	609.2	562.9	507.6	446.9	390.4	342.4
130°	690.8	686.7	676.0	659.1	631.5	595.8	550.0	496.9	441.0	389.8	346.7
132.5°	676.2	672.2	661.9	642.9	615.9	580.2	535.5	485.5	435.6	389.3	350.5
135°	649.0	645.0	634.2	615.4	588.4	554.7	513.7	469.9	427.5	388.5	356.1
137.5°	615.4	610.4	601.6	583.0	557.8	527.4	492.8	455.8	420.5	388.3	359.5
140°	591.1	585.7	576.3	561.5	538.0	509.6	479.3	447.7	416.7	387.8	362.2
142.5°	565.2	561.5	553.1	539.4	518.5	494.0	468.0	440.1	413.5	387.8	364.4
145°	529.9	526.5	519.7	508.3	491.5	472.6	452.5	429.6	407.9	386.4	365.6
147.5°	498.4	497.2	492.1	482.3	469.9	455.1	438.9	420.8	403.0	384.0	366.3
150°	480.7	480.0	476.0	467.3	456.4	444.4	430.8	415.3	399.2	382.4	366.3
152.5°	464.5	463.8	461.4	454.3	445.1	435.1	422.8	409.5	394.9	379.7	365.2
155°	443.7	443.7	441.6	436.3	429.6	421.5	411.4	400.5	388.5	375.7	363.5
157.5°	425.3	425.3	424.1	420.1	415.0	408.5	400.0	391.0	381.9	371.5	361.8
160°	414.1	414.1	413.4	409.3	405.3	399.9	392.5	385.1	377.0	368.2	360.2
162.5°	403.3	403.8	403.1	399.1	396.1	391.3	385.5	379.2	372.7	365.1	358.6
165°	387.1	387.8	388.5	385.7	383.1	379.7	375.0	370.9	365.6	360.2	355.5
167.5°	374.3	374.9	375.0	373.2	371.9	369.9	366.1	363.0	359.1	355.3	352.2
170°	366.3	366.3	366.9	366.3	364.9	362.9	360.2	358.2	354.8	352.1	350.1
172.5°	358.2	359.2	359.9	359.2	358.4	357.0	355.3	353.9	351.0	348.9	347.9
175°	348.7	350.1	351.5	350.1	350.1	350.1	348.7	348.1	346.7	345.3	345.3
177.5°	343.2	344.3	345.3	344.8	345.3	344.8	344.8	344.3	343.7	343.2	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1757.9	1750.2	1746.4	1737.6	1727.1	1721.6	1716.7	1709.5	1700.1	1690.2	1683.1
5°	1847.1	1830.7	1810.0	1785.3	1763.2	1742.0	1723.4	1704.9	1683.5	1661.6	1639.5
7.5°	1938.7	1906.3	1871.2	1830.7	1791.1	1755.3	1722.3	1690.7	1654.9	1622.9	1593.7
10°	2002.5	1958.5	1909.7	1858.1	1806.6	1761.9	1717.9	1678.0	1634.0	1594.8	1561.9
12.5°	2054.2	2002.5	1943.8	1879.6	1817.6	1763.5	1713.0	1661.0	1610.9	1568.5	1524.5
15°	2139.9	2069.2	1990.1	1913.1	1832.7	1759.1	1691.1	1630.6	1573.6	1513.7	1471.8
17.5°	2199.0	2115.0	2018.9	1926.3	1831.3	1744.6	1666.0	1594.1	1528.2	1467.1	1417.2
20°	2234.1	2141.3	2034.8	1929.6	1823.1	1730.3	1645.7	1566.0	1497.9	1431.9	1380.4
22.5°	2253.9	2151.2	2034.8	1924.7	1814.3	1713.7	1620.9	1537.9	1463.8	1397.8	1340.7
25°	2260.3	2150.3	2031.4	1904.9	1783.9	1677.3	1581.1	1491.0	1408.5	1342.6	1282.0
27.5°	2251.5	2121.9	2000.2	1870.4	1745.5	1633.2	1532.1	1437.5	1355.0	1284.1	1222.1
30°	2238.3	2099.4	1968.8	1834.1	1707.5	1599.7	1493.1	1402.4	1316.5	1242.9	1180.3
32.5°	2209.7	2071.9	1931.4	1793.4	1665.3	1554.0	1452.9	1361.7	1277.4	1202.2	1135.7
35°	2153.0	2013.4	1860.9	1719.2	1593.5	1478.0	1383.1	1295.1	1214.7	1134.3	1064.1
37.5°	2078.4	1935.8	1784.0	1628.9	1503.0	1394.0	1306.9	1224.3	1145.8	1072.4	994.7
40°	2008.0	1878.1	1721.3	1567.4	1438.1	1332.9	1252.5	1177.6	1098.5	1025.6	948.0
42.5°	1922.8	1812.1	1653.7	1499.2	1371.6	1270.2	1195.3	1122.1	1050.2	979.5	898.5
45°	1780.5	1696.6	1548.1	1399.6	1271.1	1170.7	1102.0	1037.3	974.0	906.7	830.4
47.5°	1617.4	1560.6	1432.4	1280.4	1161.5	1071.2	1004.8	951.9	898.5	831.1	764.1
50°	1504.1	1467.7	1343.9	1205.1	1091.7	1008.5	940.4	890.9	846.2	781.6	721.8
52.5°	1383.1	1363.7	1259.2	1126.4	1016.8	935.3	877.2	832.6	787.4	733.7	677.8
55°	1198.9	1209.2	1120.5	1005.7	902.6	833.9	780.9	743.8	705.3	660.0	616.6
57.5°	1010.6	1048.2	988.7	887.9	791.3	727.7	687.9	656.6	624.3	586.7	549.7
60°	897.8	929.4	895.7	807.0	722.5	663.4	626.3	602.2	569.9	535.5	507.3
62.5°	787.8	821.7	801.7	730.0	651.5	600.7	567.9	545.5	521.5	491.5	462.3
65°	649.6	671.6	662.0	612.5	556.8	513.5	483.3	466.7	444.8	422.8	396.7
67.5°	497.6	540.0	534.4	508.2	460.0	426.2	406.4	391.8	371.8	355.4	337.7
70°	409.1	448.2	447.5	426.2	400.1	368.4	354.7	342.3	324.4	308.7	294.2
72.5°	334.8	370.7	376.0	359.6	341.8	317.9	304.7	296.2	278.8	267.9	256.2
75°	234.5	260.5	267.4	267.4	259.2	246.8	235.1	229.6	217.2	207.6	200.7
77.5°	153.7	170.2	180.9	183.4	184.7	180.6	170.9	167.0	157.6	154.1	147.5
80°	108.6	119.6	132.0	136.1	139.6	138.2	134.1	131.3	122.3	118.9	116.1
82.5°	75.1	81.1	91.3	100.4	99.4	103.0	99.4	97.2	90.5	89.2	86.4
85°	39.2	39.9	41.2	47.4	50.9	52.3	53.0	51.6	49.5	49.5	44.7
87.5°	15.1	14.6	14.8	14.8	15.2	17.3	18.5	18.9	17.5	16.2	14.7
90°	9.4	9.4	5.4	5.4	4.7	4.0	2.0	0.7	2.0	4.0	4.7
92.5°	136.0	83.8	49.5	35.6	25.7	17.5	11.2	7.7	11.2	17.5	25.7
95°	253.1	142.8	84.1	55.9	39.7	31.0	24.2	22.2	24.2	31.0	39.7
97.5°	227.6	136.4	91.3	67.6	53.7	45.6	39.9	39.9	39.9	45.6	53.7
100°	214.1	138.0	98.3	76.7	64.0	55.9	51.1	51.1	51.1	55.9	64.0
102.5°	210.3	143.4	107.5	87.0	74.7	67.2	63.0	61.9	63.0	67.2	74.7
105°	212.1	156.2	123.9	104.4	92.2	84.1	80.8	78.8	80.8	84.1	92.2
107.5°	222.1	171.2	141.5	122.3	110.6	102.0	98.7	97.4	98.7	102.0	110.6
110°	229.5	182.4	152.8	134.7	122.5	114.4	111.1	109.8	111.1	114.4	122.5





TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	237.6	193.2	164.7	146.5	134.4	126.8	123.0	121.6	123.0	126.8	134.4
115°	250.5	210.1	183.1	165.0	152.1	145.4	140.7	138.7	140.7	145.4	152.1
117.5°	263.5	226.4	200.8	181.9	170.0	162.6	158.3	156.4	158.3	162.6	170.0
120°	272.7	237.6	212.1	193.2	181.8	174.4	169.6	168.3	169.6	174.4	181.8
122.5°	281.3	248.4	222.8	204.5	192.0	185.1	180.5	179.1	180.5	185.1	192.0
125°	294.2	263.2	239.0	220.2	207.3	199.9	195.9	193.2	195.9	199.9	207.3
127.5°	305.4	277.0	253.6	234.5	221.2	212.8	207.9	205.8	207.9	212.8	221.2
130°	312.4	286.1	263.2	243.7	230.9	220.8	215.4	212.8	215.4	220.8	230.9
132.5°	319.3	293.7	270.8	252.4	238.5	228.9	221.9	219.7	221.9	228.9	238.5
135°	328.6	304.3	282.1	264.6	250.5	239.0	232.3	229.5	232.3	239.0	250.5
137.5°	335.0	312.4	291.6	274.9	260.3	249.3	241.9	239.4	241.9	249.3	260.3
140°	339.3	317.8	297.6	281.4	267.3	255.8	248.4	246.4	248.4	255.8	267.3
142.5°	342.5	322.6	303.0	287.3	273.7	262.9	256.0	253.9	256.0	262.9	273.7
145°	346.0	327.9	310.4	295.6	282.8	273.4	266.6	264.6	266.6	273.4	282.8
147.5°	349.1	333.3	316.8	303.5	292.8	283.2	277.2	276.6	277.2	283.2	292.8
150°	350.8	336.0	321.2	308.3	298.3	290.2	284.8	284.1	284.8	290.2	298.3
152.5°	351.8	338.1	324.9	313.2	304.2	296.6	291.3	291.1	291.3	296.6	304.2
155°	352.8	341.3	329.8	319.8	312.4	305.7	301.6	300.9	301.6	305.7	312.4
157.5°	352.8	343.6	333.9	326.0	319.5	314.3	310.5	310.5	310.5	314.3	319.5
160°	352.8	344.7	336.7	329.2	323.8	319.1	316.4	316.4	316.4	319.1	323.8
162.5°	352.8	345.8	338.2	332.4	327.6	323.4	321.2	321.8	321.2	323.4	327.6
165°	351.5	346.0	340.0	336.0	332.6	329.2	327.9	327.9	327.9	329.2	332.6
167.5°	349.8	345.9	341.5	338.4	336.5	333.9	333.3	333.9	333.3	333.9	336.5
170°	348.7	345.3	342.0	340.0	338.6	336.7	336.0	336.7	336.0	336.7	338.6
172.5°	347.7	344.8	342.5	341.0	340.3	338.8	338.6	339.3	338.6	338.8	340.3
175°	346.0	344.1	342.7	342.7	342.0	341.3	341.3	342.0	341.3	341.3	342.0
177.5°	344.3	343.2	342.7	342.7	342.7	342.2	342.7	343.2	342.7	342.2	342.7
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1675.4	1669.9	1662.8	1654.5	1644.6	1635.8	1631.9	1635.3	1636.9	1632.5	1631.9
5°	1624.4	1607.2	1593.5	1572.9	1556.3	1542.6	1533.0	1528.9	1530.3	1519.2	1516.5
7.5°	1567.1	1546.7	1524.1	1499.7	1476.9	1456.6	1446.0	1440.3	1428.7	1423.7	1415.3
10°	1530.3	1502.7	1480.7	1451.8	1425.7	1401.7	1390.0	1380.4	1368.6	1363.1	1351.5
12.5°	1492.3	1460.3	1436.1	1406.2	1379.5	1350.6	1339.4	1321.5	1303.2	1291.7	1276.7
15°	1438.8	1400.3	1370.7	1335.0	1303.4	1270.4	1240.8	1207.8	1195.4	1169.3	1154.2
17.5°	1376.2	1337.2	1300.6	1252.7	1203.9	1162.9	1131.4	1099.8	1080.8	1064.1	1056.4
20°	1335.0	1299.2	1248.4	1192.7	1138.4	1093.0	1067.6	1047.0	1026.3	1014.7	1006.4
22.5°	1296.0	1250.3	1191.2	1131.1	1076.8	1041.3	1019.8	998.6	981.8	970.7	959.7
25°	1230.5	1170.7	1108.1	1039.4	1002.3	971.4	948.0	930.7	920.5	906.0	900.5
27.5°	1163.3	1090.8	1021.8	975.6	936.9	908.6	888.3	875.4	862.3	853.1	845.9
30°	1111.6	1038.0	976.1	932.1	892.9	869.6	853.1	838.0	827.7	820.1	814.6
32.5°	1060.4	986.9	934.9	887.6	856.7	833.9	816.2	804.9	796.9	787.1	783.8
35°	986.4	921.2	875.8	833.2	801.5	780.9	767.2	755.5	748.6	745.9	743.8
37.5°	915.4	861.9	813.1	778.2	750.0	733.7	717.6	711.8	707.1	702.1	704.4
40°	870.3	820.1	776.8	739.7	717.0	699.1	689.5	682.6	678.5	678.5	678.5
42.5°	831.2	782.1	739.9	706.7	684.0	668.9	658.1	652.4	651.0	650.5	653.8
45°	770.6	725.2	682.6	655.1	635.8	620.8	614.6	609.8	609.8	612.5	613.2
47.5°	710.5	668.0	633.8	603.0	585.4	575.9	570.6	568.1	568.3	571.1	574.3
50°	673.6	631.7	598.1	570.6	554.1	545.1	540.3	539.0	540.3	540.3	545.1
52.5°	633.5	596.0	562.8	539.8	521.1	512.7	510.1	508.2	508.9	511.2	513.2
55°	574.7	541.0	509.4	487.4	473.6	468.1	461.9	462.6	461.2	462.6	462.6
57.5°	515.7	485.4	456.1	438.6	426.5	418.5	411.7	413.7	411.6	411.4	410.3
60°	477.8	444.8	421.4	405.6	391.8	385.0	378.8	380.1	378.1	376.7	373.9
62.5°	436.5	409.1	386.8	371.5	360.5	352.5	346.3	344.9	340.2	335.4	329.4
65°	376.7	354.0	334.1	319.7	309.4	303.2	298.3	294.2	283.9	272.9	267.4
67.5°	318.6	302.2	283.6	271.4	263.0	254.9	245.7	238.7	229.0	223.0	219.6
70°	281.1	265.4	249.5	237.8	228.9	221.4	211.0	206.2	199.3	196.6	193.2
72.5°	245.4	230.7	216.0	205.4	195.9	190.0	181.9	177.1	174.1	173.0	169.5
75°	191.1	179.4	168.4	158.8	151.3	147.1	143.7	140.3	138.9	132.7	129.2
77.5°	139.4	131.7	124.8	118.0	112.6	109.9	103.2	99.3	96.9	94.0	93.3
80°	108.6	103.1	96.3	92.1	84.6	81.8	79.0	78.4	77.7	77.0	76.3
82.5°	81.7	76.2	69.3	66.8	64.7	63.1	61.5	60.8	60.1	60.5	60.4
85°	41.2	38.5	38.5	37.8	37.1	36.4	35.7	35.7	35.0	35.7	35.0
87.5°	14.8	14.3	15.1	13.9	14.8	15.1	14.4	14.6	15.2	14.2	14.2
90°	5.4	5.4	9.4	9.4	10.8	12.1	11.5	12.1	12.8	13.4	13.4
92.5°	35.6	49.5	83.8	136.0	186.9	213.5	177.9	132.2	99.5	79.2	65.7
95°	55.9	84.1	142.8	253.1	414.1	548.7	564.2	498.9	394.5	304.3	239.0
97.5°	67.6	91.3	136.4	227.6	387.5	577.9	708.8	737.0	698.3	632.4	562.1
100°	76.7	98.3	138.0	214.1	351.5	541.3	713.6	811.9	825.4	792.4	742.6
102.5°	87.0	107.5	143.4	210.3	327.2	495.5	673.2	808.1	874.9	884.5	863.8
105°	104.4	123.9	156.2	212.1	306.3	441.6	599.9	754.1	870.5	937.1	964.8
107.5°	122.3	141.5	171.2	222.1	302.6	411.5	540.6	677.2	801.2	895.0	955.0
110°	134.7	152.8	182.4	229.5	303.6	401.2	511.0	630.9	747.3	844.9	918.9



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	146.5	164.7	193.2	237.6	306.9	396.4	494.3	596.9	699.9	792.1	866.2
115°	165.0	183.1	210.1	250.5	313.1	393.8	478.6	562.8	645.7	724.4	789.0
117.5°	181.9	200.8	226.4	263.5	319.7	393.1	471.7	546.1	614.7	676.6	731.4
120°	193.2	212.1	237.6	272.7	324.5	393.1	467.9	538.6	601.2	655.0	702.8
122.5°	204.5	222.8	248.4	281.3	329.3	392.6	463.6	532.1	592.5	641.6	683.5
125°	220.2	239.0	263.2	294.2	336.7	391.8	456.4	521.1	579.0	625.4	662.5
127.5°	234.5	253.6	277.0	305.4	342.4	390.4	446.9	507.6	562.9	609.2	644.5
130°	243.7	263.2	286.1	312.4	346.7	389.8	441.0	496.9	550.0	595.8	631.5
132.5°	252.4	270.8	293.7	319.3	350.5	389.3	435.6	485.5	535.5	580.2	615.9
135°	264.6	282.1	304.3	328.6	356.1	388.5	427.5	469.9	513.7	554.7	588.4
137.5°	274.9	291.6	312.4	335.0	359.5	388.3	420.5	455.8	492.8	527.4	557.8
140°	281.4	297.6	317.8	339.3	362.2	387.8	416.7	447.7	479.3	509.6	538.0
142.5°	287.3	303.0	322.6	342.5	364.4	387.8	413.5	440.1	468.0	494.0	518.5
145°	295.6	310.4	327.9	346.0	365.6	386.4	407.9	429.6	452.5	472.6	491.5
147.5°	303.5	316.8	333.3	349.1	366.3	384.0	403.0	420.8	438.9	455.1	469.9
150°	308.3	321.2	336.0	350.8	366.3	382.4	399.2	415.3	430.8	444.4	456.4
152.5°	313.2	324.9	338.1	351.8	365.2	379.7	394.9	409.5	422.8	435.1	445.1
155°	319.8	329.8	341.3	352.8	363.5	375.7	388.5	400.5	411.4	421.5	429.6
157.5°	326.0	333.9	343.6	352.8	361.8	371.5	381.9	391.0	400.0	408.5	415.0
160°	329.2	336.7	344.7	352.8	360.2	368.2	377.0	385.1	392.5	399.9	405.3
162.5°	332.4	338.2	345.8	352.8	358.6	365.1	372.7	379.2	385.5	391.3	396.1
165°	336.0	340.0	346.0	351.5	355.5	360.2	365.6	370.9	375.0	379.7	383.1
167.5°	338.4	341.5	345.9	349.8	352.2	355.3	359.1	363.0	366.1	369.9	371.9
170°	340.0	342.0	345.3	348.7	350.1	352.1	354.8	358.2	360.2	362.9	364.9
172.5°	341.0	342.5	344.8	347.7	347.9	348.9	351.0	353.9	355.3	357.0	358.4
175°	342.7	342.7	344.1	346.0	345.3	345.3	346.7	348.1	348.7	350.1	350.1
177.5°	342.7	342.7	343.2	344.3	343.2	343.2	343.7	344.3	344.8	344.8	345.3
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1628.7	1629.8	1625.9	1624.8	1625.9	1629.8	1628.7	1631.9	1632.5	1636.9	1635.3
5°	1511.0	1509.6	1506.1	1506.8	1506.1	1509.6	1511.0	1516.5	1519.2	1530.3	1528.9
7.5°	1410.3	1405.0	1406.4	1401.0	1406.4	1405.0	1410.3	1415.3	1423.7	1428.7	1440.3
10°	1348.8	1341.2	1335.0	1329.5	1335.0	1341.2	1348.8	1351.5	1363.1	1368.6	1380.4
12.5°	1264.6	1258.1	1249.7	1251.4	1249.7	1258.1	1264.6	1276.7	1291.7	1303.2	1321.5
15°	1145.2	1135.0	1118.4	1120.5	1118.4	1135.0	1145.2	1154.2	1169.3	1195.4	1207.8
17.5°	1044.2	1044.3	1036.8	1038.5	1036.8	1044.3	1044.2	1056.4	1064.1	1080.8	1099.8
20°	992.0	987.1	987.8	985.8	987.8	987.1	992.0	1006.4	1014.7	1026.3	1047.0
22.5°	955.6	949.8	944.9	940.6	944.9	949.8	955.6	959.7	970.7	981.8	998.6
25°	894.3	890.2	884.1	882.7	884.1	890.2	894.3	900.5	906.0	920.5	930.7
27.5°	840.4	839.6	837.2	834.0	837.2	839.6	840.4	845.9	853.1	862.3	875.4
30°	809.1	807.7	806.3	804.3	806.3	807.7	809.1	814.6	820.1	827.7	838.0
32.5°	781.1	780.2	778.9	779.0	778.9	780.2	781.1	783.8	787.1	796.9	804.9
35°	741.1	740.4	739.0	738.3	739.0	740.4	741.1	743.8	745.9	748.6	755.5
37.5°	703.7	705.4	704.6	704.5	704.6	705.4	703.7	704.4	702.1	707.1	711.8
40°	677.8	678.5	679.8	679.2	679.8	678.5	677.8	678.5	678.5	678.5	682.6
42.5°	656.3	656.5	658.4	656.1	658.4	656.5	656.3	653.8	650.5	651.0	652.4
45°	618.0	622.2	621.5	621.5	621.5	622.2	618.0	613.2	612.5	609.8	609.8
47.5°	576.1	579.6	580.6	580.5	580.6	579.6	576.1	574.3	571.1	568.3	568.1
50°	548.5	547.2	549.2	548.5	549.2	547.2	548.5	545.1	540.3	540.3	539.0
52.5°	515.1	515.3	515.1	514.4	515.1	515.3	515.1	513.2	511.2	508.9	508.2
55°	463.3	464.0	462.6	463.3	462.6	464.0	463.3	462.6	462.6	461.2	462.6
57.5°	407.3	403.9	405.3	403.6	405.3	403.9	407.3	410.3	411.4	411.6	413.7
60°	367.1	361.6	360.2	357.5	360.2	361.6	367.1	373.9	376.7	378.1	380.1
62.5°	322.0	318.1	313.5	315.6	313.5	318.1	322.0	329.4	335.4	340.2	344.9
65°	261.9	259.2	257.1	259.8	257.1	259.2	261.9	267.4	272.9	283.9	294.2
67.5°	216.8	215.3	215.3	214.0	215.3	215.3	216.8	219.6	223.0	229.0	238.7
70°	193.2	191.1	191.1	189.8	191.1	191.1	193.2	193.2	196.6	199.3	206.2
72.5°	168.9	166.9	167.5	166.6	167.5	166.9	168.9	169.5	173.0	174.1	177.1
75°	125.1	121.7	121.7	122.3	121.7	121.7	125.1	129.2	132.7	138.9	140.3
77.5°	93.3	92.6	93.6	92.4	93.6	92.6	93.3	93.3	94.0	96.9	99.3
80°	76.3	75.6	74.9	77.0	74.9	75.6	76.3	76.3	77.0	77.7	78.4
82.5°	59.2	59.2	59.0	61.6	59.0	59.2	59.2	60.4	60.5	60.1	60.8
85°	35.7	34.4	35.7	34.4	35.7	34.4	35.7	35.0	35.7	35.0	35.7
87.5°	15.5	15.1	14.4	14.9	14.4	15.1	15.5	14.2	14.2	15.2	14.6
90°	14.1	14.8	14.1	14.1	14.1	14.8	14.1	13.4	13.4	12.8	12.1
92.5°	57.8	54.2	51.8	51.8	51.8	54.2	57.8	65.7	79.2	99.5	132.2
95°	206.0	185.1	173.1	164.3	173.1	185.1	206.0	239.0	304.3	394.5	498.9
97.5°	513.8	473.3	453.1	439.1	453.1	473.3	513.8	562.1	632.4	698.3	737.0
100°	684.0	642.9	622.8	617.3	622.8	642.9	684.0	742.6	792.4	825.4	811.9
102.5°	827.9	798.1	776.8	772.5	776.8	798.1	827.9	863.8	884.5	874.9	808.1
105°	966.1	960.7	951.3	947.3	951.3	960.7	966.1	964.8	937.1	870.5	754.1
107.5°	988.3	1003.7	1010.4	1012.1	1010.4	1003.7	988.3	955.0	895.0	801.2	677.2
110°	966.7	995.1	1007.2	1013.2	1007.2	995.1	966.7	918.9	844.9	747.3	630.9



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	920.4	954.7	971.6	981.5	971.6	954.7	920.4	866.2	792.1	699.9	596.9
115°	842.2	882.6	904.1	909.6	904.1	882.6	842.2	789.0	724.4	645.7	562.8
117.5°	776.8	810.7	832.5	836.7	832.5	810.7	776.8	731.4	676.6	614.7	546.1
120°	741.2	770.9	788.3	795.7	788.3	770.9	741.2	702.8	655.0	601.2	538.6
122.5°	715.9	741.2	756.0	763.4	756.0	741.2	715.9	683.5	641.6	592.5	532.1
125°	689.4	708.9	721.7	725.7	721.7	708.9	689.4	662.5	625.4	579.0	521.1
127.5°	671.5	688.9	699.6	703.7	699.6	688.9	671.5	644.5	609.2	562.9	507.6
130°	659.1	676.0	686.7	690.8	686.7	676.0	659.1	631.5	595.8	550.0	496.9
132.5°	642.9	661.9	672.2	676.2	672.2	661.9	642.9	615.9	580.2	535.5	485.5
135°	615.4	634.2	645.0	649.0	645.0	634.2	615.4	588.4	554.7	513.7	469.9
137.5°	583.0	601.6	610.4	615.4	610.4	601.6	583.0	557.8	527.4	492.8	455.8
140°	561.5	576.3	585.7	591.1	585.7	576.3	561.5	538.0	509.6	479.3	447.7
142.5°	539.4	553.1	561.5	565.2	561.5	553.1	539.4	518.5	494.0	468.0	440.1
145°	508.3	519.7	526.5	529.9	526.5	519.7	508.3	491.5	472.6	452.5	429.6
147.5°	482.3	492.1	497.2	498.4	497.2	492.1	482.3	469.9	455.1	438.9	420.8
150°	467.3	476.0	480.0	480.7	480.0	476.0	467.3	456.4	444.4	430.8	415.3
152.5°	454.3	461.4	463.8	464.5	463.8	461.4	454.3	445.1	435.1	422.8	409.5
155°	436.3	441.6	443.7	443.7	443.7	441.6	436.3	429.6	421.5	411.4	400.5
157.5°	420.1	424.1	425.3	425.3	425.3	424.1	420.1	415.0	408.5	400.0	391.0
160°	409.3	413.4	414.1	414.1	414.1	413.4	409.3	405.3	399.9	392.5	385.1
162.5°	399.1	403.1	403.8	403.3	403.8	403.1	399.1	396.1	391.3	385.5	379.2
165°	385.7	388.5	387.8	387.1	387.8	388.5	385.7	383.1	379.7	375.0	370.9
167.5°	373.2	375.0	374.9	374.3	374.9	375.0	373.2	371.9	369.9	366.1	363.0
170°	366.3	366.9	366.3	366.3	366.3	366.9	366.3	364.9	362.9	360.2	358.2
172.5°	359.2	359.9	359.2	358.2	359.2	359.9	359.2	358.4	357.0	355.3	353.9
175°	350.1	351.5	350.1	348.7	350.1	351.5	350.1	350.1	350.1	348.7	348.1
177.5°	344.8	345.3	344.3	343.2	344.3	345.3	344.8	345.3	344.8	344.8	344.3
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1631.9	1635.8	1644.6	1654.5	1662.8	1669.9	1675.4	1683.1	1690.2	1700.1	1709.5
5°	1533.0	1542.6	1556.3	1572.9	1593.5	1607.2	1624.4	1639.5	1661.6	1683.5	1704.9
7.5°	1446.0	1456.6	1476.9	1499.7	1524.1	1546.7	1567.1	1593.7	1622.9	1654.9	1690.7
10°	1390.0	1401.7	1425.7	1451.8	1480.7	1502.7	1530.3	1561.9	1594.8	1634.0	1678.0
12.5°	1339.4	1350.6	1379.5	1406.2	1436.1	1460.3	1492.3	1524.5	1568.5	1610.9	1661.0
15°	1240.8	1270.4	1303.4	1335.0	1370.7	1400.3	1438.8	1471.8	1513.7	1573.6	1630.6
17.5°	1131.4	1162.9	1203.9	1252.7	1300.6	1337.2	1376.2	1417.2	1467.1	1528.2	1594.1
20°	1067.6	1093.0	1138.4	1192.7	1248.4	1299.2	1335.0	1380.4	1431.9	1497.9	1566.0
22.5°	1019.8	1041.3	1076.8	1131.1	1191.2	1250.3	1296.0	1340.7	1397.8	1463.8	1537.9
25°	948.0	971.4	1002.3	1039.4	1108.1	1170.7	1230.5	1282.0	1342.6	1408.5	1491.0
27.5°	888.3	908.6	936.9	975.6	1021.8	1090.8	1163.3	1222.1	1284.1	1355.0	1437.5
30°	853.1	869.6	892.9	932.1	976.1	1038.0	1111.6	1180.3	1242.9	1316.5	1402.4
32.5°	816.2	833.9	856.7	887.6	934.9	986.9	1060.4	1135.7	1202.2	1277.4	1361.7
35°	767.2	780.9	801.5	833.2	875.8	921.2	986.4	1064.1	1134.3	1214.7	1295.1
37.5°	717.6	733.7	750.0	778.2	813.1	861.9	915.4	994.7	1072.4	1145.8	1224.3
40°	689.5	699.1	717.0	739.7	776.8	820.1	870.3	948.0	1025.6	1098.5	1177.6
42.5°	658.1	668.9	684.0	706.7	739.9	782.1	831.2	898.5	979.5	1050.2	1122.1
45°	614.6	620.8	635.8	655.1	682.6	725.2	770.6	830.4	906.7	974.0	1037.3
47.5°	570.6	575.9	585.4	603.0	633.8	668.0	710.5	764.1	831.1	898.5	951.9
50°	540.3	545.1	554.1	570.6	598.1	631.7	673.6	721.8	781.6	846.2	890.9
52.5°	510.1	512.7	521.1	539.8	562.8	596.0	633.5	677.8	733.7	787.4	832.6
55°	461.9	468.1	473.6	487.4	509.4	541.0	574.7	616.6	660.0	705.3	743.8
57.5°	411.7	418.5	426.5	438.6	456.1	485.4	515.7	549.7	586.7	624.3	656.6
60°	378.8	385.0	391.8	405.6	421.4	444.8	477.8	507.3	535.5	569.9	602.2
62.5°	346.3	352.5	360.5	371.5	386.8	409.1	436.5	462.3	491.5	521.5	545.5
65°	298.3	303.2	309.4	319.7	334.1	354.0	376.7	396.7	422.8	444.8	466.7
67.5°	245.7	254.9	263.0	271.4	283.6	302.2	318.6	337.7	355.4	371.8	391.8
70°	211.0	221.4	228.9	237.8	249.5	265.4	281.1	294.2	308.7	324.4	342.3
72.5°	181.9	190.0	195.9	205.4	216.0	230.7	245.4	256.2	267.9	278.8	296.2
75°	143.7	147.1	151.3	158.8	168.4	179.4	191.1	200.7	207.6	217.2	229.6
77.5°	103.2	109.9	112.6	118.0	124.8	131.7	139.4	147.5	154.1	157.6	167.0
80°	79.0	81.8	84.6	92.1	96.3	103.1	108.6	116.1	118.9	122.3	131.3
82.5°	61.5	63.1	64.7	66.8	69.3	76.2	81.7	86.4	89.2	90.5	97.2
85°	35.7	36.4	37.1	37.8	38.5	38.5	41.2	44.7	49.5	49.5	51.6
87.5°	14.4	15.1	14.8	13.9	15.1	14.3	14.8	14.7	16.2	17.5	18.9
90°	11.5	12.1	10.8	9.4	9.4	5.4	5.4	4.7	4.0	2.0	0.7
92.5°	177.9	213.5	186.9	136.0	83.8	49.5	35.6	25.7	17.5	11.2	7.7
95°	564.2	548.7	414.1	253.1	142.8	84.1	55.9	39.7	31.0	24.2	22.2
97.5°	708.8	577.9	387.5	227.6	136.4	91.3	67.6	53.7	45.6	39.9	39.9
100°	713.6	541.3	351.5	214.1	138.0	98.3	76.7	64.0	55.9	51.1	51.1
102.5°	673.2	495.5	327.2	210.3	143.4	107.5	87.0	74.7	67.2	63.0	61.9
105°	599.9	441.6	306.3	212.1	156.2	123.9	104.4	92.2	84.1	80.8	78.8
107.5°	540.6	411.5	302.6	222.1	171.2	141.5	122.3	110.6	102.0	98.7	97.4
110°	511.0	401.2	303.6	229.5	182.4	152.8	134.7	122.5	114.4	111.1	109.8



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.3	396.4	306.9	237.6	193.2	164.7	146.5	134.4	126.8	123.0	121.6
115°	478.6	393.8	313.1	250.5	210.1	183.1	165.0	152.1	145.4	140.7	138.7
117.5°	471.7	393.1	319.7	263.5	226.4	200.8	181.9	170.0	162.6	158.3	156.4
120°	467.9	393.1	324.5	272.7	237.6	212.1	193.2	181.8	174.4	169.6	168.3
122.5°	463.6	392.6	329.3	281.3	248.4	222.8	204.5	192.0	185.1	180.5	179.1
125°	456.4	391.8	336.7	294.2	263.2	239.0	220.2	207.3	199.9	195.9	193.2
127.5°	446.9	390.4	342.4	305.4	277.0	253.6	234.5	221.2	212.8	207.9	205.8
130°	441.0	389.8	346.7	312.4	286.1	263.2	243.7	230.9	220.8	215.4	212.8
132.5°	435.6	389.3	350.5	319.3	293.7	270.8	252.4	238.5	228.9	221.9	219.7
135°	427.5	388.5	356.1	328.6	304.3	282.1	264.6	250.5	239.0	232.3	229.5
137.5°	420.5	388.3	359.5	335.0	312.4	291.6	274.9	260.3	249.3	241.9	239.4
140°	416.7	387.8	362.2	339.3	317.8	297.6	281.4	267.3	255.8	248.4	246.4
142.5°	413.5	387.8	364.4	342.5	322.6	303.0	287.3	273.7	262.9	256.0	253.9
145°	407.9	386.4	365.6	346.0	327.9	310.4	295.6	282.8	273.4	266.6	264.6
147.5°	403.0	384.0	366.3	349.1	333.3	316.8	303.5	292.8	283.2	277.2	276.6
150°	399.2	382.4	366.3	350.8	336.0	321.2	308.3	298.3	290.2	284.8	284.1
152.5°	394.9	379.7	365.2	351.8	338.1	324.9	313.2	304.2	296.6	291.3	291.1
155°	388.5	375.7	363.5	352.8	341.3	329.8	319.8	312.4	305.7	301.6	300.9
157.5°	381.9	371.5	361.8	352.8	343.6	333.9	326.0	319.5	314.3	310.5	310.5
160°	377.0	368.2	360.2	352.8	344.7	336.7	329.2	323.8	319.1	316.4	316.4
162.5°	372.7	365.1	358.6	352.8	345.8	338.2	332.4	327.6	323.4	321.2	321.8
165°	365.6	360.2	355.5	351.5	346.0	340.0	336.0	332.6	329.2	327.9	327.9
167.5°	359.1	355.3	352.2	349.8	345.9	341.5	338.4	336.5	333.9	333.3	333.9
170°	354.8	352.1	350.1	348.7	345.3	342.0	340.0	338.6	336.7	336.0	336.7
172.5°	351.0	348.9	347.9	347.7	344.8	342.5	341.0	340.3	338.8	338.6	339.3
175°	346.7	345.3	345.3	346.0	344.1	342.7	342.7	342.0	341.3	341.3	342.0
177.5°	343.7	343.2	343.2	344.3	343.2	342.7	342.7	342.7	342.2	342.7	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7





TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1716.7	1721.6	1727.1	1737.6	1746.4	1750.2	1757.9	1763.4	1761.8	1769.4	1782.6
5°	1723.4	1742.0	1763.2	1785.3	1810.0	1830.7	1847.1	1863.6	1876.7	1892.5	1915.9
7.5°	1722.3	1755.3	1791.1	1830.7	1871.2	1906.3	1938.7	1971.7	2001.0	2033.0	2074.9
10°	1717.9	1761.9	1806.6	1858.1	1909.7	1958.5	2002.5	2043.8	2082.9	2124.9	2177.8
12.5°	1713.0	1763.5	1817.6	1879.6	1943.8	2002.5	2054.2	2113.6	2162.7	2216.7	2277.9
15°	1691.1	1759.1	1832.7	1913.1	1990.1	2069.2	2139.9	2212.9	2280.9	2345.5	2422.5
17.5°	1666.0	1744.6	1831.3	1926.3	2018.9	2115.0	2199.0	2290.8	2360.3	2447.1	2518.6
20°	1645.7	1730.3	1823.1	1929.6	2034.8	2141.3	2234.1	2327.6	2406.0	2493.3	2584.0
22.5°	1620.9	1713.7	1814.3	1924.7	2034.8	2151.2	2253.9	2346.9	2443.9	2542.3	2635.8
25°	1581.1	1677.3	1783.9	1904.9	2031.4	2150.3	2260.3	2375.8	2480.3	2586.8	2670.6
27.5°	1532.1	1633.2	1745.5	1870.4	2000.2	2121.9	2251.5	2374.6	2479.7	2582.2	2655.4
30°	1493.1	1599.7	1707.5	1834.1	1968.8	2099.4	2238.3	2361.3	2472.0	2564.1	2605.4
32.5°	1452.9	1554.0	1665.3	1793.4	1931.4	2071.9	2209.7	2335.5	2437.9	2493.2	2494.2
35°	1383.1	1478.0	1593.5	1719.2	1860.9	2013.4	2153.0	2276.7	2339.3	2344.2	2276.7
37.5°	1306.9	1394.0	1503.0	1628.9	1784.0	1935.8	2078.4	2160.9	2181.8	2111.8	1987.2
40°	1252.5	1332.9	1438.1	1567.4	1721.3	1878.1	2008.0	2068.5	2046.5	1933.0	1794.2
42.5°	1195.3	1270.2	1371.6	1499.2	1653.7	1812.1	1922.8	1955.2	1896.9	1765.9	1603.4
45°	1102.0	1170.7	1271.1	1399.6	1548.1	1696.6	1780.5	1763.9	1667.0	1511.7	1329.5
47.5°	1004.8	1071.2	1161.5	1280.4	1432.4	1560.6	1617.4	1567.6	1429.7	1258.8	1110.6
50°	940.4	1008.5	1091.7	1205.1	1343.9	1467.7	1504.1	1428.5	1275.1	1110.9	974.7
52.5°	877.2	935.3	1016.8	1126.4	1259.2	1363.7	1383.1	1296.0	1137.7	990.4	869.7
55°	780.9	833.9	902.6	1005.7	1120.5	1209.2	1198.9	1086.8	943.1	817.3	722.5
57.5°	687.9	727.7	791.3	887.9	988.7	1048.2	1010.6	915.0	781.1	678.1	598.1
60°	626.3	663.4	722.5	807.0	895.7	929.4	897.8	794.0	688.1	593.9	526.6
62.5°	567.9	600.7	651.5	730.0	801.7	821.7	787.8	697.2	601.8	521.3	465.5
65°	483.3	513.5	556.8	612.5	662.0	671.6	649.6	556.8	484.7	417.2	378.8
67.5°	406.4	426.2	460.0	508.2	534.4	540.0	497.6	439.3	375.7	334.2	305.2
70°	354.7	368.4	400.1	426.2	447.5	448.2	409.1	362.3	313.5	279.8	258.5
72.5°	304.7	317.9	341.8	359.6	376.0	370.7	334.8	297.9	258.5	233.1	217.2
75°	235.1	246.8	259.2	267.4	267.4	260.5	234.5	206.9	184.3	169.1	164.3
77.5°	170.9	180.6	184.7	183.4	180.9	170.2	153.7	135.7	127.6	120.5	116.8
80°	134.1	138.2	139.6	136.1	132.0	119.6	108.6	101.1	93.5	90.7	89.4
82.5°	99.4	103.0	99.4	100.4	91.3	81.1	75.1	72.5	69.3	68.2	66.8
85°	53.0	52.3	50.9	47.4	41.2	39.9	39.2	38.5	37.1	37.8	36.4
87.5°	18.5	17.3	15.2	14.8	14.8	14.6	15.1	15.3	15.6	14.9	16.2
90°	2.0	4.0	4.7	5.4	5.4	9.4	9.4	10.8	12.1	11.5	12.1
92.5°	11.2	17.5	25.7	35.6	49.5	83.8	136.0	186.9	213.5	177.9	132.2
95°	24.2	31.0	39.7	55.9	84.1	142.8	253.1	414.1	548.7	564.2	498.9
97.5°	39.9	45.6	53.7	67.6	91.3	136.4	227.6	387.5	577.9	708.8	737.0
100°	51.1	55.9	64.0	76.7	98.3	138.0	214.1	351.5	541.3	713.6	811.9
102.5°	63.0	67.2	74.7	87.0	107.5	143.4	210.3	327.2	495.5	673.2	808.1
105°	80.8	84.1	92.2	104.4	123.9	156.2	212.1	306.3	441.6	599.9	754.1
107.5°	98.7	102.0	110.6	122.3	141.5	171.2	222.1	302.6	411.5	540.6	677.2
110°	111.1	114.4	122.5	134.7	152.8	182.4	229.5	303.6	401.2	511.0	630.9





TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.0	126.8	134.4	146.5	164.7	193.2	237.6	306.9	396.4	494.3	596.9
115°	140.7	145.4	152.1	165.0	183.1	210.1	250.5	313.1	393.8	478.6	562.8
117.5°	158.3	162.6	170.0	181.9	200.8	226.4	263.5	319.7	393.1	471.7	546.1
120°	169.6	174.4	181.8	193.2	212.1	237.6	272.7	324.5	393.1	467.9	538.6
122.5°	180.5	185.1	192.0	204.5	222.8	248.4	281.3	329.3	392.6	463.6	532.1
125°	195.9	199.9	207.3	220.2	239.0	263.2	294.2	336.7	391.8	456.4	521.1
127.5°	207.9	212.8	221.2	234.5	253.6	277.0	305.4	342.4	390.4	446.9	507.6
130°	215.4	220.8	230.9	243.7	263.2	286.1	312.4	346.7	389.8	441.0	496.9
132.5°	221.9	228.9	238.5	252.4	270.8	293.7	319.3	350.5	389.3	435.6	485.5
135°	232.3	239.0	250.5	264.6	282.1	304.3	328.6	356.1	388.5	427.5	469.9
137.5°	241.9	249.3	260.3	274.9	291.6	312.4	335.0	359.5	388.3	420.5	455.8
140°	248.4	255.8	267.3	281.4	297.6	317.8	339.3	362.2	387.8	416.7	447.7
142.5°	256.0	262.9	273.7	287.3	303.0	322.6	342.5	364.4	387.8	413.5	440.1
145°	266.6	273.4	282.8	295.6	310.4	327.9	346.0	365.6	386.4	407.9	429.6
147.5°	277.2	283.2	292.8	303.5	316.8	333.3	349.1	366.3	384.0	403.0	420.8
150°	284.8	290.2	298.3	308.3	321.2	336.0	350.8	366.3	382.4	399.2	415.3
152.5°	291.3	296.6	304.2	313.2	324.9	338.1	351.8	365.2	379.7	394.9	409.5
155°	301.6	305.7	312.4	319.8	329.8	341.3	352.8	363.5	375.7	388.5	400.5
157.5°	310.5	314.3	319.5	326.0	333.9	343.6	352.8	361.8	371.5	381.9	391.0
160°	316.4	319.1	323.8	329.2	336.7	344.7	352.8	360.2	368.2	377.0	385.1
162.5°	321.2	323.4	327.6	332.4	338.2	345.8	352.8	358.6	365.1	372.7	379.2
165°	327.9	329.2	332.6	336.0	340.0	346.0	351.5	355.5	360.2	365.6	370.9
167.5°	333.3	333.9	336.5	338.4	341.5	345.9	349.8	352.2	355.3	359.1	363.0
170°	336.0	336.7	338.6	340.0	342.0	345.3	348.7	350.1	352.1	354.8	358.2
172.5°	338.6	338.8	340.3	341.0	342.5	344.8	347.7	347.9	348.9	351.0	353.9
175°	341.3	341.3	342.0	342.7	342.7	344.1	346.0	345.3	345.3	346.7	348.1
177.5°	342.7	342.2	342.7	342.7	342.7	343.2	344.3	343.2	343.2	343.7	344.3
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1789.8	1792.0	1793.6	1799.1	1799.7	1804.7	1799.7
5°	1937.9	1947.5	1962.6	1977.7	1979.1	1988.7	1971.5
7.5°	2103.9	2126.2	2140.1	2164.6	2174.2	2180.2	2170.3
10°	2218.4	2238.9	2275.4	2293.3	2311.2	2313.9	2305.7
12.5°	2328.9	2361.6	2390.3	2424.1	2423.4	2447.6	2438.7
15°	2476.1	2509.8	2549.7	2587.5	2601.3	2601.3	2612.3
17.5°	2581.2	2642.9	2684.2	2713.9	2746.2	2751.9	2748.1
20°	2652.1	2718.8	2762.8	2801.3	2823.3	2829.5	2829.5
22.5°	2704.9	2761.7	2804.6	2839.2	2857.4	2864.6	2862.5
25°	2741.5	2790.2	2816.4	2826.7	2831.5	2830.2	2817.1
27.5°	2691.4	2689.2	2672.7	2641.1	2617.4	2602.9	2586.4
30°	2595.7	2560.0	2518.8	2473.4	2414.9	2370.2	2356.5
32.5°	2453.3	2373.0	2303.2	2227.6	2164.7	2120.0	2101.4
35°	2177.8	2050.6	1946.8	1856.1	1790.1	1748.9	1735.1
37.5°	1850.8	1727.8	1599.2	1511.2	1456.6	1414.9	1399.3
40°	1643.0	1508.9	1396.9	1314.4	1258.0	1217.5	1216.8
42.5°	1453.2	1325.3	1219.8	1160.4	1099.6	1072.8	1072.6
45°	1189.9	1087.5	998.2	951.4	915.0	892.9	886.7
47.5°	985.2	900.5	841.0	803.7	774.0	760.0	751.0
50°	870.3	796.1	748.6	716.3	699.8	681.9	680.5
52.5°	774.6	714.6	677.7	651.4	630.5	619.7	620.1
55°	651.0	603.6	577.5	557.5	541.0	532.8	529.3
57.5°	548.5	512.8	493.9	475.5	468.6	462.1	460.3
60°	484.7	460.5	442.7	428.3	417.9	415.9	415.2
62.5°	431.9	406.7	394.3	383.1	375.7	372.5	371.2
65°	356.1	337.5	326.5	317.6	314.9	310.0	309.4
67.5°	287.1	276.0	268.6	262.4	258.7	258.5	258.5
70°	244.7	238.5	232.4	228.9	226.9	225.5	225.5
72.5°	208.4	203.9	198.8	197.0	196.6	195.2	194.7
75°	158.8	153.9	154.6	151.3	148.5	145.1	143.0
77.5°	112.6	109.2	108.5	108.1	105.7	105.3	106.4
80°	87.3	83.9	83.2	83.9	83.2	81.1	81.1
82.5°	66.4	63.5	62.9	62.4	61.7	62.4	61.3
85°	35.7	34.4	34.4	34.4	35.7	35.0	34.4
87.5°	15.2	14.8	15.3	14.9	15.1	14.4	14.9
90°	12.8	13.4	13.4	14.1	14.8	14.1	14.1
92.5°	99.5	79.2	65.7	57.8	54.2	51.8	51.8
95°	394.5	304.3	239.0	206.0	185.1	173.1	164.3
97.5°	698.3	632.4	562.1	513.8	473.3	453.1	439.1
100°	825.4	792.4	742.6	684.0	642.9	622.8	617.3
102.5°	874.9	884.5	863.8	827.9	798.1	776.8	772.5
105°	870.5	937.1	964.8	966.1	960.7	951.3	947.3
107.5°	801.2	895.0	955.0	988.3	1003.7	1010.4	1012.1
110°	747.3	844.9	918.9	966.7	995.1	1007.2	1013.2



TEST NUMBER: P332999-935

CATALOG NUMBER: SA4XXRDIP-C1195D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	699.9	792.1	866.2	920.4	954.7	971.6	981.5
115°	645.7	724.4	789.0	842.2	882.6	904.1	909.6
117.5°	614.7	676.6	731.4	776.8	810.7	832.5	836.7
120°	601.2	655.0	702.8	741.2	770.9	788.3	795.7
122.5°	592.5	641.6	683.5	715.9	741.2	756.0	763.4
125°	579.0	625.4	662.5	689.4	708.9	721.7	725.7
127.5°	562.9	609.2	644.5	671.5	688.9	699.6	703.7
130°	550.0	595.8	631.5	659.1	676.0	686.7	690.8
132.5°	535.5	580.2	615.9	642.9	661.9	672.2	676.2
135°	513.7	554.7	588.4	615.4	634.2	645.0	649.0
137.5°	492.8	527.4	557.8	583.0	601.6	610.4	615.4
140°	479.3	509.6	538.0	561.5	576.3	585.7	591.1
142.5°	468.0	494.0	518.5	539.4	553.1	561.5	565.2
145°	452.5	472.6	491.5	508.3	519.7	526.5	529.9
147.5°	438.9	455.1	469.9	482.3	492.1	497.2	498.4
150°	430.8	444.4	456.4	467.3	476.0	480.0	480.7
152.5°	422.8	435.1	445.1	454.3	461.4	463.8	464.5
155°	411.4	421.5	429.6	436.3	441.6	443.7	443.7
157.5°	400.0	408.5	415.0	420.1	424.1	425.3	425.3
160°	392.5	399.9	405.3	409.3	413.4	414.1	414.1
162.5°	385.5	391.3	396.1	399.1	403.1	403.8	403.3
165°	375.0	379.7	383.1	385.7	388.5	387.8	387.1
167.5°	366.1	369.9	371.9	373.2	375.0	374.9	374.3
170°	360.2	362.9	364.9	366.3	366.9	366.3	366.3
172.5°	355.3	357.0	358.4	359.2	359.9	359.2	358.2
175°	348.7	350.1	350.1	350.1	351.5	350.1	348.7
177.5°	344.8	344.8	345.3	344.8	345.3	344.3	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7

(END OF REPORT)