

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332515-830

Luminaire Tested: **SA4XXDIP-C350D810U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332515-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D810U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4075.0 lumens
Efficiency: N/A
Efficacy: 130.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332515-830
CATALOG NUMBER: SA4XXDIP-C350D810U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332515-830

CATALOG NUMBER: SA4XXDIP-C350D810U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	76	66	63	61	51	50	48	37	37	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	36	34	29	27	26	21
4	72	61	53	47	64	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	23	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332515-830

CATALOG NUMBER: SA4XXDIP-C350D810U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	1.3
10°-20°	147.7	3.6
20°-30°	217.4	5.3
30°-40°	252.8	6.2
40°-50°	252.8	6.2
50°-60°	221.1	5.4
60°-70°	164.2	4.0
70°-80°	93.3	2.3
80°-90°	29.8	0.7
90°-100°	62.8	1.5
100°-110°	186.2	4.6
110°-120°	316.0	7.8
120°-130°	416.6	10.2
130°-140°	467.9	11.5
140°-150°	459.8	11.3
150°-160°	386.7	9.5
160°-170°	257.3	6.3
170°-180°	90.1	2.2
0°-30°	417.6	10.2
0°-40°	670.4	16.5
0°-60°	1144.3	28.1
0°-90°	1431.6	35.1
90°-120°	565.0	13.9
90°-150°	1909.3	46.9
90°-180°	2643.0	64.9
0°-180°	4075.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	2	10	16	20	22	4
95°	44	51	56	58	58	49
105°	172	173	175	178	180	182
115°	321	321	320	319	318	317
125°	468	468	467	466	464	417
135°	604	608	608	606	604	467
145°	733	736	737	736	734	459
155°	840	840	839	842	839	386
165°	914	912	911	915	912	258
175°	951	948	947	952	947	90
180°	953	953	953	953	953	



TEST NUMBER: P332515-830

CATALOG NUMBER: SA4XXDIP-C350D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	9.7	10.0	10.3	10.6	10.8	11.1	11.2	11.4	11.6	11.8	12.0
90°	2.2	4.1	5.8	7.6	9.4	10.9	12.3	13.6	14.9	16.2	17.2
92.5°	15.7	17.8	19.9	22.0	24.0	25.5	26.4	27.3	28.3	29.2	29.8
95°	44.2	45.7	47.1	48.6	50.1	51.5	52.6	53.7	54.9	56.0	56.5
97.5°	77.2	78.4	79.6	80.8	81.9	83.2	84.5	85.9	87.2	88.6	89.2
100°	103.2	103.8	104.4	105.1	105.8	106.9	108.3	109.8	111.2	112.7	113.1
102.5°	130.3	130.5	130.8	131.1	131.3	132.1	133.5	134.8	136.2	137.5	138.0
105°	171.7	171.8	172.0	172.2	172.4	172.8	173.4	174.1	174.7	175.4	175.9
107.5°	215.2	215.4	215.6	215.7	215.9	216.1	216.2	216.3	216.4	216.5	217.0
110°	244.7	245.0	245.2	245.6	245.9	246.0	245.9	245.7	245.5	245.3	245.1



TEST NUMBER: P332515-830

CATALOG NUMBER: SA4XXDIP-C350D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.3	275.3	275.4	275.5	275.6	275.4	275.1	274.8	274.6	274.3	274.2
115°	321.3	321.3	321.3	321.3	321.3	321.1	320.7	320.5	320.1	319.8	319.6
117.5°	364.6	364.8	364.9	365.0	365.1	365.0	364.9	364.6	364.4	364.2	363.6
120°	393.5	394.2	394.8	395.5	396.2	396.2	395.7	395.2	394.7	394.3	393.4
122.5°	423.6	423.8	424.0	424.3	424.6	424.6	424.4	424.1	424.0	423.7	423.1
125°	467.9	467.9	467.9	467.9	467.9	467.8	467.7	467.5	467.3	467.2	466.8
127.5°	508.1	508.6	509.2	509.6	510.1	510.2	509.9	509.7	509.4	509.2	508.9
130°	536.4	537.0	537.4	537.9	538.4	538.7	538.7	538.7	538.7	538.7	538.3
132.5°	565.3	565.7	566.1	566.4	566.8	566.8	566.8	566.7	566.5	566.4	566.0
135°	603.5	604.5	605.5	606.4	607.5	607.9	607.9	607.9	607.9	607.9	607.6
137.5°	645.1	645.5	645.9	646.4	646.9	647.2	647.5	647.8	648.0	648.3	647.9
140°	672.8	673.1	673.4	673.7	674.1	674.2	674.2	674.2	674.2	674.2	674.1
142.5°	698.1	698.4	698.8	699.1	699.5	699.6	699.4	699.3	699.1	699.0	699.0
145°	733.2	733.9	734.5	735.2	735.8	736.2	736.4	736.5	736.7	736.9	736.7
147.5°	768.0	768.7	769.5	770.3	771.1	771.5	771.3	771.2	771.0	770.9	770.8
150°	789.2	789.9	790.5	791.2	791.8	792.1	792.1	792.1	792.1	792.1	792.1
152.5°	809.3	809.6	810.0	810.4	810.8	811.1	811.2	811.3	811.4	811.6	812.0
155°	840.0	840.0	840.0	840.0	840.0	839.9	839.8	839.6	839.4	839.3	839.9
157.5°	866.0	865.6	865.3	865.1	864.8	864.6	864.6	864.6	864.5	864.5	865.0
160°	881.3	881.1	881.0	880.8	880.6	880.4	880.3	880.1	880.0	879.9	880.3
162.5°	895.4	895.0	894.6	894.2	893.7	893.4	893.2	893.2	893.0	892.8	893.7
165°	914.5	914.0	913.5	912.9	912.5	912.1	911.7	911.4	911.1	910.8	911.7
167.5°	929.1	928.3	927.7	927.0	926.3	926.0	926.0	926.0	926.0	926.0	927.1
170°	937.3	936.5	935.7	934.8	934.1	933.7	933.9	934.1	934.2	934.3	935.3
172.5°	943.2	942.5	941.8	941.1	940.5	940.1	940.2	940.2	940.2	940.3	941.3
175°	951.3	950.5	949.6	948.9	948.0	947.5	947.3	947.2	947.1	946.9	948.0
177.5°	953.9	953.3	952.6	952.0	951.3	951.0	951.0	951.0	951.0	951.0	951.9
180°	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7



TEST NUMBER: P332515-830

CATALOG NUMBER: SA4XXDIP-C350D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	12.2	12.4	12.6	12.7	12.8	12.8	12.9	13.0
90°	18.2	19.1	20.2	20.8	21.1	21.5	21.8	22.1
92.5°	30.3	30.9	31.6	32.0	32.1	32.3	32.5	32.7
95°	57.0	57.5	58.0	58.2	58.2	58.2	58.2	58.2
97.5°	89.7	90.3	91.0	91.2	91.2	91.2	91.2	91.2
100°	113.4	113.8	114.0	114.2	114.2	114.2	114.2	114.2
102.5°	138.5	138.8	139.3	139.6	139.8	139.9	140.1	140.2
105°	176.3	176.8	177.3	177.9	178.3	178.8	179.3	179.8
107.5°	217.4	217.8	218.3	218.6	218.5	218.5	218.5	218.4
110°	244.7	244.4	244.0	244.1	244.7	245.2	245.6	246.1



TEST NUMBER: P332515-830

CATALOG NUMBER: SA4XXDIP-C350D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	274.1	274.1	274.0	274.0	274.1	274.2	274.3	274.4
115°	319.4	319.3	319.1	319.0	318.9	318.7	318.5	318.3
117.5°	363.1	362.5	361.9	361.5	361.2	360.8	360.5	360.1
120°	392.6	391.7	391.0	390.7	391.1	391.3	391.7	392.0
122.5°	422.5	422.1	421.5	420.9	420.3	419.7	419.1	418.6
125°	466.6	466.2	465.9	465.5	465.2	464.9	464.6	464.2
127.5°	508.5	508.2	507.8	507.6	507.3	507.1	506.8	506.5
130°	538.0	537.6	537.3	536.9	536.2	535.6	534.9	534.2
132.5°	565.7	565.3	565.1	564.8	564.5	564.2	563.9	563.7
135°	607.3	606.9	606.6	606.1	605.7	605.2	604.7	604.3
137.5°	647.4	647.1	646.6	646.4	646.5	646.6	646.7	646.9
140°	673.9	673.7	673.5	673.4	673.3	673.1	672.9	672.8
142.5°	698.9	698.9	698.9	698.8	698.8	698.8	698.7	698.7
145°	736.5	736.4	736.2	735.8	735.4	734.9	734.4	734.0
147.5°	770.6	770.5	770.3	770.2	770.1	769.9	769.8	769.6
150°	792.1	792.1	792.1	792.0	791.9	791.7	791.5	791.4
152.5°	812.4	812.8	813.1	813.1	812.8	812.3	811.9	811.4
155°	840.6	841.2	841.9	841.9	841.2	840.6	839.9	839.3
157.5°	865.4	866.0	866.5	866.4	865.9	865.3	864.8	864.2
160°	880.8	881.3	881.7	881.7	880.8	880.0	879.2	878.4
162.5°	894.6	895.4	896.4	896.4	895.5	894.8	893.9	893.1
165°	912.8	913.7	914.7	914.8	914.2	913.5	912.9	912.3
167.5°	928.0	929.1	930.0	930.0	929.0	927.9	927.0	926.0
170°	936.3	937.3	938.3	938.2	937.1	935.9	934.7	933.6
172.5°	942.4	943.6	944.7	944.7	943.6	942.4	941.2	940.1
175°	949.1	950.3	951.5	951.5	950.3	949.1	948.0	946.9
177.5°	952.8	953.8	954.7	954.6	953.6	952.5	951.5	950.4
180°	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7

(END OF REPORT)