

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332899-935

Luminaire Tested: **SA4XXRDIP-C575D365U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332899-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3114.3 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332899-935
CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332899-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65				
1	101	97	93	90	95	92	88	85	81	78	76	71	69	68	62	61	60	55				
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47				
3	85	75	68	62	79	71	65	59	63	58	54	56	52	49	49	46	44	40				
4	78	67	59	53	73	63	56	51	56	51	46	50	46	42	44	41	38	35				
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33	30				
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27				
7	61	49	41	35	58	46	39	34	42	36	31	37	32	29	33	29	26	24				
8	57	45	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24	21				
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19				
10	50	38	30	25	47	36	29	25	32	27	23	29	25	21	26	22	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7064	7064	7064
5°	7080	6994	7037
10°	7035	6909	6909
15°	6955	6764	6714
20°	6844	6574	6453
25°	6702	6350	6188
30°	6564	6114	5858
35°	6412	5870	5527
40°	6227	5592	5168
45°	6058	5316	4804
50°	5865	4999	4417
55°	5658	4669	3997
60°	5430	4306	3570
65°	5223	3851	3148
70°	4919	3354	2672
75°	4535	2779	2174
80°	3956	2115	1994
85°	3353	1927	1806



TEST NUMBER: P332899-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.2	2.6
10°-20°	229.2	7.4
20°-30°	331.0	10.6
30°-40°	375.2	12.0
40°-50°	362.3	11.6
50°-60°	301.3	9.7
60°-70°	208.0	6.7
70°-80°	105.4	3.4
80°-90°	28.2	0.9
90°-100°	25.9	0.8
100°-110°	76.9	2.5
110°-120°	130.5	4.2
120°-130°	172.0	5.5
130°-140°	193.2	6.2
140°-150°	189.8	6.1
150°-160°	159.7	5.1
160°-170°	106.2	3.4
170°-180°	37.2	1.2
0°-30°	642.4	20.6
0°-40°	1017.6	32.7
0°-60°	1681.1	54.0
0°-90°	2022.8	65.0
90°-120°	233.3	7.5
90°-150°	788.3	25.3
90°-180°	1091.0	35.0
0°-180°	3114.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	875	875	875	875	875	
5°	874	871	863	869	868	83
15°	832	825	809	808	803	234
25°	752	740	713	702	695	347
35°	651	628	596	573	561	406
45°	531	505	466	434	421	409
55°	402	374	332	298	284	359
65°	273	244	202	174	165	270
75°	145	120	89	74	70	154
85°	36	23	21	20	20	41
90°	1	4	7	8	9	3
95°	18	21	23	24	24	20
105°	71	71	72	73	74	75
115°	133	133	132	132	132	131
125°	193	193	193	192	192	172
135°	249	251	251	250	250	193
145°	303	304	304	304	303	189
155°	347	347	347	348	347	160
165°	378	377	376	378	377	106
175°	393	391	391	393	391	37
180°	393	393	393	393	393	



TEST NUMBER: P332899-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	877.2	876.7	876.2	875.7	875.3	874.3	873.1	871.8	870.4	869.1	870.4
5°	873.7	873.1	872.5	871.8	871.3	870.1	868.3	866.5	864.7	863.0	864.4
7.5°	865.7	865.1	864.5	863.9	863.2	861.8	859.5	857.1	854.8	852.5	853.4
10°	858.2	857.6	856.8	856.0	855.3	853.6	850.9	848.2	845.5	842.8	843.4
12.5°	848.6	847.7	846.9	846.0	845.2	843.2	840.0	836.8	833.7	830.5	830.9
15°	832.2	830.8	829.5	828.1	826.7	824.2	820.5	816.8	813.0	809.3	809.1
17.5°	812.2	810.2	808.3	806.3	804.4	801.2	796.8	792.3	787.8	783.3	782.6
20°	796.6	794.7	792.7	790.8	788.8	785.4	780.3	775.2	770.2	765.2	764.0
22.5°	779.5	777.3	775.2	772.9	770.8	767.0	761.6	756.1	750.7	745.3	743.5
25°	752.4	749.8	747.0	744.3	741.7	737.3	731.2	725.0	718.9	712.9	710.3
27.5°	724.0	720.7	717.3	713.9	710.5	705.6	699.0	692.6	686.0	679.5	676.4
30°	704.1	700.4	696.7	693.0	689.3	683.9	676.9	669.9	662.9	655.9	652.2
32.5°	683.3	679.1	674.9	670.6	666.5	660.7	653.5	646.3	639.0	631.8	627.5
35°	650.6	645.8	641.0	636.3	631.5	625.4	617.9	610.5	603.0	595.6	590.6
37.5°	615.6	610.7	605.8	600.9	595.9	589.4	581.1	572.8	564.6	556.4	550.7
40°	590.9	586.0	581.1	576.2	571.3	564.6	556.1	547.6	539.2	530.6	524.3
42.5°	567.3	562.2	557.1	551.9	546.7	539.8	530.9	522.0	513.2	504.4	498.0
45°	530.6	525.1	519.6	514.1	508.6	501.4	492.4	483.5	474.6	465.6	458.3
47.5°	492.8	487.1	481.3	475.6	469.9	462.4	453.1	443.9	434.6	425.3	417.8
50°	467.0	461.2	455.4	449.5	443.8	436.1	426.5	417.1	407.5	398.0	390.5
52.5°	440.7	435.1	429.4	423.7	417.9	410.3	400.5	390.7	380.9	371.2	363.6
55°	402.0	396.1	390.1	384.1	378.2	370.3	360.7	351.0	341.3	331.7	323.9
57.5°	363.7	357.5	351.3	345.1	338.9	331.1	321.5	311.9	302.5	292.9	285.1
60°	336.3	330.4	324.4	318.5	312.5	304.8	295.2	285.7	276.2	266.7	258.9
62.5°	311.7	305.5	299.3	293.1	286.9	279.0	269.1	259.4	249.6	239.9	232.7
65°	273.4	267.0	260.5	254.2	247.7	239.8	230.2	220.8	211.2	201.6	195.3
67.5°	233.6	227.4	221.3	215.2	209.1	201.6	192.7	183.8	175.0	166.2	160.7
70°	208.4	202.1	195.9	189.6	183.4	176.0	167.5	159.0	150.5	142.1	137.2
72.5°	181.6	175.9	170.2	164.6	158.9	152.1	144.1	136.1	128.0	120.0	115.9
75°	145.4	139.9	134.4	128.9	123.4	117.1	110.1	103.1	96.1	89.1	85.7
77.5°	108.7	104.0	99.4	94.6	90.0	84.8	79.1	73.5	67.8	62.2	60.2
80°	85.1	80.8	76.5	72.2	67.8	63.5	59.0	54.5	50.0	45.5	45.1
82.5°	64.7	60.8	56.8	52.9	48.9	45.6	43.0	40.5	38.0	35.4	35.0
85°	36.2	33.2	30.2	27.2	24.3	22.6	22.1	21.7	21.2	20.8	20.5
87.5°	12.5	11.7	10.9	10.1	9.3	8.9	8.9	8.9	8.9	8.9	8.8
90°	0.9	1.6	2.4	3.2	3.9	4.6	5.1	5.6	6.1	6.7	7.1
92.5°	6.5	7.4	8.2	9.0	9.9	10.5	10.9	11.3	11.7	12.1	12.3
95°	18.3	18.9	19.5	20.1	20.7	21.3	21.7	22.2	22.6	23.2	23.3
97.5°	31.9	32.4	32.9	33.3	33.8	34.4	34.9	35.5	36.0	36.6	36.9
100°	42.6	42.9	43.1	43.4	43.7	44.1	44.7	45.4	46.0	46.6	46.7
102.5°	53.8	53.9	54.0	54.2	54.2	54.6	55.1	55.7	56.2	56.7	57.0
105°	70.9	70.9	71.0	71.1	71.1	71.3	71.6	71.9	72.2	72.4	72.6
107.5°	88.9	88.9	89.0	89.1	89.2	89.2	89.3	89.3	89.4	89.4	89.5
110°	101.0	101.2	101.3	101.4	101.5	101.6	101.5	101.4	101.3	101.3	101.2



TEST NUMBER: P332899-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	113.7	113.7	113.7	113.7	113.7	113.7	113.6	113.5	113.4	113.2	113.2
115°	132.7	132.7	132.7	132.7	132.7	132.6	132.4	132.3	132.2	132.1	132.0
117.5°	150.5	150.6	150.7	150.7	150.8	150.8	150.7	150.6	150.4	150.3	150.2
120°	162.5	162.7	163.0	163.2	163.6	163.6	163.4	163.2	163.0	162.8	162.5
122.5°	174.9	175.0	175.1	175.2	175.3	175.3	175.2	175.1	175.0	175.0	174.7
125°	193.2	193.2	193.2	193.2	193.2	193.1	193.1	193.0	193.0	192.9	192.8
127.5°	209.8	210.0	210.3	210.4	210.6	210.7	210.6	210.4	210.3	210.3	210.1
130°	221.5	221.7	221.9	222.1	222.3	222.4	222.4	222.4	222.4	222.4	222.3
132.5°	233.4	233.6	233.7	233.8	234.0	234.0	234.0	233.9	233.9	233.8	233.7
135°	249.2	249.6	249.9	250.4	250.8	251.0	251.0	251.0	251.0	251.0	250.9
137.5°	266.3	266.6	266.7	266.9	267.1	267.3	267.3	267.4	267.6	267.7	267.5
140°	277.8	277.9	278.0	278.2	278.4	278.4	278.4	278.4	278.4	278.4	278.4
142.5°	288.3	288.3	288.5	288.6	288.8	288.9	288.8	288.7	288.7	288.6	288.6
145°	302.7	303.0	303.2	303.5	303.8	304.0	304.0	304.1	304.2	304.3	304.2
147.5°	317.1	317.5	317.7	318.1	318.4	318.5	318.5	318.4	318.4	318.3	318.2
150°	325.9	326.1	326.4	326.7	326.9	327.1	327.1	327.1	327.1	327.1	327.1
152.5°	334.2	334.3	334.4	334.6	334.8	334.8	334.9	335.0	335.0	335.1	335.3
155°	346.8	346.8	346.8	346.8	346.8	346.8	346.7	346.6	346.6	346.6	346.8
157.5°	357.6	357.4	357.3	357.2	357.1	357.0	357.0	357.0	357.0	357.0	357.1
160°	363.9	363.8	363.8	363.7	363.6	363.5	363.5	363.4	363.3	363.3	363.5
162.5°	369.7	369.5	369.4	369.2	369.0	368.9	368.9	368.8	368.7	368.6	369.0
165°	377.5	377.4	377.2	376.9	376.8	376.6	376.4	376.3	376.2	376.1	376.4
167.5°	383.6	383.3	383.1	382.7	382.5	382.3	382.4	382.4	382.4	382.4	382.8
170°	387.0	386.7	386.3	386.0	385.6	385.6	385.6	385.6	385.7	385.8	386.2
172.5°	389.4	389.2	388.8	388.6	388.3	388.1	388.1	388.2	388.2	388.2	388.7
175°	392.8	392.4	392.1	391.8	391.4	391.2	391.2	391.1	391.1	391.0	391.4
177.5°	393.9	393.6	393.3	393.0	392.8	392.7	392.7	392.7	392.7	392.7	393.0
180°	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4



TEST NUMBER: P332899-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	871.8	873.1	874.3	874.9	874.9	874.7	874.6	874.5
5°	865.9	867.5	868.9	869.5	869.2	868.9	868.6	868.3
7.5°	854.4	855.3	856.4	856.5	856.1	855.6	855.1	854.6
10°	844.0	844.6	845.2	845.2	844.6	844.0	843.4	842.8
12.5°	831.2	831.6	832.0	831.7	830.9	830.1	829.2	828.4
15°	808.7	808.5	808.1	807.5	806.4	805.4	804.3	803.3
17.5°	781.7	780.8	780.0	778.8	777.2	775.7	774.0	772.5
20°	762.8	761.6	760.3	758.8	756.9	754.9	753.0	751.1
22.5°	741.8	739.9	738.1	736.5	734.9	733.3	731.8	730.1
25°	707.8	705.2	702.7	700.8	699.2	697.8	696.3	694.7
27.5°	673.2	670.1	667.0	664.3	662.2	660.0	658.0	655.8
30°	648.5	644.7	641.0	638.0	635.6	633.2	630.9	628.4
32.5°	623.2	618.9	614.5	611.2	609.0	606.7	604.4	602.2
35°	585.5	580.4	575.4	571.5	568.9	566.1	563.4	560.8
37.5°	545.0	539.4	533.7	529.6	526.8	524.2	521.5	518.8
40°	518.1	511.9	505.6	501.2	498.4	495.8	493.1	490.4
42.5°	491.6	485.3	478.9	474.3	471.5	468.7	465.9	463.1
45°	451.1	443.8	436.4	431.4	428.8	426.1	423.4	420.8
47.5°	410.2	402.6	395.0	389.8	386.8	383.9	381.0	378.0
50°	383.1	375.7	368.2	363.1	360.2	357.4	354.6	351.7
52.5°	356.0	348.4	341.0	335.7	332.7	329.8	326.8	323.9
55°	316.2	308.4	300.7	295.4	292.6	289.7	286.9	284.0
57.5°	277.2	269.3	261.5	256.5	254.3	252.2	250.0	247.9
60°	251.2	243.4	235.7	230.7	228.3	225.8	223.5	221.1
62.5°	225.6	218.4	211.3	206.7	204.8	202.9	201.0	199.1
65°	188.9	182.4	176.1	171.9	170.2	168.4	166.6	164.8
67.5°	155.2	149.6	144.1	140.4	138.4	136.5	134.5	132.5
70°	132.2	127.3	122.3	119.2	117.7	116.2	114.7	113.2
72.5°	111.7	107.5	103.2	100.5	99.1	97.7	96.3	95.0
75°	82.2	78.9	75.4	73.3	72.3	71.5	70.6	69.7
77.5°	58.2	56.2	54.2	53.0	52.8	52.5	52.3	52.0
80°	44.7	44.3	43.7	43.5	43.3	43.1	43.0	42.9
82.5°	34.7	34.4	34.1	33.8	33.7	33.5	33.4	33.2
85°	20.1	19.9	19.5	19.5	19.5	19.5	19.5	19.5
87.5°	8.8	8.7	8.7	8.8	8.9	9.0	9.2	9.3
90°	7.5	7.9	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	12.6	12.7	13.0	13.2	13.3	13.3	13.4	13.5
95°	23.5	23.8	23.9	24.0	24.0	24.0	24.0	24.0
97.5°	37.0	37.3	37.5	37.6	37.6	37.6	37.6	37.6
100°	46.8	46.9	47.1	47.2	47.2	47.2	47.2	47.2
102.5°	57.2	57.3	57.5	57.7	57.7	57.8	57.8	57.9
105°	72.8	73.0	73.2	73.4	73.6	73.9	74.0	74.2
107.5°	89.8	90.0	90.1	90.2	90.2	90.2	90.2	90.1
110°	101.1	100.9	100.7	100.8	101.0	101.3	101.4	101.6



TEST NUMBER: P332899-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	113.2	113.1	113.1	113.1	113.2	113.2	113.2	113.3
115°	131.9	131.8	131.7	131.7	131.6	131.6	131.5	131.5
117.5°	149.9	149.6	149.5	149.3	149.1	149.0	148.9	148.7
120°	162.1	161.8	161.4	161.4	161.4	161.6	161.7	161.9
122.5°	174.5	174.3	174.0	173.7	173.6	173.3	173.1	172.8
125°	192.6	192.5	192.3	192.2	192.1	191.9	191.8	191.7
127.5°	210.0	209.8	209.7	209.6	209.5	209.4	209.2	209.1
130°	222.1	222.0	221.9	221.6	221.4	221.1	220.8	220.6
132.5°	233.6	233.4	233.3	233.2	233.1	233.0	232.9	232.7
135°	250.7	250.6	250.5	250.3	250.1	249.9	249.7	249.5
137.5°	267.3	267.2	267.0	266.9	266.9	267.0	267.0	267.1
140°	278.3	278.2	278.1	278.0	278.0	277.9	277.8	277.8
142.5°	288.6	288.6	288.5	288.5	288.5	288.5	288.5	288.5
145°	304.1	304.0	304.0	303.8	303.7	303.4	303.2	303.1
147.5°	318.2	318.1	318.1	318.1	318.0	317.9	317.8	317.8
150°	327.1	327.1	327.1	327.0	327.0	326.9	326.8	326.7
152.5°	335.4	335.6	335.8	335.7	335.5	335.4	335.2	335.0
155°	347.1	347.3	347.6	347.6	347.3	347.1	346.8	346.6
157.5°	357.3	357.6	357.7	357.7	357.5	357.3	357.1	356.8
160°	363.7	363.9	364.1	364.0	363.7	363.3	363.0	362.7
162.5°	369.4	369.7	370.1	370.1	369.8	369.5	369.1	368.8
165°	376.9	377.3	377.6	377.7	377.5	377.2	376.9	376.7
167.5°	383.2	383.6	384.0	384.0	383.6	383.1	382.7	382.3
170°	386.6	387.0	387.4	387.4	386.9	386.4	386.0	385.5
172.5°	389.2	389.6	390.0	390.0	389.6	389.1	388.7	388.1
175°	391.9	392.4	392.9	392.9	392.4	391.9	391.4	391.0
177.5°	393.4	393.8	394.2	394.2	393.7	393.3	392.9	392.4
180°	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4

(END OF REPORT)