

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332577-830

Luminaire Tested: **SA4XXDIP-C575D1205U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332577-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6882.6 lumens
Efficiency: N/A
Efficacy: 139.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332577-830
CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332577-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34				34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29				29
2	86	79	73	67	77	71	66	62	57	54	50	44	42	40	32	31	29	24				24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	34	29	27	25	20				20
4	71	61	53	47	64	55	49	44	45	40	36	35	31	29	26	23	22	17				17
5	65	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15				15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16	13				13
7	56	44	36	30	50	40	33	28	32	27	24	25	22	19	19	17	15	12				12
8	52	40	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13	11				11
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12	10				10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11	9				9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7389	7389	7389
5°	7412	7323	7376
10°	7365	7263	7299
15°	7276	7160	7178
20°	7158	7032	7039
25°	7023	6886	6866
30°	6858	6715	6652
35°	6686	6535	6447
40°	6509	6330	6215
45°	6322	6130	6012
50°	6116	5951	5766
55°	5895	5719	5533
60°	5672	5459	5293
65°	5421	5213	5001
70°	5141	4881	4692
75°	4713	4482	4370
80°	4193	4021	3924
85°	3668	3538	3464



TEST NUMBER: P332577-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	1.3
10°-20°	242.9	3.5
20°-30°	357.5	5.2
30°-40°	415.6	6.0
40°-50°	415.6	6.0
50°-60°	363.5	5.3
60°-70°	270.0	3.9
70°-80°	153.4	2.2
80°-90°	48.5	0.7
90°-100°	50.1	0.7
100°-110°	319.3	4.6
110°-120°	610.8	8.9
120°-130°	775.4	11.3
130°-140°	829.7	12.1
140°-150°	775.8	11.3
150°-160°	625.7	9.1
160°-170°	403.5	5.9
170°-180°	139.1	2.0
0°-30°	686.6	10.0
0°-40°	1102.1	16.0
0°-60°	1881.3	27.3
0°-90°	2353.1	34.2
90°-120°	980.2	14.2
90°-150°	3361.2	48.8
90°-180°	4529.0	65.8
0°-180°	6882.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	915	915	915	915	915	
5°	915	911	904	911	910	87
15°	871	867	857	861	859	245
25°	788	783	773	774	771	363
35°	678	673	663	658	654	424
45°	554	548	537	529	527	427
55°	419	416	406	398	393	375
65°	284	280	273	266	262	281
75°	151	147	144	141	140	161
85°	40	40	38	38	37	44
90°	3	15	24	30	33	5
95°	60	25	24	30	32	77
105°	330	336	342	349	312	345
115°	616	619	618	620	620	605
125°	865	869	867	871	872	772
135°	1073	1072	1077	1079	1081	827
145°	1238	1241	1241	1242	1244	773
155°	1357	1358	1355	1359	1356	625
165°	1431	1426	1426	1434	1425	404
175°	1464	1458	1459	1467	1456	139
180°	1464	1464	1464	1464	1464	



TEST NUMBER: P332577-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	917.7	917.3	916.9	916.5	916.2	915.2	913.8	912.4	910.9	909.5	910.8
5°	914.6	914.0	913.3	912.7	912.0	910.8	909.0	907.2	905.4	903.6	905.4
7.5°	906.1	905.4	904.8	904.2	903.5	902.2	900.2	898.2	896.2	894.2	895.7
10°	898.4	897.9	897.2	896.5	895.9	894.5	892.4	890.2	888.2	886.0	887.3
12.5°	888.5	887.9	887.2	886.6	885.9	884.5	882.2	880.0	877.7	875.4	876.8
15°	870.6	870.0	869.3	868.6	868.0	866.5	864.0	861.6	859.1	856.7	857.6
17.5°	849.0	848.2	847.4	846.6	845.7	844.2	841.9	839.6	837.3	835.0	835.6
20°	833.2	832.4	831.6	830.8	829.9	828.3	825.9	823.4	821.0	818.5	819.0
22.5°	816.1	815.1	814.1	812.9	811.9	810.1	807.7	805.2	802.8	800.3	801.3
25°	788.4	787.3	786.2	785.0	783.9	782.2	779.9	777.6	775.3	773.1	773.3
27.5°	756.8	755.6	754.4	753.3	752.1	750.5	748.3	746.2	744.0	742.0	741.6
30°	735.7	734.3	733.0	731.7	730.5	728.7	726.6	724.4	722.4	720.3	719.6
32.5°	713.3	712.2	711.0	709.8	708.7	706.9	704.7	702.5	700.2	698.0	697.2
35°	678.4	677.3	676.2	675.0	673.9	672.1	669.9	667.6	665.3	663.1	661.9
37.5°	641.6	640.6	639.5	638.5	637.4	635.7	633.3	630.8	628.4	625.9	624.7
40°	617.6	616.2	614.9	613.7	612.4	610.5	608.0	605.6	603.1	600.7	599.1
42.5°	591.7	591.0	590.2	589.4	588.6	586.8	584.2	581.5	578.7	576.1	574.2
45°	553.7	552.6	551.5	550.4	549.2	547.3	544.7	542.1	539.5	536.9	535.1
47.5°	514.0	513.2	512.5	511.6	510.9	509.3	506.9	504.4	502.0	499.6	497.6
50°	487.0	486.4	485.7	485.0	484.4	483.0	480.7	478.3	476.1	473.8	471.6
52.5°	460.6	459.9	459.0	458.3	457.5	455.9	453.5	451.1	448.7	446.2	444.2
55°	418.8	418.3	417.8	417.4	416.9	415.5	413.2	410.9	408.6	406.3	404.4
57.5°	378.9	378.3	377.8	377.2	376.6	375.3	373.1	370.8	368.5	366.3	364.4
60°	351.3	350.5	349.7	348.8	348.1	346.6	344.5	342.3	340.3	338.1	336.7
62.5°	324.3	323.7	322.9	322.3	321.6	320.1	317.9	315.7	313.4	311.1	309.8
65°	283.8	283.0	282.2	281.4	280.6	279.4	277.8	276.1	274.5	272.9	271.2
67.5°	243.1	242.3	241.6	240.8	240.1	238.9	237.3	235.8	234.2	232.6	231.1
70°	217.8	216.7	215.6	214.4	213.3	212.1	210.8	209.4	208.1	206.8	205.6
72.5°	190.9	189.7	188.6	187.4	186.2	185.2	184.2	183.1	182.1	181.0	179.9
75°	151.1	150.2	149.5	148.6	147.8	147.0	146.2	145.3	144.6	143.7	143.1
77.5°	113.1	112.7	112.4	112.1	111.7	111.1	110.4	109.7	109.0	108.3	108.0
80°	90.2	89.7	89.3	88.8	88.2	87.8	87.6	87.2	86.9	86.5	86.2
82.5°	68.0	67.7	67.5	67.2	67.0	66.8	66.8	66.7	66.6	66.6	66.4
85°	39.6	39.6	39.6	39.6	39.6	39.4	39.1	38.8	38.5	38.2	38.2
87.5°	15.9	16.3	16.7	17.2	17.5	17.9	18.1	18.4	18.7	18.9	19.2
90°	3.3	5.9	8.7	11.3	13.9	16.3	18.3	20.2	22.1	24.1	25.5
92.5°	13.8	13.9	14.1	14.2	14.4	15.5	17.3	19.3	21.3	23.2	24.7
95°	60.2	51.9	43.6	35.4	27.1	23.1	23.4	23.6	23.8	24.1	25.5
97.5°	127.9	133.1	138.3	143.4	148.5	137.5	110.4	83.2	56.1	28.9	29.0
100°	179.6	184.0	188.4	192.7	197.2	182.6	148.9	115.4	81.8	48.2	44.0
102.5°	237.4	240.6	243.8	247.0	250.2	249.7	245.3	240.9	236.6	232.1	187.6
105°	329.6	331.1	332.5	334.0	335.5	336.9	338.1	339.2	340.4	341.7	343.9
107.5°	415.3	416.0	416.8	417.5	418.2	419.4	421.0	422.7	424.3	426.0	427.1
110°	473.2	473.8	474.6	475.3	476.1	477.1	478.6	480.0	481.5	483.0	483.4



TEST NUMBER: P332577-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	529.2	530.6	531.8	533.1	534.4	535.5	536.1	536.8	537.5	538.2	538.1
115°	615.5	616.2	617.0	617.6	618.4	618.7	618.4	618.2	617.9	617.6	618.2
117.5°	693.2	694.2	695.2	696.2	697.1	697.9	698.4	699.0	699.6	700.0	699.9
120°	745.8	746.8	747.8	748.8	749.7	750.1	749.9	749.6	749.3	749.1	749.6
122.5°	794.8	795.5	796.1	796.6	797.2	797.7	798.1	798.3	798.7	799.1	799.4
125°	865.2	866.2	867.1	868.1	869.1	869.3	868.8	868.4	867.9	867.4	868.1
127.5°	931.8	932.0	932.3	932.6	932.7	933.4	934.5	935.7	936.8	937.9	937.7
130°	974.7	975.0	975.2	975.4	975.7	976.2	976.9	977.6	978.4	979.1	979.3
132.5°	1014.2	1014.6	1015.0	1015.5	1015.9	1016.6	1017.5	1018.4	1019.4	1020.3	1020.5
135°	1073.3	1073.1	1072.8	1072.5	1072.3	1072.7	1073.7	1074.6	1075.6	1076.6	1077.0
137.5°	1125.7	1125.8	1125.9	1126.0	1126.1	1126.6	1127.7	1128.8	1129.8	1130.9	1131.4
140°	1159.8	1160.3	1160.7	1161.3	1161.8	1162.2	1162.7	1163.2	1163.7	1164.2	1164.9
142.5°	1190.4	1191.4	1192.2	1193.1	1194.0	1194.6	1194.9	1195.1	1195.4	1195.7	1196.3
145°	1237.6	1238.3	1239.1	1239.7	1240.5	1240.9	1240.9	1240.9	1240.9	1240.9	1241.1
147.5°	1275.0	1276.4	1277.7	1279.1	1280.4	1281.0	1280.8	1280.5	1280.3	1280.1	1280.3
150°	1302.2	1303.2	1304.1	1305.1	1306.1	1306.5	1306.2	1306.0	1305.7	1305.4	1305.4
152.5°	1324.9	1325.8	1326.5	1327.3	1328.0	1328.2	1327.9	1327.4	1326.9	1326.5	1326.9
155°	1357.0	1357.2	1357.4	1357.6	1357.9	1357.6	1357.0	1356.2	1355.5	1354.7	1355.8
157.5°	1383.8	1383.7	1383.6	1383.5	1383.3	1382.8	1382.0	1381.2	1380.4	1379.5	1380.7
160°	1399.7	1398.9	1398.2	1397.5	1396.8	1396.3	1396.0	1395.7	1395.5	1395.2	1396.8
162.5°	1413.6	1412.8	1411.8	1410.9	1409.9	1409.4	1409.1	1408.9	1408.6	1408.4	1409.9
165°	1431.4	1430.2	1429.0	1427.8	1426.5	1426.0	1426.0	1426.0	1426.0	1426.0	1427.9
167.5°	1445.4	1444.2	1442.9	1441.6	1440.4	1439.6	1439.5	1439.4	1439.3	1439.1	1441.2
170°	1453.3	1451.9	1450.4	1449.0	1447.5	1446.9	1447.1	1447.4	1447.6	1447.8	1449.8
172.5°	1458.6	1457.1	1455.7	1454.2	1452.7	1452.1	1452.4	1452.6	1452.8	1453.1	1455.0
175°	1464.2	1462.8	1461.3	1459.9	1458.4	1457.8	1458.0	1458.3	1458.6	1458.8	1460.9
177.5°	1466.9	1465.6	1464.1	1462.8	1461.4	1460.9	1461.3	1461.7	1462.2	1462.5	1464.1
180°	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2



TEST NUMBER: P332577-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	912.1	913.4	914.7	915.3	915.1	915.0	914.9	914.7
5°	907.2	909.0	910.8	911.5	911.2	910.9	910.5	910.2
7.5°	897.1	898.5	899.9	900.6	900.4	900.2	900.0	899.8
10°	888.6	889.9	891.3	891.7	891.4	891.1	890.7	890.4
12.5°	878.4	879.8	881.2	881.7	881.2	880.7	880.3	879.9
15°	858.7	859.6	860.5	860.8	860.4	859.9	859.3	858.8
17.5°	836.2	836.8	837.4	837.5	837.3	836.9	836.6	836.3
20°	819.5	820.0	820.5	820.6	820.2	819.9	819.6	819.3
22.5°	802.1	803.0	803.9	804.0	803.4	802.9	802.3	801.6
25°	773.4	773.5	773.7	773.5	772.8	772.1	771.5	770.8
27.5°	741.2	740.7	740.4	739.8	739.0	738.2	737.4	736.5
30°	719.0	718.3	717.7	716.9	716.0	715.3	714.4	713.6
32.5°	696.4	695.6	694.8	694.0	693.2	692.4	691.5	690.8
35°	660.7	659.6	658.5	657.5	656.7	655.8	655.1	654.2
37.5°	623.5	622.2	620.9	619.8	618.8	617.6	616.6	615.5
40°	597.5	595.8	594.2	593.0	592.1	591.4	590.5	589.7
42.5°	572.3	570.3	568.4	567.2	566.8	566.2	565.6	565.1
45°	533.3	531.5	529.7	528.6	528.1	527.6	527.1	526.6
47.5°	495.6	493.5	491.5	489.9	488.7	487.4	486.2	484.9
50°	469.2	466.9	464.7	463.1	462.0	461.1	460.1	459.1
52.5°	442.1	440.2	438.2	436.5	435.3	434.0	432.8	431.6
55°	402.5	400.5	398.5	397.0	396.1	395.1	394.1	393.1
57.5°	362.6	360.7	358.8	357.4	356.5	355.5	354.6	353.6
60°	335.2	333.8	332.2	331.1	330.3	329.5	328.7	327.8
62.5°	308.5	307.1	305.8	304.7	303.9	303.1	302.3	301.4
65°	269.6	268.0	266.4	265.1	264.3	263.4	262.7	261.8
67.5°	229.5	228.0	226.4	225.5	225.3	225.1	224.8	224.6
70°	204.2	202.9	201.6	200.8	200.2	199.7	199.3	198.8
72.5°	178.9	177.9	176.8	176.1	175.6	175.1	174.7	174.1
75°	142.4	141.8	141.2	140.7	140.5	140.4	140.3	140.1
77.5°	107.8	107.6	107.4	107.2	106.7	106.3	105.8	105.5
80°	85.9	85.6	85.2	85.0	84.8	84.6	84.5	84.4
82.5°	66.2	66.0	65.8	65.6	65.5	65.3	65.1	64.9
85°	38.2	38.2	38.2	38.1	37.9	37.7	37.6	37.4
87.5°	19.5	19.8	20.1	20.3	20.4	20.5	20.5	20.6
90°	27.1	28.5	30.0	30.9	31.4	31.9	32.3	32.9
92.5°	26.1	27.6	29.0	29.9	30.0	30.1	30.2	30.3
95°	27.1	28.5	30.0	30.8	31.0	31.3	31.5	31.8
97.5°	29.2	29.3	29.5	29.7	30.0	30.2	30.4	30.6
100°	39.9	35.8	31.7	29.7	30.0	30.2	30.4	30.6
102.5°	142.9	98.3	53.6	31.4	31.4	31.5	31.5	31.6
105°	346.1	348.3	350.4	347.1	338.4	329.6	320.9	312.2
107.5°	428.2	429.2	430.3	431.3	432.3	433.2	434.0	435.0
110°	484.0	484.5	484.9	485.5	486.3	487.0	487.8	488.4



TEST NUMBER: P332577-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	538.0	537.9	537.8	538.2	539.1	540.1	541.0	541.9
115°	618.7	619.2	619.6	619.9	619.9	619.9	619.9	619.9
117.5°	699.8	699.7	699.6	699.6	699.5	699.4	699.3	699.2
120°	750.1	750.5	751.0	751.0	750.5	750.1	749.6	749.1
122.5°	799.7	799.9	800.2	800.1	799.7	799.2	798.6	798.1
125°	868.8	869.6	870.3	870.8	871.0	871.3	871.6	871.8
127.5°	937.6	937.5	937.4	937.2	937.0	936.8	936.6	936.4
130°	979.6	979.9	980.1	980.1	980.1	980.1	980.1	980.1
132.5°	1020.8	1021.1	1021.2	1021.2	1021.1	1020.9	1020.7	1020.5
135°	1077.5	1078.0	1078.6	1079.0	1079.5	1080.0	1080.4	1080.9
137.5°	1132.0	1132.5	1133.0	1133.2	1133.1	1132.9	1132.7	1132.7
140°	1165.6	1166.4	1167.2	1167.6	1167.8	1168.1	1168.3	1168.6
142.5°	1196.8	1197.3	1197.9	1198.2	1198.3	1198.3	1198.3	1198.3
145°	1241.3	1241.6	1241.8	1242.2	1242.6	1243.1	1243.7	1244.2
147.5°	1280.4	1280.6	1280.8	1281.0	1281.3	1281.6	1281.8	1282.0
150°	1305.4	1305.4	1305.4	1305.6	1305.8	1306.1	1306.4	1306.6
152.5°	1327.3	1327.7	1328.0	1328.1	1328.0	1327.9	1327.8	1327.6
155°	1356.7	1357.6	1358.7	1358.8	1358.0	1357.3	1356.6	1355.8
157.5°	1382.1	1383.3	1384.6	1384.6	1383.3	1382.1	1380.7	1379.5
160°	1398.2	1399.7	1401.1	1401.1	1399.7	1398.2	1396.8	1395.2
162.5°	1411.4	1412.8	1414.3	1414.2	1412.5	1410.9	1409.2	1407.5
165°	1429.8	1431.8	1433.7	1433.6	1431.4	1429.2	1427.0	1424.8
167.5°	1443.4	1445.5	1447.7	1447.5	1445.1	1442.7	1440.2	1437.8
170°	1451.7	1453.7	1455.7	1455.4	1452.9	1450.5	1448.1	1445.7
172.5°	1457.0	1459.0	1460.8	1460.6	1457.9	1455.3	1452.6	1450.0
175°	1463.2	1465.4	1467.5	1467.2	1464.2	1461.3	1458.4	1455.5
177.5°	1465.7	1467.2	1468.8	1468.4	1466.0	1463.7	1461.3	1459.1
180°	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2	1464.2

(END OF REPORT)