

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332905-935

Luminaire Tested: **SA4XXRDIP-C575D590U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332905-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D590U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3785.2 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332905-935
CATALOG NUMBER: SA4XXRDIP-C575D590U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332905-935

CATALOG NUMBER: SA4XXRDIP-C575D590U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				
1	99	95	91	87	91	88	85	82	75	73	71	64	62	60	53	52	51	46				
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39				
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33				
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	37	35	32	29				
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25				
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25	22				
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20				
8	55	43	35	30	51	40	33	28	35	30	26	30	26	23	26	23	20	18				
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16				
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7064	7064	7064
5°	7080	6994	7037
10°	7035	6909	6909
15°	6955	6764	6714
20°	6844	6574	6453
25°	6702	6350	6188
30°	6564	6114	5858
35°	6412	5870	5527
40°	6227	5592	5168
45°	6058	5316	4804
50°	5865	4999	4417
55°	5658	4669	3997
60°	5430	4306	3570
65°	5223	3851	3148
70°	4919	3354	2672
75°	4535	2779	2174
80°	3956	2115	1994
85°	3353	1927	1806



TEST NUMBER: P332905-935

CATALOG NUMBER: SA4XXRDIP-C575D590U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.2	2.2
10°-20°	229.2	6.1
20°-30°	331.0	8.7
30°-40°	375.2	9.9
40°-50°	362.3	9.6
50°-60°	301.3	8.0
60°-70°	208.0	5.5
70°-80°	105.4	2.8
80°-90°	29.0	0.8
90°-100°	41.9	1.1
100°-110°	124.1	3.3
110°-120°	210.6	5.6
120°-130°	277.7	7.3
130°-140°	311.8	8.2
140°-150°	306.4	8.1
150°-160°	257.7	6.8
160°-170°	171.5	4.5
170°-180°	60.0	1.6
0°-30°	642.4	17.0
0°-40°	1017.6	26.9
0°-60°	1681.1	44.4
0°-90°	2023.5	53.5
90°-120°	376.5	9.9
90°-150°	1272.4	33.6
90°-180°	1762.0	46.5
0°-180°	3785.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	875	875	875	875	875	
5°	874	871	863	869	868	83
15°	832	825	809	808	803	234
25°	752	740	713	702	695	347
35°	651	628	596	573	561	406
45°	531	505	466	434	421	409
55°	402	374	332	298	284	359
65°	273	244	202	174	165	270
75°	145	120	89	74	70	154
85°	36	23	21	20	20	41
90°	2	7	11	14	15	4
95°	29	34	37	39	39	33
105°	114	115	117	118	120	121
115°	214	214	213	213	212	211
125°	312	312	311	310	309	278
135°	402	405	405	404	403	311
145°	489	490	491	490	489	306
155°	560	560	559	561	559	257
165°	609	608	607	610	608	172
175°	634	632	631	634	631	60
180°	635	635	635	635	635	



TEST NUMBER: P332905-935

CATALOG NUMBER: SA4XXRDIP-C575D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	877.2	876.7	876.2	875.7	875.3	874.3	873.1	871.8	870.4	869.1	870.4
5°	873.7	873.1	872.5	871.8	871.3	870.1	868.3	866.5	864.7	863.0	864.4
7.5°	865.7	865.1	864.5	863.9	863.2	861.8	859.5	857.1	854.8	852.5	853.4
10°	858.2	857.6	856.8	856.0	855.3	853.6	850.9	848.2	845.5	842.8	843.4
12.5°	848.6	847.7	846.9	846.0	845.2	843.2	840.0	836.8	833.7	830.5	830.9
15°	832.2	830.8	829.5	828.1	826.7	824.2	820.5	816.8	813.0	809.3	809.1
17.5°	812.2	810.2	808.3	806.3	804.4	801.2	796.8	792.3	787.8	783.3	782.6
20°	796.6	794.7	792.7	790.8	788.8	785.4	780.3	775.2	770.2	765.2	764.0
22.5°	779.5	777.3	775.2	772.9	770.8	767.0	761.6	756.1	750.7	745.3	743.5
25°	752.4	749.8	747.0	744.3	741.7	737.3	731.2	725.0	718.9	712.9	710.3
27.5°	724.0	720.7	717.3	713.9	710.5	705.6	699.0	692.6	686.0	679.5	676.4
30°	704.1	700.4	696.7	693.0	689.3	683.9	676.9	669.9	662.9	655.9	652.2
32.5°	683.3	679.1	674.9	670.6	666.5	660.7	653.5	646.3	639.0	631.8	627.5
35°	650.6	645.8	641.0	636.3	631.5	625.4	617.9	610.5	603.0	595.6	590.6
37.5°	615.6	610.7	605.8	600.9	595.9	589.4	581.1	572.8	564.6	556.4	550.7
40°	590.9	586.0	581.1	576.2	571.3	564.6	556.1	547.6	539.2	530.6	524.3
42.5°	567.3	562.2	557.1	551.9	546.7	539.8	530.9	522.0	513.2	504.4	498.0
45°	530.6	525.1	519.6	514.1	508.6	501.4	492.4	483.5	474.6	465.6	458.3
47.5°	492.8	487.1	481.3	475.6	469.9	462.4	453.1	443.9	434.6	425.3	417.8
50°	467.0	461.2	455.4	449.5	443.8	436.1	426.5	417.1	407.5	398.0	390.5
52.5°	440.7	435.1	429.4	423.7	417.9	410.3	400.5	390.7	380.9	371.2	363.6
55°	402.0	396.1	390.1	384.1	378.2	370.3	360.7	351.0	341.3	331.7	323.9
57.5°	363.7	357.5	351.3	345.1	338.9	331.1	321.5	311.9	302.5	292.9	285.1
60°	336.3	330.4	324.4	318.5	312.5	304.8	295.2	285.7	276.2	266.7	258.9
62.5°	311.7	305.5	299.3	293.1	286.9	279.0	269.1	259.4	249.6	239.9	232.7
65°	273.4	267.0	260.5	254.2	247.7	239.8	230.2	220.8	211.2	201.6	195.3
67.5°	233.6	227.4	221.3	215.2	209.1	201.6	192.7	183.8	175.0	166.2	160.7
70°	208.4	202.1	195.9	189.6	183.4	176.0	167.5	159.0	150.5	142.1	137.2
72.5°	181.6	175.9	170.2	164.6	158.9	152.1	144.1	136.1	128.0	120.0	115.9
75°	145.4	139.9	134.4	128.9	123.4	117.1	110.1	103.1	96.1	89.1	85.7
77.5°	108.7	104.0	99.4	94.6	90.0	84.8	79.1	73.5	67.8	62.2	60.2
80°	85.1	80.8	76.5	72.2	67.8	63.5	59.0	54.5	50.0	45.5	45.1
82.5°	64.7	60.8	56.8	52.9	48.9	45.6	43.0	40.5	38.0	35.4	35.0
85°	36.2	33.2	30.2	27.2	24.3	22.6	22.1	21.7	21.2	20.8	20.5
87.5°	12.7	11.9	11.2	10.5	9.7	9.5	9.5	9.6	9.6	9.6	9.6
90°	1.5	2.7	3.9	5.1	6.3	7.3	8.2	9.0	9.9	10.8	11.5
92.5°	10.5	11.9	13.3	14.6	16.0	17.0	17.7	18.3	18.9	19.5	19.8
95°	29.4	30.5	31.4	32.4	33.4	34.3	35.0	35.8	36.6	37.3	37.6
97.5°	51.5	52.3	53.0	53.8	54.6	55.4	56.3	57.3	58.1	59.1	59.4
100°	68.7	69.2	69.7	70.1	70.5	71.2	72.2	73.2	74.1	75.2	75.3
102.5°	86.8	87.0	87.1	87.3	87.5	88.1	88.9	89.8	90.7	91.6	92.0
105°	114.4	114.5	114.6	114.8	114.9	115.1	115.5	116.0	116.4	116.8	117.2
107.5°	143.4	143.5	143.6	143.8	144.0	144.0	144.0	144.1	144.2	144.3	144.6
110°	163.1	163.2	163.5	163.7	163.9	163.9	163.8	163.8	163.7	163.5	163.3



TEST NUMBER: P332905-935

CATALOG NUMBER: SA4XXRDIP-C575D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	183.5	183.5	183.6	183.6	183.7	183.6	183.4	183.1	183.0	182.8	182.7
115°	214.1	214.1	214.1	214.1	214.1	214.0	213.8	213.5	213.4	213.1	213.0
117.5°	243.0	243.1	243.1	243.2	243.3	243.3	243.1	243.0	242.8	242.7	242.3
120°	262.3	262.7	263.1	263.6	264.0	264.1	263.7	263.4	263.0	262.7	262.2
122.5°	282.2	282.4	282.6	282.8	282.9	283.0	282.8	282.7	282.5	282.4	282.0
125°	311.9	311.9	311.9	311.9	311.9	311.8	311.7	311.6	311.4	311.3	311.1
127.5°	338.6	339.0	339.3	339.7	339.9	340.0	339.8	339.7	339.5	339.3	339.1
130°	357.5	357.8	358.2	358.5	358.8	359.0	359.0	359.0	359.0	359.0	358.8
132.5°	376.8	377.0	377.2	377.5	377.7	377.8	377.7	377.6	377.5	377.5	377.2
135°	402.2	402.9	403.5	404.2	404.8	405.1	405.1	405.1	405.1	405.1	404.9
137.5°	429.9	430.2	430.5	430.8	431.1	431.4	431.5	431.7	431.9	432.0	431.8
140°	448.3	448.6	448.8	449.0	449.2	449.4	449.4	449.4	449.4	449.4	449.2
142.5°	465.2	465.5	465.7	465.9	466.1	466.1	466.1	466.0	465.9	465.8	465.8
145°	488.6	489.0	489.5	489.9	490.3	490.6	490.8	490.9	490.9	491.0	490.9
147.5°	511.8	512.3	512.8	513.3	513.9	514.1	514.0	513.9	513.8	513.8	513.7
150°	525.9	526.4	526.8	527.3	527.7	527.9	527.9	527.9	527.9	527.9	527.9
152.5°	539.3	539.6	539.8	540.1	540.4	540.5	540.6	540.7	540.8	540.9	541.1
155°	559.8	559.8	559.8	559.8	559.8	559.7	559.6	559.6	559.5	559.3	559.7
157.5°	577.1	576.9	576.7	576.5	576.4	576.2	576.2	576.2	576.2	576.1	576.4
160°	587.3	587.2	587.1	587.0	586.9	586.8	586.7	586.6	586.4	586.3	586.7
162.5°	596.8	596.5	596.2	595.9	595.6	595.4	595.3	595.2	595.1	595.0	595.6
165°	609.4	609.1	608.7	608.5	608.1	607.9	607.6	607.4	607.2	607.0	607.6
167.5°	619.1	618.7	618.2	617.8	617.3	617.1	617.1	617.2	617.2	617.2	617.9
170°	624.7	624.1	623.5	623.0	622.4	622.2	622.3	622.4	622.6	622.7	623.4
172.5°	628.5	628.1	627.7	627.2	626.7	626.5	626.5	626.5	626.5	626.6	627.3
175°	634.0	633.4	632.9	632.3	631.8	631.5	631.4	631.3	631.1	631.0	631.8
177.5°	635.8	635.3	634.9	634.5	634.0	633.8	633.8	633.8	633.8	633.8	634.4
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0



TEST NUMBER: P332905-935

CATALOG NUMBER: SA4XXRDIP-C575D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	871.8	873.1	874.3	874.9	874.9	874.7	874.6	874.5
5°	865.9	867.5	868.9	869.5	869.2	868.9	868.6	868.3
7.5°	854.4	855.3	856.4	856.5	856.1	855.6	855.1	854.6
10°	844.0	844.6	845.2	845.2	844.6	844.0	843.4	842.8
12.5°	831.2	831.6	832.0	831.7	830.9	830.1	829.2	828.4
15°	808.7	808.5	808.1	807.5	806.4	805.4	804.3	803.3
17.5°	781.7	780.8	780.0	778.8	777.2	775.7	774.0	772.5
20°	762.8	761.6	760.3	758.8	756.9	754.9	753.0	751.1
22.5°	741.8	739.9	738.1	736.5	734.9	733.3	731.8	730.1
25°	707.8	705.2	702.7	700.8	699.2	697.8	696.3	694.7
27.5°	673.2	670.1	667.0	664.3	662.2	660.0	658.0	655.8
30°	648.5	644.7	641.0	638.0	635.6	633.2	630.9	628.4
32.5°	623.2	618.9	614.5	611.2	609.0	606.7	604.4	602.2
35°	585.5	580.4	575.4	571.5	568.9	566.1	563.4	560.8
37.5°	545.0	539.4	533.7	529.6	526.8	524.2	521.5	518.8
40°	518.1	511.9	505.6	501.2	498.4	495.8	493.1	490.4
42.5°	491.6	485.3	478.9	474.3	471.5	468.7	465.9	463.1
45°	451.1	443.8	436.4	431.4	428.8	426.1	423.4	420.8
47.5°	410.2	402.6	395.0	389.8	386.8	383.9	381.0	378.0
50°	383.1	375.7	368.2	363.1	360.2	357.4	354.6	351.7
52.5°	356.0	348.4	341.0	335.7	332.7	329.8	326.8	323.9
55°	316.2	308.4	300.7	295.4	292.6	289.7	286.9	284.0
57.5°	277.2	269.3	261.5	256.5	254.3	252.2	250.0	247.9
60°	251.2	243.4	235.7	230.7	228.3	225.8	223.5	221.1
62.5°	225.6	218.4	211.3	206.7	204.8	202.9	201.0	199.1
65°	188.9	182.4	176.1	171.9	170.2	168.4	166.6	164.8
67.5°	155.2	149.6	144.1	140.4	138.4	136.5	134.5	132.5
70°	132.2	127.3	122.3	119.2	117.7	116.2	114.7	113.2
72.5°	111.7	107.5	103.2	100.5	99.1	97.7	96.3	95.0
75°	82.2	78.9	75.4	73.3	72.3	71.5	70.6	69.7
77.5°	58.2	56.2	54.2	53.0	52.8	52.5	52.3	52.0
80°	44.7	44.3	43.7	43.5	43.3	43.1	43.0	42.9
82.5°	34.7	34.4	34.1	33.8	33.7	33.5	33.4	33.2
85°	20.1	19.9	19.5	19.5	19.5	19.5	19.5	19.5
87.5°	9.7	9.7	9.7	9.8	10.0	10.2	10.2	10.4
90°	12.1	12.7	13.4	13.9	14.1	14.3	14.6	14.7
92.5°	20.2	20.7	21.0	21.3	21.4	21.5	21.7	21.8
95°	38.0	38.3	38.7	38.8	38.8	38.8	38.8	38.8
97.5°	59.8	60.2	60.6	60.8	60.8	60.8	60.8	60.8
100°	75.6	75.8	76.0	76.1	76.1	76.1	76.1	76.1
102.5°	92.2	92.6	92.8	93.1	93.2	93.2	93.3	93.4
105°	117.5	117.9	118.2	118.5	118.8	119.2	119.5	119.9
107.5°	144.9	145.2	145.5	145.7	145.6	145.6	145.6	145.6
110°	163.1	162.9	162.6	162.7	163.1	163.3	163.7	164.0



TEST NUMBER: P332905-935

CATALOG NUMBER: SA4XXRDIP-C575D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	182.7	182.6	182.6	182.6	182.7	182.7	182.8	182.9
115°	212.9	212.8	212.7	212.6	212.5	212.3	212.2	212.2
117.5°	241.9	241.6	241.2	240.9	240.6	240.5	240.2	240.0
120°	261.7	261.1	260.5	260.4	260.6	260.8	261.1	261.2
122.5°	281.6	281.3	280.9	280.5	280.1	279.7	279.3	279.0
125°	310.9	310.6	310.5	310.2	310.0	309.8	309.6	309.4
127.5°	338.9	338.7	338.5	338.3	338.1	337.9	337.8	337.6
130°	358.5	358.3	358.1	357.7	357.3	356.9	356.5	356.0
132.5°	377.0	376.8	376.6	376.3	376.2	376.0	375.8	375.7
135°	404.7	404.5	404.2	404.0	403.6	403.3	403.0	402.7
137.5°	431.4	431.2	430.9	430.8	430.8	430.9	431.0	431.1
140°	449.1	449.0	448.9	448.8	448.7	448.6	448.5	448.3
142.5°	465.8	465.8	465.7	465.7	465.7	465.7	465.6	465.6
145°	490.9	490.8	490.6	490.4	490.1	489.7	489.4	489.1
147.5°	513.6	513.5	513.4	513.3	513.2	513.1	513.0	512.9
150°	527.9	527.9	527.9	527.9	527.7	527.6	527.5	527.4
152.5°	541.4	541.7	541.9	541.9	541.7	541.3	541.1	540.8
155°	560.2	560.6	561.1	561.1	560.6	560.2	559.7	559.3
157.5°	576.8	577.1	577.5	577.4	577.0	576.7	576.3	575.9
160°	587.0	587.3	587.6	587.5	587.0	586.4	585.9	585.4
162.5°	596.2	596.8	597.4	597.4	596.8	596.2	595.7	595.2
165°	608.3	608.9	609.6	609.7	609.2	608.8	608.4	608.0
167.5°	618.5	619.1	619.8	619.7	619.1	618.5	617.8	617.1
170°	624.0	624.7	625.3	625.3	624.5	623.7	622.9	622.2
172.5°	628.1	628.9	629.6	629.6	628.8	628.0	627.2	626.5
175°	632.6	633.4	634.0	634.0	633.4	632.6	631.8	631.0
177.5°	635.0	635.6	636.2	636.2	635.5	634.8	634.0	633.4
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0

(END OF REPORT)