

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332954-935

Luminaire Tested: **SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332954-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6469.9 lumens  
Efficiency: N/A  
Efficacy: 113.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332954-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332954-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43				43
1	96	92	88	85	88	84	81	78	70	68	66	56	55	54	44	43	42	36				36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31				31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26				26
4	74	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23				23
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	25	23	20				20
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18				18
7	58	46	38	32	53	42	35	30	35	30	26	29	25	22	23	21	18	16				16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14				14
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13				13
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	16	14	12				12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P332954-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.4	1.7
10°-20°	313.3	4.8
20°-30°	452.4	7.0
30°-40°	512.8	7.9
40°-50°	495.2	7.7
50°-60°	411.8	6.4
60°-70°	284.4	4.4
70°-80°	144.1	2.2
80°-90°	39.8	0.6
90°-100°	367.8	5.7
100°-110°	765.5	11.8
110°-120°	685.7	10.6
120°-130°	576.8	8.9
130°-140°	480.9	7.4
140°-150°	367.4	5.7
150°-160°	258.2	4.0
160°-170°	151.9	2.3
170°-180°	49.4	0.8
0°-30°	878.1	13.6
0°-40°	1390.9	21.5
0°-60°	2297.9	35.5
0°-90°	2766.2	42.8
90°-120°	1819.0	28.1
90°-150°	3244.1	50.1
90°-180°	3704.0	57.2
0°-180°	6469.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	1	8	18	20	21	4
95°	33	104	815	404	244	37
105°	117	170	656	1413	1408	125
115°	206	259	585	1125	1352	204
125°	287	341	582	957	1078	256
135°	341	406	577	849	964	264
145°	393	450	574	716	787	247
155°	447	483	558	632	659	206
165°	487	502	535	567	575	138
175°	508	509	513	520	518	48
180°	509	509	509	509	509	



TEST NUMBER: P332954-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.0	16.2	15.4	14.4	13.3	12.5	13.5	13.3	13.6	13.9	13.5
90°	1.0	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0
92.5°	11.4	16.6	26.0	38.2	52.9	73.6	124.5	202.1	277.8	317.4	264.3
95°	33.0	36.0	46.1	59.1	83.0	125.1	212.1	376.2	615.3	815.4	838.4
97.5°	59.2	59.2	67.8	79.8	100.5	135.7	202.7	338.2	575.8	858.8	1053.3
100°	76.0	76.0	83.0	95.1	114.1	146.1	205.1	318.1	522.3	804.3	1060.5
102.5°	92.0	93.7	99.9	111.1	129.2	159.7	213.1	312.5	486.2	736.3	1000.5
105°	117.1	120.0	125.1	137.1	155.1	184.1	232.1	315.1	455.2	656.3	891.4
107.5°	144.6	146.6	151.7	164.5	181.7	210.3	254.3	329.9	449.6	611.5	803.4
110°	163.1	165.1	170.0	182.1	200.1	227.1	271.1	341.1	451.3	596.3	759.4



TEST NUMBER: P332954-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	180.7	182.7	188.5	199.7	217.7	244.7	287.1	353.2	456.0	589.1	734.5
115°	206.1	209.1	216.1	226.1	245.1	272.2	312.1	372.2	465.2	585.3	711.4
117.5°	232.5	235.3	241.5	252.5	270.4	298.3	336.4	391.6	475.0	584.3	700.9
120°	250.1	252.1	259.2	270.1	287.1	315.1	353.2	405.2	482.2	584.3	695.3
122.5°	266.1	268.1	275.2	285.3	303.9	331.1	369.2	418.0	489.5	583.5	689.0
125°	287.1	291.1	297.1	308.2	327.2	355.2	391.2	437.2	500.2	582.3	678.3
127.5°	305.7	308.9	316.2	328.7	348.5	376.8	411.6	453.8	508.9	580.1	664.1
130°	316.2	320.1	328.1	343.2	362.1	391.2	425.2	464.3	515.2	579.3	655.3
132.5°	326.6	329.8	340.2	354.4	375.0	402.4	436.4	474.7	520.8	578.5	647.3
135°	341.1	345.2	355.2	372.2	393.2	419.2	452.2	488.3	529.3	577.3	635.3
137.5°	355.8	359.6	370.6	386.8	408.6	433.4	464.3	497.8	534.3	577.0	624.9
140°	366.2	369.2	380.2	397.2	418.2	442.2	472.3	504.2	538.3	576.3	619.3
142.5°	377.4	380.4	390.5	406.8	427.0	450.2	479.4	509.0	541.5	576.3	614.5
145°	393.2	396.2	406.2	420.2	439.2	461.2	487.2	514.3	543.3	574.3	606.3
147.5°	411.0	412.0	420.8	435.2	451.0	470.8	495.2	518.8	544.2	570.7	598.9
150°	422.2	423.2	431.2	443.2	458.2	477.3	499.2	521.2	544.2	568.3	593.3
152.5°	432.6	432.8	440.8	452.0	465.5	482.8	502.5	522.9	542.7	564.3	586.9
155°	447.2	448.2	454.2	464.3	475.3	490.3	507.2	524.3	540.3	558.3	577.3
157.5°	461.4	461.4	467.0	474.8	484.4	496.3	510.7	524.3	537.7	552.1	567.5
160°	470.2	470.2	474.2	481.2	489.2	500.2	512.2	524.3	535.3	547.3	560.3
162.5°	478.2	477.4	480.6	486.8	494.0	502.7	513.8	524.3	532.9	542.4	553.9
165°	487.2	487.2	489.2	494.2	499.2	505.2	514.3	522.3	528.2	535.3	543.3
167.5°	496.3	495.2	496.3	500.1	502.8	507.5	514.0	519.9	523.5	528.1	533.6
170°	500.2	499.2	500.2	503.3	505.2	508.2	513.2	518.2	520.2	523.2	527.3
172.5°	504.2	503.3	503.4	505.7	506.9	509.0	512.5	516.7	517.0	518.4	521.7
175°	508.2	507.2	507.2	508.2	509.3	509.3	511.3	514.3	513.2	513.2	515.2
177.5°	510.1	509.3	508.4	509.3	509.3	509.3	510.1	511.6	510.1	510.1	510.8
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332954-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	13.5	13.6	13.6	13.6	13.9	14.3	14.3	14.5
90°	18.0	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	196.5	147.8	117.7	97.6	85.8	80.4	77.1	77.1
95°	741.3	586.3	452.2	355.2	306.2	275.2	257.1	244.1
97.5°	1095.4	1037.7	939.9	835.4	763.5	703.4	673.3	652.6
100°	1206.6	1226.6	1177.6	1103.5	1016.5	955.5	925.5	917.5
102.5°	1201.0	1300.2	1314.4	1283.6	1230.2	1185.9	1154.3	1148.0
105°	1120.5	1293.7	1392.7	1433.7	1435.7	1427.7	1413.7	1407.6
107.5°	1006.3	1190.6	1330.1	1419.3	1468.7	1491.5	1501.5	1504.2
110°	937.5	1110.5	1255.6	1365.6	1436.7	1478.7	1496.8	1505.7





TEST NUMBER: P332954-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	887.0	1040.1	1177.2	1287.2	1367.9	1418.7	1443.9	1458.5
115°	836.4	959.5	1076.5	1172.6	1251.6	1311.6	1343.7	1351.7
117.5°	811.6	913.4	1005.5	1086.9	1154.3	1204.8	1237.2	1243.4
120°	800.4	893.5	973.4	1044.5	1101.6	1145.6	1171.6	1182.6
122.5°	790.7	880.6	953.5	1015.7	1063.9	1101.6	1123.5	1134.5
125°	774.4	860.4	929.4	984.5	1024.5	1053.5	1072.5	1078.5
127.5°	754.3	836.6	905.4	957.7	997.9	1023.7	1039.7	1045.7
130°	738.4	817.4	885.5	938.5	979.5	1004.4	1020.5	1026.5
132.5°	721.5	795.8	862.2	915.2	955.5	983.7	998.8	1004.9
135°	698.4	763.4	824.4	874.4	914.5	942.5	958.5	964.5
137.5°	677.3	732.4	783.8	829.0	866.4	894.1	907.2	914.5
140°	665.3	712.3	757.3	799.4	834.4	856.4	870.4	878.4
142.5°	654.1	695.5	734.2	770.6	801.6	822.0	834.4	840.0
145°	638.3	672.4	702.3	730.4	755.4	772.4	782.4	787.4
147.5°	625.3	652.3	676.3	698.4	716.8	731.3	739.0	740.7
150°	617.3	640.3	660.3	678.3	694.3	707.3	713.3	714.4
152.5°	608.5	628.3	646.7	661.5	675.1	685.7	689.3	690.3
155°	595.3	611.3	626.3	638.3	648.3	656.3	659.4	659.4
157.5°	581.1	594.5	607.1	616.7	624.3	630.3	632.1	632.1
160°	572.3	583.2	594.3	602.3	608.3	614.3	615.3	615.3
162.5°	563.4	572.9	581.5	588.7	593.1	599.1	600.1	599.3
165°	551.3	557.2	564.3	569.3	573.3	577.3	576.3	575.3
167.5°	539.5	544.1	549.7	552.7	554.7	557.2	557.1	556.3
170°	532.3	535.3	539.2	542.3	544.2	545.3	544.2	544.2
172.5°	525.8	528.1	530.5	532.6	533.8	534.9	533.8	532.3
175°	517.3	518.2	520.2	520.2	520.2	522.3	520.2	518.2
177.5°	511.6	512.5	512.5	513.2	512.5	513.2	511.6	510.1
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3

(END OF REPORT)