

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332541-830

Luminaire Tested: **SA4XXDIP-C575D365U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332541-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D365U830-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3727.8 lumens  
Efficiency: N/A  
Efficacy: 135.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332541-830

CATALOG NUMBER: SA4XXDIP-C575D365U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332541-830

CATALOG NUMBER: SA4XXDIP-C575D365U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	51	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	38
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25
7	60	47	39	34	56	45	37	32	40	34	30	36	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7389	7389	7389
5°	7412	7323	7376
10°	7365	7263	7299
15°	7276	7160	7178
20°	7158	7032	7039
25°	7023	6886	6866
30°	6858	6715	6652
35°	6686	6535	6447
40°	6509	6330	6215
45°	6322	6130	6012
50°	6116	5951	5766
55°	5895	5719	5533
60°	5672	5459	5293
65°	5421	5213	5001
70°	5141	4881	4692
75°	4713	4482	4370
80°	4193	4021	3924
85°	3668	3538	3464



TEST NUMBER: P332541-830

CATALOG NUMBER: SA4XXDIP-C575D365U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.2	2.3
10°-20°	242.9	6.5
20°-30°	357.5	9.6
30°-40°	415.6	11.1
40°-50°	415.6	11.1
50°-60°	363.5	9.8
60°-70°	270.0	7.2
70°-80°	153.4	4.1
80°-90°	45.6	1.2
90°-100°	15.2	0.4
100°-110°	97.1	2.6
110°-120°	185.8	5.0
120°-130°	235.8	6.3
130°-140°	252.3	6.8
140°-150°	236.0	6.3
150°-160°	190.3	5.1
160°-170°	122.7	3.3
170°-180°	42.3	1.1
0°-30°	686.6	18.4
0°-40°	1102.1	29.6
0°-60°	1881.3	50.5
0°-90°	2350.2	63.0
90°-120°	298.1	8.0
90°-150°	1022.3	27.4
90°-180°	1378.0	37.0
0°-180°	3727.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	915	915	915	915	915	
5°	915	911	904	911	910	87
15°	871	867	857	861	859	245
25°	788	783	773	774	771	363
35°	678	673	663	658	654	424
45°	554	548	537	529	527	427
55°	419	416	406	398	393	375
65°	284	280	273	266	262	281
75°	151	147	144	141	140	161
85°	40	40	38	38	37	44
90°	1	5	7	9	10	3
95°	18	8	7	9	10	24
105°	100	102	104	106	95	105
115°	187	188	188	188	188	184
125°	263	264	264	265	265	235
135°	326	326	327	328	329	251
145°	376	377	377	378	378	235
155°	413	413	412	413	412	190
165°	435	434	434	436	433	123
175°	445	444	444	446	443	42
180°	445	445	445	445	445	



TEST NUMBER: P332541-830

CATALOG NUMBER: SA4XXDIP-C575D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	917.7	917.3	916.9	916.5	916.2	915.2	913.8	912.4	910.9	909.5	910.8
5°	914.6	914.0	913.3	912.7	912.0	910.8	909.0	907.2	905.4	903.6	905.4
7.5°	906.1	905.4	904.8	904.2	903.5	902.2	900.2	898.2	896.2	894.2	895.7
10°	898.4	897.9	897.2	896.5	895.9	894.5	892.4	890.2	888.2	886.0	887.3
12.5°	888.5	887.9	887.2	886.6	885.9	884.5	882.2	880.0	877.7	875.4	876.8
15°	870.6	870.0	869.3	868.6	868.0	866.5	864.0	861.6	859.1	856.7	857.6
17.5°	849.0	848.2	847.4	846.6	845.7	844.2	841.9	839.6	837.3	835.0	835.6
20°	833.2	832.4	831.6	830.8	829.9	828.3	825.9	823.4	821.0	818.5	819.0
22.5°	816.1	815.1	814.1	812.9	811.9	810.1	807.7	805.2	802.8	800.3	801.3
25°	788.4	787.3	786.2	785.0	783.9	782.2	779.9	777.6	775.3	773.1	773.3
27.5°	756.8	755.6	754.4	753.3	752.1	750.5	748.3	746.2	744.0	742.0	741.6
30°	735.7	734.3	733.0	731.7	730.5	728.7	726.6	724.4	722.4	720.3	719.6
32.5°	713.3	712.2	711.0	709.8	708.7	706.9	704.7	702.5	700.2	698.0	697.2
35°	678.4	677.3	676.2	675.0	673.9	672.1	669.9	667.6	665.3	663.1	661.9
37.5°	641.6	640.6	639.5	638.5	637.4	635.7	633.3	630.8	628.4	625.9	624.7
40°	617.6	616.2	614.9	613.7	612.4	610.5	608.0	605.6	603.1	600.7	599.1
42.5°	591.7	591.0	590.2	589.4	588.6	586.8	584.2	581.5	578.7	576.1	574.2
45°	553.7	552.6	551.5	550.4	549.2	547.3	544.7	542.1	539.5	536.9	535.1
47.5°	514.0	513.2	512.5	511.6	510.9	509.3	506.9	504.4	502.0	499.6	497.6
50°	487.0	486.4	485.7	485.0	484.4	483.0	480.7	478.3	476.1	473.8	471.6
52.5°	460.6	459.9	459.0	458.3	457.5	455.9	453.5	451.1	448.7	446.2	444.2
55°	418.8	418.3	417.8	417.4	416.9	415.5	413.2	410.9	408.6	406.3	404.4
57.5°	378.9	378.3	377.8	377.2	376.6	375.3	373.1	370.8	368.5	366.3	364.4
60°	351.3	350.5	349.7	348.8	348.1	346.6	344.5	342.3	340.3	338.1	336.7
62.5°	324.3	323.7	322.9	322.3	321.6	320.1	317.9	315.7	313.4	311.1	309.8
65°	283.8	283.0	282.2	281.4	280.6	279.4	277.8	276.1	274.5	272.9	271.2
67.5°	243.1	242.3	241.6	240.8	240.1	238.9	237.3	235.8	234.2	232.6	231.1
70°	217.8	216.7	215.6	214.4	213.3	212.1	210.8	209.4	208.1	206.8	205.6
72.5°	190.9	189.7	188.6	187.4	186.2	185.2	184.2	183.1	182.1	181.0	179.9
75°	151.1	150.2	149.5	148.6	147.8	147.0	146.2	145.3	144.6	143.7	143.1
77.5°	113.1	112.7	112.4	112.1	111.7	111.1	110.4	109.7	109.0	108.3	108.0
80°	90.2	89.7	89.3	88.8	88.2	87.8	87.6	87.2	86.9	86.5	86.2
82.5°	68.0	67.7	67.5	67.2	67.0	66.8	66.8	66.7	66.6	66.6	66.4
85°	39.6	39.6	39.6	39.6	39.6	39.4	39.1	38.8	38.5	38.2	38.2
87.5°	15.5	15.5	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.6
90°	1.0	1.8	2.6	3.5	4.2	5.0	5.6	6.1	6.7	7.4	7.7
92.5°	4.2	4.2	4.2	4.3	4.3	4.7	5.3	5.8	6.5	7.1	7.5
95°	18.3	15.8	13.3	10.7	8.3	7.1	7.1	7.2	7.3	7.4	7.7
97.5°	38.9	40.4	42.0	43.6	45.1	41.8	33.6	25.4	17.1	8.8	8.9
100°	54.7	56.0	57.3	58.6	59.9	55.5	45.3	35.1	24.9	14.7	13.4
102.5°	72.2	73.2	74.2	75.1	76.2	76.0	74.6	73.3	71.9	70.6	57.0
105°	100.3	100.7	101.1	101.6	102.1	102.5	102.8	103.2	103.6	104.0	104.6
107.5°	126.3	126.5	126.8	127.0	127.2	127.5	128.1	128.6	129.0	129.6	129.9
110°	143.9	144.1	144.3	144.6	144.8	145.2	145.5	146.0	146.5	146.9	147.0



TEST NUMBER: P332541-830

CATALOG NUMBER: SA4XXDIP-C575D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.0	161.4	161.7	162.1	162.6	162.9	163.1	163.2	163.4	163.7	163.6
115°	187.2	187.5	187.7	187.8	188.1	188.1	188.1	188.0	187.9	187.8	188.0
117.5°	210.8	211.1	211.4	211.8	212.1	212.3	212.4	212.6	212.7	212.9	212.9
120°	226.9	227.2	227.4	227.7	228.0	228.1	228.1	228.0	227.9	227.8	228.0
122.5°	241.8	242.0	242.1	242.3	242.5	242.6	242.7	242.8	242.9	243.1	243.1
125°	263.2	263.4	263.7	264.0	264.4	264.4	264.3	264.1	264.0	263.8	264.0
127.5°	283.4	283.5	283.5	283.6	283.7	283.9	284.3	284.6	284.9	285.3	285.2
130°	296.4	296.5	296.6	296.7	296.8	296.9	297.1	297.4	297.6	297.8	297.8
132.5°	308.5	308.6	308.7	308.9	309.0	309.2	309.4	309.7	310.0	310.3	310.4
135°	326.4	326.4	326.3	326.2	326.1	326.2	326.6	326.9	327.2	327.4	327.6
137.5°	342.3	342.4	342.4	342.4	342.5	342.7	343.0	343.3	343.7	343.9	344.1
140°	352.8	352.9	353.1	353.2	353.4	353.5	353.6	353.8	353.9	354.1	354.3
142.5°	362.1	362.3	362.6	362.9	363.2	363.4	363.4	363.5	363.6	363.7	363.8
145°	376.5	376.6	376.8	377.1	377.3	377.4	377.4	377.4	377.4	377.4	377.5
147.5°	387.8	388.2	388.6	389.1	389.5	389.6	389.6	389.5	389.4	389.4	389.4
150°	396.1	396.3	396.6	397.0	397.3	397.4	397.3	397.2	397.1	397.1	397.1
152.5°	403.0	403.2	403.5	403.7	404.0	404.0	403.9	403.7	403.6	403.5	403.6
155°	412.7	412.8	412.8	412.9	413.0	412.9	412.7	412.5	412.3	412.1	412.4
157.5°	420.9	420.8	420.8	420.8	420.8	420.6	420.4	420.1	419.8	419.6	420.0
160°	425.7	425.5	425.3	425.1	424.8	424.7	424.6	424.5	424.4	424.3	424.8
162.5°	430.0	429.7	429.4	429.1	428.9	428.7	428.6	428.5	428.5	428.4	428.9
165°	435.4	435.0	434.6	434.2	433.9	433.7	433.7	433.7	433.7	433.7	434.3
167.5°	439.6	439.2	438.8	438.5	438.1	437.9	437.8	437.8	437.7	437.7	438.4
170°	442.1	441.6	441.1	440.7	440.3	440.1	440.2	440.3	440.3	440.4	440.9
172.5°	443.7	443.2	442.7	442.3	441.9	441.7	441.8	441.9	441.9	442.0	442.5
175°	445.4	444.9	444.5	444.0	443.6	443.4	443.5	443.6	443.7	443.7	444.4
177.5°	446.2	445.7	445.4	444.9	444.5	444.3	444.5	444.6	444.7	444.8	445.4
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4



TEST NUMBER: P332541-830  
 CATALOG NUMBER: SA4XXDIP-C575D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	912.1	913.4	914.7	915.3	915.1	915.0	914.9	914.7
5°	907.2	909.0	910.8	911.5	911.2	910.9	910.5	910.2
7.5°	897.1	898.5	899.9	900.6	900.4	900.2	900.0	899.8
10°	888.6	889.9	891.3	891.7	891.4	891.1	890.7	890.4
12.5°	878.4	879.8	881.2	881.7	881.2	880.7	880.3	879.9
15°	858.7	859.6	860.5	860.8	860.4	859.9	859.3	858.8
17.5°	836.2	836.8	837.4	837.5	837.3	836.9	836.6	836.3
20°	819.5	820.0	820.5	820.6	820.2	819.9	819.6	819.3
22.5°	802.1	803.0	803.9	804.0	803.4	802.9	802.3	801.6
25°	773.4	773.5	773.7	773.5	772.8	772.1	771.5	770.8
27.5°	741.2	740.7	740.4	739.8	739.0	738.2	737.4	736.5
30°	719.0	718.3	717.7	716.9	716.0	715.3	714.4	713.6
32.5°	696.4	695.6	694.8	694.0	693.2	692.4	691.5	690.8
35°	660.7	659.6	658.5	657.5	656.7	655.8	655.1	654.2
37.5°	623.5	622.2	620.9	619.8	618.8	617.6	616.6	615.5
40°	597.5	595.8	594.2	593.0	592.1	591.4	590.5	589.7
42.5°	572.3	570.3	568.4	567.2	566.8	566.2	565.6	565.1
45°	533.3	531.5	529.7	528.6	528.1	527.6	527.1	526.6
47.5°	495.6	493.5	491.5	489.9	488.7	487.4	486.2	484.9
50°	469.2	466.9	464.7	463.1	462.0	461.1	460.1	459.1
52.5°	442.1	440.2	438.2	436.5	435.3	434.0	432.8	431.6
55°	402.5	400.5	398.5	397.0	396.1	395.1	394.1	393.1
57.5°	362.6	360.7	358.8	357.4	356.5	355.5	354.6	353.6
60°	335.2	333.8	332.2	331.1	330.3	329.5	328.7	327.8
62.5°	308.5	307.1	305.8	304.7	303.9	303.1	302.3	301.4
65°	269.6	268.0	266.4	265.1	264.3	263.4	262.7	261.8
67.5°	229.5	228.0	226.4	225.5	225.3	225.1	224.8	224.6
70°	204.2	202.9	201.6	200.8	200.2	199.7	199.3	198.8
72.5°	178.9	177.9	176.8	176.1	175.6	175.1	174.7	174.1
75°	142.4	141.8	141.2	140.7	140.5	140.4	140.3	140.1
77.5°	107.8	107.6	107.4	107.2	106.7	106.3	105.8	105.5
80°	85.9	85.6	85.2	85.0	84.8	84.6	84.5	84.4
82.5°	66.2	66.0	65.8	65.6	65.5	65.3	65.1	64.9
85°	38.2	38.2	38.2	38.1	37.9	37.7	37.6	37.4
87.5°	15.7	15.8	15.9	15.9	16.0	16.0	16.0	16.1
90°	8.2	8.7	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	7.9	8.4	8.9	9.0	9.1	9.1	9.1	9.2
95°	8.2	8.7	9.1	9.3	9.4	9.5	9.6	9.6
97.5°	8.9	9.0	9.0	9.0	9.1	9.1	9.2	9.3
100°	12.2	10.8	9.6	9.0	9.1	9.1	9.2	9.3
102.5°	43.5	29.9	16.3	9.5	9.5	9.5	9.6	9.6
105°	105.3	105.9	106.6	105.6	102.9	100.3	97.6	94.9
107.5°	130.3	130.5	130.9	131.2	131.5	131.8	132.1	132.3
110°	147.2	147.3	147.5	147.7	147.9	148.2	148.4	148.5





TEST NUMBER: P332541-830

CATALOG NUMBER: SA4XXDIP-C575D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	163.6	163.6	163.5	163.7	164.0	164.3	164.6	164.9
115°	188.1	188.3	188.5	188.5	188.5	188.5	188.5	188.5
117.5°	212.8	212.8	212.8	212.7	212.7	212.7	212.7	212.6
120°	228.1	228.3	228.5	228.5	228.3	228.1	228.0	227.8
122.5°	243.2	243.3	243.4	243.4	243.2	243.1	242.9	242.8
125°	264.3	264.5	264.7	264.9	264.9	265.0	265.0	265.1
127.5°	285.2	285.1	285.1	285.0	285.0	284.9	284.8	284.8
130°	297.9	298.0	298.1	298.1	298.1	298.1	298.1	298.1
132.5°	310.5	310.6	310.7	310.7	310.6	310.5	310.5	310.4
135°	327.7	327.9	328.0	328.2	328.3	328.5	328.7	328.8
137.5°	344.3	344.5	344.6	344.7	344.6	344.6	344.5	344.5
140°	354.5	354.8	355.0	355.2	355.2	355.2	355.3	355.4
142.5°	364.0	364.2	364.3	364.4	364.5	364.5	364.5	364.5
145°	377.6	377.7	377.7	377.8	378.0	378.1	378.2	378.4
147.5°	389.5	389.6	389.6	389.6	389.7	389.7	389.8	389.9
150°	397.1	397.1	397.1	397.1	397.2	397.3	397.3	397.4
152.5°	403.7	403.8	404.0	404.0	403.9	403.9	403.9	403.8
155°	412.6	412.9	413.2	413.3	413.0	412.8	412.6	412.4
157.5°	420.4	420.8	421.1	421.1	420.8	420.4	420.0	419.6
160°	425.3	425.7	426.1	426.1	425.7	425.3	424.8	424.3
162.5°	429.2	429.7	430.2	430.1	429.6	429.1	428.6	428.1
165°	434.9	435.5	436.1	436.0	435.4	434.7	434.0	433.4
167.5°	439.0	439.7	440.3	440.3	439.5	438.8	438.0	437.3
170°	441.6	442.1	442.7	442.6	442.0	441.2	440.5	439.7
172.5°	443.2	443.7	444.3	444.2	443.5	442.6	441.9	441.0
175°	445.1	445.7	446.4	446.3	445.4	444.5	443.6	442.7
177.5°	445.8	446.3	446.8	446.6	445.9	445.2	444.5	443.7
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4

(END OF REPORT)