

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332934-935

Luminaire Tested: **SA4XXRDIP-C795D590U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332934-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4796.5 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332934-935
CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332934-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58				58
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54	49				49
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46	42				42
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	42	39	36				36
4	76	66	58	52	71	62	55	49	54	48	44	47	42	39	40	37	34	31				31
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30	27				27
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	27	24				24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21				21
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21	19				19
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19	17				17
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16				16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P332934-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	2.3
10°-20°	313.3	6.5
20°-30°	452.4	9.4
30°-40°	512.8	10.7
40°-50°	495.2	10.3
50°-60°	411.8	8.6
60°-70°	284.4	5.9
70°-80°	144.1	3.0
80°-90°	38.9	0.8
90°-100°	22.5	0.5
100°-110°	143.2	3.0
110°-120°	273.9	5.7
120°-130°	347.7	7.2
130°-140°	372.1	7.8
140°-150°	347.9	7.3
150°-160°	280.6	5.8
160°-170°	181.0	3.8
170°-180°	62.4	1.3
0°-30°	878.1	18.3
0°-40°	1390.9	29.0
0°-60°	2297.9	47.9
0°-90°	2765.3	57.7
90°-120°	439.6	9.2
90°-150°	1507.3	31.4
90°-180°	2031.0	42.3
0°-180°	4796.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	2	7	11	14	15	4
95°	27	11	11	14	14	35
105°	148	151	153	156	140	155
115°	276	277	277	278	278	272
125°	388	390	389	390	391	346
135°	481	481	483	484	485	371
145°	555	556	556	557	558	347
155°	609	609	608	609	608	280
165°	642	640	640	643	639	181
175°	657	654	654	658	653	63
180°	657	657	657	657	657	



TEST NUMBER: P332934-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.1	16.1	15.0	13.9	12.9	12.4	12.4	12.4	12.4	12.4	12.4
90°	1.5	2.7	3.9	5.1	6.3	7.3	8.2	9.0	9.9	10.8	11.5
92.5°	6.2	6.3	6.3	6.4	6.5	6.9	7.8	8.7	9.6	10.4	11.1
95°	27.0	23.3	19.6	15.8	12.1	10.3	10.5	10.6	10.7	10.8	11.5
97.5°	57.3	59.7	62.0	64.3	66.6	61.6	49.5	37.4	25.1	13.0	13.0
100°	80.5	82.5	84.5	86.4	88.4	81.9	66.8	51.7	36.7	21.6	19.7
102.5°	106.5	107.9	109.3	110.8	112.3	112.0	110.0	108.1	106.1	104.1	84.1
105°	147.8	148.5	149.1	149.8	150.4	151.0	151.6	152.1	152.7	153.3	154.2
107.5°	186.2	186.6	186.9	187.2	187.5	188.0	188.8	189.6	190.3	191.1	191.6
110°	212.2	212.5	212.8	213.2	213.4	214.0	214.6	215.2	215.9	216.6	216.8



TEST NUMBER: P332934-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	237.3	237.9	238.5	239.1	239.7	240.1	240.4	240.7	241.1	241.3	241.3
115°	276.0	276.4	276.6	277.0	277.3	277.4	277.3	277.2	277.1	277.0	277.2
117.5°	310.9	311.3	311.8	312.2	312.6	313.0	313.2	313.5	313.7	313.9	313.9
120°	334.5	334.9	335.4	335.8	336.2	336.4	336.3	336.1	336.0	336.0	336.1
122.5°	356.5	356.7	357.0	357.2	357.5	357.7	357.9	358.0	358.2	358.3	358.4
125°	388.0	388.4	388.9	389.3	389.8	389.9	389.6	389.4	389.2	389.0	389.3
127.5°	417.8	417.9	418.1	418.2	418.3	418.6	419.1	419.6	420.1	420.6	420.5
130°	437.1	437.2	437.3	437.5	437.6	437.7	438.1	438.4	438.8	439.1	439.2
132.5°	454.8	455.0	455.2	455.4	455.6	455.9	456.3	456.7	457.1	457.5	457.6
135°	481.3	481.2	481.1	481.0	480.9	481.0	481.5	481.9	482.3	482.8	483.0
137.5°	504.8	504.8	504.9	504.9	505.0	505.2	505.7	506.2	506.7	507.1	507.4
140°	520.1	520.3	520.6	520.7	521.0	521.2	521.4	521.7	521.9	522.1	522.4
142.5°	533.9	534.3	534.7	535.0	535.5	535.7	535.8	536.0	536.1	536.2	536.5
145°	555.0	555.3	555.6	555.9	556.3	556.5	556.5	556.5	556.5	556.5	556.6
147.5°	571.8	572.4	573.0	573.6	574.2	574.5	574.4	574.3	574.1	574.0	574.1
150°	583.9	584.4	584.9	585.3	585.7	585.9	585.7	585.7	585.6	585.4	585.4
152.5°	594.2	594.5	594.9	595.2	595.6	595.6	595.5	595.3	595.0	594.9	595.0
155°	608.6	608.6	608.7	608.8	609.0	608.8	608.6	608.2	607.9	607.5	608.0
157.5°	620.6	620.5	620.4	620.4	620.4	620.1	619.7	619.4	619.0	618.6	619.2
160°	627.7	627.3	627.0	626.7	626.4	626.1	626.0	625.9	625.8	625.7	626.4
162.5°	634.0	633.5	633.1	632.7	632.3	632.1	631.9	631.8	631.7	631.6	632.2
165°	641.9	641.4	640.8	640.2	639.7	639.5	639.5	639.5	639.5	639.5	640.3
167.5°	648.2	647.6	647.0	646.5	645.9	645.6	645.6	645.5	645.4	645.3	646.4
170°	651.8	651.1	650.4	649.8	649.1	648.8	648.9	649.0	649.2	649.3	650.1
172.5°	654.1	653.4	652.8	652.1	651.5	651.2	651.3	651.4	651.5	651.6	652.6
175°	656.7	656.0	655.3	654.7	654.0	653.8	653.8	654.0	654.1	654.2	655.1
177.5°	657.8	657.2	656.6	656.0	655.4	655.1	655.3	655.5	655.7	655.8	656.6
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7



TEST NUMBER: P332934-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	12.3	12.3	12.3	12.4	12.6	12.8	13.0	13.2
90°	12.1	12.7	13.4	13.9	14.1	14.3	14.6	14.7
92.5°	11.7	12.4	13.0	13.3	13.4	13.4	13.5	13.5
95°	12.1	12.7	13.4	13.8	13.9	14.0	14.1	14.2
97.5°	13.1	13.2	13.3	13.3	13.4	13.5	13.6	13.8
100°	17.9	16.0	14.2	13.3	13.4	13.5	13.6	13.8
102.5°	64.1	44.1	24.0	14.0	14.1	14.1	14.1	14.1
105°	155.2	156.2	157.1	155.7	151.8	147.8	143.9	140.0
107.5°	192.0	192.5	193.0	193.4	193.8	194.2	194.7	195.1
110°	217.1	217.2	217.5	217.7	218.1	218.3	218.7	219.0



TEST NUMBER: P332934-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	241.3	241.3	241.2	241.3	241.8	242.2	242.6	243.0
115°	277.4	277.7	277.8	278.0	278.0	278.0	278.0	278.0
117.5°	313.8	313.8	313.7	313.7	313.7	313.7	313.6	313.6
120°	336.4	336.6	336.8	336.8	336.6	336.4	336.1	336.0
122.5°	358.6	358.7	358.9	358.8	358.6	358.3	358.2	357.9
125°	389.6	389.9	390.3	390.5	390.6	390.7	390.8	391.0
127.5°	420.5	420.4	420.3	420.3	420.2	420.1	420.0	419.9
130°	439.3	439.4	439.5	439.5	439.5	439.5	439.5	439.5
132.5°	457.8	457.9	458.0	458.0	457.9	457.8	457.7	457.6
135°	483.2	483.5	483.6	483.9	484.1	484.3	484.6	484.7
137.5°	507.6	507.9	508.1	508.2	508.2	508.1	508.0	507.9
140°	522.7	523.1	523.4	523.6	523.7	523.8	523.9	524.0
142.5°	536.7	536.9	537.2	537.4	537.4	537.4	537.4	537.4
145°	556.6	556.8	556.9	557.1	557.2	557.5	557.8	557.9
147.5°	574.2	574.3	574.4	574.5	574.6	574.7	574.8	574.9
150°	585.4	585.4	585.4	585.5	585.6	585.7	585.8	585.9
152.5°	595.2	595.4	595.6	595.6	595.6	595.5	595.4	595.4
155°	608.4	608.8	609.2	609.3	609.0	608.6	608.4	608.0
157.5°	619.7	620.4	620.9	620.9	620.4	619.7	619.2	618.6
160°	627.0	627.7	628.4	628.4	627.7	627.0	626.4	625.7
162.5°	632.9	633.5	634.2	634.2	633.4	632.7	632.0	631.2
165°	641.2	642.0	643.0	642.9	641.9	640.9	640.0	638.9
167.5°	647.3	648.2	649.2	649.1	648.1	647.0	645.8	644.8
170°	651.0	651.9	652.8	652.6	651.6	650.5	649.4	648.3
172.5°	653.4	654.3	655.1	655.0	653.8	652.6	651.4	650.2
175°	656.2	657.1	658.1	658.0	656.7	655.3	654.0	652.7
177.5°	657.3	658.0	658.7	658.5	657.5	656.4	655.3	654.3
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7

(END OF REPORT)