

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332552-830

Luminaire Tested: **SA4XXDIP-C575D590U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332552-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D590U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4340.8 lumens
Efficiency: N/A
Efficacy: 132.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332552-830
CATALOG NUMBER: SA4XXDIP-C575D590U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332552-830

CATALOG NUMBER: SA4XXDIP-C575D590U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54				
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51	46				
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	44	43	38				
3	82	72	65	59	76	67	61	56	58	53	49	49	46	42	41	39	36	32				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28				
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27	24				
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21				
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	28	24	21	19				
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17				
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15				
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7389	7389	7389
5°	7412	7323	7376
10°	7365	7263	7299
15°	7276	7160	7178
20°	7158	7032	7039
25°	7023	6886	6866
30°	6858	6715	6652
35°	6686	6535	6447
40°	6509	6330	6215
45°	6322	6130	6012
50°	6116	5951	5766
55°	5895	5719	5533
60°	5672	5459	5293
65°	5421	5213	5001
70°	5141	4881	4692
75°	4713	4482	4370
80°	4193	4021	3924
85°	3668	3538	3464



TEST NUMBER: P332552-830

CATALOG NUMBER: SA4XXDIP-C575D590U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	2.0
10°-20°	242.9	5.6
20°-30°	357.5	8.2
30°-40°	415.6	9.6
40°-50°	415.6	9.6
50°-60°	363.5	8.4
60°-70°	270.0	6.2
70°-80°	153.4	3.5
80°-90°	45.8	1.1
90°-100°	197.7	4.6
100°-110°	411.4	9.5
110°-120°	368.5	8.5
120°-130°	310.0	7.1
130°-140°	258.4	6.0
140°-150°	197.4	4.5
150°-160°	138.8	3.2
160°-170°	81.6	1.9
170°-180°	26.6	0.6
0°-30°	686.6	15.8
0°-40°	1102.1	25.4
0°-60°	1881.3	43.3
0°-90°	2350.4	54.1
90°-120°	977.6	22.5
90°-150°	1743.4	40.2
90°-180°	1990.0	45.8
0°-180°	4340.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	915	915	915	915	915	
5°	915	911	904	911	910	87
15°	871	867	857	861	859	245
25°	788	783	773	774	771	363
35°	678	673	663	658	654	424
45°	554	548	537	529	527	427
55°	419	416	406	398	393	375
65°	284	280	273	266	262	281
75°	151	147	144	141	140	161
85°	40	40	38	38	37	44
90°	1	4	10	11	11	3
95°	18	56	438	217	131	20
105°	63	91	353	760	756	67
115°	111	139	314	604	726	110
125°	154	183	313	514	580	137
135°	183	218	310	456	518	142
145°	211	242	309	385	423	133
155°	240	259	300	340	354	111
165°	262	270	288	305	309	74
175°	273	274	276	280	278	26
180°	274	274	274	274	274	



TEST NUMBER: P332552-830

CATALOG NUMBER: SA4XXDIP-C575D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	917.7	917.3	916.9	916.5	916.2	915.2	913.8	912.4	910.9	909.5	910.8
5°	914.6	914.0	913.3	912.7	912.0	910.8	909.0	907.2	905.4	903.6	905.4
7.5°	906.1	905.4	904.8	904.2	903.5	902.2	900.2	898.2	896.2	894.2	895.7
10°	898.4	897.9	897.2	896.5	895.9	894.5	892.4	890.2	888.2	886.0	887.3
12.5°	888.5	887.9	887.2	886.6	885.9	884.5	882.2	880.0	877.7	875.4	876.8
15°	870.6	870.0	869.3	868.6	868.0	866.5	864.0	861.6	859.1	856.7	857.6
17.5°	849.0	848.2	847.4	846.6	845.7	844.2	841.9	839.6	837.3	835.0	835.6
20°	833.2	832.4	831.6	830.8	829.9	828.3	825.9	823.4	821.0	818.5	819.0
22.5°	816.1	815.1	814.1	812.9	811.9	810.1	807.7	805.2	802.8	800.3	801.3
25°	788.4	787.3	786.2	785.0	783.9	782.2	779.9	777.6	775.3	773.1	773.3
27.5°	756.8	755.6	754.4	753.3	752.1	750.5	748.3	746.2	744.0	742.0	741.6
30°	735.7	734.3	733.0	731.7	730.5	728.7	726.6	724.4	722.4	720.3	719.6
32.5°	713.3	712.2	711.0	709.8	708.7	706.9	704.7	702.5	700.2	698.0	697.2
35°	678.4	677.3	676.2	675.0	673.9	672.1	669.9	667.6	665.3	663.1	661.9
37.5°	641.6	640.6	639.5	638.5	637.4	635.7	633.3	630.8	628.4	625.9	624.7
40°	617.6	616.2	614.9	613.7	612.4	610.5	608.0	605.6	603.1	600.7	599.1
42.5°	591.7	591.0	590.2	589.4	588.6	586.8	584.2	581.5	578.7	576.1	574.2
45°	553.7	552.6	551.5	550.4	549.2	547.3	544.7	542.1	539.5	536.9	535.1
47.5°	514.0	513.2	512.5	511.6	510.9	509.3	506.9	504.4	502.0	499.6	497.6
50°	487.0	486.4	485.7	485.0	484.4	483.0	480.7	478.3	476.1	473.8	471.6
52.5°	460.6	459.9	459.0	458.3	457.5	455.9	453.5	451.1	448.7	446.2	444.2
55°	418.8	418.3	417.8	417.4	416.9	415.5	413.2	410.9	408.6	406.3	404.4
57.5°	378.9	378.3	377.8	377.2	376.6	375.3	373.1	370.8	368.5	366.3	364.4
60°	351.3	350.5	349.7	348.8	348.1	346.6	344.5	342.3	340.3	338.1	336.7
62.5°	324.3	323.7	322.9	322.3	321.6	320.1	317.9	315.7	313.4	311.1	309.8
65°	283.8	283.0	282.2	281.4	280.6	279.4	277.8	276.1	274.5	272.9	271.2
67.5°	243.1	242.3	241.6	240.8	240.1	238.9	237.3	235.8	234.2	232.6	231.1
70°	217.8	216.7	215.6	214.4	213.3	212.1	210.8	209.4	208.1	206.8	205.6
72.5°	190.9	189.7	188.6	187.4	186.2	185.2	184.2	183.1	182.1	181.0	179.9
75°	151.1	150.2	149.5	148.6	147.8	147.0	146.2	145.3	144.6	143.7	143.1
77.5°	113.1	112.7	112.4	112.1	111.7	111.1	110.4	109.7	109.0	108.3	108.0
80°	90.2	89.7	89.3	88.8	88.2	87.8	87.6	87.2	86.9	86.5	86.2
82.5°	68.0	67.7	67.5	67.2	67.0	66.8	66.8	66.7	66.6	66.6	66.4
85°	39.6	39.6	39.6	39.6	39.6	39.4	39.1	38.8	38.5	38.2	38.2
87.5°	15.4	15.5	15.6	15.6	15.6	15.5	16.0	15.8	15.9	16.0	15.9
90°	0.6	1.6	3.2	3.8	4.3	4.3	7.5	7.5	8.6	9.7	9.1
92.5°	6.1	9.0	13.9	20.5	28.4	39.6	66.9	108.6	149.3	170.5	142.0
95°	17.7	19.3	24.7	31.8	44.6	67.2	114.0	202.2	330.6	438.2	450.5
97.5°	31.9	31.9	36.5	42.9	54.0	73.0	109.0	181.7	309.5	461.6	566.1
100°	40.9	40.9	44.6	51.1	61.3	78.5	110.2	171.0	280.7	432.3	570.0
102.5°	49.5	50.3	53.6	59.7	69.5	85.8	114.5	168.0	261.3	395.8	537.6
105°	62.9	64.6	67.2	73.7	83.3	99.0	124.7	169.4	244.7	352.7	479.1
107.5°	77.8	78.8	81.5	88.4	97.6	113.0	136.7	177.3	241.7	328.7	431.8
110°	87.7	88.7	91.4	97.8	107.5	122.1	145.7	183.3	242.5	320.5	408.1



TEST NUMBER: P332552-830

CATALOG NUMBER: SA4XXDIP-C575D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.1	98.2	101.3	107.4	117.0	131.5	154.3	189.8	245.1	316.6	394.7
115°	110.7	112.4	116.1	121.5	131.8	146.3	167.8	200.0	250.1	314.5	382.3
117.5°	125.0	126.5	129.8	135.7	145.2	160.3	180.8	210.5	255.2	314.0	376.7
120°	134.4	135.5	139.2	145.2	154.3	169.4	189.8	217.7	259.2	314.0	373.7
122.5°	143.0	144.1	147.9	153.4	163.3	178.0	198.4	224.6	263.1	313.6	370.2
125°	154.3	156.5	159.7	165.6	175.8	190.9	210.2	235.0	268.8	312.9	364.6
127.5°	164.3	166.1	169.9	176.6	187.3	202.5	221.2	243.9	273.4	311.7	356.9
130°	169.9	172.0	176.3	184.5	194.6	210.2	228.5	249.5	276.9	311.3	352.1
132.5°	175.5	177.2	182.9	190.5	201.5	216.2	234.5	255.1	279.9	310.9	347.9
135°	183.3	185.5	190.9	200.0	211.3	225.3	243.0	262.4	284.5	310.2	341.4
137.5°	191.2	193.2	199.2	207.8	219.6	232.9	249.5	267.6	287.1	310.1	335.8
140°	196.8	198.4	204.3	213.5	224.7	237.6	253.8	271.0	289.3	309.7	332.8
142.5°	202.8	204.4	209.9	218.6	229.5	242.0	257.7	273.5	291.0	309.7	330.3
145°	211.3	212.9	218.3	225.8	236.0	247.9	261.8	276.4	292.0	308.6	325.8
147.5°	220.8	221.4	226.1	233.8	242.4	253.1	266.2	278.8	292.5	306.7	321.9
150°	226.9	227.4	231.8	238.2	246.3	256.5	268.3	280.1	292.5	305.4	318.9
152.5°	232.5	232.6	236.9	242.9	250.2	259.5	270.0	281.0	291.6	303.2	315.4
155°	240.3	240.9	244.1	249.5	255.4	263.4	272.6	281.7	290.3	300.0	310.2
157.5°	248.0	248.0	251.0	255.1	260.3	266.6	274.5	281.7	289.0	296.7	305.0
160°	252.7	252.7	254.9	258.6	262.9	268.8	275.3	281.7	287.7	294.1	301.1
162.5°	257.0	256.6	258.3	261.6	265.5	270.1	276.2	281.7	286.3	291.5	297.7
165°	261.8	261.8	262.9	265.6	268.3	271.5	276.4	280.7	283.9	287.7	292.0
167.5°	266.6	266.2	266.6	268.7	270.2	272.7	276.3	279.4	281.3	283.8	286.8
170°	268.8	268.3	268.8	270.4	271.5	273.1	275.8	278.5	279.6	281.2	283.3
172.5°	271.0	270.4	270.5	271.7	272.4	273.5	275.4	277.7	277.9	278.6	280.3
175°	273.1	272.6	272.6	273.1	273.7	273.7	274.8	276.4	275.8	275.8	276.9
177.5°	274.1	273.7	273.2	273.7	273.7	273.7	274.1	274.9	274.1	274.1	274.6
180°	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7



TEST NUMBER: P332552-830

CATALOG NUMBER: SA4XXDIP-C575D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	912.1	913.4	914.7	915.3	915.1	915.0	914.9	914.7
5°	907.2	909.0	910.8	911.5	911.2	910.9	910.5	910.2
7.5°	897.1	898.5	899.9	900.6	900.4	900.2	900.0	899.8
10°	888.6	889.9	891.3	891.7	891.4	891.1	890.7	890.4
12.5°	878.4	879.8	881.2	881.7	881.2	880.7	880.3	879.9
15°	858.7	859.6	860.5	860.8	860.4	859.9	859.3	858.8
17.5°	836.2	836.8	837.4	837.5	837.3	836.9	836.6	836.3
20°	819.5	820.0	820.5	820.6	820.2	819.9	819.6	819.3
22.5°	802.1	803.0	803.9	804.0	803.4	802.9	802.3	801.6
25°	773.4	773.5	773.7	773.5	772.8	772.1	771.5	770.8
27.5°	741.2	740.7	740.4	739.8	739.0	738.2	737.4	736.5
30°	719.0	718.3	717.7	716.9	716.0	715.3	714.4	713.6
32.5°	696.4	695.6	694.8	694.0	693.2	692.4	691.5	690.8
35°	660.7	659.6	658.5	657.5	656.7	655.8	655.1	654.2
37.5°	623.5	622.2	620.9	619.8	618.8	617.6	616.6	615.5
40°	597.5	595.8	594.2	593.0	592.1	591.4	590.5	589.7
42.5°	572.3	570.3	568.4	567.2	566.8	566.2	565.6	565.1
45°	533.3	531.5	529.7	528.6	528.1	527.6	527.1	526.6
47.5°	495.6	493.5	491.5	489.9	488.7	487.4	486.2	484.9
50°	469.2	466.9	464.7	463.1	462.0	461.1	460.1	459.1
52.5°	442.1	440.2	438.2	436.5	435.3	434.0	432.8	431.6
55°	402.5	400.5	398.5	397.0	396.1	395.1	394.1	393.1
57.5°	362.6	360.7	358.8	357.4	356.5	355.5	354.6	353.6
60°	335.2	333.8	332.2	331.1	330.3	329.5	328.7	327.8
62.5°	308.5	307.1	305.8	304.7	303.9	303.1	302.3	301.4
65°	269.6	268.0	266.4	265.1	264.3	263.4	262.7	261.8
67.5°	229.5	228.0	226.4	225.5	225.3	225.1	224.8	224.6
70°	204.2	202.9	201.6	200.8	200.2	199.7	199.3	198.8
72.5°	178.9	177.9	176.8	176.1	175.6	175.1	174.7	174.1
75°	142.4	141.8	141.2	140.7	140.5	140.4	140.3	140.1
77.5°	107.8	107.6	107.4	107.2	106.7	106.3	105.8	105.5
80°	85.9	85.6	85.2	85.0	84.8	84.6	84.5	84.4
82.5°	66.2	66.0	65.8	65.6	65.5	65.3	65.1	64.9
85°	38.2	38.2	38.2	38.1	37.9	37.7	37.6	37.4
87.5°	16.0	16.1	16.2	16.2	16.3	16.5	16.3	16.3
90°	9.7	10.2	10.7	10.7	11.3	11.8	11.3	11.3
92.5°	105.6	79.5	63.2	52.5	46.1	43.3	41.4	41.4
95°	398.4	315.1	243.0	190.9	164.6	147.9	138.2	131.2
97.5°	588.6	557.7	505.1	448.9	410.4	378.0	361.8	350.6
100°	648.5	659.2	632.8	593.0	546.3	513.5	497.4	493.0
102.5°	645.5	698.8	706.4	689.8	661.1	637.3	620.4	616.9
105°	602.2	695.2	748.5	770.5	771.6	767.2	759.7	756.5
107.5°	540.8	639.8	714.8	762.7	789.3	801.5	806.9	808.3
110°	503.8	596.8	674.8	734.0	772.1	794.7	804.4	809.2



TEST NUMBER: P332552-830

CATALOG NUMBER: SA4XXDIP-C575D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	476.7	558.9	632.6	691.7	735.1	762.4	776.0	783.8
115°	449.5	515.7	578.5	630.2	672.6	704.9	722.1	726.4
117.5°	436.1	490.9	540.4	584.1	620.4	647.4	664.9	668.3
120°	430.2	480.1	523.1	561.3	592.0	615.7	629.6	635.6
122.5°	425.0	473.3	512.4	545.8	571.7	592.0	603.8	609.7
125°	416.1	462.4	499.5	529.0	550.5	566.2	576.4	579.6
127.5°	405.4	449.6	486.6	514.6	536.3	550.2	558.7	561.9
130°	396.8	439.3	475.8	504.4	526.4	539.8	548.5	551.7
132.5°	387.8	427.6	463.4	491.8	513.5	528.7	536.8	540.1
135°	375.3	410.3	443.0	470.0	491.4	506.5	515.1	518.3
137.5°	364.0	393.6	421.2	445.5	465.6	480.5	487.6	491.4
140°	357.5	382.9	407.0	429.6	448.5	460.2	467.8	472.1
142.5°	351.6	373.8	394.5	414.2	430.7	441.8	448.5	451.4
145°	343.0	361.3	377.5	392.5	406.0	415.1	420.5	423.1
147.5°	336.0	350.5	363.4	375.3	385.2	393.0	397.1	398.1
150°	331.8	344.1	354.9	364.6	373.2	380.1	383.3	383.9
152.5°	327.0	337.6	347.5	355.5	362.8	368.5	370.4	371.0
155°	319.9	328.5	336.6	343.0	348.5	352.7	354.3	354.3
157.5°	312.3	319.5	326.2	331.4	335.5	338.7	339.7	339.7
160°	307.6	313.5	319.3	323.7	326.9	330.2	330.6	330.6
162.5°	302.8	307.8	312.5	316.4	318.8	322.0	322.5	322.1
165°	296.2	299.4	303.2	305.9	308.1	310.2	309.7	309.2
167.5°	289.9	292.4	295.4	297.0	298.1	299.4	299.4	299.0
170°	286.1	287.7	289.8	291.4	292.5	293.0	292.5	292.5
172.5°	282.6	283.8	285.1	286.3	286.9	287.5	286.9	286.1
175°	278.0	278.5	279.6	279.6	279.6	280.7	279.6	278.5
177.5°	274.9	275.4	275.4	275.8	275.4	275.8	274.9	274.1
180°	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7

(END OF REPORT)