

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332658-840

Luminaire Tested: **SA4XXDIP-C1020D1035U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332658-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D1035U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8644.8 lumens  
Efficiency: N/A  
Efficacy: 142.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332658-840  
CATALOG NUMBER: SA4XXDIP-C1020D1035U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332658-840

CATALOG NUMBER: SA4XXDIP-C1020D1035U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52				
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49	44				
2	89	82	76	70	82	76	71	66	65	61	57	54	51	49	45	43	41	36				
3	82	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31				
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	36	33	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23				
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20				
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18	16				
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	22	19	17	14				
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14067	14067	14067
5°	14109	13940	14041
10°	14021	13827	13896
15°	13852	13630	13665
20°	13626	13387	13399
25°	13370	13109	13071
30°	13055	12781	12665
35°	12728	12439	12275
40°	12390	12052	11830
45°	12036	11669	11445
50°	11645	11328	10977
55°	11222	10888	10534
60°	10798	10393	10077
65°	10323	9922	9522
70°	9788	9293	8932
75°	8971	8537	8319
80°	7987	7657	7466
85°	6984	6725	6595



TEST NUMBER: P332658-840

CATALOG NUMBER: SA4XXDIP-C1020D1035U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	164.1	1.9
10°-20°	462.4	5.3
20°-30°	680.5	7.9
30°-40°	791.1	9.2
40°-50°	791.2	9.2
50°-60°	692.1	8.0
60°-70°	514.0	5.9
70°-80°	292.0	3.4
80°-90°	88.2	1.0
90°-100°	46.1	0.5
100°-110°	293.9	3.4
110°-120°	562.3	6.5
120°-130°	713.8	8.3
130°-140°	763.7	8.8
140°-150°	714.1	8.3
150°-160°	575.9	6.7
160°-170°	371.4	4.3
170°-180°	128.0	1.5
0°-30°	1307.0	15.1
0°-40°	2098.1	24.3
0°-60°	3581.3	41.4
0°-90°	4475.4	51.8
90°-120°	902.3	10.4
90°-150°	3094.0	35.8
90°-180°	4169.0	48.2
0°-180°	8644.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1742	1742	1742	1742	1742	
5°	1741	1735	1720	1735	1733	165
15°	1657	1651	1631	1638	1635	467
25°	1501	1491	1472	1473	1467	690
35°	1292	1281	1262	1253	1246	807
45°	1054	1044	1022	1007	1002	812
55°	797	792	774	757	748	714
65°	540	533	519	506	498	535
75°	288	281	274	268	267	306
85°	75	75	73	72	71	83
90°	3	14	22	28	30	7
95°	55	23	22	28	29	71
105°	304	309	315	321	287	317
115°	566	569	569	570	571	557
125°	796	800	798	801	802	711
135°	988	987	991	993	995	761
145°	1139	1142	1142	1143	1145	712
155°	1249	1250	1247	1251	1248	576
165°	1318	1313	1312	1320	1312	372
175°	1348	1342	1343	1351	1340	128
180°	1348	1348	1348	1348	1348	



TEST NUMBER: P332658-840

CATALOG NUMBER: SA4XXDIP-C1020D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1747.0	1746.3	1745.5	1744.7	1744.0	1742.2	1739.5	1736.8	1734.0	1731.3	1733.8
5°	1741.1	1739.9	1738.7	1737.4	1736.2	1733.8	1730.4	1727.0	1723.6	1720.2	1723.6
7.5°	1725.0	1723.6	1722.4	1721.2	1720.0	1717.5	1713.6	1709.9	1706.1	1702.3	1705.1
10°	1710.4	1709.2	1707.9	1706.7	1705.5	1702.8	1698.8	1694.8	1690.7	1686.7	1689.1
12.5°	1691.4	1690.2	1688.9	1687.7	1686.5	1683.6	1679.4	1675.2	1670.8	1666.6	1669.3
15°	1657.4	1656.1	1654.9	1653.7	1652.3	1649.4	1644.8	1640.1	1635.5	1630.8	1632.6
17.5°	1616.3	1614.8	1613.2	1611.6	1610.1	1607.1	1602.7	1598.3	1593.9	1589.5	1590.6
20°	1586.1	1584.6	1583.1	1581.4	1579.9	1576.8	1572.2	1567.5	1562.9	1558.2	1559.1
22.5°	1553.8	1551.7	1549.6	1547.6	1545.6	1542.2	1537.5	1532.9	1528.2	1523.6	1525.3
25°	1501.0	1498.8	1496.6	1494.4	1492.3	1489.0	1484.7	1480.4	1476.0	1471.7	1472.0
27.5°	1440.7	1438.5	1436.1	1433.9	1431.7	1428.6	1424.5	1420.5	1416.4	1412.4	1411.7
30°	1400.5	1398.0	1395.4	1393.0	1390.5	1387.3	1383.2	1379.2	1375.1	1371.1	1369.9
32.5°	1358.0	1355.7	1353.5	1351.3	1349.1	1345.7	1341.5	1337.3	1332.9	1328.7	1327.2
35°	1291.5	1289.4	1287.2	1285.1	1282.8	1279.6	1275.3	1270.9	1266.6	1262.2	1260.0
37.5°	1221.4	1219.4	1217.5	1215.5	1213.5	1210.2	1205.5	1200.8	1196.2	1191.5	1189.2
40°	1175.7	1173.2	1170.6	1168.2	1165.7	1162.2	1157.5	1152.9	1148.2	1143.6	1140.4
42.5°	1126.5	1125.0	1123.5	1122.1	1120.5	1117.2	1112.1	1106.9	1101.8	1096.6	1093.0
45°	1054.2	1052.0	1049.9	1047.6	1045.5	1041.9	1036.9	1032.0	1027.0	1022.1	1018.7
47.5°	978.5	977.0	975.5	974.0	972.5	969.5	964.9	960.3	955.7	951.1	947.3
50°	927.2	925.8	924.6	923.4	922.1	919.4	915.0	910.7	906.4	902.0	897.7
52.5°	876.9	875.4	873.8	872.4	870.9	867.9	863.2	858.7	854.0	849.5	845.7
55°	797.3	796.3	795.4	794.5	793.6	790.9	786.6	782.2	777.9	773.6	769.8
57.5°	721.3	720.2	719.2	718.1	717.1	714.4	710.1	705.9	701.6	697.3	693.8
60°	668.8	667.2	665.7	664.2	662.6	659.8	655.8	651.8	647.7	643.7	640.9
62.5°	617.4	616.1	614.8	613.5	612.2	609.5	605.1	600.9	596.5	592.3	589.8
65°	540.4	538.8	537.2	535.7	534.1	531.8	528.7	525.6	522.5	519.4	516.3
67.5°	462.7	461.3	459.9	458.5	457.0	454.8	451.8	448.9	445.9	442.9	439.9
70°	414.7	412.5	410.3	408.2	406.0	403.6	401.2	398.7	396.3	393.7	391.2
72.5°	363.3	361.1	359.0	356.8	354.7	352.5	350.5	348.6	346.6	344.6	342.6
75°	287.6	286.1	284.5	283.0	281.4	279.8	278.3	276.8	275.2	273.7	272.5
77.5°	215.3	214.6	213.9	213.3	212.6	211.6	210.2	208.8	207.4	206.1	205.7
80°	171.8	170.8	169.9	169.0	168.0	167.2	166.6	166.0	165.4	164.7	164.1
82.5°	129.3	128.9	128.5	127.9	127.5	127.2	127.1	127.0	126.9	126.7	126.4
85°	75.4	75.4	75.4	75.4	75.4	75.1	74.4	73.8	73.2	72.6	72.6
87.5°	29.7	29.9	30.1	30.4	30.6	30.8	30.9	31.0	31.1	31.2	31.5
90°	3.0	5.5	8.0	10.4	12.9	15.0	16.8	18.6	20.4	22.2	23.5
92.5°	12.7	12.8	12.9	13.1	13.2	14.2	16.0	17.8	19.6	21.4	22.7
95°	55.4	47.9	40.2	32.6	24.9	21.3	21.5	21.7	21.9	22.2	23.5
97.5°	117.8	122.5	127.2	132.0	136.7	126.6	101.6	76.6	51.6	26.7	26.8
100°	165.3	169.4	173.4	177.4	181.5	168.0	137.1	106.2	75.2	44.3	40.6
102.5°	218.5	221.6	224.5	227.4	230.4	229.8	225.8	221.8	217.7	213.7	172.6
105°	303.5	304.8	306.1	307.5	308.8	310.0	311.1	312.3	313.5	314.6	316.6
107.5°	382.2	382.9	383.6	384.3	385.0	386.1	387.6	389.1	390.6	392.1	393.1
110°	435.6	436.2	436.9	437.5	438.2	439.2	440.5	441.9	443.2	444.5	445.0



TEST NUMBER: P332658-840

CATALOG NUMBER: SA4XXDIP-C1020D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.2	488.4	489.6	490.8	492.0	492.9	493.5	494.1	494.7	495.3	495.3
115°	566.5	567.2	567.9	568.6	569.3	569.5	569.3	569.1	568.8	568.6	569.1
117.5°	638.1	639.0	640.0	640.9	641.8	642.4	642.9	643.4	643.9	644.4	644.3
120°	686.5	687.4	688.3	689.2	690.1	690.4	690.2	690.0	689.7	689.5	690.0
122.5°	731.6	732.3	732.8	733.3	733.9	734.3	734.6	734.9	735.2	735.5	735.8
125°	796.4	797.3	798.2	799.1	800.0	800.2	799.8	799.3	798.9	798.4	799.1
127.5°	857.7	857.9	858.2	858.4	858.6	859.2	860.3	861.3	862.3	863.3	863.2
130°	897.3	897.5	897.7	897.9	898.1	898.6	899.3	899.9	900.6	901.3	901.5
132.5°	933.5	933.9	934.3	934.7	935.1	935.7	936.6	937.5	938.3	939.2	939.4
135°	988.0	987.7	987.5	987.2	987.0	987.3	988.3	989.2	990.1	991.0	991.4
137.5°	1036.1	1036.2	1036.3	1036.4	1036.5	1037.0	1038.0	1039.1	1040.0	1041.0	1041.5
140°	1067.6	1068.0	1068.5	1068.9	1069.3	1069.9	1070.3	1070.8	1071.2	1071.7	1072.3
142.5°	1095.8	1096.6	1097.4	1098.2	1099.0	1099.5	1099.8	1100.1	1100.3	1100.7	1101.2
145°	1139.1	1139.8	1140.5	1141.1	1141.9	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5
147.5°	1173.7	1174.9	1176.2	1177.4	1178.7	1179.2	1178.9	1178.7	1178.5	1178.3	1178.5
150°	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5	1202.3	1202.1	1201.9	1201.6	1201.6
152.5°	1219.6	1220.3	1221.0	1221.7	1222.4	1222.6	1222.2	1221.8	1221.4	1221.0	1221.4
155°	1249.1	1249.3	1249.5	1249.7	1249.9	1249.7	1249.1	1248.4	1247.7	1247.1	1247.9
157.5°	1273.8	1273.7	1273.5	1273.4	1273.3	1272.8	1272.1	1271.3	1270.6	1269.8	1271.0
160°	1288.4	1287.7	1287.1	1286.4	1285.7	1285.3	1285.1	1284.8	1284.5	1284.3	1285.7
162.5°	1301.3	1300.4	1299.6	1298.7	1297.9	1297.4	1297.1	1296.9	1296.7	1296.5	1297.8
165°	1317.6	1316.5	1315.3	1314.2	1313.1	1312.5	1312.5	1312.5	1312.5	1312.5	1314.3
167.5°	1330.5	1329.4	1328.2	1327.1	1325.9	1325.2	1325.0	1324.9	1324.8	1324.6	1326.7
170°	1337.8	1336.5	1335.0	1333.7	1332.4	1331.8	1332.0	1332.3	1332.5	1332.7	1334.5
172.5°	1342.6	1341.3	1339.9	1338.6	1337.3	1336.7	1336.9	1337.2	1337.4	1337.6	1339.4
175°	1347.9	1346.6	1345.1	1343.8	1342.5	1341.9	1342.1	1342.4	1342.6	1342.8	1344.8
177.5°	1350.3	1349.0	1347.8	1346.6	1345.2	1344.8	1345.1	1345.5	1345.8	1346.3	1347.7
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332658-840

CATALOG NUMBER: SA4XXDIP-C1020D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1736.3	1738.8	1741.3	1742.4	1742.1	1741.9	1741.6	1741.4
5°	1727.0	1730.4	1733.8	1735.3	1734.6	1733.9	1733.3	1732.7
7.5°	1707.8	1710.5	1713.2	1714.4	1714.0	1713.6	1713.2	1712.9
10°	1691.6	1694.1	1696.6	1697.5	1696.9	1696.3	1695.7	1695.1
12.5°	1672.0	1674.8	1677.5	1678.4	1677.6	1676.7	1675.8	1675.0
15°	1634.6	1636.4	1638.3	1638.7	1637.8	1636.9	1636.0	1635.0
17.5°	1591.9	1593.1	1594.2	1594.5	1593.9	1593.3	1592.7	1592.0
20°	1560.0	1561.0	1562.0	1562.1	1561.5	1560.8	1560.2	1559.6
22.5°	1526.9	1528.6	1530.2	1530.6	1529.4	1528.3	1527.2	1526.1
25°	1472.3	1472.6	1472.9	1472.4	1471.2	1470.0	1468.6	1467.4
27.5°	1411.0	1410.2	1409.5	1408.4	1406.7	1405.2	1403.6	1402.1
30°	1368.7	1367.4	1366.1	1364.7	1363.2	1361.6	1360.1	1358.6
32.5°	1325.6	1324.2	1322.7	1321.2	1319.6	1318.1	1316.6	1314.9
35°	1257.9	1255.7	1253.5	1251.6	1250.1	1248.6	1247.0	1245.5
37.5°	1186.8	1184.5	1182.1	1179.9	1177.9	1175.8	1173.8	1171.7
40°	1137.3	1134.2	1131.1	1128.8	1127.2	1125.7	1124.2	1122.6
42.5°	1089.4	1085.8	1082.2	1079.8	1078.8	1077.7	1076.7	1075.7
45°	1015.2	1011.8	1008.4	1006.2	1005.3	1004.4	1003.4	1002.5
47.5°	943.4	939.6	935.7	932.6	930.3	927.9	925.5	923.2
50°	893.3	889.0	884.6	881.5	879.6	877.8	876.0	874.0
52.5°	841.8	837.9	834.0	831.0	828.6	826.3	823.9	821.5
55°	766.1	762.3	758.6	755.9	754.0	752.1	750.2	748.4
57.5°	690.2	686.7	683.2	680.4	678.6	676.9	675.1	673.3
60°	638.1	635.3	632.5	630.4	628.7	627.2	625.7	624.1
62.5°	587.2	584.6	582.1	580.1	578.6	576.9	575.4	573.9
65°	513.2	510.1	507.0	504.6	503.1	501.6	500.0	498.5
67.5°	437.0	433.9	431.0	429.3	428.8	428.4	428.0	427.6
70°	388.8	386.3	383.8	382.1	381.2	380.2	379.3	378.4
72.5°	340.6	338.6	336.7	335.2	334.3	333.4	332.4	331.4
75°	271.1	269.9	268.7	267.9	267.6	267.3	267.0	266.7
77.5°	205.3	205.0	204.6	204.0	203.2	202.4	201.6	200.8
80°	163.5	162.9	162.3	161.8	161.5	161.2	160.9	160.6
82.5°	126.0	125.6	125.3	124.9	124.6	124.3	124.0	123.7
85°	72.6	72.6	72.6	72.4	72.1	71.8	71.5	71.2
87.5°	31.8	32.0	32.3	32.5	32.6	32.7	32.7	32.8
90°	24.8	26.3	27.6	28.5	28.9	29.4	29.8	30.2
92.5°	24.0	25.4	26.8	27.5	27.6	27.7	27.8	27.9
95°	24.8	26.3	27.6	28.4	28.6	28.8	29.0	29.2
97.5°	26.9	27.1	27.2	27.4	27.6	27.8	28.0	28.3
100°	36.8	32.9	29.1	27.4	27.6	27.8	28.0	28.3
102.5°	131.6	90.5	49.4	28.9	28.9	29.0	29.0	29.1
105°	318.6	320.5	322.6	319.6	311.5	303.5	295.4	287.3
107.5°	394.2	395.2	396.1	397.0	397.9	398.7	399.6	400.4
110°	445.5	446.0	446.4	447.0	447.6	448.3	449.0	449.6





TEST NUMBER: P332658-840

CATALOG NUMBER: SA4XXDIP-C1020D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	495.2	495.1	495.0	495.4	496.2	497.2	498.0	498.8
115°	569.5	570.0	570.4	570.6	570.6	570.6	570.6	570.6
117.5°	644.2	644.1	644.0	644.0	643.9	643.8	643.7	643.6
120°	690.4	690.8	691.4	691.4	690.8	690.4	690.0	689.5
122.5°	736.1	736.3	736.6	736.5	736.1	735.6	735.2	734.7
125°	799.8	800.4	801.1	801.5	801.8	802.0	802.2	802.4
127.5°	863.1	862.9	862.8	862.6	862.5	862.3	862.1	861.9
130°	901.7	901.9	902.1	902.3	902.3	902.3	902.3	902.3
132.5°	939.6	939.9	940.1	940.1	939.9	939.7	939.6	939.4
135°	991.9	992.3	992.8	993.2	993.7	994.1	994.5	995.0
137.5°	1042.0	1042.5	1043.0	1043.1	1043.0	1042.9	1042.7	1042.6
140°	1073.0	1073.7	1074.3	1074.8	1075.0	1075.2	1075.4	1075.7
142.5°	1101.7	1102.2	1102.7	1102.9	1103.0	1103.0	1103.1	1103.1
145°	1142.7	1142.9	1143.1	1143.5	1143.9	1144.3	1144.8	1145.2
147.5°	1178.6	1178.8	1179.0	1179.2	1179.4	1179.6	1179.9	1180.1
150°	1201.6	1201.6	1201.6	1201.7	1202.0	1202.2	1202.4	1202.6
152.5°	1221.7	1222.1	1222.4	1222.5	1222.4	1222.3	1222.1	1222.0
155°	1248.8	1249.7	1250.6	1250.7	1250.1	1249.4	1248.7	1248.1
157.5°	1272.1	1273.3	1274.4	1274.4	1273.3	1272.1	1271.0	1269.8
160°	1287.1	1288.4	1289.7	1289.7	1288.4	1287.1	1285.7	1284.3
162.5°	1299.1	1300.5	1301.8	1301.7	1300.2	1298.7	1297.2	1295.7
165°	1316.2	1318.0	1319.7	1319.6	1317.6	1315.6	1313.5	1311.5
167.5°	1328.6	1330.6	1332.5	1332.4	1330.2	1328.0	1325.6	1323.4
170°	1336.4	1338.1	1339.9	1339.7	1337.5	1335.2	1332.9	1330.7
172.5°	1341.2	1342.9	1344.7	1344.4	1342.0	1339.6	1337.2	1334.7
175°	1346.9	1348.9	1350.9	1350.5	1347.9	1345.1	1342.5	1339.8
177.5°	1349.1	1350.5	1352.0	1351.6	1349.5	1347.4	1345.1	1343.0
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9

(END OF REPORT)