

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332559-830

Luminaire Tested: **SA4XXDIP-C575D810U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332559-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D810U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5399.7 lumens
Efficiency: N/A
Efficacy: 140.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332559-830
CATALOG NUMBER: SA4XXDIP-C575D810U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332559-830

CATALOG NUMBER: SA4XXDIP-C575D810U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	67	65	57	55	53	44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36	31
3	80	71	63	58	73	65	58	53	54	49	45	44	41	38	35	32	30	26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17
7	57	45	37	32	52	41	34	29	35	29	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	17	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7389	7389	7389
5°	7412	7323	7376
10°	7365	7263	7299
15°	7276	7160	7178
20°	7158	7032	7039
25°	7023	6886	6866
30°	6858	6715	6652
35°	6686	6535	6447
40°	6509	6330	6215
45°	6322	6130	6012
50°	6116	5951	5766
55°	5895	5719	5533
60°	5672	5459	5293
65°	5421	5213	5001
70°	5141	4881	4692
75°	4713	4482	4370
80°	4193	4021	3924
85°	3668	3538	3464



TEST NUMBER: P332559-830

CATALOG NUMBER: SA4XXDIP-C575D810U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	1.6
10°-20°	242.9	4.5
20°-30°	357.5	6.6
30°-40°	415.6	7.7
40°-50°	415.6	7.7
50°-60°	363.5	6.7
60°-70°	270.0	5.0
70°-80°	153.4	2.8
80°-90°	47.1	0.9
90°-100°	33.7	0.6
100°-110°	214.9	4.0
110°-120°	411.0	7.6
120°-130°	521.8	9.7
130°-140°	558.3	10.3
140°-150°	522.1	9.7
150°-160°	421.0	7.8
160°-170°	271.5	5.0
170°-180°	93.6	1.7
0°-30°	686.6	12.7
0°-40°	1102.1	20.4
0°-60°	1881.3	34.8
0°-90°	2351.8	43.6
90°-120°	659.6	12.2
90°-150°	2261.8	41.9
90°-180°	3048.0	56.4
0°-180°	5399.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	915	915	915	915	915	
5°	915	911	904	911	910	87
15°	871	867	857	861	859	245
25°	788	783	773	774	771	363
35°	678	673	663	658	654	424
45°	554	548	537	529	527	427
55°	419	416	406	398	393	375
65°	284	280	273	266	262	281
75°	151	147	144	141	140	161
85°	40	40	38	38	37	44
90°	2	10	16	20	22	4
95°	40	17	16	20	21	52
105°	222	226	230	235	210	232
115°	414	416	416	417	417	407
125°	582	585	584	586	587	520
135°	722	722	724	726	727	556
145°	833	835	835	836	837	520
155°	913	914	912	914	912	421
165°	963	960	960	965	959	272
175°	985	981	982	987	979	94
180°	985	985	985	985	985	



TEST NUMBER: P332559-830
 CATALOG NUMBER: SA4XXDIP-C575D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	917.7	917.3	916.9	916.5	916.2	915.2	913.8	912.4	910.9	909.5	910.8
5°	914.6	914.0	913.3	912.7	912.0	910.8	909.0	907.2	905.4	903.6	905.4
7.5°	906.1	905.4	904.8	904.2	903.5	902.2	900.2	898.2	896.2	894.2	895.7
10°	898.4	897.9	897.2	896.5	895.9	894.5	892.4	890.2	888.2	886.0	887.3
12.5°	888.5	887.9	887.2	886.6	885.9	884.5	882.2	880.0	877.7	875.4	876.8
15°	870.6	870.0	869.3	868.6	868.0	866.5	864.0	861.6	859.1	856.7	857.6
17.5°	849.0	848.2	847.4	846.6	845.7	844.2	841.9	839.6	837.3	835.0	835.6
20°	833.2	832.4	831.6	830.8	829.9	828.3	825.9	823.4	821.0	818.5	819.0
22.5°	816.1	815.1	814.1	812.9	811.9	810.1	807.7	805.2	802.8	800.3	801.3
25°	788.4	787.3	786.2	785.0	783.9	782.2	779.9	777.6	775.3	773.1	773.3
27.5°	756.8	755.6	754.4	753.3	752.1	750.5	748.3	746.2	744.0	742.0	741.6
30°	735.7	734.3	733.0	731.7	730.5	728.7	726.6	724.4	722.4	720.3	719.6
32.5°	713.3	712.2	711.0	709.8	708.7	706.9	704.7	702.5	700.2	698.0	697.2
35°	678.4	677.3	676.2	675.0	673.9	672.1	669.9	667.6	665.3	663.1	661.9
37.5°	641.6	640.6	639.5	638.5	637.4	635.7	633.3	630.8	628.4	625.9	624.7
40°	617.6	616.2	614.9	613.7	612.4	610.5	608.0	605.6	603.1	600.7	599.1
42.5°	591.7	591.0	590.2	589.4	588.6	586.8	584.2	581.5	578.7	576.1	574.2
45°	553.7	552.6	551.5	550.4	549.2	547.3	544.7	542.1	539.5	536.9	535.1
47.5°	514.0	513.2	512.5	511.6	510.9	509.3	506.9	504.4	502.0	499.6	497.6
50°	487.0	486.4	485.7	485.0	484.4	483.0	480.7	478.3	476.1	473.8	471.6
52.5°	460.6	459.9	459.0	458.3	457.5	455.9	453.5	451.1	448.7	446.2	444.2
55°	418.8	418.3	417.8	417.4	416.9	415.5	413.2	410.9	408.6	406.3	404.4
57.5°	378.9	378.3	377.8	377.2	376.6	375.3	373.1	370.8	368.5	366.3	364.4
60°	351.3	350.5	349.7	348.8	348.1	346.6	344.5	342.3	340.3	338.1	336.7
62.5°	324.3	323.7	322.9	322.3	321.6	320.1	317.9	315.7	313.4	311.1	309.8
65°	283.8	283.0	282.2	281.4	280.6	279.4	277.8	276.1	274.5	272.9	271.2
67.5°	243.1	242.3	241.6	240.8	240.1	238.9	237.3	235.8	234.2	232.6	231.1
70°	217.8	216.7	215.6	214.4	213.3	212.1	210.8	209.4	208.1	206.8	205.6
72.5°	190.9	189.7	188.6	187.4	186.2	185.2	184.2	183.1	182.1	181.0	179.9
75°	151.1	150.2	149.5	148.6	147.8	147.0	146.2	145.3	144.6	143.7	143.1
77.5°	113.1	112.7	112.4	112.1	111.7	111.1	110.4	109.7	109.0	108.3	108.0
80°	90.2	89.7	89.3	88.8	88.2	87.8	87.6	87.2	86.9	86.5	86.2
82.5°	68.0	67.7	67.5	67.2	67.0	66.8	66.8	66.7	66.6	66.6	66.4
85°	39.6	39.6	39.6	39.6	39.6	39.4	39.1	38.8	38.5	38.2	38.2
87.5°	15.7	15.9	16.1	16.4	16.6	16.8	17.0	17.1	17.2	17.3	17.5
90°	2.2	4.1	5.8	7.6	9.4	10.9	12.3	13.6	14.9	16.2	17.2
92.5°	9.3	9.4	9.5	9.6	9.7	10.4	11.7	13.0	14.3	15.6	16.6
95°	40.5	35.0	29.4	23.8	18.3	15.6	15.7	15.9	16.0	16.2	17.2
97.5°	86.1	89.5	93.0	96.5	100.0	92.6	74.3	56.0	37.7	19.4	19.5
100°	120.8	123.9	126.8	129.7	132.6	122.8	100.2	77.7	55.0	32.4	29.6
102.5°	159.8	161.9	164.1	166.3	168.4	168.1	165.0	162.1	159.2	156.3	126.2
105°	221.8	222.8	223.8	224.8	225.7	226.7	227.4	228.3	229.1	229.9	231.4
107.5°	279.5	279.9	280.4	281.0	281.4	282.2	283.3	284.5	285.6	286.7	287.4
110°	318.4	318.9	319.3	319.8	320.4	321.0	322.1	323.0	324.0	325.0	325.4



TEST NUMBER: P332559-830

CATALOG NUMBER: SA4XXDIP-C575D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.1	356.9	357.9	358.7	359.7	360.3	360.8	361.2	361.7	362.1	362.1
115°	414.2	414.6	415.2	415.7	416.1	416.3	416.1	415.9	415.8	415.7	415.9
117.5°	466.5	467.1	467.8	468.4	469.1	469.7	470.0	470.3	470.7	471.1	471.0
120°	501.9	502.6	503.2	503.9	504.4	504.7	504.5	504.4	504.3	504.1	504.4
122.5°	534.9	535.3	535.6	536.0	536.5	536.8	537.0	537.2	537.4	537.7	537.9
125°	582.2	582.9	583.5	584.2	584.8	584.9	584.7	584.4	584.0	583.7	584.2
127.5°	627.0	627.2	627.4	627.5	627.6	628.1	628.9	629.6	630.4	631.1	631.0
130°	655.9	656.1	656.2	656.4	656.6	656.9	657.3	657.9	658.4	658.8	659.0
132.5°	682.4	682.7	683.1	683.3	683.6	684.1	684.7	685.3	685.9	686.5	686.7
135°	722.3	722.1	721.9	721.7	721.6	721.8	722.5	723.1	723.8	724.4	724.7
137.5°	757.4	757.5	757.6	757.6	757.7	758.1	758.8	759.6	760.3	761.0	761.4
140°	780.4	780.8	781.1	781.5	781.7	782.1	782.4	782.8	783.1	783.3	783.9
142.5°	801.1	801.6	802.3	802.9	803.4	803.8	804.0	804.3	804.5	804.6	805.0
145°	832.7	833.3	833.8	834.2	834.7	835.0	835.0	835.0	835.0	835.0	835.2
147.5°	858.0	858.9	859.8	860.7	861.7	862.0	861.9	861.7	861.5	861.4	861.5
150°	876.3	876.9	877.6	878.3	878.8	879.1	878.9	878.8	878.6	878.4	878.4
152.5°	891.6	892.1	892.6	893.2	893.7	893.8	893.5	893.2	892.9	892.6	892.9
155°	913.1	913.2	913.4	913.6	913.8	913.6	913.1	912.6	912.1	911.6	912.3
157.5°	931.2	931.1	931.0	930.9	930.9	930.5	929.9	929.4	928.9	928.3	929.2
160°	941.9	941.3	940.8	940.4	939.9	939.5	939.4	939.2	939.1	938.9	939.9
162.5°	951.3	950.6	950.0	949.4	948.8	948.4	948.2	948.1	947.9	947.7	948.8
165°	963.2	962.4	961.6	960.7	960.0	959.5	959.5	959.5	959.5	959.5	960.8
167.5°	972.6	971.8	970.9	970.1	969.2	968.7	968.7	968.6	968.5	968.4	969.8
170°	978.0	976.9	976.0	975.0	974.0	973.6	973.7	973.9	974.1	974.3	975.5
172.5°	981.5	980.5	979.5	978.5	977.6	977.1	977.3	977.5	977.6	977.8	979.1
175°	985.3	984.3	983.4	982.4	981.4	981.0	981.2	981.3	981.5	981.7	983.1
177.5°	987.1	986.2	985.2	984.3	983.4	983.1	983.4	983.6	983.9	984.1	985.1
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3



TEST NUMBER: P332559-830

CATALOG NUMBER: SA4XXDIP-C575D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	912.1	913.4	914.7	915.3	915.1	915.0	914.9	914.7
5°	907.2	909.0	910.8	911.5	911.2	910.9	910.5	910.2
7.5°	897.1	898.5	899.9	900.6	900.4	900.2	900.0	899.8
10°	888.6	889.9	891.3	891.7	891.4	891.1	890.7	890.4
12.5°	878.4	879.8	881.2	881.7	881.2	880.7	880.3	879.9
15°	858.7	859.6	860.5	860.8	860.4	859.9	859.3	858.8
17.5°	836.2	836.8	837.4	837.5	837.3	836.9	836.6	836.3
20°	819.5	820.0	820.5	820.6	820.2	819.9	819.6	819.3
22.5°	802.1	803.0	803.9	804.0	803.4	802.9	802.3	801.6
25°	773.4	773.5	773.7	773.5	772.8	772.1	771.5	770.8
27.5°	741.2	740.7	740.4	739.8	739.0	738.2	737.4	736.5
30°	719.0	718.3	717.7	716.9	716.0	715.3	714.4	713.6
32.5°	696.4	695.6	694.8	694.0	693.2	692.4	691.5	690.8
35°	660.7	659.6	658.5	657.5	656.7	655.8	655.1	654.2
37.5°	623.5	622.2	620.9	619.8	618.8	617.6	616.6	615.5
40°	597.5	595.8	594.2	593.0	592.1	591.4	590.5	589.7
42.5°	572.3	570.3	568.4	567.2	566.8	566.2	565.6	565.1
45°	533.3	531.5	529.7	528.6	528.1	527.6	527.1	526.6
47.5°	495.6	493.5	491.5	489.9	488.7	487.4	486.2	484.9
50°	469.2	466.9	464.7	463.1	462.0	461.1	460.1	459.1
52.5°	442.1	440.2	438.2	436.5	435.3	434.0	432.8	431.6
55°	402.5	400.5	398.5	397.0	396.1	395.1	394.1	393.1
57.5°	362.6	360.7	358.8	357.4	356.5	355.5	354.6	353.6
60°	335.2	333.8	332.2	331.1	330.3	329.5	328.7	327.8
62.5°	308.5	307.1	305.8	304.7	303.9	303.1	302.3	301.4
65°	269.6	268.0	266.4	265.1	264.3	263.4	262.7	261.8
67.5°	229.5	228.0	226.4	225.5	225.3	225.1	224.8	224.6
70°	204.2	202.9	201.6	200.8	200.2	199.7	199.3	198.8
72.5°	178.9	177.9	176.8	176.1	175.6	175.1	174.7	174.1
75°	142.4	141.8	141.2	140.7	140.5	140.4	140.3	140.1
77.5°	107.8	107.6	107.4	107.2	106.7	106.3	105.8	105.5
80°	85.9	85.6	85.2	85.0	84.8	84.6	84.5	84.4
82.5°	66.2	66.0	65.8	65.6	65.5	65.3	65.1	64.9
85°	38.2	38.2	38.2	38.1	37.9	37.7	37.6	37.4
87.5°	17.7	17.9	18.1	18.3	18.3	18.4	18.5	18.5
90°	18.2	19.1	20.2	20.8	21.1	21.5	21.8	22.1
92.5°	17.6	18.6	19.5	20.1	20.2	20.2	20.3	20.4
95°	18.2	19.1	20.2	20.7	20.9	21.0	21.2	21.4
97.5°	19.7	19.8	19.9	20.0	20.2	20.3	20.5	20.6
100°	26.9	24.0	21.3	20.0	20.2	20.3	20.5	20.6
102.5°	96.1	66.2	36.1	21.1	21.1	21.1	21.2	21.2
105°	232.9	234.3	235.8	233.7	227.7	221.8	215.9	210.0
107.5°	288.1	288.8	289.5	290.2	290.9	291.4	292.1	292.8
110°	325.6	326.0	326.3	326.7	327.3	327.7	328.2	328.7



TEST NUMBER: P332559-830

CATALOG NUMBER: SA4XXDIP-C575D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	362.0	361.9	361.8	362.1	362.8	363.4	364.0	364.7
115°	416.3	416.6	417.0	417.2	417.2	417.2	417.2	417.2
117.5°	470.9	470.9	470.8	470.7	470.7	470.6	470.5	470.5
120°	504.7	505.1	505.4	505.4	505.1	504.7	504.4	504.1
122.5°	538.1	538.3	538.5	538.4	538.1	537.7	537.4	537.1
125°	584.7	585.1	585.6	586.0	586.2	586.3	586.4	586.6
127.5°	630.9	630.8	630.7	630.7	630.5	630.4	630.3	630.1
130°	659.2	659.3	659.5	659.6	659.6	659.6	659.6	659.6
132.5°	686.9	687.0	687.2	687.2	687.1	686.9	686.8	686.7
135°	725.1	725.4	725.8	726.0	726.4	726.7	727.1	727.4
137.5°	761.7	762.0	762.4	762.5	762.4	762.3	762.2	762.1
140°	784.4	784.9	785.3	785.7	785.9	786.0	786.2	786.4
142.5°	805.3	805.7	806.1	806.3	806.3	806.3	806.3	806.3
145°	835.3	835.5	835.7	835.8	836.2	836.5	836.9	837.2
147.5°	861.7	861.8	861.9	862.0	862.2	862.3	862.5	862.7
150°	878.4	878.4	878.4	878.5	878.7	878.8	879.0	879.2
152.5°	893.2	893.4	893.6	893.7	893.6	893.5	893.4	893.3
155°	912.9	913.6	914.3	914.4	913.8	913.3	912.9	912.4
157.5°	930.0	930.9	931.7	931.7	930.9	930.0	929.2	928.3
160°	940.8	941.9	942.8	942.8	941.9	940.8	939.9	938.9
162.5°	949.7	950.6	951.7	951.6	950.5	949.3	948.3	947.2
165°	962.1	963.5	964.8	964.7	963.2	961.8	960.3	958.8
167.5°	971.3	972.7	974.1	974.0	972.4	970.7	969.1	967.5
170°	976.9	978.2	979.5	979.3	977.7	976.1	974.4	972.8
172.5°	980.4	981.8	983.1	982.8	981.1	979.3	977.5	975.7
175°	984.6	986.1	987.5	987.3	985.3	983.4	981.4	979.4
177.5°	986.3	987.3	988.4	988.1	986.5	985.0	983.4	981.8
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3

(END OF REPORT)