

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332608-830

Luminaire Tested: **SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332608-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6717.2 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332608-830
CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	86	90	87	83	80	73	71	69	61	59	58	50	49	48	42				
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36				
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35	31				
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	32	30	26				
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23				
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	20				
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18				
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16				
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15				
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9769	9769	9769	9769
5°	11505	9794	8645	9794
10°	13774	9752	7783	9752
15°	16298	9653	7148	9653
20°	18148	9552	6580	9552
25°	18441	9404	6188	9404
30°	15691	9261	6065	9261
35°	12064	9030	6067	9030
40°	9403	8759	6181	8759
45°	7840	8350	6284	8350
50°	6900	7851	6498	7851
55°	6321	7253	6759	7253
60°	5924	6717	7074	6717
65°	5515	6118	7335	6118
70°	5042	5526	7501	5526
75°	4504	4863	7411	4863
80°	3775	3984	7178	3984
85°	2788	2881	6873	2881



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.9	1.8
10°-20°	363.4	5.4
20°-30°	576.2	8.6
30°-40°	641.2	9.5
40°-50°	583.7	8.7
50°-60°	477.0	7.1
60°-70°	340.5	5.1
70°-80°	187.5	2.8
80°-90°	54.8	0.8
90°-100°	80.2	1.2
100°-110°	237.7	3.5
110°-120°	403.4	6.0
120°-130°	531.9	7.9
130°-140°	597.4	8.9
140°-150°	587.0	8.7
150°-160°	493.7	7.4
160°-170°	328.5	4.9
170°-180°	115.0	1.7
0°-30°	1057.5	15.7
0°-40°	1698.7	25.3
0°-60°	2759.4	41.1
0°-90°	3342.3	49.8
90°-120°	721.3	10.7
90°-150°	2437.7	36.3
90°-180°	3375.0	50.2
0°-180°	6717.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1210	1210	1210	1210	1210	
5°	1420	1209	1067	1209	1420	144
15°	1950	1155	855	1155	1950	551
25°	2070	1056	695	1056	2070	913
35°	1224	916	616	916	1224	777
45°	687	731	550	731	687	541
55°	449	515	480	515	449	406
65°	289	320	384	320	289	286
75°	144	156	238	156	144	154
85°	30	31	74	31	30	37
90°	28	3	28	3	28	15
95°	74	56	74	56	74	77
105°	230	219	230	219	230	242
115°	406	410	406	410	406	402
125°	593	597	593	597	593	529
135°	772	770	772	770	772	596
145°	937	936	937	936	937	586
155°	1072	1072	1072	1072	1072	493
165°	1165	1168	1165	1168	1165	328
175°	1209	1215	1209	1215	1209	115
180°	1216	1216	1216	1216	1216	



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1287.9	1287.5	1283.5	1282.7	1279.9	1276.3	1275.4	1269.0	1256.2	1250.2	1248.6
5°	1419.7	1429.6	1416.6	1414.1	1412.6	1396.1	1387.5	1377.5	1354.4	1341.0	1330.4
7.5°	1576.9	1578.0	1572.3	1567.7	1555.0	1540.5	1518.9	1495.8	1468.4	1439.7	1418.2
10°	1680.3	1684.3	1677.8	1676.8	1651.2	1635.2	1603.1	1576.0	1544.9	1510.3	1478.8
12.5°	1789.4	1783.8	1780.5	1759.0	1754.3	1725.0	1687.7	1659.8	1611.9	1572.2	1530.1
15°	1950.0	1939.0	1931.9	1902.3	1887.8	1847.2	1807.6	1777.1	1714.4	1654.7	1609.6
17.5°	2044.2	2055.2	2039.0	2026.8	1989.2	1960.8	1920.3	1856.1	1807.1	1733.1	1676.1
20°	2112.4	2113.4	2104.4	2091.9	2062.3	2026.2	1982.1	1911.9	1853.2	1779.5	1701.4
22.5°	2130.8	2131.1	2127.2	2115.5	2093.1	2063.9	2019.4	1960.8	1889.7	1809.6	1731.5
25°	2070.3	2068.3	2072.8	2085.8	2077.3	2068.3	2042.7	1999.1	1933.0	1848.2	1764.0
27.5°	1845.3	1859.2	1884.6	1916.7	1947.6	1971.1	1977.7	1968.8	1927.8	1858.1	1769.9
30°	1683.3	1700.3	1719.4	1751.4	1813.6	1849.3	1888.3	1917.9	1901.4	1845.7	1763.5
32.5°	1505.2	1509.5	1537.8	1574.2	1631.2	1699.7	1761.6	1821.7	1841.6	1812.4	1743.9
35°	1224.1	1231.1	1261.7	1297.8	1367.5	1451.2	1544.5	1627.7	1696.3	1723.9	1688.8
37.5°	998.9	1019.1	1040.7	1079.5	1140.9	1216.2	1313.1	1420.7	1523.1	1591.7	1603.3
40°	892.3	904.8	920.4	949.9	1002.0	1076.3	1159.4	1282.8	1391.6	1489.8	1521.9
42.5°	808.0	815.4	824.9	851.7	891.4	965.2	1041.1	1149.6	1258.9	1376.3	1430.0
45°	686.7	694.3	710.3	725.9	755.9	807.1	877.7	967.0	1076.8	1190.1	1289.3
47.5°	599.2	604.0	613.5	630.1	655.6	689.4	746.9	821.4	923.1	1033.1	1138.9
50°	549.4	553.4	560.9	576.0	595.5	625.6	672.7	742.4	822.1	932.9	1036.6
52.5°	510.1	511.7	517.3	527.4	543.0	568.3	606.9	664.6	738.7	837.4	940.8
55°	449.1	451.2	456.2	463.7	477.2	493.2	522.8	565.9	630.7	716.3	806.1
57.5°	399.0	400.4	404.6	407.6	418.7	431.7	454.5	485.2	534.2	606.9	687.0
60°	366.9	365.9	371.0	373.4	381.0	392.0	409.5	439.1	481.7	540.4	614.1
62.5°	335.6	334.2	338.5	341.8	346.1	355.5	369.9	393.0	427.6	480.6	544.3
65°	288.7	286.7	289.3	293.2	297.3	302.3	312.8	333.4	360.9	399.0	447.6
67.5°	241.6	243.7	244.1	246.1	248.5	255.2	262.5	277.0	296.4	327.0	368.2
70°	213.6	214.1	216.0	216.0	217.5	223.6	229.6	238.1	257.1	285.2	318.8
72.5°	185.5	187.6	186.8	188.4	189.5	193.5	197.9	206.0	222.3	243.1	271.5
75°	144.4	145.9	145.9	146.4	147.9	149.4	152.9	158.9	170.4	186.0	205.6
77.5°	105.3	105.5	106.1	108.0	108.0	110.4	113.0	117.8	123.5	134.1	146.1
80°	81.2	82.2	81.7	82.8	82.8	84.7	85.7	91.7	94.3	101.2	110.7
82.5°	59.6	60.5	60.4	61.8	62.7	63.1	64.5	66.8	69.4	75.6	79.5
85°	30.1	31.1	30.1	31.1	32.6	33.1	34.6	35.1	37.1	38.6	42.1
87.5°	14.4	15.6	15.5	15.8	16.5	16.8	17.0	16.3	17.6	17.8	19.0
90°	28.2	27.8	27.4	27.0	26.6	25.7	24.5	23.2	22.0	20.7	19.0
92.5°	41.8	41.6	41.3	41.0	40.8	40.2	39.5	38.7	38.0	37.2	36.1
95°	74.4	74.4	74.4	74.4	74.4	74.0	73.4	72.8	72.1	71.5	70.0
97.5°	116.5	116.5	116.5	116.5	116.5	116.1	115.4	114.6	113.9	113.1	111.4
100°	145.8	145.8	145.8	145.8	145.8	145.6	145.2	144.8	144.4	143.9	142.0
102.5°	178.9	178.8	178.6	178.4	178.2	177.9	177.3	176.7	176.2	175.6	173.8
105°	229.5	228.9	228.3	227.6	227.1	226.4	225.8	225.2	224.5	223.9	223.1
107.5°	278.8	278.9	278.9	279.0	279.0	278.7	278.1	277.6	277.0	276.4	276.3
110°	314.2	313.6	312.9	312.4	311.7	311.6	312.0	312.5	312.8	313.3	313.5



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	350.3	350.2	350.1	350.0	349.9	349.9	349.9	350.0	350.1	350.2	350.5
115°	406.4	406.6	406.8	407.1	407.3	407.5	407.6	407.8	408.1	408.3	408.7
117.5°	459.9	460.2	460.7	461.1	461.6	462.1	462.8	463.5	464.2	465.0	465.2
120°	500.5	500.1	499.6	499.3	498.8	499.2	500.2	501.2	502.3	503.3	504.0
122.5°	534.3	535.1	535.8	536.6	537.3	538.1	538.9	539.5	540.3	540.9	541.2
125°	592.7	593.1	593.5	594.0	594.4	594.7	595.2	595.6	596.1	596.4	596.6
127.5°	646.7	647.1	647.3	647.7	648.0	648.4	648.8	649.2	649.7	650.1	650.4
130°	682.0	682.9	683.7	684.6	685.4	686.1	686.5	686.9	687.3	687.7	687.7
132.5°	719.7	720.0	720.4	720.7	721.0	721.4	721.8	722.3	722.6	723.1	723.2
135°	771.5	772.0	772.7	773.4	773.9	774.5	774.9	775.3	775.7	776.2	776.2
137.5°	825.9	825.7	825.6	825.5	825.3	825.6	826.0	826.6	827.2	827.7	827.4
140°	858.9	859.1	859.3	859.6	859.8	860.0	860.2	860.4	860.6	860.8	860.8
142.5°	892.0	892.1	892.1	892.2	892.2	892.3	892.3	892.3	892.4	892.4	892.6
145°	937.0	937.6	938.3	938.9	939.5	939.9	940.2	940.4	940.6	940.8	940.6
147.5°	982.6	982.8	983.0	983.2	983.4	983.5	983.7	983.9	984.1	984.3	984.4
150°	1010.4	1010.6	1010.8	1011.1	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3
152.5°	1035.9	1036.5	1037.1	1037.6	1038.2	1038.2	1037.6	1037.2	1036.7	1036.1	1036.0
155°	1071.6	1072.4	1073.3	1074.0	1074.9	1074.9	1074.0	1073.3	1072.4	1071.6	1071.8
157.5°	1103.3	1104.1	1104.8	1105.5	1106.2	1106.3	1105.6	1104.9	1104.4	1103.7	1103.8
160°	1121.4	1122.5	1123.5	1124.5	1125.6	1125.8	1125.2	1124.5	1123.9	1123.3	1123.5
162.5°	1140.2	1141.3	1142.4	1143.4	1144.4	1144.3	1143.2	1142.1	1140.9	1139.8	1140.1
165°	1164.7	1165.5	1166.4	1167.2	1168.0	1167.8	1166.6	1165.4	1164.0	1162.8	1163.2
167.5°	1182.2	1183.5	1184.8	1186.1	1187.4	1187.4	1186.2	1184.9	1183.6	1182.4	1182.3
170°	1191.9	1193.4	1194.9	1196.4	1197.8	1198.0	1196.7	1195.4	1194.2	1192.9	1192.7
172.5°	1200.2	1201.7	1203.2	1204.7	1206.1	1206.2	1204.7	1203.2	1201.8	1200.4	1200.4
175°	1208.9	1210.4	1211.8	1213.3	1214.7	1214.7	1213.3	1211.8	1210.4	1208.9	1209.1
177.5°	1213.4	1214.7	1216.1	1217.5	1218.8	1218.9	1217.7	1216.5	1215.3	1214.2	1214.2
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1249.0	1243.4	1239.3	1236.1	1227.4	1222.1	1218.1	1212.5	1206.1	1199.3	1190.8
5°	1319.8	1302.8	1290.3	1271.2	1253.2	1238.1	1222.7	1208.6	1191.6	1173.0	1159.4
7.5°	1394.4	1369.0	1336.5	1308.3	1276.7	1249.1	1224.5	1199.2	1172.9	1147.5	1124.1
10°	1441.7	1409.1	1373.0	1330.4	1290.3	1254.7	1221.6	1189.6	1158.5	1127.4	1100.8
12.5°	1492.6	1452.0	1398.6	1348.9	1303.9	1256.3	1216.4	1177.1	1139.6	1106.9	1075.9
15°	1560.9	1502.3	1440.7	1374.0	1314.8	1259.2	1204.6	1155.0	1112.9	1069.7	1039.6
17.5°	1603.0	1530.4	1459.9	1390.3	1318.7	1248.5	1189.6	1132.3	1079.6	1036.7	998.8
20°	1630.7	1558.5	1470.7	1401.1	1315.9	1243.7	1175.5	1111.8	1056.7	1011.1	971.9
22.5°	1654.7	1571.3	1483.6	1391.9	1307.0	1230.5	1155.8	1091.7	1035.5	987.4	949.9
25°	1667.7	1572.0	1476.8	1385.5	1289.3	1198.5	1130.9	1055.7	995.5	944.9	904.8
27.5°	1669.1	1566.8	1459.1	1357.6	1258.3	1173.8	1088.4	1021.2	958.8	905.2	866.7
30°	1664.7	1558.0	1442.2	1332.4	1232.7	1140.9	1066.8	993.5	929.9	876.8	836.6
32.5°	1650.7	1539.5	1420.5	1304.3	1201.0	1111.3	1034.6	965.1	903.1	850.6	808.6
35°	1610.1	1500.3	1373.5	1252.7	1146.9	1056.2	987.0	916.3	854.2	804.6	763.9
37.5°	1546.6	1447.4	1318.4	1193.4	1089.6	998.4	929.9	866.0	809.9	759.5	717.9
40°	1491.3	1404.1	1274.8	1152.9	1040.7	953.9	889.8	831.1	775.5	727.8	688.2
42.5°	1427.6	1351.5	1232.3	1103.2	994.9	907.9	845.3	792.6	740.2	696.2	656.6
45°	1313.8	1263.8	1151.4	1032.2	919.4	837.2	777.5	731.4	687.3	644.1	611.1
47.5°	1183.1	1158.3	1063.8	950.5	843.4	762.3	710.6	668.0	629.3	592.9	563.6
50°	1095.3	1083.3	1001.5	892.3	790.0	713.8	661.7	625.1	592.0	560.0	532.3
52.5°	1008.7	1008.2	934.6	834.5	739.9	666.5	614.7	580.6	552.0	525.8	501.1
55°	876.3	890.2	832.6	743.4	658.6	592.5	545.9	515.3	495.3	473.7	455.2
57.5°	754.6	777.9	730.4	651.8	581.1	520.1	479.6	456.6	435.2	422.2	408.7
60°	675.2	697.3	660.2	594.0	527.4	475.2	436.6	416.0	397.5	388.5	379.0
62.5°	604.6	624.3	596.8	535.5	477.6	427.5	394.9	375.1	362.6	352.8	346.5
65°	503.8	520.3	496.8	452.1	402.6	362.4	335.8	320.3	308.3	304.3	297.3
67.5°	407.3	422.3	409.5	371.6	331.9	301.4	280.7	265.8	258.6	255.1	250.2
70°	349.9	365.0	351.4	318.3	287.8	262.2	242.6	234.1	226.6	225.1	218.0
72.5°	301.3	311.6	298.0	272.2	246.0	224.5	209.3	200.4	196.5	193.8	190.0
75°	226.1	235.1	226.1	206.0	187.5	172.5	159.4	155.9	151.4	149.9	147.4
77.5°	160.0	167.9	160.9	148.4	134.5	122.9	115.9	111.4	110.4	107.7	109.0
80°	122.3	127.3	120.8	112.3	101.2	93.2	88.2	85.7	82.8	81.7	83.7
82.5°	87.8	90.0	86.7	81.0	72.8	67.6	64.2	61.3	60.7	60.9	60.9
85°	45.6	45.1	44.6	39.6	37.1	33.6	31.6	31.1	30.5	31.6	32.6
87.5°	18.7	18.8	18.0	16.0	14.4	12.7	11.9	11.0	11.9	12.7	13.6
90°	17.3	15.6	14.0	12.1	9.7	7.4	5.1	2.8	5.1	7.4	9.7
92.5°	34.9	33.7	32.6	30.6	28.0	25.4	22.8	20.2	22.8	25.4	28.0
95°	68.6	67.1	65.6	64.0	62.1	60.2	58.3	56.5	58.3	60.2	62.1
97.5°	109.6	107.9	106.2	104.6	103.1	101.6	100.1	98.6	100.1	101.6	103.1
100°	140.2	138.3	136.4	135.1	134.2	133.4	132.5	131.7	132.5	133.4	134.2
102.5°	172.1	170.4	168.7	167.7	167.3	167.0	166.6	166.4	166.6	167.0	167.3
105°	222.3	221.4	220.6	220.1	219.8	219.6	219.4	219.2	219.4	219.6	219.8
107.5°	276.2	276.1	275.9	275.7	275.5	275.2	274.9	274.8	274.9	275.2	275.5
110°	313.7	313.9	314.1	314.1	313.6	313.2	312.7	312.4	312.7	313.2	313.6



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	350.9	351.3	351.7	351.9	351.8	351.7	351.6	351.5	351.6	351.7	351.8
115°	409.2	409.5	410.0	410.2	410.2	410.2	410.2	410.2	410.2	410.2	410.2
117.5°	465.5	465.8	466.1	466.2	466.0	465.8	465.7	465.5	465.7	465.8	466.0
120°	504.5	505.2	505.9	505.8	504.9	504.1	503.2	502.4	503.2	504.1	504.9
122.5°	541.5	541.9	542.2	542.1	541.8	541.4	541.1	540.7	541.1	541.4	541.8
125°	596.9	597.1	597.3	597.4	597.4	597.4	597.4	597.4	597.4	597.4	597.4
127.5°	650.7	651.1	651.4	651.3	650.6	650.0	649.4	648.8	649.4	650.0	650.6
130°	687.7	687.7	687.7	687.4	686.7	686.2	685.5	684.9	685.5	686.2	686.7
132.5°	723.4	723.6	723.8	723.6	723.1	722.6	722.3	721.8	722.3	722.6	723.1
135°	776.2	776.2	776.2	775.5	774.3	773.0	771.8	770.5	771.8	773.0	774.3
137.5°	827.1	826.7	826.3	826.0	825.3	824.7	824.2	823.6	824.2	824.7	825.3
140°	860.8	860.8	860.8	860.6	860.2	859.8	859.3	858.9	859.3	859.8	860.2
142.5°	892.8	893.0	893.1	893.0	892.6	892.1	891.7	891.3	891.7	892.1	892.6
145°	940.4	940.2	939.9	939.4	938.6	937.7	936.9	936.0	936.9	937.7	938.6
147.5°	984.6	984.8	985.0	984.5	983.5	982.5	981.5	980.5	981.5	982.5	983.5
150°	1011.3	1011.3	1011.3	1011.0	1010.1	1009.3	1008.4	1007.6	1008.4	1009.3	1010.1
152.5°	1035.9	1035.7	1035.5	1035.2	1034.7	1034.2	1033.7	1033.2	1033.7	1034.2	1034.7
155°	1072.0	1072.1	1072.4	1072.5	1072.5	1072.5	1072.5	1072.5	1072.5	1072.5	1072.5
157.5°	1103.8	1103.8	1103.9	1104.1	1104.5	1104.8	1105.2	1105.6	1105.2	1104.8	1104.5
160°	1123.7	1123.9	1124.2	1124.4	1124.5	1124.7	1124.9	1125.2	1124.9	1124.7	1124.5
162.5°	1140.3	1140.5	1140.7	1141.0	1141.6	1142.2	1142.7	1143.2	1142.7	1142.2	1141.6
165°	1163.7	1164.0	1164.5	1165.0	1165.6	1166.3	1166.9	1167.5	1166.9	1166.3	1165.6
167.5°	1182.3	1182.2	1182.2	1182.6	1183.6	1184.4	1185.2	1186.2	1185.2	1184.4	1183.6
170°	1192.5	1192.3	1192.0	1192.5	1193.5	1194.6	1195.6	1196.7	1195.6	1194.6	1193.5
172.5°	1200.3	1200.3	1200.2	1200.7	1201.6	1202.5	1203.3	1204.2	1203.3	1202.5	1201.6
175°	1209.3	1209.6	1209.8	1210.4	1211.4	1212.5	1213.5	1214.6	1213.5	1212.5	1211.4
177.5°	1214.2	1214.2	1214.2	1214.6	1215.4	1216.3	1217.1	1218.0	1217.1	1216.3	1215.4
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1186.8	1183.3	1178.0	1170.8	1164.8	1158.4	1156.8	1154.3	1159.1	1155.2	1154.0
5°	1147.9	1137.4	1123.9	1108.3	1099.3	1086.3	1083.7	1078.7	1073.7	1073.3	1068.2
7.5°	1106.7	1091.3	1073.6	1057.7	1043.0	1028.8	1019.5	1017.5	1010.1	1005.8	1000.8
10°	1080.2	1061.2	1040.7	1025.6	1008.6	993.5	983.0	977.0	971.9	966.5	961.5
12.5°	1049.0	1028.7	1011.8	995.5	975.2	963.8	946.5	936.1	935.1	935.2	922.2
15°	1012.6	992.5	966.5	943.4	932.4	910.3	900.8	888.7	881.3	873.7	867.7
17.5°	971.0	946.0	925.7	899.2	878.2	860.6	848.1	840.8	829.5	818.9	811.2
20°	944.9	918.3	896.8	868.7	845.6	824.1	813.6	803.5	795.0	786.0	777.5
22.5°	918.4	890.7	864.3	837.1	815.6	792.9	782.7	769.0	760.9	755.9	747.4
25°	876.8	846.7	816.6	790.5	768.5	748.4	734.9	724.3	715.3	711.3	705.8
27.5°	831.4	801.5	772.5	742.9	717.8	703.3	692.5	684.6	679.3	674.0	671.6
30°	802.6	771.5	740.4	712.8	689.8	675.2	665.2	659.7	655.6	653.2	650.6
32.5°	773.3	742.6	709.9	684.8	664.1	651.2	643.6	638.0	636.0	635.1	634.2
35°	726.3	695.3	665.2	642.6	623.1	618.1	611.5	608.6	607.6	611.1	612.6
37.5°	680.9	652.1	624.4	602.6	589.7	582.4	580.1	580.3	583.9	587.0	590.6
40°	651.7	623.6	597.6	578.4	566.5	561.9	560.9	563.5	567.4	571.0	575.0
42.5°	623.2	595.5	571.8	554.0	545.6	541.5	542.1	544.6	550.2	554.5	560.5
45°	579.0	555.9	532.8	518.3	511.3	512.3	512.3	516.8	522.4	528.9	535.4
47.5°	537.3	514.2	495.1	483.0	479.3	478.4	481.3	487.1	495.0	503.1	512.2
50°	509.3	487.2	470.7	459.7	455.6	457.1	461.2	466.7	476.2	486.3	495.8
52.5°	480.8	460.8	445.4	435.2	432.4	435.1	439.1	447.8	456.2	467.0	478.5
55°	436.6	419.5	407.6	400.0	399.0	400.5	405.0	414.5	426.6	440.2	451.2
57.5°	392.6	378.3	367.3	362.1	362.6	364.0	371.5	382.8	395.6	410.0	424.2
60°	363.0	349.9	340.9	336.9	337.3	340.4	349.4	360.0	376.0	390.0	405.0
62.5°	334.9	323.4	314.8	311.2	310.5	317.1	325.7	336.7	352.7	368.3	384.6
65°	289.7	280.7	273.7	271.7	273.2	278.2	289.3	303.8	317.4	333.8	350.9
67.5°	245.6	238.2	233.4	234.3	236.1	243.6	252.8	265.2	280.6	297.7	314.6
70°	217.5	210.6	206.5	207.0	210.0	219.0	227.1	239.6	256.2	273.7	287.8
72.5°	188.7	184.1	180.5	182.6	185.6	191.8	201.8	214.3	228.8	245.2	260.0
75°	144.9	144.9	142.9	144.4	148.9	154.9	162.4	175.4	190.0	203.0	215.1
77.5°	107.4	106.4	107.6	109.5	112.1	119.2	127.8	137.1	148.1	161.1	171.1
80°	82.2	82.8	85.2	88.2	89.3	94.7	103.8	112.3	120.8	131.9	141.4
82.5°	61.7	62.3	63.5	67.4	68.3	74.3	80.1	88.6	96.3	103.8	111.7
85°	33.6	33.6	36.1	37.6	40.1	44.1	47.6	52.6	59.7	64.7	72.2
87.5°	15.3	15.6	17.5	18.7	20.3	22.6	23.7	28.3	30.2	32.4	36.2
90°	12.1	14.0	15.6	17.3	19.0	20.7	22.0	23.2	24.5	25.7	26.6
92.5°	30.6	32.6	33.7	34.9	36.1	37.2	38.0	38.7	39.5	40.2	40.8
95°	64.0	65.6	67.1	68.6	70.0	71.5	72.1	72.8	73.4	74.0	74.4
97.5°	104.6	106.2	107.9	109.6	111.4	113.1	113.9	114.6	115.4	116.1	116.5
100°	135.1	136.4	138.3	140.2	142.0	143.9	144.4	144.8	145.2	145.6	145.8
102.5°	167.7	168.7	170.4	172.1	173.8	175.6	176.2	176.7	177.3	177.9	178.2
105°	220.1	220.6	221.4	222.3	223.1	223.9	224.5	225.2	225.8	226.4	227.1
107.5°	275.7	275.9	276.1	276.2	276.3	276.4	277.0	277.6	278.1	278.7	279.0
110°	314.1	314.1	313.9	313.7	313.5	313.3	312.8	312.5	312.0	311.6	311.7



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	351.9	351.7	351.3	350.9	350.5	350.2	350.1	350.0	349.9	349.9	349.9
115°	410.2	410.0	409.5	409.2	408.7	408.3	408.1	407.8	407.6	407.5	407.3
117.5°	466.2	466.1	465.8	465.5	465.2	465.0	464.2	463.5	462.8	462.1	461.6
120°	505.8	505.9	505.2	504.5	504.0	503.3	502.3	501.2	500.2	499.2	498.8
122.5°	542.1	542.2	541.9	541.5	541.2	540.9	540.3	539.5	538.9	538.1	537.3
125°	597.4	597.3	597.1	596.9	596.6	596.4	596.1	595.6	595.2	594.7	594.4
127.5°	651.3	651.4	651.1	650.7	650.4	650.1	649.7	649.2	648.8	648.4	648.0
130°	687.4	687.7	687.7	687.7	687.7	687.7	687.3	686.9	686.5	686.1	685.4
132.5°	723.6	723.8	723.6	723.4	723.2	723.1	722.6	722.3	721.8	721.4	721.0
135°	775.5	776.2	776.2	776.2	776.2	776.2	775.7	775.3	774.9	774.5	773.9
137.5°	826.0	826.3	826.7	827.1	827.4	827.7	827.2	826.6	826.0	825.6	825.3
140°	860.6	860.8	860.8	860.8	860.8	860.8	860.6	860.4	860.2	860.0	859.8
142.5°	893.0	893.1	893.0	892.8	892.6	892.4	892.4	892.3	892.3	892.3	892.2
145°	939.4	939.9	940.2	940.4	940.6	940.8	940.6	940.4	940.2	939.9	939.5
147.5°	984.5	985.0	984.8	984.6	984.4	984.3	984.1	983.9	983.7	983.5	983.4
150°	1011.0	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3
152.5°	1035.2	1035.5	1035.7	1035.9	1036.0	1036.1	1036.7	1037.2	1037.6	1038.2	1038.2
155°	1072.5	1072.4	1072.1	1072.0	1071.8	1071.6	1072.4	1073.3	1074.0	1074.9	1074.9
157.5°	1104.1	1103.9	1103.8	1103.8	1103.8	1103.7	1104.4	1104.9	1105.6	1106.3	1106.2
160°	1124.4	1124.2	1123.9	1123.7	1123.5	1123.3	1123.9	1124.5	1125.2	1125.8	1125.6
162.5°	1141.0	1140.7	1140.5	1140.3	1140.1	1139.8	1140.9	1142.1	1143.2	1144.3	1144.4
165°	1165.0	1164.5	1164.0	1163.7	1163.2	1162.8	1164.0	1165.4	1166.6	1167.8	1168.0
167.5°	1182.6	1182.2	1182.2	1182.3	1182.3	1182.4	1183.6	1184.9	1186.2	1187.4	1187.4
170°	1192.5	1192.0	1192.3	1192.5	1192.7	1192.9	1194.2	1195.4	1196.7	1198.0	1197.8
172.5°	1200.7	1200.2	1200.3	1200.3	1200.4	1200.4	1201.8	1203.2	1204.7	1206.2	1206.1
175°	1210.4	1209.8	1209.6	1209.3	1209.1	1208.9	1210.4	1211.8	1213.3	1214.7	1214.7
177.5°	1214.6	1214.2	1214.2	1214.2	1214.2	1214.2	1215.3	1216.5	1217.7	1218.9	1218.8
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4



TEST NUMBER: P332608-830
 CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1153.1	1152.4	1149.5	1149.1	1149.5	1152.4	1153.1	1154.0	1155.2	1159.1	1154.3
5°	1065.3	1062.7	1061.2	1066.8	1061.2	1062.7	1065.3	1068.2	1073.3	1073.7	1078.7
7.5°	998.9	996.9	992.5	991.2	992.5	996.9	998.9	1000.8	1005.8	1010.1	1017.5
10°	956.4	954.4	950.5	949.4	950.5	954.4	956.4	961.5	966.5	971.9	977.0
12.5°	915.5	911.5	910.7	911.7	910.7	911.5	915.5	922.2	935.2	935.1	936.1
15°	861.2	859.2	853.7	855.2	853.7	859.2	861.2	867.7	873.7	881.3	888.7
17.5°	807.7	805.2	798.5	804.5	798.5	805.2	807.7	811.2	818.9	829.5	840.8
20°	774.0	770.0	766.5	765.9	766.5	770.0	774.0	777.5	786.0	795.0	803.5
22.5°	741.9	738.3	738.0	734.7	738.0	738.3	741.9	747.4	755.9	760.9	769.0
25°	701.8	698.3	697.3	694.7	697.3	698.3	701.8	705.8	711.3	715.3	724.3
27.5°	671.0	669.3	667.5	668.3	667.5	669.3	671.0	671.6	674.0	679.3	684.6
30°	652.1	651.7	650.6	650.6	650.6	651.7	652.1	650.6	653.2	655.6	659.7
32.5°	636.5	636.4	637.1	637.1	637.1	636.4	636.5	634.2	635.1	636.0	638.0
35°	614.5	616.0	617.1	615.6	617.1	616.0	614.5	612.6	611.1	607.6	608.6
37.5°	594.7	596.3	597.7	599.4	597.7	596.3	594.7	590.6	587.0	583.9	580.3
40°	579.5	583.0	584.0	586.5	584.0	583.0	579.5	575.0	571.0	567.4	563.5
42.5°	565.1	568.9	571.6	572.0	571.6	568.9	565.1	560.5	554.5	550.2	544.6
45°	542.9	546.9	550.4	550.4	550.4	546.9	542.9	535.4	528.9	522.4	516.8
47.5°	519.9	525.8	529.2	530.2	529.2	525.8	519.9	512.2	503.1	495.0	487.1
50°	504.3	511.3	514.8	517.4	514.8	511.3	504.3	495.8	486.3	476.2	466.7
52.5°	489.1	496.1	500.8	502.1	500.8	496.1	489.1	478.5	467.0	456.2	447.8
55°	462.7	472.7	478.2	480.2	478.2	472.7	462.7	451.2	440.2	426.6	414.5
57.5°	437.8	447.0	453.5	455.0	453.5	447.0	437.8	424.2	410.0	395.6	382.8
60°	418.6	428.6	436.6	438.1	436.6	428.6	418.6	405.0	390.0	376.0	360.0
62.5°	398.9	409.3	416.6	420.5	416.6	409.3	398.9	384.6	368.3	352.7	336.7
65°	365.0	375.4	382.5	384.0	382.5	375.4	365.0	350.9	333.8	317.4	303.8
67.5°	327.8	338.4	343.0	345.9	343.0	338.4	327.8	314.6	297.7	280.6	265.2
70°	301.8	310.3	315.3	317.8	315.3	310.3	301.8	287.8	273.7	256.2	239.6
72.5°	272.1	281.0	286.8	287.3	286.8	281.0	272.1	260.0	245.2	228.8	214.3
75°	226.6	234.6	237.6	237.6	237.6	234.6	226.6	215.1	203.0	190.0	175.4
77.5°	179.4	183.5	187.3	188.0	187.3	183.5	179.4	171.1	161.1	148.1	137.1
80°	148.9	151.4	154.4	154.4	154.4	151.4	148.9	141.4	131.9	120.8	112.3
82.5°	117.6	119.7	122.7	122.3	122.7	119.7	117.6	111.7	103.8	96.3	88.6
85°	71.2	75.7	75.2	74.2	75.2	75.7	71.2	72.2	64.7	59.7	52.6
87.5°	37.5	38.0	39.2	40.2	39.2	38.0	37.5	36.2	32.4	30.2	28.3
90°	27.0	27.4	27.8	28.2	27.8	27.4	27.0	26.6	25.7	24.5	23.2
92.5°	41.0	41.3	41.6	41.8	41.6	41.3	41.0	40.8	40.2	39.5	38.7
95°	74.4	74.4	74.4	74.4	74.4	74.4	74.4	74.4	74.0	73.4	72.8
97.5°	116.5	116.5	116.5	116.5	116.5	116.5	116.5	116.5	116.1	115.4	114.6
100°	145.8	145.8	145.8	145.8	145.8	145.8	145.8	145.8	145.6	145.2	144.8
102.5°	178.4	178.6	178.8	178.9	178.8	178.6	178.4	178.2	177.9	177.3	176.7
105°	227.6	228.3	228.9	229.5	228.9	228.3	227.6	227.1	226.4	225.8	225.2
107.5°	279.0	278.9	278.9	278.8	278.9	278.9	279.0	279.0	278.7	278.1	277.6
110°	312.4	312.9	313.6	314.2	313.6	312.9	312.4	311.7	311.6	312.0	312.5



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	350.0	350.1	350.2	350.3	350.2	350.1	350.0	349.9	349.9	349.9	350.0
115°	407.1	406.8	406.6	406.4	406.6	406.8	407.1	407.3	407.5	407.6	407.8
117.5°	461.1	460.7	460.2	459.9	460.2	460.7	461.1	461.6	462.1	462.8	463.5
120°	499.3	499.6	500.1	500.5	500.1	499.6	499.3	498.8	499.2	500.2	501.2
122.5°	536.6	535.8	535.1	534.3	535.1	535.8	536.6	537.3	538.1	538.9	539.5
125°	594.0	593.5	593.1	592.7	593.1	593.5	594.0	594.4	594.7	595.2	595.6
127.5°	647.7	647.3	647.1	646.7	647.1	647.3	647.7	648.0	648.4	648.8	649.2
130°	684.6	683.7	682.9	682.0	682.9	683.7	684.6	685.4	686.1	686.5	686.9
132.5°	720.7	720.4	720.0	719.7	720.0	720.4	720.7	721.0	721.4	721.8	722.3
135°	773.4	772.7	772.0	771.5	772.0	772.7	773.4	773.9	774.5	774.9	775.3
137.5°	825.5	825.6	825.7	825.9	825.7	825.6	825.5	825.3	825.6	826.0	826.6
140°	859.6	859.3	859.1	858.9	859.1	859.3	859.6	859.8	860.0	860.2	860.4
142.5°	892.2	892.1	892.1	892.0	892.1	892.1	892.2	892.2	892.3	892.3	892.3
145°	938.9	938.3	937.6	937.0	937.6	938.3	938.9	939.5	939.9	940.2	940.4
147.5°	983.2	983.0	982.8	982.6	982.8	983.0	983.2	983.4	983.5	983.7	983.9
150°	1011.1	1010.8	1010.6	1010.4	1010.6	1010.8	1011.1	1011.3	1011.3	1011.3	1011.3
152.5°	1037.6	1037.1	1036.5	1035.9	1036.5	1037.1	1037.6	1038.2	1038.2	1037.6	1037.2
155°	1074.0	1073.3	1072.4	1071.6	1072.4	1073.3	1074.0	1074.9	1074.9	1074.0	1073.3
157.5°	1105.5	1104.8	1104.1	1103.3	1104.1	1104.8	1105.5	1106.2	1106.3	1105.6	1104.9
160°	1124.5	1123.5	1122.5	1121.4	1122.5	1123.5	1124.5	1125.6	1125.8	1125.2	1124.5
162.5°	1143.4	1142.4	1141.3	1140.2	1141.3	1142.4	1143.4	1144.4	1144.3	1143.2	1142.1
165°	1167.2	1166.4	1165.5	1164.7	1165.5	1166.4	1167.2	1168.0	1167.8	1166.6	1165.4
167.5°	1186.1	1184.8	1183.5	1182.2	1183.5	1184.8	1186.1	1187.4	1187.4	1186.2	1184.9
170°	1196.4	1194.9	1193.4	1191.9	1193.4	1194.9	1196.4	1197.8	1198.0	1196.7	1195.4
172.5°	1204.7	1203.2	1201.7	1200.2	1201.7	1203.2	1204.7	1206.1	1206.2	1204.7	1203.2
175°	1213.3	1211.8	1210.4	1208.9	1210.4	1211.8	1213.3	1214.7	1214.7	1213.3	1211.8
177.5°	1217.5	1216.1	1214.7	1213.4	1214.7	1216.1	1217.5	1218.8	1218.9	1217.7	1216.5
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1156.8	1158.4	1164.8	1170.8	1178.0	1183.3	1186.8	1190.8	1199.3	1206.1	1212.5
5°	1083.7	1086.3	1099.3	1108.3	1123.9	1137.4	1147.9	1159.4	1173.0	1191.6	1208.6
7.5°	1019.5	1028.8	1043.0	1057.7	1073.6	1091.3	1106.7	1124.1	1147.5	1172.9	1199.2
10°	983.0	993.5	1008.6	1025.6	1040.7	1061.2	1080.2	1100.8	1127.4	1158.5	1189.6
12.5°	946.5	963.8	975.2	995.5	1011.8	1028.7	1049.0	1075.9	1106.9	1139.6	1177.1
15°	900.8	910.3	932.4	943.4	966.5	992.5	1012.6	1039.6	1069.7	1112.9	1155.0
17.5°	848.1	860.6	878.2	899.2	925.7	946.0	971.0	998.8	1036.7	1079.6	1132.3
20°	813.6	824.1	845.6	868.7	896.8	918.3	944.9	971.9	1011.1	1056.7	1111.8
22.5°	782.7	792.9	815.6	837.1	864.3	890.7	918.4	949.9	987.4	1035.5	1091.7
25°	734.9	748.4	768.5	790.5	816.6	846.7	876.8	904.8	944.9	995.5	1055.7
27.5°	692.5	703.3	717.8	742.9	772.5	801.5	831.4	866.7	905.2	958.8	1021.2
30°	665.2	675.2	689.8	712.8	740.4	771.5	802.6	836.6	876.8	929.9	993.5
32.5°	643.6	651.2	664.1	684.8	709.9	742.6	773.3	808.6	850.6	903.1	965.1
35°	611.5	618.1	623.1	642.6	665.2	695.3	726.3	763.9	804.6	854.2	916.3
37.5°	580.1	582.4	589.7	602.6	624.4	652.1	680.9	717.9	759.5	809.9	866.0
40°	560.9	561.9	566.5	578.4	597.6	623.6	651.7	688.2	727.8	775.5	831.1
42.5°	542.1	541.5	545.6	554.0	571.8	595.5	623.2	656.6	696.2	740.2	792.6
45°	512.3	512.3	511.3	518.3	532.8	555.9	579.0	611.1	644.1	687.3	731.4
47.5°	481.3	478.4	479.3	483.0	495.1	514.2	537.3	563.6	592.9	629.3	668.0
50°	461.2	457.1	455.6	459.7	470.7	487.2	509.3	532.3	560.0	592.0	625.1
52.5°	439.1	435.1	432.4	435.2	445.4	460.8	480.8	501.1	525.8	552.0	580.6
55°	405.0	400.5	399.0	400.0	407.6	419.5	436.6	455.2	473.7	495.3	515.3
57.5°	371.5	364.0	362.6	362.1	367.3	378.3	392.6	408.7	422.2	435.2	456.6
60°	349.4	340.4	337.3	336.9	340.9	349.9	363.0	379.0	388.5	397.5	416.0
62.5°	325.7	317.1	310.5	311.2	314.8	323.4	334.9	346.5	352.8	362.6	375.1
65°	289.3	278.2	273.2	271.7	273.7	280.7	289.7	297.3	304.3	308.3	320.3
67.5°	252.8	243.6	236.1	234.3	233.4	238.2	245.6	250.2	255.1	258.6	265.8
70°	227.1	219.0	210.0	207.0	206.5	210.6	217.5	218.0	225.1	226.6	234.1
72.5°	201.8	191.8	185.6	182.6	180.5	184.1	188.7	190.0	193.8	196.5	200.4
75°	162.4	154.9	148.9	144.4	142.9	144.9	144.9	147.4	149.9	151.4	155.9
77.5°	127.8	119.2	112.1	109.5	107.6	106.4	107.4	109.0	107.7	110.4	111.4
80°	103.8	94.7	89.3	88.2	85.2	82.8	82.2	83.7	81.7	82.8	85.7
82.5°	80.1	74.3	68.3	67.4	63.5	62.3	61.7	60.9	60.9	60.7	61.3
85°	47.6	44.1	40.1	37.6	36.1	33.6	33.6	32.6	31.6	30.5	31.1
87.5°	23.7	22.6	20.3	18.7	17.5	15.6	15.3	13.6	12.7	11.9	11.0
90°	22.0	20.7	19.0	17.3	15.6	14.0	12.1	9.7	7.4	5.1	2.8
92.5°	38.0	37.2	36.1	34.9	33.7	32.6	30.6	28.0	25.4	22.8	20.2
95°	72.1	71.5	70.0	68.6	67.1	65.6	64.0	62.1	60.2	58.3	56.5
97.5°	113.9	113.1	111.4	109.6	107.9	106.2	104.6	103.1	101.6	100.1	98.6
100°	144.4	143.9	142.0	140.2	138.3	136.4	135.1	134.2	133.4	132.5	131.7
102.5°	176.2	175.6	173.8	172.1	170.4	168.7	167.7	167.3	167.0	166.6	166.4
105°	224.5	223.9	223.1	222.3	221.4	220.6	220.1	219.8	219.6	219.4	219.2
107.5°	277.0	276.4	276.3	276.2	276.1	275.9	275.7	275.5	275.2	274.9	274.8
110°	312.8	313.3	313.5	313.7	313.9	314.1	314.1	313.6	313.2	312.7	312.4



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	350.1	350.2	350.5	350.9	351.3	351.7	351.9	351.8	351.7	351.6	351.5
115°	408.1	408.3	408.7	409.2	409.5	410.0	410.2	410.2	410.2	410.2	410.2
117.5°	464.2	465.0	465.2	465.5	465.8	466.1	466.2	466.0	465.8	465.7	465.5
120°	502.3	503.3	504.0	504.5	505.2	505.9	505.8	504.9	504.1	503.2	502.4
122.5°	540.3	540.9	541.2	541.5	541.9	542.2	542.1	541.8	541.4	541.1	540.7
125°	596.1	596.4	596.6	596.9	597.1	597.3	597.4	597.4	597.4	597.4	597.4
127.5°	649.7	650.1	650.4	650.7	651.1	651.4	651.3	650.6	650.0	649.4	648.8
130°	687.3	687.7	687.7	687.7	687.7	687.7	687.4	686.7	686.2	685.5	684.9
132.5°	722.6	723.1	723.2	723.4	723.6	723.8	723.6	723.1	722.6	722.3	721.8
135°	775.7	776.2	776.2	776.2	776.2	776.2	775.5	774.3	773.0	771.8	770.5
137.5°	827.2	827.7	827.4	827.1	826.7	826.3	826.0	825.3	824.7	824.2	823.6
140°	860.6	860.8	860.8	860.8	860.8	860.8	860.6	860.2	859.8	859.3	858.9
142.5°	892.4	892.4	892.6	892.8	893.0	893.1	893.0	892.6	892.1	891.7	891.3
145°	940.6	940.8	940.6	940.4	940.2	939.9	939.4	938.6	937.7	936.9	936.0
147.5°	984.1	984.3	984.4	984.6	984.8	985.0	984.5	983.5	982.5	981.5	980.5
150°	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3	1011.0	1010.1	1009.3	1008.4	1007.6
152.5°	1036.7	1036.1	1036.0	1035.9	1035.7	1035.5	1035.2	1034.7	1034.2	1033.7	1033.2
155°	1072.4	1071.6	1071.8	1072.0	1072.1	1072.4	1072.5	1072.5	1072.5	1072.5	1072.5
157.5°	1104.4	1103.7	1103.8	1103.8	1103.8	1103.9	1104.1	1104.5	1104.8	1105.2	1105.6
160°	1123.9	1123.3	1123.5	1123.7	1123.9	1124.2	1124.4	1124.5	1124.7	1124.9	1125.2
162.5°	1140.9	1139.8	1140.1	1140.3	1140.5	1140.7	1141.0	1141.6	1142.2	1142.7	1143.2
165°	1164.0	1162.8	1163.2	1163.7	1164.0	1164.5	1165.0	1165.6	1166.3	1166.9	1167.5
167.5°	1183.6	1182.4	1182.3	1182.3	1182.2	1182.2	1182.6	1183.6	1184.4	1185.2	1186.2
170°	1194.2	1192.9	1192.7	1192.5	1192.3	1192.0	1192.5	1193.5	1194.6	1195.6	1196.7
172.5°	1201.8	1200.4	1200.4	1200.3	1200.3	1200.2	1200.7	1201.6	1202.5	1203.3	1204.2
175°	1210.4	1208.9	1209.1	1209.3	1209.6	1209.8	1210.4	1211.4	1212.5	1213.5	1214.6
177.5°	1215.3	1214.2	1214.2	1214.2	1214.2	1214.2	1214.6	1215.4	1216.3	1217.1	1218.0
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4



TEST NUMBER: P332608-830
 CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1218.1	1222.1	1227.4	1236.1	1239.3	1243.4	1249.0	1248.6	1250.2	1256.2	1269.0
5°	1222.7	1238.1	1253.2	1271.2	1290.3	1302.8	1319.8	1330.4	1341.0	1354.4	1377.5
7.5°	1224.5	1249.1	1276.7	1308.3	1336.5	1369.0	1394.4	1418.2	1439.7	1468.4	1495.8
10°	1221.6	1254.7	1290.3	1330.4	1373.0	1409.1	1441.7	1478.8	1510.3	1544.9	1576.0
12.5°	1216.4	1256.3	1303.9	1348.9	1398.6	1452.0	1492.6	1530.1	1572.2	1611.9	1659.8
15°	1204.6	1259.2	1314.8	1374.0	1440.7	1502.3	1560.9	1609.6	1654.7	1714.4	1777.1
17.5°	1189.6	1248.5	1318.7	1390.3	1459.9	1530.4	1603.0	1676.1	1733.1	1807.1	1856.1
20°	1175.5	1243.7	1315.9	1401.1	1470.7	1558.5	1630.7	1701.4	1779.5	1853.2	1911.9
22.5°	1155.8	1230.5	1307.0	1391.9	1483.6	1571.3	1654.7	1731.5	1809.6	1889.7	1960.8
25°	1130.9	1198.5	1289.3	1385.5	1476.8	1572.0	1667.7	1764.0	1848.2	1933.0	1999.1
27.5°	1088.4	1173.8	1258.3	1357.6	1459.1	1566.8	1669.1	1769.9	1858.1	1927.8	1968.8
30°	1066.8	1140.9	1232.7	1332.4	1442.2	1558.0	1664.7	1763.5	1845.7	1901.4	1917.9
32.5°	1034.6	1111.3	1201.0	1304.3	1420.5	1539.5	1650.7	1743.9	1812.4	1841.6	1821.7
35°	987.0	1056.2	1146.9	1252.7	1373.5	1500.3	1610.1	1688.8	1723.9	1696.3	1627.7
37.5°	929.9	998.4	1089.6	1193.4	1318.4	1447.4	1546.6	1603.3	1591.7	1523.1	1420.7
40°	889.8	953.9	1040.7	1152.9	1274.8	1404.1	1491.3	1521.9	1489.8	1391.6	1282.8
42.5°	845.3	907.9	994.9	1103.2	1232.3	1351.5	1427.6	1430.0	1376.3	1258.9	1149.6
45°	777.5	837.2	919.4	1032.2	1151.4	1263.8	1313.8	1289.3	1190.1	1076.8	967.0
47.5°	710.6	762.3	843.4	950.5	1063.8	1158.3	1183.1	1138.9	1033.1	923.1	821.4
50°	661.7	713.8	790.0	892.3	1001.5	1083.3	1095.3	1036.6	932.9	822.1	742.4
52.5°	614.7	666.5	739.9	834.5	934.6	1008.2	1008.7	940.8	837.4	738.7	664.6
55°	545.9	592.5	658.6	743.4	832.6	890.2	876.3	806.1	716.3	630.7	565.9
57.5°	479.6	520.1	581.1	651.8	730.4	777.9	754.6	687.0	606.9	534.2	485.2
60°	436.6	475.2	527.4	594.0	660.2	697.3	675.2	614.1	540.4	481.7	439.1
62.5°	394.9	427.5	477.6	535.5	596.8	624.3	604.6	544.3	480.6	427.6	393.0
65°	335.8	362.4	402.6	452.1	496.8	520.3	503.8	447.6	399.0	360.9	333.4
67.5°	280.7	301.4	331.9	371.6	409.5	422.3	407.3	368.2	327.0	296.4	277.0
70°	242.6	262.2	287.8	318.3	351.4	365.0	349.9	318.8	285.2	257.1	238.1
72.5°	209.3	224.5	246.0	272.2	298.0	311.6	301.3	271.5	243.1	222.3	206.0
75°	159.4	172.5	187.5	206.0	226.1	235.1	226.1	205.6	186.0	170.4	158.9
77.5°	115.9	122.9	134.5	148.4	160.9	167.9	160.0	146.1	134.1	123.5	117.8
80°	88.2	93.2	101.2	112.3	120.8	127.3	122.3	110.7	101.2	94.3	91.7
82.5°	64.2	67.6	72.8	81.0	86.7	90.0	87.8	79.5	75.6	69.4	66.8
85°	31.6	33.6	37.1	39.6	44.6	45.1	45.6	42.1	38.6	37.1	35.1
87.5°	11.9	12.7	14.4	16.0	18.0	18.8	18.7	19.0	17.8	17.6	16.3
90°	5.1	7.4	9.7	12.1	14.0	15.6	17.3	19.0	20.7	22.0	23.2
92.5°	22.8	25.4	28.0	30.6	32.6	33.7	34.9	36.1	37.2	38.0	38.7
95°	58.3	60.2	62.1	64.0	65.6	67.1	68.6	70.0	71.5	72.1	72.8
97.5°	100.1	101.6	103.1	104.6	106.2	107.9	109.6	111.4	113.1	113.9	114.6
100°	132.5	133.4	134.2	135.1	136.4	138.3	140.2	142.0	143.9	144.4	144.8
102.5°	166.6	167.0	167.3	167.7	168.7	170.4	172.1	173.8	175.6	176.2	176.7
105°	219.4	219.6	219.8	220.1	220.6	221.4	222.3	223.1	223.9	224.5	225.2
107.5°	274.9	275.2	275.5	275.7	275.9	276.1	276.2	276.3	276.4	277.0	277.6
110°	312.7	313.2	313.6	314.1	314.1	313.9	313.7	313.5	313.3	312.8	312.5



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	351.6	351.7	351.8	351.9	351.7	351.3	350.9	350.5	350.2	350.1	350.0
115°	410.2	410.2	410.2	410.2	410.0	409.5	409.2	408.7	408.3	408.1	407.8
117.5°	465.7	465.8	466.0	466.2	466.1	465.8	465.5	465.2	465.0	464.2	463.5
120°	503.2	504.1	504.9	505.8	505.9	505.2	504.5	504.0	503.3	502.3	501.2
122.5°	541.1	541.4	541.8	542.1	542.2	541.9	541.5	541.2	540.9	540.3	539.5
125°	597.4	597.4	597.4	597.4	597.3	597.1	596.9	596.6	596.4	596.1	595.6
127.5°	649.4	650.0	650.6	651.3	651.4	651.1	650.7	650.4	650.1	649.7	649.2
130°	685.5	686.2	686.7	687.4	687.7	687.7	687.7	687.7	687.7	687.3	686.9
132.5°	722.3	722.6	723.1	723.6	723.8	723.6	723.4	723.2	723.1	722.6	722.3
135°	771.8	773.0	774.3	775.5	776.2	776.2	776.2	776.2	776.2	775.7	775.3
137.5°	824.2	824.7	825.3	826.0	826.3	826.7	827.1	827.4	827.7	827.2	826.6
140°	859.3	859.8	860.2	860.6	860.8	860.8	860.8	860.8	860.8	860.6	860.4
142.5°	891.7	892.1	892.6	893.0	893.1	893.0	892.8	892.6	892.4	892.4	892.3
145°	936.9	937.7	938.6	939.4	939.9	940.2	940.4	940.6	940.8	940.6	940.4
147.5°	981.5	982.5	983.5	984.5	985.0	984.8	984.6	984.4	984.3	984.1	983.9
150°	1008.4	1009.3	1010.1	1011.0	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3
152.5°	1033.7	1034.2	1034.7	1035.2	1035.5	1035.7	1035.9	1036.0	1036.1	1036.7	1037.2
155°	1072.5	1072.5	1072.5	1072.5	1072.4	1072.1	1072.0	1071.8	1071.6	1072.4	1073.3
157.5°	1105.2	1104.8	1104.5	1104.1	1103.9	1103.8	1103.8	1103.8	1103.7	1104.4	1104.9
160°	1124.9	1124.7	1124.5	1124.4	1124.2	1123.9	1123.7	1123.5	1123.3	1123.9	1124.5
162.5°	1142.7	1142.2	1141.6	1141.0	1140.7	1140.5	1140.3	1140.1	1139.8	1140.9	1142.1
165°	1166.9	1166.3	1165.6	1165.0	1164.5	1164.0	1163.7	1163.2	1162.8	1164.0	1165.4
167.5°	1185.2	1184.4	1183.6	1182.6	1182.2	1182.2	1182.3	1182.3	1182.4	1183.6	1184.9
170°	1195.6	1194.6	1193.5	1192.5	1192.0	1192.3	1192.5	1192.7	1192.9	1194.2	1195.4
172.5°	1203.3	1202.5	1201.6	1200.7	1200.2	1200.3	1200.3	1200.4	1200.4	1201.8	1203.2
175°	1213.5	1212.5	1211.4	1210.4	1209.8	1209.6	1209.3	1209.1	1208.9	1210.4	1211.8
177.5°	1217.1	1216.3	1215.4	1214.6	1214.2	1214.2	1214.2	1214.2	1214.2	1215.3	1216.5
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4



TEST NUMBER: P332608-830
 CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1275.4	1276.3	1279.9	1282.7	1283.5	1287.5	1287.9
5°	1387.5	1396.1	1412.6	1414.1	1416.6	1429.6	1419.7
7.5°	1518.9	1540.5	1555.0	1567.7	1572.3	1578.0	1576.9
10°	1603.1	1635.2	1651.2	1676.8	1677.8	1684.3	1680.3
12.5°	1687.7	1725.0	1754.3	1759.0	1780.5	1783.8	1789.4
15°	1807.6	1847.2	1887.8	1902.3	1931.9	1939.0	1950.0
17.5°	1920.3	1960.8	1989.2	2026.8	2039.0	2055.2	2044.2
20°	1982.1	2026.2	2062.3	2091.9	2104.4	2113.4	2112.4
22.5°	2019.4	2063.9	2093.1	2115.5	2127.2	2131.1	2130.8
25°	2042.7	2068.3	2077.3	2085.8	2072.8	2068.3	2070.3
27.5°	1977.7	1971.1	1947.6	1916.7	1884.6	1859.2	1845.3
30°	1888.3	1849.3	1813.6	1751.4	1719.4	1700.3	1683.3
32.5°	1761.6	1699.7	1631.2	1574.2	1537.8	1509.5	1505.2
35°	1544.5	1451.2	1367.5	1297.8	1261.7	1231.1	1224.1
37.5°	1313.1	1216.2	1140.9	1079.5	1040.7	1019.1	998.9
40°	1159.4	1076.3	1002.0	949.9	920.4	904.8	892.3
42.5°	1041.1	965.2	891.4	851.7	824.9	815.4	808.0
45°	877.7	807.1	755.9	725.9	710.3	694.3	686.7
47.5°	746.9	689.4	655.6	630.1	613.5	604.0	599.2
50°	672.7	625.6	595.5	576.0	560.9	553.4	549.4
52.5°	606.9	568.3	543.0	527.4	517.3	511.7	510.1
55°	522.8	493.2	477.2	463.7	456.2	451.2	449.1
57.5°	454.5	431.7	418.7	407.6	404.6	400.4	399.0
60°	409.5	392.0	381.0	373.4	371.0	365.9	366.9
62.5°	369.9	355.5	346.1	341.8	338.5	334.2	335.6
65°	312.8	302.3	297.3	293.2	289.3	286.7	288.7
67.5°	262.5	255.2	248.5	246.1	244.1	243.7	241.6
70°	229.6	223.6	217.5	216.0	216.0	214.1	213.6
72.5°	197.9	193.5	189.5	188.4	186.8	187.6	185.5
75°	152.9	149.4	147.9	146.4	145.9	145.9	144.4
77.5°	113.0	110.4	108.0	108.0	106.1	105.5	105.3
80°	85.7	84.7	82.8	82.8	81.7	82.2	81.2
82.5°	64.5	63.1	62.7	61.8	60.4	60.5	59.6
85°	34.6	33.1	32.6	31.1	30.1	31.1	30.1
87.5°	17.0	16.8	16.5	15.8	15.5	15.6	14.4
90°	24.5	25.7	26.6	27.0	27.4	27.8	28.2
92.5°	39.5	40.2	40.8	41.0	41.3	41.6	41.8
95°	73.4	74.0	74.4	74.4	74.4	74.4	74.4
97.5°	115.4	116.1	116.5	116.5	116.5	116.5	116.5
100°	145.2	145.6	145.8	145.8	145.8	145.8	145.8
102.5°	177.3	177.9	178.2	178.4	178.6	178.8	178.9
105°	225.8	226.4	227.1	227.6	228.3	228.9	229.5
107.5°	278.1	278.7	279.0	279.0	278.9	278.9	278.8
110°	312.0	311.6	311.7	312.4	312.9	313.6	314.2



TEST NUMBER: P332608-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	349.9	349.9	349.9	350.0	350.1	350.2	350.3
115°	407.6	407.5	407.3	407.1	406.8	406.6	406.4
117.5°	462.8	462.1	461.6	461.1	460.7	460.2	459.9
120°	500.2	499.2	498.8	499.3	499.6	500.1	500.5
122.5°	538.9	538.1	537.3	536.6	535.8	535.1	534.3
125°	595.2	594.7	594.4	594.0	593.5	593.1	592.7
127.5°	648.8	648.4	648.0	647.7	647.3	647.1	646.7
130°	686.5	686.1	685.4	684.6	683.7	682.9	682.0
132.5°	721.8	721.4	721.0	720.7	720.4	720.0	719.7
135°	774.9	774.5	773.9	773.4	772.7	772.0	771.5
137.5°	826.0	825.6	825.3	825.5	825.6	825.7	825.9
140°	860.2	860.0	859.8	859.6	859.3	859.1	858.9
142.5°	892.3	892.3	892.2	892.2	892.1	892.1	892.0
145°	940.2	939.9	939.5	938.9	938.3	937.6	937.0
147.5°	983.7	983.5	983.4	983.2	983.0	982.8	982.6
150°	1011.3	1011.3	1011.3	1011.1	1010.8	1010.6	1010.4
152.5°	1037.6	1038.2	1038.2	1037.6	1037.1	1036.5	1035.9
155°	1074.0	1074.9	1074.9	1074.0	1073.3	1072.4	1071.6
157.5°	1105.6	1106.3	1106.2	1105.5	1104.8	1104.1	1103.3
160°	1125.2	1125.8	1125.6	1124.5	1123.5	1122.5	1121.4
162.5°	1143.2	1144.3	1144.4	1143.4	1142.4	1141.3	1140.2
165°	1166.6	1167.8	1168.0	1167.2	1166.4	1165.5	1164.7
167.5°	1186.2	1187.4	1187.4	1186.1	1184.8	1183.5	1182.2
170°	1196.7	1198.0	1197.8	1196.4	1194.9	1193.4	1191.9
172.5°	1204.7	1206.2	1206.1	1204.7	1203.2	1201.7	1200.2
175°	1213.3	1214.7	1214.7	1213.3	1211.8	1210.4	1208.9
177.5°	1217.7	1218.9	1218.8	1217.5	1216.1	1214.7	1213.4
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4

(END OF REPORT)