

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332609-830

Luminaire Tested: **SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332609-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6824.6 lumens  
Efficiency: N/A  
Efficacy: 131.2 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332609-830  
CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	98	94	90	86	90	86	83	80	73	71	68	60	59	57	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	42	40	35				
3	81	72	65	59	75	67	61	55	57	52	48	47	44	41	39	36	34	30				
4	75	64	56	50	69	59	53	47	51	45	41	42	38	35	35	32	30	26				
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23				
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	29	25	23	20				
7	58	46	38	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	28	34	28	24	29	25	21	24	21	18	16				
9	51	38	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14				
10	47	35	28	23	44	33	27	22	29	23	20	24	20	17	21	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9769	9769	9769	9769
5°	11505	9794	8645	9794
10°	13774	9752	7783	9752
15°	16298	9653	7148	9653
20°	18148	9552	6580	9552
25°	18441	9404	6188	9404
30°	15691	9261	6065	9261
35°	12064	9030	6067	9030
40°	9403	8759	6181	8759
45°	7840	8350	6284	8350
50°	6900	7851	6498	7851
55°	6321	7253	6759	7253
60°	5924	6717	7074	6717
65°	5515	6118	7335	6118
70°	5042	5526	7501	5526
75°	4504	4863	7411	4863
80°	3775	3984	7178	3984
85°	2788	2881	6873	2881



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.9	1.7
10°-20°	363.4	5.3
20°-30°	576.2	8.4
30°-40°	641.2	9.4
40°-50°	583.7	8.6
50°-60°	477.0	7.0
60°-70°	340.5	5.0
70°-80°	187.5	2.7
80°-90°	53.8	0.8
90°-100°	345.9	5.1
100°-110°	720.0	10.5
110°-120°	644.9	9.4
120°-130°	542.4	7.9
130°-140°	452.3	6.6
140°-150°	345.5	5.1
150°-160°	242.9	3.6
160°-170°	142.9	2.1
170°-180°	46.5	0.7
0°-30°	1057.5	15.5
0°-40°	1698.7	24.9
0°-60°	2759.4	40.4
0°-90°	3341.3	49.0
90°-120°	1710.8	25.1
90°-150°	3051.1	44.7
90°-180°	3483.0	51.0
0°-180°	6824.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1210	1210	1210	1210	1210	
5°	1420	1209	1067	1209	1420	144
15°	1950	1155	855	1155	1950	551
25°	2070	1056	695	1056	2070	913
35°	1224	916	616	916	1224	777
45°	687	731	550	731	687	541
55°	449	515	480	515	449	406
65°	289	320	384	320	289	286
75°	144	156	238	156	144	154
85°	30	31	74	31	30	37
90°	20	1	20	1	20	17
95°	230	31	230	31	230	356
105°	1324	110	1324	110	1324	1309
115°	1271	194	1271	194	1271	1262
125°	1014	270	1014	270	1014	922
135°	907	321	907	321	907	700
145°	741	370	741	370	741	469
155°	620	421	620	421	620	289
165°	541	458	541	458	541	155
175°	487	478	487	478	487	47
180°	479	479	479	479	479	



TEST NUMBER: P332609-830  
 CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1287.9	1287.5	1283.5	1282.7	1279.9	1276.3	1275.4	1269.0	1256.2	1250.2	1248.6
5°	1419.7	1429.6	1416.6	1414.1	1412.6	1396.1	1387.5	1377.5	1354.4	1341.0	1330.4
7.5°	1576.9	1578.0	1572.3	1567.7	1555.0	1540.5	1518.9	1495.8	1468.4	1439.7	1418.2
10°	1680.3	1684.3	1677.8	1676.8	1651.2	1635.2	1603.1	1576.0	1544.9	1510.3	1478.8
12.5°	1789.4	1783.8	1780.5	1759.0	1754.3	1725.0	1687.7	1659.8	1611.9	1572.2	1530.1
15°	1950.0	1939.0	1931.9	1902.3	1887.8	1847.2	1807.6	1777.1	1714.4	1654.7	1609.6
17.5°	2044.2	2055.2	2039.0	2026.8	1989.2	1960.8	1920.3	1856.1	1807.1	1733.1	1676.1
20°	2112.4	2113.4	2104.4	2091.9	2062.3	2026.2	1982.1	1911.9	1853.2	1779.5	1701.4
22.5°	2130.8	2131.1	2127.2	2115.5	2093.1	2063.9	2019.4	1960.8	1889.7	1809.6	1731.5
25°	2070.3	2068.3	2072.8	2085.8	2077.3	2068.3	2042.7	1999.1	1933.0	1848.2	1764.0
27.5°	1845.3	1859.2	1884.6	1916.7	1947.6	1971.1	1977.7	1968.8	1927.8	1858.1	1769.9
30°	1683.3	1700.3	1719.4	1751.4	1813.6	1849.3	1888.3	1917.9	1901.4	1845.7	1763.5
32.5°	1505.2	1509.5	1537.8	1574.2	1631.2	1699.7	1761.6	1821.7	1841.6	1812.4	1743.9
35°	1224.1	1231.1	1261.7	1297.8	1367.5	1451.2	1544.5	1627.7	1696.3	1723.9	1688.8
37.5°	998.9	1019.1	1040.7	1079.5	1140.9	1216.2	1313.1	1420.7	1523.1	1591.7	1603.3
40°	892.3	904.8	920.4	949.9	1002.0	1076.3	1159.4	1282.8	1391.6	1489.8	1521.9
42.5°	808.0	815.4	824.9	851.7	891.4	965.2	1041.1	1149.6	1258.9	1376.3	1430.0
45°	686.7	694.3	710.3	725.9	755.9	807.1	877.7	967.0	1076.8	1190.1	1289.3
47.5°	599.2	604.0	613.5	630.1	655.6	689.4	746.9	821.4	923.1	1033.1	1138.9
50°	549.4	553.4	560.9	576.0	595.5	625.6	672.7	742.4	822.1	932.9	1036.6
52.5°	510.1	511.7	517.3	527.4	543.0	568.3	606.9	664.6	738.7	837.4	940.8
55°	449.1	451.2	456.2	463.7	477.2	493.2	522.8	565.9	630.7	716.3	806.1
57.5°	399.0	400.4	404.6	407.6	418.7	431.7	454.5	485.2	534.2	606.9	687.0
60°	366.9	365.9	371.0	373.4	381.0	392.0	409.5	439.1	481.7	540.4	614.1
62.5°	335.6	334.2	338.5	341.8	346.1	355.5	369.9	393.0	427.6	480.6	544.3
65°	288.7	286.7	289.3	293.2	297.3	302.3	312.8	333.4	360.9	399.0	447.6
67.5°	241.6	243.7	244.1	246.1	248.5	255.2	262.5	277.0	296.4	327.0	368.2
70°	213.6	214.1	216.0	216.0	217.5	223.6	229.6	238.1	257.1	285.2	318.8
72.5°	185.5	187.6	186.8	188.4	189.5	193.5	197.9	206.0	222.3	243.1	271.5
75°	144.4	145.9	145.9	146.4	147.9	149.4	152.9	158.9	170.4	186.0	205.6
77.5°	105.3	105.5	106.1	108.0	108.0	110.4	113.0	117.8	123.5	134.1	146.1
80°	81.2	82.2	81.7	82.8	82.8	84.7	85.7	91.7	94.3	101.2	110.7
82.5°	59.6	60.5	60.4	61.8	62.7	63.1	64.5	66.8	69.4	75.6	79.5
85°	30.1	31.1	30.1	31.1	32.6	33.1	34.6	35.1	37.1	38.6	42.1
87.5°	12.8	13.9	14.1	14.4	15.0	15.4	15.6	15.0	16.4	17.1	18.3
90°	19.8	19.8	20.7	19.8	18.9	18.9	17.9	17.0	16.0	17.0	15.1
92.5°	72.5	72.5	75.7	80.8	91.8	110.7	139.1	184.8	248.6	298.5	261.2
95°	229.6	241.9	258.7	287.9	334.0	425.3	551.4	697.2	788.5	766.9	578.7
97.5°	613.7	633.3	661.5	718.1	785.7	883.9	975.9	1030.2	990.6	807.7	541.6
100°	862.9	870.3	898.6	956.0	1037.8	1107.5	1153.6	1134.8	997.4	756.5	491.2
102.5°	1079.7	1085.7	1115.4	1157.0	1207.2	1236.2	1222.9	1129.5	940.9	692.6	457.3
105°	1323.9	1329.6	1342.7	1350.3	1348.4	1309.8	1216.6	1053.9	838.4	617.3	428.1
107.5°	1414.7	1412.2	1402.8	1381.3	1334.8	1250.9	1119.7	946.4	755.5	575.1	422.8
110°	1416.2	1407.7	1390.7	1351.2	1284.4	1180.9	1044.4	881.7	714.2	560.8	424.3



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1371.7	1358.0	1334.3	1286.5	1210.6	1107.1	978.2	834.2	690.9	554.0	428.9
115°	1271.2	1263.7	1233.6	1177.1	1102.8	1012.5	902.4	786.6	669.0	550.4	437.5
117.5°	1169.4	1163.6	1133.1	1085.7	1022.3	945.7	859.1	763.3	659.2	549.5	446.8
120°	1112.2	1101.8	1077.4	1035.9	982.3	915.6	840.3	752.7	653.9	549.5	453.6
122.5°	1067.1	1056.7	1035.9	1000.6	955.3	896.7	828.2	743.8	647.9	548.7	460.3
125°	1014.4	1008.7	990.8	963.6	925.9	874.1	809.2	728.3	638.0	547.6	470.5
127.5°	983.4	977.8	962.8	938.5	900.7	851.6	786.8	709.5	624.6	545.5	478.5
130°	965.4	959.8	944.7	921.1	882.6	832.7	768.7	694.5	616.3	544.8	484.6
132.5°	945.1	939.4	925.1	898.6	860.8	810.9	748.5	678.6	608.8	544.0	489.8
135°	907.1	901.4	886.4	860.1	822.4	775.3	717.9	656.8	597.5	542.9	497.8
137.5°	860.1	853.3	840.8	814.8	779.7	737.2	688.8	637.1	587.7	542.7	502.5
140°	826.1	818.6	805.5	784.8	751.8	712.3	670.0	625.8	582.5	542.0	506.2
142.5°	790.0	784.8	773.1	753.8	724.7	690.5	654.1	615.2	578.0	542.0	509.3
145°	740.6	735.8	726.4	710.4	686.9	660.5	632.4	600.3	570.2	540.1	511.0
147.5°	696.6	695.0	687.9	674.1	656.8	636.1	613.5	588.1	563.3	536.7	511.9
150°	671.8	670.9	665.2	653.0	638.0	621.0	602.2	580.6	558.0	534.4	511.9
152.5°	649.2	648.3	644.9	635.0	622.2	608.2	590.9	572.3	552.0	530.7	510.4
155°	620.1	620.1	617.3	609.7	600.3	589.0	575.0	559.9	542.9	525.1	508.1
157.5°	594.5	594.5	592.8	587.1	580.0	571.0	559.1	546.5	533.7	519.2	505.7
160°	578.7	578.7	577.8	572.1	566.5	558.9	548.6	538.2	527.0	514.7	503.4
162.5°	563.6	564.4	563.5	557.8	553.6	546.9	538.8	529.9	520.9	510.2	501.1
165°	541.0	542.0	542.9	539.1	535.4	530.7	524.1	518.5	511.0	503.4	496.8
167.5°	523.2	524.0	524.1	521.7	519.8	517.0	511.7	507.4	501.9	496.6	492.3
170°	511.9	511.9	512.8	511.9	510.0	507.2	503.4	500.6	495.9	492.1	489.3
172.5°	500.6	502.1	503.0	502.1	501.0	498.9	496.6	494.6	490.6	487.6	486.3
175°	487.4	489.3	491.2	489.3	489.3	489.3	487.4	486.4	484.6	482.7	482.7
177.5°	479.7	481.2	482.7	481.9	482.7	481.9	481.9	481.2	480.4	479.7	479.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1249.0	1243.4	1239.3	1236.1	1227.4	1222.1	1218.1	1212.5	1206.1	1199.3	1190.8
5°	1319.8	1302.8	1290.3	1271.2	1253.2	1238.1	1222.7	1208.6	1191.6	1173.0	1159.4
7.5°	1394.4	1369.0	1336.5	1308.3	1276.7	1249.1	1224.5	1199.2	1172.9	1147.5	1124.1
10°	1441.7	1409.1	1373.0	1330.4	1290.3	1254.7	1221.6	1189.6	1158.5	1127.4	1100.8
12.5°	1492.6	1452.0	1398.6	1348.9	1303.9	1256.3	1216.4	1177.1	1139.6	1106.9	1075.9
15°	1560.9	1502.3	1440.7	1374.0	1314.8	1259.2	1204.6	1155.0	1112.9	1069.7	1039.6
17.5°	1603.0	1530.4	1459.9	1390.3	1318.7	1248.5	1189.6	1132.3	1079.6	1036.7	998.8
20°	1630.7	1558.5	1470.7	1401.1	1315.9	1243.7	1175.5	1111.8	1056.7	1011.1	971.9
22.5°	1654.7	1571.3	1483.6	1391.9	1307.0	1230.5	1155.8	1091.7	1035.5	987.4	949.9
25°	1667.7	1572.0	1476.8	1385.5	1289.3	1198.5	1130.9	1055.7	995.5	944.9	904.8
27.5°	1669.1	1566.8	1459.1	1357.6	1258.3	1173.8	1088.4	1021.2	958.8	905.2	866.7
30°	1664.7	1558.0	1442.2	1332.4	1232.7	1140.9	1066.8	993.5	929.9	876.8	836.6
32.5°	1650.7	1539.5	1420.5	1304.3	1201.0	1111.3	1034.6	965.1	903.1	850.6	808.6
35°	1610.1	1500.3	1373.5	1252.7	1146.9	1056.2	987.0	916.3	854.2	804.6	763.9
37.5°	1546.6	1447.4	1318.4	1193.4	1089.6	998.4	929.9	866.0	809.9	759.5	717.9
40°	1491.3	1404.1	1274.8	1152.9	1040.7	953.9	889.8	831.1	775.5	727.8	688.2
42.5°	1427.6	1351.5	1232.3	1103.2	994.9	907.9	845.3	792.6	740.2	696.2	656.6
45°	1313.8	1263.8	1151.4	1032.2	919.4	837.2	777.5	731.4	687.3	644.1	611.1
47.5°	1183.1	1158.3	1063.8	950.5	843.4	762.3	710.6	668.0	629.3	592.9	563.6
50°	1095.3	1083.3	1001.5	892.3	790.0	713.8	661.7	625.1	592.0	560.0	532.3
52.5°	1008.7	1008.2	934.6	834.5	739.9	666.5	614.7	580.6	552.0	525.8	501.1
55°	876.3	890.2	832.6	743.4	658.6	592.5	545.9	515.3	495.3	473.7	455.2
57.5°	754.6	777.9	730.4	651.8	581.1	520.1	479.6	456.6	435.2	422.2	408.7
60°	675.2	697.3	660.2	594.0	527.4	475.2	436.6	416.0	397.5	388.5	379.0
62.5°	604.6	624.3	596.8	535.5	477.6	427.5	394.9	375.1	362.6	352.8	346.5
65°	503.8	520.3	496.8	452.1	402.6	362.4	335.8	320.3	308.3	304.3	297.3
67.5°	407.3	422.3	409.5	371.6	331.9	301.4	280.7	265.8	258.6	255.1	250.2
70°	349.9	365.0	351.4	318.3	287.8	262.2	242.6	234.1	226.6	225.1	218.0
72.5°	301.3	311.6	298.0	272.2	246.0	224.5	209.3	200.4	196.5	193.8	190.0
75°	226.1	235.1	226.1	206.0	187.5	172.5	159.4	155.9	151.4	149.9	147.4
77.5°	160.0	167.9	160.9	148.4	134.5	122.9	115.9	111.4	110.4	107.7	109.0
80°	122.3	127.3	120.8	112.3	101.2	93.2	88.2	85.7	82.8	81.7	83.7
82.5°	87.8	90.0	86.7	81.0	72.8	67.6	64.2	61.3	60.7	60.9	60.9
85°	45.6	45.1	44.6	39.6	37.1	33.6	31.6	31.1	30.5	31.6	32.6
87.5°	17.9	18.3	16.8	15.2	13.8	12.3	11.4	10.7	11.4	12.3	12.9
90°	13.2	13.2	7.5	7.5	6.6	5.7	2.8	0.9	2.8	5.7	6.6
92.5°	190.1	117.1	69.3	49.7	35.9	24.5	15.6	10.7	15.6	24.5	35.9
95°	353.8	199.4	117.6	78.1	55.5	43.3	33.8	31.0	33.8	43.3	55.5
97.5°	318.0	190.7	127.6	94.4	75.1	63.8	55.7	55.7	55.7	63.8	75.1
100°	299.3	192.9	137.4	107.3	89.4	78.1	71.5	71.5	71.5	78.1	89.4
102.5°	294.0	200.4	150.1	121.6	104.4	93.9	88.0	86.5	88.0	93.9	104.4
105°	296.4	218.3	173.1	145.8	128.9	117.6	112.9	110.1	112.9	117.6	128.9
107.5°	310.3	239.2	197.7	170.9	154.7	142.6	138.0	136.1	138.0	142.6	154.7
110°	320.8	255.0	213.6	188.2	171.3	159.9	155.2	153.4	155.2	159.9	171.3





TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	332.2	270.0	230.2	204.7	187.8	177.3	171.8	169.9	171.8	177.3	187.8
115°	350.1	293.6	255.9	230.5	212.6	203.2	196.6	193.9	196.6	203.2	212.6
117.5°	368.3	316.3	280.6	254.2	237.5	227.2	221.3	218.7	221.3	227.2	237.5
120°	381.1	332.2	296.4	270.0	254.0	243.7	237.1	235.3	237.1	243.7	254.0
122.5°	393.1	347.2	311.4	285.9	268.3	258.7	252.1	250.3	252.1	258.7	268.3
125°	411.2	367.9	334.0	307.6	289.8	279.5	273.8	270.0	273.8	279.5	289.8
127.5°	426.8	387.1	354.4	327.8	309.2	297.4	290.6	287.6	290.6	297.4	309.2
130°	436.6	399.9	367.9	340.6	322.7	308.6	301.1	297.4	301.1	308.6	322.7
132.5°	446.4	410.5	378.4	352.7	333.3	319.9	310.1	307.1	310.1	319.9	333.3
135°	459.2	425.3	394.3	369.8	350.1	334.0	324.6	320.8	324.6	334.0	350.1
137.5°	468.3	436.6	407.6	384.3	363.7	348.6	338.2	334.6	338.2	348.6	363.7
140°	474.2	444.1	415.9	393.3	373.5	357.6	347.2	344.4	347.2	357.6	373.5
142.5°	478.7	450.9	423.4	401.6	382.6	367.3	357.8	355.0	357.8	367.3	382.6
145°	483.6	458.3	433.8	413.1	395.2	382.0	372.6	369.8	372.6	382.0	395.2
147.5°	488.0	465.8	442.8	424.1	409.3	395.8	387.5	386.5	387.5	395.8	409.3
150°	490.2	469.6	448.8	430.9	416.9	405.6	398.0	397.1	398.0	405.6	416.9
152.5°	491.7	472.6	454.1	437.7	425.1	414.6	407.1	406.9	407.1	414.6	425.1
155°	493.0	477.0	461.1	447.0	436.6	427.2	421.5	420.6	421.5	427.2	436.6
157.5°	493.0	480.2	466.7	455.6	446.6	439.2	433.9	433.9	433.9	439.2	446.6
160°	493.0	481.7	470.5	460.1	452.6	446.0	442.2	442.2	442.2	446.0	452.6
162.5°	493.0	483.2	472.8	464.7	457.9	452.0	449.0	449.8	449.0	452.0	457.9
165°	491.2	483.6	475.1	469.6	464.9	460.1	458.3	458.3	458.3	460.1	464.9
167.5°	488.9	483.4	477.2	473.0	470.3	466.7	465.8	466.7	465.8	466.7	470.3
170°	487.4	482.7	478.0	475.1	473.3	470.5	469.6	470.5	469.6	470.5	473.3
172.5°	485.9	481.9	478.7	476.6	475.5	473.4	473.3	474.2	473.3	473.4	475.5
175°	483.6	480.8	478.9	478.9	478.0	477.0	477.0	478.0	477.0	477.0	478.0
177.5°	481.2	479.7	478.9	478.9	478.9	478.2	478.9	479.7	478.9	478.2	478.9
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1186.8	1183.3	1178.0	1170.8	1164.8	1158.4	1156.8	1154.3	1159.1	1155.2	1154.0
5°	1147.9	1137.4	1123.9	1108.3	1099.3	1086.3	1083.7	1078.7	1073.7	1073.3	1068.2
7.5°	1106.7	1091.3	1073.6	1057.7	1043.0	1028.8	1019.5	1017.5	1010.1	1005.8	1000.8
10°	1080.2	1061.2	1040.7	1025.6	1008.6	993.5	983.0	977.0	971.9	966.5	961.5
12.5°	1049.0	1028.7	1011.8	995.5	975.2	963.8	946.5	936.1	935.1	935.2	922.2
15°	1012.6	992.5	966.5	943.4	932.4	910.3	900.8	888.7	881.3	873.7	867.7
17.5°	971.0	946.0	925.7	899.2	878.2	860.6	848.1	840.8	829.5	818.9	811.2
20°	944.9	918.3	896.8	868.7	845.6	824.1	813.6	803.5	795.0	786.0	777.5
22.5°	918.4	890.7	864.3	837.1	815.6	792.9	782.7	769.0	760.9	755.9	747.4
25°	876.8	846.7	816.6	790.5	768.5	748.4	734.9	724.3	715.3	711.3	705.8
27.5°	831.4	801.5	772.5	742.9	717.8	703.3	692.5	684.6	679.3	674.0	671.6
30°	802.6	771.5	740.4	712.8	689.8	675.2	665.2	659.7	655.6	653.2	650.6
32.5°	773.3	742.6	709.9	684.8	664.1	651.2	643.6	638.0	636.0	635.1	634.2
35°	726.3	695.3	665.2	642.6	623.1	618.1	611.5	608.6	607.6	611.1	612.6
37.5°	680.9	652.1	624.4	602.6	589.7	582.4	580.1	580.3	583.9	587.0	590.6
40°	651.7	623.6	597.6	578.4	566.5	561.9	560.9	563.5	567.4	571.0	575.0
42.5°	623.2	595.5	571.8	554.0	545.6	541.5	542.1	544.6	550.2	554.5	560.5
45°	579.0	555.9	532.8	518.3	511.3	512.3	512.3	516.8	522.4	528.9	535.4
47.5°	537.3	514.2	495.1	483.0	479.3	478.4	481.3	487.1	495.0	503.1	512.2
50°	509.3	487.2	470.7	459.7	455.6	457.1	461.2	466.7	476.2	486.3	495.8
52.5°	480.8	460.8	445.4	435.2	432.4	435.1	439.1	447.8	456.2	467.0	478.5
55°	436.6	419.5	407.6	400.0	399.0	400.5	405.0	414.5	426.6	440.2	451.2
57.5°	392.6	378.3	367.3	362.1	362.6	364.0	371.5	382.8	395.6	410.0	424.2
60°	363.0	349.9	340.9	336.9	337.3	340.4	349.4	360.0	376.0	390.0	405.0
62.5°	334.9	323.4	314.8	311.2	310.5	317.1	325.7	336.7	352.7	368.3	384.6
65°	289.7	280.7	273.7	271.7	273.2	278.2	289.3	303.8	317.4	333.8	350.9
67.5°	245.6	238.2	233.4	234.3	236.1	243.6	252.8	265.2	280.6	297.7	314.6
70°	217.5	210.6	206.5	207.0	210.0	219.0	227.1	239.6	256.2	273.7	287.8
72.5°	188.7	184.1	180.5	182.6	185.6	191.8	201.8	214.3	228.8	245.2	260.0
75°	144.9	144.9	142.9	144.4	148.9	154.9	162.4	175.4	190.0	203.0	215.1
77.5°	107.4	106.4	107.6	109.5	112.1	119.2	127.8	137.1	148.1	161.1	171.1
80°	82.2	82.8	85.2	88.2	89.3	94.7	103.8	112.3	120.8	131.9	141.4
82.5°	61.7	62.3	63.5	67.4	68.3	74.3	80.1	88.6	96.3	103.8	111.7
85°	33.6	33.6	36.1	37.6	40.1	44.1	47.6	52.6	59.7	64.7	72.2
87.5°	14.3	14.3	17.1	17.9	19.4	21.9	22.4	27.1	28.8	31.0	34.7
90°	7.5	7.5	13.2	13.2	15.1	17.0	16.0	17.0	17.9	18.9	18.9
92.5°	49.7	69.3	117.1	190.1	261.2	298.5	248.6	184.8	139.1	110.7	91.8
95°	78.1	117.6	199.4	353.8	578.7	766.9	788.5	697.2	551.4	425.3	334.0
97.5°	94.4	127.6	190.7	318.0	541.6	807.7	990.6	1030.2	975.9	883.9	785.7
100°	107.3	137.4	192.9	299.3	491.2	756.5	997.4	1134.8	1153.6	1107.5	1037.8
102.5°	121.6	150.1	200.4	294.0	457.3	692.6	940.9	1129.5	1222.9	1236.2	1207.2
105°	145.8	173.1	218.3	296.4	428.1	617.3	838.4	1053.9	1216.6	1309.8	1348.4
107.5°	170.9	197.7	239.2	310.3	422.8	575.1	755.5	946.4	1119.7	1250.9	1334.8
110°	188.2	213.6	255.0	320.8	424.3	560.8	714.2	881.7	1044.4	1180.9	1284.4



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.7	230.2	270.0	332.2	428.9	554.0	690.9	834.2	978.2	1107.1	1210.6
115°	230.5	255.9	293.6	350.1	437.5	550.4	669.0	786.6	902.4	1012.5	1102.8
117.5°	254.2	280.6	316.3	368.3	446.8	549.5	659.2	763.3	859.1	945.7	1022.3
120°	270.0	296.4	332.2	381.1	453.6	549.5	653.9	752.7	840.3	915.6	982.3
122.5°	285.9	311.4	347.2	393.1	460.3	548.7	647.9	743.8	828.2	896.7	955.3
125°	307.6	334.0	367.9	411.2	470.5	547.6	638.0	728.3	809.2	874.1	925.9
127.5°	327.8	354.4	387.1	426.8	478.5	545.5	624.6	709.5	786.8	851.6	900.7
130°	340.6	367.9	399.9	436.6	484.6	544.8	616.3	694.5	768.7	832.7	882.6
132.5°	352.7	378.4	410.5	446.4	489.8	544.0	608.8	678.6	748.5	810.9	860.8
135°	369.8	394.3	425.3	459.2	497.8	542.9	597.5	656.8	717.9	775.3	822.4
137.5°	384.3	407.6	436.6	468.3	502.5	542.7	587.7	637.1	688.8	737.2	779.7
140°	393.3	415.9	444.1	474.2	506.2	542.0	582.5	625.8	670.0	712.3	751.8
142.5°	401.6	423.4	450.9	478.7	509.3	542.0	578.0	615.2	654.1	690.5	724.7
145°	413.1	433.8	458.3	483.6	511.0	540.1	570.2	600.3	632.4	660.5	686.9
147.5°	424.1	442.8	465.8	488.0	511.9	536.7	563.3	588.1	613.5	636.1	656.8
150°	430.9	448.8	469.6	490.2	511.9	534.4	558.0	580.6	602.2	621.0	638.0
152.5°	437.7	454.1	472.6	491.7	510.4	530.7	552.0	572.3	590.9	608.2	622.2
155°	447.0	461.1	477.0	493.0	508.1	525.1	542.9	559.9	575.0	589.0	600.3
157.5°	455.6	466.7	480.2	493.0	505.7	519.2	533.7	546.5	559.1	571.0	580.0
160°	460.1	470.5	481.7	493.0	503.4	514.7	527.0	538.2	548.6	558.9	566.5
162.5°	464.7	472.8	483.2	493.0	501.1	510.2	520.9	529.9	538.8	546.9	553.6
165°	469.6	475.1	483.6	491.2	496.8	503.4	511.0	518.5	524.1	530.7	535.4
167.5°	473.0	477.2	483.4	488.9	492.3	496.6	501.9	507.4	511.7	517.0	519.8
170°	475.1	478.0	482.7	487.4	489.3	492.1	495.9	500.6	503.4	507.2	510.0
172.5°	476.6	478.7	481.9	485.9	486.3	487.6	490.6	494.6	496.6	498.9	501.0
175°	478.9	478.9	480.8	483.6	482.7	482.7	484.6	486.4	487.4	489.3	489.3
177.5°	478.9	478.9	479.7	481.2	479.7	479.7	480.4	481.2	481.9	481.9	482.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1153.1	1152.4	1149.5	1149.1	1149.5	1152.4	1153.1	1154.0	1155.2	1159.1	1154.3
5°	1065.3	1062.7	1061.2	1066.8	1061.2	1062.7	1065.3	1068.2	1073.3	1073.7	1078.7
7.5°	998.9	996.9	992.5	991.2	992.5	996.9	998.9	1000.8	1005.8	1010.1	1017.5
10°	956.4	954.4	950.5	949.4	950.5	954.4	956.4	961.5	966.5	971.9	977.0
12.5°	915.5	911.5	910.7	911.7	910.7	911.5	915.5	922.2	935.2	935.1	936.1
15°	861.2	859.2	853.7	855.2	853.7	859.2	861.2	867.7	873.7	881.3	888.7
17.5°	807.7	805.2	798.5	804.5	798.5	805.2	807.7	811.2	818.9	829.5	840.8
20°	774.0	770.0	766.5	765.9	766.5	770.0	774.0	777.5	786.0	795.0	803.5
22.5°	741.9	738.3	738.0	734.7	738.0	738.3	741.9	747.4	755.9	760.9	769.0
25°	701.8	698.3	697.3	694.7	697.3	698.3	701.8	705.8	711.3	715.3	724.3
27.5°	671.0	669.3	667.5	668.3	667.5	669.3	671.0	671.6	674.0	679.3	684.6
30°	652.1	651.7	650.6	650.6	650.6	651.7	652.1	650.6	653.2	655.6	659.7
32.5°	636.5	636.4	637.1	637.1	637.1	636.4	636.5	634.2	635.1	636.0	638.0
35°	614.5	616.0	617.1	615.6	617.1	616.0	614.5	612.6	611.1	607.6	608.6
37.5°	594.7	596.3	597.7	599.4	597.7	596.3	594.7	590.6	587.0	583.9	580.3
40°	579.5	583.0	584.0	586.5	584.0	583.0	579.5	575.0	571.0	567.4	563.5
42.5°	565.1	568.9	571.6	572.0	571.6	568.9	565.1	560.5	554.5	550.2	544.6
45°	542.9	546.9	550.4	550.4	550.4	546.9	542.9	535.4	528.9	522.4	516.8
47.5°	519.9	525.8	529.2	530.2	529.2	525.8	519.9	512.2	503.1	495.0	487.1
50°	504.3	511.3	514.8	517.4	514.8	511.3	504.3	495.8	486.3	476.2	466.7
52.5°	489.1	496.1	500.8	502.1	500.8	496.1	489.1	478.5	467.0	456.2	447.8
55°	462.7	472.7	478.2	480.2	478.2	472.7	462.7	451.2	440.2	426.6	414.5
57.5°	437.8	447.0	453.5	455.0	453.5	447.0	437.8	424.2	410.0	395.6	382.8
60°	418.6	428.6	436.6	438.1	436.6	428.6	418.6	405.0	390.0	376.0	360.0
62.5°	398.9	409.3	416.6	420.5	416.6	409.3	398.9	384.6	368.3	352.7	336.7
65°	365.0	375.4	382.5	384.0	382.5	375.4	365.0	350.9	333.8	317.4	303.8
67.5°	327.8	338.4	343.0	345.9	343.0	338.4	327.8	314.6	297.7	280.6	265.2
70°	301.8	310.3	315.3	317.8	315.3	310.3	301.8	287.8	273.7	256.2	239.6
72.5°	272.1	281.0	286.8	287.3	286.8	281.0	272.1	260.0	245.2	228.8	214.3
75°	226.6	234.6	237.6	237.6	237.6	234.6	226.6	215.1	203.0	190.0	175.4
77.5°	179.4	183.5	187.3	188.0	187.3	183.5	179.4	171.1	161.1	148.1	137.1
80°	148.9	151.4	154.4	154.4	154.4	151.4	148.9	141.4	131.9	120.8	112.3
82.5°	117.6	119.7	122.7	122.3	122.7	119.7	117.6	111.7	103.8	96.3	88.6
85°	71.2	75.7	75.2	74.2	75.2	75.7	71.2	72.2	64.7	59.7	52.6
87.5°	36.0	36.7	37.6	38.5	37.6	36.7	36.0	34.7	31.0	28.8	27.1
90°	19.8	20.7	19.8	19.8	19.8	20.7	19.8	18.9	18.9	17.9	17.0
92.5°	80.8	75.7	72.5	72.5	72.5	75.7	80.8	91.8	110.7	139.1	184.8
95°	287.9	258.7	241.9	229.6	241.9	258.7	287.9	334.0	425.3	551.4	697.2
97.5°	718.1	661.5	633.3	613.7	633.3	661.5	718.1	785.7	883.9	975.9	1030.2
100°	956.0	898.6	870.3	862.9	870.3	898.6	956.0	1037.8	1107.5	1153.6	1134.8
102.5°	1157.0	1115.4	1085.7	1079.7	1085.7	1115.4	1157.0	1207.2	1236.2	1222.9	1129.5
105°	1350.3	1342.7	1329.6	1323.9	1329.6	1342.7	1350.3	1348.4	1309.8	1216.6	1053.9
107.5°	1381.3	1402.8	1412.2	1414.7	1412.2	1402.8	1381.3	1334.8	1250.9	1119.7	946.4
110°	1351.2	1390.7	1407.7	1416.2	1407.7	1390.7	1351.2	1284.4	1180.9	1044.4	881.7



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1286.5	1334.3	1358.0	1371.7	1358.0	1334.3	1286.5	1210.6	1107.1	978.2	834.2
115°	1177.1	1233.6	1263.7	1271.2	1263.7	1233.6	1177.1	1102.8	1012.5	902.4	786.6
117.5°	1085.7	1133.1	1163.6	1169.4	1163.6	1133.1	1085.7	1022.3	945.7	859.1	763.3
120°	1035.9	1077.4	1101.8	1112.2	1101.8	1077.4	1035.9	982.3	915.6	840.3	752.7
122.5°	1000.6	1035.9	1056.7	1067.1	1056.7	1035.9	1000.6	955.3	896.7	828.2	743.8
125°	963.6	990.8	1008.7	1014.4	1008.7	990.8	963.6	925.9	874.1	809.2	728.3
127.5°	938.5	962.8	977.8	983.4	977.8	962.8	938.5	900.7	851.6	786.8	709.5
130°	921.1	944.7	959.8	965.4	959.8	944.7	921.1	882.6	832.7	768.7	694.5
132.5°	898.6	925.1	939.4	945.1	939.4	925.1	898.6	860.8	810.9	748.5	678.6
135°	860.1	886.4	901.4	907.1	901.4	886.4	860.1	822.4	775.3	717.9	656.8
137.5°	814.8	840.8	853.3	860.1	853.3	840.8	814.8	779.7	737.2	688.8	637.1
140°	784.8	805.5	818.6	826.1	818.6	805.5	784.8	751.8	712.3	670.0	625.8
142.5°	753.8	773.1	784.8	790.0	784.8	773.1	753.8	724.7	690.5	654.1	615.2
145°	710.4	726.4	735.8	740.6	735.8	726.4	710.4	686.9	660.5	632.4	600.3
147.5°	674.1	687.9	695.0	696.6	695.0	687.9	674.1	656.8	636.1	613.5	588.1
150°	653.0	665.2	670.9	671.8	670.9	665.2	653.0	638.0	621.0	602.2	580.6
152.5°	635.0	644.9	648.3	649.2	648.3	644.9	635.0	622.2	608.2	590.9	572.3
155°	609.7	617.3	620.1	620.1	620.1	617.3	609.7	600.3	589.0	575.0	559.9
157.5°	587.1	592.8	594.5	594.5	594.5	592.8	587.1	580.0	571.0	559.1	546.5
160°	572.1	577.8	578.7	578.7	578.7	577.8	572.1	566.5	558.9	548.6	538.2
162.5°	557.8	563.5	564.4	563.6	564.4	563.5	557.8	553.6	546.9	538.8	529.9
165°	539.1	542.9	542.0	541.0	542.0	542.9	539.1	535.4	530.7	524.1	518.5
167.5°	521.7	524.1	524.0	523.2	524.0	524.1	521.7	519.8	517.0	511.7	507.4
170°	511.9	512.8	511.9	511.9	511.9	512.8	511.9	510.0	507.2	503.4	500.6
172.5°	502.1	503.0	502.1	500.6	502.1	503.0	502.1	501.0	498.9	496.6	494.6
175°	489.3	491.2	489.3	487.4	489.3	491.2	489.3	489.3	489.3	487.4	486.4
177.5°	481.9	482.7	481.2	479.7	481.2	482.7	481.9	482.7	481.9	481.9	481.2
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1156.8	1158.4	1164.8	1170.8	1178.0	1183.3	1186.8	1190.8	1199.3	1206.1	1212.5
5°	1083.7	1086.3	1099.3	1108.3	1123.9	1137.4	1147.9	1159.4	1173.0	1191.6	1208.6
7.5°	1019.5	1028.8	1043.0	1057.7	1073.6	1091.3	1106.7	1124.1	1147.5	1172.9	1199.2
10°	983.0	993.5	1008.6	1025.6	1040.7	1061.2	1080.2	1100.8	1127.4	1158.5	1189.6
12.5°	946.5	963.8	975.2	995.5	1011.8	1028.7	1049.0	1075.9	1106.9	1139.6	1177.1
15°	900.8	910.3	932.4	943.4	966.5	992.5	1012.6	1039.6	1069.7	1112.9	1155.0
17.5°	848.1	860.6	878.2	899.2	925.7	946.0	971.0	998.8	1036.7	1079.6	1132.3
20°	813.6	824.1	845.6	868.7	896.8	918.3	944.9	971.9	1011.1	1056.7	1111.8
22.5°	782.7	792.9	815.6	837.1	864.3	890.7	918.4	949.9	987.4	1035.5	1091.7
25°	734.9	748.4	768.5	790.5	816.6	846.7	876.8	904.8	944.9	995.5	1055.7
27.5°	692.5	703.3	717.8	742.9	772.5	801.5	831.4	866.7	905.2	958.8	1021.2
30°	665.2	675.2	689.8	712.8	740.4	771.5	802.6	836.6	876.8	929.9	993.5
32.5°	643.6	651.2	664.1	684.8	709.9	742.6	773.3	808.6	850.6	903.1	965.1
35°	611.5	618.1	623.1	642.6	665.2	695.3	726.3	763.9	804.6	854.2	916.3
37.5°	580.1	582.4	589.7	602.6	624.4	652.1	680.9	717.9	759.5	809.9	866.0
40°	560.9	561.9	566.5	578.4	597.6	623.6	651.7	688.2	727.8	775.5	831.1
42.5°	542.1	541.5	545.6	554.0	571.8	595.5	623.2	656.6	696.2	740.2	792.6
45°	512.3	512.3	511.3	518.3	532.8	555.9	579.0	611.1	644.1	687.3	731.4
47.5°	481.3	478.4	479.3	483.0	495.1	514.2	537.3	563.6	592.9	629.3	668.0
50°	461.2	457.1	455.6	459.7	470.7	487.2	509.3	532.3	560.0	592.0	625.1
52.5°	439.1	435.1	432.4	435.2	445.4	460.8	480.8	501.1	525.8	552.0	580.6
55°	405.0	400.5	399.0	400.0	407.6	419.5	436.6	455.2	473.7	495.3	515.3
57.5°	371.5	364.0	362.6	362.1	367.3	378.3	392.6	408.7	422.2	435.2	456.6
60°	349.4	340.4	337.3	336.9	340.9	349.9	363.0	379.0	388.5	397.5	416.0
62.5°	325.7	317.1	310.5	311.2	314.8	323.4	334.9	346.5	352.8	362.6	375.1
65°	289.3	278.2	273.2	271.7	273.7	280.7	289.7	297.3	304.3	308.3	320.3
67.5°	252.8	243.6	236.1	234.3	233.4	238.2	245.6	250.2	255.1	258.6	265.8
70°	227.1	219.0	210.0	207.0	206.5	210.6	217.5	218.0	225.1	226.6	234.1
72.5°	201.8	191.8	185.6	182.6	180.5	184.1	188.7	190.0	193.8	196.5	200.4
75°	162.4	154.9	148.9	144.4	142.9	144.9	144.9	147.4	149.9	151.4	155.9
77.5°	127.8	119.2	112.1	109.5	107.6	106.4	107.4	109.0	107.7	110.4	111.4
80°	103.8	94.7	89.3	88.2	85.2	82.8	82.2	83.7	81.7	82.8	85.7
82.5°	80.1	74.3	68.3	67.4	63.5	62.3	61.7	60.9	60.9	60.7	61.3
85°	47.6	44.1	40.1	37.6	36.1	33.6	33.6	32.6	31.6	30.5	31.1
87.5°	22.4	21.9	19.4	17.9	17.1	14.3	14.3	12.9	12.3	11.4	10.7
90°	16.0	17.0	15.1	13.2	13.2	7.5	7.5	6.6	5.7	2.8	0.9
92.5°	248.6	298.5	261.2	190.1	117.1	69.3	49.7	35.9	24.5	15.6	10.7
95°	788.5	766.9	578.7	353.8	199.4	117.6	78.1	55.5	43.3	33.8	31.0
97.5°	990.6	807.7	541.6	318.0	190.7	127.6	94.4	75.1	63.8	55.7	55.7
100°	997.4	756.5	491.2	299.3	192.9	137.4	107.3	89.4	78.1	71.5	71.5
102.5°	940.9	692.6	457.3	294.0	200.4	150.1	121.6	104.4	93.9	88.0	86.5
105°	838.4	617.3	428.1	296.4	218.3	173.1	145.8	128.9	117.6	112.9	110.1
107.5°	755.5	575.1	422.8	310.3	239.2	197.7	170.9	154.7	142.6	138.0	136.1
110°	714.2	560.8	424.3	320.8	255.0	213.6	188.2	171.3	159.9	155.2	153.4



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	690.9	554.0	428.9	332.2	270.0	230.2	204.7	187.8	177.3	171.8	169.9
115°	669.0	550.4	437.5	350.1	293.6	255.9	230.5	212.6	203.2	196.6	193.9
117.5°	659.2	549.5	446.8	368.3	316.3	280.6	254.2	237.5	227.2	221.3	218.7
120°	653.9	549.5	453.6	381.1	332.2	296.4	270.0	254.0	243.7	237.1	235.3
122.5°	647.9	548.7	460.3	393.1	347.2	311.4	285.9	268.3	258.7	252.1	250.3
125°	638.0	547.6	470.5	411.2	367.9	334.0	307.6	289.8	279.5	273.8	270.0
127.5°	624.6	545.5	478.5	426.8	387.1	354.4	327.8	309.2	297.4	290.6	287.6
130°	616.3	544.8	484.6	436.6	399.9	367.9	340.6	322.7	308.6	301.1	297.4
132.5°	608.8	544.0	489.8	446.4	410.5	378.4	352.7	333.3	319.9	310.1	307.1
135°	597.5	542.9	497.8	459.2	425.3	394.3	369.8	350.1	334.0	324.6	320.8
137.5°	587.7	542.7	502.5	468.3	436.6	407.6	384.3	363.7	348.6	338.2	334.6
140°	582.5	542.0	506.2	474.2	444.1	415.9	393.3	373.5	357.6	347.2	344.4
142.5°	578.0	542.0	509.3	478.7	450.9	423.4	401.6	382.6	367.3	357.8	355.0
145°	570.2	540.1	511.0	483.6	458.3	433.8	413.1	395.2	382.0	372.6	369.8
147.5°	563.3	536.7	511.9	488.0	465.8	442.8	424.1	409.3	395.8	387.5	386.5
150°	558.0	534.4	511.9	490.2	469.6	448.8	430.9	416.9	405.6	398.0	397.1
152.5°	552.0	530.7	510.4	491.7	472.6	454.1	437.7	425.1	414.6	407.1	406.9
155°	542.9	525.1	508.1	493.0	477.0	461.1	447.0	436.6	427.2	421.5	420.6
157.5°	533.7	519.2	505.7	493.0	480.2	466.7	455.6	446.6	439.2	433.9	433.9
160°	527.0	514.7	503.4	493.0	481.7	470.5	460.1	452.6	446.0	442.2	442.2
162.5°	520.9	510.2	501.1	493.0	483.2	472.8	464.7	457.9	452.0	449.0	449.8
165°	511.0	503.4	496.8	491.2	483.6	475.1	469.6	464.9	460.1	458.3	458.3
167.5°	501.9	496.6	492.3	488.9	483.4	477.2	473.0	470.3	466.7	465.8	466.7
170°	495.9	492.1	489.3	487.4	482.7	478.0	475.1	473.3	470.5	469.6	470.5
172.5°	490.6	487.6	486.3	485.9	481.9	478.7	476.6	475.5	473.4	473.3	474.2
175°	484.6	482.7	482.7	483.6	480.8	478.9	478.9	478.0	477.0	477.0	478.0
177.5°	480.4	479.7	479.7	481.2	479.7	478.9	478.9	478.9	478.2	478.9	479.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1218.1	1222.1	1227.4	1236.1	1239.3	1243.4	1249.0	1248.6	1250.2	1256.2	1269.0
5°	1222.7	1238.1	1253.2	1271.2	1290.3	1302.8	1319.8	1330.4	1341.0	1354.4	1377.5
7.5°	1224.5	1249.1	1276.7	1308.3	1336.5	1369.0	1394.4	1418.2	1439.7	1468.4	1495.8
10°	1221.6	1254.7	1290.3	1330.4	1373.0	1409.1	1441.7	1478.8	1510.3	1544.9	1576.0
12.5°	1216.4	1256.3	1303.9	1348.9	1398.6	1452.0	1492.6	1530.1	1572.2	1611.9	1659.8
15°	1204.6	1259.2	1314.8	1374.0	1440.7	1502.3	1560.9	1609.6	1654.7	1714.4	1777.1
17.5°	1189.6	1248.5	1318.7	1390.3	1459.9	1530.4	1603.0	1676.1	1733.1	1807.1	1856.1
20°	1175.5	1243.7	1315.9	1401.1	1470.7	1558.5	1630.7	1701.4	1779.5	1853.2	1911.9
22.5°	1155.8	1230.5	1307.0	1391.9	1483.6	1571.3	1654.7	1731.5	1809.6	1889.7	1960.8
25°	1130.9	1198.5	1289.3	1385.5	1476.8	1572.0	1667.7	1764.0	1848.2	1933.0	1999.1
27.5°	1088.4	1173.8	1258.3	1357.6	1459.1	1566.8	1669.1	1769.9	1858.1	1927.8	1968.8
30°	1066.8	1140.9	1232.7	1332.4	1442.2	1558.0	1664.7	1763.5	1845.7	1901.4	1917.9
32.5°	1034.6	1111.3	1201.0	1304.3	1420.5	1539.5	1650.7	1743.9	1812.4	1841.6	1821.7
35°	987.0	1056.2	1146.9	1252.7	1373.5	1500.3	1610.1	1688.8	1723.9	1696.3	1627.7
37.5°	929.9	998.4	1089.6	1193.4	1318.4	1447.4	1546.6	1603.3	1591.7	1523.1	1420.7
40°	889.8	953.9	1040.7	1152.9	1274.8	1404.1	1491.3	1521.9	1489.8	1391.6	1282.8
42.5°	845.3	907.9	994.9	1103.2	1232.3	1351.5	1427.6	1430.0	1376.3	1258.9	1149.6
45°	777.5	837.2	919.4	1032.2	1151.4	1263.8	1313.8	1289.3	1190.1	1076.8	967.0
47.5°	710.6	762.3	843.4	950.5	1063.8	1158.3	1183.1	1138.9	1033.1	923.1	821.4
50°	661.7	713.8	790.0	892.3	1001.5	1083.3	1095.3	1036.6	932.9	822.1	742.4
52.5°	614.7	666.5	739.9	834.5	934.6	1008.2	1008.7	940.8	837.4	738.7	664.6
55°	545.9	592.5	658.6	743.4	832.6	890.2	876.3	806.1	716.3	630.7	565.9
57.5°	479.6	520.1	581.1	651.8	730.4	777.9	754.6	687.0	606.9	534.2	485.2
60°	436.6	475.2	527.4	594.0	660.2	697.3	675.2	614.1	540.4	481.7	439.1
62.5°	394.9	427.5	477.6	535.5	596.8	624.3	604.6	544.3	480.6	427.6	393.0
65°	335.8	362.4	402.6	452.1	496.8	520.3	503.8	447.6	399.0	360.9	333.4
67.5°	280.7	301.4	331.9	371.6	409.5	422.3	407.3	368.2	327.0	296.4	277.0
70°	242.6	262.2	287.8	318.3	351.4	365.0	349.9	318.8	285.2	257.1	238.1
72.5°	209.3	224.5	246.0	272.2	298.0	311.6	301.3	271.5	243.1	222.3	206.0
75°	159.4	172.5	187.5	206.0	226.1	235.1	226.1	205.6	186.0	170.4	158.9
77.5°	115.9	122.9	134.5	148.4	160.9	167.9	160.0	146.1	134.1	123.5	117.8
80°	88.2	93.2	101.2	112.3	120.8	127.3	122.3	110.7	101.2	94.3	91.7
82.5°	64.2	67.6	72.8	81.0	86.7	90.0	87.8	79.5	75.6	69.4	66.8
85°	31.6	33.6	37.1	39.6	44.6	45.1	45.6	42.1	38.6	37.1	35.1
87.5°	11.4	12.3	13.8	15.2	16.8	18.3	17.9	18.3	17.1	16.4	15.0
90°	2.8	5.7	6.6	7.5	7.5	13.2	13.2	15.1	17.0	16.0	17.0
92.5°	15.6	24.5	35.9	49.7	69.3	117.1	190.1	261.2	298.5	248.6	184.8
95°	33.8	43.3	55.5	78.1	117.6	199.4	353.8	578.7	766.9	788.5	697.2
97.5°	55.7	63.8	75.1	94.4	127.6	190.7	318.0	541.6	807.7	990.6	1030.2
100°	71.5	78.1	89.4	107.3	137.4	192.9	299.3	491.2	756.5	997.4	1134.8
102.5°	88.0	93.9	104.4	121.6	150.1	200.4	294.0	457.3	692.6	940.9	1129.5
105°	112.9	117.6	128.9	145.8	173.1	218.3	296.4	428.1	617.3	838.4	1053.9
107.5°	138.0	142.6	154.7	170.9	197.7	239.2	310.3	422.8	575.1	755.5	946.4
110°	155.2	159.9	171.3	188.2	213.6	255.0	320.8	424.3	560.8	714.2	881.7





TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	171.8	177.3	187.8	204.7	230.2	270.0	332.2	428.9	554.0	690.9	834.2
115°	196.6	203.2	212.6	230.5	255.9	293.6	350.1	437.5	550.4	669.0	786.6
117.5°	221.3	227.2	237.5	254.2	280.6	316.3	368.3	446.8	549.5	659.2	763.3
120°	237.1	243.7	254.0	270.0	296.4	332.2	381.1	453.6	549.5	653.9	752.7
122.5°	252.1	258.7	268.3	285.9	311.4	347.2	393.1	460.3	548.7	647.9	743.8
125°	273.8	279.5	289.8	307.6	334.0	367.9	411.2	470.5	547.6	638.0	728.3
127.5°	290.6	297.4	309.2	327.8	354.4	387.1	426.8	478.5	545.5	624.6	709.5
130°	301.1	308.6	322.7	340.6	367.9	399.9	436.6	484.6	544.8	616.3	694.5
132.5°	310.1	319.9	333.3	352.7	378.4	410.5	446.4	489.8	544.0	608.8	678.6
135°	324.6	334.0	350.1	369.8	394.3	425.3	459.2	497.8	542.9	597.5	656.8
137.5°	338.2	348.6	363.7	384.3	407.6	436.6	468.3	502.5	542.7	587.7	637.1
140°	347.2	357.6	373.5	393.3	415.9	444.1	474.2	506.2	542.0	582.5	625.8
142.5°	357.8	367.3	382.6	401.6	423.4	450.9	478.7	509.3	542.0	578.0	615.2
145°	372.6	382.0	395.2	413.1	433.8	458.3	483.6	511.0	540.1	570.2	600.3
147.5°	387.5	395.8	409.3	424.1	442.8	465.8	488.0	511.9	536.7	563.3	588.1
150°	398.0	405.6	416.9	430.9	448.8	469.6	490.2	511.9	534.4	558.0	580.6
152.5°	407.1	414.6	425.1	437.7	454.1	472.6	491.7	510.4	530.7	552.0	572.3
155°	421.5	427.2	436.6	447.0	461.1	477.0	493.0	508.1	525.1	542.9	559.9
157.5°	433.9	439.2	446.6	455.6	466.7	480.2	493.0	505.7	519.2	533.7	546.5
160°	442.2	446.0	452.6	460.1	470.5	481.7	493.0	503.4	514.7	527.0	538.2
162.5°	449.0	452.0	457.9	464.7	472.8	483.2	493.0	501.1	510.2	520.9	529.9
165°	458.3	460.1	464.9	469.6	475.1	483.6	491.2	496.8	503.4	511.0	518.5
167.5°	465.8	466.7	470.3	473.0	477.2	483.4	488.9	492.3	496.6	501.9	507.4
170°	469.6	470.5	473.3	475.1	478.0	482.7	487.4	489.3	492.1	495.9	500.6
172.5°	473.3	473.4	475.5	476.6	478.7	481.9	485.9	486.3	487.6	490.6	494.6
175°	477.0	477.0	478.0	478.9	478.9	480.8	483.6	482.7	482.7	484.6	486.4
177.5°	478.9	478.2	478.9	478.9	478.9	479.7	481.2	479.7	479.7	480.4	481.2
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1275.4	1276.3	1279.9	1282.7	1283.5	1287.5	1287.9
5°	1387.5	1396.1	1412.6	1414.1	1416.6	1429.6	1419.7
7.5°	1518.9	1540.5	1555.0	1567.7	1572.3	1578.0	1576.9
10°	1603.1	1635.2	1651.2	1676.8	1677.8	1684.3	1680.3
12.5°	1687.7	1725.0	1754.3	1759.0	1780.5	1783.8	1789.4
15°	1807.6	1847.2	1887.8	1902.3	1931.9	1939.0	1950.0
17.5°	1920.3	1960.8	1989.2	2026.8	2039.0	2055.2	2044.2
20°	1982.1	2026.2	2062.3	2091.9	2104.4	2113.4	2112.4
22.5°	2019.4	2063.9	2093.1	2115.5	2127.2	2131.1	2130.8
25°	2042.7	2068.3	2077.3	2085.8	2072.8	2068.3	2070.3
27.5°	1977.7	1971.1	1947.6	1916.7	1884.6	1859.2	1845.3
30°	1888.3	1849.3	1813.6	1751.4	1719.4	1700.3	1683.3
32.5°	1761.6	1699.7	1631.2	1574.2	1537.8	1509.5	1505.2
35°	1544.5	1451.2	1367.5	1297.8	1261.7	1231.1	1224.1
37.5°	1313.1	1216.2	1140.9	1079.5	1040.7	1019.1	998.9
40°	1159.4	1076.3	1002.0	949.9	920.4	904.8	892.3
42.5°	1041.1	965.2	891.4	851.7	824.9	815.4	808.0
45°	877.7	807.1	755.9	725.9	710.3	694.3	686.7
47.5°	746.9	689.4	655.6	630.1	613.5	604.0	599.2
50°	672.7	625.6	595.5	576.0	560.9	553.4	549.4
52.5°	606.9	568.3	543.0	527.4	517.3	511.7	510.1
55°	522.8	493.2	477.2	463.7	456.2	451.2	449.1
57.5°	454.5	431.7	418.7	407.6	404.6	400.4	399.0
60°	409.5	392.0	381.0	373.4	371.0	365.9	366.9
62.5°	369.9	355.5	346.1	341.8	338.5	334.2	335.6
65°	312.8	302.3	297.3	293.2	289.3	286.7	288.7
67.5°	262.5	255.2	248.5	246.1	244.1	243.7	241.6
70°	229.6	223.6	217.5	216.0	216.0	214.1	213.6
72.5°	197.9	193.5	189.5	188.4	186.8	187.6	185.5
75°	152.9	149.4	147.9	146.4	145.9	145.9	144.4
77.5°	113.0	110.4	108.0	108.0	106.1	105.5	105.3
80°	85.7	84.7	82.8	82.8	81.7	82.2	81.2
82.5°	64.5	63.1	62.7	61.8	60.4	60.5	59.6
85°	34.6	33.1	32.6	31.1	30.1	31.1	30.1
87.5°	15.6	15.4	15.0	14.4	14.1	13.9	12.8
90°	17.9	18.9	18.9	19.8	20.7	19.8	19.8
92.5°	139.1	110.7	91.8	80.8	75.7	72.5	72.5
95°	551.4	425.3	334.0	287.9	258.7	241.9	229.6
97.5°	975.9	883.9	785.7	718.1	661.5	633.3	613.7
100°	1153.6	1107.5	1037.8	956.0	898.6	870.3	862.9
102.5°	1222.9	1236.2	1207.2	1157.0	1115.4	1085.7	1079.7
105°	1216.6	1309.8	1348.4	1350.3	1342.7	1329.6	1323.9
107.5°	1119.7	1250.9	1334.8	1381.3	1402.8	1412.2	1414.7
110°	1044.4	1180.9	1284.4	1351.2	1390.7	1407.7	1416.2



TEST NUMBER: P332609-830

CATALOG NUMBER: SA4XXDIP-C795D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	978.2	1107.1	1210.6	1286.5	1334.3	1358.0	1371.7
115°	902.4	1012.5	1102.8	1177.1	1233.6	1263.7	1271.2
117.5°	859.1	945.7	1022.3	1085.7	1133.1	1163.6	1169.4
120°	840.3	915.6	982.3	1035.9	1077.4	1101.8	1112.2
122.5°	828.2	896.7	955.3	1000.6	1035.9	1056.7	1067.1
125°	809.2	874.1	925.9	963.6	990.8	1008.7	1014.4
127.5°	786.8	851.6	900.7	938.5	962.8	977.8	983.4
130°	768.7	832.7	882.6	921.1	944.7	959.8	965.4
132.5°	748.5	810.9	860.8	898.6	925.1	939.4	945.1
135°	717.9	775.3	822.4	860.1	886.4	901.4	907.1
137.5°	688.8	737.2	779.7	814.8	840.8	853.3	860.1
140°	670.0	712.3	751.8	784.8	805.5	818.6	826.1
142.5°	654.1	690.5	724.7	753.8	773.1	784.8	790.0
145°	632.4	660.5	686.9	710.4	726.4	735.8	740.6
147.5°	613.5	636.1	656.8	674.1	687.9	695.0	696.6
150°	602.2	621.0	638.0	653.0	665.2	670.9	671.8
152.5°	590.9	608.2	622.2	635.0	644.9	648.3	649.2
155°	575.0	589.0	600.3	609.7	617.3	620.1	620.1
157.5°	559.1	571.0	580.0	587.1	592.8	594.5	594.5
160°	548.6	558.9	566.5	572.1	577.8	578.7	578.7
162.5°	538.8	546.9	553.6	557.8	563.5	564.4	563.6
165°	524.1	530.7	535.4	539.1	542.9	542.0	541.0
167.5°	511.7	517.0	519.8	521.7	524.1	524.0	523.2
170°	503.4	507.2	510.0	511.9	512.8	511.9	511.9
172.5°	496.6	498.9	501.0	502.1	503.0	502.1	500.6
175°	487.4	489.3	489.3	489.3	491.2	489.3	487.4
177.5°	481.9	481.9	482.7	481.9	482.7	481.2	479.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9

(END OF REPORT)