

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332984-830

Luminaire Tested: **SA4XXRDIP-C1020D1205U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332984-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1205U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7989.7 lumens
Efficiency: N/A
Efficacy: 122.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332984-830
CATALOG NUMBER: SA4XXRDIP-C1020D1205U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332984-830

CATALOG NUMBER: SA4XXRDIP-C1020D1205U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49	49	49
1	98	94	90	86	90	87	83	80	73	71	69	61	59	58	49	48	47	42	42	42
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36	36	36
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35	30	30	30
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	32	30	26	26	26
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23	23	23
6	63	51	43	38	58	48	41	36	41	36	31	35	30	27	29	26	23	20	20	20
7	59	47	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18	18	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16	16	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	19	22	19	17	15	15	15
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P332984-830

CATALOG NUMBER: SA4XXRDIP-C1020D1205U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	2.0
10°-20°	445.8	5.6
20°-30°	643.8	8.1
30°-40°	729.7	9.1
40°-50°	704.7	8.8
50°-60°	586.0	7.3
60°-70°	404.6	5.1
70°-80°	205.1	2.6
80°-90°	55.7	0.7
90°-100°	402.7	5.0
100°-110°	838.0	10.5
110°-120°	750.6	9.4
120°-130°	631.4	7.9
130°-140°	526.5	6.6
140°-150°	402.2	5.0
150°-160°	282.7	3.5
160°-170°	166.3	2.1
170°-180°	54.1	0.7
0°-30°	1249.5	15.6
0°-40°	1979.2	24.8
0°-60°	3269.8	40.9
0°-90°	3935.3	49.3
90°-120°	1991.3	24.9
90°-150°	3551.4	44.4
90°-180°	4054.0	50.7
0°-180°	7989.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	1	9	20	22	23	5
95°	36	114	893	442	267	40
105°	128	186	718	1547	1541	137
115°	226	283	641	1231	1480	224
125°	314	374	637	1048	1181	280
135°	373	445	632	930	1056	289
145°	430	493	629	784	862	270
155°	490	528	611	692	722	226
165°	533	550	586	620	630	151
175°	556	558	562	570	567	53
180°	558	558	558	558	558	



TEST NUMBER: P332984-830

CATALOG NUMBER: SA4XXRDIP-C1020D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.2	22.8	21.6	20.0	18.3	17.2	18.4	18.1	18.3	18.6	18.1
90°	1.1	3.3	6.6	7.6	8.8	8.8	15.4	15.4	17.5	19.7	18.7
92.5°	12.4	18.2	28.5	41.8	57.9	80.6	136.3	221.2	304.1	347.4	289.4
95°	36.1	39.4	50.4	64.7	90.9	137.0	232.1	411.8	673.5	892.6	917.8
97.5°	64.8	64.8	74.3	87.4	110.0	148.5	221.9	370.2	630.4	940.2	1153.1
100°	83.2	83.2	90.9	104.1	124.9	159.9	224.5	348.3	571.7	880.5	1160.9
102.5°	100.8	102.5	109.3	121.6	141.5	174.8	233.3	342.1	532.3	806.1	1095.2
105°	128.2	131.4	137.0	150.1	169.8	201.5	254.1	345.0	498.3	718.5	975.8
107.5°	158.3	160.5	166.1	180.0	198.9	230.3	278.4	361.2	492.2	669.4	879.5
110°	178.5	180.7	186.2	199.3	219.0	248.6	296.8	373.4	494.0	652.8	831.3



TEST NUMBER: P332984-830

CATALOG NUMBER: SA4XXRDIP-C1020D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	197.8	200.0	206.3	218.6	238.4	267.9	314.3	386.6	499.2	644.9	804.1
115°	225.6	228.9	236.6	247.5	268.3	297.9	341.7	407.5	509.3	640.7	778.7
117.5°	254.5	257.6	264.4	276.4	296.0	326.6	368.3	428.7	520.0	639.6	767.3
120°	273.8	276.0	283.7	295.7	314.3	345.0	386.6	443.6	527.9	639.6	761.2
122.5°	291.3	293.5	301.2	312.4	332.7	362.5	404.2	457.6	535.8	638.8	754.2
125°	314.3	318.7	325.3	337.3	358.2	388.8	428.2	478.6	547.6	637.4	742.5
127.5°	334.7	338.2	346.1	359.9	381.5	412.5	450.5	496.8	557.0	635.0	727.0
130°	346.1	350.4	359.2	375.7	396.4	428.2	465.5	508.2	564.0	634.1	717.4
132.5°	357.5	361.0	372.4	388.0	410.5	440.5	477.8	519.6	570.1	633.3	708.6
135°	373.4	377.9	388.8	407.5	430.5	458.9	495.0	534.5	579.4	632.0	695.5
137.5°	389.5	393.6	405.7	423.4	447.3	474.5	508.2	545.0	584.8	631.7	684.1
140°	400.9	404.2	416.2	434.8	457.8	484.1	517.0	552.0	589.3	630.8	678.0
142.5°	413.1	416.4	427.5	445.4	467.4	492.9	524.8	557.2	592.8	630.8	672.7
145°	430.5	433.8	444.7	460.0	480.8	504.9	533.4	563.0	594.7	628.7	663.7
147.5°	449.9	451.0	460.6	476.5	493.7	515.4	542.2	568.0	595.8	624.7	655.6
150°	462.2	463.3	472.0	485.2	501.6	522.5	546.5	570.6	595.8	622.1	649.5
152.5°	473.5	473.8	482.6	494.8	509.5	528.6	550.1	572.4	594.1	617.7	642.4
155°	489.6	490.7	497.2	508.2	520.3	536.7	555.3	573.9	591.4	611.1	632.0
157.5°	505.1	505.1	511.2	519.8	530.3	543.3	559.0	573.9	588.6	604.4	621.2
160°	514.7	514.7	519.2	526.8	535.6	547.6	560.7	573.9	586.0	599.1	613.3
162.5°	523.5	522.6	526.1	532.9	540.8	550.3	562.5	573.9	583.3	593.8	606.3
165°	533.4	533.4	535.6	541.0	546.5	553.1	563.0	571.7	578.2	586.0	594.7
167.5°	543.3	542.2	543.3	547.4	550.4	555.5	562.7	569.1	573.1	578.1	584.2
170°	547.6	546.5	547.6	550.9	553.1	556.4	561.8	567.3	569.5	572.8	577.2
172.5°	552.0	550.9	551.1	553.6	554.9	557.2	561.0	565.6	566.0	567.5	571.1
175°	556.4	555.3	555.3	556.4	557.5	557.5	559.7	563.0	561.8	561.8	564.0
177.5°	558.4	557.5	556.6	557.5	557.5	557.5	558.4	560.1	558.4	558.4	559.2
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332984-830

CATALOG NUMBER: SA4XXRDIP-C1020D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	18.1	18.1	18.0	18.0	18.5	18.9	18.9	19.2
90°	19.7	20.8	21.9	21.9	23.0	24.1	23.0	23.0
92.5°	215.1	161.8	128.8	106.9	94.0	88.0	84.4	84.4
95°	811.5	641.8	495.0	388.8	335.2	301.2	281.4	267.2
97.5°	1199.1	1136.0	1028.9	914.5	835.8	770.0	737.1	714.4
100°	1320.9	1342.7	1289.1	1208.1	1112.8	1045.9	1013.1	1004.4
102.5°	1314.8	1423.3	1438.9	1405.1	1346.7	1298.3	1263.7	1256.7
105°	1226.6	1416.2	1524.6	1569.4	1571.7	1562.9	1547.6	1541.0
107.5°	1101.5	1303.3	1456.0	1553.7	1607.8	1632.8	1643.7	1646.6
110°	1026.2	1215.7	1374.5	1495.0	1572.7	1618.7	1638.5	1648.3



TEST NUMBER: P332984-830

CATALOG NUMBER: SA4XXRDIP-C1020D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	971.0	1138.6	1288.6	1409.1	1497.4	1553.0	1580.6	1596.7
115°	915.6	1050.4	1178.5	1283.6	1370.2	1435.9	1470.9	1479.7
117.5°	888.4	999.9	1100.7	1189.9	1263.7	1318.9	1354.3	1361.1
120°	876.2	978.1	1065.6	1143.4	1205.9	1254.1	1282.5	1294.6
122.5°	865.6	964.0	1043.8	1111.9	1164.7	1205.9	1229.9	1242.0
125°	847.7	941.9	1017.5	1077.7	1121.5	1153.3	1174.1	1180.6
127.5°	825.8	915.9	991.2	1048.4	1092.4	1120.7	1138.2	1144.7
130°	808.3	894.8	969.3	1027.4	1072.2	1099.6	1117.1	1123.7
132.5°	789.9	871.2	943.9	1001.9	1045.9	1076.9	1093.4	1100.0
135°	764.5	835.7	902.5	957.2	1001.1	1031.7	1049.2	1055.8
137.5°	741.5	801.7	858.0	907.5	948.5	978.7	993.2	1001.1
140°	728.3	779.8	829.1	875.1	913.4	937.5	952.8	961.6
142.5°	716.0	761.4	803.7	843.6	877.5	899.8	913.4	919.5
145°	698.8	736.0	768.8	799.6	826.9	845.6	856.5	862.0
147.5°	684.6	714.1	740.4	764.5	784.7	800.6	809.0	810.9
150°	675.8	701.0	722.8	742.5	760.1	774.3	780.9	782.0
152.5°	666.1	687.8	707.9	724.2	739.0	750.6	754.6	755.7
155°	651.7	669.2	685.6	698.8	709.7	718.5	721.8	721.8
157.5°	636.1	650.8	664.6	675.1	683.4	690.0	692.0	692.0
160°	626.5	638.5	650.5	659.3	665.9	672.5	673.5	673.5
162.5°	616.8	627.2	636.6	644.4	649.2	655.8	657.0	656.0
165°	603.5	610.0	617.7	623.2	627.5	632.0	630.8	629.8
167.5°	590.6	595.6	601.7	605.0	607.2	610.0	609.8	609.0
170°	582.7	586.0	590.3	593.6	595.8	596.9	595.8	595.8
172.5°	575.6	578.1	580.7	583.1	584.4	585.5	584.4	582.7
175°	566.3	567.3	569.5	569.5	569.5	571.7	569.5	567.3
177.5°	560.1	561.0	561.0	561.8	561.0	561.8	560.1	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5

(END OF REPORT)