

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332677-840

Luminaire Tested: **SA4XXDIP-C1195D365U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332677-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D365U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6445.8 lumens
Efficiency: N/A
Efficacy: 129.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332677-840
CATALOG NUMBER: SA4XXDIP-C1195D365U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332677-840

CATALOG NUMBER: SA4XXDIP-C1195D365U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	92	92	92	84	84	84	80
1	104	100	96	92	100	96	92	89	88	85	82	81	78	76	74	72	71	67
2	95	87	81	75	91	84	78	73	77	72	68	71	67	64	65	62	60	56
3	87	77	69	63	83	74	67	61	68	62	57	63	58	54	58	54	51	48
4	80	68	60	53	76	66	58	52	61	54	49	56	51	46	52	47	44	41
5	73	61	52	46	70	59	51	45	54	48	43	50	45	40	47	42	38	36
6	68	55	46	40	64	53	45	39	49	42	37	46	40	35	42	37	34	31
7	63	50	41	35	60	48	40	35	45	38	33	42	36	31	39	34	30	28
8	58	45	37	32	56	44	36	31	41	34	30	38	32	28	36	31	27	25
9	54	42	34	28	52	40	33	28	38	31	27	35	30	25	33	28	24	22
10	51	38	31	26	49	37	30	25	35	28	24	33	27	23	31	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332677-840

CATALOG NUMBER: SA4XXDIP-C1195D365U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	2.9
10°-20°	534.0	8.3
20°-30°	786.0	12.2
30°-40°	913.7	14.2
40°-50°	913.7	14.2
50°-60°	799.3	12.4
60°-70°	593.6	9.2
70°-80°	337.2	5.2
80°-90°	98.7	1.5
90°-100°	30.4	0.5
100°-110°	90.2	1.4
110°-120°	153.0	2.4
120°-130°	201.8	3.1
130°-140°	226.6	3.5
140°-150°	222.7	3.5
150°-160°	187.3	2.9
160°-170°	124.6	1.9
170°-180°	43.6	0.7
0°-30°	1509.5	23.4
0°-40°	2423.2	37.6
0°-60°	4136.2	64.2
0°-90°	5165.7	80.1
90°-120°	273.6	4.2
90°-150°	924.6	14.3
90°-180°	1280.0	19.9
0°-180°	6445.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	1	5	8	10	11	6
95°	21	25	27	28	28	24
105°	83	84	85	86	87	88
115°	156	156	155	154	154	153
125°	227	227	226	226	225	202
135°	292	294	294	294	293	226
145°	355	356	357	356	356	222
155°	407	407	406	408	406	187
165°	443	442	441	443	442	125
175°	461	459	459	461	459	44
180°	461	461	461	461	461	



TEST NUMBER: P332677-840

CATALOG NUMBER: SA4XXDIP-C1195D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	33.7	33.6	33.5	33.4	33.3	33.1	33.0	32.8	32.7	32.5	32.6
90°	1.1	1.9	2.8	3.7	4.5	5.4	6.0	6.6	7.2	7.9	8.3
92.5°	7.7	8.7	9.6	10.6	11.6	12.3	12.8	13.2	13.7	14.1	14.4
95°	21.4	22.1	22.8	23.5	24.2	24.9	25.4	26.1	26.6	27.2	27.4
97.5°	37.4	38.0	38.6	39.1	39.7	40.3	40.9	41.6	42.2	42.9	43.2
100°	50.0	50.3	50.6	50.9	51.2	51.7	52.4	53.2	53.9	54.6	54.7
102.5°	63.1	63.2	63.3	63.5	63.6	64.0	64.6	65.3	65.9	66.6	66.9
105°	83.1	83.2	83.3	83.4	83.4	83.6	84.0	84.3	84.6	84.9	85.1
107.5°	104.2	104.3	104.4	104.5	104.6	104.6	104.7	104.7	104.8	104.8	105.0
110°	118.5	118.7	118.8	119.0	119.1	119.2	119.1	119.0	118.9	118.9	118.7



TEST NUMBER: P332677-840

CATALOG NUMBER: SA4XXDIP-C1195D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	133.3	133.3	133.4	133.4	133.4	133.4	133.2	133.1	133.0	132.8	132.8
115°	155.6	155.6	155.6	155.6	155.6	155.5	155.3	155.2	155.0	154.9	154.8
117.5°	176.5	176.6	176.7	176.7	176.8	176.8	176.7	176.6	176.4	176.3	176.1
120°	190.6	190.9	191.2	191.5	191.9	191.9	191.7	191.4	191.2	191.0	190.6
122.5°	205.1	205.2	205.4	205.5	205.6	205.6	205.5	205.4	205.3	205.2	204.9
125°	226.6	226.6	226.6	226.6	226.6	226.5	226.5	226.4	226.3	226.2	226.1
127.5°	246.1	246.3	246.6	246.8	247.0	247.1	247.0	246.8	246.7	246.6	246.4
130°	259.8	260.0	260.2	260.5	260.7	260.8	260.8	260.8	260.8	260.8	260.7
132.5°	273.8	274.0	274.1	274.3	274.5	274.5	274.5	274.4	274.4	274.3	274.1
135°	292.3	292.8	293.2	293.7	294.2	294.4	294.4	294.4	294.4	294.4	294.3
137.5°	312.4	312.7	312.9	313.1	313.3	313.5	313.6	313.7	313.9	314.0	313.8
140°	325.8	326.0	326.1	326.3	326.5	326.5	326.5	326.5	326.5	326.5	326.5
142.5°	338.1	338.2	338.4	338.5	338.7	338.8	338.7	338.6	338.6	338.5	338.5
145°	355.1	355.4	355.7	356.0	356.4	356.6	356.6	356.7	356.8	356.9	356.8
147.5°	371.9	372.3	372.6	373.0	373.4	373.5	373.5	373.4	373.4	373.3	373.2
150°	382.2	382.5	382.8	383.1	383.4	383.6	383.6	383.6	383.6	383.6	383.6
152.5°	391.9	392.1	392.2	392.4	392.6	392.7	392.8	392.9	392.9	393.0	393.2
155°	406.8	406.8	406.8	406.8	406.8	406.8	406.7	406.6	406.6	406.5	406.8
157.5°	419.4	419.2	419.1	419.0	418.8	418.7	418.7	418.7	418.7	418.7	418.9
160°	426.8	426.7	426.7	426.6	426.5	426.4	426.4	426.3	426.2	426.1	426.4
162.5°	433.6	433.4	433.2	433.0	432.8	432.7	432.6	432.5	432.4	432.3	432.8
165°	442.8	442.6	442.4	442.1	441.9	441.7	441.5	441.4	441.2	441.1	441.5
167.5°	449.9	449.6	449.3	448.9	448.6	448.4	448.5	448.5	448.5	448.5	449.0
170°	453.9	453.5	453.1	452.7	452.3	452.2	452.2	452.3	452.4	452.5	452.9
172.5°	456.8	456.5	456.1	455.8	455.4	455.2	455.2	455.3	455.3	455.3	455.9
175°	460.7	460.3	459.9	459.5	459.1	458.9	458.8	458.7	458.7	458.6	459.1
177.5°	462.0	461.7	461.3	461.0	460.7	460.6	460.6	460.6	460.6	460.6	461.0
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P332677-840
 CATALOG NUMBER: SA4XXDIP-C1195D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	32.7	32.8	32.9	33.0	33.0	33.0	33.0	33.1
90°	8.8	9.3	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	14.7	14.9	15.2	15.5	15.6	15.7	15.8	15.9
95°	27.6	27.9	28.1	28.2	28.2	28.2	28.2	28.2
97.5°	43.4	43.7	44.0	44.1	44.1	44.1	44.1	44.1
100°	54.9	55.0	55.2	55.3	55.3	55.3	55.3	55.3
102.5°	67.1	67.3	67.5	67.7	67.7	67.8	67.8	67.9
105°	85.4	85.6	85.8	86.1	86.3	86.6	86.8	87.1
107.5°	105.3	105.5	105.7	105.8	105.8	105.8	105.8	105.7
110°	118.6	118.4	118.2	118.3	118.5	118.8	119.0	119.2



TEST NUMBER: P332677-840

CATALOG NUMBER: SA4XXDIP-C1195D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	132.8	132.7	132.7	132.7	132.8	132.8	132.8	132.9
115°	154.7	154.6	154.5	154.5	154.4	154.3	154.2	154.2
117.5°	175.8	175.5	175.3	175.1	174.9	174.7	174.6	174.4
120°	190.2	189.8	189.3	189.2	189.3	189.6	189.7	189.9
122.5°	204.7	204.4	204.1	203.8	203.6	203.3	203.0	202.7
125°	225.9	225.8	225.6	225.4	225.3	225.1	225.0	224.8
127.5°	246.3	246.1	245.9	245.8	245.7	245.6	245.4	245.3
130°	260.5	260.3	260.2	259.9	259.6	259.3	259.0	258.7
132.5°	274.0	273.8	273.7	273.5	273.4	273.3	273.2	273.0
135°	294.1	294.0	293.8	293.6	293.4	293.1	292.9	292.7
137.5°	313.6	313.4	313.2	313.1	313.1	313.2	313.2	313.3
140°	326.4	326.3	326.2	326.1	326.1	326.0	325.9	325.8
142.5°	338.5	338.5	338.4	338.4	338.4	338.4	338.4	338.4
145°	356.7	356.6	356.6	356.4	356.2	355.9	355.7	355.5
147.5°	373.2	373.1	373.0	373.0	372.9	372.8	372.7	372.7
150°	383.6	383.6	383.6	383.5	383.5	383.4	383.3	383.2
152.5°	393.4	393.6	393.8	393.7	393.5	393.3	393.1	392.9
155°	407.1	407.4	407.7	407.7	407.4	407.1	406.8	406.5
157.5°	419.1	419.4	419.6	419.6	419.3	419.1	418.8	418.5
160°	426.6	426.8	427.1	427.0	426.6	426.2	425.8	425.4
162.5°	433.2	433.6	434.0	434.0	433.7	433.3	432.9	432.5
165°	442.0	442.5	442.9	443.0	442.7	442.4	442.1	441.8
167.5°	449.5	449.9	450.4	450.4	449.9	449.4	448.9	448.4
170°	453.4	453.9	454.4	454.3	453.8	453.2	452.7	452.1
172.5°	456.5	457.0	457.5	457.5	457.0	456.4	455.9	455.2
175°	459.7	460.2	460.8	460.8	460.2	459.7	459.1	458.6
177.5°	461.4	461.9	462.3	462.3	461.8	461.3	460.8	460.3
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4

(END OF REPORT)