

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332960-830

Luminaire Tested: **SA4XXRDIP-C1020D365U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332960-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D365U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5166.3 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332960-830

CATALOG NUMBER: SA4XXRDIP-C1020D365U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332960-830

CATALOG NUMBER: SA4XXRDIP-C1020D365U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	76				76
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69				65	
2	95	88	81	76	90	84	78	73	76	72	68	70	66	63	63	61	58				55	
3	87	77	70	64	83	74	67	62	68	62	58	62	58	54	57	53	50				47	
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	51	47	44				41	
5	74	62	53	47	70	59	52	46	54	48	43	50	45	41	46	42	38				36	
6	68	56	47	41	65	53	46	40	49	43	38	45	40	36	42	37	34				31	
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	38	34	30				28	
8	59	46	38	33	56	44	37	32	41	35	30	38	33	29	35	31	27				25	
9	55	42	35	29	52	41	34	29	38	32	27	35	30	26	33	28	25				23	
10	51	39	32	27	49	38	31	26	35	29	25	33	27	24	30	26	23				21	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P332960-830

CATALOG NUMBER: SA4XXRDIP-C1020D365U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	3.1
10°-20°	445.8	8.6
20°-30°	643.8	12.5
30°-40°	729.7	14.1
40°-50°	704.7	13.6
50°-60°	586.0	11.3
60°-70°	404.6	7.8
70°-80°	205.1	4.0
80°-90°	53.6	1.0
90°-100°	122.5	2.4
100°-110°	254.9	4.9
110°-120°	228.3	4.4
120°-130°	192.0	3.7
130°-140°	160.1	3.1
140°-150°	122.3	2.4
150°-160°	86.0	1.7
160°-170°	50.6	1.0
170°-180°	16.5	0.3
0°-30°	1249.5	24.2
0°-40°	1979.2	38.3
0°-60°	3269.8	63.3
0°-90°	3933.1	76.1
90°-120°	605.7	11.7
90°-150°	1080.2	20.9
90°-180°	1233.0	23.9
0°-180°	5166.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	0	3	6	7	7	4
95°	11	35	272	134	81	12
105°	39	56	218	471	469	42
115°	69	86	195	374	450	68
125°	96	114	194	319	359	85
135°	114	135	192	283	321	88
145°	131	150	191	238	262	82
155°	149	161	186	210	220	69
165°	162	167	178	189	192	46
175°	169	170	171	173	173	16
180°	170	170	170	170	170	



TEST NUMBER: P332960-830

CATALOG NUMBER: SA4XXRDIP-C1020D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.0	22.3	20.6	18.9	17.1	16.0	16.2	16.0	15.9	15.8	15.5
90°	0.4	1.0	2.0	2.4	2.6	2.6	4.6	4.6	5.4	6.0	5.7
92.5°	3.8	5.6	8.7	12.7	17.6	24.5	41.5	67.3	92.5	105.7	88.0
95°	11.0	12.0	15.4	19.7	27.6	41.7	70.6	125.3	204.9	271.5	279.2
97.5°	19.7	19.7	22.6	26.6	33.5	45.1	67.5	112.6	191.7	286.0	350.7
100°	25.4	25.4	27.6	31.7	38.0	48.6	68.3	105.9	173.9	267.9	353.1
102.5°	30.6	31.2	33.3	36.9	43.1	53.2	71.0	104.1	161.9	245.2	333.1
105°	39.0	40.0	41.7	45.6	51.7	61.3	77.3	104.9	151.6	218.5	296.8
107.5°	48.2	48.8	50.5	54.8	60.5	70.0	84.6	109.9	149.7	203.6	267.5
110°	54.3	55.0	56.6	60.6	66.6	75.6	90.3	113.6	150.2	198.5	252.9



TEST NUMBER: P332960-830

CATALOG NUMBER: SA4XXRDIP-C1020D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	60.1	60.8	62.8	66.4	72.5	81.4	95.6	117.6	151.8	196.1	244.6
115°	68.6	69.7	71.9	75.3	81.6	90.6	104.0	123.9	154.9	194.9	236.9
117.5°	77.4	78.3	80.4	84.1	90.0	99.3	112.0	130.4	158.2	194.5	233.4
120°	83.3	84.0	86.2	89.9	95.6	104.9	117.6	134.9	160.6	194.5	231.5
122.5°	88.6	89.3	91.6	95.0	101.2	110.3	122.9	139.2	163.0	194.3	229.4
125°	95.6	96.9	99.0	102.6	109.0	118.3	130.3	145.5	166.5	193.9	225.8
127.5°	101.8	102.8	105.3	109.4	116.0	125.5	137.0	151.1	169.5	193.1	221.1
130°	105.3	106.6	109.2	114.2	120.6	130.3	141.6	154.6	171.5	192.8	218.2
132.5°	108.8	109.8	113.3	118.0	124.9	133.9	145.3	158.1	173.4	192.7	215.6
135°	113.6	114.9	118.3	123.9	130.9	139.6	150.5	162.6	176.3	192.2	211.5
137.5°	118.5	119.7	123.4	128.8	136.0	144.3	154.6	165.8	177.9	192.2	208.1
140°	122.0	122.9	126.6	132.2	139.2	147.2	157.2	167.9	179.2	191.9	206.2
142.5°	125.6	126.7	130.1	135.4	142.1	149.9	159.7	169.5	180.3	191.9	204.6
145°	130.9	132.0	135.3	139.9	146.3	153.5	162.2	171.3	180.9	191.2	201.9
147.5°	136.9	137.1	140.2	144.9	150.1	156.7	164.9	172.8	181.3	190.0	199.4
150°	140.5	140.9	143.5	147.6	152.6	158.9	166.3	173.5	181.3	189.2	197.6
152.5°	144.0	144.1	146.8	150.5	155.0	160.8	167.3	174.1	180.7	187.8	195.4
155°	148.9	149.2	151.3	154.6	158.3	163.2	168.9	174.6	179.9	185.9	192.2
157.5°	153.6	153.6	155.5	158.1	161.3	165.2	170.0	174.6	179.0	183.8	189.0
160°	156.6	156.6	157.9	160.2	162.9	166.5	170.6	174.6	178.2	182.2	186.5
162.5°	159.2	159.0	160.0	162.1	164.5	167.4	171.1	174.6	177.4	180.6	184.5
165°	162.2	162.2	162.9	164.6	166.3	168.2	171.3	173.9	175.9	178.2	180.9
167.5°	165.2	164.9	165.2	166.5	167.4	169.0	171.2	173.1	174.3	175.8	177.7
170°	166.5	166.3	166.5	167.6	168.2	169.2	170.9	172.6	173.2	174.2	175.6
172.5°	167.9	167.6	167.6	168.3	168.7	169.5	170.6	172.0	172.2	172.6	173.7
175°	169.2	168.9	168.9	169.2	169.6	169.6	170.2	171.3	170.9	170.9	171.5
177.5°	169.8	169.6	169.3	169.6	169.6	169.6	169.8	170.3	169.8	169.8	170.1
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6



TEST NUMBER: P332960-830

CATALOG NUMBER: SA4XXRDIP-C1020D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	15.4	15.2	15.0	15.0	15.3	15.6	15.7	16.0
90°	6.0	6.3	6.7	6.7	7.0	7.4	7.0	7.0
92.5°	65.4	49.2	39.2	32.5	28.6	26.8	25.6	25.6
95°	246.9	195.2	150.5	118.3	101.9	91.6	85.6	81.2
97.5°	364.7	345.5	312.9	278.1	254.2	234.2	224.2	217.3
100°	401.7	408.4	392.1	367.4	338.5	318.1	308.1	305.5
102.5°	399.9	432.9	437.6	427.3	409.6	394.9	384.4	382.2
105°	373.1	430.7	463.7	477.4	478.1	475.3	470.7	468.7
107.5°	335.1	396.4	442.8	472.6	489.0	496.6	499.9	500.8
110°	312.2	369.8	418.1	454.7	478.3	492.4	498.3	501.3



TEST NUMBER: P332960-830

CATALOG NUMBER: SA4XXRDIP-C1020D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	295.3	346.3	391.9	428.6	455.4	472.4	480.8	485.6
115°	278.5	319.4	358.4	390.4	416.7	436.7	447.4	450.1
117.5°	270.2	304.2	334.8	361.9	384.4	401.1	411.9	414.0
120°	266.5	297.5	324.1	347.8	366.7	381.4	390.1	393.8
122.5°	263.3	293.2	317.4	338.2	354.2	366.7	374.1	377.8
125°	257.9	286.4	309.4	327.8	341.1	350.8	357.1	359.1
127.5°	251.2	278.5	301.5	318.9	332.2	340.8	346.2	348.2
130°	245.8	272.2	294.8	312.5	326.1	334.4	339.8	341.8
132.5°	240.3	264.9	287.1	304.7	318.1	327.5	332.6	334.6
135°	232.5	254.2	274.5	291.2	304.4	313.8	319.1	321.1
137.5°	225.6	243.8	261.0	276.0	288.5	297.7	302.1	304.4
140°	221.5	237.1	252.1	266.2	277.9	285.1	289.8	292.5
142.5°	217.8	231.6	244.4	256.6	266.9	273.7	277.9	279.7
145°	212.5	223.9	233.8	243.2	251.5	257.1	260.5	262.1
147.5°	208.2	217.2	225.2	232.5	238.7	243.6	246.0	246.7
150°	205.6	213.2	219.9	225.8	231.2	235.5	237.5	237.8
152.5°	202.6	209.2	215.4	220.3	224.8	228.3	229.5	229.9
155°	198.2	203.5	208.5	212.5	215.8	218.5	219.5	219.5
157.5°	193.5	197.9	202.2	205.4	207.8	209.9	210.5	210.5
160°	190.6	194.2	197.8	200.6	202.6	204.5	204.9	204.9
162.5°	187.7	190.8	193.6	196.0	197.5	199.4	199.8	199.5
165°	183.5	185.6	187.8	189.5	190.9	192.2	191.9	191.5
167.5°	179.6	181.2	183.0	184.0	184.6	185.6	185.5	185.2
170°	177.2	178.2	179.6	180.6	181.3	181.5	181.3	181.3
172.5°	175.1	175.8	176.6	177.4	177.8	178.0	177.8	177.2
175°	172.2	172.6	173.2	173.2	173.2	173.9	173.2	172.6
177.5°	170.3	170.6	170.6	170.9	170.6	170.9	170.3	169.8
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6

(END OF REPORT)