

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332970-830

Luminaire Tested: **SA4XXRDIP-C1020D810U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332970-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D810U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6982.9 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332970-830

CATALOG NUMBER: SA4XXRDIP-C1020D810U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332970-830

CATALOG NUMBER: SA4XXRDIP-C1020D810U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56																			
1	100	95	91	88	92	89	86	83	77	74	72	66	64	62	55	54	53	48																			
2	91	84	77	72	84	78	73	68	68	64	60	58	55	52	49	47	45	41																			
3	83	74	66	61	77	69	62	57	60	55	51	51	48	45	44	41	39	35																			
4	76	65	58	52	71	61	54	49	53	48	44	46	42	38	39	36	34	30																			
5	70	58	50	44	65	55	48	42	48	42	38	41	37	34	35	32	29	26																			
6	65	53	44	39	60	49	42	37	43	37	33	38	33	30	32	29	26	23																			
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23	21																			
8	56	43	36	30	52	41	34	29	36	30	26	31	27	24	27	24	21	19																			
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	22	19	17																			
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P332970-830

CATALOG NUMBER: SA4XXRDIP-C1020D810U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	2.3
10°-20°	445.8	6.4
20°-30°	643.8	9.2
30°-40°	729.7	10.5
40°-50°	704.7	10.1
50°-60°	586.0	8.4
60°-70°	404.6	5.8
70°-80°	205.1	2.9
80°-90°	55.5	0.8
90°-100°	33.7	0.5
100°-110°	214.9	3.1
110°-120°	411.0	5.9
120°-130°	521.8	7.5
130°-140°	558.3	8.0
140°-150°	522.1	7.5
150°-160°	421.0	6.0
160°-170°	271.5	3.9
170°-180°	93.6	1.3
0°-30°	1249.5	17.9
0°-40°	1979.2	28.3
0°-60°	3269.8	46.8
0°-90°	3935.0	56.4
90°-120°	659.6	9.4
90°-150°	2261.8	32.4
90°-180°	3048.0	43.6
0°-180°	6982.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	2	10	16	20	22	5
95°	40	17	16	20	21	52
105°	222	226	230	235	210	232
115°	414	416	416	417	417	407
125°	582	585	584	586	587	520
135°	722	722	724	726	727	556
145°	833	835	835	836	837	520
155°	913	914	912	914	912	421
165°	963	960	960	965	959	272
175°	985	981	982	987	979	94
180°	985	985	985	985	985	



TEST NUMBER: P332970-830

CATALOG NUMBER: SA4XXRDIP-C1020D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.4	22.9	21.4	20.0	18.5	17.7	17.7	17.8	17.8	17.8	17.8
90°	2.2	4.1	5.8	7.6	9.4	10.9	12.3	13.6	14.9	16.2	17.2
92.5°	9.3	9.4	9.5	9.6	9.7	10.4	11.7	13.0	14.3	15.6	16.6
95°	40.5	35.0	29.4	23.8	18.3	15.6	15.7	15.9	16.0	16.2	17.2
97.5°	86.1	89.5	93.0	96.5	100.0	92.6	74.3	56.0	37.7	19.4	19.5
100°	120.8	123.9	126.8	129.7	132.6	122.8	100.2	77.7	55.0	32.4	29.6
102.5°	159.8	161.9	164.1	166.3	168.4	168.1	165.0	162.1	159.2	156.3	126.2
105°	221.8	222.8	223.8	224.8	225.7	226.7	227.4	228.3	229.1	229.9	231.4
107.5°	279.5	279.9	280.4	281.0	281.4	282.2	283.3	284.5	285.6	286.7	287.4
110°	318.4	318.9	319.3	319.8	320.4	321.0	322.1	323.0	324.0	325.0	325.4



TEST NUMBER: P332970-830

CATALOG NUMBER: SA4XXRDIP-C1020D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.1	356.9	357.9	358.7	359.7	360.3	360.8	361.2	361.7	362.1	362.1
115°	414.2	414.6	415.2	415.7	416.1	416.3	416.1	415.9	415.8	415.7	415.9
117.5°	466.5	467.1	467.8	468.4	469.1	469.7	470.0	470.3	470.7	471.1	471.0
120°	501.9	502.6	503.2	503.9	504.4	504.7	504.5	504.4	504.3	504.1	504.4
122.5°	534.9	535.3	535.6	536.0	536.5	536.8	537.0	537.2	537.4	537.7	537.9
125°	582.2	582.9	583.5	584.2	584.8	584.9	584.7	584.4	584.0	583.7	584.2
127.5°	627.0	627.2	627.4	627.5	627.6	628.1	628.9	629.6	630.4	631.1	631.0
130°	655.9	656.1	656.2	656.4	656.6	656.9	657.3	657.9	658.4	658.8	659.0
132.5°	682.4	682.7	683.1	683.3	683.6	684.1	684.7	685.3	685.9	686.5	686.7
135°	722.3	722.1	721.9	721.7	721.6	721.8	722.5	723.1	723.8	724.4	724.7
137.5°	757.4	757.5	757.6	757.6	757.7	758.1	758.8	759.6	760.3	761.0	761.4
140°	780.4	780.8	781.1	781.5	781.7	782.1	782.4	782.8	783.1	783.3	783.9
142.5°	801.1	801.6	802.3	802.9	803.4	803.8	804.0	804.3	804.5	804.6	805.0
145°	832.7	833.3	833.8	834.2	834.7	835.0	835.0	835.0	835.0	835.0	835.2
147.5°	858.0	858.9	859.8	860.7	861.7	862.0	861.9	861.7	861.5	861.4	861.5
150°	876.3	876.9	877.6	878.3	878.8	879.1	878.9	878.8	878.6	878.4	878.4
152.5°	891.6	892.1	892.6	893.2	893.7	893.8	893.5	893.2	892.9	892.6	892.9
155°	913.1	913.2	913.4	913.6	913.8	913.6	913.1	912.6	912.1	911.6	912.3
157.5°	931.2	931.1	931.0	930.9	930.9	930.5	929.9	929.4	928.9	928.3	929.2
160°	941.9	941.3	940.8	940.4	939.9	939.5	939.4	939.2	939.1	938.9	939.9
162.5°	951.3	950.6	950.0	949.4	948.8	948.4	948.2	948.1	947.9	947.7	948.8
165°	963.2	962.4	961.6	960.7	960.0	959.5	959.5	959.5	959.5	959.5	960.8
167.5°	972.6	971.8	970.9	970.1	969.2	968.7	968.7	968.6	968.5	968.4	969.8
170°	978.0	976.9	976.0	975.0	974.0	973.6	973.7	973.9	974.1	974.3	975.5
172.5°	981.5	980.5	979.5	978.5	977.6	977.1	977.3	977.5	977.6	977.8	979.1
175°	985.3	984.3	983.4	982.4	981.4	981.0	981.2	981.3	981.5	981.7	983.1
177.5°	987.1	986.2	985.2	984.3	983.4	983.1	983.4	983.6	983.9	984.1	985.1
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3



TEST NUMBER: P332970-830

CATALOG NUMBER: SA4XXRDIP-C1020D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	17.8	17.7	17.7	17.8	18.1	18.4	18.8	19.0
90°	18.2	19.1	20.2	20.8	21.1	21.5	21.8	22.1
92.5°	17.6	18.6	19.5	20.1	20.2	20.2	20.3	20.4
95°	18.2	19.1	20.2	20.7	20.9	21.0	21.2	21.4
97.5°	19.7	19.8	19.9	20.0	20.2	20.3	20.5	20.6
100°	26.9	24.0	21.3	20.0	20.2	20.3	20.5	20.6
102.5°	96.1	66.2	36.1	21.1	21.1	21.1	21.2	21.2
105°	232.9	234.3	235.8	233.7	227.7	221.8	215.9	210.0
107.5°	288.1	288.8	289.5	290.2	290.9	291.4	292.1	292.8
110°	325.6	326.0	326.3	326.7	327.3	327.7	328.2	328.7



TEST NUMBER: P332970-830

CATALOG NUMBER: SA4XXRDIP-C1020D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	362.0	361.9	361.8	362.1	362.8	363.4	364.0	364.7
115°	416.3	416.6	417.0	417.2	417.2	417.2	417.2	417.2
117.5°	470.9	470.9	470.8	470.7	470.7	470.6	470.5	470.5
120°	504.7	505.1	505.4	505.4	505.1	504.7	504.4	504.1
122.5°	538.1	538.3	538.5	538.4	538.1	537.7	537.4	537.1
125°	584.7	585.1	585.6	586.0	586.2	586.3	586.4	586.6
127.5°	630.9	630.8	630.7	630.7	630.5	630.4	630.3	630.1
130°	659.2	659.3	659.5	659.6	659.6	659.6	659.6	659.6
132.5°	686.9	687.0	687.2	687.2	687.1	686.9	686.8	686.7
135°	725.1	725.4	725.8	726.0	726.4	726.7	727.1	727.4
137.5°	761.7	762.0	762.4	762.5	762.4	762.3	762.2	762.1
140°	784.4	784.9	785.3	785.7	785.9	786.0	786.2	786.4
142.5°	805.3	805.7	806.1	806.3	806.3	806.3	806.3	806.3
145°	835.3	835.5	835.7	835.8	836.2	836.5	836.9	837.2
147.5°	861.7	861.8	861.9	862.0	862.2	862.3	862.5	862.7
150°	878.4	878.4	878.4	878.5	878.7	878.8	879.0	879.2
152.5°	893.2	893.4	893.6	893.7	893.6	893.5	893.4	893.3
155°	912.9	913.6	914.3	914.4	913.8	913.3	912.9	912.4
157.5°	930.0	930.9	931.7	931.7	930.9	930.0	929.2	928.3
160°	940.8	941.9	942.8	942.8	941.9	940.8	939.9	938.9
162.5°	949.7	950.6	951.7	951.6	950.5	949.3	948.3	947.2
165°	962.1	963.5	964.8	964.7	963.2	961.8	960.3	958.8
167.5°	971.3	972.7	974.1	974.0	972.4	970.7	969.1	967.5
170°	976.9	978.2	979.5	979.3	977.7	976.1	974.4	972.8
172.5°	980.4	981.8	983.1	982.8	981.1	979.3	977.5	975.7
175°	984.6	986.1	987.5	987.3	985.3	983.4	981.4	979.4
177.5°	986.3	987.3	988.4	988.1	986.5	985.0	983.4	981.8
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3

(END OF REPORT)